

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640883

Luminaire Tested: GWS-SA5E-827-U-AFL-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5E-827-U-AFL-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND
AUTOMOTIVE FRONTLINE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (80) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25035.8 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 269.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640883
 CATALOG NUMBER: GWS-SA5E-827-U-AFL-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 14.6 fc
 Type II - Short - N/A

REPORT NUMBER: P640883
CATALOG NUMBER: GWS-SA5E-827-U-AFL-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 51-Deg Lateral - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P640883

CATALOG NUMBER: GWS-SA5E-827-U-AFL-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4878.0 | 0.0 | 4878.0 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 20157.8 | 0.0 | 20157.8 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 25035.8 | 0.0 | 25035.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 695.6 | 2.8 |
| 10°-20° | 1807.4 | 7.2 |
| 20°-30° | 2938.8 | 11.7 |
| 30°-40° | 4657.3 | 18.6 |
| 40°-50° | 7024.2 | 28.1 |
| 50°-60° | 6076.5 | 24.3 |
| 60°-70° | 1377.6 | 5.5 |
| 70°-80° | 406.2 | 1.6 |
| 80°-90° | 52.3 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 25035.8 | 100.0 |
| 0°-180° | 25035.8 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P640883

CATALOG NUMBER: GWS-SA5E-827-U-AFL-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 3736.7 | 14.9 | | | |
| FM (30°-60°) | 15317.3 | 61.2 | | | |
| FH (60°-80°) | 1084.1 | 4.3 | | | G1/1800 |
| FVH (80°-90°) | 19.7 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1705.1 | 6.8 | B3/2500 | | |
| BM (30°-60°) | 2440.6 | 9.7 | B2/2500 | | |
| BH (60°-80°) | 699.6 | 2.8 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 32.6 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2
 Type II Short





REPORT NUMBER: P640883

CATALOG NUMBER: GWS-SA5E-827-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 51° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 |
| 2.5° | 8307.1 | 8354.6 | 8281.4 | 8253.7 | 8208.2 | 8129.0 | 8038.0 | 8012.3 | 7816.4 | 7687.9 | 7543.4 |
| 5° | 9141.9 | 9167.7 | 9108.3 | 9049.0 | 8936.2 | 8795.7 | 8619.7 | 8582.1 | 8226.0 | 7931.2 | 7624.5 |
| 7.5° | 9327.9 | 9318.0 | 9369.4 | 9403.1 | 9389.2 | 9333.8 | 9177.5 | 9104.3 | 8679.0 | 8212.1 | 7759.1 |
| 10° | 8592.0 | 8536.6 | 8726.5 | 8952.0 | 9223.0 | 9535.6 | 9517.8 | 9511.9 | 9141.9 | 8590.0 | 7931.2 |
| 12.5° | 7616.6 | 7588.9 | 7743.2 | 8026.1 | 8538.5 | 9231.0 | 9490.1 | 9691.9 | 9559.4 | 8950.0 | 8123.1 |
| 15° | 7058.7 | 7048.8 | 7153.7 | 7357.5 | 7765.0 | 8639.4 | 9193.4 | 9593.0 | 9917.4 | 9335.8 | 8326.9 |
| 17.5° | 6957.8 | 6963.8 | 6999.4 | 7116.1 | 7408.9 | 8129.0 | 8770.0 | 9327.9 | 10196.4 | 9759.2 | 8582.1 |
| 20° | 7252.6 | 7292.2 | 7230.9 | 7248.7 | 7406.9 | 7945.0 | 8481.2 | 9060.8 | 10374.4 | 10184.5 | 8857.1 |
| 22.5° | 7907.4 | 7893.6 | 7759.1 | 7679.9 | 7681.9 | 8057.8 | 8449.5 | 8936.2 | 10491.2 | 10598.0 | 9106.3 |
| 25° | 8649.3 | 8633.5 | 8473.3 | 8297.2 | 8186.4 | 8364.4 | 8677.0 | 9068.7 | 10596.0 | 10975.9 | 9306.1 |
| 27.5° | 9525.7 | 9476.3 | 9298.2 | 9072.7 | 8827.4 | 8904.5 | 9116.2 | 9426.8 | 10758.2 | 11347.8 | 9438.7 |
| 30° | 10374.4 | 10431.8 | 10176.6 | 9909.5 | 9650.4 | 9602.9 | 9725.5 | 10006.5 | 11088.6 | 11783.0 | 9597.0 |
| 32.5° | 11500.1 | 11480.3 | 11197.4 | 10849.2 | 10479.3 | 10443.7 | 10540.6 | 10797.8 | 11682.1 | 12384.4 | 9838.3 |
| 35° | 12863.2 | 12867.2 | 12465.6 | 11994.7 | 11468.5 | 11373.5 | 11535.7 | 11785.0 | 12566.5 | 13199.5 | 10220.1 |
| 37.5° | 14279.7 | 14273.8 | 13923.6 | 13389.4 | 12671.3 | 12536.8 | 12722.7 | 12908.7 | 13672.3 | 14309.4 | 10813.6 |
| 40° | 15272.8 | 15312.4 | 15148.2 | 14867.3 | 14186.7 | 13858.3 | 14022.5 | 14151.1 | 14875.2 | 15615.1 | 11595.1 |
| 42.5° | 15836.7 | 15896.0 | 15931.6 | 16099.8 | 15741.7 | 15391.5 | 15332.2 | 15399.4 | 15949.4 | 16827.8 | 12329.1 |
| 45° | 15957.3 | 16036.5 | 16295.6 | 16918.8 | 17057.3 | 16958.4 | 16764.5 | 16602.3 | 16750.7 | 17688.4 | 12809.8 |
| 47.5° | 15425.2 | 15563.6 | 16117.6 | 17207.7 | 18016.8 | 18327.4 | 18111.8 | 17864.5 | 17213.6 | 17910.0 | 12760.3 |
| 50° | 13316.2 | 13478.5 | 14726.8 | 16618.1 | 18153.3 | 19284.9 | 19304.7 | 18938.7 | 17158.2 | 17271.0 | 12139.1 |
| 52.5° | 10542.6 | 10653.4 | 11367.6 | 14087.8 | 16814.0 | 19245.3 | 20036.7 | 19645.0 | 16891.1 | 16471.7 | 11361.6 |
| 55° | 6301.0 | 6479.1 | 7145.8 | 9294.3 | 13098.6 | 17057.3 | 18742.8 | 18932.8 | 16760.5 | 15801.0 | 10831.4 |
| 57.5° | 2126.7 | 2213.8 | 2850.8 | 4105.1 | 7719.5 | 12489.3 | 14481.5 | 15253.0 | 15215.5 | 14776.3 | 9796.8 |
| 60° | 1012.9 | 1032.7 | 1161.3 | 1557.0 | 3090.2 | 6526.6 | 8572.2 | 9462.4 | 10273.5 | 10354.7 | 6095.3 |
| 62.5° | 771.6 | 783.4 | 848.7 | 933.8 | 1242.4 | 2749.9 | 3929.0 | 4609.5 | 4924.1 | 4225.7 | 2219.7 |
| 65° | 644.9 | 654.8 | 704.3 | 757.7 | 844.8 | 1191.0 | 1507.5 | 1739.0 | 1566.8 | 1220.6 | 1058.4 |
| 67.5° | 538.1 | 546.0 | 583.6 | 641.0 | 700.3 | 797.3 | 836.8 | 860.6 | 902.1 | 1012.9 | 973.3 |
| 70° | 421.4 | 429.3 | 468.9 | 518.3 | 575.7 | 599.4 | 637.0 | 660.8 | 743.9 | 886.3 | 882.3 |
| 72.5° | 324.4 | 334.3 | 356.1 | 387.8 | 435.2 | 459.0 | 500.5 | 528.2 | 575.7 | 690.4 | 737.9 |
| 75° | 237.4 | 243.3 | 263.1 | 273.0 | 278.9 | 273.0 | 314.6 | 346.2 | 409.5 | 453.0 | 464.9 |
| 77.5° | 96.9 | 108.8 | 104.9 | 104.9 | 124.6 | 150.4 | 172.1 | 191.9 | 235.4 | 261.1 | 263.1 |
| 80° | 39.6 | 43.5 | 51.4 | 57.4 | 69.2 | 89.0 | 102.9 | 110.8 | 130.6 | 146.4 | 158.3 |
| 82.5° | 23.7 | 25.7 | 29.7 | 31.7 | 39.6 | 51.4 | 59.4 | 65.3 | 81.1 | 96.9 | 102.9 |
| 85° | 11.9 | 11.9 | 13.8 | 15.8 | 19.8 | 23.7 | 27.7 | 31.7 | 41.5 | 51.4 | 57.4 |
| 87.5° | 2.0 | 2.0 | 2.0 | 4.0 | 5.9 | 7.9 | 9.9 | 11.9 | 13.8 | 15.8 | 19.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640883

CATALOG NUMBER: GWS-SA5E-827-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 | 7454.4 |
| 2.5° | 7458.4 | 7351.5 | 7226.9 | 7128.0 | 7013.2 | 6928.2 | 6807.5 | 6732.3 | 6661.1 | 6601.7 | 6558.2 |
| 5° | 7466.3 | 7286.2 | 7027.1 | 6797.6 | 6560.2 | 6334.7 | 6103.2 | 5915.3 | 5747.1 | 5606.6 | 5594.8 |
| 7.5° | 7511.8 | 7252.6 | 6847.1 | 6445.5 | 5982.5 | 5535.4 | 5088.3 | 4724.3 | 4447.3 | 4302.9 | 4273.2 |
| 10° | 7588.9 | 7248.7 | 6663.1 | 6022.1 | 5232.7 | 4512.6 | 3982.4 | 3705.4 | 3545.2 | 3487.8 | 3468.0 |
| 12.5° | 7670.0 | 7238.8 | 6427.6 | 5424.6 | 4328.6 | 3697.5 | 3406.7 | 3373.1 | 3402.8 | 3406.7 | 3404.7 |
| 15° | 7769.0 | 7232.8 | 6130.9 | 4724.3 | 3667.9 | 3319.7 | 3339.4 | 3410.7 | 3479.9 | 3495.7 | 3495.7 |
| 17.5° | 7889.6 | 7219.0 | 5727.3 | 4039.8 | 3254.4 | 3246.5 | 3351.3 | 3446.3 | 3511.6 | 3523.4 | 3523.4 |
| 20° | 8016.3 | 7183.4 | 5230.7 | 3481.9 | 3086.2 | 3201.0 | 3313.7 | 3386.9 | 3432.4 | 3448.3 | 3450.2 |
| 22.5° | 8103.3 | 7088.4 | 4659.0 | 3068.4 | 2981.4 | 3113.9 | 3195.0 | 3270.2 | 3270.2 | 3230.6 | 3218.8 |
| 25° | 8121.1 | 6884.6 | 4039.8 | 2785.5 | 2856.7 | 2979.4 | 3062.5 | 3019.0 | 2937.8 | 2906.2 | 2904.2 |
| 27.5° | 8055.8 | 6587.9 | 3428.5 | 2583.7 | 2706.4 | 2829.0 | 2815.2 | 2751.9 | 2716.3 | 2684.6 | 2696.5 |
| 30° | 7976.7 | 6231.8 | 2898.3 | 2417.5 | 2532.3 | 2653.0 | 2605.5 | 2583.7 | 2558.0 | 2522.4 | 2530.3 |
| 32.5° | 7923.3 | 5834.1 | 2490.7 | 2288.9 | 2415.6 | 2435.3 | 2469.0 | 2467.0 | 2443.3 | 2376.0 | 2372.0 |
| 35° | 7939.1 | 5432.5 | 2217.7 | 2184.1 | 2318.6 | 2310.7 | 2374.0 | 2362.1 | 2197.9 | 2105.0 | 2099.0 |
| 37.5° | 8065.7 | 5046.8 | 2057.5 | 2101.0 | 2164.3 | 2213.8 | 2269.2 | 2126.7 | 2069.3 | 2010.0 | 2014.0 |
| 40° | 8307.1 | 4688.7 | 1970.4 | 2055.5 | 2071.3 | 2144.5 | 2015.9 | 2014.0 | 1988.2 | 1934.8 | 1932.8 |
| 42.5° | 8580.1 | 4386.0 | 1911.1 | 2033.7 | 2012.0 | 2025.8 | 1889.3 | 1905.1 | 1903.2 | 1869.5 | 1859.6 |
| 45° | 8746.3 | 4107.0 | 1863.6 | 1952.6 | 1958.6 | 1820.1 | 1778.5 | 1796.3 | 1806.2 | 1788.4 | 1786.4 |
| 47.5° | 8574.2 | 3786.6 | 1814.1 | 1828.0 | 1879.4 | 1727.1 | 1675.7 | 1677.6 | 1695.4 | 1697.4 | 1689.5 |
| 50° | 8091.4 | 3428.5 | 1754.8 | 1721.2 | 1687.5 | 1630.2 | 1582.7 | 1572.8 | 1590.6 | 1608.4 | 1614.3 |
| 52.5° | 7468.3 | 3086.2 | 1655.9 | 1604.4 | 1525.3 | 1525.3 | 1503.5 | 1471.9 | 1495.6 | 1519.4 | 1527.3 |
| 55° | 7011.3 | 2833.0 | 1515.4 | 1458.0 | 1371.0 | 1400.7 | 1396.7 | 1369.0 | 1400.7 | 1418.5 | 1424.4 |
| 57.5° | 6075.5 | 2277.1 | 1333.4 | 1315.6 | 1242.4 | 1278.0 | 1285.9 | 1250.3 | 1234.5 | 1238.4 | 1244.4 |
| 60° | 3606.5 | 1469.9 | 1202.8 | 1200.9 | 1135.6 | 1177.1 | 1200.9 | 1165.2 | 1117.8 | 1123.7 | 1131.6 |
| 62.5° | 1618.3 | 1123.7 | 1038.6 | 1030.7 | 1028.7 | 1082.2 | 1107.9 | 1074.2 | 1007.0 | 1012.9 | 1020.8 |
| 65° | 1018.8 | 971.4 | 902.1 | 902.1 | 933.8 | 979.3 | 999.1 | 971.4 | 894.2 | 884.3 | 892.2 |
| 67.5° | 945.6 | 904.1 | 832.9 | 819.0 | 834.9 | 872.5 | 874.4 | 821.0 | 775.5 | 767.6 | 767.6 |
| 70° | 848.7 | 817.1 | 747.8 | 720.1 | 714.2 | 712.2 | 706.3 | 692.4 | 662.7 | 654.8 | 658.8 |
| 72.5° | 702.3 | 680.6 | 637.0 | 607.4 | 591.5 | 589.5 | 565.8 | 553.9 | 528.2 | 524.3 | 522.3 |
| 75° | 464.9 | 470.8 | 470.8 | 466.9 | 453.0 | 447.1 | 421.4 | 409.5 | 379.8 | 368.0 | 366.0 |
| 77.5° | 275.0 | 280.9 | 288.8 | 290.8 | 288.8 | 288.8 | 265.1 | 251.2 | 221.6 | 205.7 | 201.8 |
| 80° | 168.2 | 172.1 | 176.1 | 182.0 | 174.1 | 168.2 | 146.4 | 132.5 | 118.7 | 108.8 | 106.8 |
| 82.5° | 108.8 | 112.8 | 114.7 | 118.7 | 114.7 | 106.8 | 89.0 | 81.1 | 71.2 | 63.3 | 61.3 |
| 85° | 61.3 | 63.3 | 67.3 | 67.3 | 61.3 | 55.4 | 45.5 | 39.6 | 33.6 | 29.7 | 29.7 |
| 87.5° | 21.8 | 21.8 | 21.8 | 23.7 | 19.8 | 17.8 | 11.9 | 7.9 | 5.9 | 5.9 | 5.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)