

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643372

Luminaire Tested: GWS-SA6E-827-U-SL4-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGE-827-U-SL4-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: (96) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25928 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 323.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643372
 CATALOG NUMBER: GWS-SA6E-827-U-SL4-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P643372
CATALOG NUMBER: GWS-SA6E-827-U-SL4-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P643372
 CATALOG NUMBER: GWS-SA6E-827-U-SL4-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2120.3 | 0.0 | 2120.3 |
| | % Fixture | 8.2 | 0.0 | 8.2 |
| Street Side | Lumens | 23807.7 | 0.0 | 23807.7 |
| | % Fixture | 91.8 | 0.0 | 91.8 |
| Total | Lumens | 25928.0 | 0.0 | 25928.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 371.9 | 1.4 |
| 10°-20° | 943.1 | 3.6 |
| 20°-30° | 1578.5 | 6.1 |
| 30°-40° | 2479.2 | 9.6 |
| 40°-50° | 3921.5 | 15.1 |
| 50°-60° | 5720.5 | 22.1 |
| 60°-70° | 7091.3 | 27.4 |
| 70°-80° | 3587.8 | 13.8 |
| 80°-90° | 234.2 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 25928.0 | 100.0 |
| 0°-180° | 25928.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P643372


CATALOG NUMBER: GWS-SA6E-827-U-SL4-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 2216.4 | 8.5 | | | |
| FM (30°-60°) | 10995.8 | 42.4 | | | |
| FH (60°-80°) | 10376.8 | 40.0 | | | G4/12000 |
| FVH (80°-90°) | 218.8 | 0.8 | | | G2/225 |
| BL (0°-30°) | 677.1 | 2.6 | B2/1000 | | |
| BM (30°-60°) | 1125.4 | 4.3 | B2/2500 | | |
| BH (60°-80°) | 302.3 | 1.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 15.5 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G4

Type IV Short





REPORT NUMBER: P643372

CATALOG NUMBER: GWS-SA6E-827-U-SL4-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 40° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 |
| 2.5° | 4729.9 | 4746.5 | 4744.1 | 4751.2 | 4734.7 | 4708.7 | 4704.0 | 4668.6 | 4604.9 | 4524.7 | 4435.1 |
| 5° | 4826.7 | 4845.5 | 4831.4 | 4824.3 | 4793.6 | 4765.3 | 4758.2 | 4720.5 | 4647.4 | 4538.9 | 4383.2 |
| 7.5° | 4909.2 | 4913.9 | 4904.5 | 4888.0 | 4843.2 | 4805.4 | 4779.5 | 4727.6 | 4640.3 | 4531.8 | 4352.5 |
| 10° | 4923.4 | 4921.0 | 4925.7 | 4928.1 | 4899.8 | 4866.8 | 4845.5 | 4774.8 | 4663.9 | 4548.3 | 4354.8 |
| 12.5° | 4906.9 | 4906.9 | 4937.5 | 4972.9 | 4972.9 | 4956.4 | 4935.2 | 4871.5 | 4741.7 | 4604.9 | 4402.0 |
| 15° | 4928.1 | 4935.2 | 4994.2 | 5060.2 | 5081.4 | 5064.9 | 5055.5 | 4989.4 | 4855.0 | 4704.0 | 4487.0 |
| 17.5° | 5003.6 | 5010.7 | 5105.0 | 5204.1 | 5230.1 | 5211.2 | 5192.3 | 5126.3 | 4982.4 | 4817.2 | 4583.7 |
| 20° | 5114.5 | 5133.3 | 5253.7 | 5381.0 | 5404.6 | 5381.0 | 5343.3 | 5251.3 | 5107.4 | 4939.9 | 4675.7 |
| 22.5° | 5317.4 | 5329.1 | 5458.9 | 5593.4 | 5605.2 | 5567.4 | 5510.8 | 5383.4 | 5232.4 | 5069.6 | 4779.5 |
| 25° | 5586.3 | 5602.8 | 5732.5 | 5862.3 | 5831.6 | 5775.0 | 5697.2 | 5553.3 | 5381.0 | 5223.0 | 4911.6 |
| 27.5° | 5907.1 | 5926.0 | 6053.4 | 6166.6 | 6086.4 | 6020.4 | 5933.1 | 5753.8 | 5579.2 | 5435.3 | 5081.4 |
| 30° | 6253.9 | 6270.4 | 6383.7 | 6485.1 | 6378.9 | 6301.1 | 6197.3 | 6013.3 | 5836.3 | 5727.8 | 5322.1 |
| 32.5° | 6588.9 | 6586.5 | 6695.0 | 6777.6 | 6669.1 | 6607.8 | 6513.4 | 6327.0 | 6185.5 | 6138.3 | 5680.6 |
| 35° | 6900.3 | 6900.3 | 6989.9 | 7072.5 | 6994.7 | 6961.6 | 6874.3 | 6725.7 | 6645.5 | 6702.1 | 6159.5 |
| 37.5° | 7214.0 | 7197.5 | 7282.5 | 7374.5 | 7367.4 | 7369.7 | 7320.2 | 7249.4 | 7254.1 | 7454.7 | 6817.7 |
| 40° | 7473.5 | 7466.5 | 7565.5 | 7685.9 | 7780.2 | 7855.7 | 7825.0 | 7851.0 | 7999.6 | 8374.7 | 7659.9 |
| 42.5° | 7681.1 | 7697.7 | 7825.0 | 8016.1 | 8254.4 | 8407.7 | 8429.0 | 8535.1 | 8917.3 | 9497.6 | 8610.6 |
| 45° | 7919.4 | 7921.8 | 8098.7 | 8391.2 | 8771.0 | 9014.0 | 9098.9 | 9372.6 | 9915.2 | 10663.0 | 9653.3 |
| 47.5° | 8211.9 | 8183.6 | 8381.8 | 8792.3 | 9341.9 | 9700.5 | 9851.5 | 10193.6 | 11033.4 | 11800.1 | 10502.6 |
| 50° | 8535.1 | 8483.2 | 8707.3 | 9266.4 | 9981.2 | 10429.5 | 10736.1 | 11236.3 | 12142.1 | 12734.3 | 11134.8 |
| 52.5° | 8910.2 | 8860.7 | 9115.5 | 9811.4 | 10747.9 | 11292.9 | 11686.8 | 12191.7 | 13092.9 | 13446.7 | 11512.3 |
| 55° | 9386.8 | 9337.2 | 9606.1 | 10464.8 | 11653.8 | 12361.5 | 12774.4 | 13199.0 | 13977.5 | 13972.8 | 11785.9 |
| 57.5° | 9915.2 | 9846.8 | 10219.5 | 11290.5 | 12783.8 | 13519.8 | 13939.8 | 14147.4 | 14649.8 | 14380.9 | 11969.9 |
| 60° | 10521.5 | 10460.1 | 10976.8 | 12274.3 | 14088.4 | 14770.2 | 15034.4 | 14949.4 | 15201.9 | 14621.5 | 11906.2 |
| 62.5° | 11068.8 | 11040.5 | 11682.1 | 13317.0 | 15331.6 | 15907.2 | 15980.4 | 15610.0 | 15607.6 | 14626.3 | 11476.9 |
| 65° | 11637.3 | 11691.6 | 12644.6 | 14517.7 | 16581.9 | 16968.8 | 16843.8 | 16265.8 | 15770.4 | 14048.3 | 10207.7 |
| 67.5° | 11849.6 | 12007.7 | 13279.2 | 15602.9 | 17568.0 | 17870.0 | 17650.6 | 16593.7 | 15093.3 | 12104.4 | 7773.1 |
| 70° | 10538.0 | 10835.2 | 12680.0 | 15664.2 | 17976.1 | 18263.9 | 17737.9 | 15711.4 | 12583.3 | 8018.5 | 4258.1 |
| 72.5° | 8013.8 | 8360.6 | 10566.3 | 12826.3 | 16166.7 | 16822.5 | 15923.7 | 12800.3 | 8110.5 | 3512.7 | 1429.6 |
| 75° | 4484.6 | 4859.7 | 7869.9 | 9658.0 | 10854.1 | 11453.3 | 11123.0 | 8211.9 | 3592.9 | 917.7 | 427.0 |
| 77.5° | 1516.9 | 1641.9 | 3661.3 | 5975.5 | 7164.5 | 6626.6 | 5609.9 | 4078.8 | 1321.1 | 349.1 | 226.5 |
| 80° | 898.8 | 946.0 | 1363.5 | 2974.8 | 3769.8 | 3125.8 | 2467.6 | 1507.4 | 672.3 | 186.4 | 158.1 |
| 82.5° | 268.9 | 318.5 | 752.5 | 1104.0 | 1476.8 | 920.0 | 778.5 | 861.1 | 349.1 | 101.4 | 132.1 |
| 85° | 0.0 | 0.0 | 160.4 | 342.1 | 386.9 | 151.0 | 151.0 | 488.3 | 63.7 | 42.5 | 96.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.4 | 11.8 | 7.1 | 9.4 | 21.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643372

CATALOG NUMBER: GWS-SA6E-827-U-SL4-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 | 4399.7 |
| 2.5° | 4371.4 | 4288.8 | 4192.1 | 4100.1 | 4012.8 | 3899.5 | 3845.3 | 3779.2 | 3722.6 | 3691.9 | 3708.5 |
| 5° | 4284.1 | 4154.3 | 3956.2 | 3755.6 | 3552.8 | 3361.7 | 3189.5 | 3073.9 | 2970.1 | 2915.8 | 2927.6 |
| 7.5° | 4208.6 | 4034.0 | 3725.0 | 3397.1 | 3071.5 | 2743.6 | 2477.0 | 2269.4 | 2109.0 | 2043.0 | 2031.2 |
| 10° | 4175.6 | 3956.2 | 3519.7 | 3047.9 | 2547.8 | 2106.7 | 1729.2 | 1500.4 | 1337.6 | 1257.4 | 1271.5 |
| 12.5° | 4192.1 | 3916.1 | 3345.2 | 2705.9 | 2057.1 | 1542.8 | 1181.9 | 967.2 | 851.6 | 804.4 | 792.6 |
| 15° | 4239.3 | 3906.6 | 3189.5 | 2356.7 | 1587.7 | 1078.1 | 816.2 | 729.0 | 705.4 | 700.6 | 700.6 |
| 17.5° | 4293.5 | 3909.0 | 3029.0 | 2002.9 | 1205.5 | 799.7 | 698.3 | 681.8 | 674.7 | 670.0 | 672.3 |
| 20° | 4347.8 | 3909.0 | 2845.0 | 1644.3 | 905.9 | 691.2 | 665.3 | 653.5 | 646.4 | 644.0 | 644.0 |
| 22.5° | 4413.8 | 3909.0 | 2639.8 | 1311.6 | 726.6 | 655.8 | 634.6 | 627.5 | 620.4 | 618.1 | 615.7 |
| 25° | 4494.0 | 3911.3 | 2413.3 | 1026.2 | 660.5 | 625.2 | 608.6 | 601.6 | 594.5 | 589.8 | 589.8 |
| 27.5° | 4609.6 | 3930.2 | 2163.3 | 799.7 | 622.8 | 596.8 | 582.7 | 575.6 | 568.5 | 561.5 | 561.5 |
| 30° | 4777.1 | 3977.4 | 1882.5 | 660.5 | 587.4 | 566.2 | 552.0 | 547.3 | 540.2 | 533.2 | 530.8 |
| 32.5° | 5027.2 | 4060.0 | 1592.4 | 592.1 | 554.4 | 533.2 | 516.6 | 511.9 | 504.8 | 497.8 | 495.4 |
| 35° | 5376.3 | 4210.9 | 1309.3 | 549.7 | 511.9 | 490.7 | 481.3 | 478.9 | 469.5 | 462.4 | 462.4 |
| 37.5° | 5888.2 | 4456.3 | 1038.0 | 507.2 | 476.5 | 460.0 | 448.2 | 443.5 | 434.1 | 427.0 | 424.6 |
| 40° | 6513.4 | 4774.8 | 806.8 | 474.2 | 443.5 | 427.0 | 415.2 | 408.1 | 396.3 | 386.9 | 382.2 |
| 42.5° | 7310.8 | 5164.0 | 636.9 | 438.8 | 412.8 | 396.3 | 386.9 | 372.7 | 356.2 | 342.1 | 339.7 |
| 45° | 8141.2 | 5565.1 | 526.1 | 405.8 | 384.5 | 370.4 | 358.6 | 339.7 | 316.1 | 299.6 | 294.9 |
| 47.5° | 8778.1 | 5815.1 | 460.0 | 370.4 | 353.9 | 342.1 | 327.9 | 304.3 | 276.0 | 257.1 | 252.4 |
| 50° | 9233.4 | 5852.9 | 410.5 | 337.3 | 327.9 | 316.1 | 294.9 | 266.6 | 235.9 | 217.0 | 212.3 |
| 52.5° | 9457.5 | 5683.0 | 370.4 | 306.7 | 299.6 | 287.8 | 261.9 | 231.2 | 198.2 | 179.3 | 174.6 |
| 55° | 9559.0 | 5362.2 | 332.6 | 280.7 | 271.3 | 257.1 | 228.8 | 195.8 | 162.8 | 146.3 | 141.5 |
| 57.5° | 9518.9 | 4888.0 | 299.6 | 254.8 | 243.0 | 226.5 | 195.8 | 160.4 | 134.5 | 118.0 | 115.6 |
| 60° | 9221.6 | 4222.7 | 266.6 | 228.8 | 214.7 | 195.8 | 165.1 | 132.1 | 108.5 | 96.7 | 94.4 |
| 62.5° | 8579.9 | 3397.1 | 233.5 | 198.2 | 188.7 | 169.9 | 141.5 | 108.5 | 89.6 | 82.6 | 80.2 |
| 65° | 7265.9 | 2401.5 | 200.5 | 167.5 | 162.8 | 143.9 | 118.0 | 89.6 | 77.8 | 73.1 | 70.8 |
| 67.5° | 5223.0 | 1460.3 | 169.9 | 143.9 | 139.2 | 122.7 | 99.1 | 77.8 | 70.8 | 68.4 | 68.4 |
| 70° | 2625.6 | 691.2 | 134.5 | 118.0 | 118.0 | 101.4 | 84.9 | 70.8 | 68.4 | 66.1 | 66.1 |
| 72.5° | 891.7 | 294.9 | 101.4 | 92.0 | 96.7 | 87.3 | 73.1 | 66.1 | 66.1 | 66.1 | 66.1 |
| 75° | 304.3 | 155.7 | 70.8 | 66.1 | 70.8 | 70.8 | 63.7 | 63.7 | 66.1 | 66.1 | 66.1 |
| 77.5° | 198.2 | 103.8 | 49.5 | 44.8 | 54.3 | 54.3 | 54.3 | 59.0 | 63.7 | 63.7 | 63.7 |
| 80° | 162.8 | 56.6 | 33.0 | 30.7 | 40.1 | 40.1 | 44.8 | 54.3 | 59.0 | 59.0 | 59.0 |
| 82.5° | 139.2 | 35.4 | 18.9 | 21.2 | 28.3 | 30.7 | 37.7 | 44.8 | 51.9 | 54.3 | 54.3 |
| 85° | 94.4 | 18.9 | 14.2 | 16.5 | 18.9 | 23.6 | 30.7 | 37.7 | 42.5 | 47.2 | 47.2 |
| 87.5° | 25.9 | 7.1 | 9.4 | 11.8 | 11.8 | 16.5 | 23.6 | 28.3 | 33.0 | 35.4 | 35.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)