

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631490

Luminaire Tested: GWS-SA1F-827-U-SL3-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631490
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1F-827-U-SL3-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5016.1 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 67.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P631490
 CATALOG NUMBER: GWS-SA1F-827-U-SL3-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 14.5 fc
 Type III - Short - N/A

REPORT NUMBER: P631490
CATALOG NUMBER: GWS-SA1F-827-U-SL3-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P631490
 CATALOG NUMBER: GWS-SA1F-827-U-SL3-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 490.0 | 0.0 | 490.0 |
| | % Fixture | 9.8 | 0.0 | 9.8 |
| Street Side | Lumens | 4526.1 | 0.0 | 4526.1 |
| | % Fixture | 90.2 | 0.0 | 90.2 |
| Total | Lumens | 5016.1 | 0.0 | 5016.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 117.6 | 2.3 |
| 10°-20° | 244.7 | 4.9 |
| 20°-30° | 330.1 | 6.6 |
| 30°-40° | 463.8 | 9.2 |
| 40°-50° | 716.3 | 14.3 |
| 50°-60° | 1145.4 | 22.8 |
| 60°-70° | 1356.3 | 27.0 |
| 70°-80° | 600.0 | 12.0 |
| 80°-90° | 41.9 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5016.1 | 100.0 |
| 0°-180° | 5016.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P631490


CATALOG NUMBER: GWS-SA1F-827-U-SL3-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 516.0 | 10.3 | | | |
| FM (30°-60°) | 2133.2 | 42.5 | | | |
| FH (60°-80°) | 1836.6 | 36.6 | | | G2/5000 |
| FVH (80°-90°) | 40.2 | 0.8 | | | G1/100 |
| BL (0°-30°) | 176.3 | 3.5 | B1/500 | | |
| BM (30°-60°) | 192.3 | 3.8 | B0/220 | | |
| BH (60°-80°) | 119.6 | 2.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.8 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type III Short





REPORT NUMBER: P631490

CATALOG NUMBER: GWS-SA1F-827-U-SL3-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 |
| 2.5° | 1521.9 | 1524.6 | 1528.1 | 1532.6 | 1531.7 | 1527.7 | 1522.8 | 1511.7 | 1504.6 | 1482.4 | 1455.3 |
| 5° | 1473.1 | 1472.6 | 1481.5 | 1489.9 | 1505.0 | 1513.0 | 1524.1 | 1513.9 | 1510.4 | 1483.7 | 1439.8 |
| 7.5° | 1377.6 | 1382.5 | 1392.7 | 1406.0 | 1427.8 | 1451.3 | 1478.0 | 1474.8 | 1485.5 | 1467.7 | 1413.1 |
| 10° | 1283.9 | 1281.3 | 1297.3 | 1317.2 | 1350.5 | 1380.7 | 1419.4 | 1418.9 | 1446.9 | 1445.1 | 1382.9 |
| 12.5° | 1201.8 | 1201.4 | 1213.8 | 1236.4 | 1275.5 | 1317.7 | 1370.1 | 1371.4 | 1406.0 | 1420.2 | 1357.2 |
| 15° | 1132.6 | 1133.4 | 1145.4 | 1169.0 | 1209.4 | 1260.9 | 1321.7 | 1332.8 | 1371.8 | 1400.7 | 1331.9 |
| 17.5° | 1083.3 | 1083.7 | 1090.8 | 1111.2 | 1150.8 | 1205.8 | 1279.1 | 1294.2 | 1344.3 | 1386.1 | 1311.5 |
| 20° | 1060.6 | 1058.9 | 1060.2 | 1070.4 | 1101.0 | 1151.2 | 1235.6 | 1255.1 | 1319.0 | 1375.8 | 1292.8 |
| 22.5° | 1063.7 | 1061.1 | 1054.9 | 1053.5 | 1067.3 | 1105.5 | 1189.4 | 1213.4 | 1291.5 | 1369.6 | 1276.0 |
| 25° | 1091.3 | 1085.5 | 1076.6 | 1063.3 | 1058.0 | 1077.1 | 1149.0 | 1173.8 | 1265.7 | 1370.1 | 1263.1 |
| 27.5° | 1133.4 | 1127.2 | 1116.1 | 1098.4 | 1077.5 | 1069.5 | 1121.5 | 1145.0 | 1247.5 | 1380.3 | 1256.9 |
| 30° | 1187.2 | 1182.3 | 1171.6 | 1150.3 | 1122.3 | 1089.5 | 1115.7 | 1135.2 | 1238.7 | 1401.2 | 1259.5 |
| 32.5° | 1250.6 | 1247.1 | 1238.2 | 1218.7 | 1186.7 | 1136.5 | 1135.2 | 1150.3 | 1245.8 | 1431.3 | 1269.7 |
| 35° | 1311.9 | 1313.2 | 1313.7 | 1303.0 | 1268.8 | 1208.0 | 1188.9 | 1194.3 | 1275.1 | 1476.6 | 1292.8 |
| 37.5° | 1378.1 | 1375.0 | 1390.9 | 1398.5 | 1365.6 | 1300.8 | 1272.0 | 1272.4 | 1331.0 | 1543.7 | 1336.3 |
| 40° | 1428.2 | 1429.1 | 1463.7 | 1494.8 | 1481.1 | 1418.5 | 1377.2 | 1376.7 | 1417.1 | 1635.6 | 1406.5 |
| 42.5° | 1475.3 | 1481.1 | 1532.1 | 1585.4 | 1604.5 | 1549.0 | 1519.2 | 1508.1 | 1537.9 | 1759.9 | 1511.7 |
| 45° | 1525.5 | 1533.9 | 1605.4 | 1681.3 | 1731.5 | 1698.6 | 1675.1 | 1679.5 | 1683.1 | 1904.6 | 1653.3 |
| 47.5° | 1584.1 | 1589.4 | 1677.7 | 1784.7 | 1878.4 | 1870.0 | 1871.3 | 1866.0 | 1864.2 | 2087.1 | 1840.7 |
| 50° | 1655.1 | 1667.5 | 1769.2 | 1897.1 | 2024.9 | 2080.9 | 2099.5 | 2101.7 | 2072.9 | 2286.0 | 2034.7 |
| 52.5° | 1806.0 | 1821.1 | 1908.2 | 2020.0 | 2184.7 | 2302.4 | 2378.3 | 2363.2 | 2318.8 | 2478.7 | 2247.3 |
| 55° | 1984.1 | 1995.6 | 2079.5 | 2195.4 | 2380.1 | 2545.2 | 2725.5 | 2719.3 | 2610.5 | 2681.5 | 2422.3 |
| 57.5° | 2000.9 | 2013.8 | 2143.9 | 2321.5 | 2630.9 | 2845.4 | 3034.9 | 3054.9 | 2895.5 | 2825.4 | 2578.5 |
| 60° | 1811.4 | 1837.6 | 2015.2 | 2254.0 | 2726.8 | 3248.9 | 3374.1 | 3378.1 | 3104.6 | 2971.5 | 2769.4 |
| 62.5° | 1451.8 | 1464.2 | 1643.1 | 1954.8 | 2579.0 | 3484.2 | 3892.2 | 3807.9 | 3373.2 | 3197.4 | 3071.8 |
| 65° | 761.0 | 811.6 | 967.4 | 1312.4 | 2091.5 | 3402.1 | 4515.6 | 4492.5 | 3856.3 | 3521.1 | 3307.1 |
| 67.5° | 522.1 | 521.7 | 558.5 | 684.1 | 1247.1 | 2929.3 | 4821.4 | 5075.4 | 4414.8 | 3632.1 | 3136.6 |
| 70° | 397.3 | 398.7 | 431.5 | 513.2 | 646.0 | 1949.9 | 4485.8 | 4920.0 | 4518.7 | 3297.8 | 2536.8 |
| 72.5° | 263.7 | 266.4 | 321.0 | 414.7 | 515.9 | 955.9 | 3486.0 | 3936.6 | 3802.1 | 2648.7 | 1785.6 |
| 75° | 157.6 | 159.8 | 198.9 | 301.5 | 458.6 | 535.0 | 2214.9 | 2721.5 | 2617.2 | 1825.6 | 957.2 |
| 77.5° | 64.8 | 66.6 | 102.1 | 187.8 | 335.6 | 415.6 | 1224.9 | 1780.7 | 1567.6 | 725.9 | 261.5 |
| 80° | 27.1 | 28.0 | 49.3 | 131.4 | 242.0 | 260.6 | 567.4 | 836.9 | 642.4 | 156.3 | 79.9 |
| 82.5° | 9.8 | 10.2 | 18.2 | 72.4 | 150.5 | 196.2 | 286.4 | 330.8 | 181.1 | 51.1 | 43.1 |
| 85° | 0.4 | 0.4 | 4.4 | 24.4 | 57.3 | 55.5 | 163.8 | 158.5 | 59.9 | 21.3 | 25.7 |
| 87.5° | 0.0 | 0.0 | 0.4 | 0.4 | 0.9 | 2.2 | 15.5 | 27.5 | 12.9 | 5.3 | 11.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631490
 CATALOG NUMBER: GWS-SA1F-827-U-SL3-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 | 1446.9 |
| 2.5° | 1437.6 | 1414.0 | 1388.3 | 1364.3 | 1326.1 | 1303.5 | 1275.5 | 1263.1 | 1245.3 | 1240.9 | 1243.5 |
| 5° | 1408.3 | 1367.9 | 1306.1 | 1250.2 | 1177.8 | 1119.7 | 1061.1 | 1036.2 | 1004.2 | 982.9 | 974.1 |
| 7.5° | 1367.0 | 1314.1 | 1217.8 | 1116.1 | 1016.7 | 910.6 | 829.8 | 776.5 | 728.1 | 701.5 | 696.1 |
| 10° | 1325.2 | 1256.4 | 1118.3 | 972.7 | 818.7 | 691.7 | 582.5 | 501.7 | 436.0 | 406.2 | 383.1 |
| 12.5° | 1282.2 | 1196.5 | 1017.1 | 827.1 | 648.2 | 475.0 | 340.1 | 261.5 | 214.4 | 195.8 | 198.9 |
| 15° | 1242.7 | 1138.8 | 916.8 | 681.5 | 456.4 | 286.8 | 187.8 | 158.5 | 147.4 | 143.8 | 143.4 |
| 17.5° | 1204.9 | 1084.2 | 816.9 | 539.9 | 301.0 | 175.8 | 143.8 | 136.7 | 133.6 | 131.9 | 131.9 |
| 20° | 1170.7 | 1031.8 | 719.2 | 406.7 | 194.5 | 139.4 | 130.1 | 126.5 | 123.9 | 122.5 | 122.5 |
| 22.5° | 1138.8 | 981.2 | 623.8 | 287.7 | 143.4 | 125.2 | 119.4 | 115.9 | 112.8 | 111.0 | 111.0 |
| 25° | 1109.9 | 935.4 | 532.8 | 198.0 | 123.4 | 114.5 | 108.3 | 104.3 | 99.0 | 95.9 | 95.9 |
| 27.5° | 1089.0 | 894.6 | 445.3 | 144.3 | 111.4 | 103.0 | 95.9 | 90.6 | 84.8 | 81.2 | 80.4 |
| 30° | 1076.6 | 860.0 | 356.9 | 118.5 | 100.3 | 91.9 | 83.9 | 77.2 | 70.6 | 67.0 | 66.6 |
| 32.5° | 1069.5 | 828.0 | 276.1 | 103.4 | 91.0 | 81.2 | 72.4 | 65.3 | 58.6 | 54.6 | 54.2 |
| 35° | 1072.2 | 803.1 | 206.9 | 93.2 | 82.1 | 71.9 | 62.2 | 55.1 | 49.3 | 45.7 | 44.8 |
| 37.5° | 1095.3 | 792.0 | 155.4 | 85.2 | 74.6 | 63.9 | 53.7 | 47.1 | 41.7 | 39.1 | 38.6 |
| 40° | 1140.1 | 794.3 | 122.1 | 79.0 | 68.4 | 55.9 | 46.2 | 40.0 | 36.0 | 33.7 | 33.3 |
| 42.5° | 1209.8 | 812.9 | 100.8 | 73.7 | 61.7 | 48.8 | 40.0 | 35.1 | 31.1 | 28.9 | 28.4 |
| 45° | 1313.7 | 851.5 | 87.9 | 67.5 | 54.6 | 42.2 | 34.6 | 30.2 | 26.6 | 24.0 | 23.5 |
| 47.5° | 1464.2 | 918.6 | 79.5 | 61.7 | 48.4 | 36.4 | 29.7 | 25.3 | 22.2 | 20.0 | 19.5 |
| 50° | 1624.5 | 998.9 | 72.4 | 55.9 | 43.1 | 31.5 | 25.3 | 20.9 | 18.2 | 16.0 | 15.5 |
| 52.5° | 1795.4 | 1085.5 | 67.0 | 50.6 | 38.2 | 27.1 | 21.3 | 17.3 | 14.7 | 12.4 | 12.0 |
| 55° | 1959.7 | 1172.5 | 60.8 | 47.1 | 32.4 | 23.1 | 17.8 | 14.2 | 11.5 | 9.8 | 9.8 |
| 57.5° | 2119.5 | 1252.4 | 54.2 | 41.3 | 26.6 | 19.5 | 14.7 | 11.5 | 9.3 | 8.0 | 7.5 |
| 60° | 2310.4 | 1363.0 | 46.6 | 35.1 | 22.2 | 16.4 | 12.0 | 9.3 | 7.5 | 6.2 | 6.2 |
| 62.5° | 2594.1 | 1478.0 | 40.0 | 29.3 | 18.6 | 13.8 | 9.8 | 7.5 | 6.2 | 5.3 | 4.9 |
| 65° | 2686.9 | 1415.8 | 33.7 | 24.0 | 15.1 | 11.1 | 8.0 | 6.7 | 5.3 | 4.9 | 4.4 |
| 67.5° | 2439.1 | 1160.5 | 28.0 | 19.5 | 12.4 | 9.3 | 7.1 | 5.8 | 4.9 | 4.4 | 4.0 |
| 70° | 1903.3 | 823.6 | 21.8 | 14.7 | 10.2 | 7.5 | 6.2 | 5.3 | 4.4 | 4.0 | 4.0 |
| 72.5° | 1294.6 | 487.0 | 17.3 | 11.1 | 8.4 | 6.7 | 5.3 | 4.9 | 4.4 | 4.0 | 3.6 |
| 75° | 637.5 | 173.1 | 13.3 | 8.4 | 6.7 | 5.8 | 4.9 | 4.4 | 4.0 | 3.6 | 3.6 |
| 77.5° | 171.8 | 47.9 | 10.2 | 6.7 | 5.3 | 4.4 | 4.4 | 4.4 | 4.0 | 3.1 | 3.1 |
| 80° | 58.2 | 20.0 | 7.5 | 4.9 | 4.4 | 3.6 | 3.1 | 4.0 | 3.6 | 3.1 | 2.7 |
| 82.5° | 32.0 | 9.8 | 5.3 | 4.0 | 3.1 | 2.7 | 2.7 | 2.7 | 2.7 | 2.2 | 2.2 |
| 85° | 20.4 | 5.3 | 3.6 | 3.1 | 3.1 | 2.2 | 1.8 | 1.8 | 1.3 | 1.3 | 1.3 |
| 87.5° | 9.3 | 3.1 | 3.1 | 2.7 | 2.7 | 2.2 | 1.3 | 0.9 | 0.4 | 0.4 | 0.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)