

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633969

Luminaire Tested: GWS-SA2F-827-U-SLL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2F-827-U-SLL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6394.7 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 124.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633969
 CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 17.1 fc
 Type III - Short - N/A

REPORT NUMBER: P633969
CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P633969

CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1377.6 | 0.0 | 1377.6 |
| | % Fixture | 21.5 | 0.0 | 21.5 |
| Street Side | Lumens | 5017.1 | 0.0 | 5017.1 |
| | % Fixture | 78.5 | 0.0 | 78.5 |
| Total | Lumens | 6394.7 | 0.0 | 6394.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 107.4 | 1.7 |
| 10°-20° | 353.4 | 5.5 |
| 20°-30° | 573.5 | 9.0 |
| 30°-40° | 880.2 | 13.8 |
| 40°-50° | 1405.7 | 22.0 |
| 50°-60° | 1968.2 | 30.8 |
| 60°-70° | 1009.2 | 15.8 |
| 70°-80° | 97.2 | 1.5 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 6394.7 | 100.0 |
| 0°-180° | 6394.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P633969


CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 633.1 | 9.9 | | | |
| FM (30°-60°) | 3381.7 | 52.9 | | | |
| FH (60°-80°) | 1002.3 | 15.7 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 401.1 | 6.3 | B1/500 | | |
| BM (30°-60°) | 872.4 | 13.6 | B1/1000 | | |
| BH (60°-80°) | 104.0 | 1.6 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type III Short





REPORT NUMBER: P633969

CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 |
| 2.5° | 1207.1 | 1204.5 | 1196.0 | 1166.9 | 1149.0 | 1120.7 | 1100.2 | 1073.7 | 1044.7 | 1026.7 | 1008.8 |
| 5° | 1335.3 | 1328.5 | 1305.4 | 1238.7 | 1187.4 | 1131.9 | 1087.4 | 1038.7 | 986.5 | 952.3 | 920.7 |
| 7.5° | 1458.4 | 1448.2 | 1417.4 | 1304.5 | 1226.8 | 1147.3 | 1084.0 | 1013.0 | 939.5 | 888.2 | 848.9 |
| 10° | 1579.0 | 1555.9 | 1507.2 | 1368.7 | 1263.5 | 1167.8 | 1093.4 | 1012.2 | 925.8 | 860.9 | 817.3 |
| 12.5° | 1678.1 | 1661.0 | 1594.4 | 1429.4 | 1294.3 | 1172.0 | 1080.6 | 1005.3 | 947.2 | 903.6 | 863.4 |
| 15° | 1763.6 | 1744.8 | 1681.6 | 1484.1 | 1320.8 | 1154.9 | 1026.7 | 960.9 | 970.3 | 987.4 | 953.2 |
| 17.5° | 1842.3 | 1822.6 | 1754.2 | 1529.4 | 1331.1 | 1113.1 | 951.5 | 919.9 | 972.0 | 1036.1 | 1023.3 |
| 20° | 1923.5 | 1901.3 | 1817.5 | 1566.1 | 1327.6 | 1047.2 | 875.4 | 884.8 | 958.3 | 1031.8 | 1038.7 |
| 22.5° | 2018.4 | 1995.3 | 1897.8 | 1613.2 | 1325.1 | 968.6 | 809.6 | 854.0 | 932.7 | 995.1 | 1007.1 |
| 25° | 2144.0 | 2116.7 | 2009.8 | 1682.4 | 1331.9 | 896.8 | 762.6 | 824.1 | 889.1 | 945.5 | 952.3 |
| 27.5° | 2309.9 | 2274.8 | 2138.9 | 1767.9 | 1346.4 | 840.3 | 742.0 | 783.1 | 833.5 | 883.9 | 889.9 |
| 30° | 2526.2 | 2481.7 | 2286.8 | 1842.3 | 1339.6 | 801.0 | 728.4 | 742.0 | 772.0 | 813.0 | 813.8 |
| 32.5° | 2779.2 | 2718.5 | 2452.7 | 1906.4 | 1280.6 | 772.0 | 709.6 | 700.1 | 707.0 | 738.6 | 744.6 |
| 35° | 3076.7 | 2998.1 | 2635.6 | 1967.1 | 1172.9 | 715.5 | 675.4 | 643.7 | 641.2 | 656.5 | 671.1 |
| 37.5° | 3417.8 | 3323.8 | 2866.4 | 2044.9 | 1045.5 | 656.5 | 624.9 | 593.3 | 579.6 | 587.3 | 609.5 |
| 40° | 3732.4 | 3628.1 | 3107.5 | 2138.9 | 915.6 | 603.5 | 565.9 | 533.4 | 517.2 | 519.8 | 547.1 |
| 42.5° | 4101.7 | 3994.0 | 3402.4 | 2262.0 | 807.9 | 567.6 | 504.4 | 471.0 | 449.7 | 461.6 | 493.3 |
| 45° | 4662.5 | 4540.3 | 3832.4 | 2368.9 | 722.4 | 559.1 | 450.5 | 403.5 | 393.2 | 413.8 | 451.4 |
| 47.5° | 5428.5 | 5278.9 | 4423.2 | 2433.8 | 649.7 | 566.8 | 412.9 | 348.8 | 351.4 | 374.4 | 412.1 |
| 50° | 6188.5 | 6026.9 | 5106.2 | 2348.4 | 589.9 | 551.4 | 394.1 | 306.0 | 322.3 | 342.8 | 377.0 |
| 52.5° | 6710.8 | 6500.5 | 5438.8 | 2101.3 | 535.2 | 493.3 | 392.4 | 265.9 | 296.6 | 303.5 | 332.5 |
| 55° | 6731.3 | 6472.3 | 5268.6 | 1656.8 | 460.8 | 416.3 | 374.4 | 232.5 | 268.4 | 271.0 | 295.8 |
| 57.5° | 5900.4 | 5666.2 | 4604.4 | 1137.8 | 409.5 | 305.2 | 298.4 | 203.5 | 220.6 | 241.9 | 257.3 |
| 60° | 4489.0 | 4289.8 | 3443.5 | 521.5 | 311.2 | 194.1 | 204.3 | 175.3 | 165.0 | 196.6 | 212.0 |
| 62.5° | 2749.3 | 2621.9 | 2065.4 | 230.8 | 198.3 | 103.4 | 124.0 | 139.3 | 124.0 | 135.9 | 148.7 |
| 65° | 1091.7 | 1035.3 | 783.9 | 98.3 | 81.2 | 52.1 | 56.4 | 81.2 | 87.2 | 95.7 | 107.7 |
| 67.5° | 189.8 | 179.5 | 131.7 | 43.6 | 33.3 | 31.6 | 27.4 | 37.6 | 53.0 | 59.0 | 68.4 |
| 70° | 24.8 | 23.9 | 21.4 | 18.0 | 17.1 | 15.4 | 12.0 | 23.9 | 35.9 | 37.6 | 43.6 |
| 72.5° | 6.0 | 5.1 | 5.1 | 4.3 | 5.1 | 1.7 | 1.7 | 12.8 | 25.6 | 26.5 | 30.8 |
| 75° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 4.3 | 16.2 | 18.0 | 21.4 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633969
 CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 |
| 2.5° | 994.2 | 977.1 | 971.1 | 962.6 | 951.5 | 954.9 | 939.5 | 934.4 | 942.1 | 952.3 | 949.8 |
| 5° | 903.6 | 884.8 | 872.0 | 852.3 | 848.9 | 841.2 | 836.1 | 829.2 | 837.8 | 849.8 | 852.3 |
| 7.5° | 831.8 | 815.6 | 802.7 | 796.7 | 792.5 | 789.1 | 778.8 | 773.7 | 773.7 | 778.8 | 783.1 |
| 10° | 801.0 | 789.1 | 786.5 | 788.2 | 795.0 | 794.2 | 784.8 | 777.9 | 769.4 | 765.1 | 770.2 |
| 12.5° | 843.8 | 824.1 | 820.7 | 821.5 | 830.1 | 829.2 | 819.0 | 810.4 | 808.7 | 810.4 | 826.7 |
| 15° | 916.4 | 886.5 | 864.3 | 860.0 | 864.3 | 862.6 | 854.9 | 849.8 | 852.3 | 877.1 | 904.5 |
| 17.5° | 981.4 | 935.2 | 895.1 | 879.7 | 878.8 | 876.3 | 868.6 | 866.8 | 879.7 | 925.8 | 966.0 |
| 20° | 1000.2 | 954.9 | 897.6 | 878.0 | 873.7 | 871.1 | 862.6 | 865.1 | 881.4 | 937.0 | 971.1 |
| 22.5° | 975.4 | 931.8 | 872.0 | 852.3 | 848.9 | 848.0 | 839.5 | 842.9 | 856.6 | 905.3 | 933.5 |
| 25° | 928.4 | 891.6 | 829.2 | 812.1 | 812.1 | 810.4 | 802.7 | 804.4 | 813.0 | 855.7 | 883.1 |
| 27.5° | 871.1 | 836.1 | 783.9 | 766.8 | 769.4 | 772.0 | 762.6 | 760.0 | 766.8 | 807.0 | 823.3 |
| 30° | 805.3 | 780.5 | 739.5 | 724.1 | 723.2 | 733.5 | 720.7 | 717.2 | 726.6 | 758.3 | 761.7 |
| 32.5° | 741.2 | 729.2 | 700.1 | 688.2 | 689.0 | 690.7 | 683.9 | 683.9 | 692.5 | 709.6 | 708.7 |
| 35° | 678.8 | 671.1 | 666.0 | 657.4 | 656.5 | 653.1 | 653.1 | 654.8 | 664.2 | 670.2 | 659.1 |
| 37.5° | 618.9 | 626.6 | 632.6 | 624.1 | 617.2 | 617.2 | 617.2 | 624.9 | 633.5 | 630.9 | 612.1 |
| 40° | 565.9 | 582.2 | 601.0 | 591.6 | 575.3 | 574.5 | 577.9 | 590.7 | 603.5 | 588.2 | 571.1 |
| 42.5° | 520.6 | 541.1 | 567.6 | 562.5 | 544.6 | 542.0 | 544.6 | 560.8 | 571.1 | 551.4 | 532.6 |
| 45° | 476.2 | 501.8 | 533.4 | 533.4 | 513.8 | 511.2 | 512.1 | 533.4 | 539.4 | 516.3 | 492.4 |
| 47.5° | 438.6 | 466.8 | 500.1 | 500.1 | 483.9 | 478.7 | 483.0 | 505.2 | 509.5 | 477.0 | 454.8 |
| 50° | 402.6 | 433.4 | 470.2 | 467.6 | 456.5 | 452.2 | 459.9 | 483.9 | 478.7 | 442.8 | 419.7 |
| 52.5° | 357.3 | 389.8 | 440.3 | 442.8 | 436.8 | 437.7 | 447.1 | 462.5 | 448.0 | 404.4 | 384.7 |
| 55° | 316.3 | 349.6 | 400.1 | 413.8 | 413.8 | 412.9 | 417.2 | 429.2 | 417.2 | 365.0 | 341.1 |
| 57.5° | 271.9 | 300.1 | 342.0 | 345.4 | 347.9 | 338.5 | 344.5 | 360.8 | 354.8 | 310.3 | 296.6 |
| 60° | 223.1 | 247.1 | 271.0 | 273.6 | 262.4 | 242.8 | 253.9 | 272.7 | 277.0 | 243.6 | 228.3 |
| 62.5° | 158.2 | 181.2 | 209.4 | 209.4 | 198.3 | 178.7 | 193.2 | 209.4 | 203.5 | 169.3 | 159.9 |
| 65° | 118.0 | 139.3 | 160.7 | 170.1 | 160.7 | 147.0 | 158.2 | 170.1 | 160.7 | 132.5 | 118.8 |
| 67.5° | 76.1 | 90.6 | 103.4 | 111.1 | 112.8 | 111.1 | 116.3 | 112.8 | 101.7 | 82.9 | 75.2 |
| 70° | 46.2 | 53.9 | 60.7 | 67.5 | 72.7 | 75.2 | 77.8 | 70.1 | 59.0 | 48.7 | 46.2 |
| 72.5° | 33.3 | 40.2 | 46.2 | 51.3 | 57.3 | 59.0 | 59.0 | 53.9 | 43.6 | 34.2 | 31.6 |
| 75° | 23.1 | 29.1 | 34.2 | 37.6 | 42.7 | 44.5 | 44.5 | 40.2 | 32.5 | 24.8 | 22.2 |
| 77.5° | 0.9 | 6.0 | 6.0 | 5.1 | 6.8 | 8.5 | 8.5 | 10.3 | 9.4 | 6.8 | 6.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633969

CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 |
| 2.5° | 954.9 | 985.7 | 994.2 | 1025.9 | 1054.1 | 1082.3 | 1116.5 | 1137.0 | 1167.8 | 1189.1 | 1201.1 |
| 5° | 860.9 | 886.5 | 917.3 | 964.3 | 1013.0 | 1066.9 | 1131.9 | 1188.3 | 1259.2 | 1311.4 | 1328.5 |
| 7.5° | 792.5 | 825.8 | 861.7 | 920.7 | 987.4 | 1059.2 | 1150.7 | 1243.0 | 1351.6 | 1422.5 | 1467.8 |
| 10° | 779.7 | 813.8 | 861.7 | 919.9 | 990.0 | 1072.0 | 1184.0 | 1303.7 | 1439.6 | 1526.0 | 1577.3 |
| 12.5° | 841.2 | 878.0 | 898.5 | 925.0 | 978.0 | 1069.5 | 1213.1 | 1365.2 | 1525.1 | 1619.1 | 1673.9 |
| 15° | 931.8 | 964.3 | 931.0 | 897.6 | 931.8 | 1042.1 | 1229.3 | 1416.5 | 1600.3 | 1708.9 | 1765.3 |
| 17.5° | 994.2 | 996.8 | 924.1 | 853.2 | 862.6 | 992.5 | 1235.3 | 1467.8 | 1680.7 | 1794.4 | 1853.4 |
| 20° | 988.2 | 967.7 | 894.2 | 815.6 | 786.5 | 928.4 | 1228.5 | 1513.1 | 1761.9 | 1880.7 | 1938.9 |
| 22.5° | 942.1 | 918.1 | 855.7 | 778.8 | 722.4 | 852.3 | 1216.5 | 1554.2 | 1836.3 | 1971.4 | 2026.1 |
| 25° | 886.5 | 860.9 | 809.6 | 742.0 | 681.3 | 778.8 | 1207.1 | 1610.6 | 1930.3 | 2089.3 | 2132.1 |
| 27.5° | 821.5 | 799.3 | 755.7 | 707.0 | 664.2 | 723.2 | 1204.5 | 1685.0 | 2044.0 | 2233.0 | 2262.9 |
| 30° | 758.3 | 737.8 | 703.6 | 675.4 | 657.4 | 690.7 | 1196.0 | 1764.5 | 2179.9 | 2397.9 | 2430.4 |
| 32.5° | 697.6 | 677.1 | 655.7 | 651.4 | 652.3 | 678.8 | 1166.9 | 1843.1 | 2341.5 | 2637.3 | 2661.2 |
| 35° | 645.4 | 621.5 | 612.9 | 623.2 | 642.0 | 658.3 | 1084.8 | 1908.1 | 2515.1 | 2898.0 | 2917.7 |
| 37.5° | 595.9 | 571.9 | 571.1 | 595.9 | 616.4 | 626.6 | 988.2 | 1972.2 | 2749.3 | 3163.1 | 3187.9 |
| 40° | 550.5 | 526.6 | 535.2 | 565.1 | 581.3 | 586.4 | 871.1 | 2069.7 | 2997.2 | 3442.6 | 3428.9 |
| 42.5° | 512.1 | 487.3 | 492.4 | 530.9 | 545.4 | 559.1 | 763.4 | 2150.9 | 3235.7 | 3707.6 | 3703.3 |
| 45° | 474.5 | 455.7 | 452.2 | 494.1 | 506.9 | 561.7 | 684.8 | 2213.3 | 3542.6 | 4045.3 | 4052.1 |
| 47.5° | 437.7 | 423.2 | 424.0 | 442.0 | 473.6 | 574.5 | 618.1 | 2254.3 | 3988.0 | 4580.5 | 4461.6 |
| 50° | 404.4 | 393.2 | 402.6 | 382.1 | 452.2 | 558.2 | 560.8 | 2245.8 | 4485.6 | 5093.4 | 4854.9 |
| 52.5° | 367.6 | 365.0 | 369.3 | 319.7 | 418.0 | 492.4 | 506.9 | 2132.1 | 4718.9 | 5443.9 | 5308.0 |
| 55° | 330.0 | 329.1 | 294.9 | 255.6 | 349.6 | 393.2 | 434.3 | 1779.0 | 4711.3 | 5630.2 | 5795.2 |
| 57.5° | 285.5 | 278.7 | 224.0 | 208.6 | 271.9 | 273.6 | 395.8 | 1165.2 | 4175.2 | 5184.0 | 5526.0 |
| 60° | 216.3 | 211.2 | 164.1 | 169.3 | 189.8 | 175.3 | 315.5 | 580.5 | 3120.3 | 4038.5 | 4424.0 |
| 62.5° | 149.6 | 142.8 | 122.2 | 130.8 | 122.2 | 100.0 | 193.2 | 287.2 | 1890.1 | 2550.1 | 2899.8 |
| 65° | 109.4 | 101.7 | 83.8 | 71.8 | 57.3 | 57.3 | 73.5 | 110.3 | 731.8 | 1084.0 | 1307.1 |
| 67.5° | 67.5 | 64.1 | 49.6 | 35.9 | 35.1 | 37.6 | 38.5 | 54.7 | 118.0 | 188.1 | 230.0 |
| 70° | 43.6 | 40.2 | 33.3 | 23.1 | 21.4 | 22.2 | 23.1 | 25.6 | 29.9 | 32.5 | 39.3 |
| 72.5° | 29.9 | 28.2 | 23.9 | 12.8 | 10.3 | 11.1 | 12.0 | 12.0 | 14.5 | 13.7 | 16.2 |
| 75° | 21.4 | 19.7 | 17.1 | 6.0 | 3.4 | 4.3 | 5.1 | 4.3 | 5.1 | 3.4 | 4.3 |
| 77.5° | 6.0 | 6.0 | 4.3 | 0.9 | 0.0 | 0.9 | 1.7 | 1.7 | 0.9 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633969

CATALOG NUMBER: GWS-SA2F-827-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|---------|--------|--------|--------|--------|--------|--------|
| 0° | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 | 1086.6 |
| 2.5° | 1231.9 | 1251.5 | 1259.2 | 1248.1 | 1257.5 | 1242.1 | 1236.2 | 1213.1 | 1211.4 | 1207.1 |
| 5° | 1397.7 | 1442.2 | 1468.7 | 1484.9 | 1466.1 | 1445.6 | 1414.8 | 1361.8 | 1345.6 | 1335.3 |
| 7.5° | 1561.0 | 1630.3 | 1675.6 | 1696.9 | 1691.8 | 1649.9 | 1594.4 | 1505.4 | 1473.8 | 1458.4 |
| 10° | 1702.9 | 1787.6 | 1842.3 | 1868.8 | 1857.7 | 1820.9 | 1741.4 | 1630.3 | 1588.4 | 1579.0 |
| 12.5° | 1802.1 | 1879.9 | 1917.5 | 1940.6 | 1941.4 | 1926.9 | 1851.7 | 1739.7 | 1690.1 | 1678.1 |
| 15° | 1864.5 | 1897.8 | 1898.7 | 1912.4 | 1936.3 | 1968.8 | 1933.7 | 1834.6 | 1781.6 | 1763.6 |
| 17.5° | 1903.8 | 1867.1 | 1829.4 | 1832.9 | 1872.2 | 1958.5 | 1994.4 | 1918.4 | 1861.9 | 1842.3 |
| 20° | 1932.0 | 1815.8 | 1745.7 | 1746.5 | 1786.7 | 1917.5 | 2036.3 | 1999.6 | 1941.4 | 1923.5 |
| 22.5° | 1950.0 | 1770.5 | 1670.4 | 1667.9 | 1710.6 | 1868.8 | 2074.8 | 2096.2 | 2038.9 | 2018.4 |
| 25° | 1986.7 | 1749.1 | 1625.1 | 1639.7 | 1677.3 | 1853.4 | 2126.9 | 2224.4 | 2171.4 | 2144.0 |
| 27.5° | 2052.6 | 1770.5 | 1620.9 | 1654.2 | 1696.9 | 1898.7 | 2217.6 | 2395.4 | 2340.7 | 2309.9 |
| 30° | 2166.3 | 1850.8 | 1686.7 | 1732.8 | 1784.1 | 2017.5 | 2369.7 | 2633.9 | 2555.2 | 2526.2 |
| 32.5° | 2349.2 | 2017.5 | 1890.1 | 1989.3 | 2038.9 | 2212.4 | 2598.0 | 2901.5 | 2837.4 | 2779.2 |
| 35° | 2601.4 | 2397.9 | 2383.4 | 2614.2 | 2602.3 | 2581.7 | 2878.4 | 3229.7 | 3133.1 | 3076.7 |
| 37.5° | 2948.5 | 3010.0 | 3117.8 | 3346.9 | 3339.2 | 3182.7 | 3246.8 | 3540.1 | 3490.5 | 3417.8 |
| 40° | 3381.9 | 3512.7 | 3695.7 | 4023.9 | 3921.3 | 3724.7 | 3699.1 | 3858.1 | 3817.9 | 3732.4 |
| 42.5° | 3637.5 | 3863.2 | 4212.0 | 4506.9 | 4424.9 | 4081.2 | 4052.1 | 4283.0 | 4194.9 | 4101.7 |
| 45° | 3756.3 | 4148.7 | 4832.6 | 5231.9 | 4983.1 | 4318.0 | 4306.9 | 4836.9 | 4787.3 | 4662.5 |
| 47.5° | 3811.1 | 4436.8 | 5559.3 | 6163.7 | 5698.6 | 4525.7 | 4485.6 | 5640.5 | 5575.5 | 5428.5 |
| 50° | 3871.8 | 4834.4 | 6434.7 | 7243.4 | 6562.9 | 4760.8 | 4789.9 | 6389.4 | 6362.0 | 6188.5 |
| 52.5° | 4005.1 | 5255.0 | 7512.7 | 8477.9 | 7611.0 | 5129.3 | 5312.2 | 7095.5 | 6910.9 | 6710.8 |
| 55° | 4205.2 | 5713.2 | 8634.3 | 9738.8 | 8680.5 | 5624.3 | 5877.3 | 7470.8 | 6952.8 | 6731.3 |
| 57.5° | 3983.7 | 5827.7 | 9298.5 | 10619.3 | 9154.9 | 5626.0 | 5399.4 | 6820.2 | 6115.0 | 5900.4 |
| 60° | 3161.4 | 5421.7 | 9042.9 | 10428.7 | 8750.6 | 4995.9 | 4134.2 | 5325.1 | 4632.6 | 4489.0 |
| 62.5° | 2137.2 | 4547.1 | 7960.7 | 8819.8 | 7489.6 | 3929.9 | 2686.9 | 3463.1 | 2868.1 | 2749.3 |
| 65° | 1171.2 | 3392.2 | 6432.1 | 6672.3 | 5861.9 | 2745.0 | 1382.3 | 1502.9 | 1144.7 | 1091.7 |
| 67.5° | 323.1 | 2361.2 | 4732.6 | 4426.6 | 4112.8 | 1787.6 | 357.3 | 268.4 | 191.5 | 189.8 |
| 70° | 81.2 | 1561.9 | 2835.6 | 2922.8 | 2521.9 | 1144.7 | 68.4 | 32.5 | 25.6 | 24.8 |
| 72.5° | 34.2 | 671.9 | 1345.6 | 1546.5 | 1290.9 | 530.0 | 24.8 | 9.4 | 7.7 | 6.0 |
| 75° | 4.3 | 53.9 | 114.6 | 173.5 | 118.8 | 57.3 | 0.0 | 0.0 | 0.0 | 0.0 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26




| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)