

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833918

Luminaire Tested: **TTN-D3-740-U-DL-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833918
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D3-740-U-DL-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
4000K, 70 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7255.7 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type IV - Short
BUG Rating: B1 - U4 - G3


Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833918
 CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P833918
CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical



REPORT NUMBER: P833918
 CATALOG NUMBER: TTN-D3-740-U-DL-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1420.8	292.5	1713.2
	% Fixture	19.6	4.0	23.6
Street Side	Lumens	5250.0	292.4	5542.5
	% Fixture	72.4	4.0	76.4
Total	Lumens	6670.8	584.9	7255.7
	% Fixture	91.9	8.1	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.0	0.7
10°-20°	169.1	2.3
20°-30°	357.2	4.9
30°-40°	652.8	9.0
40°-50°	1060.8	14.6
50°-60°	1474.4	20.3
60°-70°	1528.4	21.1
70°-80°	1095.2	15.1
80°-90°	280.0	3.9
90°-100°	13.1	0.2
100°-110°	132.7	1.8
110°-120°	194.0	2.7
120°-130°	112.6	1.6
130°-140°	59.7	0.8
140°-150°	35.4	0.5
150°-160°	21.8	0.3
160°-170°	11.9	0.2
170°-180°	3.9	0.1
0°-90°	6670.8	91.9
0°-180°	7255.7	100.0

Coefficient of Utilization




REPORT NUMBER: P833918
 CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	390.3	5.4			
FM (30°-60°)	2490.6	34.3			
FH (60°-80°)	2136.1	29.4			G2/5000
FVH (80°-90°)	233.0	3.2			G3/500
BL (0°-30°)	188.9	2.6	B1/500		
BM (30°-60°)	697.3	9.6	B1/1000		
BH (60°-80°)	487.5	6.7	B1/500		G1/500
BVH (80°-90°)	47.0	0.6			G1/100
UL (90°-100°)	13.1	0.2		U2/50	
UH (100°-180°)	571.8	7.9		U4/1000	

BUG Rating: B1-U4-G3
 Type IV Short





REPORT NUMBER: P833918

CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8
2.5°	602.3	602.3	602.3	602.3	596.5	596.5	590.7	584.9	579.1	573.3	561.8
5°	654.4	654.4	648.6	642.8	631.3	625.5	619.7	608.1	596.5	584.9	567.6
7.5°	677.6	677.6	677.6	671.8	654.4	648.6	637.0	619.7	602.3	584.9	561.8
10°	718.1	718.1	712.3	706.5	689.2	683.4	671.8	648.6	619.7	590.7	561.8
12.5°	770.2	764.5	758.7	752.9	735.5	723.9	706.5	683.4	648.6	613.9	579.1
15°	834.0	822.4	822.4	810.8	793.4	776.0	764.5	729.7	695.0	648.6	602.3
17.5°	903.5	897.7	891.9	880.3	862.9	851.3	834.0	793.4	747.1	689.2	637.0
20°	990.3	978.7	984.5	967.2	949.8	944.0	915.0	868.7	810.8	747.1	683.4
22.5°	1094.6	1083.0	1083.0	1065.6	1054.0	1042.4	1013.5	961.4	886.1	816.6	735.5
25°	1210.4	1198.8	1198.8	1187.2	1175.6	1164.1	1129.3	1071.4	984.5	897.7	805.0
27.5°	1337.8	1326.2	1326.2	1320.4	1291.5	1274.1	1245.1	1181.4	1094.6	984.5	874.5
30°	1471.0	1459.4	1471.0	1459.4	1442.0	1407.3	1372.6	1303.1	1204.6	1083.0	949.8
32.5°	1575.2	1575.2	1581.0	1592.6	1581.0	1552.1	1511.5	1453.6	1320.4	1169.9	1019.3
35°	1696.9	1696.9	1708.4	1725.8	1720.0	1691.1	1650.5	1586.8	1447.8	1268.3	1094.6
37.5°	1830.1	1830.1	1841.6	1870.6	1859.0	1841.6	1812.7	1731.6	1575.2	1366.8	1175.6
40°	1974.9	1969.1	1980.6	2021.2	2027.0	2003.8	1969.1	1888.0	1708.4	1494.2	1262.5
42.5°	2119.6	2113.8	2137.0	2177.5	2183.3	2177.5	2142.8	2050.1	1847.4	1621.6	1349.4
45°	2264.4	2264.4	2299.2	2362.9	2391.8	2380.2	2351.3	2235.5	2021.2	1754.8	1465.2
47.5°	2415.0	2415.0	2461.3	2542.4	2577.2	2571.4	2559.8	2420.8	2189.1	1893.8	1563.7
50°	2530.8	2530.8	2606.1	2698.8	2756.7	2779.8	2721.9	2594.5	2333.9	2015.4	1644.7
52.5°	2646.6	2646.6	2721.9	2866.7	2924.6	2959.4	2884.1	2750.9	2496.1	2125.4	1720.0
55°	2704.6	2716.1	2820.4	2959.4	3052.0	3034.7	3063.6	2884.1	2600.3	2206.5	1766.4
57.5°	2710.4	2727.7	2843.6	2988.3	3092.6	3086.8	3092.6	2930.4	2640.9	2223.9	1772.2
60°	2681.4	2710.4	2814.6	2959.4	3057.8	3104.2	3046.3	2901.5	2617.7	2206.5	1766.4
62.5°	2611.9	2669.8	2779.8	2889.9	3034.7	3052.0	3005.7	2884.1	2554.0	2189.1	1737.4
65°	2455.5	2519.2	2675.6	2803.0	2918.8	2942.0	2889.9	2785.6	2490.3	2108.1	1644.7
67.5°	2299.2	2339.7	2472.9	2669.8	2750.9	2774.1	2756.7	2635.1	2380.2	1945.9	1534.7
70°	2119.6	2171.8	2276.0	2478.7	2559.8	2554.0	2606.1	2467.1	2212.3	1806.9	1418.9
72.5°	1876.4	1951.7	2055.9	2223.9	2322.3	2287.6	2368.7	2252.8	1992.2	1633.2	1262.5
75°	1592.6	1656.3	1789.5	1922.7	2032.8	1992.2	2055.9	1974.9	1737.4	1424.7	1083.0
77.5°	1274.1	1349.4	1471.0	1592.6	1667.9	1667.9	1696.9	1627.4	1442.0	1169.9	886.1
80°	944.0	1013.5	1123.5	1210.4	1279.9	1285.7	1314.6	1279.9	1111.9	909.2	677.6
82.5°	625.5	660.2	758.7	828.2	897.7	891.9	938.2	915.0	776.0	625.5	451.7
85°	266.4	289.6	370.6	428.6	492.3	469.1	532.8	527.0	417.0	301.2	202.7
87.5°	11.6	17.4	17.4	11.6	17.4	5.8	17.4	23.2	17.4	11.6	11.6
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0
92.5°	5.0	5.0	5.0	7.0	8.0	7.5	7.0	8.0	6.0	6.0	5.0
95°	6.0	6.0	7.0	9.0	11.0	11.5	12.0	12.0	7.0	7.0	6.0
97.5°	8.0	9.0	9.0	11.0	18.0	25.5	33.0	20.0	10.0	10.0	9.0
100°	13.0	14.0	14.0	25.0	53.0	62.0	71.1	51.0	26.0	19.0	14.0
102.5°	42.0	44.0	54.0	81.1	120.1	114.6	109.1	92.1	87.1	60.0	48.0
105°	107.1	106.1	114.1	135.1	168.1	166.6	165.1	152.1	138.1	119.1	110.1
107.5°	141.1	141.1	148.1	166.1	191.1	207.2	223.2	226.2	179.1	157.1	147.1
110°	159.1	159.1	165.1	180.1	213.2	235.7	258.2	256.2	221.2	194.1	181.1



REPORT NUMBER: P833918
 CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
112.5°	163.1	164.1	172.1	195.1	231.2	241.2	251.2	242.2	228.2	216.2	206.2
115°	169.1	169.1	178.1	200.2	220.2	224.2	228.2	218.2	207.2	199.2	195.1
117.5°	167.1	170.1	172.1	184.1	197.1	200.1	203.2	198.1	183.1	177.1	175.1
120°	155.1	155.1	157.1	163.1	170.1	171.6	173.1	171.1	161.1	156.1	155.1
122.5°	138.1	139.1	138.1	141.1	146.1	147.6	149.1	147.1	139.1	137.1	137.1
125°	121.1	121.1	120.1	122.1	125.1	124.6	124.1	125.1	121.1	120.1	120.1
127.5°	109.1	108.1	106.1	107.1	108.1	108.1	108.1	109.1	105.1	106.1	107.1
130°	97.1	97.1	95.1	95.1	95.1	94.1	93.1	95.1	93.1	94.1	95.1
132.5°	86.1	86.1	83.1	82.1	82.1	82.1	82.1	83.1	82.1	84.1	86.1
135°	77.1	77.1	74.1	75.1	75.1	74.6	74.1	75.1	74.1	76.1	77.1
137.5°	70.1	70.1	68.1	68.1	68.1	67.6	67.1	68.1	68.1	69.1	71.1
140°	64.0	64.0	63.0	63.0	62.0	62.5	63.0	63.0	63.0	64.0	65.0
142.5°	61.0	60.0	59.0	58.0	59.0	59.0	59.0	59.0	58.0	59.0	61.0
145°	56.0	56.0	55.0	55.0	55.0	55.5	56.0	55.0	55.0	56.0	56.0
147.5°	53.0	53.0	52.0	53.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0
150°	52.0	51.0	50.0	51.0	51.0	50.5	50.0	50.0	50.0	50.0	51.0
152.5°	49.0	49.0	48.0	49.0	48.0	48.0	48.0	48.0	48.0	48.0	49.0
155°	47.0	47.0	46.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
157.5°	45.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0
160°	44.0	44.0	44.0	44.0	43.0	43.0	43.0	43.0	44.0	44.0	44.0
162.5°	43.0	43.0	43.0	43.0	42.0	42.0	42.0	42.0	42.0	43.0	43.0
165°	43.0	42.0	42.0	42.0	41.0	41.0	41.0	41.0	41.0	42.0	43.0
167.5°	41.0	41.0	41.0	41.0	41.0	40.5	40.0	40.0	41.0	41.0	41.0
170°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0
172.5°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0
175°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	41.0	41.0	41.0
177.5°	41.0	41.0	41.0	41.0	40.0	40.5	41.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0



REPORT NUMBER: P833918
 CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8
2.5°	561.8	556.0	544.4	538.6	532.8	521.2	521.2	515.4	515.4	515.4	509.6
5°	561.8	550.2	538.6	521.2	509.6	498.1	486.5	474.9	469.1	469.1	463.3
7.5°	550.2	538.6	521.2	503.8	486.5	463.3	451.7	428.6	422.8	417.0	417.0
10°	550.2	538.6	509.6	486.5	463.3	440.1	422.8	399.6	382.2	376.4	376.4
12.5°	556.0	538.6	509.6	480.7	451.7	422.8	399.6	376.4	359.1	347.5	347.5
15°	579.1	556.0	521.2	480.7	445.9	411.2	388.0	359.1	341.7	330.1	330.1
17.5°	608.1	584.9	532.8	486.5	445.9	405.4	376.4	347.5	330.1	318.5	312.7
20°	648.6	613.9	556.0	492.3	445.9	405.4	370.6	341.7	318.5	306.9	306.9
22.5°	695.0	654.4	579.1	503.8	451.7	405.4	370.6	335.9	312.7	301.2	301.2
25°	752.9	700.8	613.9	527.0	463.3	411.2	370.6	335.9	312.7	301.2	301.2
27.5°	816.6	758.7	648.6	550.2	474.9	417.0	370.6	335.9	312.7	301.2	301.2
30°	874.5	810.8	683.4	573.3	492.3	422.8	376.4	341.7	318.5	306.9	301.2
32.5°	938.2	857.1	718.1	596.5	503.8	434.4	382.2	347.5	318.5	306.9	306.9
35°	1001.9	915.0	752.9	625.5	521.2	445.9	388.0	353.3	324.3	312.7	312.7
37.5°	1071.4	978.7	793.4	648.6	538.6	457.5	399.6	359.1	330.1	318.5	318.5
40°	1152.5	1042.4	834.0	677.6	556.0	469.1	405.4	370.6	341.7	330.1	330.1
42.5°	1227.8	1100.4	874.5	700.8	573.3	480.7	417.0	376.4	353.3	341.7	341.7
45°	1303.1	1169.9	915.0	729.7	590.7	498.1	428.6	393.8	364.9	353.3	353.3
47.5°	1389.9	1233.6	961.4	752.9	608.1	509.6	440.1	405.4	376.4	370.6	364.9
50°	1459.4	1279.9	990.3	776.0	619.7	521.2	451.7	411.2	388.0	376.4	376.4
52.5°	1523.1	1326.2	1013.5	787.6	625.5	527.0	463.3	422.8	399.6	388.0	388.0
55°	1557.9	1343.6	1030.9	787.6	631.3	532.8	463.3	422.8	399.6	393.8	388.0
57.5°	1557.9	1343.6	1019.3	776.0	619.7	521.2	457.5	417.0	399.6	388.0	388.0
60°	1534.7	1326.2	990.3	752.9	602.3	503.8	445.9	405.4	388.0	382.2	382.2
62.5°	1500.0	1297.3	967.2	723.9	579.1	480.7	428.6	388.0	376.4	376.4	370.6
65°	1407.3	1210.4	915.0	683.4	544.4	451.7	405.4	370.6	359.1	353.3	347.5
67.5°	1308.8	1129.3	834.0	637.0	498.1	422.8	376.4	347.5	330.1	330.1	324.3
70°	1210.4	1042.4	758.7	573.3	445.9	388.0	341.7	312.7	301.2	301.2	301.2
72.5°	1077.2	932.4	671.8	503.8	393.8	341.7	306.9	278.0	272.2	272.2	266.4
75°	920.8	793.4	567.6	428.6	330.1	289.6	260.6	231.7	231.7	231.7	231.7
77.5°	752.9	642.8	451.7	341.7	260.6	231.7	214.3	191.1	191.1	191.1	191.1
80°	567.6	474.9	330.1	249.0	191.1	167.9	156.4	144.8	150.6	150.6	144.8
82.5°	370.6	312.7	208.5	156.4	121.6	110.0	110.0	98.5	104.2	104.2	104.2
85°	162.2	139.0	86.9	69.5	57.9	57.9	57.9	52.1	57.9	57.9	57.9
87.5°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	0.0	5.8	11.6	5.8
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0	5.0
92.5°	5.0	5.0	6.0	6.0	8.0	7.0	8.0	7.0	5.0	5.0	5.0
95°	6.0	6.0	7.0	7.0	12.0	12.0	11.0	9.0	7.0	6.0	6.0
97.5°	8.0	9.0	10.0	10.0	20.0	33.0	18.0	11.0	9.0	9.0	8.0
100°	14.0	14.0	19.0	26.0	51.0	71.1	53.0	25.0	14.0	14.0	13.0
102.5°	46.0	48.0	60.0	87.1	92.1	109.1	120.1	81.1	54.0	44.0	42.0
105°	110.1	110.1	119.1	138.1	152.1	165.1	168.1	135.1	114.1	106.1	107.1
107.5°	146.1	147.1	157.1	179.1	226.2	223.2	191.1	166.1	148.1	141.1	141.1
110°	179.1	181.1	194.1	221.2	256.2	258.2	213.2	180.1	165.1	159.1	159.1



REPORT NUMBER: P833918
 CATALOG NUMBER: TTN-D3-740-U-DL-UPL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	204.2	206.2	216.2	228.2	242.2	251.2	231.2	195.1	172.1	164.1	163.1
115°	197.1	195.1	199.2	207.2	218.2	228.2	220.2	200.2	178.1	169.1	169.1
117.5°	172.1	175.1	177.1	183.1	198.1	203.2	197.1	184.1	172.1	170.1	167.1
120°	153.1	155.1	156.1	161.1	171.1	173.1	170.1	163.1	157.1	155.1	155.1
122.5°	135.1	137.1	137.1	139.1	147.1	149.1	146.1	141.1	138.1	139.1	138.1
125°	119.1	120.1	120.1	121.1	125.1	124.1	125.1	122.1	120.1	121.1	121.1
127.5°	106.1	107.1	106.1	105.1	109.1	108.1	108.1	107.1	106.1	108.1	109.1
130°	96.1	95.1	94.1	93.1	95.1	93.1	95.1	95.1	95.1	97.1	97.1
132.5°	86.1	86.1	84.1	82.1	83.1	82.1	82.1	82.1	83.1	86.1	86.1
135°	77.1	77.1	76.1	74.1	75.1	74.1	75.1	75.1	74.1	77.1	77.1
137.5°	72.1	71.1	69.1	68.1	68.1	67.1	68.1	68.1	68.1	70.1	70.1
140°	65.0	65.0	64.0	63.0	63.0	63.0	62.0	63.0	63.0	64.0	64.0
142.5°	61.0	61.0	59.0	58.0	59.0	59.0	59.0	58.0	59.0	60.0	61.0
145°	57.0	56.0	56.0	55.0	55.0	56.0	55.0	55.0	55.0	56.0	56.0
147.5°	54.0	53.0	53.0	52.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0
150°	51.0	51.0	50.0	50.0	50.0	50.0	51.0	51.0	50.0	51.0	52.0
152.5°	50.0	49.0	48.0	48.0	48.0	48.0	48.0	49.0	48.0	49.0	49.0
155°	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	46.0	47.0	47.0
157.5°	46.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0	45.0
160°	45.0	44.0	44.0	44.0	43.0	43.0	43.0	44.0	44.0	44.0	44.0
162.5°	44.0	43.0	43.0	42.0	42.0	42.0	42.0	43.0	43.0	43.0	43.0
165°	42.0	43.0	42.0	41.0	41.0	41.0	41.0	42.0	42.0	42.0	43.0
167.5°	42.0	41.0	41.0	41.0	40.0	40.0	41.0	41.0	41.0	41.0	41.0
170°	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0
172.5°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0	41.0	41.0
175°	40.0	41.0	41.0	41.0	40.0	40.0	40.0	41.0	41.0	41.0	41.0
177.5°	41.0	41.0	41.0	41.0	41.0	41.0	40.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2411-284-2

Test Date: 11/20/2024

Luminaire Tested: TTN-D0-740-U-WQ

Data in this report applies to TT and TTN families of products


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2411-284-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/20/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **TTN-D0-740-U-WQ**
 Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE. 4000K, 70 CRI LEDS AND WIDE DISTRIBUTION

Spectral Parameters

CCT (K): 3863
 CIE u': 0.2247
 CIE v': 0.5111
 Duv: 0.0055
 CIE x: 0.3911
 CIE y: 0.3954
 CIE z: 0.2136
 Peak Wavelength (nm): 448
 Dominant Wavelength (nm): 577
 Purity: 36.03443
 Rf: 74.7
 Rg: 95.4

CRI (Ra):	71.9		
R1:	69.4	R9:	-23.5
R2:	76.9	R10:	45.4
R3:	83.3	R11:	68.7
R4:	72.7	R12:	38.7
R5:	68.4	R13:	70.0
R6:	67.5	R14:	90.3
R7:	82.0	R15:	62.1
R8:	55.3		



Test Conditions


Stabilization Time: 37M
 Operation Time: 1H 37M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2411-284-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2411-284-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2411-284-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	730	NR	750	25	NR	880	1	NR
365	0	NR	495	170	NR	625	680	NR	755	22	NR	885	0	NR
370	0	NR	500	245	NR	630	630	NR	760	19	NR	890	0	NR
375	0	NR	505	338	NR	635	579	NR	765	17	NR	895	0	NR
380	0	NR	510	431	NR	640	529	NR	770	14	NR	900	0	NR
385	0	NR	515	521	NR	645	477	NR	775	13	NR	905	0	NR
390	1	NR	520	596	NR	650	429	NR	780	11	NR	910	0	NR
395	3	NR	525	655	NR	655	383	NR	785	9	NR	915	0	NR
400	6	NR	530	701	NR	660	338	NR	790	8	NR	920	0	NR
405	9	NR	535	739	NR	665	298	NR	795	7	NR	925	0	NR
410	16	NR	540	766	NR	670	261	NR	800	6	NR	930	0	NR
415	32	NR	545	791	NR	675	228	NR	805	5	NR	935	0	NR
420	65	NR	550	813	NR	680	200	NR	810	5	NR	940	0	NR
425	131	NR	555	833	NR	685	173	NR	815	4	NR	945	0	NR
430	245	NR	560	852	NR	690	151	NR	820	3	NR	950	0	NR
435	432	NR	565	870	NR	695	130	NR	825	3	NR	955	0	NR
440	622	NR	570	885	NR	700	112	NR	830	3	NR	960	0	NR
445	870	NR	575	900	NR	705	97	NR	835	2	NR	965	0	NR
450	969	NR	580	911	NR	710	83	NR	840	2	NR	970	0	NR
455	544	NR	585	916	NR	715	71	NR	845	2	NR	975	0	NR
460	304	NR	590	912	NR	720	60	NR	850	1	NR	980	0	NR
465	231	NR	595	901	NR	725	51	NR	855	1	NR	985	0	NR
470	142	NR	600	882	NR	730	43	NR	860	1	NR	990	0	NR
475	96	NR	605	855	NR	735	37	NR	865	1	NR	995	0	NR
480	92	NR	610	820	NR	740	32	NR	870	1	NR	1000	0	NR
485	96	NR	615	776	NR	745	29	NR	875	1	NR			

REPORT NUMBER: SP1-2411-284-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.45

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	730	NR	750	25	NR	880	1	NR
365	0	NR	495	170	NR	625	680	NR	755	22	NR	885	0	NR
370	0	NR	500	245	NR	630	630	NR	760	19	NR	890	0	NR
375	0	NR	505	338	NR	635	579	NR	765	17	NR	895	0	NR
380	0	NR	510	431	NR	640	529	NR	770	14	NR	900	0	NR
385	0	NR	515	521	NR	645	477	NR	775	13	NR	905	0	NR
390	1	NR	520	596	NR	650	429	NR	780	11	NR	910	0	NR
395	3	NR	525	655	NR	655	383	NR	785	9	NR	915	0	NR
400	6	NR	530	701	NR	660	338	NR	790	8	NR	920	0	NR
405	9	NR	535	739	NR	665	298	NR	795	7	NR	925	0	NR
410	16	NR	540	766	NR	670	261	NR	800	6	NR	930	0	NR
415	32	NR	545	791	NR	675	228	NR	805	5	NR	935	0	NR
420	65	NR	550	813	NR	680	200	NR	810	5	NR	940	0	NR
425	131	NR	555	833	NR	685	173	NR	815	4	NR	945	0	NR
430	245	NR	560	852	NR	690	151	NR	820	3	NR	950	0	NR
435	432	NR	565	870	NR	695	130	NR	825	3	NR	955	0	NR
440	622	NR	570	885	NR	700	112	NR	830	3	NR	960	0	NR
445	870	NR	575	900	NR	705	97	NR	835	2	NR	965	0	NR
450	969	NR	580	911	NR	710	83	NR	840	2	NR	970	0	NR
455	544	NR	585	916	NR	715	71	NR	845	2	NR	975	0	NR
460	304	NR	590	912	NR	720	60	NR	850	1	NR	980	0	NR
465	231	NR	595	901	NR	725	51	NR	855	1	NR	985	0	NR
470	142	NR	600	882	NR	730	43	NR	860	1	NR	990	0	NR
475	96	NR	605	855	NR	735	37	NR	865	1	NR	995	0	NR
480	92	NR	610	820	NR	740	32	NR	870	1	NR	1000	0	NR
485	96	NR	615	776	NR	745	29	NR	875	1	NR			

REPORT NUMBER: SP1-2411-284-2

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.72





λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	730	NR	750	25	NR	880	1	NR
365	0	NR	495	170	NR	625	680	NR	755	22	NR	885	0	NR
370	0	NR	500	245	NR	630	630	NR	760	19	NR	890	0	NR
375	0	NR	505	338	NR	635	579	NR	765	17	NR	895	0	NR
380	0	NR	510	431	NR	640	529	NR	770	14	NR	900	0	NR
385	0	NR	515	521	NR	645	477	NR	775	13	NR	905	0	NR
390	1	NR	520	596	NR	650	429	NR	780	11	NR	910	0	NR
395	3	NR	525	655	NR	655	383	NR	785	9	NR	915	0	NR
400	6	NR	530	701	NR	660	338	NR	790	8	NR	920	0	NR
405	9	NR	535	739	NR	665	298	NR	795	7	NR	925	0	NR
410	16	NR	540	766	NR	670	261	NR	800	6	NR	930	0	NR
415	32	NR	545	791	NR	675	228	NR	805	5	NR	935	0	NR
420	65	NR	550	813	NR	680	200	NR	810	5	NR	940	0	NR
425	131	NR	555	833	NR	685	173	NR	815	4	NR	945	0	NR
430	245	NR	560	852	NR	690	151	NR	820	3	NR	950	0	NR
435	432	NR	565	870	NR	695	130	NR	825	3	NR	955	0	NR
440	622	NR	570	885	NR	700	112	NR	830	3	NR	960	0	NR
445	870	NR	575	900	NR	705	97	NR	835	2	NR	965	0	NR
450	969	NR	580	911	NR	710	83	NR	840	2	NR	970	0	NR
455	544	NR	585	916	NR	715	71	NR	845	2	NR	975	0	NR
460	304	NR	590	912	NR	720	60	NR	850	1	NR	980	0	NR
465	231	NR	595	901	NR	725	51	NR	855	1	NR	985	0	NR
470	142	NR	600	882	NR	730	43	NR	860	1	NR	990	0	NR
475	96	NR	605	855	NR	735	37	NR	865	1	NR	995	0	NR
480	92	NR	610	820	NR	740	32	NR	870	1	NR	1000	0	NR
485	96	NR	615	776	NR	745	29	NR	875	1	NR			

Summary

$R_f = 74.7$
 $R_g = 95.4$
 $CIE R_a = 71.9$
 $R_9 = -23.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 63	CES51 = 88	CES76 = 51
CES02 = 61	CES27 = 87	CES52 = 88	CES77 = 70
CES03 = 30	CES28 = 81	CES53 = 76	CES78 = 54
CES04 = 70	CES29 = 63	CES54 = 84	CES79 = 81
CES05 = 47	CES30 = 76	CES55 = 83	CES80 = 78
CES06 = 50	CES31 = 67	CES56 = 72	CES81 = 79
CES07 = 40	CES32 = 61	CES57 = 71	CES82 = 91
CES08 = 39	CES33 = 73	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 70	CES59 = 86	CES84 = 87
CES10 = 74	CES35 = 83	CES60 = 91	CES85 = 80
CES11 = 57	CES36 = 96	CES61 = 85	CES86 = 74
CES12 = 63	CES37 = 77	CES62 = 86	CES87 = 78
CES13 = 42	CES38 = 85	CES63 = 72	CES88 = 80
CES14 = 74	CES39 = 95	CES64 = 68	CES89 = 72
CES15 = 71	CES40 = 89	CES65 = 64	CES90 = 79
CES16 = 46	CES41 = 90	CES66 = 61	CES91 = 80
CES17 = 49	CES42 = 78	CES67 = 58	CES92 = 64
CES18 = 56	CES43 = 76	CES68 = 67	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 76	CES94 = 57
CES20 = 65	CES45 = 84	CES70 = 58	CES95 = 69
CES21 = 86	CES46 = 81	CES71 = 52	CES96 = 78
CES22 = 78	CES47 = 82	CES72 = 84	CES97 = 84
CES23 = 92	CES48 = 75	CES73 = 49	CES98 = 75
CES24 = 91	CES49 = 79	CES74 = 95	CES99 = 66
CES25 = 72	CES50 = 87	CES75 = 52	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)