

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633973

Luminaire Tested: GWS-SA2F-827-U-SLR-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P633973  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA2F-827-U-SLR-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (32) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6362.2 lumens  
Efficiency: N/A  
Efficacy: 51.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B1 - U0 - G1  
  
Input Watts (W): 124.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P633973  
 CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 19.9 fc  
 Type III - Short - N/A

REPORT NUMBER: P633973  
CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P633973

CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1424.7   | 0.0    | 1424.7 |
|                    | % Fixture | 22.4     | 0.0    | 22.4   |
| <b>Street Side</b> | Lumens    | 4937.5   | 0.0    | 4937.5 |
|                    | % Fixture | 77.6     | 0.0    | 77.6   |
| <b>Total</b>       | Lumens    | 6362.2   | 0.0    | 6362.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 110.0  | 1.7       |
| 10°-20°   | 355.9  | 5.6       |
| 20°-30°   | 578.1  | 9.1       |
| 30°-40°   | 893.2  | 14.0      |
| 40°-50°   | 1432.3 | 22.5      |
| 50°-60°   | 1957.6 | 30.8      |
| 60°-70°   | 948.1  | 14.9      |
| 70°-80°   | 86.8   | 1.4       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6362.2 | 100.0     |
| 0°-180°   | 6362.2 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P633973


CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 622.4  | 9.8       |                         |      |         |
| FM (30°-60°)   | 3386.7 | 53.2      |                         |      |         |
| FH (60°-80°)   | 928.1  | 14.6      |                         |      | G1/1800 |
| FVH (80°-90°)  | 0.3    | 0.0       |                         |      | G0/10   |
| BL (0°-30°)    | 421.5  | 6.6       | B1/500                  |      |         |
| BM (30°-60°)   | 896.3  | 14.1      | B1/1000                 |      |         |
| BH (60°-80°)   | 106.8  | 1.7       | B0/110                  |      | G0/110  |
| BVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**

Type III Short





REPORT NUMBER: P633973

CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°    | 45°     | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|---------|--------|--------|--------|--------|
| 0°    | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2  | 1118.2 | 1118.2 | 1118.2 | 1118.2 |
| 2.5°  | 1211.4 | 1219.1 | 1231.9 | 1259.3 | 1282.4 | 1297.8 | 1304.6  | 1302.9 | 1293.5 | 1286.6 | 1273.0 |
| 5°    | 1341.4 | 1341.4 | 1366.1 | 1428.6 | 1476.4 | 1506.4 | 1521.7  | 1512.3 | 1493.5 | 1463.6 | 1417.4 |
| 7.5°  | 1455.1 | 1459.3 | 1501.2 | 1590.1 | 1662.8 | 1705.5 | 1730.3  | 1725.2 | 1691.9 | 1634.6 | 1542.3 |
| 10°   | 1544.0 | 1549.1 | 1604.7 | 1713.2 | 1798.7 | 1842.3 | 1879.1  | 1882.5 | 1845.8 | 1769.7 | 1663.7 |
| 12.5° | 1630.3 | 1635.4 | 1693.6 | 1797.9 | 1873.1 | 1891.1 | 1923.6  | 1936.4 | 1927.0 | 1873.1 | 1762.8 |
| 15°   | 1723.5 | 1735.5 | 1785.1 | 1862.9 | 1894.5 | 1873.1 | 1894.5  | 1917.6 | 1949.2 | 1944.1 | 1844.9 |
| 17.5° | 1815.0 | 1823.5 | 1874.0 | 1901.3 | 1866.3 | 1810.7 | 1821.0  | 1848.3 | 1920.1 | 1990.2 | 1926.1 |
| 20°   | 1899.6 | 1911.6 | 1953.5 | 1917.6 | 1811.6 | 1725.2 | 1726.1  | 1762.0 | 1871.4 | 2018.4 | 2009.0 |
| 22.5° | 1988.5 | 2006.5 | 2036.4 | 1935.5 | 1761.1 | 1657.7 | 1661.9  | 1694.4 | 1832.9 | 2044.9 | 2103.1 |
| 25°   | 2104.8 | 2121.9 | 2141.6 | 1980.0 | 1744.9 | 1624.3 | 1640.6  | 1670.5 | 1832.9 | 2090.3 | 2219.4 |
| 27.5° | 2262.1 | 2274.1 | 2274.9 | 2062.9 | 1773.1 | 1629.5 | 1663.7  | 1697.9 | 1887.6 | 2180.9 | 2374.9 |
| 30°   | 2459.6 | 2478.4 | 2453.6 | 2192.0 | 1861.1 | 1697.9 | 1748.3  | 1791.0 | 2005.6 | 2333.9 | 2604.1 |
| 32.5° | 2699.8 | 2726.3 | 2693.0 | 2383.5 | 2044.9 | 1933.8 | 2025.3  | 2050.1 | 2193.7 | 2555.3 | 2864.0 |
| 35°   | 2981.9 | 3004.2 | 2968.3 | 2648.5 | 2474.1 | 2494.6 | 2660.5  | 2628.9 | 2571.6 | 2828.0 | 3167.4 |
| 37.5° | 3291.4 | 3311.9 | 3242.7 | 3050.3 | 3108.5 | 3197.4 | 3462.4  | 3353.8 | 3169.2 | 3179.4 | 3496.6 |
| 40°   | 3575.2 | 3597.5 | 3488.9 | 3487.2 | 3606.9 | 3769.3 | 4089.0  | 3939.4 | 3688.1 | 3639.4 | 3805.2 |
| 42.5° | 3869.3 | 3884.7 | 3786.4 | 3719.7 | 3991.6 | 4325.9 | 4664.4  | 4462.6 | 4031.8 | 3978.8 | 4191.6 |
| 45°   | 4289.1 | 4321.6 | 4146.3 | 3834.3 | 4337.8 | 4966.2 | 5438.1  | 5044.0 | 4266.0 | 4223.3 | 4783.2 |
| 47.5° | 4906.3 | 4930.3 | 4572.9 | 3906.1 | 4660.1 | 5763.8 | 6405.0  | 5798.0 | 4472.0 | 4374.6 | 5592.0 |
| 50°   | 5416.7 | 5433.0 | 4965.3 | 3984.7 | 5002.9 | 6623.9 | 7507.0  | 6692.3 | 4703.7 | 4625.1 | 6346.9 |
| 52.5° | 5792.9 | 5854.4 | 5480.8 | 4146.3 | 5453.5 | 7635.2 | 8726.9  | 7751.5 | 5065.4 | 5109.0 | 6972.7 |
| 55°   | 5870.7 | 5954.5 | 5833.1 | 4245.5 | 5850.2 | 8665.4 | 9853.7  | 8699.6 | 5426.1 | 5475.7 | 7183.0 |
| 57.5° | 5159.4 | 5226.1 | 5327.0 | 3845.4 | 5840.8 | 9137.3 | 10507.7 | 9014.2 | 5262.0 | 4910.6 | 6395.6 |
| 60°   | 3865.1 | 3911.2 | 4094.2 | 2939.2 | 5371.4 | 8720.1 | 9998.2  | 8479.0 | 4601.1 | 3747.1 | 4873.0 |
| 62.5° | 2292.0 | 2312.5 | 2544.2 | 1903.9 | 4458.4 | 7509.5 | 8291.8  | 7316.3 | 3635.9 | 2520.3 | 2984.5 |
| 65°   | 879.7  | 871.2  | 1048.1 | 939.5  | 3278.6 | 5981.8 | 6167.3  | 5577.4 | 2494.6 | 1155.0 | 1137.9 |
| 67.5° | 135.9  | 129.9  | 175.3  | 277.8  | 2364.7 | 4145.5 | 4069.4  | 4019.8 | 1562.8 | 269.3  | 235.1  |
| 70°   | 30.8   | 30.8   | 37.6   | 82.1   | 1444.8 | 2435.6 | 2606.6  | 2485.2 | 1000.2 | 57.3   | 30.8   |
| 72.5° | 14.5   | 14.5   | 18.0   | 35.1   | 523.2  | 1003.7 | 1169.5  | 1151.6 | 324.9  | 18.8   | 11.1   |
| 75°   | 5.1    | 6.0    | 6.0    | 7.7    | 31.6   | 52.1   | 119.7   | 85.5   | 20.5   | 0.0    | 0.0    |
| 77.5° | 1.7    | 1.7    | 1.7    | 1.7    | 0.0    | 0.0    | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |
| 80°   | 0.9    | 0.9    | 0.9    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.9    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P633973

CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 |
| 2.5°  | 1243.0 | 1237.1 | 1214.8 | 1184.9 | 1155.8 | 1130.2 | 1103.7 | 1072.1 | 1049.0 | 1022.5 | 1013.9 |
| 5°    | 1381.5 | 1343.9 | 1283.2 | 1220.0 | 1161.8 | 1112.2 | 1064.4 | 1013.1 | 975.5  | 937.8  | 925.0  |
| 7.5°  | 1498.7 | 1443.1 | 1344.8 | 1249.9 | 1170.4 | 1100.3 | 1031.0 | 960.9  | 906.2  | 861.8  | 848.1  |
| 10°   | 1603.8 | 1539.7 | 1408.0 | 1290.9 | 1190.9 | 1109.7 | 1025.9 | 937.8  | 866.9  | 813.9  | 801.1  |
| 12.5° | 1694.4 | 1620.1 | 1461.9 | 1321.7 | 1199.4 | 1106.3 | 1025.0 | 954.9  | 890.8  | 830.1  | 813.9  |
| 15°   | 1770.5 | 1688.5 | 1507.2 | 1342.2 | 1186.6 | 1063.5 | 992.6  | 981.4  | 976.3  | 909.6  | 878.0  |
| 17.5° | 1844.9 | 1752.6 | 1544.0 | 1351.6 | 1150.7 | 988.3  | 937.0  | 987.4  | 1041.3 | 997.7  | 957.5  |
| 20°   | 1922.7 | 1817.5 | 1581.6 | 1353.3 | 1090.9 | 903.6  | 895.1  | 974.6  | 1043.0 | 1029.3 | 991.7  |
| 22.5° | 2014.2 | 1898.8 | 1628.6 | 1352.5 | 1015.6 | 831.8  | 864.3  | 949.8  | 1005.4 | 1004.5 | 974.6  |
| 25°   | 2146.7 | 2001.3 | 1691.9 | 1357.6 | 933.6  | 776.3  | 830.1  | 907.9  | 953.2  | 951.5  | 926.7  |
| 27.5° | 2288.6 | 2123.6 | 1773.9 | 1370.4 | 863.5  | 743.8  | 789.9  | 850.6  | 890.0  | 888.3  | 866.9  |
| 30°   | 2487.8 | 2264.7 | 1852.6 | 1371.3 | 813.0  | 726.7  | 745.5  | 787.4  | 825.0  | 820.7  | 804.5  |
| 32.5° | 2729.7 | 2423.7 | 1918.4 | 1322.5 | 781.4  | 710.4  | 699.3  | 720.7  | 749.8  | 743.8  | 739.5  |
| 35°   | 3022.1 | 2612.6 | 1974.8 | 1215.7 | 732.7  | 677.9  | 648.0  | 652.3  | 672.8  | 676.2  | 674.5  |
| 37.5° | 3355.5 | 2837.5 | 2044.9 | 1074.6 | 666.8  | 630.9  | 590.7  | 587.3  | 599.3  | 610.4  | 619.0  |
| 40°   | 3684.7 | 3090.5 | 2139.8 | 931.9  | 607.0  | 571.1  | 532.6  | 524.1  | 529.2  | 548.9  | 566.8  |
| 42.5° | 4054.8 | 3383.7 | 2242.4 | 809.6  | 566.0  | 505.3  | 468.5  | 452.2  | 466.8  | 498.4  | 519.8  |
| 45°   | 4588.3 | 3795.0 | 2342.5 | 712.1  | 548.9  | 447.1  | 397.5  | 395.8  | 412.1  | 453.1  | 477.0  |
| 47.5° | 5337.2 | 4326.7 | 2408.3 | 636.1  | 548.0  | 401.8  | 342.8  | 353.1  | 371.9  | 412.1  | 439.4  |
| 50°   | 6067.3 | 4992.7 | 2335.6 | 577.9  | 530.0  | 371.9  | 301.8  | 322.3  | 341.1  | 376.2  | 404.4  |
| 52.5° | 6507.6 | 5350.9 | 2052.6 | 523.2  | 474.5  | 358.2  | 261.6  | 297.5  | 300.9  | 332.6  | 362.5  |
| 55°   | 6461.4 | 5119.2 | 1572.2 | 438.6  | 392.4  | 338.5  | 219.7  | 268.4  | 270.2  | 294.1  | 319.7  |
| 57.5° | 5608.2 | 4395.1 | 1079.8 | 355.6  | 294.9  | 279.6  | 181.2  | 226.6  | 242.8  | 257.3  | 276.1  |
| 60°   | 4179.7 | 3206.8 | 481.3  | 289.0  | 187.2  | 188.9  | 154.7  | 171.0  | 195.8  | 212.9  | 229.1  |
| 62.5° | 2463.0 | 1844.9 | 195.8  | 173.5  | 103.4  | 118.8  | 124.8  | 124.8  | 140.2  | 153.0  | 163.3  |
| 65°   | 931.0  | 645.5  | 79.5   | 87.2   | 53.9   | 55.6   | 73.5   | 90.6   | 102.6  | 113.7  | 127.4  |
| 67.5° | 163.3  | 112.8  | 41.0   | 32.5   | 31.6   | 28.2   | 37.6   | 59.0   | 65.8   | 74.4   | 80.4   |
| 70°   | 27.4   | 23.1   | 17.1   | 16.2   | 14.5   | 15.4   | 24.8   | 41.9   | 46.2   | 48.7   | 51.3   |
| 72.5° | 7.7    | 6.8    | 5.1    | 4.3    | 3.4    | 4.3    | 15.4   | 32.5   | 34.2   | 35.9   | 38.5   |
| 75°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 6.0    | 23.1   | 24.8   | 25.6   | 28.2   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 5.1    | 6.8    | 8.5    | 6.8    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P633973  
 CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 |
| 2.5°  | 1008.8 | 991.7  | 982.3  | 977.2  | 977.2  | 970.3  | 962.6  | 960.1  | 971.2  | 971.2  | 990.0  |
| 5°    | 908.8  | 895.1  | 879.7  | 870.3  | 855.8  | 858.3  | 849.8  | 848.9  | 860.0  | 865.2  | 884.8  |
| 7.5°  | 839.5  | 822.4  | 813.0  | 807.0  | 799.3  | 795.9  | 788.2  | 785.7  | 791.6  | 800.2  | 819.0  |
| 10°   | 793.4  | 790.8  | 789.9  | 794.2  | 794.2  | 789.9  | 783.1  | 778.8  | 780.5  | 796.8  | 818.2  |
| 12.5° | 805.3  | 810.5  | 812.2  | 819.0  | 822.4  | 819.0  | 813.9  | 815.6  | 826.7  | 856.6  | 888.3  |
| 15°   | 857.5  | 853.2  | 851.5  | 854.9  | 857.5  | 854.1  | 852.3  | 865.2  | 903.6  | 946.4  | 982.3  |
| 17.5° | 913.0  | 885.7  | 873.7  | 873.7  | 875.4  | 873.7  | 875.4  | 900.2  | 962.6  | 1005.4 | 1031.9 |
| 20°   | 941.3  | 890.8  | 872.0  | 867.7  | 871.2  | 872.0  | 878.0  | 906.2  | 974.6  | 1004.5 | 1010.5 |
| 22.5° | 932.7  | 869.4  | 848.1  | 844.7  | 848.1  | 851.5  | 857.5  | 881.4  | 945.5  | 960.9  | 958.4  |
| 25°   | 890.0  | 827.6  | 810.5  | 810.5  | 818.2  | 817.3  | 819.9  | 837.0  | 890.0  | 899.4  | 895.1  |
| 27.5° | 836.1  | 777.1  | 762.6  | 771.1  | 778.0  | 776.3  | 777.1  | 791.6  | 831.0  | 833.5  | 829.3  |
| 30°   | 781.4  | 730.1  | 716.4  | 726.7  | 736.1  | 734.4  | 735.2  | 749.8  | 774.6  | 772.0  | 766.0  |
| 32.5° | 725.8  | 688.2  | 677.9  | 683.9  | 698.5  | 696.8  | 700.2  | 715.6  | 725.0  | 713.9  | 707.0  |
| 35°   | 674.5  | 654.9  | 647.2  | 650.6  | 661.7  | 664.3  | 670.3  | 680.5  | 680.5  | 666.8  | 654.9  |
| 37.5° | 626.7  | 624.1  | 619.0  | 614.7  | 624.9  | 632.6  | 641.2  | 653.2  | 636.1  | 616.4  | 605.3  |
| 40°   | 582.2  | 593.3  | 586.5  | 575.4  | 581.3  | 592.5  | 609.6  | 619.0  | 598.4  | 578.8  | 560.0  |
| 42.5° | 541.2  | 560.0  | 557.4  | 543.7  | 548.9  | 559.1  | 578.8  | 586.5  | 562.5  | 540.3  | 522.4  |
| 45°   | 501.8  | 528.3  | 530.0  | 512.9  | 518.1  | 528.3  | 551.4  | 554.0  | 523.2  | 499.3  | 486.4  |
| 47.5° | 467.6  | 496.7  | 497.6  | 484.7  | 486.4  | 501.0  | 522.4  | 523.2  | 488.2  | 465.9  | 449.7  |
| 50°   | 435.2  | 468.5  | 471.1  | 459.9  | 461.7  | 478.8  | 496.7  | 493.3  | 455.7  | 432.6  | 418.1  |
| 52.5° | 395.8  | 441.1  | 447.1  | 442.0  | 448.8  | 462.5  | 473.6  | 461.7  | 418.1  | 395.0  | 382.1  |
| 55°   | 353.1  | 412.1  | 424.9  | 421.5  | 429.2  | 440.3  | 442.8  | 435.2  | 380.4  | 357.4  | 345.4  |
| 57.5° | 303.5  | 339.4  | 361.6  | 354.8  | 360.8  | 371.9  | 379.6  | 373.6  | 332.6  | 314.6  | 304.3  |
| 60°   | 251.3  | 275.3  | 280.4  | 269.3  | 264.2  | 283.8  | 301.8  | 294.1  | 259.0  | 247.9  | 236.0  |
| 62.5° | 183.8  | 211.2  | 214.6  | 200.0  | 194.1  | 215.4  | 230.8  | 223.1  | 184.7  | 172.7  | 163.3  |
| 65°   | 147.0  | 172.7  | 179.5  | 165.9  | 162.4  | 178.7  | 188.1  | 169.3  | 141.9  | 129.1  | 118.8  |
| 67.5° | 96.6   | 117.1  | 135.1  | 134.2  | 127.4  | 132.5  | 125.7  | 110.3  | 90.6   | 83.8   | 76.9   |
| 70°   | 59.8   | 71.8   | 82.9   | 87.2   | 86.3   | 84.6   | 75.2   | 64.1   | 58.1   | 55.6   | 52.1   |
| 72.5° | 46.2   | 58.1   | 66.7   | 69.2   | 70.1   | 67.5   | 59.8   | 49.6   | 43.6   | 40.2   | 37.6   |
| 75°   | 34.2   | 43.6   | 50.4   | 53.9   | 55.6   | 53.9   | 46.2   | 39.3   | 33.3   | 30.8   | 28.2   |
| 77.5° | 12.0   | 14.5   | 18.0   | 19.7   | 18.8   | 18.0   | 16.2   | 16.2   | 12.8   | 12.0   | 10.3   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P633973  
 CATALOG NUMBER: GWS-SA2F-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 | 1118.2 |
| 2.5°  | 1011.4 | 1026.7 | 1055.0 | 1080.6 | 1108.0 | 1136.2 | 1167.0 | 1198.6 | 1213.1 | 1211.4 |
| 5°    | 914.8  | 948.1  | 994.3  | 1044.7 | 1101.1 | 1161.8 | 1229.4 | 1298.6 | 1328.5 | 1341.4 |
| 7.5°  | 854.1  | 901.1  | 961.8  | 1025.9 | 1100.3 | 1186.6 | 1288.4 | 1396.9 | 1440.5 | 1455.1 |
| 10°   | 861.8  | 916.5  | 966.9  | 1029.3 | 1108.8 | 1220.8 | 1347.3 | 1476.4 | 1527.7 | 1544.0 |
| 12.5° | 924.2  | 936.1  | 949.8  | 1001.1 | 1101.1 | 1246.5 | 1401.2 | 1555.1 | 1614.1 | 1630.3 |
| 15°   | 980.6  | 925.0  | 899.4  | 946.4  | 1073.8 | 1264.4 | 1455.9 | 1639.7 | 1704.7 | 1723.5 |
| 17.5° | 983.1  | 899.4  | 842.1  | 878.8  | 1029.3 | 1272.1 | 1509.8 | 1726.1 | 1797.0 | 1815.0 |
| 20°   | 951.5  | 871.2  | 797.6  | 798.5  | 968.6  | 1270.4 | 1554.2 | 1803.9 | 1883.4 | 1899.6 |
| 22.5° | 905.4  | 837.8  | 761.7  | 735.2  | 903.6  | 1267.0 | 1603.0 | 1886.8 | 1973.1 | 1988.5 |
| 25°   | 854.1  | 795.1  | 727.5  | 687.3  | 838.7  | 1270.4 | 1671.4 | 1995.4 | 2090.3 | 2104.8 |
| 27.5° | 798.5  | 748.0  | 701.0  | 668.5  | 784.0  | 1283.2 | 1753.4 | 2133.9 | 2246.7 | 2262.1 |
| 30°   | 740.4  | 702.7  | 683.9  | 664.3  | 749.8  | 1286.6 | 1842.3 | 2295.4 | 2438.2 | 2459.6 |
| 32.5° | 683.1  | 662.6  | 663.4  | 666.8  | 717.3  | 1262.7 | 1923.6 | 2475.0 | 2665.6 | 2699.8 |
| 35°   | 630.1  | 624.1  | 641.2  | 658.3  | 670.3  | 1201.2 | 1994.5 | 2687.0 | 2946.9 | 2981.9 |
| 37.5° | 584.8  | 589.9  | 611.3  | 628.4  | 619.0  | 1114.0 | 2088.6 | 2952.0 | 3261.5 | 3291.4 |
| 40°   | 541.2  | 554.0  | 578.8  | 586.5  | 579.6  | 1012.2 | 2201.4 | 3207.6 | 3534.2 | 3575.2 |
| 42.5° | 501.0  | 510.4  | 545.4  | 547.1  | 568.5  | 908.8  | 2310.0 | 3482.9 | 3848.0 | 3869.3 |
| 45°   | 468.5  | 466.8  | 502.7  | 513.8  | 583.1  | 794.2  | 2416.0 | 3849.7 | 4258.3 | 4289.1 |
| 47.5° | 436.9  | 435.2  | 443.7  | 494.1  | 589.0  | 688.2  | 2521.1 | 4386.6 | 4853.3 | 4906.3 |
| 50°   | 406.9  | 409.5  | 383.0  | 484.7  | 556.5  | 607.0  | 2569.0 | 4883.3 | 5394.5 | 5416.7 |
| 52.5° | 380.4  | 371.0  | 324.9  | 454.0  | 487.3  | 530.0  | 2433.1 | 5109.0 | 5729.6 | 5792.9 |
| 55°   | 342.8  | 290.7  | 267.6  | 368.5  | 384.7  | 462.5  | 1992.8 | 4978.2 | 5758.7 | 5870.7 |
| 57.5° | 293.2  | 228.3  | 227.4  | 271.9  | 271.9  | 429.2  | 1276.4 | 4253.2 | 4962.8 | 5159.4 |
| 60°   | 225.7  | 177.0  | 188.1  | 188.9  | 174.4  | 312.9  | 716.4  | 3081.1 | 3669.3 | 3865.1 |
| 62.5° | 160.7  | 135.1  | 141.9  | 112.8  | 100.0  | 156.4  | 343.7  | 1773.9 | 2264.7 | 2292.0 |
| 65°   | 107.7  | 91.5   | 74.4   | 62.4   | 61.6   | 66.7   | 141.9  | 641.2  | 779.7  | 879.7  |
| 67.5° | 71.0   | 55.6   | 39.3   | 39.3   | 44.5   | 44.5   | 53.9   | 106.0  | 148.8  | 135.9  |
| 70°   | 46.2   | 38.5   | 24.8   | 23.9   | 29.1   | 29.1   | 27.4   | 29.1   | 30.8   | 30.8   |
| 72.5° | 34.2   | 29.1   | 14.5   | 12.8   | 16.2   | 17.1   | 15.4   | 14.5   | 14.5   | 14.5   |
| 75°   | 25.6   | 20.5   | 8.5    | 6.0    | 7.7    | 10.3   | 8.5    | 6.0    | 6.0    | 5.1    |
| 77.5° | 10.3   | 7.7    | 3.4    | 2.6    | 4.3    | 6.0    | 5.1    | 2.6    | 1.7    | 1.7    |
| 80°   | 0.9    | 1.7    | 1.7    | 1.7    | 2.6    | 3.4    | 4.3    | 1.7    | 0.9    | 0.9    |
| 82.5° | 0.0    | 0.9    | 0.9    | 0.9    | 1.7    | 2.6    | 3.4    | 1.7    | 0.9    | 0.9    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 1.7    | 2.6    | 1.7    | 0.9    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.9    | 2.6    | 1.7    | 0.9    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**


Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360               | 0                      | 0.0                     | 490               | 18018                  | 2.6                     | 620               | 87426                  | 22.8                    | 750               | 2680                   | 0.0                     | 880               | 58                     | 0.0                     |
| 365               | 0                      | 0.0                     | 495               | 22295                  | 3.9                     | 625               | 83013                  | 18.2                    | 755               | 2287                   | 0.0                     | 885               | 46                     | 0.0                     |
| 370               | 0                      | 0.0                     | 500               | 26478                  | 5.8                     | 630               | 78077                  | 14.1                    | 760               | 1944                   | 0.0                     | 890               | 45                     | 0.0                     |
| 375               | 0                      | 0.0                     | 505               | 30524                  | 8.5                     | 635               | 72080                  | 10.7                    | 765               | 1653                   | 0.0                     | 895               | 41                     | 0.0                     |
| 380               | 0                      | 0.0                     | 510               | 33611                  | 11.5                    | 640               | 66249                  | 7.9                     | 770               | 1413                   | 0.0                     | 900               | 38                     | 0.0                     |
| 385               | 0                      | 0.0                     | 515               | 36490                  | 15.2                    | 645               | 59973                  | 5.7                     | 775               | 1198                   | 0.0                     | 905               | 33                     | 0.0                     |
| 390               | 0                      | 0.0                     | 520               | 38610                  | 18.7                    | 650               | 53972                  | 3.9                     | 780               | 1025                   | 0.0                     | 910               | 30                     | 0.0                     |
| 395               | 0                      | 0.0                     | 525               | 40511                  | 21.9                    | 655               | 48369                  | 2.7                     | 785               | 874                    | 0.0                     | 915               | 23                     | 0.0                     |
| 400               | 48                     | 0.0                     | 530               | 42223                  | 24.9                    | 660               | 42641                  | 1.8                     | 790               | 747                    | 0.0                     | 920               | 24                     | 0.0                     |
| 405               | 201                    | 0.0                     | 535               | 44137                  | 27.6                    | 665               | 37602                  | 1.1                     | 795               | 639                    | 0.0                     | 925               | 22                     | 0.0                     |
| 410               | 457                    | 0.0                     | 540               | 46032                  | 30.0                    | 670               | 32798                  | 0.7                     | 800               | 547                    | 0.0                     | 930               | 22                     | 0.0                     |
| 415               | 925                    | 0.0                     | 545               | 48553                  | 32.5                    | 675               | 28558                  | 0.5                     | 805               | 473                    | 0.0                     | 935               | 17                     | 0.0                     |
| 420               | 1816                   | 0.0                     | 550               | 51408                  | 34.9                    | 680               | 24782                  | 0.3                     | 810               | 401                    | 0.0                     | 940               | 13                     | 0.0                     |
| 425               | 3217                   | 0.0                     | 555               | 54711                  | 37.4                    | 685               | 21386                  | 0.2                     | 815               | 351                    | 0.0                     | 945               | 6                      | 0.0                     |
| 430               | 5520                   | 0.0                     | 560               | 58847                  | 40.0                    | 690               | 18413                  | 0.1                     | 820               | 307                    | 0.0                     | 950               | 10                     | 0.0                     |
| 435               | 9225                   | 0.1                     | 565               | 63386                  | 42.4                    | 695               | 15721                  | 0.1                     | 825               | 261                    | 0.0                     | 955               | 11                     | 0.0                     |
| 440               | 15522                  | 0.2                     | 570               | 68196                  | 44.3                    | 700               | 13432                  | 0.0                     | 830               | 228                    | 0.0                     | 960               | 8                      | 0.0                     |
| 445               | 27642                  | 0.6                     | 575               | 73613                  | 46.0                    | 705               | 11513                  | 0.0                     | 835               | 193                    | 0.0                     | 965               | 12                     | 0.0                     |
| 450               | 36602                  | 0.9                     | 580               | 79207                  | 47.1                    | 710               | 9780                   | 0.0                     | 840               | 174                    | 0.0                     | 970               | 3                      | 0.0                     |
| 455               | 28292                  | 0.9                     | 585               | 84248                  | 47.0                    | 715               | 8356                   | 0.0                     | 845               | 151                    | 0.0                     | 975               | 8                      | 0.0                     |
| 460               | 21166                  | 0.9                     | 590               | 88397                  | 45.7                    | 720               | 7161                   | 0.0                     | 850               | 123                    | 0.0                     | 980               | 2                      | 0.0                     |
| 465               | 19092                  | 1.0                     | 595               | 91428                  | 43.4                    | 725               | 6067                   | 0.0                     | 855               | 106                    | 0.0                     | 985               | 13                     | 0.0                     |
| 470               | 14951                  | 0.9                     | 600               | 93452                  | 40.3                    | 730               | 5164                   | 0.0                     | 860               | 95                     | 0.0                     | 990               | 16                     | 0.0                     |
| 475               | 12606                  | 1.0                     | 605               | 93959                  | 36.4                    | 735               | 4393                   | 0.0                     | 865               | 82                     | 0.0                     | 995               | 20                     | 0.0                     |
| 480               | 13323                  | 1.3                     | 610               | 93079                  | 32.0                    | 740               | 3694                   | 0.0                     | 870               | 77                     | 0.0                     | 1000              | 0                      | 0.0                     |
| 485               | 15164                  | 1.8                     | 615               | 90707                  | 27.3                    | 745               | 3157                   | 0.0                     | 875               | 65                     | 0.0                     |                   |                        |                         |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**


**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |



REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$



**Color Vector Graphics**




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)