

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636439

Luminaire Tested: GWS-SA3F-827-U-SL3-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P636439  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-33)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA3F-827-U-SL3-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (48) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 15052.3 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B3 - U0 - G2  
  
Input Watts (W): 183.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P636439  
 CATALOG NUMBER: GWS-SA3F-827-U-SL3-W-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.2 fc  
 Type II - Short - N/A

REPORT NUMBER: P636439  
CATALOG NUMBER: GWS-SA3F-827-U-SL3-W-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 54-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636439  
 CATALOG NUMBER: GWS-SA3F-827-U-SL3-W-GRSWH


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 4375.9   | 0.0    | 4375.9  |
|                    | % Fixture | 29.1     | 0.0    | 29.1    |
| <b>Street Side</b> | Lumens    | 10676.4  | 0.0    | 10676.4 |
|                    | % Fixture | 70.9     | 0.0    | 70.9    |
| <b>Total</b>       | Lumens    | 15052.3  | 0.0    | 15052.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 508.0   | 3.4       |
| 10°-20°   | 1212.1  | 8.1       |
| 20°-30°   | 1677.3  | 11.1      |
| 30°-40°   | 2330.6  | 15.5      |
| 40°-50°   | 3078.0  | 20.4      |
| 50°-60°   | 3657.8  | 24.3      |
| 60°-70°   | 2026.5  | 13.5      |
| 70°-80°   | 504.6   | 3.4       |
| 80°-90°   | 57.4    | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 15052.3 | 100.0     |
| 0°-180°   | 15052.3 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P636439


CATALOG NUMBER: GWS-SA3F-827-U-SL3-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 2048.9 | 13.6      |                         |      |         |
| FM (30°-60°)   | 6907.7 | 45.9      |                         |      |         |
| FH (60°-80°)   | 1701.9 | 11.3      |                         |      | G1/1800 |
| FVH (80°-90°)  | 18.0   | 0.1       |                         |      | G1/100  |
| BL (0°-30°)    | 1348.5 | 9.0       | B3/2500                 |      |         |
| BM (30°-60°)   | 2158.7 | 14.3      | B2/2500                 |      |         |
| BH (60°-80°)   | 829.2  | 5.5       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 39.4   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type II Short





REPORT NUMBER: P636439

CATALOG NUMBER: GWS-SA3F-827-U-SL3-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 54°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 |
| 2.5°  | 5670.7 | 5682.3 | 5690.0 | 5717.1 | 5740.3 | 5760.9 | 5782.8 | 5782.8 | 5781.5 | 5777.6 | 5769.9 |
| 5°    | 5446.5 | 5459.4 | 5477.4 | 5514.8 | 5565.0 | 5601.1 | 5660.4 | 5665.5 | 5691.3 | 5701.6 | 5696.5 |
| 7.5°  | 5186.2 | 5190.1 | 5213.3 | 5262.2 | 5342.1 | 5406.5 | 5491.6 | 5501.9 | 5563.7 | 5599.8 | 5593.4 |
| 10°   | 4901.5 | 4888.6 | 4929.8 | 5002.0 | 5106.3 | 5214.6 | 5324.1 | 5333.1 | 5432.3 | 5500.6 | 5495.4 |
| 12.5° | 4641.2 | 4642.5 | 4683.7 | 4771.3 | 4901.5 | 5035.5 | 5182.3 | 5203.0 | 5325.4 | 5413.0 | 5404.0 |
| 15°   | 4423.4 | 4428.6 | 4478.8 | 4578.0 | 4726.2 | 4886.0 | 5069.0 | 5088.3 | 5242.9 | 5358.9 | 5333.1 |
| 17.5° | 4249.5 | 4254.6 | 4298.4 | 4411.8 | 4570.3 | 4763.6 | 4986.5 | 5005.8 | 5197.8 | 5335.7 | 5282.8 |
| 20°   | 4129.6 | 4127.1 | 4169.6 | 4277.8 | 4441.5 | 4651.5 | 4914.3 | 4942.7 | 5183.6 | 5344.7 | 5249.3 |
| 22.5° | 4080.7 | 4079.4 | 4110.3 | 4199.2 | 4352.6 | 4565.2 | 4870.5 | 4909.2 | 5199.1 | 5384.6 | 5228.7 |
| 25°   | 4105.2 | 4100.0 | 4127.1 | 4192.8 | 4315.2 | 4531.7 | 4883.4 | 4924.6 | 5264.8 | 5467.1 | 5232.6 |
| 27.5° | 4181.2 | 4174.7 | 4197.9 | 4257.2 | 4350.0 | 4566.4 | 4973.6 | 5021.3 | 5404.0 | 5617.9 | 5284.1 |
| 30°   | 4297.1 | 4293.3 | 4316.5 | 4373.2 | 4454.3 | 4682.4 | 5146.3 | 5200.4 | 5619.1 | 5852.4 | 5396.2 |
| 32.5° | 4432.4 | 4426.0 | 4467.2 | 4532.9 | 4627.0 | 4893.7 | 5378.2 | 5449.1 | 5874.3 | 6153.9 | 5584.4 |
| 35°   | 4584.5 | 4579.3 | 4636.0 | 4731.4 | 4866.7 | 5187.5 | 5659.1 | 5736.4 | 6134.5 | 6495.3 | 5834.3 |
| 37.5° | 4732.7 | 4732.7 | 4842.2 | 4983.9 | 5154.0 | 5507.0 | 5923.2 | 5972.2 | 6314.9 | 6798.1 | 6102.3 |
| 40°   | 4864.1 | 4871.8 | 5036.7 | 5249.3 | 5465.8 | 5795.7 | 6097.2 | 6138.4 | 6394.8 | 7006.9 | 6335.6 |
| 42.5° | 5009.7 | 5016.1 | 5208.1 | 5486.4 | 5744.1 | 6028.9 | 6202.8 | 6223.5 | 6410.3 | 7111.2 | 6500.5 |
| 45°   | 5125.7 | 5134.7 | 5373.0 | 5670.7 | 5986.4 | 6204.1 | 6286.6 | 6304.6 | 6432.2 | 7167.9 | 6620.3 |
| 47.5° | 5186.2 | 5199.1 | 5472.3 | 5818.9 | 6150.0 | 6361.3 | 6424.5 | 6432.2 | 6522.4 | 7267.1 | 6764.6 |
| 50°   | 5175.9 | 5201.7 | 5509.6 | 5892.3 | 6271.1 | 6519.8 | 6646.1 | 6659.0 | 6706.6 | 7412.7 | 6933.4 |
| 52.5° | 5267.4 | 5279.0 | 5589.5 | 5979.9 | 6443.8 | 6812.3 | 7031.3 | 7049.4 | 7027.5 | 7522.3 | 7033.9 |
| 55°   | 5115.3 | 5170.7 | 5490.3 | 5967.0 | 6706.6 | 7264.6 | 7602.1 | 7593.1 | 7318.7 | 7644.7 | 7201.4 |
| 57.5° | 4137.4 | 4218.5 | 4511.0 | 5065.1 | 6273.7 | 7581.5 | 8028.6 | 8006.7 | 7544.2 | 7738.7 | 7383.1 |
| 60°   | 2864.3 | 2877.2 | 3141.4 | 3534.4 | 4842.2 | 6697.6 | 7903.7 | 7951.3 | 7585.4 | 7620.2 | 7046.8 |
| 62.5° | 2291.0 | 2287.1 | 2311.6 | 2321.9 | 3079.5 | 4708.2 | 6238.9 | 6412.9 | 6302.1 | 5937.4 | 4994.2 |
| 65°   | 1955.9 | 1970.1 | 2042.3 | 2004.9 | 2010.1 | 2651.7 | 3727.6 | 3752.1 | 3674.8 | 3543.4 | 2641.4 |
| 67.5° | 1530.7 | 1555.2 | 1682.8 | 1828.4 | 1782.0 | 1707.3 | 1934.0 | 1922.4 | 1515.3 | 1172.5 | 969.0  |
| 70°   | 958.6  | 974.1  | 1110.7 | 1435.4 | 1551.4 | 1401.9 | 1243.4 | 1238.2 | 811.8  | 667.4  | 731.9  |
| 72.5° | 559.2  | 561.8  | 600.4  | 800.2  | 1029.5 | 958.6  | 914.8  | 881.3  | 521.8  | 532.2  | 583.7  |
| 75°   | 308.0  | 308.0  | 306.7  | 345.3  | 405.9  | 359.5  | 347.9  | 338.9  | 349.2  | 395.6  | 434.2  |
| 77.5° | 64.4   | 65.7   | 69.6   | 91.5   | 118.5  | 144.3  | 181.7  | 183.0  | 228.1  | 264.1  | 295.1  |
| 80°   | 29.6   | 30.9   | 38.7   | 49.0   | 63.1   | 83.8   | 110.8  | 112.1  | 137.9  | 166.2  | 186.8  |
| 82.5° | 15.5   | 16.8   | 20.6   | 25.8   | 33.5   | 43.8   | 61.8   | 61.8   | 82.5   | 97.9   | 110.8  |
| 85°   | 5.2    | 5.2    | 7.7    | 10.3   | 14.2   | 18.0   | 24.5   | 24.5   | 36.1   | 47.7   | 55.4   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 1.3    | 2.6    | 5.2    | 5.2    | 6.4    | 7.7    | 12.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P636439

CATALOG NUMBER: GWS-SA3F-827-U-SL3-W-GRSWH

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 | 5778.9 |
| 2.5°  | 5753.1 | 5713.2 | 5714.5 | 5722.2 | 5697.7 | 5660.4 | 5635.9 | 5605.0 | 5585.6 | 5581.8 | 5596.0 |
| 5°    | 5670.7 | 5624.3 | 5592.1 | 5558.6 | 5489.0 | 5406.5 | 5342.1 | 5289.3 | 5254.5 | 5241.6 | 5226.2 |
| 7.5°  | 5557.3 | 5496.7 | 5415.6 | 5321.5 | 5195.2 | 5048.3 | 4945.3 | 4848.6 | 4781.6 | 4762.3 | 4753.3 |
| 10°   | 5443.9 | 5356.3 | 5212.0 | 5036.7 | 4826.7 | 4628.3 | 4441.5 | 4298.4 | 4185.0 | 4120.6 | 4141.2 |
| 12.5° | 5326.7 | 5218.4 | 4992.9 | 4723.6 | 4431.1 | 4132.2 | 3887.4 | 3650.3 | 3467.4 | 3375.9 | 3348.8 |
| 15°   | 5223.6 | 5076.7 | 4762.3 | 4397.6 | 4008.5 | 3632.3 | 3277.9 | 2922.3 | 2690.4 | 2564.1 | 2529.3 |
| 17.5° | 5136.0 | 4945.3 | 4518.8 | 4065.2 | 3600.1 | 3064.1 | 2628.5 | 2298.7 | 2140.2 | 2070.6 | 2065.5 |
| 20°   | 5049.6 | 4816.4 | 4277.8 | 3707.0 | 3128.5 | 2528.0 | 2138.9 | 1984.3 | 1927.6 | 1903.1 | 1901.8 |
| 22.5° | 4972.3 | 4681.1 | 4024.0 | 3348.8 | 2659.5 | 2124.7 | 1910.8 | 1843.8 | 1828.4 | 1828.4 | 1825.8 |
| 25°   | 4906.6 | 4545.8 | 3763.7 | 2968.7 | 2235.5 | 1891.5 | 1792.3 | 1764.0 | 1770.4 | 1782.0 | 1783.3 |
| 27.5° | 4879.5 | 4440.2 | 3512.4 | 2578.3 | 1943.1 | 1756.2 | 1711.1 | 1707.3 | 1725.3 | 1743.3 | 1745.9 |
| 30°   | 4907.9 | 4368.0 | 3254.7 | 2204.6 | 1767.8 | 1673.8 | 1653.1 | 1660.9 | 1682.8 | 1700.8 | 1700.8 |
| 32.5° | 4995.5 | 4331.9 | 2991.9 | 1931.5 | 1666.0 | 1615.8 | 1609.3 | 1617.1 | 1633.8 | 1644.1 | 1645.4 |
| 35°   | 5143.7 | 4346.1 | 2720.0 | 1747.2 | 1600.3 | 1573.3 | 1572.0 | 1577.1 | 1583.6 | 1590.0 | 1591.3 |
| 37.5° | 5330.5 | 4409.2 | 2428.8 | 1640.3 | 1557.8 | 1542.3 | 1539.8 | 1538.5 | 1539.8 | 1539.8 | 1541.0 |
| 40°   | 5513.5 | 4504.6 | 2168.5 | 1577.1 | 1528.2 | 1515.3 | 1508.8 | 1499.8 | 1498.5 | 1495.9 | 1494.7 |
| 42.5° | 5648.8 | 4578.0 | 1961.1 | 1532.0 | 1501.1 | 1485.6 | 1477.9 | 1463.7 | 1462.4 | 1461.2 | 1459.9 |
| 45°   | 5750.6 | 4639.9 | 1788.4 | 1488.2 | 1472.8 | 1458.6 | 1441.8 | 1428.9 | 1431.5 | 1434.1 | 1434.1 |
| 47.5° | 5865.2 | 4694.0 | 1662.2 | 1447.0 | 1438.0 | 1423.8 | 1403.2 | 1394.2 | 1403.2 | 1412.2 | 1412.2 |
| 50°   | 6004.4 | 4770.0 | 1559.1 | 1405.8 | 1401.9 | 1385.1 | 1367.1 | 1363.2 | 1373.5 | 1386.4 | 1386.4 |
| 52.5° | 6106.2 | 4835.7 | 1485.6 | 1364.5 | 1364.5 | 1342.6 | 1327.2 | 1325.9 | 1337.5 | 1350.3 | 1351.6 |
| 55°   | 6296.9 | 4989.1 | 1459.9 | 1316.8 | 1311.7 | 1294.9 | 1283.3 | 1274.3 | 1288.5 | 1300.1 | 1300.1 |
| 57.5° | 6512.1 | 5192.7 | 1466.3 | 1248.6 | 1242.1 | 1237.0 | 1227.9 | 1217.6 | 1221.5 | 1234.4 | 1235.7 |
| 60°   | 6055.9 | 4798.4 | 1395.4 | 1180.3 | 1176.4 | 1173.8 | 1162.2 | 1144.2 | 1149.3 | 1159.6 | 1160.9 |
| 62.5° | 4230.1 | 3189.0 | 1128.7 | 1095.2 | 1108.1 | 1106.8 | 1091.4 | 1070.7 | 1072.0 | 1086.2 | 1086.2 |
| 65°   | 2195.6 | 1725.3 | 990.9  | 1017.9 | 1037.2 | 1029.5 | 1003.7 | 985.7  | 983.1  | 1001.2 | 997.3  |
| 67.5° | 947.0  | 941.9  | 901.9  | 936.7  | 957.4  | 940.6  | 913.5  | 883.9  | 886.5  | 892.9  | 887.8  |
| 70°   | 762.8  | 786.0  | 802.7  | 840.1  | 856.9  | 825.9  | 796.3  | 779.5  | 765.4  | 764.1  | 755.1  |
| 72.5° | 609.5  | 641.7  | 679.0  | 717.7  | 722.8  | 691.9  | 654.6  | 639.1  | 617.2  | 615.9  | 606.9  |
| 75°   | 458.7  | 485.8  | 515.4  | 546.3  | 546.3  | 516.7  | 492.2  | 484.5  | 458.7  | 451.0  | 443.2  |
| 77.5° | 313.1  | 329.9  | 353.0  | 360.8  | 368.5  | 356.9  | 332.4  | 319.5  | 289.9  | 282.2  | 271.9  |
| 80°   | 197.1  | 208.7  | 222.9  | 228.1  | 235.8  | 221.6  | 202.3  | 188.1  | 167.5  | 161.1  | 155.9  |
| 82.5° | 118.5  | 126.3  | 135.3  | 137.9  | 144.3  | 134.0  | 116.0  | 105.7  | 94.1   | 88.9   | 85.0   |
| 85°   | 60.6   | 64.4   | 69.6   | 70.9   | 69.6   | 59.3   | 52.8   | 47.7   | 39.9   | 38.7   | 36.1   |
| 87.5° | 15.5   | 18.0   | 19.3   | 18.0   | 16.8   | 12.9   | 9.0    | 6.4    | 2.6    | 2.6    | 1.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 27.7                           | 620               | 87426                                | 1.1                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 36.0                           | 625               | 83013                                | 0.7                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 44.2                           | 630               | 78077                                | 0.4                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 51.8                           | 635               | 72080                                | 0.3                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 57.0                           | 640               | 66249                                | 0.2                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 60.5                           | 645               | 59973                                | 0.1                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 61.4                           | 650               | 53972                                | 0.1                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 60.6                           | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 58.2                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 55.0                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 50.9                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.1                            | 545               | 48553                                | 46.6                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.3                            | 550               | 51408                                | 42.0                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.8                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 1.9                            | 560               | 58847                                | 32.9                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 4.1                            | 565               | 63386                                | 28.4                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 8.7                            | 570               | 68196                                | 24.1                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 18.5                           | 575               | 73613                                | 20.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 28.3                           | 580               | 79207                                | 16.3                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 24.7                           | 585               | 84248                                | 12.9                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 20.4                           | 590               | 88397                                | 9.8                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 20.1                           | 595               | 91428                                | 7.3                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 17.2                           | 600               | 93452                                | 5.3                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 15.7                           | 605               | 93959                                | 3.7                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 18.0                           | 610               | 93079                                | 2.5                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 21.9                           | 615               | 90707                                | 1.7                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)