

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636446

Luminaire Tested: GWS-SA3F-827-U-SLL-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-40)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-827-U-SLL-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10882.7 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636446
 CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 4.8 fc
 Type III - Short - N/A

REPORT NUMBER: P636446
CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical



REPORT NUMBER: P636446
 CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1264.4 | 0.0 | 1264.4 |
| | % Fixture | 11.6 | 0.0 | 11.6 |
| Street Side | Lumens | 9618.3 | 0.0 | 9618.3 |
| | % Fixture | 88.4 | 0.0 | 88.4 |
| Total | Lumens | 10882.7 | 0.0 | 10882.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 48.7 | 0.4 |
| 10°-20° | 167.0 | 1.5 |
| 20°-30° | 377.4 | 3.5 |
| 30°-40° | 650.1 | 6.0 |
| 40°-50° | 1226.4 | 11.3 |
| 50°-60° | 2738.2 | 25.2 |
| 60°-70° | 3662.3 | 33.7 |
| 70°-80° | 1836.5 | 16.9 |
| 80°-90° | 176.0 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10882.7 | 100.0 |
| 0°-180° | 10882.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636446


CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 407.6 | 3.7 | | | |
| FM (30°-60°) | 3869.1 | 35.6 | | | |
| FH (60°-80°) | 5177.3 | 47.6 | | | G3/7500 |
| FVH (80°-90°) | 164.3 | 1.5 | | | G2/225 |
| BL (0°-30°) | 185.6 | 1.7 | B1/500 | | |
| BM (30°-60°) | 745.6 | 6.9 | B1/1000 | | |
| BH (60°-80°) | 321.5 | 3.0 | B1/500 | | G1/500 |
| BVH (80°-90°) | 11.7 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G3

Type III Short





REPORT NUMBER: P636446

CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 2° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 |
| 2.5° | 557.9 | 556.7 | 554.1 | 546.4 | 539.9 | 536.0 | 528.3 | 528.3 | 527.0 | 524.4 | 519.3 |
| 5° | 539.9 | 534.8 | 529.6 | 515.4 | 500.0 | 490.9 | 480.6 | 479.3 | 479.3 | 476.8 | 475.5 |
| 7.5° | 511.6 | 506.4 | 500.0 | 476.8 | 462.6 | 453.6 | 444.6 | 443.3 | 439.4 | 439.4 | 439.4 |
| 10° | 496.1 | 488.4 | 478.1 | 452.3 | 438.1 | 430.4 | 423.9 | 420.1 | 417.5 | 413.6 | 412.3 |
| 12.5° | 529.6 | 515.4 | 493.5 | 447.1 | 427.8 | 417.5 | 409.8 | 407.2 | 399.5 | 394.3 | 390.4 |
| 15° | 634.0 | 599.2 | 555.4 | 458.7 | 423.9 | 408.5 | 398.2 | 393.0 | 386.6 | 377.6 | 371.1 |
| 17.5° | 805.4 | 755.1 | 681.7 | 496.1 | 420.1 | 400.7 | 387.9 | 378.8 | 369.8 | 359.5 | 351.8 |
| 20° | 1042.5 | 967.7 | 880.1 | 564.4 | 420.1 | 391.7 | 376.3 | 364.7 | 351.8 | 340.2 | 331.2 |
| 22.5° | 1344.0 | 1269.2 | 1119.8 | 680.4 | 425.2 | 380.1 | 362.1 | 346.6 | 331.2 | 320.9 | 310.5 |
| 25° | 1681.6 | 1575.9 | 1436.8 | 820.8 | 439.4 | 364.7 | 345.3 | 329.9 | 315.7 | 302.8 | 291.2 |
| 27.5° | 2057.8 | 1943.2 | 1757.6 | 1020.5 | 470.3 | 349.2 | 327.3 | 313.1 | 300.2 | 287.4 | 271.9 |
| 30° | 2404.5 | 2336.2 | 2146.8 | 1260.2 | 520.6 | 338.9 | 313.1 | 300.2 | 287.4 | 270.6 | 256.4 |
| 32.5° | 2820.7 | 2699.5 | 2543.6 | 1533.4 | 587.6 | 328.6 | 301.5 | 283.5 | 273.2 | 257.7 | 242.3 |
| 35° | 3239.5 | 3136.4 | 2931.5 | 1869.7 | 662.3 | 318.3 | 287.4 | 270.6 | 261.6 | 243.5 | 226.8 |
| 37.5° | 3671.1 | 3647.9 | 3445.6 | 2242.1 | 735.8 | 306.7 | 270.6 | 260.3 | 251.3 | 230.7 | 211.3 |
| 40° | 4096.4 | 4053.8 | 3867.0 | 2667.3 | 780.9 | 293.8 | 256.4 | 250.0 | 239.7 | 216.5 | 194.6 |
| 42.5° | 4503.5 | 4471.3 | 4289.6 | 3074.5 | 774.4 | 282.2 | 242.3 | 234.5 | 226.8 | 203.6 | 176.5 |
| 45° | 5003.5 | 4950.7 | 4721.3 | 3376.0 | 708.7 | 295.1 | 228.1 | 215.2 | 213.9 | 192.0 | 158.5 |
| 47.5° | 5939.0 | 5765.0 | 5375.9 | 3608.0 | 643.0 | 328.6 | 212.6 | 197.2 | 206.2 | 180.4 | 140.5 |
| 50° | 7249.5 | 7044.6 | 6481.5 | 3788.4 | 641.7 | 372.4 | 210.0 | 180.4 | 199.7 | 171.4 | 125.0 |
| 52.5° | 8566.4 | 8205.6 | 7521.4 | 3885.0 | 689.4 | 404.6 | 233.2 | 163.6 | 192.0 | 162.4 | 113.4 |
| 55° | 9827.9 | 9079.2 | 7956.9 | 3565.5 | 726.8 | 439.4 | 275.8 | 154.6 | 177.8 | 152.1 | 107.0 |
| 57.5° | 11030.1 | 9781.5 | 8146.3 | 2820.7 | 851.7 | 453.6 | 301.5 | 158.5 | 157.2 | 139.2 | 101.8 |
| 60° | 11195.1 | 9748.0 | 7763.6 | 1640.3 | 939.4 | 429.1 | 291.2 | 176.5 | 137.9 | 123.7 | 92.8 |
| 62.5° | 10571.4 | 9099.9 | 6891.3 | 1023.1 | 872.4 | 420.1 | 259.0 | 201.0 | 125.0 | 109.5 | 81.2 |
| 65° | 9624.3 | 8083.2 | 5745.7 | 659.7 | 661.0 | 466.5 | 226.8 | 197.2 | 117.3 | 96.6 | 69.6 |
| 67.5° | 8143.7 | 6765.0 | 4526.7 | 442.0 | 373.7 | 398.2 | 198.4 | 135.3 | 114.7 | 82.5 | 54.1 |
| 70° | 5944.2 | 4815.4 | 2947.0 | 295.1 | 222.9 | 318.3 | 166.2 | 96.6 | 108.2 | 68.3 | 38.7 |
| 72.5° | 4345.0 | 3235.6 | 1645.5 | 193.3 | 126.3 | 185.6 | 122.4 | 69.6 | 83.8 | 50.3 | 27.1 |
| 75° | 3127.4 | 2226.6 | 939.4 | 123.7 | 83.8 | 101.8 | 79.9 | 47.7 | 54.1 | 39.9 | 24.5 |
| 77.5° | 1505.0 | 1085.0 | 426.5 | 68.3 | 56.7 | 51.5 | 42.5 | 29.6 | 33.5 | 36.1 | 21.9 |
| 80° | 56.7 | 42.5 | 32.2 | 33.5 | 36.1 | 23.2 | 19.3 | 15.5 | 19.3 | 24.5 | 11.6 |
| 82.5° | 0.0 | 0.0 | 0.0 | 3.9 | 5.2 | 6.4 | 7.7 | 6.4 | 7.7 | 9.0 | 1.3 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636446

CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 |
| 2.5° | 523.2 | 520.6 | 523.2 | 525.7 | 528.3 | 530.9 | 527.0 | 529.6 | 532.2 | 525.7 | 528.3 |
| 5° | 481.9 | 480.6 | 488.4 | 492.2 | 497.4 | 500.0 | 497.4 | 497.4 | 496.1 | 488.4 | 488.4 |
| 7.5° | 445.8 | 447.1 | 453.6 | 462.6 | 469.0 | 472.9 | 470.3 | 469.0 | 465.2 | 453.6 | 453.6 |
| 10° | 418.8 | 418.8 | 429.1 | 436.8 | 445.8 | 449.7 | 447.1 | 443.3 | 439.4 | 427.8 | 426.5 |
| 12.5° | 396.9 | 396.9 | 404.6 | 417.5 | 427.8 | 433.0 | 431.7 | 426.5 | 420.1 | 408.5 | 407.2 |
| 15° | 376.3 | 375.0 | 386.6 | 398.2 | 412.3 | 418.8 | 416.2 | 412.3 | 400.7 | 390.4 | 387.9 |
| 17.5° | 355.6 | 354.4 | 364.7 | 380.1 | 395.6 | 404.6 | 403.3 | 394.3 | 384.0 | 371.1 | 368.5 |
| 20° | 335.0 | 332.5 | 345.3 | 360.8 | 376.3 | 385.3 | 382.7 | 375.0 | 362.1 | 349.2 | 346.6 |
| 22.5° | 314.4 | 313.1 | 322.1 | 335.0 | 349.2 | 356.9 | 355.6 | 349.2 | 336.3 | 324.7 | 324.7 |
| 25° | 291.2 | 291.2 | 297.7 | 306.7 | 317.0 | 320.9 | 322.1 | 319.6 | 311.8 | 305.4 | 305.4 |
| 27.5° | 271.9 | 268.0 | 270.6 | 273.2 | 278.3 | 284.8 | 284.8 | 287.4 | 288.6 | 286.1 | 287.4 |
| 30° | 256.4 | 250.0 | 246.1 | 241.0 | 238.4 | 241.0 | 243.5 | 252.6 | 261.6 | 266.7 | 269.3 |
| 32.5° | 238.4 | 230.7 | 220.3 | 206.2 | 197.2 | 194.6 | 202.3 | 219.1 | 235.8 | 247.4 | 253.8 |
| 35° | 220.3 | 210.0 | 190.7 | 170.1 | 158.5 | 154.6 | 163.6 | 183.0 | 207.5 | 228.1 | 237.1 |
| 37.5° | 202.3 | 188.1 | 161.1 | 136.6 | 123.7 | 121.1 | 130.1 | 150.8 | 179.1 | 207.5 | 219.1 |
| 40° | 181.7 | 164.9 | 132.7 | 107.0 | 96.6 | 94.1 | 101.8 | 122.4 | 152.1 | 184.3 | 202.3 |
| 42.5° | 161.1 | 140.5 | 107.0 | 85.0 | 74.7 | 74.7 | 85.0 | 100.5 | 127.6 | 162.4 | 184.3 |
| 45° | 140.5 | 118.5 | 87.6 | 68.3 | 61.9 | 63.1 | 69.6 | 85.0 | 107.0 | 143.0 | 163.6 |
| 47.5° | 121.1 | 101.8 | 72.2 | 56.7 | 51.5 | 52.8 | 60.6 | 73.4 | 91.5 | 123.7 | 145.6 |
| 50° | 104.4 | 86.3 | 63.1 | 47.7 | 43.8 | 46.4 | 54.1 | 65.7 | 81.2 | 109.5 | 127.6 |
| 52.5° | 94.1 | 77.3 | 58.0 | 41.2 | 38.7 | 41.2 | 49.0 | 59.3 | 73.4 | 96.6 | 114.7 |
| 55° | 88.9 | 76.0 | 58.0 | 37.4 | 33.5 | 36.1 | 43.8 | 54.1 | 65.7 | 87.6 | 103.1 |
| 57.5° | 87.6 | 78.6 | 61.9 | 33.5 | 28.3 | 30.9 | 38.7 | 49.0 | 60.6 | 79.9 | 92.8 |
| 60° | 82.5 | 74.7 | 60.6 | 27.1 | 21.9 | 25.8 | 32.2 | 42.5 | 55.4 | 74.7 | 86.3 |
| 62.5° | 72.2 | 65.7 | 52.8 | 21.9 | 16.8 | 19.3 | 27.1 | 37.4 | 50.3 | 68.3 | 81.2 |
| 65° | 59.3 | 52.8 | 41.2 | 14.2 | 10.3 | 12.9 | 20.6 | 32.2 | 43.8 | 61.9 | 73.4 |
| 67.5° | 43.8 | 37.4 | 28.3 | 9.0 | 5.2 | 9.0 | 16.8 | 27.1 | 39.9 | 55.4 | 67.0 |
| 70° | 27.1 | 21.9 | 15.5 | 5.2 | 3.9 | 7.7 | 15.5 | 25.8 | 36.1 | 51.5 | 63.1 |
| 72.5° | 15.5 | 10.3 | 6.4 | 2.6 | 3.9 | 7.7 | 15.5 | 25.8 | 34.8 | 49.0 | 59.3 |
| 75° | 11.6 | 6.4 | 2.6 | 1.3 | 2.6 | 6.4 | 14.2 | 23.2 | 33.5 | 46.4 | 56.7 |
| 77.5° | 7.7 | 3.9 | 1.3 | 0.0 | 1.3 | 5.2 | 12.9 | 21.9 | 30.9 | 43.8 | 54.1 |
| 80° | 1.3 | 0.0 | 0.0 | 0.0 | 0.0 | 3.9 | 11.6 | 19.3 | 28.3 | 38.7 | 47.7 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.3 | 9.0 | 16.8 | 24.5 | 32.2 | 38.7 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 5.2 | 12.9 | 19.3 | 24.5 | 27.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 6.4 | 12.9 | 15.5 | 18.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636446
 CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|---------|---------|
| 0° | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 |
| 2.5° | 527.0 | 534.8 | 534.8 | 539.9 | 546.4 | 557.9 | 564.4 | 573.4 | 579.9 | 586.3 | 588.9 |
| 5° | 487.1 | 488.4 | 489.7 | 492.2 | 500.0 | 512.8 | 524.4 | 538.6 | 555.4 | 568.3 | 576.0 |
| 7.5° | 453.6 | 453.6 | 453.6 | 457.4 | 465.2 | 474.2 | 485.8 | 505.1 | 524.4 | 539.9 | 552.8 |
| 10° | 425.2 | 429.1 | 430.4 | 436.8 | 445.8 | 457.4 | 470.3 | 487.1 | 509.0 | 529.6 | 552.8 |
| 12.5° | 407.2 | 411.1 | 417.5 | 423.9 | 433.0 | 445.8 | 460.0 | 481.9 | 527.0 | 569.5 | 618.5 |
| 15° | 390.4 | 395.6 | 403.3 | 412.3 | 422.7 | 436.8 | 452.3 | 497.4 | 603.0 | 682.9 | 760.3 |
| 17.5° | 372.4 | 380.1 | 390.4 | 399.5 | 412.3 | 427.8 | 447.1 | 534.8 | 742.2 | 874.9 | 1006.4 |
| 20° | 349.2 | 359.5 | 371.1 | 385.3 | 400.7 | 418.8 | 447.1 | 612.1 | 943.2 | 1133.9 | 1307.9 |
| 22.5° | 327.3 | 337.6 | 351.8 | 369.8 | 387.9 | 405.9 | 453.6 | 729.3 | 1202.2 | 1443.2 | 1663.5 |
| 25° | 309.3 | 322.1 | 336.3 | 351.8 | 372.4 | 393.0 | 469.0 | 894.3 | 1514.1 | 1824.6 | 1980.5 |
| 27.5° | 292.5 | 308.0 | 322.1 | 335.0 | 353.1 | 376.3 | 503.8 | 1114.6 | 1882.6 | 2198.3 | 2320.7 |
| 30° | 275.8 | 293.8 | 308.0 | 320.9 | 338.9 | 363.4 | 556.7 | 1395.5 | 2292.4 | 2599.0 | 2611.9 |
| 32.5° | 261.6 | 278.3 | 295.1 | 308.0 | 324.7 | 353.1 | 630.1 | 1724.1 | 2712.4 | 3008.8 | 2887.7 |
| 35° | 246.1 | 265.4 | 280.9 | 295.1 | 313.1 | 344.0 | 715.2 | 2078.5 | 3136.4 | 3385.1 | 3162.1 |
| 37.5° | 230.7 | 252.6 | 271.9 | 282.2 | 300.2 | 335.0 | 777.0 | 2448.3 | 3569.3 | 3752.3 | 3403.1 |
| 40° | 216.5 | 241.0 | 262.9 | 273.2 | 282.2 | 323.4 | 786.0 | 2827.1 | 4008.7 | 4114.4 | 3629.9 |
| 42.5° | 201.0 | 228.1 | 247.4 | 261.6 | 269.3 | 315.7 | 731.9 | 3146.7 | 4377.3 | 4475.2 | 3926.3 |
| 45° | 184.3 | 216.5 | 231.9 | 242.3 | 257.7 | 320.9 | 662.3 | 3394.1 | 4798.6 | 4967.4 | 4414.6 |
| 47.5° | 167.5 | 203.6 | 216.5 | 224.2 | 244.8 | 351.8 | 636.6 | 3559.0 | 5493.2 | 5843.7 | 5238.0 |
| 50° | 152.1 | 192.0 | 206.2 | 204.9 | 242.3 | 391.7 | 664.9 | 3684.0 | 6536.9 | 6949.2 | 6366.8 |
| 52.5° | 135.3 | 179.1 | 195.9 | 190.7 | 261.6 | 422.7 | 721.6 | 3783.2 | 7339.7 | 8245.5 | 7883.5 |
| 55° | 121.1 | 164.9 | 180.4 | 179.1 | 297.7 | 445.8 | 765.4 | 3260.1 | 7672.1 | 9450.4 | 9592.1 |
| 57.5° | 110.8 | 149.5 | 162.4 | 184.3 | 320.9 | 445.8 | 885.2 | 2314.3 | 7678.6 | 10336.9 | 11860.0 |
| 60° | 101.8 | 135.3 | 144.3 | 202.3 | 311.8 | 422.7 | 876.2 | 1417.4 | 7076.8 | 10276.3 | 13066.1 |
| 62.5° | 94.1 | 122.4 | 134.0 | 207.5 | 275.8 | 418.8 | 791.2 | 878.8 | 6035.6 | 9494.2 | 12191.1 |
| 65° | 87.6 | 112.1 | 128.9 | 190.7 | 250.0 | 448.4 | 533.5 | 631.4 | 4895.3 | 8602.5 | 11187.3 |
| 67.5° | 81.2 | 103.1 | 136.6 | 155.9 | 226.8 | 400.7 | 385.3 | 448.4 | 3842.5 | 7624.5 | 10266.0 |
| 70° | 76.0 | 97.9 | 144.3 | 127.6 | 198.4 | 313.1 | 273.2 | 340.2 | 2941.8 | 6361.7 | 8968.4 |
| 72.5° | 72.2 | 91.5 | 121.1 | 100.5 | 161.1 | 242.3 | 190.7 | 247.4 | 1922.5 | 4966.1 | 7311.3 |
| 75° | 68.3 | 83.8 | 88.9 | 81.2 | 119.8 | 158.5 | 144.3 | 166.2 | 1145.5 | 3629.9 | 5547.3 |
| 77.5° | 67.0 | 78.6 | 72.2 | 65.7 | 81.2 | 94.1 | 109.5 | 112.1 | 559.2 | 1815.6 | 2907.0 |
| 80° | 59.3 | 70.9 | 61.9 | 54.1 | 55.4 | 61.9 | 81.2 | 74.7 | 127.6 | 461.3 | 775.7 |
| 82.5° | 46.4 | 55.4 | 51.5 | 45.1 | 45.1 | 45.1 | 54.1 | 50.3 | 41.2 | 207.5 | 350.5 |
| 85° | 32.2 | 38.7 | 38.7 | 36.1 | 34.8 | 34.8 | 33.5 | 32.2 | 11.6 | 12.9 | 19.3 |
| 87.5° | 21.9 | 27.1 | 28.3 | 27.1 | 23.2 | 20.6 | 18.0 | 15.5 | 5.2 | 0.0 | 2.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636446

CATALOG NUMBER: GWS-SA3F-827-U-SLL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 358° | 360° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 | 564.4 |
| 2.5° | 597.9 | 601.8 | 601.8 | 596.6 | 592.7 | 582.4 | 572.1 | 561.8 | 559.2 | 557.9 |
| 5° | 597.9 | 613.4 | 621.1 | 619.8 | 610.8 | 594.0 | 572.1 | 548.9 | 542.5 | 539.9 |
| 7.5° | 588.9 | 618.5 | 641.7 | 645.6 | 628.8 | 599.2 | 559.2 | 524.4 | 515.4 | 511.6 |
| 10° | 609.5 | 667.5 | 713.9 | 720.3 | 701.0 | 643.0 | 578.6 | 519.3 | 505.1 | 496.1 |
| 12.5° | 720.3 | 815.7 | 872.4 | 899.4 | 862.1 | 788.6 | 681.7 | 576.0 | 543.8 | 529.6 |
| 15° | 944.5 | 1079.8 | 1188.1 | 1188.1 | 1153.3 | 1023.1 | 887.8 | 716.4 | 672.6 | 634.0 |
| 17.5° | 1231.9 | 1402.0 | 1497.3 | 1487.0 | 1434.2 | 1342.7 | 1180.3 | 934.2 | 845.3 | 805.4 |
| 20° | 1559.2 | 1661.0 | 1682.9 | 1676.4 | 1653.2 | 1600.4 | 1488.3 | 1224.1 | 1104.3 | 1042.5 |
| 22.5° | 1842.7 | 1815.6 | 1783.4 | 1757.6 | 1751.2 | 1766.6 | 1751.2 | 1547.6 | 1453.5 | 1344.0 |
| 25° | 2034.6 | 1881.3 | 1784.7 | 1738.3 | 1760.2 | 1849.1 | 1945.7 | 1869.7 | 1795.0 | 1681.6 |
| 27.5° | 2139.0 | 1873.6 | 1734.4 | 1686.7 | 1724.1 | 1850.4 | 2060.4 | 2189.3 | 2112.0 | 2057.8 |
| 30° | 2195.7 | 1867.1 | 1702.2 | 1655.8 | 1712.5 | 1871.0 | 2140.3 | 2488.2 | 2490.8 | 2404.5 |
| 32.5° | 2276.9 | 1908.4 | 1708.6 | 1666.1 | 1742.1 | 1932.9 | 2240.8 | 2792.3 | 2867.1 | 2820.7 |
| 35° | 2368.4 | 1971.5 | 1738.3 | 1699.6 | 1793.7 | 2015.3 | 2352.9 | 3099.0 | 3254.9 | 3239.5 |
| 37.5° | 2454.7 | 2042.4 | 1807.9 | 1770.5 | 1872.3 | 2086.2 | 2461.2 | 3400.5 | 3617.0 | 3671.1 |
| 40° | 2544.9 | 2141.6 | 2021.8 | 2057.8 | 2114.5 | 2198.3 | 2557.8 | 3662.1 | 4015.2 | 4096.4 |
| 42.5° | 2757.5 | 2485.6 | 2668.6 | 2736.9 | 2744.6 | 2572.0 | 2769.1 | 3997.1 | 4406.9 | 4503.5 |
| 45° | 3231.7 | 3097.7 | 3622.2 | 3718.8 | 3668.6 | 3145.4 | 3278.1 | 4480.3 | 4954.5 | 5003.5 |
| 47.5° | 3830.9 | 3892.8 | 4927.5 | 5261.2 | 4959.7 | 3821.9 | 3895.3 | 5497.0 | 5957.0 | 5939.0 |
| 50° | 4529.3 | 4821.8 | 6409.3 | 7196.6 | 6475.1 | 4700.7 | 4606.6 | 6746.9 | 7304.9 | 7249.5 |
| 52.5° | 5355.3 | 5901.6 | 8190.1 | 9308.6 | 8625.7 | 5689.0 | 5650.4 | 8402.7 | 8742.9 | 8566.4 |
| 55° | 6395.2 | 6944.1 | 10239.0 | 11802.0 | 10830.4 | 6895.1 | 7027.8 | 10322.7 | 10388.4 | 9827.9 |
| 57.5° | 7946.6 | 8303.5 | 12653.7 | 14661.3 | 13131.8 | 8534.2 | 9496.7 | 12877.9 | 12091.9 | 11030.1 |
| 60° | 10763.4 | 10052.1 | 14987.3 | 17586.4 | 15580.1 | 10839.4 | 12753.0 | 14392.0 | 12658.9 | 11195.1 |
| 62.5° | 11744.0 | 11536.5 | 16448.6 | 18823.4 | 17226.9 | 12732.3 | 13599.5 | 13533.8 | 11924.4 | 10571.4 |
| 65° | 10258.3 | 11166.7 | 16187.0 | 18170.1 | 17015.5 | 12420.5 | 12204.0 | 12586.7 | 11097.1 | 9624.3 |
| 67.5° | 9476.1 | 10298.2 | 15196.1 | 16367.4 | 15844.2 | 11362.6 | 10878.1 | 10773.7 | 9316.3 | 8143.7 |
| 70° | 8687.5 | 9501.9 | 13759.3 | 13904.9 | 13661.4 | 9638.5 | 9001.9 | 8302.2 | 6963.4 | 5944.2 |
| 72.5° | 7739.1 | 8187.6 | 11765.9 | 11075.2 | 10799.5 | 7570.3 | 7436.3 | 6252.1 | 5220.0 | 4345.0 |
| 75° | 6749.5 | 6619.4 | 9173.3 | 7601.3 | 7807.4 | 5890.0 | 6280.5 | 4591.2 | 3824.5 | 3127.4 |
| 77.5° | 4909.4 | 4812.8 | 6143.9 | 4616.9 | 5113.0 | 3858.0 | 3466.2 | 1832.3 | 1744.7 | 1505.0 |
| 80° | 2739.5 | 3302.6 | 3318.1 | 2587.4 | 3227.9 | 2515.3 | 867.2 | 60.6 | 38.7 | 56.7 |
| 82.5° | 1273.1 | 1420.0 | 1798.8 | 1199.7 | 1841.4 | 1246.0 | 179.1 | 0.0 | 0.0 | 0.0 |
| 85° | 412.3 | 603.0 | 505.1 | 176.5 | 445.8 | 421.4 | 29.6 | 0.0 | 0.0 | 0.0 |
| 87.5° | 24.5 | 50.3 | 12.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength




Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength




Melanopic Lumens: 9797

M/P: 2.26





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)