

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636466

Luminaire Tested: GWS-SA3F-827-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-827-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15758.4 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636466
 CATALOG NUMBER: GWS-SA3F-827-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.3 fc
 Type II - Short - N/A

REPORT NUMBER: P636466
CATALOG NUMBER: GWS-SA3F-827-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636466

CATALOG NUMBER: GWS-SA3F-827-U-T3R-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4684.2 | 0.0 | 4684.2 |
| | % Fixture | 29.7 | 0.0 | 29.7 |
| Street Side | Lumens | 11074.2 | 0.0 | 11074.2 |
| | % Fixture | 70.3 | 0.0 | 70.3 |
| Total | Lumens | 15758.4 | 0.0 | 15758.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 361.7 | 2.3 |
| 10°-20° | 1005.1 | 6.4 |
| 20°-30° | 1703.6 | 10.8 |
| 30°-40° | 2607.6 | 16.5 |
| 40°-50° | 3477.0 | 22.1 |
| 50°-60° | 4015.7 | 25.5 |
| 60°-70° | 2086.7 | 13.2 |
| 70°-80° | 443.6 | 2.8 |
| 80°-90° | 57.4 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 15758.4 | 100.0 |
| 0°-180° | 15758.4 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636466


CATALOG NUMBER: GWS-SA3F-827-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1740.1 | 11.0 | | | |
| FM (30°-60°) | 7614.9 | 48.3 | | | |
| FH (60°-80°) | 1699.1 | 10.8 | | | G1/1800 |
| FVH (80°-90°) | 20.0 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1330.3 | 8.4 | B3/2500 | | |
| BM (30°-60°) | 2485.4 | 15.8 | B2/2500 | | |
| BH (60°-80°) | 831.1 | 5.3 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 37.4 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type II Short





REPORT NUMBER: P636466

CATALOG NUMBER: GWS-SA3F-827-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 |
| 2.5° | 3727.5 | 3719.8 | 3722.3 | 3732.6 | 3771.3 | 3799.6 | 3829.3 | 3856.3 | 3882.1 | 3889.8 | 3896.3 |
| 5° | 3594.8 | 3580.6 | 3584.5 | 3601.2 | 3646.3 | 3694.0 | 3746.8 | 3811.2 | 3873.1 | 3893.7 | 3920.8 |
| 7.5° | 3500.7 | 3498.1 | 3504.6 | 3530.4 | 3578.0 | 3623.1 | 3691.4 | 3782.9 | 3889.8 | 3924.6 | 3972.3 |
| 10° | 3375.7 | 3370.6 | 3396.4 | 3449.2 | 3527.8 | 3599.9 | 3681.1 | 3789.3 | 3938.8 | 3990.3 | 4063.8 |
| 12.5° | 3276.5 | 3274.0 | 3301.0 | 3374.5 | 3475.0 | 3589.6 | 3701.7 | 3822.8 | 4004.5 | 4075.4 | 4165.6 |
| 15° | 3334.5 | 3322.9 | 3324.2 | 3375.7 | 3465.9 | 3601.2 | 3753.3 | 3883.4 | 4070.2 | 4160.4 | 4276.4 |
| 17.5° | 3503.3 | 3482.7 | 3467.2 | 3476.2 | 3527.8 | 3668.2 | 3831.9 | 3964.6 | 4146.2 | 4251.9 | 4393.6 |
| 20° | 3736.5 | 3724.9 | 3682.4 | 3654.0 | 3665.6 | 3789.3 | 3955.5 | 4079.2 | 4245.4 | 4364.0 | 4516.0 |
| 22.5° | 4049.6 | 4021.3 | 3963.3 | 3918.2 | 3883.4 | 3980.0 | 4133.4 | 4240.3 | 4383.3 | 4507.0 | 4665.5 |
| 25° | 4437.4 | 4396.2 | 4304.7 | 4233.9 | 4159.1 | 4258.3 | 4394.9 | 4476.1 | 4572.7 | 4687.4 | 4838.1 |
| 27.5° | 4833.0 | 4798.2 | 4696.4 | 4601.1 | 4508.3 | 4570.1 | 4732.5 | 4778.9 | 4768.6 | 4852.3 | 4981.2 |
| 30° | 5254.3 | 5210.5 | 5113.9 | 5010.8 | 4891.0 | 4930.9 | 5076.5 | 5099.7 | 4990.2 | 5059.7 | 5147.4 |
| 32.5° | 5698.8 | 5656.3 | 5572.6 | 5452.7 | 5317.4 | 5332.9 | 5372.8 | 5394.7 | 5290.4 | 5330.3 | 5397.3 |
| 35° | 6151.1 | 6111.1 | 6026.1 | 5907.5 | 5808.3 | 5714.3 | 5613.8 | 5701.4 | 5640.8 | 5718.1 | 5713.0 |
| 37.5° | 6564.7 | 6524.7 | 6471.9 | 6380.4 | 6210.3 | 6024.8 | 5792.9 | 5901.1 | 5995.2 | 6093.1 | 6076.3 |
| 40° | 6844.3 | 6817.2 | 6830.1 | 6815.9 | 6596.9 | 6229.7 | 5880.5 | 5999.0 | 6255.4 | 6422.9 | 6413.9 |
| 42.5° | 7085.2 | 7058.1 | 7132.9 | 7187.0 | 6929.3 | 6419.1 | 5923.0 | 6036.4 | 6421.6 | 6683.2 | 6670.3 |
| 45° | 7192.1 | 7184.4 | 7308.1 | 7479.5 | 7233.4 | 6620.1 | 6032.5 | 6113.7 | 6547.9 | 6882.9 | 6833.9 |
| 47.5° | 7064.6 | 7091.6 | 7335.2 | 7625.1 | 7485.9 | 6858.4 | 6256.7 | 6277.3 | 6712.8 | 7099.4 | 6961.5 |
| 50° | 6810.8 | 6870.0 | 7198.6 | 7628.9 | 7670.2 | 7127.7 | 6567.2 | 6515.7 | 6934.4 | 7330.0 | 7028.5 |
| 52.5° | 6441.0 | 6502.8 | 7038.8 | 7599.3 | 7775.8 | 7439.5 | 6980.8 | 6907.4 | 7214.0 | 7560.6 | 7040.1 |
| 55° | 5591.9 | 5675.6 | 6672.9 | 7532.3 | 7878.9 | 7723.0 | 7447.2 | 7297.8 | 7574.8 | 7877.6 | 7154.8 |
| 57.5° | 4851.0 | 4894.8 | 5781.3 | 7234.7 | 7899.5 | 7931.7 | 7779.7 | 7601.9 | 7933.0 | 8220.3 | 7283.6 |
| 60° | 3560.0 | 3570.3 | 4367.8 | 5986.1 | 7266.9 | 7810.6 | 7752.6 | 7488.5 | 7762.9 | 7945.9 | 6693.5 |
| 62.5° | 2011.3 | 2012.6 | 2649.1 | 3995.5 | 5428.2 | 6366.2 | 6402.3 | 6169.1 | 5938.5 | 5992.6 | 4659.0 |
| 65° | 755.0 | 825.9 | 1209.9 | 1963.6 | 3129.6 | 3758.4 | 3907.9 | 3962.0 | 3578.0 | 3339.7 | 2498.3 |
| 67.5° | 505.1 | 521.8 | 706.1 | 1010.1 | 1392.8 | 1608.0 | 1798.7 | 1803.8 | 1319.4 | 1176.4 | 984.4 |
| 70° | 385.2 | 402.0 | 555.3 | 722.8 | 706.1 | 652.0 | 704.8 | 685.5 | 708.6 | 728.0 | 748.6 |
| 72.5° | 287.3 | 304.1 | 430.3 | 510.2 | 423.9 | 417.5 | 472.9 | 525.7 | 574.6 | 595.3 | 627.5 |
| 75° | 190.7 | 203.6 | 289.9 | 273.2 | 234.5 | 277.0 | 345.3 | 398.1 | 426.5 | 451.0 | 475.4 |
| 77.5° | 121.1 | 130.1 | 154.6 | 125.0 | 130.1 | 162.3 | 201.0 | 248.7 | 275.7 | 300.2 | 313.1 |
| 80° | 55.4 | 54.1 | 52.8 | 59.3 | 73.4 | 95.3 | 121.1 | 149.5 | 170.1 | 180.4 | 188.1 |
| 82.5° | 21.9 | 24.5 | 27.1 | 32.2 | 39.9 | 51.5 | 68.3 | 87.6 | 104.4 | 106.9 | 113.4 |
| 85° | 9.0 | 10.3 | 11.6 | 14.2 | 18.0 | 23.2 | 28.3 | 39.9 | 50.2 | 54.1 | 58.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.3 | 2.6 | 3.9 | 6.4 | 11.6 | 12.9 | 14.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636466

CATALOG NUMBER: GWS-SA3F-827-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 | 3905.3 |
| 2.5° | 3931.1 | 3914.3 | 3942.7 | 3962.0 | 3980.0 | 3960.7 | 3954.3 | 3937.5 | 3934.9 | 3934.9 | 3943.9 |
| 5° | 3967.1 | 3955.5 | 3985.2 | 3996.8 | 3995.5 | 3953.0 | 3927.2 | 3893.7 | 3876.9 | 3876.9 | 3879.5 |
| 7.5° | 4031.6 | 4025.1 | 4041.9 | 4023.8 | 3982.6 | 3896.3 | 3811.2 | 3740.4 | 3692.7 | 3668.2 | 3676.0 |
| 10° | 4138.5 | 4130.8 | 4116.6 | 4049.6 | 3931.1 | 3752.0 | 3578.0 | 3449.2 | 3371.9 | 3328.1 | 3330.6 |
| 12.5° | 4242.9 | 4230.0 | 4179.7 | 4031.6 | 3788.0 | 3503.3 | 3275.2 | 3130.9 | 3045.9 | 2994.4 | 2982.8 |
| 15° | 4357.5 | 4324.0 | 4215.8 | 3938.8 | 3554.8 | 3199.2 | 2960.9 | 2805.0 | 2713.5 | 2682.6 | 2681.3 |
| 17.5° | 4467.1 | 4407.8 | 4211.9 | 3773.9 | 3275.2 | 2881.0 | 2641.3 | 2544.7 | 2529.2 | 2543.4 | 2547.3 |
| 20° | 4577.9 | 4482.5 | 4169.4 | 3545.8 | 2942.8 | 2564.0 | 2440.3 | 2480.3 | 2538.2 | 2576.9 | 2585.9 |
| 22.5° | 4692.5 | 4544.4 | 4072.8 | 3252.1 | 2592.4 | 2350.1 | 2401.7 | 2489.3 | 2561.4 | 2613.0 | 2618.1 |
| 25° | 4821.4 | 4602.3 | 3928.5 | 2892.6 | 2311.5 | 2290.9 | 2392.7 | 2485.4 | 2562.7 | 2622.0 | 2632.3 |
| 27.5° | 4894.8 | 4603.6 | 3726.2 | 2522.8 | 2182.6 | 2267.7 | 2370.8 | 2458.4 | 2535.7 | 2600.1 | 2611.7 |
| 30° | 4967.0 | 4568.8 | 3405.4 | 2222.6 | 2145.3 | 2240.6 | 2333.4 | 2414.6 | 2488.0 | 2551.1 | 2565.3 |
| 32.5° | 5068.8 | 4536.6 | 3035.6 | 2049.9 | 2123.4 | 2214.8 | 2290.9 | 2363.0 | 2419.7 | 2448.1 | 2455.8 |
| 35° | 5195.0 | 4495.4 | 2642.6 | 1975.2 | 2109.2 | 2194.2 | 2261.2 | 2299.9 | 2226.4 | 2211.0 | 2227.7 |
| 37.5° | 5371.6 | 4456.8 | 2250.9 | 1943.0 | 2100.2 | 2186.5 | 2245.8 | 2146.6 | 2056.4 | 2020.3 | 2033.2 |
| 40° | 5562.2 | 4434.8 | 1985.5 | 1917.2 | 2104.0 | 2194.2 | 2181.3 | 2034.5 | 1904.3 | 1828.3 | 1825.7 |
| 42.5° | 5724.6 | 4401.3 | 1815.4 | 1900.5 | 2114.3 | 2223.9 | 2093.7 | 1935.3 | 1742.0 | 1696.9 | 1698.2 |
| 45° | 5834.1 | 4316.3 | 1725.2 | 1882.4 | 2123.4 | 2230.3 | 2052.5 | 1798.7 | 1660.8 | 1632.5 | 1631.2 |
| 47.5° | 5879.2 | 4161.7 | 1667.3 | 1854.1 | 2122.1 | 2177.5 | 1968.8 | 1742.0 | 1604.1 | 1596.4 | 1601.5 |
| 50° | 5849.6 | 3907.9 | 1608.0 | 1798.7 | 2091.2 | 2122.1 | 1872.1 | 1691.7 | 1565.5 | 1608.0 | 1638.9 |
| 52.5° | 5740.1 | 3579.3 | 1537.1 | 1722.7 | 2035.8 | 2058.9 | 1823.2 | 1660.8 | 1537.1 | 1593.8 | 1618.3 |
| 55° | 5711.7 | 3312.6 | 1446.9 | 1623.4 | 1953.3 | 1946.8 | 1771.6 | 1645.4 | 1517.8 | 1495.9 | 1499.8 |
| 57.5° | 5674.3 | 3052.3 | 1297.5 | 1445.6 | 1744.6 | 1754.9 | 1722.7 | 1627.3 | 1467.5 | 1461.1 | 1467.5 |
| 60° | 4929.6 | 2339.8 | 1157.0 | 1247.2 | 1432.8 | 1488.2 | 1667.3 | 1593.8 | 1386.4 | 1359.3 | 1358.0 |
| 62.5° | 3219.8 | 1417.3 | 1029.5 | 1087.5 | 1167.3 | 1231.8 | 1520.4 | 1497.2 | 1297.5 | 1280.7 | 1292.3 |
| 65° | 1731.7 | 1010.1 | 936.7 | 971.5 | 1015.3 | 1064.3 | 1260.1 | 1333.5 | 1172.5 | 1113.2 | 1114.5 |
| 67.5° | 885.2 | 859.4 | 867.1 | 891.6 | 925.1 | 949.6 | 1016.6 | 1081.0 | 999.8 | 949.6 | 948.3 |
| 70° | 757.6 | 778.2 | 789.8 | 804.0 | 825.9 | 822.0 | 828.5 | 840.1 | 833.6 | 809.1 | 807.9 |
| 72.5° | 645.5 | 677.7 | 680.3 | 682.9 | 690.6 | 672.6 | 661.0 | 641.6 | 642.9 | 646.8 | 648.1 |
| 75° | 490.9 | 521.8 | 529.6 | 525.7 | 533.4 | 510.2 | 494.8 | 475.4 | 452.2 | 448.4 | 451.0 |
| 77.5° | 319.5 | 344.0 | 355.6 | 353.0 | 356.9 | 338.9 | 331.1 | 310.5 | 283.5 | 273.2 | 273.2 |
| 80° | 193.3 | 207.4 | 216.5 | 219.0 | 222.9 | 210.0 | 197.1 | 179.1 | 167.5 | 155.9 | 155.9 |
| 82.5° | 117.2 | 126.3 | 132.7 | 132.7 | 136.6 | 122.4 | 112.1 | 99.2 | 94.1 | 83.7 | 83.7 |
| 85° | 59.3 | 65.7 | 68.3 | 67.0 | 64.4 | 52.8 | 49.0 | 42.5 | 39.9 | 34.8 | 34.8 |
| 87.5° | 14.2 | 18.0 | 18.0 | 12.9 | 12.9 | 6.4 | 3.9 | 1.3 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)