

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832511

Luminaire Tested: **TTN-D0-750-U-DL-CG**

Issue Date: 5/14/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P832511  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/14/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TTN-D0-750-U-DL-CG  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE  
5000K, 70 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH CLEAR GLASS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1141.9 lumens  
Efficiency: N/A  
Efficacy: 106.7 lumens/watt  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B0 - U0 - G1  
  
Input Watts (W): 10.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P832511  
 CATALOG NUMBER: TTN-D0-750-U-DL-CG

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P832511  
CATALOG NUMBER: TTN-D0-750-U-DL-CG

### Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832511

CATALOG NUMBER: TTN-D0-750-U-DL-CG


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	251.9	0.0	251.9
	% Fixture	22.1	0.0	22.1
<b>Street Side</b>	Lumens	890.0	0.0	890.0
	% Fixture	77.9	0.0	77.9
<b>Total</b>	Lumens	1141.9	0.0	1141.9
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	10.2	0.9
10°-20°	33.2	2.9
20°-30°	70.0	6.1
30°-40°	127.2	11.1
40°-50°	200.9	17.6
50°-60°	266.9	23.4
60°-70°	256.9	22.5
70°-80°	150.8	13.2
80°-90°	25.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1141.9	100.0
0°-180°	1141.9	100.0

**Coefficient of Utilization**



REPORT NUMBER: P832511


CATALOG NUMBER: TTN-D0-750-U-DL-CG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	76.4	6.7			
FM (30°-60°)	462.0	40.5			
FH (60°-80°)	329.7	28.9			G0/660
FVH (80°-90°)	21.9	1.9			G1/100
BL (0°-30°)	37.1	3.2	B0/110		
BM (30°-60°)	133.0	11.6	B0/220		
BH (60°-80°)	77.9	6.8	B0/110		G0/110
BVH (80°-90°)	4.0	0.4			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G1**

Type IV Short





REPORT NUMBER: P832511  
 CATALOG NUMBER: TTN-D0-750-U-DL-CG

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
2.5°	114.0	115.0	114.0	114.0	113.0	113.0	112.0	111.0	110.0	109.0	107.0
5°	127.0	127.0	126.0	124.0	123.0	122.0	120.0	117.0	115.0	112.0	109.0
7.5°	133.0	133.0	132.0	130.0	128.0	127.0	124.0	120.0	117.0	113.0	109.0
10°	141.0	142.0	140.0	138.0	136.0	135.0	131.0	126.0	121.0	116.0	110.0
12.5°	150.0	151.0	150.0	147.0	144.0	143.0	139.0	133.0	127.0	120.0	113.0
15°	162.1	164.1	161.0	159.0	156.0	155.0	150.0	143.0	136.0	127.0	118.0
17.5°	176.1	177.1	175.1	172.1	170.1	169.1	164.1	156.0	146.0	136.0	125.0
20°	192.1	193.1	192.1	188.1	186.1	185.1	180.1	171.1	159.0	148.0	134.0
22.5°	211.1	213.1	210.1	207.1	205.1	205.1	199.1	189.1	175.1	161.0	145.0
25°	233.1	236.1	232.1	230.1	228.1	227.1	222.1	210.1	194.1	177.1	157.0
27.5°	260.1	262.1	259.1	258.1	254.1	254.1	246.1	232.1	215.1	195.1	172.1
30°	284.1	286.1	284.1	284.1	281.1	280.1	272.1	258.1	237.1	213.1	185.1
32.5°	307.1	309.1	308.1	309.1	308.1	307.1	297.1	282.1	261.1	230.1	198.1
35°	330.1	333.1	332.1	335.1	334.1	333.1	325.1	307.1	282.1	251.1	212.1
37.5°	354.1	357.1	357.1	360.1	361.1	361.1	352.1	333.1	305.1	270.1	228.1
40°	380.1	383.1	383.1	388.1	390.1	390.1	380.1	361.1	330.1	291.1	245.1
42.5°	405.1	408.1	409.1	414.1	417.1	418.1	410.1	388.1	352.1	312.1	261.1
45°	429.1	432.1	435.1	445.1	450.1	449.1	443.1	420.1	380.1	334.1	278.1
47.5°	452.1	456.1	461.1	474.1	481.1	480.1	476.1	450.1	406.1	355.1	293.1
50°	470.1	473.1	483.1	497.2	506.2	507.2	501.2	476.1	428.1	371.1	304.1
52.5°	484.1	488.2	500.2	520.2	527.2	530.2	523.2	498.2	450.1	385.1	313.1
55°	494.2	494.2	512.2	535.2	545.2	547.2	547.2	516.2	463.1	394.1	318.1
57.5°	489.2	489.2	509.2	534.2	550.2	549.2	547.2	517.2	465.1	392.1	315.1
60°	475.1	478.1	497.2	522.2	538.2	537.2	531.2	504.2	455.1	384.1	309.1
62.5°	456.1	461.1	481.1	500.2	518.2	521.2	513.2	489.2	438.1	372.1	298.1
65°	420.1	427.1	452.1	473.1	487.2	493.2	483.1	461.1	415.1	349.1	275.1
67.5°	380.1	385.1	406.1	436.1	444.1	450.1	445.1	422.1	383.1	312.1	249.1
70°	334.1	342.1	356.1	386.1	395.1	401.1	401.1	378.1	341.1	274.1	218.1
72.5°	280.1	289.1	306.1	328.1	340.1	344.1	343.1	324.1	291.1	232.1	184.1
75°	221.1	228.1	248.1	264.1	277.1	280.1	279.1	263.1	233.1	187.1	146.0
77.5°	163.1	170.1	185.1	197.1	209.1	207.1	207.1	195.1	176.1	139.0	111.0
80°	107.0	113.0	126.0	130.0	143.0	142.0	142.0	133.0	120.0	93.0	74.0
82.5°	59.0	64.0	73.0	77.0	85.0	83.0	84.0	78.0	70.0	52.0	42.0
85°	21.0	25.0	30.0	33.0	37.0	37.0	37.0	32.0	30.0	20.0	17.0
87.5°	1.0	2.0	4.0	4.0	6.0	6.0	6.0	4.0	4.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P832511  
 CATALOG NUMBER: TTN-D0-750-U-DL-CG

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
2.5°	106.0	105.0	104.0	102.0	101.0	100.0	99.0	98.0	98.0	98.0	98.0
5°	107.0	106.0	103.0	100.0	97.0	94.0	92.0	91.0	90.0	89.0	89.0
7.5°	107.0	105.0	101.0	97.0	94.0	90.0	87.0	84.0	82.0	81.0	81.0
10°	108.0	105.0	100.0	96.0	91.0	86.0	82.0	78.0	76.0	74.0	74.0
12.5°	110.0	107.0	100.0	95.0	89.0	83.0	78.0	74.0	71.0	69.0	69.0
15°	114.0	110.0	102.0	95.0	88.0	81.0	76.0	71.0	68.0	66.0	66.0
17.5°	120.0	115.0	105.0	95.0	87.0	80.0	74.0	69.0	65.0	63.0	63.0
20°	127.0	121.0	109.0	97.0	87.0	79.0	73.0	67.0	63.0	61.0	61.0
22.5°	137.0	128.0	114.0	100.0	89.0	80.0	72.0	66.0	62.0	60.0	60.0
25°	148.0	138.0	120.0	104.0	91.0	80.0	72.0	66.0	62.0	60.0	59.0
27.5°	160.0	149.0	127.0	108.0	93.0	82.0	73.0	66.0	62.0	60.0	60.0
30°	171.1	158.0	134.0	113.0	96.0	83.0	74.0	67.0	62.0	60.0	60.0
32.5°	183.1	168.1	141.0	118.0	99.0	85.0	75.0	68.0	63.0	61.0	60.0
35°	195.1	178.1	148.0	122.0	102.0	87.0	76.0	69.0	64.0	62.0	62.0
37.5°	208.1	189.1	155.0	127.0	105.0	89.0	78.0	70.0	65.0	63.0	63.0
40°	222.1	200.1	162.1	131.0	108.0	91.0	80.0	72.0	67.0	65.0	65.0
42.5°	236.1	212.1	170.1	136.0	111.0	93.0	81.0	74.0	69.0	67.0	67.0
45°	250.1	222.1	177.1	141.0	114.0	96.0	84.0	76.0	71.0	69.0	69.0
47.5°	263.1	233.1	183.1	144.0	117.0	98.0	85.0	78.0	73.0	72.0	71.0
50°	272.1	240.1	187.1	147.0	118.0	99.0	87.0	79.0	75.0	73.0	73.0
52.5°	279.1	247.1	190.1	149.0	119.0	100.0	88.0	81.0	77.0	75.0	74.0
55°	283.1	248.1	190.1	147.0	118.0	100.0	88.0	81.0	77.0	75.0	75.0
57.5°	279.1	243.1	186.1	143.0	115.0	97.0	85.0	79.0	75.0	74.0	73.0
60°	271.1	235.1	178.1	137.0	110.0	92.0	81.0	76.0	73.0	72.0	71.0
62.5°	260.1	225.1	170.1	129.0	103.0	86.0	78.0	72.0	70.0	69.0	68.0
65°	238.1	206.1	157.0	119.0	94.0	79.0	71.0	67.0	65.0	63.0	62.0
67.5°	214.1	185.1	139.0	107.0	83.0	71.0	64.0	60.0	57.0	57.0	56.0
70°	188.1	163.1	120.0	91.0	72.0	62.0	55.0	52.0	50.0	50.0	49.0
72.5°	157.0	137.0	100.0	74.0	59.0	51.0	46.0	43.0	42.0	42.0	41.0
75°	126.0	108.0	79.0	58.0	46.0	40.0	36.0	34.0	33.0	33.0	32.0
77.5°	93.0	79.0	57.0	42.0	33.0	29.0	26.0	25.0	24.0	24.0	23.0
80°	62.0	52.0	37.0	27.0	20.0	18.0	16.0	16.0	15.0	16.0	15.0
82.5°	34.0	28.0	20.0	14.0	10.0	9.0	8.0	8.0	9.0	9.0	8.0
85°	13.0	10.0	7.0	4.0	3.0	3.0	3.0	3.0	3.0	3.0	2.0
87.5°	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)