

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832878

Luminaire Tested: **TTN-D0-750-U-RW-CG-UPL3**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P832878
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D0-750-U-RW-CG-UPL3
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
5000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1923.6 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type II - Short
BUG Rating: B1 - U4 - G1


Input Watts (W): 17.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832878
 CATALOG NUMBER: TTN-D0-750-U-RW-CG-UPL3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.2 fc
 Type II - Short - N/A

REPORT NUMBER: P832878
CATALOG NUMBER: TTN-D0-750-U-RW-CG-UPL3

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832878

CATALOG NUMBER: TTN-D0-750-U-RW-CG-UPL3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	556.1	405.8	961.8
	% Fixture	28.9	21.1	50.0
Street Side	Lumens	556.1	405.8	961.8
	% Fixture	28.9	21.1	50.0
Total	Lumens	1112.1	811.5	1923.6
	% Fixture	57.8	42.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.5	0.5
10°-20°	30.7	1.6
20°-30°	65.3	3.4
30°-40°	120.4	6.3
40°-50°	193.9	10.1
50°-60°	262.4	13.6
60°-70°	255.2	13.3
70°-80°	148.5	7.7
80°-90°	26.2	1.4
90°-100°	18.1	0.9
100°-110°	184.1	9.6
110°-120°	269.1	14.0
120°-130°	156.2	8.1
130°-140°	82.7	4.3
140°-150°	49.1	2.6
150°-160°	30.3	1.6
160°-170°	16.5	0.9
170°-180°	5.4	0.3
0°-90°	1112.1	57.8
0°-180°	1923.6	100.0

Coefficient of Utilization




REPORT NUMBER: P832878
 CATALOG NUMBER: TTN-D0-750-U-RW-CG-UPL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	52.8	2.7			
FM (30°-60°)	288.4	15.0			
FH (60°-80°)	201.8	10.5			G0/660
FVH (80°-90°)	13.1	0.7			G1/100
BL (0°-30°)	52.8	2.7	B0/110		
BM (30°-60°)	288.4	15.0	B1/1000		
BH (60°-80°)	201.8	10.5	B1/500		G1/500
BVH (80°-90°)	13.1	0.7			G1/100
UL (90°-100°)	18.1	0.9		U2/50	
UH (100°-180°)	793.4	41.2		U4/1000	

BUG Rating: B1-U4-G1
 Type II Short





REPORT NUMBER: P832878

CATALOG NUMBER: TTN-D0-750-U-RW-CG-UPL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0	100.0
2.5°	100.0	100.0	100.0	100.0	99.0	99.0	99.0	98.0	98.0	98.0	98.0
5°	100.0	100.0	100.0	101.0	101.0	101.0	100.0	100.0	100.0	100.0	100.0
7.5°	100.0	101.0	101.0	100.0	100.0	99.0	99.0	99.0	98.0	98.0	98.0
10°	100.0	100.0	100.0	100.0	99.0	99.0	100.0	100.0	101.0	101.0	101.0
12.5°	99.0	99.0	100.0	100.0	100.0	101.0	103.0	104.0	105.0	106.0	106.0
15°	100.0	100.0	101.0	102.0	103.0	105.0	108.0	111.0	113.0	114.0	113.0
17.5°	100.0	101.0	102.0	104.0	107.0	110.0	115.0	119.0	123.0	124.0	125.0
20°	102.0	102.0	103.0	107.0	112.0	117.0	124.0	130.9	135.9	137.9	137.9
22.5°	103.0	104.0	105.0	110.0	118.0	126.0	135.9	143.9	150.9	154.9	155.9
25°	106.0	106.0	108.0	115.0	125.0	136.9	149.9	161.9	170.9	175.9	176.9
27.5°	108.0	109.0	112.0	121.0	133.9	148.9	166.9	180.9	191.9	197.9	198.9
30°	110.0	111.0	117.0	127.0	142.9	160.9	181.9	199.9	213.9	220.9	221.9
32.5°	113.0	114.0	121.0	131.9	150.9	172.9	196.9	218.9	238.9	244.9	245.9
35°	116.0	117.0	125.0	137.9	159.9	184.9	212.9	238.9	262.9	270.9	272.9
37.5°	119.0	120.0	128.0	143.9	168.9	197.9	230.9	261.9	287.9	298.9	301.9
40°	122.0	123.0	131.9	149.9	177.9	211.9	249.9	283.9	313.9	326.9	328.9
42.5°	124.0	125.0	134.9	154.9	186.9	224.9	269.9	307.9	339.9	356.9	358.9
45°	127.0	128.0	138.9	161.9	194.9	239.9	288.9	334.9	371.9	390.8	392.8
47.5°	129.0	129.9	141.9	165.9	203.9	253.9	308.9	358.9	402.8	422.8	428.8
50°	129.9	130.9	143.9	169.9	209.9	263.9	324.9	382.9	429.8	454.8	457.8
52.5°	129.9	131.9	144.9	172.9	213.9	272.9	337.9	402.8	455.8	483.8	484.8
55°	129.0	129.9	143.9	171.9	215.9	276.9	346.9	414.8	473.8	500.8	509.8
57.5°	125.0	126.0	139.9	168.9	211.9	274.9	344.9	417.8	477.8	503.8	514.8
60°	119.0	121.0	133.9	161.9	205.9	267.9	338.9	411.8	471.8	503.8	504.8
62.5°	112.0	113.0	126.0	152.9	196.9	256.9	327.9	399.8	457.8	490.8	489.8
65°	102.0	103.0	114.0	141.9	180.9	235.9	305.9	380.9	430.8	465.8	462.8
67.5°	91.0	92.0	102.0	127.0	161.9	212.9	275.9	348.9	392.8	428.8	426.8
70°	79.0	79.0	88.0	109.0	141.9	186.9	242.9	306.9	350.9	380.9	381.9
72.5°	65.0	65.0	73.0	91.0	119.0	156.9	204.9	261.9	297.9	323.9	325.9
75°	51.0	50.0	57.0	72.0	94.0	125.0	161.9	210.9	238.9	263.9	262.9
77.5°	36.0	36.0	40.0	52.0	68.0	93.0	120.0	158.9	177.9	198.9	194.9
80°	23.0	23.0	25.0	34.0	45.0	62.0	79.0	108.0	121.0	136.9	131.9
82.5°	12.0	11.0	13.0	18.0	24.0	34.0	44.0	63.0	69.0	81.0	77.0
85°	4.0	4.0	4.0	6.0	9.0	13.0	17.0	27.0	28.0	36.0	33.0
87.5°	1.0	0.0	0.0	1.0	1.0	1.0	1.0	3.0	3.0	6.0	4.0
90°	6.9	6.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	6.9	6.9
92.5°	6.9	6.9	6.9	9.7	11.1	9.7	11.1	8.3	8.3	6.9	6.9
95°	8.3	8.3	9.7	12.5	15.3	16.7	16.7	9.7	9.7	8.3	8.3
97.5°	11.1	12.5	12.5	15.3	25.0	45.8	27.8	13.9	13.9	12.5	11.1
100°	18.0	19.4	19.4	34.7	73.6	98.6	70.8	36.1	26.4	19.4	19.4
102.5°	58.3	61.1	75.0	112.5	166.6	151.3	127.7	120.8	83.3	66.6	63.9
105°	148.6	147.2	158.3	187.4	233.3	229.1	211.0	191.6	165.2	152.7	152.7
107.5°	195.8	195.8	205.5	230.5	265.2	309.6	313.8	248.5	218.0	204.1	202.7
110°	220.8	220.8	229.1	249.9	295.7	358.2	355.4	306.8	269.4	251.3	248.5



REPORT NUMBER: P832878
 CATALOG NUMBER: TTN-D0-750-U-RW-CG-UPL3

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	226.3	227.7	238.8	270.7	320.7	348.5	336.0	316.6	299.9	286.0	283.2
115°	234.6	234.6	247.1	277.7	305.5	316.6	302.7	287.4	276.3	270.7	273.5
117.5°	231.9	236.0	238.8	255.5	273.5	281.8	274.9	254.1	245.8	243.0	238.8
120°	215.2	215.2	218.0	226.3	236.0	240.2	237.4	223.5	216.6	215.2	212.4
122.5°	191.6	193.0	191.6	195.8	202.7	206.9	204.1	193.0	190.2	190.2	187.4
125°	168.0	168.0	166.6	169.4	173.6	172.2	173.6	168.0	166.6	166.6	165.2
127.5°	151.3	149.9	147.2	148.6	149.9	149.9	151.3	145.8	147.2	148.6	147.2
130°	134.7	134.7	131.9	131.9	131.9	129.1	131.9	129.1	130.5	131.9	133.3
132.5°	119.4	119.4	115.2	113.9	113.9	113.9	115.2	113.9	116.6	119.4	119.4
135°	106.9	106.9	102.7	104.1	104.1	102.7	104.1	102.7	105.5	106.9	106.9
137.5°	97.2	97.2	94.4	94.4	94.4	93.0	94.4	94.4	95.8	98.6	100.0
140°	88.9	88.9	87.5	87.5	86.1	87.5	87.5	87.5	88.9	90.2	90.2
142.5°	84.7	83.3	81.9	80.5	81.9	81.9	81.9	80.5	81.9	84.7	84.7
145°	77.8	77.8	76.4	76.4	76.4	77.8	76.4	76.4	77.8	77.8	79.1
147.5°	73.6	73.6	72.2	73.6	73.6	73.6	73.6	72.2	73.6	73.6	75.0
150°	72.2	70.8	69.4	70.8	70.8	69.4	69.4	69.4	69.4	70.8	70.8
152.5°	68.0	68.0	66.6	68.0	66.6	66.6	66.6	66.6	66.6	68.0	69.4
155°	65.3	65.3	63.9	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
157.5°	62.5	63.9	62.5	62.5	62.5	62.5	62.5	62.5	62.5	63.9	63.9
160°	61.1	61.1	61.1	61.1	59.7	59.7	59.7	61.1	61.1	61.1	62.5
162.5°	59.7	59.7	59.7	59.7	58.3	58.3	58.3	58.3	59.7	59.7	61.1
165°	59.7	58.3	58.3	58.3	56.9	56.9	56.9	56.9	58.3	59.7	58.3
167.5°	56.9	56.9	56.9	56.9	56.9	55.5	55.5	56.9	56.9	56.9	58.3
170°	56.9	56.9	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	56.9
172.5°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	55.5	55.5	56.9	56.9
175°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	56.9	56.9	56.9	55.5
177.5°	56.9	56.9	56.9	56.9	55.5	56.9	56.9	56.9	56.9	56.9	56.9
180°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9

(END OF REPORT)