

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629011

Luminaire Tested: GWS-SA1A-827-U-SL2-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-827-U-SL2-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1227.5 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G0


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629011
 CATALOG NUMBER: GWS-SA1A-827-U-SL2-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.3 fc
 Type II - Short - N/A

REPORT NUMBER: P629011
CATALOG NUMBER: GWS-SA1A-827-U-SL2-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P629011
 CATALOG NUMBER: GWS-SA1A-827-U-SL2-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 241.9 | 0.0 | 241.9 |
| | % Fixture | 19.7 | 0.0 | 19.7 |
| Street Side | Lumens | 985.6 | 0.0 | 985.6 |
| | % Fixture | 80.3 | 0.0 | 80.3 |
| Total | Lumens | 1227.5 | 0.0 | 1227.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 37.8 | 3.1 |
| 10°-20° | 93.1 | 7.6 |
| 20°-30° | 131.3 | 10.7 |
| 30°-40° | 194.3 | 15.8 |
| 40°-50° | 280.3 | 22.8 |
| 50°-60° | 330.6 | 26.9 |
| 60°-70° | 147.5 | 12.0 |
| 70°-80° | 12.7 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1227.5 | 100.0 |
| 0°-180° | 1227.5 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P629011

CATALOG NUMBER: GWS-SA1A-827-U-SL2-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 158.5 | 12.9 | | | |
| FM (30°-60°) | 688.8 | 56.1 | | | |
| FH (60°-80°) | 138.3 | 11.3 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 103.7 | 8.4 | B0/110 | | |
| BM (30°-60°) | 116.3 | 9.5 | B0/220 | | |
| BH (60°-80°) | 21.8 | 1.8 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G0
 Type II Short





REPORT NUMBER: P629011
 CATALOG NUMBER: GWS-SA1A-827-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 |
| 2.5° | 400.1 | 400.4 | 400.6 | 404.6 | 406.1 | 412.1 | 415.2 | 416.9 | 421.2 | 426.3 | 430.5 |
| 5° | 373.3 | 372.8 | 373.6 | 378.7 | 382.0 | 390.8 | 395.6 | 398.9 | 408.5 | 420.5 | 430.5 |
| 7.5° | 349.9 | 350.8 | 351.7 | 357.2 | 362.2 | 371.8 | 378.7 | 383.6 | 397.0 | 414.8 | 431.7 |
| 10° | 333.4 | 333.4 | 334.8 | 341.1 | 346.9 | 358.7 | 365.6 | 371.9 | 387.8 | 409.7 | 433.1 |
| 12.5° | 321.3 | 321.4 | 323.1 | 330.3 | 337.0 | 349.3 | 356.5 | 362.6 | 380.2 | 404.6 | 433.4 |
| 15° | 315.6 | 315.1 | 316.5 | 324.1 | 331.6 | 343.2 | 350.7 | 356.6 | 374.8 | 401.8 | 434.9 |
| 17.5° | 314.1 | 313.8 | 314.8 | 322.3 | 330.0 | 341.2 | 348.6 | 354.6 | 374.0 | 402.7 | 439.4 |
| 20° | 318.4 | 317.8 | 317.4 | 323.8 | 331.0 | 342.1 | 349.8 | 356.5 | 377.6 | 407.6 | 446.3 |
| 22.5° | 328.8 | 328.8 | 327.7 | 330.9 | 335.7 | 345.7 | 353.7 | 362.5 | 387.1 | 417.5 | 456.4 |
| 25° | 347.8 | 346.3 | 344.4 | 345.7 | 345.1 | 351.4 | 360.8 | 373.1 | 404.9 | 433.8 | 468.9 |
| 27.5° | 369.5 | 370.9 | 367.6 | 367.7 | 362.5 | 360.2 | 371.2 | 389.8 | 431.4 | 456.9 | 487.3 |
| 30° | 399.1 | 398.0 | 398.2 | 397.7 | 385.6 | 374.9 | 386.8 | 411.5 | 464.8 | 492.1 | 511.3 |
| 32.5° | 422.1 | 423.6 | 428.6 | 431.4 | 415.5 | 398.5 | 411.0 | 441.0 | 502.9 | 532.3 | 540.7 |
| 35° | 446.6 | 449.3 | 459.3 | 468.6 | 455.3 | 435.6 | 449.1 | 480.1 | 538.7 | 572.0 | 574.4 |
| 37.5° | 472.3 | 477.7 | 489.7 | 506.1 | 504.0 | 486.6 | 498.9 | 526.1 | 566.9 | 596.0 | 602.3 |
| 40° | 501.9 | 507.1 | 526.7 | 550.3 | 555.2 | 551.3 | 555.4 | 571.2 | 585.5 | 597.0 | 614.2 |
| 42.5° | 534.2 | 541.4 | 566.3 | 597.8 | 616.3 | 619.8 | 610.3 | 608.7 | 593.6 | 585.0 | 611.7 |
| 45° | 572.4 | 580.8 | 609.0 | 649.8 | 679.3 | 683.9 | 667.6 | 646.5 | 598.7 | 576.2 | 604.1 |
| 47.5° | 615.3 | 623.2 | 651.3 | 700.3 | 744.2 | 746.0 | 717.5 | 683.5 | 613.8 | 586.4 | 609.9 |
| 50° | 629.7 | 634.6 | 658.9 | 716.4 | 797.4 | 811.2 | 769.9 | 725.1 | 644.2 | 616.3 | 638.4 |
| 52.5° | 580.2 | 582.2 | 603.3 | 661.4 | 786.6 | 875.1 | 846.5 | 787.3 | 698.3 | 662.0 | 682.3 |
| 55° | 459.7 | 456.6 | 473.7 | 527.0 | 683.6 | 862.1 | 915.9 | 885.0 | 768.0 | 715.7 | 739.4 |
| 57.5° | 321.6 | 317.8 | 313.9 | 350.1 | 510.1 | 730.8 | 844.0 | 898.7 | 834.4 | 768.9 | 801.0 |
| 60° | 264.3 | 260.7 | 241.9 | 225.2 | 308.4 | 524.8 | 648.3 | 751.2 | 829.0 | 766.2 | 799.0 |
| 62.5° | 228.4 | 226.3 | 218.6 | 196.0 | 181.5 | 299.6 | 405.9 | 504.6 | 636.1 | 601.7 | 603.5 |
| 65° | 179.4 | 178.8 | 184.0 | 186.4 | 160.5 | 165.7 | 207.1 | 262.2 | 343.9 | 324.3 | 307.5 |
| 67.5° | 122.6 | 121.2 | 131.1 | 161.2 | 154.3 | 130.8 | 121.2 | 122.3 | 148.8 | 91.0 | 72.2 |
| 70° | 77.9 | 74.8 | 74.9 | 100.0 | 125.6 | 103.2 | 93.5 | 82.3 | 74.0 | 13.5 | 15.3 |
| 72.5° | 49.9 | 48.0 | 41.2 | 45.1 | 58.1 | 50.4 | 50.8 | 43.8 | 29.2 | 7.2 | 8.4 |
| 75° | 21.0 | 19.3 | 14.8 | 11.8 | 11.7 | 7.3 | 6.4 | 6.0 | 4.0 | 4.0 | 4.3 |
| 77.5° | 0.1 | 0.0 | 0.0 | 0.1 | 0.3 | 0.1 | 0.1 | 0.3 | 0.6 | 0.9 | 1.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.1 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629011
 CATALOG NUMBER: GWS-SA1A-827-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 | 430.7 |
| 2.5° | 433.1 | 429.5 | 433.5 | 435.0 | 434.9 | 435.0 | 430.7 | 427.7 | 427.5 | 423.8 | 422.0 |
| 5° | 434.7 | 431.9 | 434.9 | 432.9 | 428.3 | 422.4 | 414.6 | 407.9 | 404.9 | 400.6 | 398.5 |
| 7.5° | 437.9 | 434.9 | 434.4 | 426.6 | 415.1 | 402.8 | 389.0 | 376.7 | 370.1 | 362.2 | 362.6 |
| 10° | 440.1 | 436.7 | 430.8 | 414.9 | 395.8 | 376.1 | 355.6 | 337.3 | 325.8 | 315.1 | 313.3 |
| 12.5° | 441.0 | 435.9 | 422.3 | 398.3 | 371.3 | 345.7 | 315.6 | 289.5 | 271.5 | 257.6 | 255.6 |
| 15° | 442.7 | 434.4 | 411.3 | 378.2 | 341.2 | 304.9 | 266.6 | 230.9 | 207.1 | 191.1 | 192.4 |
| 17.5° | 445.2 | 432.8 | 399.1 | 355.7 | 308.8 | 257.6 | 205.7 | 164.8 | 143.0 | 133.7 | 133.8 |
| 20° | 448.8 | 430.8 | 385.6 | 331.0 | 270.0 | 204.1 | 143.9 | 113.0 | 106.8 | 106.5 | 106.1 |
| 22.5° | 453.6 | 428.9 | 371.2 | 303.9 | 224.0 | 143.0 | 95.8 | 86.2 | 88.7 | 93.7 | 94.6 |
| 25° | 459.3 | 426.5 | 355.1 | 273.3 | 173.8 | 93.8 | 71.8 | 70.3 | 76.4 | 83.0 | 84.5 |
| 27.5° | 468.1 | 425.3 | 336.9 | 238.6 | 122.0 | 67.3 | 58.7 | 59.6 | 65.2 | 70.7 | 72.1 |
| 30° | 483.1 | 427.5 | 316.9 | 199.6 | 78.4 | 53.6 | 50.9 | 52.3 | 55.3 | 58.1 | 59.3 |
| 32.5° | 503.5 | 434.1 | 297.6 | 157.0 | 55.9 | 46.6 | 46.0 | 46.8 | 48.0 | 49.6 | 50.1 |
| 35° | 527.3 | 445.5 | 277.7 | 112.4 | 46.2 | 42.6 | 42.0 | 42.0 | 42.6 | 42.9 | 43.0 |
| 37.5° | 547.0 | 457.5 | 258.9 | 74.8 | 41.4 | 39.4 | 38.5 | 38.1 | 37.9 | 38.2 | 38.4 |
| 40° | 555.5 | 462.4 | 238.6 | 54.4 | 37.9 | 36.6 | 35.2 | 33.9 | 33.9 | 34.9 | 35.1 |
| 42.5° | 549.5 | 456.9 | 215.0 | 45.0 | 35.5 | 33.6 | 31.5 | 30.3 | 30.9 | 31.9 | 32.2 |
| 45° | 536.8 | 443.3 | 189.1 | 39.7 | 33.1 | 30.6 | 28.2 | 27.4 | 28.0 | 29.4 | 29.7 |
| 47.5° | 534.7 | 434.3 | 158.1 | 36.3 | 30.6 | 28.0 | 25.5 | 24.7 | 25.5 | 26.5 | 26.8 |
| 50° | 555.5 | 442.1 | 123.6 | 33.3 | 28.2 | 25.3 | 23.2 | 22.5 | 22.9 | 23.5 | 23.8 |
| 52.5° | 593.6 | 471.0 | 99.8 | 30.4 | 25.3 | 22.6 | 21.3 | 20.4 | 20.4 | 21.0 | 21.1 |
| 55° | 649.8 | 521.5 | 86.2 | 27.1 | 22.0 | 20.5 | 19.3 | 18.4 | 18.4 | 18.7 | 18.9 |
| 57.5° | 714.5 | 582.6 | 89.3 | 22.8 | 19.3 | 18.6 | 17.5 | 16.8 | 17.1 | 17.1 | 17.1 |
| 60° | 705.5 | 578.1 | 95.6 | 19.2 | 17.1 | 16.8 | 15.9 | 15.6 | 16.3 | 15.7 | 15.4 |
| 62.5° | 519.7 | 399.4 | 50.1 | 15.7 | 14.7 | 14.4 | 13.8 | 14.4 | 15.4 | 13.8 | 13.2 |
| 65° | 252.4 | 193.3 | 20.1 | 12.9 | 12.4 | 12.1 | 11.8 | 12.7 | 13.3 | 10.8 | 10.2 |
| 67.5° | 59.3 | 48.3 | 13.0 | 10.9 | 10.3 | 9.7 | 10.0 | 10.2 | 9.7 | 7.3 | 7.0 |
| 70° | 15.4 | 15.1 | 10.2 | 9.1 | 8.2 | 7.6 | 7.6 | 7.5 | 6.4 | 4.6 | 4.3 |
| 72.5° | 8.4 | 8.2 | 7.3 | 6.9 | 5.7 | 5.1 | 5.2 | 4.6 | 3.6 | 2.7 | 2.5 |
| 75° | 4.2 | 4.5 | 4.2 | 3.9 | 3.1 | 2.8 | 2.8 | 2.5 | 1.8 | 1.0 | 1.0 |
| 77.5° | 0.9 | 1.0 | 1.0 | 0.9 | 0.7 | 0.6 | 0.6 | 0.7 | 0.3 | 0.0 | 0.0 |
| 80° | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)