

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629031

Luminaire Tested: GWS-SA1A-827-U-T2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-827-U-T2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS W/ FACTORY INSALLED GLARE SHIELD, WH
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1742.9 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629031
 CATALOG NUMBER: GWS-SA1A-827-U-T2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.6 fc
 Type II - Short - N/A

REPORT NUMBER: P629031
CATALOG NUMBER: GWS-SA1A-827-U-T2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P629031
 CATALOG NUMBER: GWS-SA1A-827-U-T2-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 471.5 | 0.0 | 471.5 |
| | % Fixture | 27.1 | 0.0 | 27.1 |
| Street Side | Lumens | 1271.4 | 0.0 | 1271.4 |
| | % Fixture | 72.9 | 0.0 | 72.9 |
| Total | Lumens | 1742.9 | 0.0 | 1742.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 32.7 | 1.9 |
| 10°-20° | 104.0 | 6.0 |
| 20°-30° | 184.4 | 10.6 |
| 30°-40° | 282.3 | 16.2 |
| 40°-50° | 393.1 | 22.6 |
| 50°-60° | 450.4 | 25.8 |
| 60°-70° | 231.4 | 13.3 |
| 70°-80° | 58.3 | 3.3 |
| 80°-90° | 6.2 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1742.9 | 100.0 |
| 0°-180° | 1742.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P629031

CATALOG NUMBER: GWS-SA1A-827-U-T2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 195.8 | 11.2 | | | |
| FM (30°-60°) | 877.9 | 50.4 | | | |
| FH (60°-80°) | 195.4 | 11.2 | | | G0/660 |
| FVH (80°-90°) | 2.3 | 0.1 | | | G0/10 |
| BL (0°-30°) | 125.3 | 7.2 | B1/500 | | |
| BM (30°-60°) | 248.0 | 14.2 | B1/1000 | | |
| BH (60°-80°) | 94.3 | 5.4 | B0/110 | | G0/110 |
| BVH (80°-90°) | 3.9 | 0.2 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0
 Type II Short





REPORT NUMBER: P629031

CATALOG NUMBER: GWS-SA1A-827-U-T2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 74° | 75° | 85° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|-------|
| 0° | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 |
| 2.5° | 350.7 | 351.6 | 350.7 | 352.2 | 349.2 | 347.8 | 344.5 | 339.6 | 335.7 | 335.1 | 330.7 |
| 5° | 378.0 | 379.9 | 378.7 | 378.1 | 374.1 | 371.1 | 366.1 | 356.2 | 348.1 | 346.9 | 338.4 |
| 7.5° | 395.5 | 396.8 | 396.8 | 397.3 | 395.8 | 392.3 | 387.1 | 375.4 | 364.0 | 362.2 | 349.3 |
| 10° | 401.3 | 402.4 | 404.3 | 408.1 | 411.1 | 412.1 | 408.7 | 397.4 | 383.5 | 381.7 | 363.7 |
| 12.5° | 402.7 | 403.9 | 406.9 | 413.8 | 422.0 | 429.5 | 430.1 | 421.9 | 406.3 | 404.3 | 380.4 |
| 15° | 405.2 | 406.4 | 410.5 | 419.0 | 431.2 | 445.5 | 454.4 | 448.7 | 431.5 | 429.4 | 399.2 |
| 17.5° | 404.9 | 406.3 | 412.3 | 423.7 | 440.0 | 460.8 | 477.9 | 480.3 | 462.5 | 458.9 | 420.7 |
| 20° | 404.2 | 405.4 | 411.8 | 425.8 | 446.0 | 474.6 | 505.5 | 517.9 | 498.7 | 495.4 | 445.7 |
| 22.5° | 410.2 | 411.5 | 416.5 | 428.0 | 449.1 | 485.3 | 531.0 | 560.9 | 541.8 | 537.1 | 474.5 |
| 25° | 423.7 | 425.6 | 428.6 | 436.6 | 454.8 | 494.7 | 557.0 | 609.6 | 590.0 | 584.5 | 505.8 |
| 27.5° | 444.5 | 446.9 | 451.1 | 454.8 | 467.6 | 506.7 | 583.0 | 664.2 | 644.6 | 638.7 | 538.9 |
| 30° | 470.0 | 473.1 | 478.5 | 481.1 | 489.8 | 524.4 | 611.1 | 720.4 | 709.0 | 700.9 | 576.2 |
| 32.5° | 505.2 | 509.5 | 514.6 | 515.4 | 520.6 | 551.2 | 639.0 | 776.1 | 776.0 | 770.3 | 618.6 |
| 35° | 551.0 | 555.7 | 556.7 | 557.8 | 560.3 | 588.1 | 672.7 | 826.9 | 846.6 | 840.0 | 664.8 |
| 37.5° | 601.1 | 607.8 | 609.5 | 604.9 | 608.4 | 632.4 | 710.7 | 867.7 | 908.0 | 901.0 | 709.5 |
| 40° | 654.6 | 657.3 | 661.8 | 654.5 | 659.0 | 683.2 | 747.8 | 893.8 | 953.9 | 946.4 | 744.7 |
| 42.5° | 693.0 | 697.9 | 704.7 | 702.0 | 704.5 | 726.7 | 773.9 | 906.4 | 986.6 | 979.1 | 770.0 |
| 45° | 734.6 | 736.1 | 740.5 | 739.9 | 741.4 | 762.1 | 792.6 | 911.9 | 1015.8 | 1009.0 | 791.6 |
| 47.5° | 770.9 | 773.1 | 776.0 | 772.7 | 769.4 | 782.9 | 807.9 | 916.7 | 1049.5 | 1041.4 | 814.2 |
| 50° | 805.8 | 807.8 | 811.2 | 801.6 | 789.3 | 792.8 | 815.4 | 923.3 | 1081.1 | 1075.4 | 832.0 |
| 52.5° | 812.3 | 814.4 | 830.5 | 832.5 | 816.8 | 804.6 | 828.6 | 937.8 | 1099.7 | 1096.1 | 838.5 |
| 55° | 731.2 | 734.9 | 767.2 | 804.2 | 843.0 | 839.1 | 849.7 | 945.5 | 1107.0 | 1107.9 | 850.0 |
| 57.5° | 567.5 | 572.9 | 620.0 | 670.8 | 752.5 | 820.1 | 852.4 | 943.5 | 1104.5 | 1109.4 | 861.9 |
| 60° | 372.3 | 375.4 | 431.2 | 488.1 | 572.8 | 666.3 | 763.0 | 908.5 | 1081.9 | 1088.9 | 858.9 |
| 62.5° | 224.8 | 228.4 | 273.2 | 316.4 | 366.3 | 428.8 | 517.5 | 730.1 | 906.8 | 922.6 | 687.9 |
| 65° | 156.9 | 161.7 | 201.0 | 236.5 | 253.7 | 240.8 | 262.1 | 407.8 | 565.0 | 571.6 | 420.4 |
| 67.5° | 113.7 | 117.0 | 149.3 | 191.5 | 210.6 | 170.1 | 129.6 | 180.6 | 246.1 | 248.5 | 173.4 |
| 70° | 74.5 | 78.2 | 107.5 | 145.8 | 171.9 | 137.9 | 97.0 | 97.7 | 103.6 | 104.8 | 100.7 |
| 72.5° | 40.9 | 43.2 | 66.4 | 96.8 | 101.6 | 82.4 | 75.7 | 81.2 | 85.3 | 85.3 | 86.3 |
| 75° | 21.1 | 23.1 | 27.1 | 31.9 | 38.5 | 45.1 | 54.6 | 62.8 | 67.1 | 67.4 | 67.0 |
| 77.5° | 10.8 | 11.5 | 14.5 | 15.7 | 17.2 | 20.1 | 26.1 | 33.4 | 37.3 | 38.8 | 38.5 |
| 80° | 5.1 | 5.4 | 6.1 | 7.2 | 8.8 | 11.2 | 14.1 | 16.8 | 19.2 | 19.5 | 21.1 |
| 82.5° | 2.7 | 3.0 | 3.3 | 3.9 | 4.8 | 6.0 | 8.2 | 9.9 | 11.4 | 11.7 | 13.0 |
| 85° | 1.0 | 1.2 | 1.3 | 1.5 | 2.1 | 2.5 | 3.4 | 4.6 | 5.7 | 5.7 | 6.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.1 | 0.3 | 0.6 | 0.7 | 1.0 | 1.0 | 1.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629031

CATALOG NUMBER: GWS-SA1A-827-U-T2-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 | 326.4 |
| 2.5° | 329.7 | 325.4 | 323.4 | 320.3 | 317.7 | 314.9 | 312.6 | 311.0 | 309.9 | 309.3 | 308.7 |
| 5° | 335.1 | 328.5 | 323.3 | 317.0 | 312.6 | 308.4 | 305.0 | 302.6 | 301.4 | 300.5 | 299.9 |
| 7.5° | 343.5 | 334.6 | 324.8 | 315.0 | 307.4 | 300.6 | 296.3 | 293.7 | 292.1 | 291.5 | 291.0 |
| 10° | 355.0 | 342.7 | 326.4 | 311.0 | 299.6 | 292.2 | 289.2 | 288.0 | 288.2 | 287.9 | 287.7 |
| 12.5° | 368.1 | 351.3 | 326.0 | 303.8 | 291.2 | 286.8 | 287.0 | 288.9 | 291.2 | 291.8 | 291.9 |
| 15° | 382.2 | 359.7 | 321.6 | 294.5 | 284.6 | 285.0 | 288.9 | 293.6 | 297.8 | 299.4 | 299.7 |
| 17.5° | 397.4 | 366.7 | 313.7 | 284.3 | 279.2 | 284.0 | 291.2 | 298.8 | 305.0 | 307.7 | 308.4 |
| 20° | 414.5 | 372.7 | 302.4 | 274.3 | 274.1 | 282.0 | 292.5 | 302.6 | 310.4 | 314.0 | 314.6 |
| 22.5° | 432.7 | 376.5 | 288.6 | 265.0 | 268.9 | 279.5 | 291.5 | 302.0 | 310.2 | 313.8 | 314.6 |
| 25° | 450.9 | 377.7 | 273.5 | 256.4 | 263.5 | 275.4 | 286.4 | 294.8 | 302.6 | 305.7 | 306.3 |
| 27.5° | 468.0 | 374.2 | 259.1 | 249.1 | 258.5 | 269.5 | 276.8 | 281.3 | 286.7 | 289.1 | 289.5 |
| 30° | 485.4 | 367.3 | 247.0 | 243.2 | 253.0 | 261.2 | 264.5 | 264.8 | 266.9 | 266.9 | 267.2 |
| 32.5° | 502.9 | 357.1 | 236.3 | 237.5 | 246.1 | 251.5 | 251.9 | 248.5 | 245.9 | 241.7 | 241.6 |
| 35° | 523.2 | 346.8 | 227.6 | 231.1 | 238.0 | 241.3 | 239.9 | 233.3 | 227.2 | 220.3 | 220.0 |
| 37.5° | 541.9 | 336.1 | 220.3 | 224.5 | 228.8 | 231.2 | 228.1 | 220.1 | 215.1 | 208.0 | 207.0 |
| 40° | 557.3 | 326.6 | 213.3 | 217.6 | 219.7 | 221.8 | 216.7 | 210.3 | 211.0 | 207.1 | 207.0 |
| 42.5° | 566.3 | 317.3 | 206.7 | 210.0 | 211.3 | 212.8 | 208.3 | 203.5 | 207.6 | 204.6 | 204.7 |
| 45° | 572.9 | 309.2 | 200.7 | 201.9 | 205.2 | 207.4 | 203.2 | 197.8 | 198.7 | 187.2 | 184.5 |
| 47.5° | 580.4 | 304.7 | 195.0 | 193.8 | 199.6 | 203.5 | 197.1 | 189.3 | 183.9 | 172.5 | 171.4 |
| 50° | 588.4 | 303.0 | 189.0 | 185.7 | 192.7 | 196.5 | 189.0 | 179.2 | 172.2 | 166.0 | 165.4 |
| 52.5° | 591.1 | 302.9 | 181.5 | 175.9 | 183.0 | 188.2 | 181.9 | 172.0 | 163.7 | 157.7 | 157.4 |
| 55° | 601.7 | 307.2 | 171.9 | 162.6 | 169.2 | 180.0 | 175.3 | 161.1 | 154.4 | 151.7 | 151.4 |
| 57.5° | 614.1 | 308.0 | 156.8 | 148.1 | 157.2 | 169.9 | 164.1 | 151.8 | 144.5 | 141.2 | 140.9 |
| 60° | 609.0 | 289.5 | 140.6 | 137.0 | 147.0 | 160.5 | 155.1 | 144.5 | 135.9 | 132.8 | 132.5 |
| 62.5° | 464.1 | 204.4 | 128.7 | 127.4 | 136.1 | 146.9 | 145.8 | 134.7 | 126.6 | 124.4 | 124.1 |
| 65° | 279.2 | 143.6 | 117.3 | 117.2 | 123.3 | 133.7 | 135.0 | 126.0 | 117.5 | 114.3 | 114.3 |
| 67.5° | 138.0 | 109.9 | 104.5 | 103.7 | 107.6 | 114.9 | 120.6 | 113.3 | 106.1 | 103.1 | 102.7 |
| 70° | 97.6 | 96.8 | 95.0 | 92.9 | 93.7 | 96.7 | 99.1 | 92.9 | 85.3 | 82.3 | 81.7 |
| 72.5° | 84.4 | 84.5 | 83.3 | 81.7 | 81.1 | 79.0 | 76.9 | 72.4 | 67.7 | 64.6 | 64.9 |
| 75° | 65.5 | 65.8 | 66.5 | 65.9 | 64.3 | 62.0 | 59.8 | 54.1 | 50.4 | 47.4 | 46.8 |
| 77.5° | 38.2 | 39.7 | 42.1 | 41.5 | 41.8 | 38.7 | 37.8 | 32.2 | 28.8 | 26.7 | 26.2 |
| 80° | 21.6 | 22.5 | 23.5 | 24.3 | 23.4 | 22.0 | 20.1 | 17.1 | 16.0 | 14.5 | 14.2 |
| 82.5° | 13.0 | 13.9 | 14.4 | 15.0 | 14.7 | 12.9 | 11.4 | 9.4 | 8.5 | 7.8 | 7.6 |
| 85° | 6.6 | 7.2 | 7.6 | 7.9 | 7.0 | 5.8 | 5.2 | 4.2 | 3.6 | 3.1 | 3.1 |
| 87.5° | 1.6 | 1.8 | 2.1 | 1.8 | 1.6 | 0.7 | 0.6 | 0.1 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797 M/P: 2.26


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)