

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629034

Luminaire Tested: GWS-SA1A-827-U-T2R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-827-U-T2R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1401.4 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G0


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629034
 CATALOG NUMBER: GWS-SA1A-827-U-T2R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5.1 fc
 Type II - Short - N/A

REPORT NUMBER: P629034
CATALOG NUMBER: GWS-SA1A-827-U-T2R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P629034

CATALOG NUMBER: GWS-SA1A-827-U-T2R-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 196.3 | 0.0 | 196.3 |
| | % Fixture | 14.0 | 0.0 | 14.0 |
| Street Side | Lumens | 1205.1 | 0.0 | 1205.1 |
| | % Fixture | 86.0 | 0.0 | 86.0 |
| Total | Lumens | 1401.4 | 0.0 | 1401.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 20.7 | 1.5 |
| 10°-20° | 82.1 | 5.9 |
| 20°-30° | 166.1 | 11.9 |
| 30°-40° | 293.9 | 21.0 |
| 40°-50° | 428.4 | 30.6 |
| 50°-60° | 343.4 | 24.5 |
| 60°-70° | 61.9 | 4.4 |
| 70°-80° | 4.9 | 0.3 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1401.4 | 100.0 |
| 0°-180° | 1401.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P629034

CATALOG NUMBER: GWS-SA1A-827-U-T2R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 208.5 | 14.9 | | | |
| FM (30°-60°) | 943.8 | 67.3 | | | |
| FH (60°-80°) | 52.8 | 3.8 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 60.4 | 4.3 | B0/110 | | |
| BM (30°-60°) | 121.9 | 8.7 | B0/220 | | |
| BH (60°-80°) | 13.9 | 1.0 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G0
 Type II Short





REPORT NUMBER: P629034

CATALOG NUMBER: GWS-SA1A-827-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|-------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0° | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 |
| 2.5° | 247.7 | 243.8 | 241.6 | 239.8 | 231.8 | 219.2 | 211.0 | 206.7 | 199.5 | 187.3 | 176.8 |
| 5° | 323.3 | 320.4 | 315.2 | 311.6 | 301.4 | 283.5 | 265.1 | 257.8 | 241.4 | 214.0 | 189.4 |
| 7.5° | 373.3 | 371.2 | 369.3 | 364.5 | 354.9 | 338.7 | 318.3 | 310.7 | 285.5 | 246.5 | 206.2 |
| 10° | 411.8 | 410.2 | 407.9 | 407.8 | 400.3 | 385.7 | 365.8 | 357.9 | 330.6 | 281.9 | 226.0 |
| 12.5° | 445.7 | 444.3 | 443.9 | 448.1 | 443.3 | 432.5 | 410.9 | 401.0 | 372.1 | 318.0 | 247.9 |
| 15° | 468.9 | 468.6 | 470.6 | 478.8 | 481.5 | 476.6 | 458.4 | 447.8 | 414.5 | 354.3 | 272.0 |
| 17.5° | 479.6 | 480.5 | 484.2 | 498.4 | 510.4 | 514.6 | 500.7 | 491.7 | 456.6 | 391.0 | 297.8 |
| 20° | 497.7 | 497.4 | 499.6 | 513.1 | 527.8 | 542.8 | 538.6 | 531.0 | 499.2 | 429.8 | 326.4 |
| 22.5° | 548.8 | 544.4 | 539.6 | 541.7 | 547.0 | 564.5 | 572.3 | 568.4 | 543.1 | 469.7 | 355.9 |
| 25° | 627.3 | 622.8 | 607.4 | 592.4 | 582.5 | 590.5 | 601.1 | 603.0 | 586.7 | 510.6 | 386.8 |
| 27.5° | 710.6 | 706.6 | 689.2 | 666.7 | 638.4 | 624.6 | 632.6 | 636.5 | 629.6 | 559.3 | 419.6 |
| 30° | 788.7 | 783.3 | 764.3 | 736.4 | 703.6 | 682.5 | 673.5 | 676.2 | 680.2 | 617.0 | 458.1 |
| 32.5° | 856.5 | 852.4 | 829.6 | 800.3 | 768.6 | 746.6 | 725.6 | 730.1 | 740.0 | 687.6 | 507.4 |
| 35° | 913.9 | 911.8 | 887.6 | 858.4 | 825.0 | 813.7 | 795.8 | 796.7 | 806.6 | 772.8 | 567.5 |
| 37.5° | 963.8 | 960.2 | 938.3 | 911.2 | 884.6 | 882.8 | 877.9 | 878.3 | 883.4 | 872.2 | 636.6 |
| 40° | 995.2 | 991.9 | 976.3 | 959.6 | 940.7 | 941.0 | 966.6 | 968.6 | 962.7 | 969.8 | 709.6 |
| 42.5° | 1007.1 | 1004.7 | 996.3 | 996.4 | 994.5 | 1003.3 | 1051.4 | 1055.0 | 1034.0 | 1046.3 | 771.9 |
| 45° | 986.5 | 985.5 | 986.1 | 1007.7 | 1031.0 | 1058.3 | 1120.8 | 1127.1 | 1097.4 | 1097.1 | 820.6 |
| 47.5° | 920.3 | 918.2 | 935.7 | 972.4 | 1026.5 | 1079.6 | 1162.8 | 1172.5 | 1141.8 | 1126.2 | 851.2 |
| 50° | 790.5 | 796.5 | 824.2 | 879.4 | 961.7 | 1050.4 | 1162.3 | 1179.3 | 1143.4 | 1123.7 | 846.1 |
| 52.5° | 572.6 | 571.4 | 632.1 | 707.9 | 808.1 | 956.9 | 1100.6 | 1125.3 | 1103.4 | 1098.6 | 834.7 |
| 55° | 311.6 | 322.5 | 363.4 | 463.8 | 588.8 | 779.9 | 959.6 | 1013.5 | 1038.8 | 1089.5 | 855.3 |
| 57.5° | 114.5 | 119.3 | 144.9 | 215.9 | 311.7 | 485.0 | 733.0 | 814.3 | 892.6 | 1064.0 | 851.8 |
| 60° | 46.2 | 47.1 | 57.2 | 79.4 | 131.0 | 246.8 | 439.7 | 511.9 | 585.7 | 814.5 | 653.7 |
| 62.5° | 33.6 | 34.8 | 38.8 | 46.5 | 66.2 | 107.9 | 189.6 | 220.4 | 241.0 | 403.4 | 322.1 |
| 65° | 27.1 | 28.0 | 31.3 | 34.8 | 43.8 | 58.0 | 61.1 | 58.9 | 58.6 | 104.3 | 73.9 |
| 67.5° | 22.5 | 23.4 | 25.8 | 28.2 | 31.5 | 28.9 | 21.0 | 22.0 | 18.0 | 17.8 | 14.5 |
| 70° | 16.5 | 17.5 | 19.9 | 22.5 | 18.9 | 7.8 | 12.1 | 18.0 | 13.6 | 11.4 | 11.1 |
| 72.5° | 12.4 | 13.2 | 15.4 | 14.7 | 5.5 | 3.0 | 8.1 | 13.0 | 10.5 | 8.4 | 8.2 |
| 75° | 9.3 | 9.7 | 7.8 | 2.4 | 0.6 | 0.7 | 3.0 | 5.4 | 5.8 | 4.8 | 4.8 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.4 | 0.6 | 0.7 | 0.9 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629034

CATALOG NUMBER: GWS-SA1A-827-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 | 167.4 |
| 2.5° | 170.8 | 164.5 | 155.6 | 148.1 | 142.4 | 136.8 | 132.6 | 128.4 | 128.3 | 126.2 | 125.7 |
| 5° | 178.0 | 166.6 | 150.2 | 138.3 | 131.1 | 126.8 | 123.8 | 122.3 | 121.5 | 120.8 | 120.5 |
| 7.5° | 188.4 | 172.0 | 149.3 | 136.7 | 130.7 | 127.8 | 125.7 | 124.8 | 124.4 | 123.8 | 123.6 |
| 10° | 201.1 | 179.8 | 152.6 | 139.8 | 134.6 | 131.9 | 129.6 | 128.3 | 127.5 | 126.5 | 126.2 |
| 12.5° | 216.4 | 189.4 | 157.8 | 145.1 | 139.5 | 135.9 | 132.9 | 131.0 | 129.9 | 128.6 | 128.3 |
| 15° | 232.9 | 199.8 | 163.6 | 149.9 | 143.3 | 138.6 | 134.9 | 131.9 | 129.9 | 128.3 | 127.8 |
| 17.5° | 250.0 | 210.3 | 168.9 | 153.2 | 145.1 | 139.5 | 134.1 | 130.1 | 127.7 | 125.6 | 125.0 |
| 20° | 269.2 | 221.0 | 172.3 | 153.8 | 144.5 | 137.1 | 130.8 | 125.7 | 123.3 | 120.5 | 119.9 |
| 22.5° | 289.2 | 231.1 | 173.8 | 152.4 | 141.2 | 132.6 | 125.9 | 120.6 | 117.2 | 114.2 | 113.3 |
| 25° | 308.7 | 240.1 | 173.1 | 148.7 | 136.2 | 126.3 | 119.4 | 114.0 | 110.3 | 107.3 | 106.6 |
| 27.5° | 329.4 | 247.6 | 170.4 | 143.1 | 129.5 | 119.4 | 112.8 | 108.2 | 104.8 | 101.5 | 100.7 |
| 30° | 352.6 | 254.5 | 166.0 | 136.4 | 121.5 | 112.4 | 107.3 | 104.2 | 100.4 | 97.0 | 95.9 |
| 32.5° | 380.6 | 260.6 | 159.8 | 128.3 | 114.5 | 106.3 | 103.4 | 101.0 | 96.7 | 93.1 | 92.3 |
| 35° | 412.7 | 265.7 | 151.8 | 119.9 | 107.6 | 102.4 | 101.8 | 98.6 | 92.9 | 88.7 | 87.8 |
| 37.5° | 449.9 | 270.6 | 142.4 | 111.6 | 102.5 | 100.6 | 100.7 | 95.3 | 88.4 | 83.3 | 82.7 |
| 40° | 489.9 | 275.6 | 131.9 | 104.5 | 97.9 | 99.5 | 98.2 | 90.5 | 79.3 | 74.3 | 73.7 |
| 42.5° | 531.6 | 281.0 | 121.2 | 97.7 | 94.0 | 95.5 | 93.5 | 80.9 | 72.8 | 70.3 | 70.0 |
| 45° | 569.2 | 287.4 | 109.7 | 91.0 | 90.1 | 89.6 | 86.3 | 73.3 | 69.8 | 68.0 | 67.9 |
| 47.5° | 596.3 | 286.4 | 97.4 | 84.5 | 85.9 | 84.4 | 74.3 | 69.7 | 66.8 | 64.4 | 63.8 |
| 50° | 591.4 | 268.1 | 84.7 | 77.3 | 80.5 | 79.1 | 66.8 | 65.5 | 62.9 | 60.4 | 59.5 |
| 52.5° | 578.8 | 243.2 | 73.6 | 69.7 | 74.6 | 71.5 | 61.7 | 60.4 | 58.1 | 54.8 | 53.8 |
| 55° | 585.5 | 219.8 | 64.9 | 63.5 | 68.6 | 59.2 | 56.0 | 53.9 | 51.6 | 48.0 | 47.5 |
| 57.5° | 563.8 | 179.4 | 52.2 | 53.1 | 60.7 | 50.5 | 49.2 | 45.9 | 41.8 | 39.4 | 39.1 |
| 60° | 390.2 | 96.4 | 32.7 | 33.7 | 43.9 | 42.4 | 44.1 | 41.1 | 36.1 | 33.9 | 33.4 |
| 62.5° | 179.2 | 38.7 | 17.8 | 17.1 | 23.1 | 28.8 | 37.8 | 37.5 | 31.3 | 27.7 | 27.4 |
| 65° | 43.5 | 17.7 | 12.7 | 12.0 | 13.0 | 17.2 | 24.6 | 29.5 | 25.3 | 21.1 | 20.7 |
| 67.5° | 14.1 | 14.4 | 11.7 | 10.9 | 11.5 | 12.9 | 14.7 | 16.3 | 16.2 | 14.8 | 14.5 |
| 70° | 11.2 | 13.0 | 10.8 | 9.9 | 9.9 | 10.3 | 9.9 | 7.9 | 6.9 | 7.5 | 7.8 |
| 72.5° | 8.4 | 9.9 | 8.5 | 7.6 | 7.3 | 7.2 | 6.1 | 4.5 | 3.1 | 2.8 | 2.7 |
| 75° | 4.9 | 5.5 | 5.2 | 4.5 | 4.2 | 3.7 | 3.0 | 1.9 | 1.0 | 0.7 | 0.4 |
| 77.5° | 0.9 | 1.0 | 1.2 | 0.9 | 0.7 | 0.6 | 0.4 | 0.1 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.1 | 0.1 | 0.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)