

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833249

Luminaire Tested: **TTN-D1-750-U-WQ-UPL2**

Issue Date: 5/15/2024

Test Information

Test Method: LM-79-08
Report Number: P833249
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND
Test Lab: INNOVATION CENTER
Issue Date: 5/15/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TTN-D1-750-U-WQ-UPL2
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
5000K, 70 CRI LEDS AND WIDE DISTRIBUTION
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3946.7 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')
IES Classification: Type V - Short
BUG Rating: B2 - U4 - G1


Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P833249
 CATALOG NUMBER: TTN-D1-750-U-WQ-UPL2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc
 Type V - Short - N/A

REPORT NUMBER: P833249
CATALOG NUMBER: TTN-D1-750-U-WQ-UPL2

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P833249

CATALOG NUMBER: TTN-D1-750-U-WQ-UPL2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1680.9	292.5	1973.3
	% Fixture	42.6	7.4	50.0
Street Side	Lumens	1680.9	292.5	1973.3
	% Fixture	42.6	7.4	50.0
Total	Lumens	3361.8	584.9	3946.7
	% Fixture	85.2	14.8	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.8	0.7
10°-20°	85.5	2.2
20°-30°	179.3	4.5
30°-40°	325.3	8.2
40°-50°	530.3	13.4
50°-60°	742.2	18.8
60°-70°	774.9	19.6
70°-80°	553.6	14.0
80°-90°	144.0	3.6
90°-100°	13.1	0.3
100°-110°	132.7	3.4
110°-120°	194.0	4.9
120°-130°	112.6	2.9
130°-140°	59.7	1.5
140°-150°	35.4	0.9
150°-160°	21.8	0.6
160°-170°	11.9	0.3
170°-180°	3.9	0.1
0°-90°	3361.8	85.2
0°-180°	3946.7	100.0

Coefficient of Utilization



REPORT NUMBER: P833249


CATALOG NUMBER: TTN-D1-750-U-WQ-UPL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	145.8	3.7			
FM (30°-60°)	798.9	20.2			
FH (60°-80°)	664.2	16.8			G1/1800
FVH (80°-90°)	72.0	1.8			G1/100
BL (0°-30°)	145.8	3.7	B1/500		
BM (30°-60°)	798.9	20.2	B1/1000		
BH (60°-80°)	664.2	16.8	B2/1000		G1/1800
BVH (80°-90°)	72.0	1.8			G1/100
UL (90°-100°)	13.1	0.3		U2/50	
UH (100°-180°)	571.8	14.5		U4/1000	

BUG Rating: B2-U4-G1

Type V Short





REPORT NUMBER: P833249
 CATALOG NUMBER: TTN-D1-750-U-WQ-UPL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9	284.9
2.5°	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1
5°	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1	282.1
7.5°	276.6	276.6	279.4	279.4	279.4	279.4	279.4	279.4	279.4	279.4	279.4
10°	276.6	276.6	279.4	279.4	282.1	282.1	282.1	279.4	279.4	276.6	276.6
12.5°	282.1	282.1	282.1	284.9	287.7	287.7	287.7	284.9	284.9	282.1	282.1
15°	290.4	293.2	293.2	296.0	298.7	298.7	298.7	296.0	296.0	293.2	293.2
17.5°	307.0	307.0	307.0	309.8	312.6	315.3	315.3	309.8	309.8	307.0	309.8
20°	323.6	326.4	326.4	329.1	331.9	334.7	331.9	329.1	326.4	326.4	326.4
22.5°	348.5	348.5	351.3	351.3	356.8	356.8	356.8	351.3	351.3	351.3	351.3
25°	376.2	376.2	378.9	381.7	387.2	387.2	384.5	378.9	378.9	378.9	381.7
27.5°	409.4	409.4	412.1	412.1	417.7	417.7	414.9	412.1	412.1	412.1	414.9
30°	439.8	439.8	445.3	448.1	450.8	450.8	450.8	445.3	445.3	442.5	442.5
32.5°	467.4	470.2	473.0	481.3	486.8	484.0	486.8	481.3	475.7	473.0	473.0
35°	497.9	500.6	506.2	514.5	522.8	522.8	522.8	514.5	508.9	503.4	506.2
37.5°	533.8	533.8	542.1	550.4	561.5	564.2	561.5	553.2	544.9	539.4	539.4
40°	572.5	572.5	580.8	589.1	603.0	605.7	603.0	591.9	580.8	578.1	578.1
42.5°	611.3	611.3	622.3	630.6	647.2	652.8	647.2	633.4	622.3	614.0	616.8
45°	652.8	655.5	669.4	686.0	705.3	713.6	705.3	688.7	672.1	655.5	655.5
47.5°	699.8	699.8	716.4	735.7	757.9	766.2	755.1	738.5	716.4	702.5	702.5
50°	730.2	733.0	755.1	780.0	807.7	813.2	804.9	780.0	755.1	735.7	733.0
52.5°	760.6	763.4	788.3	824.2	851.9	860.2	849.1	824.2	788.3	763.4	763.4
55°	780.0	785.5	813.2	851.9	882.3	896.2	879.6	851.9	810.4	782.8	780.0
57.5°	782.8	788.3	815.9	863.0	893.4	910.0	896.2	860.2	815.9	785.5	782.8
60°	777.2	780.0	807.7	857.4	893.4	904.5	893.4	854.7	804.9	780.0	774.5
62.5°	763.4	768.9	796.6	838.1	879.6	887.9	876.8	835.3	793.8	763.4	757.9
65°	719.1	724.7	766.2	807.7	843.6	851.9	843.6	807.7	763.4	719.1	713.6
67.5°	669.4	672.1	713.6	763.4	796.6	810.4	796.6	766.2	710.8	669.4	663.8
70°	616.8	619.6	652.8	705.3	738.5	755.1	741.3	708.1	650.0	614.0	611.3
72.5°	556.0	556.0	589.1	630.6	663.8	680.4	669.4	627.9	583.6	547.7	542.1
75°	473.0	475.7	511.7	542.1	578.1	589.1	578.1	544.9	503.4	467.4	461.9
77.5°	387.2	390.0	420.4	445.3	478.5	486.8	478.5	450.8	412.1	381.7	378.9
80°	293.2	296.0	320.8	343.0	370.6	381.7	373.4	345.7	315.3	287.7	279.4
82.5°	190.8	193.6	218.5	235.1	260.0	268.3	262.8	237.9	213.0	185.3	182.6
85°	85.7	88.5	110.6	124.5	143.8	152.1	146.6	124.5	105.1	80.2	74.7
87.5°	8.3	8.3	8.3	8.3	8.3	11.1	11.1	8.3	8.3	8.3	8.3
90°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0	5.0
92.5°	5.0	5.0	5.0	7.0	8.0	7.0	8.0	6.0	6.0	5.0	5.0
95°	6.0	6.0	7.0	9.0	11.0	12.0	12.0	7.0	7.0	6.0	6.0
97.5°	8.0	9.0	9.0	11.0	18.0	33.0	20.0	10.0	10.0	9.0	8.0
100°	13.0	14.0	14.0	25.0	53.0	71.1	51.0	26.0	19.0	14.0	14.0
102.5°	42.0	44.0	54.0	81.1	120.1	109.1	92.1	87.1	60.0	48.0	46.0
105°	107.1	106.1	114.1	135.1	168.1	165.1	152.1	138.1	119.1	110.1	110.1
107.5°	141.1	141.1	148.1	166.1	191.1	223.2	226.2	179.1	157.1	147.1	146.1
110°	159.1	159.1	165.1	180.1	213.2	258.2	256.2	221.2	194.1	181.1	179.1



REPORT NUMBER: P833249
 CATALOG NUMBER: TTN-D1-750-U-WQ-UPL2

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	163.1	164.1	172.1	195.1	231.2	251.2	242.2	228.2	216.2	206.2	204.2
115°	169.1	169.1	178.1	200.2	220.2	228.2	218.2	207.2	199.2	195.1	197.1
117.5°	167.1	170.1	172.1	184.1	197.1	203.2	198.1	183.1	177.1	175.1	172.1
120°	155.1	155.1	157.1	163.1	170.1	173.1	171.1	161.1	156.1	155.1	153.1
122.5°	138.1	139.1	138.1	141.1	146.1	149.1	147.1	139.1	137.1	137.1	135.1
125°	121.1	121.1	120.1	122.1	125.1	124.1	125.1	121.1	120.1	120.1	119.1
127.5°	109.1	108.1	106.1	107.1	108.1	108.1	109.1	105.1	106.1	107.1	106.1
130°	97.1	97.1	95.1	95.1	95.1	93.1	95.1	93.1	94.1	95.1	96.1
132.5°	86.1	86.1	83.1	82.1	82.1	82.1	83.1	82.1	84.1	86.1	86.1
135°	77.1	77.1	74.1	75.1	75.1	74.1	75.1	74.1	76.1	77.1	77.1
137.5°	70.1	70.1	68.1	68.1	68.1	67.1	68.1	68.1	69.1	71.1	72.1
140°	64.0	64.0	63.0	63.0	62.0	63.0	63.0	63.0	64.0	65.0	65.0
142.5°	61.0	60.0	59.0	58.0	59.0	59.0	59.0	58.0	59.0	61.0	61.0
145°	56.0	56.0	55.0	55.0	55.0	56.0	55.0	55.0	56.0	56.0	57.0
147.5°	53.0	53.0	52.0	53.0	53.0	53.0	53.0	52.0	53.0	53.0	54.0
150°	52.0	51.0	50.0	51.0	51.0	50.0	50.0	50.0	50.0	51.0	51.0
152.5°	49.0	49.0	48.0	49.0	48.0	48.0	48.0	48.0	48.0	49.0	50.0
155°	47.0	47.0	46.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
157.5°	45.0	46.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.0	46.0
160°	44.0	44.0	44.0	44.0	43.0	43.0	43.0	44.0	44.0	44.0	45.0
162.5°	43.0	43.0	43.0	43.0	42.0	42.0	42.0	42.0	43.0	43.0	44.0
165°	43.0	42.0	42.0	42.0	41.0	41.0	41.0	41.0	42.0	43.0	42.0
167.5°	41.0	41.0	41.0	41.0	41.0	40.0	40.0	41.0	41.0	41.0	42.0
170°	41.0	41.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	41.0
172.5°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	40.0	40.0	41.0	41.0
175°	41.0	41.0	41.0	41.0	40.0	40.0	40.0	41.0	41.0	41.0	40.0
177.5°	41.0	41.0	41.0	41.0	40.0	41.0	41.0	41.0	41.0	41.0	41.0
180°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0

(END OF REPORT)