

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629038

Luminaire Tested: GWS-SA1A-827-U-T3-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-827-U-T3-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1290.9 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G0


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629038
 CATALOG NUMBER: GWS-SA1A-827-U-T3-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.1 fc
 Type II - Short - N/A

REPORT NUMBER: P629038
CATALOG NUMBER: GWS-SA1A-827-U-T3-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P629038
 CATALOG NUMBER: GWS-SA1A-827-U-T3-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 280.0 | 0.0 | 280.0 |
| | % Fixture | 21.7 | 0.0 | 21.7 |
| Street Side | Lumens | 1010.8 | 0.0 | 1010.8 |
| | % Fixture | 78.3 | 0.0 | 78.3 |
| Total | Lumens | 1290.9 | 0.0 | 1290.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 21.5 | 1.7 |
| 10°-20° | 72.5 | 5.6 |
| 20°-30° | 134.7 | 10.4 |
| 30°-40° | 215.6 | 16.7 |
| 40°-50° | 315.2 | 24.4 |
| 50°-60° | 389.0 | 30.1 |
| 60°-70° | 130.0 | 10.1 |
| 70°-80° | 12.1 | 0.9 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1290.9 | 100.0 |
| 0°-180° | 1290.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P629038

CATALOG NUMBER: GWS-SA1A-827-U-T3-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 133.4 | 10.3 | | | |
| FM (30°-60°) | 756.5 | 58.6 | | | |
| FH (60°-80°) | 120.8 | 9.4 | | | G0/660 |
| FVH (80°-90°) | 0.2 | 0.0 | | | G0/10 |
| BL (0°-30°) | 95.3 | 7.4 | B0/110 | | |
| BM (30°-60°) | 163.4 | 12.7 | B0/220 | | |
| BH (60°-80°) | 21.3 | 1.6 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.1 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G0
 Type II Short





REPORT NUMBER: P629038
 CATALOG NUMBER: GWS-SA1A-827-U-T3-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 |
| 2.5° | 218.3 | 218.2 | 218.0 | 218.9 | 218.6 | 218.5 | 218.8 | 218.8 | 218.8 | 217.9 | 216.1 |
| 5° | 223.6 | 223.6 | 223.4 | 224.3 | 223.6 | 223.1 | 223.3 | 223.3 | 222.7 | 221.0 | 218.8 |
| 7.5° | 231.8 | 231.5 | 231.2 | 232.1 | 231.4 | 231.2 | 231.5 | 230.6 | 229.6 | 226.9 | 223.7 |
| 10° | 243.7 | 243.7 | 243.2 | 244.1 | 243.5 | 243.2 | 243.2 | 242.6 | 240.7 | 236.5 | 231.8 |
| 12.5° | 260.0 | 259.3 | 258.2 | 257.5 | 257.2 | 257.0 | 257.2 | 256.3 | 254.2 | 248.8 | 242.3 |
| 15° | 277.8 | 277.2 | 275.6 | 274.4 | 272.7 | 272.4 | 273.3 | 272.6 | 270.5 | 263.2 | 254.0 |
| 17.5° | 300.3 | 301.1 | 296.9 | 294.3 | 289.5 | 289.2 | 289.5 | 290.7 | 289.2 | 279.8 | 266.5 |
| 20° | 319.5 | 320.1 | 317.0 | 315.2 | 310.8 | 308.9 | 309.5 | 311.4 | 309.8 | 298.7 | 280.1 |
| 22.5° | 340.0 | 340.8 | 337.5 | 333.7 | 331.8 | 331.8 | 334.0 | 336.7 | 334.5 | 320.0 | 295.7 |
| 25° | 364.6 | 365.2 | 362.5 | 357.6 | 354.1 | 358.5 | 361.8 | 369.0 | 365.2 | 345.4 | 314.1 |
| 27.5° | 392.8 | 392.9 | 389.0 | 383.9 | 382.1 | 390.2 | 393.5 | 404.6 | 403.1 | 374.1 | 333.6 |
| 30° | 422.9 | 423.1 | 422.2 | 418.7 | 417.1 | 427.7 | 432.2 | 448.2 | 447.2 | 409.6 | 360.1 |
| 32.5° | 454.2 | 454.2 | 455.9 | 455.6 | 457.5 | 474.9 | 482.1 | 500.4 | 499.3 | 453.0 | 393.1 |
| 35° | 485.7 | 485.8 | 488.7 | 495.9 | 504.0 | 527.1 | 536.5 | 558.7 | 556.3 | 505.0 | 435.2 |
| 37.5° | 521.5 | 520.0 | 523.9 | 534.7 | 552.7 | 579.4 | 588.4 | 609.5 | 606.8 | 558.2 | 490.2 |
| 40° | 564.7 | 562.0 | 562.0 | 574.6 | 594.9 | 625.7 | 633.3 | 643.8 | 634.7 | 601.2 | 544.1 |
| 42.5° | 612.3 | 609.8 | 606.5 | 617.6 | 634.7 | 658.6 | 664.9 | 662.1 | 654.6 | 641.9 | 605.6 |
| 45° | 660.6 | 656.7 | 658.9 | 665.7 | 675.6 | 687.0 | 689.4 | 676.2 | 672.7 | 676.3 | 656.4 |
| 47.5° | 697.3 | 694.6 | 700.1 | 709.6 | 717.7 | 719.3 | 717.7 | 699.4 | 699.1 | 711.8 | 691.6 |
| 50° | 709.6 | 709.9 | 725.2 | 745.9 | 758.9 | 760.2 | 758.0 | 737.0 | 734.2 | 737.9 | 710.6 |
| 52.5° | 710.8 | 712.0 | 734.3 | 773.7 | 809.2 | 825.4 | 823.6 | 801.0 | 773.1 | 769.1 | 739.4 |
| 55° | 681.9 | 688.9 | 720.1 | 777.6 | 853.2 | 904.9 | 910.8 | 867.5 | 826.2 | 822.7 | 801.3 |
| 57.5° | 545.0 | 559.4 | 597.0 | 679.0 | 804.1 | 913.1 | 928.7 | 897.5 | 857.5 | 842.8 | 784.7 |
| 60° | 325.8 | 343.6 | 379.7 | 480.3 | 612.0 | 750.5 | 777.3 | 781.7 | 763.2 | 720.8 | 602.0 |
| 62.5° | 139.8 | 138.3 | 182.8 | 259.9 | 364.0 | 477.0 | 489.1 | 508.0 | 524.1 | 479.7 | 365.4 |
| 65° | 48.0 | 52.2 | 72.5 | 117.2 | 182.2 | 221.5 | 232.3 | 249.2 | 272.0 | 224.5 | 133.8 |
| 67.5° | 29.7 | 31.5 | 41.8 | 69.2 | 98.3 | 96.8 | 92.0 | 89.3 | 86.9 | 59.5 | 36.7 |
| 70° | 21.6 | 23.1 | 29.4 | 47.7 | 66.1 | 46.5 | 40.3 | 32.7 | 36.3 | 33.4 | 26.1 |
| 72.5° | 14.5 | 15.7 | 20.2 | 28.9 | 33.9 | 22.6 | 21.0 | 23.8 | 28.8 | 27.4 | 21.3 |
| 75° | 8.7 | 9.4 | 11.5 | 14.1 | 13.8 | 11.7 | 11.8 | 16.8 | 22.0 | 20.5 | 15.1 |
| 77.5° | 6.0 | 6.3 | 7.6 | 9.1 | 6.7 | 3.6 | 3.3 | 4.6 | 7.5 | 7.5 | 5.1 |
| 80° | 1.5 | 1.9 | 1.9 | 1.2 | 1.0 | 0.9 | 0.9 | 1.3 | 2.1 | 1.5 | 0.7 |
| 82.5° | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.3 | 0.3 | 0.3 | 0.3 |
| 85° | 0.0 | 0.0 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.3 | 0.3 | 0.3 |
| 87.5° | 0.0 | 0.0 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.1 | 0.3 | 0.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629038
 CATALOG NUMBER: GWS-SA1A-827-U-T3-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 | 216.1 |
| 2.5° | 217.1 | 215.3 | 216.5 | 216.2 | 217.1 | 217.4 | 216.1 | 215.8 | 215.9 | 214.1 | 213.6 |
| 5° | 219.2 | 217.1 | 217.7 | 217.1 | 218.2 | 219.1 | 218.6 | 219.2 | 220.0 | 218.6 | 218.0 |
| 7.5° | 223.7 | 221.6 | 221.5 | 220.6 | 222.1 | 222.7 | 222.5 | 224.2 | 225.7 | 224.8 | 223.9 |
| 10° | 231.5 | 228.7 | 228.4 | 227.6 | 228.1 | 228.5 | 226.9 | 227.2 | 228.5 | 227.5 | 227.0 |
| 12.5° | 241.1 | 237.7 | 236.9 | 235.1 | 235.1 | 232.9 | 229.3 | 228.5 | 229.6 | 228.8 | 228.1 |
| 15° | 251.5 | 246.8 | 245.6 | 242.5 | 239.5 | 235.3 | 231.5 | 230.6 | 231.4 | 230.5 | 229.9 |
| 17.5° | 263.0 | 257.8 | 253.9 | 248.3 | 241.7 | 236.8 | 232.6 | 230.6 | 229.4 | 227.6 | 227.5 |
| 20° | 274.4 | 267.5 | 260.9 | 252.1 | 243.4 | 235.9 | 229.0 | 223.9 | 219.5 | 216.8 | 215.8 |
| 22.5° | 287.6 | 277.4 | 266.8 | 254.3 | 241.9 | 230.5 | 218.3 | 209.7 | 202.2 | 199.6 | 198.4 |
| 25° | 301.7 | 288.5 | 272.6 | 256.4 | 236.8 | 218.5 | 202.0 | 189.1 | 179.2 | 175.9 | 174.6 |
| 27.5° | 317.3 | 299.1 | 278.6 | 256.0 | 226.3 | 201.4 | 179.5 | 163.5 | 153.8 | 150.8 | 151.8 |
| 30° | 337.0 | 312.9 | 286.1 | 251.3 | 210.6 | 177.4 | 151.8 | 138.3 | 131.0 | 128.1 | 128.3 |
| 32.5° | 363.4 | 332.7 | 297.0 | 241.4 | 190.3 | 150.2 | 127.7 | 117.8 | 112.8 | 109.1 | 108.8 |
| 35° | 401.2 | 362.8 | 307.2 | 225.5 | 165.7 | 125.9 | 109.5 | 101.8 | 94.9 | 90.5 | 91.3 |
| 37.5° | 446.4 | 400.7 | 312.8 | 204.1 | 138.2 | 107.0 | 95.9 | 88.0 | 80.2 | 73.7 | 74.5 |
| 40° | 500.1 | 450.3 | 312.3 | 175.9 | 113.0 | 94.1 | 84.5 | 75.2 | 65.5 | 59.6 | 60.2 |
| 42.5° | 559.9 | 497.2 | 302.6 | 146.1 | 93.7 | 83.6 | 73.6 | 61.9 | 52.5 | 48.9 | 49.0 |
| 45° | 611.7 | 535.3 | 285.5 | 115.2 | 78.8 | 73.4 | 62.2 | 50.2 | 46.0 | 43.5 | 43.3 |
| 47.5° | 650.1 | 563.2 | 261.1 | 90.7 | 66.8 | 64.1 | 51.1 | 45.0 | 41.7 | 39.6 | 39.3 |
| 50° | 671.5 | 572.9 | 234.1 | 71.0 | 56.5 | 54.4 | 45.7 | 40.8 | 38.5 | 37.2 | 36.9 |
| 52.5° | 700.3 | 584.6 | 214.7 | 56.0 | 47.4 | 44.5 | 42.1 | 37.9 | 36.4 | 35.4 | 34.9 |
| 55° | 745.9 | 607.2 | 198.0 | 44.5 | 39.4 | 38.8 | 39.7 | 36.3 | 35.4 | 33.7 | 33.1 |
| 57.5° | 703.0 | 545.5 | 153.8 | 34.5 | 33.3 | 35.5 | 38.4 | 34.6 | 32.4 | 30.9 | 30.3 |
| 60° | 494.7 | 362.7 | 77.3 | 27.7 | 29.7 | 33.3 | 36.1 | 31.3 | 29.1 | 29.4 | 29.1 |
| 62.5° | 272.7 | 181.5 | 34.8 | 23.2 | 25.8 | 29.4 | 30.9 | 27.1 | 25.6 | 28.2 | 28.6 |
| 65° | 89.2 | 61.7 | 20.1 | 18.0 | 20.4 | 24.0 | 26.7 | 25.8 | 25.5 | 28.5 | 29.4 |
| 67.5° | 27.4 | 20.4 | 13.6 | 12.9 | 14.1 | 17.7 | 22.5 | 27.9 | 30.0 | 30.9 | 31.3 |
| 70° | 20.5 | 16.0 | 11.7 | 10.9 | 11.5 | 13.5 | 19.0 | 23.2 | 21.9 | 22.0 | 21.7 |
| 72.5° | 16.5 | 12.7 | 10.0 | 9.6 | 9.6 | 9.3 | 10.0 | 12.6 | 14.2 | 15.0 | 15.0 |
| 75° | 11.5 | 9.0 | 7.6 | 7.0 | 5.5 | 4.5 | 4.0 | 4.0 | 3.6 | 3.4 | 3.3 |
| 77.5° | 3.9 | 3.3 | 3.0 | 2.4 | 1.6 | 1.3 | 1.2 | 1.0 | 0.7 | 0.4 | 0.3 |
| 80° | 0.6 | 0.4 | 0.3 | 0.3 | 0.3 | 0.1 | 0.1 | 0.1 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.1 | 0.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.1 | 0.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.3 | 0.3 | 0.3 | 0.3 | 0.1 | 0.1 | 0.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797 M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)