

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634463

Luminaire Tested: GWS-SA3B-827-U-SL4-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P634463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3B-827-U-SL4-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7343.4 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 68.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P634463
 CATALOG NUMBER: GWS-SA3B-827-U-SL4-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P634463
CATALOG NUMBER: GWS-SA3B-827-U-SL4-W

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P634463

CATALOG NUMBER: GWS-SA3B-827-U-SL4-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1131.1 | 0.0 | 1131.1 |
| | % Fixture | 15.4 | 0.0 | 15.4 |
| Street Side | Lumens | 6212.3 | 0.0 | 6212.3 |
| | % Fixture | 84.6 | 0.0 | 84.6 |
| Total | Lumens | 7343.4 | 0.0 | 7343.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 110.2 | 1.5 |
| 10°-20° | 287.1 | 3.9 |
| 20°-30° | 450.9 | 6.1 |
| 30°-40° | 677.9 | 9.2 |
| 40°-50° | 1046.3 | 14.2 |
| 50°-60° | 1553.9 | 21.2 |
| 60°-70° | 1958.7 | 26.7 |
| 70°-80° | 1132.7 | 15.4 |
| 80°-90° | 125.7 | 1.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 7343.4 | 100.0 |
| 0°-180° | 7343.4 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P634463


CATALOG NUMBER: GWS-SA3B-827-U-SL4-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 556.7 | 7.6 | | | |
| FM (30°-60°) | 2720.6 | 37.0 | | | |
| FH (60°-80°) | 2830.3 | 38.5 | | | G2/5000 |
| FVH (80°-90°) | 104.7 | 1.4 | | | G2/225 |
| BL (0°-30°) | 291.5 | 4.0 | B1/500 | | |
| BM (30°-60°) | 557.5 | 7.6 | B1/1000 | | |
| BH (60°-80°) | 261.0 | 3.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 21.0 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P634463
 CATALOG NUMBER: GWS-SA3B-827-U-SL4-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 40° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 |
| 2.5° | 1254.7 | 1256.9 | 1258.5 | 1260.7 | 1259.6 | 1256.3 | 1259.1 | 1259.1 | 1253.0 | 1246.4 | 1240.4 |
| 5° | 1256.3 | 1259.1 | 1258.5 | 1258.0 | 1253.6 | 1248.1 | 1248.1 | 1244.8 | 1234.4 | 1224.0 | 1214.1 |
| 7.5° | 1253.0 | 1252.5 | 1251.9 | 1250.3 | 1245.3 | 1239.3 | 1238.2 | 1231.6 | 1217.9 | 1203.7 | 1189.4 |
| 10° | 1238.2 | 1237.7 | 1239.3 | 1243.2 | 1242.1 | 1236.6 | 1236.6 | 1230.5 | 1214.7 | 1197.1 | 1178.5 |
| 12.5° | 1226.2 | 1226.2 | 1232.7 | 1243.2 | 1247.0 | 1244.8 | 1245.3 | 1241.0 | 1222.9 | 1202.0 | 1180.1 |
| 15° | 1227.8 | 1228.4 | 1242.6 | 1259.6 | 1266.7 | 1265.1 | 1265.6 | 1260.7 | 1240.4 | 1219.6 | 1190.0 |
| 17.5° | 1238.8 | 1241.5 | 1266.2 | 1289.7 | 1299.1 | 1296.9 | 1293.0 | 1284.8 | 1261.8 | 1238.2 | 1202.0 |
| 20° | 1261.8 | 1266.2 | 1298.0 | 1327.6 | 1338.5 | 1333.6 | 1327.0 | 1310.6 | 1285.4 | 1259.6 | 1215.2 |
| 22.5° | 1307.3 | 1310.0 | 1345.1 | 1374.2 | 1382.9 | 1376.9 | 1363.7 | 1340.2 | 1311.1 | 1284.3 | 1231.1 |
| 25° | 1371.4 | 1374.7 | 1408.1 | 1435.0 | 1432.8 | 1425.7 | 1407.6 | 1378.5 | 1344.0 | 1315.5 | 1254.1 |
| 27.5° | 1447.6 | 1453.1 | 1486.0 | 1507.4 | 1493.1 | 1482.7 | 1462.4 | 1427.3 | 1388.4 | 1362.6 | 1289.2 |
| 30° | 1530.9 | 1533.1 | 1561.1 | 1582.4 | 1560.5 | 1546.3 | 1521.6 | 1483.8 | 1448.7 | 1429.5 | 1341.8 |
| 32.5° | 1611.5 | 1613.7 | 1637.8 | 1649.9 | 1626.8 | 1616.4 | 1595.1 | 1555.0 | 1530.4 | 1520.0 | 1420.2 |
| 35° | 1696.5 | 1695.9 | 1715.6 | 1726.1 | 1702.5 | 1698.1 | 1676.2 | 1645.5 | 1641.1 | 1654.8 | 1534.8 |
| 37.5° | 1781.4 | 1776.5 | 1786.9 | 1800.6 | 1787.4 | 1791.8 | 1777.6 | 1767.2 | 1784.2 | 1819.8 | 1687.1 |
| 40° | 1849.4 | 1849.4 | 1860.3 | 1877.3 | 1881.7 | 1900.9 | 1892.7 | 1906.4 | 1961.2 | 2046.2 | 1875.7 |
| 42.5° | 1909.7 | 1910.2 | 1933.3 | 1959.6 | 1991.4 | 2021.0 | 2027.5 | 2063.2 | 2176.6 | 2309.8 | 2112.5 |
| 45° | 1972.7 | 1973.3 | 2004.5 | 2042.9 | 2110.3 | 2166.8 | 2179.9 | 2259.9 | 2422.2 | 2584.4 | 2369.6 |
| 47.5° | 2045.6 | 2039.6 | 2082.9 | 2147.0 | 2242.9 | 2324.1 | 2358.1 | 2471.5 | 2676.5 | 2876.0 | 2611.8 |
| 50° | 2127.8 | 2115.2 | 2163.5 | 2274.2 | 2392.6 | 2503.9 | 2560.9 | 2690.8 | 2949.5 | 3145.2 | 2839.9 |
| 52.5° | 2220.5 | 2213.3 | 2263.8 | 2398.6 | 2579.5 | 2707.8 | 2785.0 | 2955.5 | 3214.8 | 3413.2 | 3020.7 |
| 55° | 2335.6 | 2318.6 | 2391.5 | 2563.1 | 2798.7 | 2962.1 | 3053.6 | 3217.5 | 3504.7 | 3656.6 | 3158.9 |
| 57.5° | 2461.6 | 2443.0 | 2540.6 | 2768.6 | 3083.8 | 3263.0 | 3377.6 | 3512.4 | 3777.7 | 3842.9 | 3240.0 |
| 60° | 2597.6 | 2591.6 | 2707.2 | 3009.8 | 3423.6 | 3631.9 | 3714.7 | 3836.9 | 4015.0 | 3950.9 | 3219.7 |
| 62.5° | 2722.0 | 2719.8 | 2888.1 | 3271.2 | 3783.7 | 4012.9 | 4078.6 | 4111.0 | 4186.1 | 3943.8 | 3058.6 |
| 65° | 2853.0 | 2871.6 | 3099.1 | 3574.3 | 4196.5 | 4421.2 | 4448.6 | 4366.4 | 4243.6 | 3756.9 | 2728.6 |
| 67.5° | 2869.5 | 2905.6 | 3231.8 | 3858.3 | 4587.8 | 4800.0 | 4778.0 | 4463.4 | 4073.7 | 3236.7 | 2138.8 |
| 70° | 2566.3 | 2629.4 | 3020.2 | 3901.6 | 4863.5 | 5019.8 | 4861.4 | 4254.6 | 3457.0 | 2344.9 | 1345.1 |
| 72.5° | 2144.3 | 2198.5 | 2543.9 | 3327.1 | 4507.8 | 4706.8 | 4492.5 | 3601.2 | 2443.0 | 1345.1 | 685.2 |
| 75° | 1669.1 | 1732.1 | 2050.6 | 2644.7 | 3374.8 | 3454.3 | 3346.9 | 2511.5 | 1342.9 | 554.7 | 311.3 |
| 77.5° | 1018.4 | 1063.9 | 1311.7 | 1791.8 | 2361.3 | 2242.4 | 1900.4 | 1408.1 | 589.2 | 265.8 | 192.4 |
| 80° | 450.6 | 478.5 | 646.2 | 962.5 | 1364.3 | 1289.7 | 1016.8 | 601.3 | 322.3 | 168.8 | 134.3 |
| 82.5° | 241.7 | 259.8 | 318.5 | 380.9 | 599.1 | 626.5 | 508.1 | 346.4 | 173.2 | 96.5 | 76.7 |
| 85° | 106.3 | 116.8 | 144.7 | 138.1 | 196.8 | 193.5 | 195.1 | 237.9 | 82.8 | 44.4 | 49.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.5 | 0.5 | 6.0 | 31.8 | 8.2 | 13.2 | 11.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634463
 CATALOG NUMBER: GWS-SA3B-827-U-SL4-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 | 1247.0 |
| 2.5° | 1233.8 | 1224.0 | 1221.2 | 1217.9 | 1211.9 | 1201.5 | 1193.8 | 1185.1 | 1181.2 | 1176.8 | 1177.4 |
| 5° | 1203.1 | 1191.1 | 1179.6 | 1164.8 | 1146.1 | 1125.3 | 1111.1 | 1094.6 | 1085.8 | 1077.6 | 1079.8 |
| 7.5° | 1176.8 | 1158.2 | 1134.6 | 1103.4 | 1069.9 | 1032.7 | 1002.5 | 979.0 | 963.1 | 952.1 | 957.6 |
| 10° | 1160.4 | 1138.5 | 1097.4 | 1046.4 | 989.9 | 932.9 | 889.6 | 849.1 | 823.8 | 804.1 | 803.0 |
| 12.5° | 1157.1 | 1128.6 | 1068.9 | 994.9 | 913.2 | 837.0 | 773.4 | 718.6 | 685.2 | 660.5 | 669.8 |
| 15° | 1160.4 | 1124.2 | 1044.2 | 947.2 | 844.1 | 741.1 | 662.1 | 599.1 | 559.1 | 536.6 | 535.0 |
| 17.5° | 1164.2 | 1119.8 | 1016.2 | 895.6 | 771.8 | 653.9 | 562.4 | 495.5 | 454.4 | 431.9 | 432.5 |
| 20° | 1167.5 | 1113.3 | 983.3 | 839.2 | 698.3 | 572.8 | 478.0 | 414.4 | 377.7 | 361.2 | 364.0 |
| 22.5° | 1173.0 | 1106.7 | 948.3 | 778.9 | 623.2 | 494.4 | 411.1 | 359.6 | 337.6 | 326.7 | 327.2 |
| 25° | 1183.4 | 1102.8 | 912.1 | 713.1 | 549.2 | 431.9 | 365.1 | 330.5 | 316.8 | 310.2 | 309.7 |
| 27.5° | 1204.8 | 1106.1 | 874.3 | 649.5 | 482.4 | 384.2 | 335.5 | 313.0 | 303.7 | 299.3 | 298.7 |
| 30° | 1240.4 | 1119.3 | 841.4 | 584.9 | 424.8 | 347.0 | 315.2 | 301.5 | 296.0 | 292.2 | 291.6 |
| 32.5° | 1294.7 | 1143.9 | 805.7 | 524.6 | 378.2 | 319.6 | 299.3 | 292.2 | 288.3 | 286.1 | 286.1 |
| 35° | 1376.9 | 1188.9 | 770.7 | 471.9 | 342.0 | 298.2 | 286.7 | 283.9 | 280.6 | 279.5 | 280.6 |
| 37.5° | 1495.3 | 1260.7 | 738.9 | 425.9 | 316.3 | 281.7 | 273.0 | 274.1 | 271.3 | 273.0 | 274.6 |
| 40° | 1645.5 | 1356.6 | 712.0 | 388.1 | 297.1 | 269.7 | 260.9 | 264.7 | 263.1 | 264.7 | 267.5 |
| 42.5° | 1835.7 | 1475.6 | 691.7 | 358.5 | 283.4 | 259.8 | 251.6 | 255.4 | 254.3 | 256.5 | 259.3 |
| 45° | 2047.8 | 1632.3 | 682.4 | 337.6 | 273.5 | 252.7 | 243.9 | 246.7 | 245.6 | 247.2 | 249.9 |
| 47.5° | 2251.2 | 1774.8 | 690.6 | 325.6 | 265.3 | 246.7 | 237.3 | 238.4 | 237.9 | 237.3 | 239.0 |
| 50° | 2426.6 | 1888.3 | 714.2 | 321.8 | 259.8 | 240.6 | 231.9 | 232.4 | 230.8 | 227.5 | 228.6 |
| 52.5° | 2569.6 | 1979.3 | 728.5 | 321.8 | 257.1 | 234.1 | 225.8 | 226.4 | 223.1 | 218.7 | 219.3 |
| 55° | 2663.9 | 2016.0 | 717.0 | 321.2 | 256.0 | 228.6 | 219.8 | 220.3 | 217.1 | 211.6 | 212.1 |
| 57.5° | 2690.8 | 1980.4 | 668.7 | 315.2 | 254.9 | 224.2 | 213.8 | 214.9 | 212.7 | 206.6 | 206.6 |
| 60° | 2615.7 | 1849.9 | 580.5 | 301.5 | 252.1 | 221.4 | 209.4 | 211.0 | 209.9 | 203.9 | 203.9 |
| 62.5° | 2418.9 | 1618.1 | 475.2 | 280.6 | 244.5 | 218.2 | 205.5 | 208.8 | 211.6 | 208.3 | 207.7 |
| 65° | 2050.6 | 1296.3 | 386.4 | 257.6 | 234.6 | 212.7 | 200.1 | 208.3 | 214.3 | 218.7 | 218.7 |
| 67.5° | 1538.6 | 928.0 | 315.2 | 233.5 | 219.8 | 201.7 | 192.9 | 200.6 | 205.0 | 207.7 | 209.4 |
| 70° | 937.8 | 545.9 | 248.3 | 205.5 | 198.4 | 185.3 | 178.7 | 171.0 | 165.0 | 163.9 | 164.4 |
| 72.5° | 458.8 | 312.4 | 201.7 | 174.9 | 169.4 | 157.3 | 142.5 | 139.2 | 136.5 | 134.8 | 134.3 |
| 75° | 252.7 | 217.6 | 166.6 | 145.3 | 135.4 | 120.6 | 117.3 | 111.8 | 110.7 | 108.5 | 109.1 |
| 77.5° | 178.7 | 171.6 | 137.6 | 117.8 | 103.0 | 95.4 | 97.0 | 93.2 | 93.2 | 91.5 | 91.0 |
| 80° | 134.3 | 134.8 | 105.8 | 86.1 | 76.2 | 73.4 | 75.1 | 75.1 | 74.0 | 73.4 | 72.9 |
| 82.5° | 85.0 | 95.9 | 71.3 | 55.4 | 54.3 | 54.8 | 54.3 | 53.7 | 54.8 | 53.2 | 52.6 |
| 85° | 58.6 | 69.1 | 43.3 | 32.9 | 32.9 | 32.3 | 33.4 | 32.9 | 34.0 | 32.3 | 32.3 |
| 87.5° | 13.2 | 30.7 | 15.9 | 9.9 | 10.4 | 9.9 | 10.4 | 11.0 | 12.1 | 12.6 | 12.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength




Melanopic Lumens: 9797 M/P: 2.26


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)