

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636938

Luminaire Tested: GWS-SA4B-827-U-SL4-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-827-U-SL4-W
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS
Light Source: (64) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10218.9 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636938
 CATALOG NUMBER: GWS-SA4B-827-U-SL4-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 4.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P636938
CATALOG NUMBER: GWS-SA4B-827-U-SL4-W

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P636938

CATALOG NUMBER: GWS-SA4B-827-U-SL4-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1574.0 | 0.0 | 1574.0 |
| | % Fixture | 15.4 | 0.0 | 15.4 |
| Street Side | Lumens | 8644.9 | 0.0 | 8644.9 |
| | % Fixture | 84.6 | 0.0 | 84.6 |
| Total | Lumens | 10218.9 | 0.0 | 10218.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 153.3 | 1.5 |
| 10°-20° | 399.6 | 3.9 |
| 20°-30° | 627.4 | 6.1 |
| 30°-40° | 943.3 | 9.2 |
| 40°-50° | 1456.1 | 14.2 |
| 50°-60° | 2162.4 | 21.2 |
| 60°-70° | 2725.7 | 26.7 |
| 70°-80° | 1576.2 | 15.4 |
| 80°-90° | 174.9 | 1.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10218.9 | 100.0 |
| 0°-180° | 10218.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636938


CATALOG NUMBER: GWS-SA4B-827-U-SL4-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 774.7 | 7.6 | | | |
| FM (30°-60°) | 3786.0 | 37.0 | | | |
| FH (60°-80°) | 3938.6 | 38.5 | | | G2/5000 |
| FVH (80°-90°) | 145.7 | 1.4 | | | G2/225 |
| BL (0°-30°) | 405.6 | 4.0 | B1/500 | | |
| BM (30°-60°) | 775.8 | 7.6 | B1/1000 | | |
| BH (60°-80°) | 363.3 | 3.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 29.2 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P636938

CATALOG NUMBER: GWS-SA4B-827-U-SL4-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 40° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 |
| 2.5° | 1746.0 | 1749.0 | 1751.3 | 1754.4 | 1752.8 | 1748.3 | 1752.1 | 1752.1 | 1743.7 | 1734.5 | 1726.1 |
| 5° | 1748.3 | 1752.1 | 1751.3 | 1750.5 | 1744.4 | 1736.8 | 1736.8 | 1732.2 | 1717.7 | 1703.3 | 1689.5 |
| 7.5° | 1743.7 | 1742.9 | 1742.2 | 1739.9 | 1733.0 | 1724.6 | 1723.1 | 1713.9 | 1694.9 | 1675.0 | 1655.2 |
| 10° | 1723.1 | 1722.3 | 1724.6 | 1729.9 | 1728.4 | 1720.8 | 1720.8 | 1712.4 | 1690.3 | 1665.9 | 1639.9 |
| 12.5° | 1706.3 | 1706.3 | 1715.5 | 1729.9 | 1735.3 | 1732.2 | 1733.0 | 1726.9 | 1701.7 | 1672.7 | 1642.2 |
| 15° | 1708.6 | 1709.4 | 1729.2 | 1752.8 | 1762.7 | 1760.5 | 1761.2 | 1754.4 | 1726.1 | 1697.1 | 1656.0 |
| 17.5° | 1723.8 | 1727.7 | 1762.0 | 1794.8 | 1807.7 | 1804.7 | 1799.4 | 1787.9 | 1755.9 | 1723.1 | 1672.7 |
| 20° | 1755.9 | 1762.0 | 1806.2 | 1847.4 | 1862.7 | 1855.8 | 1846.6 | 1823.8 | 1788.7 | 1752.8 | 1691.0 |
| 22.5° | 1819.2 | 1823.0 | 1871.8 | 1912.2 | 1924.5 | 1916.1 | 1897.8 | 1865.0 | 1824.5 | 1787.2 | 1713.2 |
| 25° | 1908.4 | 1913.0 | 1959.5 | 1996.9 | 1993.9 | 1983.9 | 1958.8 | 1918.3 | 1870.3 | 1830.6 | 1745.2 |
| 27.5° | 2014.5 | 2022.1 | 2067.9 | 2097.6 | 2077.8 | 2063.3 | 2035.1 | 1986.2 | 1932.1 | 1896.2 | 1794.0 |
| 30° | 2130.4 | 2133.4 | 2172.3 | 2202.1 | 2171.6 | 2151.8 | 2117.4 | 2064.8 | 2016.0 | 1989.3 | 1867.2 |
| 32.5° | 2242.5 | 2245.6 | 2279.1 | 2295.9 | 2263.9 | 2249.4 | 2219.6 | 2164.0 | 2129.6 | 2115.1 | 1976.3 |
| 35° | 2360.8 | 2360.0 | 2387.4 | 2401.9 | 2369.1 | 2363.0 | 2332.5 | 2289.8 | 2283.7 | 2302.8 | 2135.7 |
| 37.5° | 2479.0 | 2472.1 | 2486.6 | 2505.7 | 2487.4 | 2493.5 | 2473.6 | 2459.1 | 2482.8 | 2532.4 | 2347.8 |
| 40° | 2573.6 | 2573.6 | 2588.8 | 2612.5 | 2618.6 | 2645.3 | 2633.8 | 2652.9 | 2729.2 | 2847.4 | 2610.2 |
| 42.5° | 2657.5 | 2658.2 | 2690.3 | 2726.9 | 2771.1 | 2812.3 | 2821.5 | 2871.0 | 3028.9 | 3214.3 | 2939.7 |
| 45° | 2745.2 | 2745.9 | 2789.4 | 2842.8 | 2936.6 | 3015.2 | 3033.5 | 3144.9 | 3370.7 | 3596.4 | 3297.4 |
| 47.5° | 2846.6 | 2838.2 | 2898.5 | 2987.7 | 3121.2 | 3234.1 | 3281.4 | 3439.3 | 3724.6 | 4002.2 | 3634.6 |
| 50° | 2961.0 | 2943.5 | 3010.6 | 3164.7 | 3329.5 | 3484.3 | 3563.6 | 3744.4 | 4104.4 | 4376.7 | 3951.9 |
| 52.5° | 3090.0 | 3080.0 | 3150.2 | 3337.9 | 3589.6 | 3768.1 | 3875.6 | 4112.8 | 4473.6 | 4749.7 | 4203.6 |
| 55° | 3250.1 | 3226.5 | 3327.9 | 3566.7 | 3894.7 | 4122.0 | 4249.4 | 4477.4 | 4877.1 | 5088.4 | 4395.8 |
| 57.5° | 3425.6 | 3399.6 | 3535.4 | 3852.7 | 4291.3 | 4540.7 | 4700.1 | 4887.8 | 5257.0 | 5347.7 | 4508.7 |
| 60° | 3614.7 | 3606.3 | 3767.3 | 4188.3 | 4764.2 | 5054.1 | 5169.2 | 5339.3 | 5587.2 | 5498.0 | 4480.5 |
| 62.5° | 3787.9 | 3784.8 | 4019.0 | 4552.2 | 5265.4 | 5584.2 | 5675.7 | 5720.7 | 5825.2 | 5488.1 | 4256.2 |
| 65° | 3970.2 | 3996.1 | 4312.7 | 4974.0 | 5839.7 | 6152.4 | 6190.6 | 6076.2 | 5905.3 | 5228.0 | 3797.0 |
| 67.5° | 3993.1 | 4043.4 | 4497.3 | 5369.1 | 6384.3 | 6679.5 | 6649.0 | 6211.2 | 5668.9 | 4504.1 | 2976.3 |
| 70° | 3571.3 | 3659.0 | 4202.8 | 5429.3 | 6768.0 | 6985.4 | 6764.9 | 5920.6 | 4810.7 | 3263.1 | 1871.8 |
| 72.5° | 2983.9 | 3059.4 | 3540.0 | 4630.0 | 6273.0 | 6549.8 | 6251.6 | 5011.4 | 3399.6 | 1871.8 | 953.5 |
| 75° | 2322.6 | 2410.3 | 2853.5 | 3680.3 | 4696.3 | 4806.9 | 4657.4 | 3495.0 | 1868.8 | 771.9 | 433.2 |
| 77.5° | 1417.2 | 1480.5 | 1825.3 | 2493.5 | 3286.0 | 3120.5 | 2644.5 | 1959.5 | 820.0 | 369.9 | 267.7 |
| 80° | 627.0 | 665.9 | 899.3 | 1339.4 | 1898.5 | 1794.8 | 1414.9 | 836.8 | 448.5 | 234.9 | 186.9 |
| 82.5° | 336.4 | 361.5 | 443.2 | 530.1 | 833.7 | 871.8 | 707.1 | 482.1 | 241.0 | 134.2 | 106.8 |
| 85° | 148.0 | 162.5 | 201.4 | 192.2 | 273.8 | 269.3 | 271.5 | 331.0 | 115.2 | 61.8 | 69.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.8 | 0.8 | 8.4 | 44.2 | 11.4 | 18.3 | 16.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636938
 CATALOG NUMBER: GWS-SA4B-827-U-SL4-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 | 1735.3 |
| 2.5° | 1717.0 | 1703.3 | 1699.4 | 1694.9 | 1686.5 | 1672.0 | 1661.3 | 1649.1 | 1643.8 | 1637.7 | 1638.4 |
| 5° | 1674.3 | 1657.5 | 1641.5 | 1620.9 | 1594.9 | 1566.0 | 1546.1 | 1523.2 | 1511.0 | 1499.6 | 1502.6 |
| 7.5° | 1637.7 | 1611.7 | 1578.9 | 1535.4 | 1488.9 | 1437.0 | 1395.1 | 1362.3 | 1340.2 | 1324.9 | 1332.5 |
| 10° | 1614.8 | 1584.3 | 1527.1 | 1456.1 | 1377.6 | 1298.2 | 1238.0 | 1181.5 | 1146.4 | 1119.0 | 1117.4 |
| 12.5° | 1610.2 | 1570.5 | 1487.4 | 1384.4 | 1270.8 | 1164.7 | 1076.3 | 1000.0 | 953.5 | 919.1 | 932.1 |
| 15° | 1614.8 | 1564.4 | 1453.1 | 1318.1 | 1174.7 | 1031.3 | 921.4 | 833.7 | 778.0 | 746.7 | 744.5 |
| 17.5° | 1620.1 | 1558.3 | 1414.2 | 1246.4 | 1074.0 | 910.0 | 782.6 | 689.5 | 632.3 | 601.1 | 601.8 |
| 20° | 1624.7 | 1549.2 | 1368.4 | 1167.8 | 971.8 | 797.1 | 665.1 | 576.6 | 525.5 | 502.7 | 506.5 |
| 22.5° | 1632.3 | 1540.0 | 1319.6 | 1083.9 | 867.3 | 688.0 | 572.1 | 500.4 | 469.9 | 454.6 | 455.4 |
| 25° | 1646.8 | 1534.7 | 1269.2 | 992.4 | 764.3 | 601.1 | 508.0 | 459.9 | 440.9 | 431.7 | 431.0 |
| 27.5° | 1676.6 | 1539.3 | 1216.6 | 903.9 | 671.2 | 534.7 | 466.8 | 435.5 | 422.6 | 416.5 | 415.7 |
| 30° | 1726.1 | 1557.6 | 1170.8 | 813.9 | 591.1 | 482.8 | 438.6 | 419.5 | 411.9 | 406.6 | 405.8 |
| 32.5° | 1801.6 | 1591.9 | 1121.3 | 730.0 | 526.3 | 444.7 | 416.5 | 406.6 | 401.2 | 398.2 | 398.2 |
| 35° | 1916.1 | 1654.4 | 1072.4 | 656.7 | 476.0 | 414.9 | 398.9 | 395.1 | 390.5 | 389.0 | 390.5 |
| 37.5° | 2080.8 | 1754.4 | 1028.2 | 592.7 | 440.1 | 392.1 | 379.9 | 381.4 | 377.6 | 379.9 | 382.1 |
| 40° | 2289.8 | 1887.8 | 990.8 | 540.0 | 413.4 | 375.3 | 363.1 | 368.4 | 366.1 | 368.4 | 372.2 |
| 42.5° | 2554.5 | 2053.4 | 962.6 | 498.8 | 394.3 | 361.5 | 350.1 | 355.4 | 353.9 | 357.0 | 360.8 |
| 45° | 2849.7 | 2271.5 | 949.6 | 469.9 | 380.6 | 351.6 | 339.4 | 343.2 | 341.7 | 344.0 | 347.8 |
| 47.5° | 3132.7 | 2469.8 | 961.1 | 453.1 | 369.2 | 343.2 | 330.3 | 331.8 | 331.0 | 330.3 | 332.6 |
| 50° | 3376.8 | 2627.7 | 993.9 | 447.7 | 361.5 | 334.9 | 322.6 | 323.4 | 321.1 | 316.5 | 318.1 |
| 52.5° | 3575.8 | 2754.3 | 1013.7 | 447.7 | 357.7 | 325.7 | 314.3 | 315.0 | 310.4 | 304.3 | 305.1 |
| 55° | 3707.0 | 2805.4 | 997.7 | 447.0 | 356.2 | 318.1 | 305.9 | 306.6 | 302.1 | 294.4 | 295.2 |
| 57.5° | 3744.4 | 2755.9 | 930.6 | 438.6 | 354.7 | 312.0 | 297.5 | 299.0 | 296.0 | 287.6 | 287.6 |
| 60° | 3639.9 | 2574.3 | 807.8 | 419.5 | 350.9 | 308.2 | 291.4 | 293.7 | 292.1 | 283.7 | 283.7 |
| 62.5° | 3366.1 | 2251.7 | 661.3 | 390.5 | 340.2 | 303.6 | 286.0 | 290.6 | 294.4 | 289.9 | 289.1 |
| 65° | 2853.5 | 1803.9 | 537.7 | 358.5 | 326.5 | 296.0 | 278.4 | 289.9 | 298.2 | 304.3 | 304.3 |
| 67.5° | 2141.1 | 1291.4 | 438.6 | 324.9 | 305.9 | 280.7 | 268.5 | 279.2 | 285.3 | 289.1 | 291.4 |
| 70° | 1305.1 | 759.7 | 345.5 | 286.0 | 276.1 | 257.8 | 248.7 | 238.0 | 229.6 | 228.1 | 228.8 |
| 72.5° | 638.4 | 434.8 | 280.7 | 243.3 | 235.7 | 218.9 | 198.3 | 193.7 | 189.9 | 187.6 | 186.9 |
| 75° | 351.6 | 302.8 | 231.9 | 202.1 | 188.4 | 167.8 | 163.2 | 155.6 | 154.1 | 151.0 | 151.8 |
| 77.5° | 248.7 | 238.7 | 191.5 | 164.0 | 143.4 | 132.7 | 135.0 | 129.7 | 129.7 | 127.4 | 126.6 |
| 80° | 186.9 | 187.6 | 147.2 | 119.8 | 106.0 | 102.2 | 104.5 | 104.5 | 103.0 | 102.2 | 101.4 |
| 82.5° | 118.2 | 133.5 | 99.2 | 77.0 | 75.5 | 76.3 | 75.5 | 74.8 | 76.3 | 74.0 | 73.2 |
| 85° | 81.6 | 96.1 | 60.3 | 45.8 | 45.8 | 45.0 | 46.5 | 45.8 | 47.3 | 45.0 | 45.0 |
| 87.5° | 18.3 | 42.7 | 22.1 | 13.7 | 14.5 | 13.7 | 14.5 | 15.3 | 16.8 | 17.5 | 17.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)