

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636948

Luminaire Tested: GWS-SA4B-827-U-T2-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P636948  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4B-827-U-T2-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (64) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6320.3 lumens  
Efficiency: N/A  
Efficacy: 67.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B1 - U0 - G0  
  
Input Watts (W): 94.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P636948  
 CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 19.7 fc  
 Type II - Short - N/A

REPORT NUMBER: P636948  
CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636948

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1032.4   | 0.0    | 1032.4 |
|                    | % Fixture | 16.3     | 0.0    | 16.3   |
| <b>Street Side</b> | Lumens    | 5287.9   | 0.0    | 5287.9 |
|                    | % Fixture | 83.7     | 0.0    | 83.7   |
| <b>Total</b>       | Lumens    | 6320.3   | 0.0    | 6320.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 107.3  | 1.7       |
| 10°-20°   | 348.5  | 5.5       |
| 20°-30°   | 638.1  | 10.1      |
| 30°-40°   | 1058.7 | 16.8      |
| 40°-50°   | 1616.8 | 25.6      |
| 50°-60°   | 1816.8 | 28.7      |
| 60°-70°   | 670.1  | 10.6      |
| 70°-80°   | 64.1   | 1.0       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6320.3 | 100.0     |
| 0°-180°   | 6320.3 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P636948

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 737.6  | 11.7      |                         |      |        |
| FM (30°-60°)   | 3923.3 | 62.1      |                         |      |        |
| FH (60°-80°)   | 627.0  | 9.9       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 356.2  | 5.6       | B1/500                  |      |        |
| BM (30°-60°)   | 568.9  | 9.0       | B1/1000                 |      |        |
| BH (60°-80°)   | 107.2  | 1.7       | B0/110                  |      | G0/110 |
| BVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B1-U0-G0**  
 Type II Short





REPORT NUMBER: P636948

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 76°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 |
| 2.5°  | 1177.7 | 1189.9 | 1186.1 | 1178.5 | 1173.9 | 1157.9 | 1148.0 | 1119.0 | 1098.4 | 1096.1 | 1077.0 |
| 5°    | 1326.4 | 1324.2 | 1321.1 | 1312.0 | 1304.3 | 1279.2 | 1249.4 | 1200.6 | 1157.1 | 1151.8 | 1111.3 |
| 7.5°  | 1408.1 | 1409.6 | 1411.1 | 1409.6 | 1404.2 | 1385.2 | 1352.4 | 1295.2 | 1228.8 | 1224.2 | 1160.2 |
| 10°   | 1441.6 | 1444.7 | 1452.3 | 1466.8 | 1479.8 | 1478.2 | 1459.2 | 1400.4 | 1318.8 | 1311.2 | 1225.0 |
| 12.5° | 1457.6 | 1461.5 | 1473.7 | 1501.1 | 1536.2 | 1563.7 | 1566.7 | 1514.1 | 1424.1 | 1411.9 | 1302.0 |
| 15°   | 1479.8 | 1483.6 | 1498.8 | 1534.7 | 1585.8 | 1639.9 | 1675.0 | 1641.5 | 1540.8 | 1527.8 | 1386.7 |
| 17.5° | 1489.7 | 1495.0 | 1517.1 | 1564.4 | 1630.8 | 1713.9 | 1793.3 | 1790.2 | 1678.8 | 1668.9 | 1485.1 |
| 20°   | 1508.7 | 1512.6 | 1532.4 | 1583.5 | 1663.6 | 1783.3 | 1916.8 | 1964.9 | 1847.4 | 1832.9 | 1604.1 |
| 22.5° | 1569.0 | 1570.5 | 1579.7 | 1611.7 | 1686.5 | 1833.7 | 2042.7 | 2168.5 | 2046.5 | 2027.4 | 1737.6 |
| 25°   | 1667.4 | 1666.6 | 1670.5 | 1675.8 | 1730.7 | 1884.8 | 2164.0 | 2398.1 | 2274.6 | 2254.0 | 1888.6 |
| 27.5° | 1792.5 | 1792.5 | 1801.6 | 1786.4 | 1808.5 | 1948.1 | 2283.7 | 2662.0 | 2540.0 | 2511.0 | 2054.1 |
| 30°   | 1939.7 | 1938.9 | 1960.3 | 1935.9 | 1942.8 | 2048.0 | 2412.6 | 2949.6 | 2860.4 | 2824.5 | 2244.8 |
| 32.5° | 2139.5 | 2135.0 | 2159.4 | 2125.8 | 2102.9 | 2199.0 | 2569.7 | 3250.1 | 3244.0 | 3189.1 | 2484.3 |
| 35°   | 2392.0 | 2384.4 | 2392.0 | 2359.2 | 2318.0 | 2410.3 | 2775.7 | 3549.9 | 3669.7 | 3611.7 | 2769.6 |
| 37.5° | 2643.0 | 2667.4 | 2675.8 | 2619.3 | 2585.8 | 2678.1 | 3023.6 | 3818.4 | 4076.2 | 4015.9 | 3066.3 |
| 40°   | 2938.9 | 2931.3 | 2960.3 | 2897.0 | 2875.6 | 2977.8 | 3266.1 | 4018.2 | 4398.1 | 4340.9 | 3330.2 |
| 42.5° | 3157.1 | 3170.8 | 3206.7 | 3171.6 | 3154.8 | 3250.9 | 3469.8 | 4134.9 | 4621.6 | 4565.1 | 3518.6 |
| 45°   | 3418.7 | 3428.6 | 3442.3 | 3413.4 | 3395.8 | 3490.4 | 3617.0 | 4186.0 | 4791.7 | 4730.7 | 3645.2 |
| 47.5° | 3701.7 | 3709.3 | 3709.3 | 3649.8 | 3593.4 | 3632.3 | 3715.4 | 4215.0 | 4948.0 | 4889.3 | 3739.1 |
| 50°   | 3904.6 | 3908.4 | 3942.0 | 3900.0 | 3777.2 | 3716.9 | 3760.4 | 4243.2 | 5051.8 | 4996.9 | 3769.6 |
| 52.5° | 3724.6 | 3720.0 | 3830.6 | 3917.5 | 3950.3 | 3830.6 | 3838.2 | 4284.4 | 5102.1 | 5054.8 | 3794.0 |
| 55°   | 3136.5 | 3128.9 | 3284.5 | 3495.7 | 3784.8 | 3938.1 | 3932.0 | 4308.8 | 5157.8 | 5128.8 | 3882.5 |
| 57.5° | 2273.8 | 2260.8 | 2477.5 | 2712.4 | 3091.5 | 3507.2 | 3751.3 | 4295.1 | 5182.2 | 5179.9 | 3985.4 |
| 60°   | 1366.9 | 1356.2 | 1560.6 | 1807.7 | 2100.6 | 2518.6 | 2923.7 | 3847.4 | 4855.7 | 4860.3 | 3717.7 |
| 62.5° | 841.3  | 851.2  | 1035.8 | 1161.7 | 1270.8 | 1396.6 | 1630.8 | 2588.1 | 3597.2 | 3626.9 | 2612.5 |
| 65°   | 566.0  | 573.6  | 744.5  | 903.1  | 903.1  | 738.4  | 633.9  | 1237.2 | 1919.1 | 1868.8 | 1235.7 |
| 67.5° | 379.9  | 388.2  | 523.3  | 708.6  | 735.3  | 514.9  | 257.1  | 369.2  | 534.7  | 518.7  | 305.9  |
| 70°   | 223.5  | 232.6  | 348.6  | 485.9  | 535.5  | 358.5  | 171.6  | 156.4  | 151.8  | 147.2  | 119.0  |
| 72.5° | 99.9   | 103.7  | 177.7  | 247.1  | 225.8  | 151.0  | 121.3  | 125.1  | 118.2  | 115.9  | 96.9   |
| 75°   | 30.5   | 32.0   | 45.8   | 53.4   | 54.2   | 54.2   | 73.2   | 98.4   | 93.1   | 93.8   | 74.8   |
| 77.5° | 7.6    | 7.6    | 12.2   | 11.4   | 6.1    | 5.3    | 13.7   | 22.1   | 22.9   | 20.6   | 15.3   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P636948

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 | 1054.1 |
| 2.5°  | 1068.6 | 1048.8 | 1035.8 | 1017.5 | 1004.6 | 990.8  | 978.6  | 968.7  | 963.4  | 961.8  | 962.6  |
| 5°    | 1093.0 | 1061.8 | 1031.3 | 996.2  | 971.8  | 948.9  | 930.6  | 916.1  | 909.2  | 906.9  | 906.9  |
| 7.5°  | 1130.4 | 1086.9 | 1032.8 | 977.9  | 936.7  | 900.8  | 879.5  | 863.4  | 857.3  | 855.8  | 851.2  |
| 10°   | 1179.2 | 1119.7 | 1030.5 | 945.1  | 887.1  | 849.7  | 834.5  | 829.9  | 832.2  | 832.9  | 832.2  |
| 12.5° | 1238.0 | 1154.1 | 1016.0 | 897.0  | 834.5  | 811.6  | 813.1  | 825.3  | 839.0  | 845.9  | 847.4  |
| 15°   | 1300.5 | 1185.3 | 983.2  | 839.8  | 789.5  | 788.7  | 810.8  | 839.0  | 865.7  | 877.2  | 880.2  |
| 17.5° | 1370.7 | 1210.5 | 932.9  | 778.8  | 750.6  | 772.7  | 812.3  | 855.8  | 891.7  | 910.7  | 914.6  |
| 20°   | 1447.7 | 1231.1 | 868.8  | 721.6  | 716.2  | 755.9  | 810.8  | 864.2  | 908.5  | 929.8  | 933.6  |
| 22.5° | 1527.8 | 1245.6 | 794.8  | 668.9  | 685.0  | 736.8  | 796.3  | 848.2  | 890.1  | 914.6  | 917.6  |
| 25°   | 1619.3 | 1247.1 | 719.3  | 624.7  | 656.0  | 710.9  | 761.2  | 804.0  | 839.0  | 860.4  | 862.7  |
| 27.5° | 1699.4 | 1228.8 | 652.2  | 588.9  | 629.3  | 678.9  | 712.4  | 736.1  | 760.5  | 772.7  | 773.4  |
| 30°   | 1791.7 | 1196.8 | 588.9  | 559.9  | 601.8  | 639.2  | 656.0  | 661.3  | 663.6  | 665.9  | 662.8  |
| 32.5° | 1901.6 | 1157.9 | 541.6  | 531.6  | 570.5  | 595.7  | 600.3  | 589.6  | 576.6  | 558.3  | 553.8  |
| 35°   | 2036.6 | 1122.8 | 502.7  | 504.2  | 536.2  | 551.5  | 547.7  | 524.8  | 499.6  | 477.5  | 473.7  |
| 37.5° | 2183.0 | 1093.0 | 472.9  | 477.5  | 498.8  | 509.5  | 498.1  | 472.9  | 461.5  | 442.4  | 443.2  |
| 40°   | 2312.7 | 1068.6 | 446.2  | 450.8  | 460.7  | 470.6  | 452.3  | 435.5  | 456.9  | 455.4  | 456.9  |
| 42.5° | 2405.0 | 1048.0 | 423.3  | 421.0  | 427.9  | 434.8  | 421.0  | 412.7  | 448.5  | 438.6  | 443.9  |
| 45°   | 2459.1 | 1029.0 | 404.3  | 390.5  | 401.2  | 413.4  | 404.3  | 393.6  | 405.8  | 360.0  | 356.2  |
| 47.5° | 2495.8 | 1018.3 | 387.5  | 360.8  | 379.9  | 401.2  | 382.1  | 356.2  | 338.7  | 299.0  | 296.0  |
| 50°   | 2499.6 | 1012.9 | 367.7  | 330.3  | 354.7  | 377.6  | 355.4  | 319.6  | 294.4  | 276.9  | 274.6  |
| 52.5° | 2519.4 | 1023.6 | 340.2  | 291.4  | 318.1  | 354.7  | 339.4  | 303.6  | 269.3  | 254.0  | 250.9  |
| 55°   | 2607.9 | 1068.6 | 294.4  | 238.0  | 276.9  | 337.1  | 326.5  | 270.8  | 238.0  | 228.8  | 226.5  |
| 57.5° | 2699.4 | 1077.8 | 231.9  | 188.4  | 241.0  | 312.0  | 298.2  | 249.4  | 217.4  | 206.7  | 204.4  |
| 60°   | 2468.3 | 887.9  | 173.9  | 155.6  | 212.8  | 288.3  | 276.1  | 236.5  | 199.1  | 186.1  | 183.8  |
| 62.5° | 1621.6 | 479.8  | 138.1  | 132.0  | 179.2  | 244.1  | 251.7  | 213.6  | 177.7  | 164.0  | 163.2  |
| 65°   | 747.5  | 222.7  | 106.0  | 104.5  | 140.3  | 194.5  | 216.6  | 186.9  | 150.3  | 138.1  | 138.1  |
| 67.5° | 203.7  | 110.6  | 83.1   | 77.0   | 95.3   | 130.4  | 157.9  | 139.6  | 106.8  | 92.3   | 91.5   |
| 70°   | 101.4  | 89.2   | 74.8   | 66.4   | 68.6   | 80.9   | 93.1   | 77.8   | 54.2   | 44.2   | 43.5   |
| 72.5° | 83.1   | 73.2   | 63.3   | 56.4   | 51.9   | 49.6   | 48.1   | 38.9   | 25.2   | 19.1   | 18.3   |
| 75°   | 61.8   | 52.6   | 45.0   | 36.6   | 31.3   | 29.0   | 25.9   | 19.1   | 10.7   | 6.1    | 5.3    |
| 77.5° | 13.7   | 13.0   | 12.2   | 9.2    | 8.4    | 6.9    | 5.3    | 3.8    | 1.5    | 0.0    | 0.0    |
| 80°   | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 2.6           | 620    | 87426         | 22.8          | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 3.9           | 625    | 83013         | 18.2          | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 5.8           | 630    | 78077         | 14.1          | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 8.5           | 635    | 72080         | 10.7          | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 11.5          | 640    | 66249         | 7.9           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 15.2          | 645    | 59973         | 5.7           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 18.7          | 650    | 53972         | 3.9           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 21.9          | 655    | 48369         | 2.7           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 24.9          | 660    | 42641         | 1.8           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 27.6          | 665    | 37602         | 1.1           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 30.0          | 670    | 32798         | 0.7           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.0           | 545    | 48553         | 32.5          | 675    | 28558         | 0.5           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.0           | 550    | 51408         | 34.9          | 680    | 24782         | 0.3           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.0           | 555    | 54711         | 37.4          | 685    | 21386         | 0.2           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 0.0           | 560    | 58847         | 40.0          | 690    | 18413         | 0.1           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 0.1           | 565    | 63386         | 42.4          | 695    | 15721         | 0.1           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 0.2           | 570    | 68196         | 44.3          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 0.6           | 575    | 73613         | 46.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 0.9           | 580    | 79207         | 47.1          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 0.9           | 585    | 84248         | 47.0          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 0.9           | 590    | 88397         | 45.7          | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 1.0           | 595    | 91428         | 43.4          | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 0.9           | 600    | 93452         | 40.3          | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 1.0           | 605    | 93959         | 36.4          | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 1.3           | 610    | 93079         | 32.0          | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 1.8           | 615    | 90707         | 27.3          | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 0                                 | 0.0                         | 490            | 18018                             | 75.9                        | 620            | 87426                             | 0.4                         | 750            | 2680                              | 0.0                         | 880            | 58                                | 0.0                         |
| 365            | 0                                 | 0.0                         | 495            | 22295                             | 93.2                        | 625            | 83013                             | 0.2                         | 755            | 2287                              | 0.0                         | 885            | 46                                | 0.0                         |
| 370            | 0                                 | 0.0                         | 500            | 26478                             | 107.8                       | 630            | 78077                             | 0.1                         | 760            | 1944                              | 0.0                         | 890            | 45                                | 0.0                         |
| 375            | 0                                 | 0.0                         | 505            | 30524                             | 118.7                       | 635            | 72080                             | 0.1                         | 765            | 1653                              | 0.0                         | 895            | 41                                | 0.0                         |
| 380            | 0                                 | 0.0                         | 510            | 33611                             | 122.2                       | 640            | 66249                             | 0.1                         | 770            | 1413                              | 0.0                         | 900            | 38                                | 0.0                         |
| 385            | 0                                 | 0.0                         | 515            | 36490                             | 120.8                       | 645            | 59973                             | 0.0                         | 775            | 1198                              | 0.0                         | 905            | 33                                | 0.0                         |
| 390            | 0                                 | 0.0                         | 520            | 38610                             | 113.9                       | 650            | 53972                             | 0.0                         | 780            | 1025                              | 0.0                         | 910            | 30                                | 0.0                         |
| 395            | 0                                 | 0.0                         | 525            | 40511                             | 104.1                       | 655            | 48369                             | 0.0                         | 785            | 874                               | 0.0                         | 915            | 23                                | 0.0                         |
| 400            | 48                                | 0.0                         | 530            | 42223                             | 92.4                        | 660            | 42641                             | 0.0                         | 790            | 747                               | 0.0                         | 920            | 24                                | 0.0                         |
| 405            | 201                               | 0.0                         | 535            | 44137                             | 80.5                        | 665            | 37602                             | 0.0                         | 795            | 639                               | 0.0                         | 925            | 22                                | 0.0                         |
| 410            | 457                               | 0.1                         | 540            | 46032                             | 68.2                        | 670            | 32798                             | 0.0                         | 800            | 547                               | 0.0                         | 930            | 22                                | 0.0                         |
| 415            | 925                               | 0.3                         | 545            | 48553                             | 57.1                        | 675            | 28558                             | 0.0                         | 805            | 473                               | 0.0                         | 935            | 17                                | 0.0                         |
| 420            | 1816                              | 1.1                         | 550            | 51408                             | 46.7                        | 680            | 24782                             | 0.0                         | 810            | 401                               | 0.0                         | 940            | 13                                | 0.0                         |
| 425            | 3217                              | 2.5                         | 555            | 54711                             | 37.4                        | 685            | 21386                             | 0.0                         | 815            | 351                               | 0.0                         | 945            | 6                                 | 0.0                         |
| 430            | 5520                              | 5.9                         | 560            | 58847                             | 29.4                        | 690            | 18413                             | 0.0                         | 820            | 307                               | 0.0                         | 950            | 10                                | 0.0                         |
| 435            | 9225                              | 12.5                        | 565            | 63386                             | 22.5                        | 695            | 15721                             | 0.0                         | 825            | 261                               | 0.0                         | 955            | 11                                | 0.0                         |
| 440            | 15522                             | 26.3                        | 570            | 68196                             | 16.9                        | 700            | 13432                             | 0.0                         | 830            | 228                               | 0.0                         | 960            | 8                                 | 0.0                         |
| 445            | 27642                             | 55.2                        | 575            | 73613                             | 12.4                        | 705            | 11513                             | 0.0                         | 835            | 193                               | 0.0                         | 965            | 12                                | 0.0                         |
| 450            | 36602                             | 85.4                        | 580            | 79207                             | 9.0                         | 710            | 9780                              | 0.0                         | 840            | 174                               | 0.0                         | 970            | 3                                 | 0.0                         |
| 455            | 28292                             | 75.1                        | 585            | 84248                             | 6.3                         | 715            | 8356                              | 0.0                         | 845            | 151                               | 0.0                         | 975            | 8                                 | 0.0                         |
| 460            | 21166                             | 63.2                        | 590            | 88397                             | 4.4                         | 720            | 7161                              | 0.0                         | 850            | 123                               | 0.0                         | 980            | 2                                 | 0.0                         |
| 465            | 19092                             | 63.2                        | 595            | 91428                             | 3.0                         | 725            | 6067                              | 0.0                         | 855            | 106                               | 0.0                         | 985            | 13                                | 0.0                         |
| 470            | 14951                             | 54.2                        | 600            | 93452                             | 2.0                         | 730            | 5164                              | 0.0                         | 860            | 95                                | 0.0                         | 990            | 16                                | 0.0                         |
| 475            | 12606                             | 48.8                        | 605            | 93959                             | 1.3                         | 735            | 4393                              | 0.0                         | 865            | 82                                | 0.0                         | 995            | 20                                | 0.0                         |
| 480            | 13323                             | 54.2                        | 610            | 93079                             | 0.9                         | 740            | 3694                              | 0.0                         | 870            | 77                                | 0.0                         | 1000           | 0                                 | 0.0                         |
| 485            | 15164                             | 63.3                        | 615            | 90707                             | 0.5                         | 745            | 3157                              | 0.0                         | 875            | 65                                | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360               | 0                      | 0.0                     | 490               | 18018                  | 27.7                    | 620               | 87426                  | 1.1                     | 750               | 2680                   | 0.0                     | 880               | 58                     | 0.0                     |
| 365               | 0                      | 0.0                     | 495               | 22295                  | 36.0                    | 625               | 83013                  | 0.7                     | 755               | 2287                   | 0.0                     | 885               | 46                     | 0.0                     |
| 370               | 0                      | 0.0                     | 500               | 26478                  | 44.2                    | 630               | 78077                  | 0.4                     | 760               | 1944                   | 0.0                     | 890               | 45                     | 0.0                     |
| 375               | 0                      | 0.0                     | 505               | 30524                  | 51.8                    | 635               | 72080                  | 0.3                     | 765               | 1653                   | 0.0                     | 895               | 41                     | 0.0                     |
| 380               | 0                      | 0.0                     | 510               | 33611                  | 57.0                    | 640               | 66249                  | 0.2                     | 770               | 1413                   | 0.0                     | 900               | 38                     | 0.0                     |
| 385               | 0                      | 0.0                     | 515               | 36490                  | 60.5                    | 645               | 59973                  | 0.1                     | 775               | 1198                   | 0.0                     | 905               | 33                     | 0.0                     |
| 390               | 0                      | 0.0                     | 520               | 38610                  | 61.4                    | 650               | 53972                  | 0.1                     | 780               | 1025                   | 0.0                     | 910               | 30                     | 0.0                     |
| 395               | 0                      | 0.0                     | 525               | 40511                  | 60.6                    | 655               | 48369                  | 0.0                     | 785               | 874                    | 0.0                     | 915               | 23                     | 0.0                     |
| 400               | 48                     | 0.0                     | 530               | 42223                  | 58.2                    | 660               | 42641                  | 0.0                     | 790               | 747                    | 0.0                     | 920               | 24                     | 0.0                     |
| 405               | 201                    | 0.0                     | 535               | 44137                  | 55.0                    | 665               | 37602                  | 0.0                     | 795               | 639                    | 0.0                     | 925               | 22                     | 0.0                     |
| 410               | 457                    | 0.0                     | 540               | 46032                  | 50.9                    | 670               | 32798                  | 0.0                     | 800               | 547                    | 0.0                     | 930               | 22                     | 0.0                     |
| 415               | 925                    | 0.1                     | 545               | 48553                  | 46.6                    | 675               | 28558                  | 0.0                     | 805               | 473                    | 0.0                     | 935               | 17                     | 0.0                     |
| 420               | 1816                   | 0.3                     | 550               | 51408                  | 42.0                    | 680               | 24782                  | 0.0                     | 810               | 401                    | 0.0                     | 940               | 13                     | 0.0                     |
| 425               | 3217                   | 0.8                     | 555               | 54711                  | 37.4                    | 685               | 21386                  | 0.0                     | 815               | 351                    | 0.0                     | 945               | 6                      | 0.0                     |
| 430               | 5520                   | 1.9                     | 560               | 58847                  | 32.9                    | 690               | 18413                  | 0.0                     | 820               | 307                    | 0.0                     | 950               | 10                     | 0.0                     |
| 435               | 9225                   | 4.1                     | 565               | 63386                  | 28.4                    | 695               | 15721                  | 0.0                     | 825               | 261                    | 0.0                     | 955               | 11                     | 0.0                     |
| 440               | 15522                  | 8.7                     | 570               | 68196                  | 24.1                    | 700               | 13432                  | 0.0                     | 830               | 228                    | 0.0                     | 960               | 8                      | 0.0                     |
| 445               | 27642                  | 18.5                    | 575               | 73613                  | 20.0                    | 705               | 11513                  | 0.0                     | 835               | 193                    | 0.0                     | 965               | 12                     | 0.0                     |
| 450               | 36602                  | 28.3                    | 580               | 79207                  | 16.3                    | 710               | 9780                   | 0.0                     | 840               | 174                    | 0.0                     | 970               | 3                      | 0.0                     |
| 455               | 28292                  | 24.7                    | 585               | 84248                  | 12.9                    | 715               | 8356                   | 0.0                     | 845               | 151                    | 0.0                     | 975               | 8                      | 0.0                     |
| 460               | 21166                  | 20.4                    | 590               | 88397                  | 9.8                     | 720               | 7161                   | 0.0                     | 850               | 123                    | 0.0                     | 980               | 2                      | 0.0                     |
| 465               | 19092                  | 20.1                    | 595               | 91428                  | 7.3                     | 725               | 6067                   | 0.0                     | 855               | 106                    | 0.0                     | 985               | 13                     | 0.0                     |
| 470               | 14951                  | 17.2                    | 600               | 93452                  | 5.3                     | 730               | 5164                   | 0.0                     | 860               | 95                     | 0.0                     | 990               | 16                     | 0.0                     |
| 475               | 12606                  | 15.7                    | 605               | 93959                  | 3.7                     | 735               | 4393                   | 0.0                     | 865               | 82                     | 0.0                     | 995               | 20                     | 0.0                     |
| 480               | 13323                  | 18.0                    | 610               | 93079                  | 2.5                     | 740               | 3694                   | 0.0                     | 870               | 77                     | 0.0                     | 1000              | 0                      | 0.0                     |
| 485               | 15164                  | 21.9                    | 615               | 90707                  | 1.7                     | 745               | 3157                   | 0.0                     | 875               | 65                     | 0.0                     |                   |                        |                         |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_g = -1.5$



**Color Vector Graphics**





Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)