

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637450

Luminaire Tested: GWS-SA4C-827-U-T2R-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P637450  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4C-827-U-T2R-W  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS  
Light Source: (64) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14550.6 lumens  
Efficiency: N/A  
Efficacy: 113.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B2 - U0 - G2  
  
Input Watts (W): 128.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P637450

CATALOG NUMBER: GWS-SA4C-827-U-T2R-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.9 fc  
 Type II - Short - N/A

REPORT NUMBER: P637450  
CATALOG NUMBER: GWS-SA4C-827-U-T2R-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral    - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P637450

CATALOG NUMBER: GWS-SA4C-827-U-T2R-W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2432.1   | 0.0    | 2432.1  |
|                    | % Fixture | 16.7     | 0.0    | 16.7    |
| <b>Street Side</b> | Lumens    | 12118.5  | 0.0    | 12118.5 |
|                    | % Fixture | 83.3     | 0.0    | 83.3    |
| <b>Total</b>       | Lumens    | 14550.6  | 0.0    | 14550.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 163.7   | 1.1       |
| 10°-20°   | 623.5   | 4.3       |
| 20°-30°   | 1215.1  | 8.4       |
| 30°-40°   | 2032.3  | 14.0      |
| 40°-50°   | 2909.8  | 20.0      |
| 50°-60°   | 3444.8  | 23.7      |
| 60°-70°   | 2864.4  | 19.7      |
| 70°-80°   | 1172.2  | 8.1       |
| 80°-90°   | 124.8   | 0.9       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 14550.6 | 100.0     |
| 0°-180°   | 14550.6 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P637450

CATALOG NUMBER: GWS-SA4C-827-U-T2R-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1493.6 | 10.3      |                         |      |         |
| FM (30°-60°)   | 7204.9 | 49.5      |                         |      |         |
| FH (60°-80°)   | 3345.5 | 23.0      |                         |      | G2/5000 |
| FVH (80°-90°)  | 74.4   | 0.5       |                         |      | G1/100  |
| BL (0°-30°)    | 508.8  | 3.5       | B2/1000                 |      |         |
| BM (30°-60°)   | 1182.0 | 8.1       | B2/2500                 |      |         |
| BH (60°-80°)   | 691.0  | 4.7       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 50.4   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**  
 Type II Short





REPORT NUMBER: P637450

CATALOG NUMBER: GWS-SA4C-827-U-T2R-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°     | 76°     | 85°     |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°    | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9  | 1377.9  | 1377.9  |
| 2.5°  | 1931.3 | 1938.5 | 1914.9 | 1906.7 | 1851.5 | 1776.8 | 1714.4 | 1620.3 | 1533.4  | 1520.1  | 1442.3  |
| 5°    | 2453.0 | 2422.3 | 2395.7 | 2378.3 | 2301.6 | 2216.7 | 2084.7 | 1907.8 | 1722.6  | 1700.1  | 1532.4  |
| 7.5°  | 2762.9 | 2757.8 | 2725.1 | 2714.9 | 2655.5 | 2570.6 | 2434.6 | 2214.6 | 1945.6  | 1908.8  | 1654.1  |
| 10°   | 3011.5 | 3008.4 | 2992.1 | 3001.3 | 2947.1 | 2864.2 | 2732.2 | 2505.2 | 2190.1  | 2153.3  | 1790.1  |
| 12.5° | 3228.4 | 3233.5 | 3230.4 | 3264.2 | 3236.6 | 3172.1 | 3035.0 | 2785.4 | 2434.6  | 2394.7  | 1955.8  |
| 15°   | 3386.9 | 3391.0 | 3406.4 | 3480.0 | 3495.4 | 3482.1 | 3342.9 | 3060.6 | 2676.0  | 2618.7  | 2126.7  |
| 17.5° | 3431.9 | 3440.1 | 3476.9 | 3595.6 | 3678.5 | 3733.7 | 3630.4 | 3340.9 | 2913.3  | 2850.9  | 2300.6  |
| 20°   | 3492.3 | 3501.5 | 3538.3 | 3662.1 | 3783.8 | 3909.6 | 3891.2 | 3625.3 | 3152.7  | 3101.5  | 2476.5  |
| 22.5° | 3771.5 | 3764.4 | 3748.0 | 3807.3 | 3894.3 | 4050.8 | 4096.8 | 3898.4 | 3400.2  | 3351.1  | 2670.9  |
| 25°   | 4309.6 | 4296.3 | 4192.0 | 4137.8 | 4109.1 | 4204.2 | 4286.1 | 4147.0 | 3641.6  | 3568.0  | 2851.9  |
| 27.5° | 4902.9 | 4895.7 | 4762.8 | 4633.9 | 4457.9 | 4417.0 | 4465.1 | 4363.8 | 3875.9  | 3801.2  | 3009.5  |
| 30°   | 5464.5 | 5443.0 | 5303.9 | 5142.3 | 4907.0 | 4731.1 | 4660.5 | 4576.6 | 4132.6  | 4054.9  | 3193.6  |
| 32.5° | 5966.8 | 5939.1 | 5775.5 | 5596.5 | 5349.9 | 5142.3 | 4931.6 | 4802.7 | 4423.2  | 4333.1  | 3381.8  |
| 35°   | 6379.0 | 6351.4 | 6183.6 | 5993.4 | 5722.3 | 5568.8 | 5280.4 | 5048.2 | 4718.8  | 4627.7  | 3603.8  |
| 37.5° | 6698.2 | 6672.6 | 6497.7 | 6310.5 | 6074.2 | 5952.4 | 5701.8 | 5324.4 | 5059.4  | 4964.3  | 3839.1  |
| 40°   | 6877.2 | 6858.8 | 6718.6 | 6570.3 | 6371.8 | 6266.5 | 6154.0 | 5673.2 | 5441.0  | 5345.8  | 4116.3  |
| 42.5° | 6931.4 | 6919.1 | 6820.9 | 6744.2 | 6610.2 | 6530.4 | 6594.8 | 6083.4 | 5848.1  | 5765.2  | 4428.3  |
| 45°   | 6795.3 | 6795.3 | 6766.7 | 6805.6 | 6811.7 | 6810.7 | 7036.7 | 6546.8 | 6348.3  | 6257.3  | 4868.1  |
| 47.5° | 6447.5 | 6470.0 | 6512.0 | 6703.3 | 6904.8 | 7073.6 | 7553.3 | 7164.6 | 6991.7  | 6917.1  | 5491.1  |
| 50°   | 5811.3 | 5872.6 | 6015.9 | 6389.2 | 6817.8 | 7247.5 | 8042.3 | 8078.1 | 8242.8  | 8110.8  | 6407.6  |
| 52.5° | 4879.4 | 4870.2 | 5235.4 | 5767.3 | 6420.9 | 7254.6 | 8311.3 | 8884.2 | 9327.1  | 9236.0  | 7088.9  |
| 55°   | 3877.9 | 3862.6 | 4203.2 | 4936.7 | 5812.3 | 6980.5 | 8472.9 | 9253.4 | 9928.6  | 9846.7  | 7701.6  |
| 57.5° | 2969.6 | 2950.1 | 3252.9 | 3914.8 | 4953.0 | 6398.4 | 8442.2 | 9693.3 | 10756.1 | 10714.2 | 8534.3  |
| 60°   | 2043.8 | 2020.3 | 2303.6 | 2882.6 | 3936.2 | 5508.5 | 8102.6 | 9919.4 | 11724.8 | 11739.2 | 9425.3  |
| 62.5° | 1227.5 | 1214.2 | 1419.8 | 1868.9 | 2831.5 | 4405.8 | 7307.8 | 9782.3 | 12496.1 | 12560.6 | 9998.1  |
| 65°   | 740.6  | 731.4  | 852.1  | 1115.0 | 1796.3 | 3215.1 | 6082.3 | 9081.6 | 12607.6 | 12755.9 | 10011.4 |
| 67.5° | 539.1  | 540.1  | 574.9  | 679.2  | 1047.5 | 2076.5 | 4564.3 | 7825.4 | 12026.6 | 12180.0 | 9380.3  |
| 70°   | 468.5  | 470.5  | 489.0  | 512.5  | 633.2  | 1188.6 | 2967.5 | 6177.5 | 10309.1 | 10427.8 | 7867.4  |
| 72.5° | 416.3  | 416.3  | 428.6  | 440.9  | 495.1  | 724.2  | 1589.6 | 4317.8 | 8136.4  | 8168.1  | 6004.6  |
| 75°   | 366.2  | 363.1  | 369.3  | 375.4  | 429.6  | 506.4  | 773.3  | 3008.4 | 6009.7  | 5936.1  | 3881.0  |
| 77.5° | 291.5  | 288.5  | 289.5  | 295.6  | 344.7  | 362.1  | 391.8  | 1879.1 | 3386.9  | 3196.7  | 1714.4  |
| 80°   | 207.7  | 205.6  | 216.9  | 232.2  | 254.7  | 222.0  | 245.5  | 909.4  | 1343.1  | 1250.0  | 664.9   |
| 82.5° | 123.8  | 127.9  | 145.3  | 157.5  | 175.9  | 139.1  | 158.6  | 303.8  | 475.7   | 463.4   | 270.1   |
| 85°   | 17.4   | 18.4   | 52.2   | 60.4   | 75.7   | 54.2   | 83.9   | 137.1  | 190.3   | 203.6   | 95.1    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 7.2    | 24.6   | 54.2    | 55.2    | 23.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P637450  
 CATALOG NUMBER: GWS-SA4C-827-U-T2R-W

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 | 1377.9 |
| 2.5°  | 1402.4 | 1354.4 | 1285.8 | 1228.5 | 1180.5 | 1141.6 | 1108.9 | 1084.3 | 1077.1 | 1066.9 | 1066.9 |
| 5°    | 1453.6 | 1366.6 | 1243.9 | 1156.9 | 1106.8 | 1077.1 | 1056.7 | 1046.5 | 1041.3 | 1035.2 | 1032.1 |
| 7.5°  | 1524.2 | 1402.4 | 1236.7 | 1148.8 | 1109.9 | 1091.5 | 1078.2 | 1072.0 | 1067.9 | 1061.8 | 1061.8 |
| 10°   | 1621.3 | 1455.6 | 1259.2 | 1177.4 | 1146.7 | 1128.3 | 1112.9 | 1102.7 | 1093.5 | 1084.3 | 1082.3 |
| 12.5° | 1726.7 | 1525.2 | 1300.1 | 1216.3 | 1183.5 | 1161.0 | 1139.5 | 1124.2 | 1112.9 | 1101.7 | 1098.6 |
| 15°   | 1843.3 | 1596.8 | 1344.1 | 1254.1 | 1213.2 | 1182.5 | 1156.9 | 1133.4 | 1118.1 | 1101.7 | 1099.7 |
| 17.5° | 1957.9 | 1669.4 | 1381.0 | 1279.7 | 1227.5 | 1189.7 | 1152.8 | 1122.2 | 1102.7 | 1084.3 | 1079.2 |
| 20°   | 2095.0 | 1742.1 | 1406.5 | 1286.8 | 1224.4 | 1174.3 | 1130.3 | 1091.5 | 1070.0 | 1048.5 | 1045.4 |
| 22.5° | 2220.8 | 1809.6 | 1418.8 | 1276.6 | 1200.9 | 1141.6 | 1090.4 | 1048.5 | 1025.0 | 1003.5 | 999.4  |
| 25°   | 2342.5 | 1868.9 | 1413.7 | 1252.1 | 1165.1 | 1096.6 | 1043.4 | 1001.4 | 978.9  | 956.4  | 950.3  |
| 27.5° | 2460.1 | 1908.8 | 1393.2 | 1214.2 | 1120.1 | 1046.5 | 995.3  | 957.5  | 938.0  | 918.6  | 910.4  |
| 30°   | 2575.7 | 1945.6 | 1361.5 | 1165.1 | 1062.8 | 994.3  | 952.3  | 925.8  | 906.3  | 885.9  | 879.7  |
| 32.5° | 2692.4 | 1972.2 | 1313.4 | 1107.8 | 1004.5 | 948.3  | 922.7  | 903.2  | 882.8  | 862.3  | 856.2  |
| 35°   | 2810.0 | 1983.5 | 1255.1 | 1042.4 | 955.4  | 918.6  | 909.4  | 886.9  | 859.3  | 834.7  | 826.5  |
| 37.5° | 2950.1 | 1993.7 | 1182.5 | 977.9  | 912.5  | 904.3  | 902.2  | 868.5  | 835.7  | 802.0  | 792.8  |
| 40°   | 3118.9 | 2007.0 | 1107.8 | 919.6  | 877.7  | 899.2  | 891.0  | 844.9  | 779.5  | 746.7  | 736.5  |
| 42.5° | 3325.5 | 2031.5 | 1030.1 | 866.4  | 852.1  | 879.7  | 870.5  | 787.7  | 743.7  | 725.3  | 720.1  |
| 45°   | 3629.4 | 2121.6 | 952.3  | 824.5  | 832.7  | 852.1  | 837.8  | 753.9  | 736.5  | 724.2  | 718.1  |
| 47.5° | 4170.5 | 2259.7 | 884.8  | 792.8  | 817.3  | 827.6  | 772.3  | 744.7  | 731.4  | 715.0  | 707.9  |
| 50°   | 4733.1 | 2320.0 | 830.6  | 773.3  | 799.9  | 805.0  | 736.5  | 732.4  | 723.2  | 705.8  | 698.7  |
| 52.5° | 5113.6 | 2311.8 | 797.9  | 766.2  | 785.6  | 766.2  | 720.1  | 719.1  | 713.0  | 692.5  | 684.3  |
| 55°   | 5543.3 | 2326.1 | 783.6  | 768.2  | 779.5  | 700.7  | 699.7  | 702.8  | 699.7  | 677.2  | 673.1  |
| 57.5° | 6123.3 | 2370.1 | 776.4  | 775.4  | 775.4  | 669.0  | 680.2  | 684.3  | 678.2  | 668.0  | 664.9  |
| 60°   | 6680.8 | 2373.2 | 763.1  | 783.6  | 772.3  | 649.6  | 657.7  | 661.8  | 654.7  | 652.6  | 651.6  |
| 62.5° | 6890.5 | 2225.9 | 733.4  | 777.4  | 760.0  | 628.1  | 634.2  | 636.3  | 629.1  | 634.2  | 633.2  |
| 65°   | 6578.5 | 1912.9 | 684.3  | 747.8  | 722.2  | 608.6  | 604.6  | 609.7  | 597.4  | 610.7  | 611.7  |
| 67.5° | 5840.9 | 1520.1 | 609.7  | 691.5  | 669.0  | 587.2  | 579.0  | 579.0  | 558.5  | 579.0  | 578.0  |
| 70°   | 4709.6 | 1074.1 | 500.2  | 601.5  | 610.7  | 561.6  | 557.5  | 534.0  | 501.2  | 531.9  | 528.9  |
| 72.5° | 3570.0 | 771.3  | 393.8  | 475.7  | 525.8  | 525.8  | 526.8  | 486.9  | 449.1  | 463.4  | 451.1  |
| 75°   | 2261.7 | 543.2  | 315.1  | 364.2  | 412.2  | 461.3  | 484.9  | 411.2  | 377.5  | 371.3  | 365.2  |
| 77.5° | 1018.8 | 357.0  | 245.5  | 279.3  | 292.6  | 364.2  | 442.9  | 353.9  | 307.9  | 294.6  | 290.5  |
| 80°   | 426.6  | 222.0  | 174.9  | 197.4  | 180.0  | 305.9  | 390.8  | 275.2  | 226.1  | 207.7  | 194.4  |
| 82.5° | 187.2  | 132.0  | 111.5  | 106.4  | 112.5  | 227.1  | 291.5  | 183.1  | 141.2  | 191.3  | 193.3  |
| 85°   | 78.8   | 69.6   | 57.3   | 52.2   | 46.0   | 86.9   | 137.1  | 71.6   | 88.0   | 50.1   | 40.9   |
| 87.5° | 18.4   | 20.5   | 15.3   | 10.2   | 6.1    | 1.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)