

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630494

Luminaire Tested: GWS-SA1D-827-U-SL2-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-827-U-SL2-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2617.4 lumens
Efficiency: N/A
Efficacy: 59.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630494
 CATALOG NUMBER: GWS-SA1D-827-U-SL2-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 9.2 fc
 Type II - Short - N/A

REPORT NUMBER: P630494
CATALOG NUMBER: GWS-SA1D-827-U-SL2-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P630494
 CATALOG NUMBER: GWS-SA1D-827-U-SL2-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 515.7 | 0.0 | 515.7 |
| | % Fixture | 19.7 | 0.0 | 19.7 |
| Street Side | Lumens | 2101.6 | 0.0 | 2101.6 |
| | % Fixture | 80.3 | 0.0 | 80.3 |
| Total | Lumens | 2617.4 | 0.0 | 2617.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 80.6 | 3.1 |
| 10°-20° | 198.5 | 7.6 |
| 20°-30° | 279.9 | 10.7 |
| 30°-40° | 414.3 | 15.8 |
| 40°-50° | 597.6 | 22.8 |
| 50°-60° | 704.9 | 26.9 |
| 60°-70° | 314.5 | 12.0 |
| 70°-80° | 27.0 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2617.4 | 100.0 |
| 0°-180° | 2617.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P630494

CATALOG NUMBER: GWS-SA1D-827-U-SL2-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 337.9 | 12.9 | | | |
| FM (30°-60°) | 1468.8 | 56.1 | | | |
| FH (60°-80°) | 294.9 | 11.3 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 221.1 | 8.4 | B1/500 | | |
| BM (30°-60°) | 248.0 | 9.5 | B1/1000 | | |
| BH (60°-80°) | 46.6 | 1.8 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0
 Type II Short





REPORT NUMBER: P630494
 CATALOG NUMBER: GWS-SA1D-827-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 |
| 2.5° | 853.1 | 853.8 | 854.1 | 862.7 | 865.9 | 878.7 | 885.4 | 888.9 | 898.2 | 909.1 | 918.0 |
| 5° | 795.9 | 795.0 | 796.6 | 807.5 | 814.5 | 833.3 | 843.6 | 850.6 | 871.0 | 896.6 | 918.0 |
| 7.5° | 746.1 | 748.0 | 749.9 | 761.8 | 772.3 | 792.8 | 807.5 | 818.0 | 846.4 | 884.5 | 920.6 |
| 10° | 711.0 | 711.0 | 713.8 | 727.3 | 739.7 | 765.0 | 779.7 | 793.1 | 826.9 | 873.6 | 923.4 |
| 12.5° | 685.1 | 685.4 | 688.9 | 704.2 | 718.6 | 744.8 | 760.2 | 773.3 | 810.6 | 862.7 | 924.1 |
| 15° | 672.9 | 672.0 | 674.8 | 691.1 | 707.1 | 731.7 | 747.7 | 760.5 | 799.1 | 856.7 | 927.3 |
| 17.5° | 669.7 | 669.1 | 671.3 | 687.3 | 703.6 | 727.6 | 743.2 | 756.0 | 797.5 | 858.6 | 936.9 |
| 20° | 679.0 | 677.7 | 676.8 | 690.5 | 705.8 | 729.5 | 745.8 | 760.2 | 805.2 | 869.1 | 951.6 |
| 22.5° | 701.0 | 701.0 | 698.8 | 705.5 | 715.7 | 737.2 | 754.1 | 772.9 | 825.3 | 890.2 | 973.3 |
| 25° | 741.6 | 738.4 | 734.3 | 737.2 | 735.9 | 749.3 | 769.4 | 795.6 | 863.4 | 925.0 | 999.8 |
| 27.5° | 788.0 | 790.8 | 783.8 | 784.1 | 772.9 | 768.2 | 791.5 | 831.1 | 919.9 | 974.2 | 1039.1 |
| 30° | 850.9 | 848.7 | 849.0 | 848.0 | 822.2 | 799.5 | 824.7 | 877.4 | 991.2 | 1049.3 | 1090.2 |
| 32.5° | 900.1 | 903.3 | 913.9 | 919.9 | 886.1 | 849.6 | 876.5 | 940.4 | 1072.3 | 1135.0 | 1152.9 |
| 35° | 952.2 | 958.0 | 979.4 | 999.2 | 970.7 | 928.9 | 957.6 | 1023.8 | 1148.7 | 1219.6 | 1224.8 |
| 37.5° | 1007.2 | 1018.7 | 1044.2 | 1079.1 | 1074.6 | 1037.5 | 1063.7 | 1121.9 | 1208.8 | 1270.8 | 1284.2 |
| 40° | 1070.1 | 1081.3 | 1123.1 | 1173.3 | 1183.9 | 1175.6 | 1184.2 | 1218.0 | 1248.4 | 1273.0 | 1309.8 |
| 42.5° | 1139.1 | 1154.5 | 1207.5 | 1274.6 | 1314.2 | 1321.6 | 1301.4 | 1297.9 | 1265.7 | 1247.4 | 1304.3 |
| 45° | 1220.6 | 1238.5 | 1298.6 | 1385.5 | 1448.4 | 1458.3 | 1423.5 | 1378.5 | 1276.5 | 1228.6 | 1288.0 |
| 47.5° | 1312.0 | 1328.9 | 1388.7 | 1493.2 | 1586.8 | 1590.6 | 1529.9 | 1457.4 | 1308.8 | 1250.3 | 1300.5 |
| 50° | 1342.7 | 1353.2 | 1405.0 | 1527.7 | 1700.2 | 1729.6 | 1641.7 | 1546.2 | 1373.7 | 1314.2 | 1361.2 |
| 52.5° | 1237.2 | 1241.4 | 1286.4 | 1410.4 | 1677.2 | 1866.1 | 1805.0 | 1678.8 | 1489.0 | 1411.7 | 1454.8 |
| 55° | 980.3 | 973.6 | 1010.0 | 1123.8 | 1457.7 | 1838.3 | 1953.0 | 1887.1 | 1637.6 | 1526.1 | 1576.6 |
| 57.5° | 685.7 | 677.7 | 669.4 | 746.4 | 1087.7 | 1558.3 | 1799.6 | 1916.2 | 1779.1 | 1639.5 | 1707.9 |
| 60° | 563.7 | 556.0 | 515.7 | 480.3 | 657.6 | 1119.0 | 1382.3 | 1601.8 | 1767.6 | 1633.8 | 1703.7 |
| 62.5° | 487.0 | 482.5 | 466.2 | 417.9 | 387.0 | 638.7 | 865.6 | 1075.9 | 1356.4 | 1282.9 | 1286.7 |
| 65° | 382.5 | 381.2 | 392.4 | 397.5 | 342.2 | 353.4 | 441.6 | 559.2 | 733.3 | 691.5 | 655.7 |
| 67.5° | 261.4 | 258.5 | 279.6 | 343.8 | 329.1 | 278.9 | 258.5 | 260.7 | 317.3 | 194.0 | 154.0 |
| 70° | 166.2 | 159.4 | 159.8 | 213.1 | 267.8 | 220.2 | 199.4 | 175.4 | 157.8 | 28.8 | 32.6 |
| 72.5° | 106.4 | 102.2 | 87.9 | 96.2 | 124.0 | 107.4 | 108.3 | 93.3 | 62.3 | 15.3 | 17.9 |
| 75° | 44.7 | 41.2 | 31.6 | 25.2 | 24.9 | 15.7 | 13.7 | 12.8 | 8.6 | 8.6 | 9.3 |
| 77.5° | 0.3 | 0.0 | 0.0 | 0.3 | 0.6 | 0.3 | 0.3 | 0.6 | 1.3 | 1.9 | 2.2 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630494
 CATALOG NUMBER: GWS-SA1D-827-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 | 918.3 |
| 2.5° | 923.4 | 915.8 | 924.4 | 927.6 | 927.3 | 927.6 | 918.3 | 911.9 | 911.6 | 903.6 | 899.8 |
| 5° | 927.0 | 920.9 | 927.3 | 923.1 | 913.2 | 900.8 | 884.1 | 869.8 | 863.4 | 854.1 | 849.6 |
| 7.5° | 933.7 | 927.3 | 926.3 | 909.7 | 885.1 | 858.9 | 829.5 | 803.3 | 789.2 | 772.3 | 773.3 |
| 10° | 938.5 | 931.1 | 918.6 | 884.8 | 843.9 | 802.0 | 758.2 | 719.3 | 694.7 | 672.0 | 668.1 |
| 12.5° | 940.4 | 929.5 | 900.4 | 849.3 | 791.8 | 737.2 | 672.9 | 617.3 | 579.0 | 549.3 | 545.1 |
| 15° | 943.9 | 926.3 | 877.1 | 806.5 | 727.6 | 650.2 | 568.4 | 492.4 | 441.6 | 407.4 | 410.3 |
| 17.5° | 949.3 | 922.8 | 850.9 | 758.6 | 658.6 | 549.3 | 438.7 | 351.5 | 304.8 | 285.0 | 285.3 |
| 20° | 957.0 | 918.6 | 822.2 | 705.8 | 575.8 | 435.2 | 306.7 | 240.9 | 227.8 | 227.2 | 226.2 |
| 22.5° | 967.2 | 914.5 | 791.5 | 648.0 | 477.7 | 304.8 | 204.2 | 183.7 | 189.2 | 199.7 | 201.6 |
| 25° | 979.4 | 909.4 | 757.3 | 582.8 | 370.7 | 200.0 | 153.1 | 149.9 | 163.0 | 177.0 | 180.2 |
| 27.5° | 998.2 | 906.8 | 718.3 | 508.7 | 260.1 | 143.5 | 125.3 | 127.2 | 139.0 | 150.8 | 153.7 |
| 30° | 1030.2 | 911.6 | 675.8 | 425.6 | 167.1 | 114.4 | 108.6 | 111.5 | 117.9 | 124.0 | 126.5 |
| 32.5° | 1073.6 | 925.7 | 634.6 | 334.9 | 119.2 | 99.4 | 98.1 | 99.7 | 102.2 | 105.8 | 106.7 |
| 35° | 1124.4 | 950.0 | 592.1 | 239.6 | 98.4 | 90.7 | 89.5 | 89.5 | 90.7 | 91.4 | 91.7 |
| 37.5° | 1166.3 | 975.5 | 552.1 | 159.4 | 88.2 | 84.0 | 82.1 | 81.2 | 80.8 | 81.5 | 81.8 |
| 40° | 1184.5 | 986.1 | 508.7 | 116.0 | 80.8 | 78.0 | 75.1 | 72.2 | 72.2 | 74.5 | 74.8 |
| 42.5° | 1171.7 | 974.2 | 458.5 | 95.9 | 75.7 | 71.6 | 67.1 | 64.5 | 65.8 | 68.1 | 68.7 |
| 45° | 1144.6 | 945.2 | 403.2 | 84.7 | 70.6 | 65.2 | 60.1 | 58.5 | 59.8 | 62.6 | 63.3 |
| 47.5° | 1140.1 | 926.0 | 337.1 | 77.3 | 65.2 | 59.8 | 54.3 | 52.7 | 54.3 | 56.6 | 57.2 |
| 50° | 1184.5 | 942.6 | 263.6 | 70.9 | 60.1 | 54.0 | 49.5 | 47.9 | 48.9 | 50.2 | 50.8 |
| 52.5° | 1265.7 | 1004.3 | 212.8 | 64.9 | 54.0 | 48.2 | 45.4 | 43.5 | 43.5 | 44.7 | 45.1 |
| 55° | 1385.5 | 1112.0 | 183.7 | 57.8 | 47.0 | 43.8 | 41.2 | 39.3 | 39.3 | 39.9 | 40.3 |
| 57.5° | 1523.5 | 1242.3 | 190.4 | 48.6 | 41.2 | 39.6 | 37.4 | 35.8 | 36.4 | 36.4 | 36.4 |
| 60° | 1504.3 | 1232.7 | 203.9 | 40.9 | 36.4 | 35.8 | 33.9 | 33.2 | 34.8 | 33.6 | 32.9 |
| 62.5° | 1108.1 | 851.5 | 106.7 | 33.6 | 31.3 | 30.7 | 29.4 | 30.7 | 32.9 | 29.4 | 28.1 |
| 65° | 538.1 | 412.2 | 42.8 | 27.5 | 26.5 | 25.9 | 25.2 | 27.2 | 28.4 | 23.0 | 21.7 |
| 67.5° | 126.5 | 102.9 | 27.8 | 23.3 | 22.0 | 20.8 | 21.4 | 21.7 | 20.8 | 15.7 | 15.0 |
| 70° | 32.9 | 32.3 | 21.7 | 19.5 | 17.6 | 16.3 | 16.3 | 16.0 | 13.7 | 9.9 | 9.3 |
| 72.5° | 17.9 | 17.6 | 15.7 | 14.7 | 12.1 | 10.9 | 11.2 | 9.9 | 7.7 | 5.8 | 5.4 |
| 75° | 8.9 | 9.6 | 8.9 | 8.3 | 6.7 | 6.1 | 6.1 | 5.4 | 3.8 | 2.2 | 2.2 |
| 77.5° | 1.9 | 2.2 | 2.2 | 1.9 | 1.6 | 1.3 | 1.3 | 1.6 | 0.6 | 0.0 | 0.0 |
| 80° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)