

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630507

Luminaire Tested: GWS-SA1D-827-U-SLL-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-827-U-SLL-W
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4177.8 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630507
 CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7 fc
 Type III - Short - N/A

REPORT NUMBER: P630507
CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P630507

CATALOG NUMBER: GWS-SA1D-827-U-SLL-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 998.9 | 0.0 | 998.9 |
| | % Fixture | 23.9 | 0.0 | 23.9 |
| Street Side | Lumens | 3178.9 | 0.0 | 3178.9 |
| | % Fixture | 76.1 | 0.0 | 76.1 |
| Total | Lumens | 4177.8 | 0.0 | 4177.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 51.3 | 1.2 |
| 10°-20° | 166.8 | 4.0 |
| 20°-30° | 262.5 | 6.3 |
| 30°-40° | 359.9 | 8.6 |
| 40°-50° | 561.5 | 13.4 |
| 50°-60° | 968.1 | 23.2 |
| 60°-70° | 1121.9 | 26.9 |
| 70°-80° | 592.2 | 14.2 |
| 80°-90° | 93.5 | 2.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4177.8 | 100.0 |
| 0°-180° | 4177.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P630507


CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 276.3 | 6.6 | | | |
| FM (30°-60°) | 1379.2 | 33.0 | | | |
| FH (60°-80°) | 1451.1 | 34.7 | | | G1/1800 |
| FVH (80°-90°) | 72.2 | 1.7 | | | G1/100 |
| BL (0°-30°) | 204.3 | 4.9 | B1/500 | | |
| BM (30°-60°) | 510.2 | 12.2 | B1/1000 | | |
| BH (60°-80°) | 263.0 | 6.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 21.3 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type III Short





REPORT NUMBER: P630507
 CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 2° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 |
| 2.5° | 565.9 | 563.7 | 560.5 | 549.6 | 542.9 | 535.3 | 527.3 | 518.0 | 507.5 | 500.1 | 492.8 |
| 5° | 613.9 | 610.4 | 602.7 | 576.8 | 558.9 | 539.4 | 523.1 | 504.6 | 486.4 | 473.9 | 461.4 |
| 7.5° | 659.9 | 655.4 | 643.6 | 604.0 | 574.9 | 546.8 | 522.2 | 495.3 | 468.2 | 449.6 | 434.9 |
| 10° | 705.9 | 696.6 | 681.6 | 629.9 | 591.5 | 558.9 | 530.8 | 497.9 | 461.8 | 436.5 | 420.9 |
| 12.5° | 741.1 | 732.4 | 716.1 | 653.5 | 608.1 | 567.2 | 535.6 | 505.2 | 474.5 | 447.7 | 431.7 |
| 15° | 774.0 | 762.8 | 744.3 | 675.6 | 621.9 | 566.9 | 526.0 | 499.5 | 495.0 | 488.3 | 467.5 |
| 17.5° | 797.6 | 787.4 | 768.2 | 693.4 | 629.5 | 557.0 | 499.5 | 483.8 | 503.9 | 524.4 | 504.6 |
| 20° | 818.4 | 806.6 | 787.1 | 705.9 | 631.1 | 534.9 | 467.2 | 467.5 | 499.2 | 527.3 | 522.5 |
| 22.5° | 836.0 | 822.9 | 805.6 | 720.0 | 630.5 | 504.3 | 439.1 | 458.3 | 489.9 | 511.9 | 512.6 |
| 25° | 857.7 | 846.8 | 832.5 | 740.7 | 630.5 | 473.0 | 418.6 | 447.1 | 474.2 | 492.8 | 492.1 |
| 27.5° | 884.2 | 876.9 | 865.1 | 772.4 | 636.2 | 446.7 | 407.1 | 432.7 | 454.1 | 470.1 | 469.8 |
| 30° | 913.9 | 907.2 | 898.3 | 805.9 | 646.2 | 427.3 | 400.7 | 414.8 | 430.4 | 443.2 | 443.2 |
| 32.5° | 944.3 | 941.7 | 932.2 | 832.8 | 638.5 | 421.2 | 395.3 | 396.9 | 405.2 | 415.7 | 414.8 |
| 35° | 986.5 | 983.9 | 971.8 | 853.5 | 605.2 | 412.6 | 386.7 | 378.7 | 379.6 | 386.3 | 388.6 |
| 37.5° | 1048.2 | 1044.3 | 1026.4 | 877.8 | 555.1 | 390.8 | 372.6 | 359.5 | 356.6 | 359.5 | 363.7 |
| 40° | 1122.6 | 1116.9 | 1092.6 | 910.8 | 497.2 | 361.4 | 350.6 | 339.7 | 334.9 | 335.9 | 340.7 |
| 42.5° | 1215.9 | 1203.8 | 1169.0 | 945.6 | 440.0 | 335.5 | 326.0 | 319.2 | 313.8 | 313.2 | 322.4 |
| 45° | 1367.4 | 1334.2 | 1278.9 | 976.6 | 391.8 | 321.8 | 303.9 | 299.1 | 294.6 | 297.2 | 308.1 |
| 47.5° | 1632.0 | 1570.6 | 1463.0 | 1003.1 | 362.4 | 322.1 | 286.3 | 281.2 | 280.9 | 286.0 | 298.2 |
| 50° | 1995.7 | 1907.1 | 1741.0 | 1021.0 | 347.0 | 326.0 | 275.8 | 267.5 | 273.5 | 278.7 | 290.2 |
| 52.5° | 2344.0 | 2208.8 | 2011.0 | 1020.7 | 340.3 | 326.6 | 278.7 | 254.7 | 273.5 | 274.8 | 285.7 |
| 55° | 2641.5 | 2396.7 | 2083.9 | 915.9 | 330.7 | 324.0 | 289.8 | 244.8 | 270.0 | 274.8 | 283.5 |
| 57.5° | 2878.0 | 2516.2 | 2078.4 | 739.8 | 359.8 | 310.0 | 296.6 | 242.5 | 259.8 | 275.5 | 285.4 |
| 60° | 2851.8 | 2461.6 | 1944.5 | 454.1 | 357.0 | 285.0 | 295.6 | 246.7 | 242.5 | 266.8 | 283.1 |
| 62.5° | 2677.6 | 2265.7 | 1714.1 | 315.1 | 335.2 | 270.7 | 279.9 | 254.1 | 226.6 | 254.4 | 272.3 |
| 65° | 2433.8 | 2012.9 | 1428.4 | 241.6 | 277.7 | 271.3 | 253.4 | 248.9 | 212.5 | 234.6 | 253.7 |
| 67.5° | 2111.3 | 1699.4 | 1127.7 | 191.4 | 193.7 | 234.9 | 230.1 | 221.1 | 199.4 | 217.0 | 234.2 |
| 70° | 1587.3 | 1240.2 | 775.9 | 154.0 | 146.7 | 196.2 | 206.8 | 198.8 | 186.6 | 191.7 | 210.0 |
| 72.5° | 1118.5 | 809.8 | 425.0 | 122.1 | 113.1 | 150.8 | 179.6 | 178.3 | 164.9 | 168.7 | 186.6 |
| 75° | 831.2 | 573.0 | 265.6 | 96.5 | 92.0 | 108.0 | 150.5 | 154.3 | 143.2 | 147.6 | 161.4 |
| 77.5° | 553.2 | 371.0 | 147.6 | 71.6 | 71.6 | 78.9 | 112.2 | 130.1 | 121.8 | 125.3 | 134.9 |
| 80° | 305.2 | 188.9 | 73.8 | 47.0 | 48.3 | 54.3 | 81.8 | 93.6 | 94.0 | 102.6 | 105.1 |
| 82.5° | 96.5 | 60.1 | 32.9 | 27.5 | 25.9 | 31.0 | 52.7 | 67.1 | 62.6 | 79.9 | 73.5 |
| 85° | 22.0 | 14.1 | 6.1 | 6.1 | 6.7 | 10.2 | 20.1 | 35.8 | 45.7 | 55.0 | 39.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 14.1 | 20.8 | 18.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630507
 CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 |
| 2.5° | 488.3 | 481.9 | 480.0 | 474.5 | 473.9 | 468.8 | 466.9 | 466.9 | 469.1 | 469.1 | 471.4 |
| 5° | 456.3 | 448.3 | 443.9 | 437.5 | 435.9 | 432.0 | 429.5 | 429.8 | 432.7 | 434.6 | 438.4 |
| 7.5° | 428.2 | 422.8 | 419.6 | 416.7 | 416.1 | 415.4 | 412.6 | 412.2 | 413.2 | 416.1 | 418.9 |
| 10° | 416.4 | 412.6 | 413.5 | 415.7 | 419.3 | 421.2 | 418.6 | 417.3 | 416.4 | 418.3 | 420.9 |
| 12.5° | 427.9 | 424.1 | 426.0 | 429.8 | 434.6 | 436.5 | 435.6 | 435.2 | 436.2 | 443.6 | 449.0 |
| 15° | 453.1 | 445.8 | 443.2 | 444.8 | 448.7 | 450.6 | 449.6 | 450.9 | 457.0 | 476.1 | 489.9 |
| 17.5° | 484.5 | 466.6 | 456.3 | 453.5 | 455.1 | 456.7 | 456.7 | 459.8 | 470.4 | 498.5 | 515.8 |
| 20° | 501.4 | 478.1 | 460.8 | 453.8 | 454.4 | 456.0 | 456.0 | 460.5 | 472.3 | 502.4 | 513.5 |
| 22.5° | 496.9 | 475.5 | 454.4 | 446.7 | 447.1 | 448.3 | 448.3 | 452.2 | 462.7 | 489.2 | 494.4 |
| 25° | 479.3 | 460.5 | 439.7 | 433.0 | 433.6 | 435.9 | 435.2 | 437.5 | 445.5 | 467.2 | 470.1 |
| 27.5° | 458.3 | 441.6 | 421.2 | 416.1 | 418.9 | 423.4 | 419.6 | 419.9 | 427.3 | 445.5 | 445.8 |
| 30° | 435.6 | 421.8 | 403.6 | 399.8 | 405.2 | 407.4 | 403.9 | 403.9 | 411.3 | 423.7 | 423.4 |
| 32.5° | 411.0 | 402.3 | 389.2 | 385.1 | 391.1 | 394.7 | 390.2 | 390.8 | 396.6 | 404.9 | 401.7 |
| 35° | 387.9 | 383.5 | 377.4 | 374.5 | 378.4 | 381.6 | 378.7 | 380.0 | 385.4 | 387.6 | 383.2 |
| 37.5° | 365.9 | 365.3 | 365.9 | 365.9 | 366.9 | 367.8 | 365.9 | 369.1 | 373.9 | 371.0 | 365.9 |
| 40° | 346.7 | 349.3 | 355.4 | 353.8 | 352.8 | 353.8 | 352.5 | 357.9 | 362.7 | 357.6 | 351.5 |
| 42.5° | 330.7 | 335.5 | 344.8 | 344.8 | 342.9 | 343.5 | 342.9 | 349.6 | 353.1 | 346.1 | 339.4 |
| 45° | 317.0 | 324.0 | 335.9 | 337.5 | 334.3 | 334.3 | 335.5 | 343.8 | 345.1 | 335.5 | 328.5 |
| 47.5° | 307.4 | 316.0 | 329.5 | 332.3 | 327.6 | 327.2 | 330.7 | 339.7 | 339.7 | 328.5 | 320.5 |
| 50° | 300.7 | 310.3 | 326.3 | 330.1 | 325.3 | 324.0 | 329.8 | 338.4 | 336.5 | 323.1 | 315.1 |
| 52.5° | 296.2 | 306.1 | 326.0 | 331.4 | 328.2 | 326.9 | 332.7 | 338.7 | 333.9 | 319.6 | 311.3 |
| 55° | 293.4 | 304.2 | 326.9 | 331.4 | 327.9 | 325.6 | 331.4 | 336.8 | 334.3 | 317.6 | 309.7 |
| 57.5° | 295.0 | 305.8 | 325.6 | 327.9 | 323.7 | 319.9 | 326.6 | 334.3 | 333.3 | 318.3 | 310.3 |
| 60° | 292.4 | 302.3 | 318.6 | 319.2 | 312.2 | 306.1 | 316.0 | 327.6 | 327.6 | 316.0 | 309.0 |
| 62.5° | 280.6 | 290.5 | 304.9 | 305.5 | 297.5 | 290.8 | 302.3 | 316.0 | 315.7 | 306.5 | 299.1 |
| 65° | 261.1 | 270.3 | 286.6 | 288.2 | 280.3 | 273.2 | 285.0 | 297.8 | 298.8 | 290.5 | 284.1 |
| 67.5° | 239.7 | 248.0 | 260.1 | 266.5 | 259.8 | 252.5 | 263.3 | 275.5 | 275.1 | 265.2 | 258.5 |
| 70° | 214.1 | 221.8 | 233.0 | 238.4 | 234.2 | 227.2 | 237.1 | 243.5 | 240.6 | 235.8 | 231.4 |
| 72.5° | 188.9 | 196.2 | 206.8 | 206.8 | 202.3 | 195.6 | 198.4 | 210.0 | 213.5 | 210.0 | 207.1 |
| 75° | 162.3 | 168.7 | 176.1 | 177.7 | 167.8 | 155.6 | 169.0 | 179.0 | 183.1 | 181.5 | 178.0 |
| 77.5° | 135.2 | 140.0 | 150.8 | 148.0 | 129.4 | 123.0 | 133.9 | 148.6 | 151.5 | 150.5 | 145.7 |
| 80° | 104.2 | 107.1 | 118.6 | 112.8 | 98.4 | 94.3 | 99.1 | 110.6 | 111.2 | 108.0 | 101.9 |
| 82.5° | 70.0 | 73.8 | 81.5 | 70.3 | 70.0 | 66.1 | 62.3 | 63.6 | 69.3 | 68.7 | 64.6 |
| 85° | 35.8 | 37.7 | 45.1 | 42.2 | 36.1 | 31.3 | 29.7 | 31.6 | 28.4 | 25.9 | 22.4 |
| 87.5° | 15.0 | 16.3 | 22.4 | 12.5 | 3.8 | 0.0 | 0.0 | 1.9 | 2.9 | 4.2 | 4.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630507
 CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|
| 0° | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 |
| 2.5° | 476.5 | 480.0 | 488.6 | 499.5 | 510.0 | 520.9 | 532.7 | 540.1 | 549.0 | 560.5 | 560.8 |
| 5° | 443.2 | 451.2 | 463.7 | 480.3 | 497.6 | 517.4 | 540.4 | 559.6 | 582.6 | 600.8 | 608.1 |
| 7.5° | 422.8 | 434.3 | 449.9 | 471.0 | 493.7 | 518.3 | 548.4 | 580.6 | 618.4 | 642.6 | 657.0 |
| 10° | 424.7 | 442.3 | 457.9 | 475.8 | 496.3 | 522.8 | 561.5 | 604.3 | 650.6 | 682.6 | 700.5 |
| 12.5° | 458.9 | 477.4 | 474.5 | 473.6 | 487.3 | 519.6 | 572.0 | 628.3 | 684.8 | 716.8 | 738.2 |
| 15° | 502.0 | 509.1 | 481.9 | 461.4 | 469.8 | 508.1 | 577.8 | 649.7 | 713.3 | 752.2 | 773.3 |
| 17.5° | 524.1 | 510.0 | 477.1 | 446.4 | 444.2 | 490.5 | 580.6 | 671.4 | 745.2 | 784.2 | 806.6 |
| 20° | 513.9 | 493.4 | 465.6 | 436.5 | 420.5 | 466.6 | 579.0 | 688.7 | 774.3 | 817.8 | 836.0 |
| 22.5° | 491.8 | 473.9 | 452.2 | 424.4 | 401.4 | 440.4 | 574.9 | 705.9 | 800.2 | 844.0 | 859.9 |
| 25° | 467.8 | 454.4 | 436.5 | 412.2 | 390.5 | 417.3 | 572.0 | 728.9 | 829.9 | 871.8 | 882.0 |
| 27.5° | 443.9 | 434.0 | 419.3 | 400.4 | 387.9 | 401.4 | 573.0 | 759.0 | 868.2 | 907.9 | 903.7 |
| 30° | 420.2 | 411.6 | 401.4 | 393.1 | 387.6 | 397.5 | 570.4 | 790.9 | 910.4 | 947.2 | 922.6 |
| 32.5° | 397.9 | 389.9 | 383.5 | 384.8 | 387.9 | 399.1 | 557.3 | 820.0 | 949.1 | 980.4 | 943.0 |
| 35° | 378.7 | 370.4 | 370.4 | 374.8 | 386.7 | 393.7 | 523.4 | 842.7 | 991.9 | 1023.2 | 972.1 |
| 37.5° | 360.8 | 353.4 | 358.2 | 365.6 | 376.8 | 379.0 | 480.0 | 864.7 | 1054.2 | 1083.6 | 1017.2 |
| 40° | 345.1 | 337.8 | 346.4 | 355.7 | 361.4 | 360.5 | 435.9 | 895.4 | 1127.7 | 1158.1 | 1076.9 |
| 42.5° | 332.7 | 326.0 | 333.6 | 345.4 | 346.4 | 347.4 | 403.6 | 924.8 | 1213.1 | 1251.7 | 1179.8 |
| 45° | 322.4 | 317.6 | 321.5 | 333.3 | 333.3 | 348.0 | 383.5 | 949.4 | 1341.5 | 1409.9 | 1368.7 |
| 47.5° | 314.4 | 311.6 | 313.5 | 317.3 | 323.7 | 359.5 | 370.7 | 968.3 | 1575.4 | 1709.7 | 1668.1 |
| 50° | 310.0 | 307.1 | 309.7 | 301.7 | 320.8 | 365.3 | 366.5 | 982.7 | 1883.8 | 2094.1 | 2042.6 |
| 52.5° | 306.1 | 305.2 | 306.8 | 288.2 | 327.2 | 361.4 | 363.3 | 963.5 | 2090.6 | 2472.4 | 2523.3 |
| 55° | 304.9 | 305.5 | 297.8 | 278.3 | 334.9 | 348.6 | 353.8 | 826.4 | 2146.8 | 2798.7 | 3114.1 |
| 57.5° | 305.5 | 303.6 | 284.1 | 279.3 | 335.2 | 323.1 | 367.5 | 589.6 | 2065.0 | 2940.6 | 3692.2 |
| 60° | 303.3 | 293.7 | 267.5 | 287.9 | 320.5 | 293.0 | 357.6 | 384.4 | 1849.3 | 2831.6 | 3725.8 |
| 62.5° | 293.4 | 279.3 | 253.1 | 292.7 | 294.3 | 275.1 | 324.7 | 296.2 | 1561.7 | 2598.4 | 3402.4 |
| 65° | 279.0 | 260.1 | 240.9 | 282.8 | 267.8 | 266.8 | 244.1 | 237.4 | 1255.9 | 2320.7 | 3095.6 |
| 67.5° | 255.3 | 236.5 | 232.0 | 260.1 | 240.9 | 236.5 | 196.2 | 196.8 | 1002.1 | 2024.7 | 2787.2 |
| 70° | 228.5 | 209.6 | 213.1 | 235.2 | 214.4 | 196.5 | 158.8 | 163.9 | 760.2 | 1687.0 | 2371.5 |
| 72.5° | 210.9 | 185.7 | 186.0 | 207.1 | 188.5 | 159.1 | 130.7 | 135.2 | 482.5 | 1271.5 | 1885.4 |
| 75° | 178.0 | 163.6 | 156.6 | 167.8 | 160.1 | 124.0 | 109.9 | 109.0 | 286.0 | 911.4 | 1411.8 |
| 77.5° | 148.6 | 137.4 | 133.9 | 138.4 | 119.5 | 91.7 | 88.5 | 86.9 | 162.0 | 583.8 | 925.1 |
| 80° | 107.7 | 104.8 | 104.5 | 106.7 | 92.0 | 67.4 | 67.4 | 67.7 | 87.2 | 317.0 | 521.5 |
| 82.5° | 68.4 | 74.8 | 66.1 | 73.5 | 62.6 | 47.9 | 44.7 | 50.8 | 50.2 | 135.2 | 219.9 |
| 85° | 28.4 | 39.0 | 36.4 | 38.7 | 29.7 | 26.2 | 28.1 | 30.4 | 29.1 | 52.1 | 85.6 |
| 87.5° | 5.4 | 6.4 | 7.0 | 6.7 | 6.7 | 8.3 | 9.3 | 11.2 | 11.2 | 15.0 | 25.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630507
 CATALOG NUMBER: GWS-SA1D-827-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 358° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 | 520.9 |
| 2.5° | 573.0 | 582.2 | 580.3 | 584.5 | 579.0 | 581.0 | 570.1 | 567.2 | 565.3 | 565.9 |
| 5° | 631.8 | 650.6 | 654.1 | 661.2 | 656.4 | 656.4 | 637.2 | 622.8 | 617.7 | 613.9 |
| 7.5° | 691.5 | 718.7 | 736.6 | 738.5 | 736.0 | 730.8 | 703.0 | 677.2 | 667.9 | 659.9 |
| 10° | 744.6 | 777.2 | 797.3 | 806.9 | 802.1 | 794.1 | 759.6 | 724.1 | 712.9 | 705.9 |
| 12.5° | 785.2 | 813.9 | 827.3 | 833.7 | 833.1 | 830.2 | 802.1 | 763.8 | 751.9 | 741.1 |
| 15° | 811.4 | 825.7 | 820.6 | 820.3 | 824.8 | 836.3 | 827.7 | 797.6 | 783.9 | 774.0 |
| 17.5° | 828.3 | 814.6 | 791.9 | 781.3 | 790.9 | 818.1 | 837.9 | 821.0 | 808.5 | 797.6 |
| 20° | 834.4 | 785.5 | 752.6 | 733.1 | 744.3 | 783.6 | 832.5 | 837.9 | 827.3 | 818.4 |
| 22.5° | 827.3 | 750.0 | 705.3 | 682.3 | 693.1 | 740.1 | 816.5 | 851.6 | 844.6 | 836.0 |
| 25° | 810.1 | 712.9 | 659.3 | 638.5 | 650.3 | 698.2 | 788.0 | 864.4 | 864.7 | 857.7 |
| 27.5° | 788.7 | 678.7 | 627.0 | 607.5 | 619.0 | 663.7 | 760.2 | 875.6 | 886.8 | 884.2 |
| 30° | 766.9 | 658.3 | 611.6 | 597.9 | 606.5 | 646.2 | 731.8 | 887.1 | 909.5 | 913.9 |
| 32.5° | 757.0 | 668.2 | 647.8 | 653.8 | 642.6 | 656.4 | 721.6 | 903.4 | 937.0 | 944.3 |
| 35° | 770.1 | 756.1 | 807.9 | 831.8 | 792.2 | 740.1 | 734.7 | 928.0 | 975.6 | 986.5 |
| 37.5° | 833.7 | 944.3 | 1021.6 | 1106.0 | 1037.3 | 922.6 | 799.5 | 969.9 | 1030.9 | 1048.2 |
| 40° | 972.1 | 1108.6 | 1248.2 | 1357.2 | 1253.3 | 1099.0 | 922.9 | 1032.2 | 1107.0 | 1122.6 |
| 42.5° | 1102.5 | 1262.6 | 1455.0 | 1595.9 | 1461.0 | 1243.1 | 1055.8 | 1137.0 | 1207.3 | 1215.9 |
| 45° | 1230.3 | 1413.7 | 1705.2 | 1901.1 | 1718.0 | 1380.2 | 1191.6 | 1314.0 | 1367.1 | 1367.4 |
| 47.5° | 1380.2 | 1584.1 | 2019.0 | 2298.0 | 2058.9 | 1532.0 | 1319.1 | 1594.3 | 1668.1 | 1632.0 |
| 50° | 1559.5 | 1753.4 | 2342.1 | 2759.7 | 2474.7 | 1718.6 | 1481.2 | 1935.9 | 2036.6 | 1995.7 |
| 52.5° | 1799.5 | 1940.1 | 2698.1 | 3210.0 | 2927.8 | 1931.1 | 1716.0 | 2387.1 | 2420.4 | 2344.0 |
| 55° | 2137.2 | 2209.4 | 3155.0 | 3766.0 | 3433.7 | 2192.8 | 2059.6 | 2953.4 | 2860.4 | 2641.5 |
| 57.5° | 2906.4 | 2635.7 | 3741.7 | 4400.4 | 4006.0 | 2668.3 | 2812.5 | 3577.8 | 3247.1 | 2878.0 |
| 60° | 3550.0 | 3153.4 | 4284.7 | 5029.9 | 4496.5 | 3192.4 | 3519.3 | 3686.5 | 3232.7 | 2851.8 |
| 62.5° | 3333.0 | 3285.4 | 4480.6 | 5099.2 | 4664.0 | 3450.3 | 3388.0 | 3412.6 | 3021.8 | 2677.6 |
| 65° | 2924.3 | 3030.7 | 4305.8 | 4770.4 | 4478.3 | 3219.3 | 3064.6 | 3159.5 | 2780.5 | 2433.8 |
| 67.5° | 2683.0 | 2761.3 | 3994.8 | 4244.1 | 4140.9 | 2969.4 | 2813.1 | 2744.4 | 2406.0 | 2111.3 |
| 70° | 2436.3 | 2501.2 | 3558.3 | 3583.6 | 3614.6 | 2553.9 | 2300.2 | 2095.7 | 1793.4 | 1587.3 |
| 72.5° | 2105.3 | 2108.8 | 3006.4 | 2860.1 | 2918.9 | 1998.5 | 1851.5 | 1566.8 | 1305.4 | 1118.5 |
| 75° | 1766.2 | 1669.7 | 2379.8 | 1999.2 | 2117.1 | 1554.7 | 1537.4 | 1180.8 | 984.6 | 831.2 |
| 77.5° | 1346.6 | 1233.8 | 1738.4 | 1314.7 | 1486.9 | 1035.4 | 1155.9 | 800.8 | 692.8 | 553.2 |
| 80° | 904.0 | 833.7 | 960.6 | 742.0 | 972.7 | 713.6 | 753.8 | 453.8 | 393.4 | 305.2 |
| 82.5° | 476.8 | 407.1 | 593.7 | 440.0 | 586.7 | 392.1 | 282.8 | 140.3 | 119.5 | 96.5 |
| 85° | 184.7 | 213.8 | 291.1 | 156.6 | 227.5 | 140.0 | 81.8 | 34.8 | 29.1 | 22.0 |
| 87.5° | 35.8 | 55.3 | 30.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797 M/P: 2.26



| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)