

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P632995

Luminaire Tested: GWS-SA2D-827-U-T2R-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P632995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2D-827-U-T2R-W
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8752.2 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 82.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P632995
 CATALOG NUMBER: GWS-SA2D-827-U-T2R-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 21.5 fc
 Type II - Short - N/A

REPORT NUMBER: P632995
CATALOG NUMBER: GWS-SA2D-827-U-T2R-W

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P632995

CATALOG NUMBER: GWS-SA2D-827-U-T2R-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1462.9 | 0.0 | 1462.9 |
| | % Fixture | 16.7 | 0.0 | 16.7 |
| Street Side | Lumens | 7289.3 | 0.0 | 7289.3 |
| | % Fixture | 83.3 | 0.0 | 83.3 |
| Total | Lumens | 8752.2 | 0.0 | 8752.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 98.5 | 1.1 |
| 10°-20° | 375.0 | 4.3 |
| 20°-30° | 730.9 | 8.4 |
| 30°-40° | 1222.4 | 14.0 |
| 40°-50° | 1750.2 | 20.0 |
| 50°-60° | 2072.1 | 23.7 |
| 60°-70° | 1722.9 | 19.7 |
| 70°-80° | 705.1 | 8.1 |
| 80°-90° | 75.1 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 8752.2 | 100.0 |
| 0°-180° | 8752.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P632995


CATALOG NUMBER: GWS-SA2D-827-U-T2R-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 898.4 | 10.3 | | | |
| FM (30°-60°) | 4333.8 | 49.5 | | | |
| FH (60°-80°) | 2012.4 | 23.0 | | | G2/5000 |
| FVH (80°-90°) | 44.8 | 0.5 | | | G1/100 |
| BL (0°-30°) | 306.0 | 3.5 | B1/500 | | |
| BM (30°-60°) | 711.0 | 8.1 | B1/1000 | | |
| BH (60°-80°) | 415.6 | 4.7 | B1/500 | | G1/500 |
| BVH (80°-90°) | 30.3 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type II Short





REPORT NUMBER: P632995
 CATALOG NUMBER: GWS-SA2D-827-U-T2R-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 76° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 |
| 2.5° | 1161.7 | 1166.0 | 1151.8 | 1146.9 | 1113.7 | 1068.8 | 1031.2 | 974.6 | 922.3 | 914.3 | 867.6 |
| 5° | 1475.5 | 1457.0 | 1441.0 | 1430.6 | 1384.4 | 1333.3 | 1254.0 | 1147.5 | 1036.2 | 1022.6 | 921.7 |
| 7.5° | 1661.9 | 1658.8 | 1639.1 | 1633.0 | 1597.3 | 1546.2 | 1464.4 | 1332.1 | 1170.3 | 1148.1 | 994.9 |
| 10° | 1811.4 | 1809.6 | 1799.7 | 1805.3 | 1772.7 | 1722.8 | 1643.5 | 1506.9 | 1317.3 | 1295.2 | 1076.8 |
| 12.5° | 1941.9 | 1944.9 | 1943.1 | 1963.4 | 1946.8 | 1908.0 | 1825.6 | 1675.4 | 1464.4 | 1440.4 | 1176.4 |
| 15° | 2037.2 | 2039.7 | 2048.9 | 2093.2 | 2102.5 | 2094.5 | 2010.8 | 1841.0 | 1609.6 | 1575.2 | 1279.2 |
| 17.5° | 2064.3 | 2069.2 | 2091.4 | 2162.8 | 2212.6 | 2245.8 | 2183.7 | 2009.6 | 1752.4 | 1714.8 | 1383.8 |
| 20° | 2100.6 | 2106.2 | 2128.3 | 2202.8 | 2276.0 | 2351.7 | 2340.6 | 2180.6 | 1896.3 | 1865.6 | 1489.6 |
| 22.5° | 2268.6 | 2264.3 | 2254.4 | 2290.1 | 2342.4 | 2436.6 | 2464.3 | 2344.9 | 2045.2 | 2015.7 | 1606.5 |
| 25° | 2592.2 | 2584.2 | 2521.5 | 2488.9 | 2471.6 | 2528.9 | 2578.1 | 2494.4 | 2190.4 | 2146.1 | 1715.4 |
| 27.5° | 2949.1 | 2944.8 | 2864.8 | 2787.3 | 2681.5 | 2656.8 | 2685.8 | 2624.8 | 2331.3 | 2286.4 | 1810.2 |
| 30° | 3286.9 | 3274.0 | 3190.3 | 3093.1 | 2951.6 | 2845.7 | 2803.3 | 2752.8 | 2485.8 | 2439.0 | 1920.9 |
| 32.5° | 3589.0 | 3572.4 | 3473.9 | 3366.3 | 3218.0 | 3093.1 | 2966.3 | 2888.8 | 2660.5 | 2606.4 | 2034.2 |
| 35° | 3837.0 | 3820.4 | 3719.5 | 3605.0 | 3442.0 | 3349.7 | 3176.1 | 3036.5 | 2838.4 | 2783.6 | 2167.7 |
| 37.5° | 4028.9 | 4013.6 | 3908.3 | 3795.7 | 3653.6 | 3580.4 | 3429.6 | 3202.6 | 3043.2 | 2986.0 | 2309.2 |
| 40° | 4136.6 | 4125.5 | 4041.3 | 3952.0 | 3832.7 | 3769.3 | 3701.6 | 3412.4 | 3272.7 | 3215.5 | 2475.9 |
| 42.5° | 4169.2 | 4161.8 | 4102.8 | 4056.6 | 3976.0 | 3928.0 | 3966.8 | 3659.2 | 3517.6 | 3467.8 | 2663.6 |
| 45° | 4087.4 | 4087.4 | 4070.2 | 4093.6 | 4097.2 | 4096.6 | 4232.6 | 3937.9 | 3818.5 | 3763.8 | 2928.2 |
| 47.5° | 3878.2 | 3891.7 | 3917.0 | 4032.0 | 4153.2 | 4254.8 | 4543.3 | 4309.5 | 4205.5 | 4160.6 | 3302.9 |
| 50° | 3495.5 | 3532.4 | 3618.5 | 3843.1 | 4100.9 | 4359.4 | 4837.4 | 4859.0 | 4958.0 | 4878.7 | 3854.2 |
| 52.5° | 2935.0 | 2929.4 | 3149.1 | 3469.0 | 3862.2 | 4363.7 | 4999.3 | 5343.8 | 5610.3 | 5555.5 | 4264.0 |
| 55° | 2332.6 | 2323.4 | 2528.2 | 2969.4 | 3496.1 | 4198.8 | 5096.5 | 5565.9 | 5972.0 | 5922.8 | 4632.5 |
| 57.5° | 1786.2 | 1774.5 | 1956.6 | 2354.7 | 2979.3 | 3848.7 | 5078.0 | 5830.5 | 6469.8 | 6444.6 | 5133.4 |
| 60° | 1229.4 | 1215.2 | 1385.6 | 1733.9 | 2367.7 | 3313.4 | 4873.7 | 5966.5 | 7052.5 | 7061.1 | 5669.3 |
| 62.5° | 738.4 | 730.4 | 854.0 | 1124.1 | 1703.1 | 2650.1 | 4395.7 | 5884.1 | 7516.4 | 7555.2 | 6013.9 |
| 65° | 445.5 | 439.9 | 512.5 | 670.7 | 1080.5 | 1933.9 | 3658.5 | 5462.6 | 7583.5 | 7672.7 | 6021.9 |
| 67.5° | 324.3 | 324.9 | 345.8 | 408.6 | 630.1 | 1249.0 | 2745.4 | 4707.0 | 7234.0 | 7326.3 | 5642.2 |
| 70° | 281.8 | 283.0 | 294.1 | 308.3 | 380.9 | 715.0 | 1785.0 | 3715.8 | 6200.9 | 6272.3 | 4732.2 |
| 72.5° | 250.4 | 250.4 | 257.8 | 265.2 | 297.8 | 435.6 | 956.2 | 2597.2 | 4894.0 | 4913.1 | 3611.8 |
| 75° | 220.3 | 218.4 | 222.1 | 225.8 | 258.4 | 304.6 | 465.2 | 1809.6 | 3614.9 | 3570.6 | 2334.4 |
| 77.5° | 175.4 | 173.5 | 174.1 | 177.8 | 207.4 | 217.8 | 235.7 | 1130.3 | 2037.2 | 1922.8 | 1031.2 |
| 80° | 124.9 | 123.7 | 130.4 | 139.7 | 153.2 | 133.5 | 147.7 | 547.0 | 807.9 | 751.9 | 399.9 |
| 82.5° | 74.5 | 76.9 | 87.4 | 94.8 | 105.8 | 83.7 | 95.4 | 182.7 | 286.1 | 278.7 | 162.4 |
| 85° | 10.5 | 11.1 | 31.4 | 36.3 | 45.5 | 32.6 | 50.5 | 82.4 | 114.4 | 122.4 | 57.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 4.3 | 14.8 | 32.6 | 33.2 | 14.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P632995
 CATALOG NUMBER: GWS-SA2D-827-U-T2R-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 | 828.8 |
| 2.5° | 843.6 | 814.6 | 773.4 | 739.0 | 710.0 | 686.7 | 667.0 | 652.2 | 647.9 | 641.8 | 641.8 |
| 5° | 874.3 | 822.0 | 748.2 | 695.9 | 665.7 | 647.9 | 635.6 | 629.4 | 626.4 | 622.7 | 620.8 |
| 7.5° | 916.8 | 843.6 | 743.9 | 691.0 | 667.6 | 656.5 | 648.5 | 644.8 | 642.4 | 638.7 | 638.7 |
| 10° | 975.2 | 875.6 | 757.4 | 708.2 | 689.7 | 678.7 | 669.4 | 663.3 | 657.7 | 652.2 | 651.0 |
| 12.5° | 1038.6 | 917.4 | 782.0 | 731.6 | 711.9 | 698.4 | 685.4 | 676.2 | 669.4 | 662.7 | 660.8 |
| 15° | 1108.8 | 960.5 | 808.5 | 754.4 | 729.7 | 711.3 | 695.9 | 681.7 | 672.5 | 662.7 | 661.4 |
| 17.5° | 1177.7 | 1004.2 | 830.6 | 769.7 | 738.4 | 715.6 | 693.4 | 675.0 | 663.3 | 652.2 | 649.1 |
| 20° | 1260.1 | 1047.8 | 846.0 | 774.0 | 736.5 | 706.4 | 679.9 | 656.5 | 643.6 | 630.7 | 628.8 |
| 22.5° | 1335.8 | 1088.5 | 853.4 | 767.9 | 722.4 | 686.7 | 655.9 | 630.7 | 616.5 | 603.6 | 601.1 |
| 25° | 1409.0 | 1124.1 | 850.3 | 753.1 | 700.8 | 659.6 | 627.6 | 602.4 | 588.8 | 575.3 | 571.6 |
| 27.5° | 1479.8 | 1148.1 | 838.0 | 730.4 | 673.7 | 629.4 | 598.7 | 575.9 | 564.2 | 552.5 | 547.6 |
| 30° | 1549.3 | 1170.3 | 819.0 | 700.8 | 639.3 | 598.1 | 572.8 | 556.8 | 545.2 | 532.8 | 529.2 |
| 32.5° | 1619.5 | 1186.3 | 790.0 | 666.4 | 604.2 | 570.4 | 555.0 | 543.3 | 531.0 | 518.7 | 515.0 |
| 35° | 1690.2 | 1193.1 | 755.0 | 627.0 | 574.7 | 552.5 | 547.0 | 533.5 | 516.8 | 502.1 | 497.2 |
| 37.5° | 1774.5 | 1199.2 | 711.3 | 588.2 | 548.8 | 543.9 | 542.7 | 522.4 | 502.7 | 482.4 | 476.9 |
| 40° | 1876.0 | 1207.2 | 666.4 | 553.1 | 527.9 | 540.8 | 535.9 | 508.2 | 468.9 | 449.2 | 443.0 |
| 42.5° | 2000.3 | 1222.0 | 619.6 | 521.2 | 512.5 | 529.2 | 523.6 | 473.8 | 447.3 | 436.2 | 433.2 |
| 45° | 2183.1 | 1276.1 | 572.8 | 495.9 | 500.8 | 512.5 | 503.9 | 453.5 | 443.0 | 435.6 | 431.9 |
| 47.5° | 2508.6 | 1359.2 | 532.2 | 476.9 | 491.6 | 497.8 | 464.5 | 447.9 | 439.9 | 430.1 | 425.8 |
| 50° | 2847.0 | 1395.5 | 499.6 | 465.2 | 481.2 | 484.2 | 443.0 | 440.6 | 435.0 | 424.6 | 420.2 |
| 52.5° | 3075.9 | 1390.6 | 479.9 | 460.9 | 472.5 | 460.9 | 433.2 | 432.6 | 428.9 | 416.6 | 411.6 |
| 55° | 3334.3 | 1399.2 | 471.3 | 462.1 | 468.9 | 421.5 | 420.9 | 422.7 | 420.9 | 407.3 | 404.9 |
| 57.5° | 3683.1 | 1425.6 | 467.0 | 466.4 | 466.4 | 402.4 | 409.2 | 411.6 | 407.9 | 401.8 | 399.9 |
| 60° | 4018.5 | 1427.5 | 459.0 | 471.3 | 464.5 | 390.7 | 395.6 | 398.1 | 393.8 | 392.6 | 391.9 |
| 62.5° | 4144.6 | 1338.9 | 441.2 | 467.6 | 457.2 | 377.8 | 381.5 | 382.7 | 378.4 | 381.5 | 380.9 |
| 65° | 3957.0 | 1150.6 | 411.6 | 449.8 | 434.4 | 366.1 | 363.6 | 366.7 | 359.3 | 367.3 | 367.9 |
| 67.5° | 3513.3 | 914.3 | 366.7 | 415.9 | 402.4 | 353.2 | 348.3 | 348.3 | 336.0 | 348.3 | 347.6 |
| 70° | 2832.8 | 646.1 | 300.9 | 361.8 | 367.3 | 337.8 | 335.3 | 321.2 | 301.5 | 320.0 | 318.1 |
| 72.5° | 2147.4 | 463.9 | 236.9 | 286.1 | 316.3 | 316.3 | 316.9 | 292.9 | 270.1 | 278.7 | 271.3 |
| 75° | 1360.4 | 326.7 | 189.5 | 219.0 | 248.0 | 277.5 | 291.6 | 247.3 | 227.0 | 223.4 | 219.7 |
| 77.5° | 612.8 | 214.7 | 147.7 | 168.0 | 176.0 | 219.0 | 266.4 | 212.9 | 185.2 | 177.2 | 174.7 |
| 80° | 256.6 | 133.5 | 105.2 | 118.8 | 108.3 | 184.0 | 235.0 | 165.5 | 136.0 | 124.9 | 116.9 |
| 82.5° | 112.6 | 79.4 | 67.1 | 64.0 | 67.7 | 136.6 | 175.4 | 110.1 | 84.9 | 115.1 | 116.3 |
| 85° | 47.4 | 41.8 | 34.5 | 31.4 | 27.7 | 52.3 | 82.4 | 43.1 | 52.9 | 30.1 | 24.6 |
| 87.5° | 11.1 | 12.3 | 9.2 | 6.2 | 3.7 | 0.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797 M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)