

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P832691

Luminaire Tested: **TTN-D3-750-U-DL-CG**

Issue Date: 5/14/2024

Test Information

Test Method: LM-79-08
Report Number: P832691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-254-15)
Test Lab: INNOVATION CENTER
Issue Date: 5/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TTN-D3-750-U-DL-CG
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE
5000K, 70 CRI LEDS AND DRIVE LANE DISTRIBUTION WITH CLEAR GLASS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6612 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Luminous Opening: Circular (Dia: 0.71' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 59.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P832691
 CATALOG NUMBER: TTN-D3-750-U-DL-CG

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P832691
CATALOG NUMBER: TTN-D3-750-U-DL-CG

Luminous Intensity Polar Plot



— Vertical Plane Through 33-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P832691

CATALOG NUMBER: TTN-D3-750-U-DL-CG


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1459.0	0.0	1459.0
	% Fixture	22.1	0.0	22.1
Street Side	Lumens	5153.0	0.0	5153.0
	% Fixture	77.9	0.0	77.9
Total	Lumens	6612.0	0.0	6612.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.3	0.9
10°-20°	192.3	2.9
20°-30°	405.4	6.1
30°-40°	736.3	11.1
40°-50°	1163.5	17.6
50°-60°	1545.1	23.4
60°-70°	1487.2	22.5
70°-80°	873.0	13.2
80°-90°	149.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6612.0	100.0
0°-180°	6612.0	100.0

Coefficient of Utilization



REPORT NUMBER: P832691


CATALOG NUMBER: TTN-D3-750-U-DL-CG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	442.4	6.7			
FM (30°-60°)	2675.0	40.5			
FH (60°-80°)	1909.0	28.9			G2/5000
FVH (80°-90°)	126.6	1.9			G2/225
BL (0°-30°)	214.6	3.2	B1/500		
BM (30°-60°)	769.9	11.6	B1/1000		
BH (60°-80°)	451.2	6.8	B1/500		G1/500
BVH (80°-90°)	23.3	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P832691
 CATALOG NUMBER: TTN-D3-750-U-DL-CG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	33°	35°	45°	55°	65°	75°	85°
0°	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7
2.5°	660.2	666.0	660.2	660.2	654.5	654.5	648.7	642.9	637.1	631.3	619.7
5°	735.5	735.5	729.7	718.2	712.4	706.6	695.0	677.6	666.0	648.7	631.3
7.5°	770.3	770.3	764.5	752.9	741.3	735.5	718.2	695.0	677.6	654.5	631.3
10°	816.6	822.4	810.8	799.2	787.7	781.9	758.7	729.7	700.8	671.8	637.1
12.5°	868.7	874.5	868.7	851.4	834.0	828.2	805.0	770.3	735.5	695.0	654.5
15°	938.2	949.8	932.5	920.9	903.5	897.7	868.7	828.2	787.7	735.5	683.4
17.5°	1019.3	1025.1	1013.5	996.2	984.6	978.8	949.8	903.5	845.6	787.7	724.0
20°	1112.0	1117.8	1112.0	1088.8	1077.2	1071.5	1042.5	990.4	920.9	857.2	776.1
22.5°	1222.0	1233.6	1216.2	1198.9	1187.3	1187.3	1152.5	1094.6	1013.5	932.5	839.8
25°	1349.5	1366.8	1343.7	1332.1	1320.5	1314.7	1285.7	1216.2	1123.6	1025.1	909.3
27.5°	1505.8	1517.4	1500.0	1494.2	1471.1	1471.1	1424.7	1343.7	1245.2	1129.4	996.2
30°	1644.8	1656.4	1644.8	1644.8	1627.4	1621.7	1575.3	1494.2	1372.6	1233.6	1071.5
32.5°	1778.0	1789.6	1783.8	1789.6	1783.8	1778.0	1720.1	1633.2	1511.6	1332.1	1146.7
35°	1911.2	1928.6	1922.8	1940.2	1934.4	1928.6	1882.3	1778.0	1633.2	1453.7	1227.8
37.5°	2050.2	2067.6	2067.6	2085.0	2090.8	2090.8	2038.7	1928.6	1766.4	1563.7	1320.5
40°	2200.8	2218.2	2218.2	2247.2	2258.7	2258.7	2200.8	2090.8	1911.2	1685.4	1418.9
42.5°	2345.6	2363.0	2368.8	2397.7	2415.1	2420.9	2374.6	2247.2	2038.7	1807.0	1511.6
45°	2484.6	2502.0	2519.4	2577.3	2606.2	2600.4	2565.7	2432.5	2200.8	1934.4	1610.1
47.5°	2617.8	2641.0	2669.9	2745.2	2785.8	2780.0	2756.8	2606.2	2351.4	2056.0	1696.9
50°	2722.1	2739.4	2797.4	2878.4	2930.6	2936.4	2901.6	2756.8	2478.8	2148.7	1760.7
52.5°	2803.1	2826.3	2895.8	3011.6	3052.2	3069.6	3029.0	2884.2	2606.2	2229.8	1812.8
55°	2861.1	2861.1	2965.3	3098.5	3156.4	3168.0	3168.0	2988.5	2681.5	2281.9	1841.7
57.5°	2832.1	2832.1	2947.9	3092.7	3185.4	3179.6	3168.0	2994.3	2693.1	2270.3	1824.4
60°	2751.0	2768.4	2878.4	3023.2	3115.9	3110.1	3075.4	2919.0	2635.2	2224.0	1789.6
62.5°	2641.0	2669.9	2785.8	2895.8	3000.1	3017.4	2971.1	2832.1	2536.7	2154.5	1725.9
65°	2432.5	2473.0	2617.8	2739.4	2820.5	2855.3	2797.4	2669.9	2403.5	2021.3	1592.7
67.5°	2200.8	2229.8	2351.4	2525.2	2571.5	2606.2	2577.3	2444.1	2218.2	1807.0	1442.1
70°	1934.4	1980.7	2061.8	2235.6	2287.7	2322.4	2322.4	2189.2	1974.9	1586.9	1262.6
72.5°	1621.7	1673.8	1772.2	1899.7	1969.2	1992.3	1986.5	1876.5	1685.4	1343.7	1065.7
75°	1280.0	1320.5	1436.3	1529.0	1604.3	1621.7	1615.9	1523.2	1349.5	1083.0	845.6
77.5°	944.0	984.6	1071.5	1141.0	1210.5	1198.9	1198.9	1129.4	1019.3	805.0	642.9
80°	619.7	654.5	729.7	752.9	828.2	822.4	822.4	770.3	695.0	538.6	428.6
82.5°	341.7	370.7	422.8	446.0	492.3	480.7	486.5	451.7	405.4	301.2	243.2
85°	121.6	144.8	173.7	191.1	214.3	214.3	214.3	185.3	173.7	115.8	98.5
87.5°	5.8	11.6	23.2	23.2	34.7	34.7	34.7	23.2	23.2	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P832691
 CATALOG NUMBER: TTN-D3-750-U-DL-CG

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7	619.7
2.5°	613.9	608.1	602.3	590.7	585.0	579.2	573.4	567.6	567.6	567.6	567.6
5°	619.7	613.9	596.5	579.2	561.8	544.4	532.8	527.0	521.2	515.5	515.5
7.5°	619.7	608.1	585.0	561.8	544.4	521.2	503.9	486.5	474.9	469.1	469.1
10°	625.5	608.1	579.2	556.0	527.0	498.1	474.9	451.7	440.2	428.6	428.6
12.5°	637.1	619.7	579.2	550.2	515.5	480.7	451.7	428.6	411.2	399.6	399.6
15°	660.2	637.1	590.7	550.2	509.7	469.1	440.2	411.2	393.8	382.2	382.2
17.5°	695.0	666.0	608.1	550.2	503.9	463.3	428.6	399.6	376.5	364.9	364.9
20°	735.5	700.8	631.3	561.8	503.9	457.5	422.8	388.0	364.9	353.3	353.3
22.5°	793.5	741.3	660.2	579.2	515.5	463.3	417.0	382.2	359.1	347.5	347.5
25°	857.2	799.2	695.0	602.3	527.0	463.3	417.0	382.2	359.1	347.5	341.7
27.5°	926.7	863.0	735.5	625.5	538.6	474.9	422.8	382.2	359.1	347.5	347.5
30°	990.4	915.1	776.1	654.5	556.0	480.7	428.6	388.0	359.1	347.5	347.5
32.5°	1059.9	973.0	816.6	683.4	573.4	492.3	434.4	393.8	364.9	353.3	347.5
35°	1129.4	1030.9	857.2	706.6	590.7	503.9	440.2	399.6	370.7	359.1	359.1
37.5°	1204.7	1094.6	897.7	735.5	608.1	515.5	451.7	405.4	376.5	364.9	364.9
40°	1285.7	1158.3	938.2	758.7	625.5	527.0	463.3	417.0	388.0	376.5	376.5
42.5°	1366.8	1227.8	984.6	787.7	642.9	538.6	469.1	428.6	399.6	388.0	388.0
45°	1447.9	1285.7	1025.1	816.6	660.2	556.0	486.5	440.2	411.2	399.6	399.6
47.5°	1523.2	1349.5	1059.9	834.0	677.6	567.6	492.3	451.7	422.8	417.0	411.2
50°	1575.3	1390.0	1083.0	851.4	683.4	573.4	503.9	457.5	434.4	422.8	422.8
52.5°	1615.9	1430.5	1100.4	863.0	689.2	579.2	509.7	469.1	446.0	434.4	428.6
55°	1639.0	1436.3	1100.4	851.4	683.4	579.2	509.7	469.1	446.0	434.4	434.4
57.5°	1615.9	1407.4	1077.2	828.2	666.0	561.8	492.3	457.5	434.4	428.6	422.8
60°	1569.5	1361.0	1030.9	793.5	637.1	532.8	469.1	440.2	422.8	417.0	411.2
62.5°	1505.8	1303.1	984.6	747.1	596.5	498.1	451.7	417.0	405.4	399.6	393.8
65°	1378.4	1193.1	909.3	689.2	544.4	457.5	411.2	388.0	376.5	364.9	359.1
67.5°	1239.4	1071.5	805.0	619.7	480.7	411.2	370.7	347.5	330.1	330.1	324.3
70°	1088.8	944.0	695.0	527.0	417.0	359.1	318.5	301.2	289.6	289.6	283.8
72.5°	909.3	793.5	579.2	428.6	341.7	295.4	266.4	249.0	243.2	243.2	237.5
75°	729.7	625.5	457.5	335.9	266.4	231.7	208.5	196.9	191.1	191.1	185.3
77.5°	538.6	457.5	330.1	243.2	191.1	168.0	150.6	144.8	139.0	139.0	133.2
80°	359.1	301.2	214.3	156.4	115.8	104.2	92.7	92.7	86.9	92.7	86.9
82.5°	196.9	162.2	115.8	81.1	57.9	52.1	46.3	46.3	52.1	52.1	46.3
85°	75.3	57.9	40.5	23.2	17.4	17.4	17.4	17.4	17.4	17.4	11.6
87.5°	5.8	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)