

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637928

Luminaire Tested: GWS-SA4D-827-U-SL4-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P637928  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-35)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4D-827-U-SL4-W  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS  
Light Source: (64) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 17289.2 lumens  
Efficiency: N/A  
Efficacy: 106.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3  
  
Input Watts (W): 162.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P637928  
 CATALOG NUMBER: GWS-SA4D-827-U-SL4-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P637928  
CATALOG NUMBER: GWS-SA4D-827-U-SL4-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P637928

CATALOG NUMBER: GWS-SA4D-827-U-SL4-W

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2663.0   | 0.0    | 2663.0  |
|                    | % Fixture | 15.4     | 0.0    | 15.4    |
| <b>Street Side</b> | Lumens    | 14626.2  | 0.0    | 14626.2 |
|                    | % Fixture | 84.6     | 0.0    | 84.6    |
| <b>Total</b>       | Lumens    | 17289.2  | 0.0    | 17289.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 259.4   | 1.5       |
| 10°-20°   | 676.1   | 3.9       |
| 20°-30°   | 1061.5  | 6.1       |
| 30°-40°   | 1596.0  | 9.2       |
| 40°-50°   | 2463.5  | 14.2      |
| 50°-60°   | 3658.5  | 21.2      |
| 60°-70°   | 4611.5  | 26.7      |
| 70°-80°   | 2666.8  | 15.4      |
| 80°-90°   | 296.0   | 1.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 17289.2 | 100.0     |
| 0°-180°   | 17289.2 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P637928


CATALOG NUMBER: GWS-SA4D-827-U-SL4-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1310.6 | 7.6       |                         |      |         |
| FM (30°-60°)   | 6405.4 | 37.0      |                         |      |         |
| FH (60°-80°)   | 6663.7 | 38.5      |                         |      | G3/7500 |
| FVH (80°-90°)  | 246.5  | 1.4       |                         |      | G3/500  |
| BL (0°-30°)    | 686.3  | 4.0       | B2/1000                 |      |         |
| BM (30°-60°)   | 1312.6 | 7.6       | B2/2500                 |      |         |
| BH (60°-80°)   | 614.6  | 3.6       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 49.5   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P637928  
 CATALOG NUMBER: GWS-SA4D-827-U-SL4-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°     | 40°     | 45°     | 55°     | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|--------|--------|--------|
| 0°    | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9  | 2935.9  | 2935.9  | 2935.9  | 2935.9 | 2935.9 | 2935.9 |
| 2.5°  | 2954.0 | 2959.1 | 2963.0 | 2968.2 | 2965.6  | 2957.8  | 2964.3  | 2964.3  | 2950.1 | 2934.6 | 2920.4 |
| 5°    | 2957.8 | 2964.3 | 2963.0 | 2961.7 | 2951.4  | 2938.5  | 2938.5  | 2930.7  | 2906.2 | 2881.7 | 2858.5 |
| 7.5°  | 2950.1 | 2948.8 | 2947.5 | 2943.6 | 2932.0  | 2917.8  | 2915.3  | 2899.8  | 2867.5 | 2834.0 | 2800.4 |
| 10°   | 2915.3 | 2914.0 | 2917.8 | 2926.9 | 2924.3  | 2911.4  | 2911.4  | 2897.2  | 2859.8 | 2818.5 | 2774.6 |
| 12.5° | 2886.9 | 2886.9 | 2902.4 | 2926.9 | 2935.9  | 2930.7  | 2932.0  | 2921.7  | 2879.1 | 2830.1 | 2778.5 |
| 15°   | 2890.7 | 2892.0 | 2925.6 | 2965.6 | 2982.4  | 2978.5  | 2979.8  | 2968.2  | 2920.4 | 2871.4 | 2801.7 |
| 17.5° | 2916.5 | 2923.0 | 2981.1 | 3036.6 | 3058.5  | 3053.3  | 3044.3  | 3024.9  | 2970.7 | 2915.3 | 2830.1 |
| 20°   | 2970.7 | 2981.1 | 3055.9 | 3125.6 | 3151.4  | 3139.8  | 3124.3  | 3085.6  | 3026.2 | 2965.6 | 2861.1 |
| 22.5° | 3077.9 | 3084.3 | 3166.9 | 3235.3 | 3256.0  | 3241.8  | 3210.8  | 3155.3  | 3086.9 | 3023.7 | 2898.5 |
| 25°   | 3228.8 | 3236.6 | 3315.3 | 3378.5 | 3373.4  | 3356.6  | 3314.0  | 3245.6  | 3164.3 | 3097.2 | 2952.7 |
| 27.5° | 3408.2 | 3421.1 | 3498.6 | 3548.9 | 3515.3  | 3490.8  | 3443.1  | 3360.5  | 3268.9 | 3208.2 | 3035.3 |
| 30°   | 3604.4 | 3609.5 | 3675.4 | 3725.7 | 3674.1  | 3640.5  | 3582.4  | 3493.4  | 3410.8 | 3365.6 | 3159.2 |
| 32.5° | 3794.1 | 3799.3 | 3856.0 | 3884.4 | 3830.2  | 3805.7  | 3755.4  | 3661.2  | 3603.1 | 3578.6 | 3343.7 |
| 35°   | 3994.1 | 3992.8 | 4039.3 | 4063.8 | 4008.3  | 3998.0  | 3946.4  | 3874.1  | 3863.8 | 3896.0 | 3613.4 |
| 37.5° | 4194.1 | 4182.5 | 4207.1 | 4239.3 | 4208.3  | 4218.7  | 4185.1  | 4160.6  | 4200.6 | 4284.5 | 3972.2 |
| 40°   | 4354.2 | 4354.2 | 4380.0 | 4420.0 | 4430.3  | 4475.5  | 4456.1  | 4488.4  | 4617.4 | 4817.5 | 4416.1 |
| 42.5° | 4496.1 | 4497.4 | 4551.6 | 4613.6 | 4688.4  | 4758.1  | 4773.6  | 4857.5  | 5124.6 | 5438.2 | 4973.6 |
| 45°   | 4644.5 | 4645.8 | 4719.4 | 4809.7 | 4968.5  | 5101.4  | 5132.3  | 5320.8  | 5702.8 | 6084.7 | 5578.9 |
| 47.5° | 4816.2 | 4802.0 | 4903.9 | 5054.9 | 5280.8  | 5471.8  | 5551.8  | 5818.9  | 6301.5 | 6771.3 | 6149.3 |
| 50°   | 5009.7 | 4980.1 | 5093.6 | 5354.3 | 5633.1  | 5895.0  | 6029.3  | 6335.1  | 6944.2 | 7404.9 | 6686.1 |
| 52.5° | 5227.8 | 5211.1 | 5329.8 | 5647.3 | 6073.1  | 6375.1  | 6557.1  | 6958.4  | 7568.8 | 8036.0 | 7112.0 |
| 55°   | 5498.9 | 5458.8 | 5630.5 | 6034.4 | 6589.3  | 6973.9  | 7189.4  | 7575.3  | 8251.5 | 8609.0 | 7437.2 |
| 57.5° | 5795.7 | 5751.8 | 5981.5 | 6518.4 | 7260.4  | 7682.4  | 7952.1  | 8269.6  | 8894.2 | 9047.7 | 7628.2 |
| 60°   | 6115.7 | 6101.5 | 6373.8 | 7086.2 | 8060.5  | 8550.9  | 8745.8  | 9033.6  | 9453.0 | 9302.0 | 7580.4 |
| 62.5° | 6408.7 | 6403.5 | 6799.7 | 7701.7 | 8908.4  | 9447.8  | 9602.7  | 9678.8  | 9855.6 | 9285.2 | 7201.0 |
| 65°   | 6717.1 | 6761.0 | 7296.5 | 8415.4 | 9880.1  | 10409.2 | 10473.8 | 10280.2 | 9991.1 | 8845.1 | 6424.1 |
| 67.5° | 6755.8 | 6841.0 | 7608.8 | 9083.9 | 10801.5 | 11301.0 | 11249.4 | 10508.6 | 9591.1 | 7620.4 | 5035.6 |
| 70°   | 6042.2 | 6190.6 | 7110.7 | 9185.8 | 11450.7 | 11818.5 | 11445.5 | 10016.9 | 8139.2 | 5520.8 | 3166.9 |
| 72.5° | 5048.5 | 5176.2 | 5989.2 | 7833.4 | 10613.1 | 11081.6 | 10577.0 | 8478.6  | 5751.8 | 3166.9 | 1613.1 |
| 75°   | 3929.6 | 4078.0 | 4827.8 | 6226.7 | 7945.7  | 8132.8  | 7879.8  | 5913.1  | 3161.7 | 1306.0 | 733.0  |
| 77.5° | 2397.8 | 2504.9 | 3088.2 | 4218.7 | 5559.5  | 5279.5  | 4474.2  | 3315.3  | 1387.3 | 625.9  | 453.0  |
| 80°   | 1060.8 | 1126.6 | 1521.5 | 2266.1 | 3212.1  | 3036.6  | 2393.9  | 1415.7  | 758.8  | 397.5  | 316.2  |
| 82.5° | 569.1  | 611.7  | 749.8  | 896.9  | 1410.5  | 1475.0  | 1196.3  | 815.6   | 407.8  | 227.1  | 180.7  |
| 85°   | 250.4  | 274.9  | 340.7  | 325.2  | 463.3   | 455.5   | 459.4   | 560.1   | 194.9  | 104.5  | 117.4  |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 1.3     | 1.3     | 14.2    | 74.8    | 19.4   | 31.0   | 27.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P637928  
 CATALOG NUMBER: GWS-SA4D-827-U-SL4-W

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 | 2935.9 |
| 2.5°  | 2904.9 | 2881.7 | 2875.3 | 2867.5 | 2853.3 | 2828.8 | 2810.7 | 2790.1 | 2781.0 | 2770.7 | 2772.0 |
| 5°    | 2832.7 | 2804.3 | 2777.2 | 2742.3 | 2698.5 | 2649.4 | 2615.9 | 2577.1 | 2556.5 | 2537.1 | 2542.3 |
| 7.5°  | 2770.7 | 2726.8 | 2671.4 | 2597.8 | 2519.1 | 2431.3 | 2360.3 | 2304.8 | 2267.4 | 2241.6 | 2254.5 |
| 10°   | 2732.0 | 2680.4 | 2583.6 | 2463.6 | 2330.7 | 2196.4 | 2094.5 | 1999.0 | 1939.6 | 1893.2 | 1890.6 |
| 12.5° | 2724.3 | 2657.2 | 2516.5 | 2342.3 | 2150.0 | 1970.6 | 1820.9 | 1691.9 | 1613.1 | 1555.1 | 1577.0 |
| 15°   | 2732.0 | 2646.8 | 2458.4 | 2230.0 | 1987.4 | 1744.8 | 1558.9 | 1410.5 | 1316.3 | 1263.4 | 1259.5 |
| 17.5° | 2741.0 | 2636.5 | 2392.6 | 2108.7 | 1817.0 | 1539.6 | 1324.1 | 1166.6 | 1069.8 | 1016.9 | 1018.2 |
| 20°   | 2748.8 | 2621.0 | 2315.2 | 1975.8 | 1644.1 | 1348.6 | 1125.3 | 975.6  | 889.2  | 850.4  | 856.9  |
| 22.5° | 2761.7 | 2605.5 | 2232.6 | 1833.8 | 1467.3 | 1164.0 | 967.9  | 846.6  | 795.0  | 769.1  | 770.4  |
| 25°   | 2786.2 | 2596.5 | 2147.4 | 1679.0 | 1293.1 | 1016.9 | 859.5  | 778.2  | 745.9  | 730.4  | 729.1  |
| 27.5° | 2836.5 | 2604.2 | 2058.4 | 1529.3 | 1135.6 | 904.6  | 789.8  | 736.9  | 714.9  | 704.6  | 703.3  |
| 30°   | 2920.4 | 2635.2 | 1980.9 | 1377.0 | 1000.1 | 816.9  | 742.0  | 709.8  | 696.9  | 687.8  | 686.5  |
| 32.5° | 3048.2 | 2693.3 | 1897.0 | 1235.0 | 890.5  | 752.4  | 704.6  | 687.8  | 678.8  | 673.6  | 673.6  |
| 35°   | 3241.8 | 2799.1 | 1814.5 | 1111.1 | 805.3  | 702.0  | 674.9  | 668.5  | 660.7  | 658.2  | 660.7  |
| 37.5° | 3520.5 | 2968.2 | 1739.6 | 1002.7 | 744.6  | 663.3  | 642.7  | 645.3  | 638.8  | 642.7  | 646.5  |
| 40°   | 3874.1 | 3194.0 | 1676.4 | 913.7  | 699.5  | 634.9  | 614.3  | 623.3  | 619.4  | 623.3  | 629.8  |
| 42.5° | 4321.9 | 3474.0 | 1628.6 | 844.0  | 667.2  | 611.7  | 592.3  | 601.4  | 598.8  | 604.0  | 610.4  |
| 45°   | 4821.3 | 3843.1 | 1606.7 | 795.0  | 644.0  | 594.9  | 574.3  | 580.7  | 578.1  | 582.0  | 588.5  |
| 47.5° | 5300.1 | 4178.7 | 1626.0 | 766.6  | 624.6  | 580.7  | 558.8  | 561.4  | 560.1  | 558.8  | 562.7  |
| 50°   | 5713.1 | 4445.8 | 1681.5 | 757.5  | 611.7  | 566.5  | 545.9  | 547.2  | 543.3  | 535.6  | 538.1  |
| 52.5° | 6049.9 | 4660.0 | 1715.1 | 757.5  | 605.2  | 551.0  | 531.7  | 533.0  | 525.2  | 514.9  | 516.2  |
| 55°   | 6271.9 | 4746.5 | 1688.0 | 756.2  | 602.7  | 538.1  | 517.5  | 518.8  | 511.0  | 498.1  | 499.4  |
| 57.5° | 6335.1 | 4662.6 | 1574.4 | 742.0  | 600.1  | 527.8  | 503.3  | 505.9  | 500.7  | 486.5  | 486.5  |
| 60°   | 6158.3 | 4355.5 | 1366.6 | 709.8  | 593.6  | 521.4  | 493.0  | 496.8  | 494.3  | 480.1  | 480.1  |
| 62.5° | 5695.0 | 3809.6 | 1118.9 | 660.7  | 575.6  | 513.6  | 483.9  | 491.7  | 498.1  | 490.4  | 489.1  |
| 65°   | 4827.8 | 3052.1 | 909.8  | 606.5  | 552.3  | 500.7  | 471.0  | 490.4  | 504.6  | 514.9  | 514.9  |
| 67.5° | 3622.5 | 2184.8 | 742.0  | 549.8  | 517.5  | 474.9  | 454.3  | 472.3  | 482.6  | 489.1  | 493.0  |
| 70°   | 2208.1 | 1285.3 | 584.6  | 483.9  | 467.2  | 436.2  | 420.7  | 402.6  | 388.4  | 385.9  | 387.2  |
| 72.5° | 1080.2 | 735.6  | 474.9  | 411.7  | 398.8  | 370.4  | 335.5  | 327.8  | 321.3  | 317.5  | 316.2  |
| 75°   | 594.9  | 512.3  | 392.3  | 342.0  | 318.8  | 283.9  | 276.2  | 263.3  | 260.7  | 255.5  | 256.8  |
| 77.5° | 420.7  | 403.9  | 323.9  | 277.5  | 242.6  | 224.5  | 228.4  | 219.4  | 219.4  | 215.5  | 214.2  |
| 80°   | 316.2  | 317.5  | 249.1  | 202.6  | 179.4  | 172.9  | 176.8  | 176.8  | 174.2  | 172.9  | 171.6  |
| 82.5° | 200.0  | 225.8  | 167.8  | 130.3  | 127.8  | 129.1  | 127.8  | 126.5  | 129.1  | 125.2  | 123.9  |
| 85°   | 138.1  | 162.6  | 102.0  | 77.4   | 77.4   | 76.1   | 78.7   | 77.4   | 80.0   | 76.1   | 76.1   |
| 87.5° | 31.0   | 72.3   | 37.4   | 23.2   | 24.5   | 23.2   | 24.5   | 25.8   | 28.4   | 29.7   | 29.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K  
 CIE x = 0.4581  
 CIE y = 0.4156  
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>( $\mu$ W/nm) | Lumens<br>( $\phi$ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360               | 0                      | 0.0                     | 490               | 18018                  | 27.7                    | 620               | 87426                  | 1.1                     | 750               | 2680                   | 0.0                     | 880               | 58                     | 0.0                     |
| 365               | 0                      | 0.0                     | 495               | 22295                  | 36.0                    | 625               | 83013                  | 0.7                     | 755               | 2287                   | 0.0                     | 885               | 46                     | 0.0                     |
| 370               | 0                      | 0.0                     | 500               | 26478                  | 44.2                    | 630               | 78077                  | 0.4                     | 760               | 1944                   | 0.0                     | 890               | 45                     | 0.0                     |
| 375               | 0                      | 0.0                     | 505               | 30524                  | 51.8                    | 635               | 72080                  | 0.3                     | 765               | 1653                   | 0.0                     | 895               | 41                     | 0.0                     |
| 380               | 0                      | 0.0                     | 510               | 33611                  | 57.0                    | 640               | 66249                  | 0.2                     | 770               | 1413                   | 0.0                     | 900               | 38                     | 0.0                     |
| 385               | 0                      | 0.0                     | 515               | 36490                  | 60.5                    | 645               | 59973                  | 0.1                     | 775               | 1198                   | 0.0                     | 905               | 33                     | 0.0                     |
| 390               | 0                      | 0.0                     | 520               | 38610                  | 61.4                    | 650               | 53972                  | 0.1                     | 780               | 1025                   | 0.0                     | 910               | 30                     | 0.0                     |
| 395               | 0                      | 0.0                     | 525               | 40511                  | 60.6                    | 655               | 48369                  | 0.0                     | 785               | 874                    | 0.0                     | 915               | 23                     | 0.0                     |
| 400               | 48                     | 0.0                     | 530               | 42223                  | 58.2                    | 660               | 42641                  | 0.0                     | 790               | 747                    | 0.0                     | 920               | 24                     | 0.0                     |
| 405               | 201                    | 0.0                     | 535               | 44137                  | 55.0                    | 665               | 37602                  | 0.0                     | 795               | 639                    | 0.0                     | 925               | 22                     | 0.0                     |
| 410               | 457                    | 0.0                     | 540               | 46032                  | 50.9                    | 670               | 32798                  | 0.0                     | 800               | 547                    | 0.0                     | 930               | 22                     | 0.0                     |
| 415               | 925                    | 0.1                     | 545               | 48553                  | 46.6                    | 675               | 28558                  | 0.0                     | 805               | 473                    | 0.0                     | 935               | 17                     | 0.0                     |
| 420               | 1816                   | 0.3                     | 550               | 51408                  | 42.0                    | 680               | 24782                  | 0.0                     | 810               | 401                    | 0.0                     | 940               | 13                     | 0.0                     |
| 425               | 3217                   | 0.8                     | 555               | 54711                  | 37.4                    | 685               | 21386                  | 0.0                     | 815               | 351                    | 0.0                     | 945               | 6                      | 0.0                     |
| 430               | 5520                   | 1.9                     | 560               | 58847                  | 32.9                    | 690               | 18413                  | 0.0                     | 820               | 307                    | 0.0                     | 950               | 10                     | 0.0                     |
| 435               | 9225                   | 4.1                     | 565               | 63386                  | 28.4                    | 695               | 15721                  | 0.0                     | 825               | 261                    | 0.0                     | 955               | 11                     | 0.0                     |
| 440               | 15522                  | 8.7                     | 570               | 68196                  | 24.1                    | 700               | 13432                  | 0.0                     | 830               | 228                    | 0.0                     | 960               | 8                      | 0.0                     |
| 445               | 27642                  | 18.5                    | 575               | 73613                  | 20.0                    | 705               | 11513                  | 0.0                     | 835               | 193                    | 0.0                     | 965               | 12                     | 0.0                     |
| 450               | 36602                  | 28.3                    | 580               | 79207                  | 16.3                    | 710               | 9780                   | 0.0                     | 840               | 174                    | 0.0                     | 970               | 3                      | 0.0                     |
| 455               | 28292                  | 24.7                    | 585               | 84248                  | 12.9                    | 715               | 8356                   | 0.0                     | 845               | 151                    | 0.0                     | 975               | 8                      | 0.0                     |
| 460               | 21166                  | 20.4                    | 590               | 88397                  | 9.8                     | 720               | 7161                   | 0.0                     | 850               | 123                    | 0.0                     | 980               | 2                      | 0.0                     |
| 465               | 19092                  | 20.1                    | 595               | 91428                  | 7.3                     | 725               | 6067                   | 0.0                     | 855               | 106                    | 0.0                     | 985               | 13                     | 0.0                     |
| 470               | 14951                  | 17.2                    | 600               | 93452                  | 5.3                     | 730               | 5164                   | 0.0                     | 860               | 95                     | 0.0                     | 990               | 16                     | 0.0                     |
| 475               | 12606                  | 15.7                    | 605               | 93959                  | 3.7                     | 735               | 4393                   | 0.0                     | 865               | 82                     | 0.0                     | 995               | 20                     | 0.0                     |
| 480               | 13323                  | 18.0                    | 610               | 93079                  | 2.5                     | 740               | 3694                   | 0.0                     | 870               | 77                     | 0.0                     | 1000              | 0                      | 0.0                     |
| 485               | 15164                  | 21.9                    | 615               | 90707                  | 1.7                     | 745               | 3157                   | 0.0                     | 875               | 65                     | 0.0                     |                   |                        |                         |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_g = -1.5$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)