

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P833955

Luminaire Tested: **TTN-D3-750-U-MQ-UPL3**

Issue Date: 5/15/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P833955  
REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G3-2308-121-4) AND  
Test Lab: INNOVATION CENTER  
Issue Date: 5/15/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TTN-D3-750-U-MQ-UPL3  
Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE WITH UPLIGHT  
5000K, 70 CRI LEDS AND MEDIUM DISTRIBUTION  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8189.6 lumens  
Efficiency: N/A  
Efficacy: 123.7 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 0.71' x H: 0.1')  
IES Classification: Type V - Short  
BUG Rating: B3 - U4 - G2  
  
Input Watts (W): 66.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P833955  
 CATALOG NUMBER: TTN-D3-750-U-MQ-UPL3

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P833955  
CATALOG NUMBER: TTN-D3-750-U-MQ-UPL3

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P833955

CATALOG NUMBER: TTN-D3-750-U-MQ-UPL3


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	3689.0	405.8	4094.8
	% Fixture	45.0	5.0	50.0
<b>Street Side</b>	Lumens	3689.0	405.8	4094.8
	% Fixture	45.0	5.0	50.0
<b>Total</b>	Lumens	7378.1	811.5	8189.6
	% Fixture	90.1	9.9	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.3	1.8
10°-20°	417.0	5.1
20°-30°	674.0	8.2
30°-40°	912.1	11.1
40°-50°	1142.4	13.9
50°-60°	1400.0	17.1
60°-70°	1403.4	17.1
70°-80°	1012.7	12.4
80°-90°	271.1	3.3
90°-100°	18.1	0.2
100°-110°	184.1	2.2
110°-120°	269.1	3.3
120°-130°	156.2	1.9
130°-140°	82.7	1.0
140°-150°	49.1	0.6
150°-160°	30.3	0.4
160°-170°	16.5	0.2
170°-180°	5.4	0.1
0°-90°	7378.1	90.1
0°-180°	8189.6	100.0

**Coefficient of Utilization**



REPORT NUMBER: P833955


CATALOG NUMBER: TTN-D3-750-U-MQ-UPL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	618.2	7.5			
FM (30°-60°)	1727.2	21.1			
FH (60°-80°)	1208.1	14.8			G1/1800
FVH (80°-90°)	135.6	1.7			G2/225
BL (0°-30°)	618.2	7.5	B2/1000		
BM (30°-60°)	1727.2	21.1	B2/2500		
BH (60°-80°)	1208.1	14.8	B3/2500		G1/1800
BVH (80°-90°)	135.6	1.7			G2/225
UL (90°-100°)	18.1	0.2		U2/50	
UH (100°-180°)	793.4	9.7		U4/1000	

**BUG Rating: B3-U4-G2**

Type V Short





REPORT NUMBER: P833955

CATALOG NUMBER: TTN-D3-750-U-MQ-UPL3

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1552.1	1552.1	1552.1	1552.1	1552.1	1552.1	1552.1	1552.1	1552.1	1552.1	1552.1
2.5°	1546.3	1546.3	1546.3	1540.5	1546.3	1546.3	1546.3	1546.3	1546.3	1546.3	1546.3
5°	1534.7	1534.7	1534.7	1534.7	1534.7	1534.7	1534.7	1534.7	1534.7	1534.7	1534.7
7.5°	1517.3	1517.3	1517.3	1517.3	1517.3	1517.3	1517.3	1517.3	1517.3	1517.3	1517.3
10°	1494.2	1494.2	1494.2	1494.2	1499.9	1499.9	1499.9	1499.9	1494.2	1494.2	1494.2
12.5°	1476.8	1476.8	1476.8	1482.6	1482.6	1482.6	1482.6	1482.6	1482.6	1482.6	1476.8
15°	1471.0	1471.0	1471.0	1471.0	1476.8	1476.8	1476.8	1476.8	1471.0	1471.0	1471.0
17.5°	1459.4	1459.4	1459.4	1465.2	1465.2	1465.2	1465.2	1465.2	1459.4	1459.4	1459.4
20°	1447.8	1447.8	1453.6	1453.6	1459.4	1459.4	1459.4	1453.6	1453.6	1447.8	1453.6
22.5°	1447.8	1447.8	1447.8	1453.6	1453.6	1453.6	1453.6	1447.8	1447.8	1447.8	1447.8
25°	1447.8	1447.8	1453.6	1459.4	1459.4	1465.2	1459.4	1453.6	1447.8	1447.8	1447.8
27.5°	1453.6	1453.6	1459.4	1465.2	1465.2	1471.0	1465.2	1459.4	1453.6	1453.6	1453.6
30°	1453.6	1453.6	1459.4	1465.2	1465.2	1471.0	1465.2	1459.4	1453.6	1453.6	1453.6
32.5°	1442.0	1447.8	1453.6	1459.4	1465.2	1465.2	1465.2	1459.4	1453.6	1447.8	1447.8
35°	1436.2	1442.0	1447.8	1453.6	1459.4	1459.4	1459.4	1453.6	1447.8	1442.0	1442.0
37.5°	1430.4	1430.4	1442.0	1447.8	1453.6	1465.2	1459.4	1447.8	1442.0	1436.2	1436.2
40°	1424.7	1430.4	1436.2	1447.8	1453.6	1465.2	1459.4	1447.8	1436.2	1430.4	1430.4
42.5°	1424.7	1424.7	1436.2	1447.8	1459.4	1471.0	1465.2	1453.6	1436.2	1430.4	1424.7
45°	1430.4	1436.2	1453.6	1476.8	1488.4	1499.9	1494.2	1476.8	1447.8	1436.2	1430.4
47.5°	1453.6	1459.4	1476.8	1499.9	1528.9	1546.3	1528.9	1499.9	1476.8	1459.4	1453.6
50°	1465.2	1471.0	1499.9	1528.9	1569.4	1575.2	1569.4	1528.9	1499.9	1471.0	1471.0
52.5°	1488.4	1488.4	1523.1	1575.2	1610.0	1621.6	1610.0	1581.0	1523.1	1494.2	1488.4
55°	1494.2	1494.2	1534.7	1598.4	1650.5	1679.5	1650.5	1604.2	1540.5	1499.9	1499.9
57.5°	1459.4	1471.0	1523.1	1586.8	1650.5	1667.9	1650.5	1592.6	1528.9	1476.8	1471.0
60°	1418.9	1436.2	1482.6	1557.9	1604.2	1621.6	1610.0	1557.9	1488.4	1436.2	1430.4
62.5°	1378.3	1401.5	1453.6	1511.5	1581.0	1598.4	1581.0	1511.5	1453.6	1401.5	1378.3
65°	1291.5	1314.6	1389.9	1459.4	1523.1	1534.7	1528.9	1459.4	1389.9	1314.6	1303.0
67.5°	1204.6	1222.0	1274.1	1384.1	1436.2	1453.6	1442.0	1378.3	1279.9	1222.0	1216.2
70°	1111.9	1129.3	1175.6	1279.9	1332.0	1361.0	1337.8	1279.9	1175.6	1129.3	1123.5
72.5°	990.3	1013.5	1065.6	1158.3	1210.4	1239.3	1216.2	1158.3	1065.6	1007.7	996.1
75°	845.5	862.9	926.6	1001.9	1054.0	1077.2	1059.8	1007.7	926.6	862.9	857.1
77.5°	689.2	706.5	764.4	839.7	868.7	891.9	874.5	833.9	764.4	706.5	700.7
80°	521.2	538.6	590.7	648.6	677.6	700.7	683.4	642.8	590.7	538.6	532.8
82.5°	341.7	359.1	405.4	451.7	480.7	503.8	486.5	445.9	411.2	359.1	353.3
85°	144.8	162.2	202.7	249.0	272.2	295.4	278.0	243.2	202.7	167.9	162.2
87.5°	11.6	17.4	17.4	23.2	17.4	29.0	17.4	17.4	17.4	17.4	17.4
90°	6.9	6.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	6.9	6.9
92.5°	6.9	6.9	6.9	9.7	11.1	9.7	11.1	8.3	8.3	6.9	6.9
95°	8.3	8.3	9.7	12.5	15.3	16.7	16.7	9.7	9.7	8.3	8.3
97.5°	11.1	12.5	12.5	15.3	25.0	45.8	27.8	13.9	13.9	12.5	11.1
100°	18.0	19.4	19.4	34.7	73.6	98.6	70.8	36.1	26.4	19.4	19.4
102.5°	58.3	61.1	75.0	112.5	166.6	151.3	127.7	120.8	83.3	66.6	63.9
105°	148.6	147.2	158.3	187.4	233.3	229.1	211.0	191.6	165.2	152.7	152.7
107.5°	195.8	195.8	205.5	230.5	265.2	309.6	313.8	248.5	218.0	204.1	202.7
110°	220.8	220.8	229.1	249.9	295.7	358.2	355.4	306.8	269.4	251.3	248.5



REPORT NUMBER: P833955  
 CATALOG NUMBER: TTN-D3-750-U-MQ-UPL3

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	226.3	227.7	238.8	270.7	320.7	348.5	336.0	316.6	299.9	286.0	283.2
115°	234.6	234.6	247.1	277.7	305.5	316.6	302.7	287.4	276.3	270.7	273.5
117.5°	231.9	236.0	238.8	255.5	273.5	281.8	274.9	254.1	245.8	243.0	238.8
120°	215.2	215.2	218.0	226.3	236.0	240.2	237.4	223.5	216.6	215.2	212.4
122.5°	191.6	193.0	191.6	195.8	202.7	206.9	204.1	193.0	190.2	190.2	187.4
125°	168.0	168.0	166.6	169.4	173.6	172.2	173.6	168.0	166.6	166.6	165.2
127.5°	151.3	149.9	147.2	148.6	149.9	149.9	151.3	145.8	147.2	148.6	147.2
130°	134.7	134.7	131.9	131.9	131.9	129.1	131.9	129.1	130.5	131.9	133.3
132.5°	119.4	119.4	115.2	113.9	113.9	113.9	115.2	113.9	116.6	119.4	119.4
135°	106.9	106.9	102.7	104.1	104.1	102.7	104.1	102.7	105.5	106.9	106.9
137.5°	97.2	97.2	94.4	94.4	94.4	93.0	94.4	94.4	95.8	98.6	100.0
140°	88.9	88.9	87.5	87.5	86.1	87.5	87.5	87.5	88.9	90.2	90.2
142.5°	84.7	83.3	81.9	80.5	81.9	81.9	81.9	80.5	81.9	84.7	84.7
145°	77.8	77.8	76.4	76.4	76.4	77.8	76.4	76.4	77.8	77.8	79.1
147.5°	73.6	73.6	72.2	73.6	73.6	73.6	73.6	72.2	73.6	73.6	75.0
150°	72.2	70.8	69.4	70.8	70.8	69.4	69.4	69.4	69.4	70.8	70.8
152.5°	68.0	68.0	66.6	68.0	66.6	66.6	66.6	66.6	66.6	68.0	69.4
155°	65.3	65.3	63.9	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
157.5°	62.5	63.9	62.5	62.5	62.5	62.5	62.5	62.5	62.5	63.9	63.9
160°	61.1	61.1	61.1	61.1	59.7	59.7	59.7	61.1	61.1	61.1	62.5
162.5°	59.7	59.7	59.7	59.7	58.3	58.3	58.3	58.3	59.7	59.7	61.1
165°	59.7	58.3	58.3	58.3	56.9	56.9	56.9	56.9	58.3	59.7	58.3
167.5°	56.9	56.9	56.9	56.9	56.9	55.5	55.5	56.9	56.9	56.9	58.3
170°	56.9	56.9	55.5	55.5	55.5	55.5	55.5	55.5	55.5	55.5	56.9
172.5°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	55.5	55.5	56.9	56.9
175°	56.9	56.9	56.9	56.9	55.5	55.5	55.5	56.9	56.9	56.9	55.5
177.5°	56.9	56.9	56.9	56.9	55.5	56.9	56.9	56.9	56.9	56.9	56.9
180°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9

(END OF REPORT)