

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640415

Luminaire Tested: GWS-SA5D-827-U-T2-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5D-827-U-T2-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS WITH HOUSE SIDE SHIELD
Light Source: (80) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16541.9 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 204.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640415
 CATALOG NUMBER: GWS-SA5D-827-U-T2-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5 fc
 Type II - Short - N/A

REPORT NUMBER: P640415
CATALOG NUMBER: GWS-SA5D-827-U-T2-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 68-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P640415
 CATALOG NUMBER: GWS-SA5D-827-U-T2-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1194.5 | 0.0 | 1194.5 |
| | % Fixture | 7.2 | 0.0 | 7.2 |
| Street Side | Lumens | 15347.4 | 0.0 | 15347.4 |
| | % Fixture | 92.8 | 0.0 | 92.8 |
| Total | Lumens | 16541.9 | 0.0 | 16541.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 187.7 | 1.1 |
| 10°-20° | 539.2 | 3.3 |
| 20°-30° | 926.5 | 5.6 |
| 30°-40° | 1610.9 | 9.7 |
| 40°-50° | 2810.9 | 17.0 |
| 50°-60° | 4239.6 | 25.6 |
| 60°-70° | 4251.2 | 25.7 |
| 70°-80° | 1875.6 | 11.3 |
| 80°-90° | 100.2 | 0.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 16541.9 | 100.0 |
| 0°-180° | 16541.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P640415
 CATALOG NUMBER: GWS-SA5D-827-U-T2-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1304.0 | 7.9 | | | |
| FM (30°-60°) | 8194.8 | 49.5 | | | |
| FH (60°-80°) | 5754.0 | 34.8 | | | G3/7500 |
| FVH (80°-90°) | 94.5 | 0.6 | | | G1/100 |
| BL (0°-30°) | 349.5 | 2.1 | B1/500 | | |
| BM (30°-60°) | 466.6 | 2.8 | B1/1000 | | |
| BH (60°-80°) | 372.8 | 2.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 5.7 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G3
 Type II Short





REPORT NUMBER: P640415

CATALOG NUMBER: GWS-SA5D-827-U-T2-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 68° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|
| 0° | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 |
| 2.5° | 2241.7 | 2255.9 | 2241.7 | 2244.8 | 2203.7 | 2184.7 | 2143.5 | 2086.5 | 2072.3 | 2035.9 | 1980.5 |
| 5° | 2515.6 | 2528.2 | 2514.0 | 2510.8 | 2463.3 | 2428.5 | 2360.4 | 2262.3 | 2233.8 | 2162.5 | 2053.3 |
| 7.5° | 2664.4 | 2672.3 | 2677.0 | 2684.9 | 2667.5 | 2639.0 | 2577.3 | 2455.4 | 2425.3 | 2309.8 | 2156.2 |
| 10° | 2680.2 | 2686.5 | 2710.3 | 2757.8 | 2792.6 | 2810.0 | 2775.2 | 2662.8 | 2615.3 | 2502.9 | 2282.8 |
| 12.5° | 2635.9 | 2645.4 | 2683.4 | 2762.5 | 2859.1 | 2947.7 | 2969.9 | 2871.8 | 2829.0 | 2684.9 | 2431.7 |
| 15° | 2577.3 | 2585.2 | 2637.5 | 2745.1 | 2890.8 | 3053.8 | 3145.6 | 3102.9 | 3055.4 | 2905.0 | 2596.3 |
| 17.5° | 2487.1 | 2498.1 | 2571.0 | 2716.6 | 2905.0 | 3137.7 | 3335.6 | 3349.9 | 3316.6 | 3153.5 | 2778.4 |
| 20° | 2436.4 | 2444.3 | 2509.2 | 2659.6 | 2895.5 | 3199.5 | 3512.9 | 3647.5 | 3611.1 | 3440.1 | 2987.3 |
| 22.5° | 2479.1 | 2485.5 | 2528.2 | 2645.4 | 2863.8 | 3234.3 | 3677.6 | 3945.1 | 3924.5 | 3747.2 | 3207.4 |
| 25° | 2703.9 | 2724.5 | 2699.2 | 2719.8 | 2878.1 | 3253.3 | 3810.5 | 4242.7 | 4247.5 | 4068.6 | 3435.3 |
| 27.5° | 3159.9 | 3133.0 | 3072.8 | 2969.9 | 2988.9 | 3303.9 | 3924.5 | 4522.9 | 4564.1 | 4382.0 | 3638.0 |
| 30° | 3623.7 | 3607.9 | 3571.5 | 3411.6 | 3278.6 | 3416.3 | 4021.1 | 4809.5 | 4874.4 | 4690.7 | 3818.5 |
| 32.5° | 4144.6 | 4160.4 | 4095.5 | 3903.9 | 3677.6 | 3644.3 | 4120.8 | 5081.8 | 5203.7 | 5040.6 | 4030.6 |
| 35° | 4766.7 | 4771.5 | 4643.2 | 4431.1 | 4174.6 | 4021.1 | 4299.7 | 5382.6 | 5607.4 | 5487.0 | 4314.0 |
| 37.5° | 5373.1 | 5401.6 | 5331.9 | 4997.9 | 4769.9 | 4489.7 | 4595.8 | 5768.8 | 6085.5 | 6038.0 | 4670.2 |
| 40° | 5909.7 | 5954.1 | 5931.9 | 5608.9 | 5309.7 | 5073.9 | 5054.9 | 6221.6 | 6663.3 | 6717.1 | 5140.3 |
| 42.5° | 6337.2 | 6365.7 | 6383.1 | 6153.5 | 5889.2 | 5756.2 | 5621.6 | 6747.2 | 7345.6 | 7565.7 | 5716.6 |
| 45° | 6788.4 | 6797.9 | 6834.3 | 6679.1 | 6448.0 | 6459.1 | 6291.3 | 7385.2 | 8064.3 | 8506.0 | 6378.3 |
| 47.5° | 7363.0 | 7394.7 | 7377.3 | 7214.2 | 7005.2 | 7130.3 | 6983.1 | 8042.2 | 8773.6 | 9509.7 | 7055.9 |
| 50° | 8062.8 | 8096.0 | 8080.2 | 7890.2 | 7657.5 | 7709.7 | 7617.9 | 8680.2 | 9457.5 | 10456.4 | 7619.5 |
| 52.5° | 8423.7 | 8450.6 | 8646.9 | 8732.4 | 8610.5 | 8278.1 | 8159.3 | 9381.5 | 10035.3 | 11235.3 | 8137.2 |
| 55° | 8249.6 | 8268.6 | 8696.0 | 9056.9 | 9503.4 | 9170.9 | 8703.9 | 9922.9 | 10545.1 | 11843.2 | 8521.9 |
| 57.5° | 7527.7 | 7630.6 | 8211.6 | 8822.6 | 9761.4 | 10052.7 | 9587.3 | 10511.8 | 11035.8 | 12265.9 | 8900.2 |
| 60° | 6047.5 | 6042.7 | 6875.4 | 7972.5 | 9258.0 | 10294.9 | 10834.8 | 11308.1 | 11528.2 | 12590.4 | 9406.8 |
| 62.5° | 3341.9 | 3372.0 | 4480.2 | 5925.6 | 7858.5 | 9668.0 | 11770.4 | 12683.8 | 12650.6 | 13157.2 | 10200.0 |
| 65° | 1663.8 | 1724.0 | 2325.6 | 3394.2 | 5229.0 | 7989.9 | 11931.9 | 14783.0 | 14688.1 | 14491.7 | 11838.5 |
| 67.5° | 1055.9 | 1079.7 | 1412.1 | 1972.5 | 2906.6 | 5135.6 | 10926.6 | 16348.7 | 16568.8 | 16074.9 | 13464.3 |
| 70° | 683.9 | 723.5 | 981.5 | 1348.8 | 1754.1 | 2647.0 | 8004.2 | 15334.0 | 15839.0 | 15900.7 | 12451.1 |
| 72.5° | 372.0 | 400.5 | 626.9 | 962.5 | 1266.5 | 1323.5 | 4496.0 | 11507.6 | 12319.7 | 13488.1 | 9740.8 |
| 75° | 212.1 | 232.7 | 343.5 | 653.8 | 929.3 | 805.8 | 1993.1 | 7703.4 | 8221.1 | 9639.5 | 6979.9 |
| 77.5° | 128.2 | 145.6 | 193.1 | 318.2 | 582.6 | 538.3 | 753.6 | 4689.2 | 5018.4 | 5751.4 | 3663.3 |
| 80° | 58.6 | 69.7 | 121.9 | 175.7 | 318.2 | 254.9 | 288.1 | 2186.3 | 2257.5 | 2360.4 | 1212.7 |
| 82.5° | 26.9 | 31.7 | 55.4 | 104.5 | 180.5 | 147.2 | 110.8 | 505.0 | 710.8 | 672.8 | 308.7 |
| 85° | 3.2 | 3.2 | 20.6 | 42.7 | 50.7 | 38.0 | 45.9 | 114.0 | 144.1 | 202.6 | 88.7 |
| 87.5° | 0.0 | 0.0 | 1.6 | 1.6 | 3.2 | 4.7 | 9.5 | 14.2 | 20.6 | 33.2 | 22.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640415

CATALOG NUMBER: GWS-SA5D-827-U-T2-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 | 1925.1 |
| 2.5° | 1955.1 | 1910.8 | 1871.2 | 1812.7 | 1773.1 | 1728.8 | 1698.7 | 1662.3 | 1648.0 | 1636.9 | 1621.1 |
| 5° | 1999.5 | 1928.2 | 1831.7 | 1724.0 | 1635.3 | 1551.4 | 1473.9 | 1423.2 | 1378.9 | 1372.6 | 1350.4 |
| 7.5° | 2072.3 | 1966.2 | 1803.2 | 1627.4 | 1477.0 | 1337.7 | 1228.5 | 1139.8 | 1095.5 | 1081.3 | 1055.9 |
| 10° | 2168.9 | 2023.2 | 1760.4 | 1491.3 | 1274.4 | 1108.2 | 984.7 | 885.0 | 815.3 | 790.0 | 771.0 |
| 12.5° | 2276.5 | 2075.5 | 1692.3 | 1323.5 | 1076.5 | 886.5 | 729.8 | 623.7 | 579.4 | 563.6 | 549.3 |
| 15° | 2400.0 | 2124.5 | 1584.7 | 1155.7 | 883.4 | 652.2 | 541.4 | 495.5 | 476.5 | 471.8 | 467.0 |
| 17.5° | 2518.7 | 2156.2 | 1456.5 | 981.5 | 679.2 | 506.6 | 454.4 | 436.9 | 432.2 | 427.4 | 424.3 |
| 20° | 2653.3 | 2178.4 | 1306.1 | 816.9 | 527.2 | 429.0 | 403.7 | 391.0 | 381.5 | 372.0 | 370.4 |
| 22.5° | 2791.0 | 2178.4 | 1143.0 | 655.4 | 441.7 | 384.7 | 356.2 | 332.5 | 315.0 | 305.5 | 302.4 |
| 25° | 2922.4 | 2148.3 | 981.5 | 524.0 | 389.4 | 342.0 | 305.5 | 278.6 | 254.9 | 243.8 | 240.6 |
| 27.5° | 3015.8 | 2070.7 | 840.6 | 443.3 | 353.0 | 304.0 | 259.6 | 229.6 | 210.6 | 199.5 | 197.9 |
| 30° | 3074.4 | 1955.1 | 710.8 | 395.8 | 321.4 | 264.4 | 220.1 | 194.7 | 180.5 | 172.6 | 169.4 |
| 32.5° | 3118.7 | 1812.7 | 595.2 | 362.5 | 291.3 | 229.6 | 191.6 | 171.0 | 158.3 | 152.0 | 150.4 |
| 35° | 3207.4 | 1678.1 | 509.8 | 332.5 | 259.6 | 201.1 | 167.8 | 152.0 | 142.5 | 134.6 | 133.0 |
| 37.5° | 3330.9 | 1565.7 | 441.7 | 305.5 | 229.6 | 178.9 | 152.0 | 137.7 | 129.8 | 121.9 | 120.3 |
| 40° | 3512.9 | 1494.5 | 391.0 | 278.6 | 202.6 | 161.5 | 139.3 | 126.6 | 115.6 | 107.7 | 106.1 |
| 42.5° | 3793.1 | 1461.2 | 357.8 | 251.7 | 178.9 | 145.6 | 128.2 | 112.4 | 101.3 | 93.4 | 91.8 |
| 45° | 4127.2 | 1478.6 | 329.3 | 224.8 | 163.1 | 134.6 | 114.0 | 98.2 | 87.1 | 79.2 | 77.6 |
| 47.5° | 4484.9 | 1540.4 | 305.5 | 199.5 | 147.2 | 123.5 | 101.3 | 83.9 | 74.4 | 66.5 | 64.9 |
| 50° | 4858.6 | 1641.7 | 285.0 | 175.7 | 134.6 | 110.8 | 87.1 | 72.8 | 63.3 | 57.0 | 55.4 |
| 52.5° | 5183.1 | 1779.4 | 264.4 | 158.3 | 123.5 | 98.2 | 76.0 | 63.3 | 53.8 | 47.5 | 45.9 |
| 55° | 5493.4 | 1909.2 | 248.5 | 142.5 | 110.8 | 85.5 | 66.5 | 53.8 | 45.9 | 39.6 | 38.0 |
| 57.5° | 5830.6 | 2047.0 | 229.6 | 128.2 | 99.7 | 76.0 | 58.6 | 45.9 | 39.6 | 33.2 | 31.7 |
| 60° | 6321.3 | 2251.2 | 201.1 | 117.1 | 87.1 | 66.5 | 50.7 | 41.2 | 34.8 | 26.9 | 25.3 |
| 62.5° | 7029.0 | 2623.2 | 169.4 | 101.3 | 74.4 | 57.0 | 42.7 | 34.8 | 28.5 | 22.2 | 19.0 |
| 65° | 8352.5 | 3256.4 | 139.3 | 83.9 | 60.2 | 47.5 | 36.4 | 28.5 | 22.2 | 15.8 | 14.2 |
| 67.5° | 9305.5 | 3421.1 | 112.4 | 68.1 | 49.1 | 36.4 | 30.1 | 22.2 | 15.8 | 11.1 | 9.5 |
| 70° | 8135.6 | 2457.0 | 87.1 | 55.4 | 41.2 | 28.5 | 23.7 | 17.4 | 11.1 | 7.9 | 6.3 |
| 72.5° | 6129.8 | 1605.3 | 64.9 | 42.7 | 31.7 | 23.7 | 17.4 | 14.2 | 9.5 | 6.3 | 4.7 |
| 75° | 4320.3 | 927.7 | 47.5 | 31.7 | 22.2 | 17.4 | 14.2 | 11.1 | 7.9 | 4.7 | 4.7 |
| 77.5° | 2214.8 | 383.1 | 33.2 | 22.2 | 15.8 | 11.1 | 9.5 | 6.3 | 6.3 | 4.7 | 3.2 |
| 80° | 672.8 | 126.6 | 19.0 | 14.2 | 11.1 | 7.9 | 4.7 | 4.7 | 4.7 | 3.2 | 1.6 |
| 82.5° | 153.6 | 41.2 | 11.1 | 11.1 | 7.9 | 6.3 | 4.7 | 1.6 | 1.6 | 0.0 | 0.0 |
| 85° | 39.6 | 12.7 | 9.5 | 7.9 | 7.9 | 6.3 | 3.2 | 1.6 | 0.0 | 0.0 | 0.0 |
| 87.5° | 14.2 | 7.9 | 7.9 | 7.9 | 6.3 | 4.7 | 3.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 $CIE R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)