

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636028

Luminaire Tested: GWS-SA3E-830-U-T3R-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P636028  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA3E-830-U-T3R-W  
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS  
Light Source: (48) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17759.7 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B2 - U0 - G3  
  
Input Watts (W): 159.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P636028

CATALOG NUMBER: GWS-SA3E-830-U-T3R-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P636028  
CATALOG NUMBER: GWS-SA3E-830-U-T3R-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P636028

CATALOG NUMBER: GWS-SA3E-830-U-T3R-W

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	3414.3	0.0	3414.3
	% Fixture	19.2	0.0	19.2
<b>Street Side</b>	Lumens	14345.4	0.0	14345.4
	% Fixture	80.8	0.0	80.8
<b>Total</b>	Lumens	17759.7	0.0	17759.7
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	265.3	1.5
10°-20°	718.8	4.0
20°-30°	1188.3	6.7
30°-40°	1776.7	10.0
40°-50°	2644.0	14.9
50°-60°	3759.0	21.2
60°-70°	4655.7	26.2
70°-80°	2570.7	14.5
80°-90°	181.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17759.7	100.0
0°-180°	17759.7	100.0

**Coefficient of Utilization**




REPORT NUMBER: P636028

CATALOG NUMBER: GWS-SA3E-830-U-T3R-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1248.1	7.0			
FM (30°-60°)	6652.5	37.5			
FH (60°-80°)	6318.9	35.6			G3/7500
FVH (80°-90°)	125.8	0.7			G2/225
BL (0°-30°)	924.3	5.2	B2/1000		
BM (30°-60°)	1527.3	8.6	B2/2500		
BH (60°-80°)	907.5	5.1	B2/1000		G2/1000
BVH (80°-90°)	55.2	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**  
 Type III Medium





REPORT NUMBER: P636028  
 CATALOG NUMBER: GWS-SA3E-830-U-T3R-W

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	56°	65°	75°	85°
0°	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7
2.5°	2682.6	2667.6	2685.1	2693.9	2716.4	2749.0	2777.8	2779.0	2794.1	2830.4	2865.4
5°	2561.1	2553.6	2558.6	2584.9	2608.7	2650.0	2693.9	2697.6	2740.2	2811.6	2881.7
7.5°	2467.2	2457.2	2475.9	2509.8	2539.8	2586.2	2643.8	2648.8	2708.9	2816.6	2924.3
10°	2331.9	2324.4	2359.5	2404.6	2469.7	2546.1	2622.5	2628.7	2707.6	2849.2	2999.4
12.5°	2273.1	2273.1	2288.1	2330.7	2402.1	2503.5	2618.7	2628.7	2727.7	2899.3	3095.9
15°	2364.5	2370.7	2358.2	2355.7	2384.5	2481.0	2623.7	2638.8	2765.2	2950.6	3191.1
17.5°	2548.6	2554.8	2522.3	2470.9	2442.1	2502.2	2642.5	2658.8	2805.3	3007.0	3293.7
20°	2806.6	2814.1	2742.7	2663.8	2564.9	2563.6	2678.8	2693.9	2856.7	3068.3	3402.7
22.5°	3108.4	3113.4	3023.2	2898.0	2746.5	2677.6	2741.5	2756.5	2923.0	3153.5	3520.4
25°	3457.8	3472.8	3363.9	3182.3	2976.9	2834.1	2845.4	2862.9	3042.0	3267.4	3659.4
27.5°	3831.0	3849.8	3724.6	3524.2	3241.1	3007.0	2979.4	2994.4	3168.5	3337.6	3733.3
30°	4213.0	4226.8	4101.5	3872.3	3525.4	3202.3	3092.1	3100.9	3223.6	3371.4	3808.5
32.5°	4637.5	4626.3	4506.0	4241.8	3853.6	3436.5	3197.3	3194.8	3285.0	3439.0	3916.2
35°	5035.8	5052.1	4924.3	4632.5	4214.2	3725.8	3355.1	3345.1	3415.2	3549.2	4067.7
37.5°	5518.0	5513.0	5360.2	5044.6	4576.2	4002.6	3576.8	3559.3	3584.3	3720.8	4279.4
40°	5862.4	5897.4	5798.5	5504.2	4999.5	4343.2	3836.0	3797.2	3803.5	3932.5	4562.4
42.5°	6144.2	6176.7	6186.7	5998.9	5484.2	4764.0	4159.1	4120.3	4124.1	4306.9	4910.6
45°	6360.8	6404.7	6546.2	6491.1	6030.2	5250.0	4596.2	4556.1	4558.6	4761.5	5331.4
47.5°	6449.7	6497.3	6784.1	6915.6	6610.0	5831.1	5139.8	5080.9	5089.7	5313.8	5812.3
50°	6420.9	6484.8	6873.0	7242.5	7096.0	6422.2	5789.7	5748.4	5714.6	6040.2	6334.5
52.5°	6173.0	6243.1	6864.3	7450.4	7493.0	6980.7	6461.0	6437.2	6429.7	6811.7	6918.1
55°	5442.8	5560.5	6562.5	7505.5	7803.6	7506.7	7188.6	7148.6	7187.4	7638.2	7508.0
57.5°	5038.3	5126.0	5971.3	7444.1	8057.8	8007.7	7915.0	7918.8	7962.6	8536.2	8223.1
60°	4807.9	4910.6	5643.2	7276.3	8302.0	8616.3	8675.2	8675.2	8754.1	9504.3	8949.5
62.5°	4502.3	4606.2	5336.4	6953.2	8527.4	9332.7	9630.8	9627.0	9658.3	10542.5	9659.6
65°	3882.4	3978.8	4720.2	6443.5	8637.6	10121.7	10716.6	10705.3	10642.7	11466.8	10129.2
67.5°	2819.1	2910.5	3615.6	5474.1	8240.6	10757.9	11835.0	11840.0	11465.5	12049.1	10154.3
70°	1858.5	1921.1	2324.4	3555.5	6701.5	10483.6	12303.3	12318.4	11592.0	11685.9	9037.1
72.5°	1159.7	1203.5	1451.5	2120.3	3960.0	8298.2	11101.1	11142.4	10428.5	10269.5	7425.3
75°	770.2	800.3	965.6	1236.1	1832.2	4491.0	8438.5	8571.3	8358.4	8050.3	5173.6
77.5°	463.4	488.4	614.9	785.2	811.5	1754.6	4925.6	5268.7	5298.8	4203.0	2166.6
80°	211.7	240.5	339.4	448.4	432.1	611.2	1737.0	1817.2	2144.1	1335.0	683.8
82.5°	125.2	137.8	225.4	222.9	184.1	296.8	624.9	641.2	544.8	488.4	291.8
85°	50.1	58.9	95.2	83.9	67.6	96.4	235.4	246.7	236.7	212.9	107.7
87.5°	0.0	0.0	0.0	0.0	1.3	2.5	21.3	22.5	32.6	58.9	32.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P636028  
 CATALOG NUMBER: GWS-SA3E-830-U-T3R-W

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7	2866.7
2.5°	2888.0	2880.5	2918.0	2946.8	2959.4	2971.9	2960.6	2956.9	2956.9	2931.8	2919.3
5°	2919.3	2923.0	2974.4	2998.2	2998.2	2988.2	2958.1	2936.8	2929.3	2896.7	2888.0
7.5°	2978.2	2994.4	3042.0	3040.8	3005.7	2950.6	2875.5	2817.8	2765.2	2742.7	2728.9
10°	3074.6	3095.9	3128.4	3075.8	2978.2	2832.9	2673.8	2548.6	2473.4	2413.3	2413.3
12.5°	3184.8	3204.8	3198.6	3077.1	2875.5	2603.7	2374.5	2230.5	2125.3	2070.2	2070.2
15°	3295.0	3311.3	3243.7	3019.5	2661.3	2299.4	2048.9	1876.1	1784.6	1733.3	1733.3
17.5°	3406.5	3405.2	3262.4	2886.7	2382.0	1962.5	1717.0	1583.0	1551.7	1542.9	1541.7
20°	3514.2	3485.4	3238.6	2665.1	2057.7	1623.1	1467.8	1476.6	1522.9	1542.9	1545.4
22.5°	3635.6	3564.3	3168.5	2382.0	1689.5	1387.6	1397.7	1470.3	1537.9	1568.0	1571.7
25°	3759.6	3631.9	3050.8	2050.1	1381.4	1301.2	1378.9	1460.3	1536.7	1575.5	1579.2
27.5°	3809.7	3631.9	2850.4	1665.7	1217.3	1264.9	1350.1	1429.0	1509.1	1554.2	1563.0
30°	3851.1	3600.6	2569.9	1318.8	1149.7	1229.8	1303.7	1376.4	1455.3	1510.4	1520.4
32.5°	3908.7	3573.0	2230.5	1108.4	1118.4	1196.0	1247.4	1308.7	1380.1	1416.4	1412.7
35°	3976.3	3530.4	1821.0	1008.2	1092.1	1167.2	1203.5	1239.9	1207.3	1206.0	1209.8
37.5°	4072.7	3492.9	1464.0	963.1	1074.5	1147.2	1177.2	1099.6	1054.5	1035.7	1028.2
40°	4211.7	3477.8	1154.7	936.8	1072.0	1145.9	1124.6	1004.4	943.0	877.9	876.7
42.5°	4387.1	3466.6	954.3	924.3	1080.8	1174.7	1052.0	941.8	815.3	786.5	784.0
45°	4612.5	3449.0	854.1	921.7	1102.1	1197.3	1044.5	855.4	769.0	756.4	756.4
47.5°	4884.3	3421.5	809.0	921.7	1125.9	1187.3	1021.9	836.6	747.7	761.4	770.2
50°	5196.1	3386.4	785.2	919.2	1149.7	1187.3	974.3	832.8	742.7	814.0	842.8
52.5°	5529.2	3346.3	769.0	909.2	1166.0	1188.5	976.9	845.4	747.7	826.6	850.4
55°	5897.4	3340.1	746.4	887.9	1171.0	1155.9	983.1	872.9	755.2	748.9	750.2
57.5°	6362.1	3415.2	730.1	856.6	1150.9	1089.6	995.6	892.9	746.4	747.7	756.4
60°	6848.0	3556.7	743.9	826.6	1109.6	1026.9	1004.4	882.9	703.8	683.8	686.3
62.5°	7261.3	3664.5	755.2	812.8	1049.5	971.8	995.6	860.4	680.0	675.0	686.3
65°	7434.1	3575.5	727.6	784.0	961.8	904.2	976.9	831.6	660.0	641.2	642.5
67.5°	7242.5	3158.5	673.8	720.1	862.9	817.8	946.8	794.0	632.4	609.9	604.9
70°	6186.7	2320.7	581.1	618.7	742.7	716.4	900.5	745.2	588.6	572.3	561.1
72.5°	4985.7	1643.1	482.2	492.2	582.4	603.6	820.3	683.8	538.5	492.2	475.9
75°	3470.3	1032.0	402.0	392.0	420.8	460.9	640.0	567.3	464.6	415.8	400.8
77.5°	1492.8	529.8	314.3	309.3	280.5	319.4	490.9	473.4	389.5	333.1	324.4
80°	499.7	306.8	226.7	217.9	186.6	224.2	345.7	378.2	305.6	246.7	231.7
82.5°	250.5	177.8	144.0	130.2	125.2	141.5	204.1	235.4	211.7	170.3	144.0
85°	122.7	101.4	78.9	77.6	65.1	61.4	85.2	100.2	95.2	70.1	66.4
87.5°	45.1	40.1	25.0	20.0	12.5	8.8	5.0	5.0	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)