

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640976

Luminaire Tested: GWS-SA5E-830-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5E-830-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (80) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26145.8 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 269.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640976
 CATALOG NUMBER: GWS-SA5E-830-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.5 fc
 Type II - Short - N/A

REPORT NUMBER: P640976
CATALOG NUMBER: GWS-SA5E-830-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P640976

CATALOG NUMBER: GWS-SA5E-830-U-T3R-W-GRSWH


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7771.9	0.0	7771.9
	% Fixture	29.7	0.0	29.7
Street Side	Lumens	18373.9	0.0	18373.9
	% Fixture	70.3	0.0	70.3
Total	Lumens	26145.8	0.0	26145.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	600.1	2.3
10°-20°	1667.6	6.4
20°-30°	2826.6	10.8
30°-40°	4326.5	16.5
40°-50°	5769.0	22.1
50°-60°	6662.7	25.5
60°-70°	3462.2	13.2
70°-80°	736.0	2.8
80°-90°	95.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26145.8	100.0
0°-180°	26145.8	100.0

Coefficient of Utilization



REPORT NUMBER: P640976


CATALOG NUMBER: GWS-SA5E-830-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2887.1	11.0			
FM (30°-60°)	12634.4	48.3			
FH (60°-80°)	2819.2	10.8			G2/5000
FVH (80°-90°)	33.2	0.1			G1/100
BL (0°-30°)	2207.1	8.4	B3/2500		
BM (30°-60°)	4123.7	15.8	B3/5000		
BH (60°-80°)	1379.0	5.3	B3/2500		G3/2500
BVH (80°-90°)	62.1	0.2			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P640976

CATALOG NUMBER: GWS-SA5E-830-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5
2.5°	6184.5	6171.7	6176.0	6193.1	6257.2	6304.2	6353.4	6398.3	6441.1	6453.9	6464.6
5°	5964.3	5940.8	5947.2	5975.0	6049.8	6128.9	6216.6	6323.5	6426.1	6460.3	6505.2
7.5°	5808.3	5804.0	5814.7	5857.4	5936.5	6011.4	6124.7	6276.4	6453.9	6511.6	6590.7
10°	5600.9	5592.4	5635.1	5722.8	5853.2	5972.9	6107.6	6287.1	6535.1	6620.6	6742.5
12.5°	5436.3	5432.0	5476.9	5598.8	5765.5	5955.8	6141.8	6342.7	6644.1	6761.7	6911.4
15°	5532.5	5513.3	5515.4	5600.9	5750.6	5975.0	6227.3	6443.2	6753.2	6902.8	7095.2
17.5°	5812.6	5778.4	5752.7	5767.7	5853.2	6086.2	6357.7	6577.9	6879.3	7054.6	7289.7
20°	6199.5	6180.2	6109.7	6062.7	6081.9	6287.1	6562.9	6768.1	7043.9	7240.6	7492.8
22.5°	6719.0	6671.9	6575.7	6500.9	6443.2	6603.5	6857.9	7035.3	7272.6	7477.9	7740.8
25°	7362.4	7294.0	7142.2	7024.7	6900.7	7065.3	7291.9	7426.6	7586.9	7777.2	8027.3
27.5°	8018.7	7961.0	7792.1	7633.9	7480.0	7582.6	7852.0	7928.9	7911.8	8050.8	8264.6
30°	8717.8	8645.1	8484.7	8313.7	8114.9	8181.2	8422.8	8461.2	8279.5	8395.0	8540.3
32.5°	9455.3	9384.7	9245.8	9047.0	8822.5	8848.2	8914.4	8950.8	8777.6	8843.9	8955.1
35°	10205.6	10139.4	9998.3	9801.6	9637.0	9480.9	9314.2	9459.6	9359.1	9487.4	9478.8
37.5°	10891.9	10825.6	10737.9	10586.2	10304.0	9996.1	9611.3	9790.9	9947.0	10109.4	10081.6
40°	11355.8	11310.9	11332.2	11308.7	10945.3	10336.0	9756.7	9953.4	10378.8	10656.7	10641.7
42.5°	11755.5	11710.6	11834.6	11924.4	11496.8	10650.3	9827.3	10015.4	10654.6	11088.5	11067.2
45°	11932.9	11920.1	12125.3	12409.7	12001.4	10983.8	10009.0	10143.6	10864.1	11419.9	11338.6
47.5°	11721.3	11766.2	12170.2	12651.2	12420.4	11379.3	10380.9	10415.1	11137.7	11779.0	11550.3
50°	11300.2	11398.5	11943.6	12657.6	12726.1	11826.1	10896.1	10810.6	11505.4	12161.7	11661.5
52.5°	10686.6	10789.2	11678.6	12608.5	12901.3	12343.4	11582.4	11460.5	11969.3	12544.3	11680.7
55°	9277.9	9416.8	11071.4	12497.3	13072.4	12813.7	12356.2	12108.2	12567.9	13070.2	11871.0
57.5°	8048.6	8121.3	9592.1	12003.5	13106.6	13160.0	12907.8	12612.8	13162.2	13638.9	12084.7
60°	5906.6	5923.7	7247.0	9932.0	12056.9	12959.1	12862.9	12424.6	12880.0	13183.5	11105.6
62.5°	3337.0	3339.2	4395.2	6629.2	9006.4	10562.6	10622.5	10235.6	9852.9	9942.7	7730.1
65°	1252.7	1370.3	2007.4	3257.9	5192.6	6235.8	6483.8	6573.6	5936.5	5541.1	4145.1
67.5°	838.0	865.8	1171.5	1676.0	2310.9	2667.9	2984.3	2992.9	2189.1	1951.8	1633.2
70°	639.2	667.0	921.4	1199.3	1171.5	1081.7	1169.4	1137.3	1175.8	1207.8	1242.0
72.5°	476.7	504.5	714.0	846.6	703.3	692.6	784.6	872.2	953.4	987.6	1041.1
75°	316.4	337.8	481.0	453.2	389.1	459.6	572.9	660.6	707.6	748.2	788.8
77.5°	200.9	215.9	256.5	207.4	215.9	269.4	333.5	412.6	457.5	498.1	519.5
80°	91.9	89.8	87.6	98.3	121.9	158.2	200.9	248.0	282.2	299.3	312.1
82.5°	36.3	40.6	44.9	53.4	66.3	85.5	113.3	145.4	173.2	177.4	188.1
85°	15.0	17.1	19.2	23.5	29.9	38.5	47.0	66.3	83.4	89.8	96.2
87.5°	0.0	0.0	0.0	0.0	2.1	4.3	6.4	10.7	19.2	21.4	23.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P640976

CATALOG NUMBER: GWS-SA5E-830-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5	6479.5
2.5°	6522.3	6494.5	6541.5	6573.6	6603.5	6571.5	6560.8	6533.0	6528.7	6528.7	6543.7
5°	6582.1	6562.9	6612.1	6631.3	6629.2	6558.6	6515.9	6460.3	6432.5	6432.5	6436.8
7.5°	6689.0	6678.3	6706.1	6676.2	6607.8	6464.6	6323.5	6205.9	6126.8	6086.2	6099.0
10°	6866.5	6853.6	6830.1	6719.0	6522.3	6225.1	5936.5	5722.8	5594.5	5521.8	5526.1
12.5°	7039.6	7018.2	6934.9	6689.0	6285.0	5812.6	5434.2	5194.7	5053.7	4968.1	4948.9
15°	7229.9	7174.3	6994.7	6535.1	5898.1	5308.0	4912.6	4653.9	4502.1	4450.8	4448.7
17.5°	7411.6	7313.3	6988.3	6261.5	5434.2	4780.0	4382.4	4222.1	4196.4	4219.9	4226.3
20°	7595.4	7437.2	6917.8	5883.1	4882.6	4254.1	4048.9	4115.2	4211.4	4275.5	4290.5
22.5°	7785.7	7539.9	6757.4	5395.7	4301.2	3899.3	3984.8	4130.1	4249.9	4335.4	4343.9
25°	7999.5	7636.1	6518.0	4799.3	3835.1	3800.9	3969.8	4123.7	4252.0	4350.3	4367.4
27.5°	8121.3	7638.2	6182.4	4185.7	3621.4	3762.4	3933.5	4078.8	4207.1	4314.0	4333.2
30°	8241.0	7580.5	5650.1	3687.6	3559.4	3717.6	3871.5	4006.2	4128.0	4232.8	4256.3
32.5°	8409.9	7527.0	5036.5	3401.2	3523.0	3674.8	3800.9	3920.6	4014.7	4061.7	4074.6
35°	8619.4	7458.6	4384.5	3277.2	3499.5	3640.6	3751.8	3815.9	3694.0	3668.4	3696.2
37.5°	8912.3	7394.5	3734.7	3223.7	3484.5	3627.8	3726.1	3561.5	3411.9	3352.0	3373.4
40°	9228.7	7358.2	3294.3	3181.0	3491.0	3640.6	3619.2	3375.5	3159.6	3033.5	3029.2
42.5°	9498.0	7302.6	3012.1	3153.2	3508.1	3689.8	3473.9	3210.9	2890.2	2815.4	2817.6
45°	9679.8	7161.5	2862.5	3123.3	3523.0	3700.5	3405.4	2984.3	2755.6	2708.5	2706.4
47.5°	9754.6	6904.9	2766.3	3076.2	3520.9	3612.8	3266.5	2890.2	2661.5	2648.7	2657.2
50°	9705.4	6483.8	2667.9	2984.3	3469.6	3520.9	3106.2	2806.9	2597.4	2667.9	2719.2
52.5°	9523.7	5938.7	2550.3	2858.2	3377.7	3416.1	3024.9	2755.6	2550.3	2644.4	2685.0
55°	9476.7	5496.2	2400.7	2693.6	3240.8	3230.1	2939.4	2729.9	2518.3	2481.9	2488.3
57.5°	9414.7	5064.3	2152.7	2398.6	2894.5	2911.6	2858.2	2700.0	2434.9	2424.2	2434.9
60°	8179.0	3882.2	1919.7	2069.3	2377.2	2469.1	2766.3	2644.4	2300.2	2255.3	2253.2
62.5°	5342.2	2351.5	1708.1	1804.3	1936.8	2043.7	2522.6	2484.1	2152.7	2124.9	2144.2
65°	2873.1	1676.0	1554.1	1611.9	1684.6	1765.8	2090.7	2212.6	1945.4	1847.0	1849.2
67.5°	1468.6	1425.9	1438.7	1479.3	1534.9	1575.5	1686.7	1793.6	1658.9	1575.5	1573.4
70°	1257.0	1291.2	1310.4	1334.0	1370.3	1363.9	1374.6	1393.8	1383.1	1342.5	1340.4
72.5°	1071.0	1124.5	1128.7	1133.0	1145.8	1115.9	1096.7	1064.6	1066.7	1073.2	1075.3
75°	814.5	865.8	878.6	872.2	885.0	846.6	820.9	788.8	750.4	743.9	748.2
77.5°	530.2	570.8	590.0	585.7	592.2	562.2	549.4	515.2	470.3	453.2	453.2
80°	320.7	344.2	359.1	363.4	369.8	348.5	327.1	297.1	277.9	258.7	258.7
82.5°	194.5	209.5	220.2	220.2	226.6	203.1	186.0	164.6	156.1	139.0	139.0
85°	98.3	109.0	113.3	111.2	106.9	87.6	81.2	70.5	66.3	57.7	57.7
87.5°	23.5	29.9	29.9	21.4	21.4	10.7	6.4	2.1	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)