

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631524

Luminaire Tested: GWS-SA1F-830-U-5MQ-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P631524  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1F-830-U-5MQ-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V MEDIUM OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (16) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5860 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 67.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P631524  
 CATALOG NUMBER: GWS-SA1F-830-U-5MQ-W-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 11.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P631524  
CATALOG NUMBER: GWS-SA1F-830-U-5MQ-W-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 35-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P631524

CATALOG NUMBER: GWS-SA1F-830-U-5MQ-W-GRSWH

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2930.0   | 0.0    | 2930.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2930.0   | 0.0    | 2930.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 5860.0   | 0.0    | 5860.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 106.7  | 1.8       |
| 10°-20°   | 318.2  | 5.4       |
| 20°-30°   | 555.3  | 9.5       |
| 30°-40°   | 910.5  | 15.5      |
| 40°-50°   | 1341.0 | 22.9      |
| 50°-60°   | 1711.3 | 29.2      |
| 60°-70°   | 721.2  | 12.3      |
| 70°-80°   | 172.3  | 2.9       |
| 80°-90°   | 23.5   | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5860.0 | 100.0     |
| 0°-180°   | 5860.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P631524


CATALOG NUMBER: GWS-SA1F-830-U-5MQ-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 490.1  | 8.4       |                         |      |        |
| FM (30°-60°)   | 1981.4 | 33.8      |                         |      |        |
| FH (60°-80°)   | 446.8  | 7.6       |                         |      | G0/660 |
| FVH (80°-90°)  | 11.7   | 0.2       |                         |      | G1/100 |
| BL (0°-30°)    | 490.1  | 8.4       | B1/500                  |      |        |
| BM (30°-60°)   | 1981.4 | 33.8      | B2/2500                 |      |        |
| BH (60°-80°)   | 446.8  | 7.6       | B1/500                  |      | G0/660 |
| BVH (80°-90°)  | 11.7   | 0.2       |                         |      | G1/100 |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B2-U0-G1**

Type V Short





REPORT NUMBER: P631524

CATALOG NUMBER: GWS-SA1F-830-U-5MQ-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 | 1121.2 |
| 2.5°  | 1114.5 | 1114.5 | 1116.9 | 1119.3 | 1120.3 | 1124.6 | 1124.1 | 1122.7 | 1121.7 | 1118.8 | 1122.7 |
| 5°    | 1116.9 | 1116.9 | 1118.8 | 1120.3 | 1119.8 | 1123.2 | 1121.7 | 1119.3 | 1117.9 | 1115.0 | 1119.3 |
| 7.5°  | 1116.4 | 1116.4 | 1117.9 | 1119.3 | 1118.4 | 1121.2 | 1118.8 | 1115.5 | 1113.1 | 1110.2 | 1114.0 |
| 10°   | 1110.2 | 1111.2 | 1112.6 | 1116.0 | 1117.4 | 1121.7 | 1118.4 | 1113.1 | 1109.2 | 1105.9 | 1109.7 |
| 12.5° | 1109.2 | 1110.2 | 1112.1 | 1116.4 | 1118.8 | 1125.1 | 1120.8 | 1112.1 | 1106.4 | 1102.1 | 1105.9 |
| 15°   | 1113.6 | 1114.5 | 1117.4 | 1122.7 | 1126.5 | 1133.2 | 1127.0 | 1115.0 | 1106.9 | 1101.1 | 1104.5 |
| 17.5° | 1118.8 | 1120.3 | 1124.6 | 1132.3 | 1138.5 | 1145.7 | 1138.0 | 1123.6 | 1112.1 | 1104.5 | 1107.3 |
| 20°   | 1124.6 | 1126.5 | 1133.2 | 1144.8 | 1156.3 | 1165.4 | 1155.8 | 1136.6 | 1122.7 | 1112.6 | 1115.5 |
| 22.5° | 1134.7 | 1137.1 | 1145.7 | 1162.0 | 1179.3 | 1192.7 | 1180.7 | 1154.8 | 1136.6 | 1123.6 | 1126.0 |
| 25°   | 1155.3 | 1158.2 | 1169.2 | 1188.9 | 1213.4 | 1229.7 | 1212.9 | 1183.6 | 1158.2 | 1142.4 | 1144.8 |
| 27.5° | 1191.8 | 1193.2 | 1207.6 | 1233.5 | 1263.7 | 1282.4 | 1262.3 | 1227.8 | 1199.4 | 1181.2 | 1183.1 |
| 30°   | 1239.7 | 1244.1 | 1258.5 | 1292.5 | 1328.5 | 1353.5 | 1327.1 | 1286.3 | 1253.7 | 1231.6 | 1233.5 |
| 32.5° | 1298.3 | 1301.2 | 1322.8 | 1358.3 | 1410.1 | 1438.9 | 1402.9 | 1354.4 | 1315.1 | 1288.2 | 1290.1 |
| 35°   | 1375.0 | 1377.4 | 1398.1 | 1443.2 | 1506.0 | 1532.9 | 1491.6 | 1436.0 | 1390.4 | 1365.0 | 1372.2 |
| 37.5° | 1466.7 | 1471.0 | 1485.9 | 1530.5 | 1600.5 | 1626.9 | 1579.4 | 1527.6 | 1480.1 | 1456.6 | 1461.9 |
| 40°   | 1565.0 | 1564.6 | 1576.6 | 1615.9 | 1679.7 | 1696.0 | 1653.3 | 1612.1 | 1571.3 | 1555.9 | 1564.6 |
| 42.5° | 1649.5 | 1647.1 | 1655.7 | 1688.3 | 1732.5 | 1733.9 | 1705.6 | 1682.6 | 1653.8 | 1643.2 | 1651.4 |
| 45°   | 1708.5 | 1709.5 | 1722.4 | 1745.0 | 1767.5 | 1755.5 | 1746.9 | 1743.0 | 1720.5 | 1706.1 | 1707.5 |
| 47.5° | 1755.0 | 1758.9 | 1779.5 | 1794.9 | 1797.7 | 1777.6 | 1789.6 | 1795.3 | 1776.6 | 1754.6 | 1748.3 |
| 50°   | 1796.3 | 1802.5 | 1829.4 | 1845.7 | 1839.5 | 1814.0 | 1837.6 | 1846.2 | 1804.9 | 1762.7 | 1750.2 |
| 52.5° | 1871.1 | 1878.3 | 1911.0 | 1932.1 | 1924.9 | 1899.4 | 1921.5 | 1890.8 | 1821.2 | 1769.4 | 1753.6 |
| 55°   | 1990.6 | 1994.0 | 2033.8 | 2068.3 | 2065.0 | 2033.8 | 2016.0 | 1947.9 | 1863.5 | 1809.7 | 1794.9 |
| 57.5° | 1965.2 | 1970.9 | 2040.0 | 2132.1 | 2184.0 | 2155.6 | 2051.5 | 1935.4 | 1820.8 | 1756.0 | 1735.8 |
| 60°   | 1546.3 | 1560.2 | 1646.1 | 1808.3 | 1998.3 | 1997.8 | 1804.4 | 1624.1 | 1485.9 | 1400.0 | 1391.4 |
| 62.5° | 902.9  | 912.5  | 990.7  | 1154.8 | 1325.2 | 1335.7 | 1199.9 | 1076.1 | 955.2  | 897.2  | 869.4  |
| 65°   | 427.5  | 427.0  | 458.2  | 532.1  | 647.2  | 656.3  | 615.6  | 547.9  | 476.4  | 456.7  | 451.5  |
| 67.5° | 315.7  | 315.7  | 313.3  | 318.6  | 340.6  | 345.4  | 340.6  | 329.6  | 322.9  | 327.2  | 324.3  |
| 70°   | 274.0  | 274.4  | 271.6  | 270.1  | 270.1  | 268.7  | 270.6  | 274.9  | 277.8  | 283.5  | 280.7  |
| 72.5° | 222.1  | 222.6  | 222.6  | 223.1  | 223.6  | 221.7  | 224.5  | 226.9  | 227.4  | 229.3  | 227.4  |
| 75°   | 157.8  | 158.8  | 161.7  | 164.1  | 166.0  | 166.0  | 167.0  | 167.4  | 165.5  | 167.9  | 164.1  |
| 77.5° | 86.8   | 87.8   | 93.1   | 97.4   | 101.7  | 102.2  | 103.6  | 104.6  | 103.6  | 105.6  | 102.7  |
| 80°   | 48.0   | 48.9   | 51.3   | 53.3   | 56.6   | 59.5   | 61.4   | 62.4   | 62.4   | 63.8   | 62.4   |
| 82.5° | 27.3   | 28.3   | 29.7   | 30.7   | 33.6   | 36.0   | 37.9   | 39.3   | 39.3   | 39.8   | 38.9   |
| 85°   | 13.0   | 13.0   | 13.9   | 14.9   | 16.3   | 17.3   | 19.7   | 21.1   | 21.1   | 22.1   | 21.1   |
| 87.5° | 1.9    | 2.4    | 2.9    | 2.9    | 3.8    | 4.8    | 5.8    | 6.2    | 7.2    | 7.7    | 7.7    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2408-195-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 08/07/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: MCGRAW EDISON  
 Catalog Number: **GALN-SB1A-830-U-5WQ**  
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

**Spectral Parameters**

CCT (K): 3050  
 CIE u': 0.2476  
 CIE v': 0.5251  
 Duv: 0.0034  
 CIE x: 0.4383  
 CIE y: 0.4131  
 CIE z: 0.1487  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 581  
 Purity: 55.55201  
 Rf: 81.5  
 Rg: 99.2

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 81.0 |      |      |
| R1:       | 79.6 | R9:  | 7.1  |
| R2:       | 85.6 | R10: | 67.0 |
| R3:       | 92.0 | R11: | 82.7 |
| R4:       | 82.6 | R12: | 63.2 |
| R5:       | 78.9 | R13: | 80.3 |
| R6:       | 81.7 | R14: | 95.0 |
| R7:       | 85.2 | R15: | 71.7 |
| R8:       | 62.0 |      |      |



**Test Conditions**

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2408-195-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

| $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360               | 0                           | NR                      | 490               | 168                         | NR                      | 620               | 940                         | NR                      | 750               | 35                          | NR                      | 880               | 1                           | NR                      |
| 365               | 0                           | NR                      | 495               | 233                         | NR                      | 625               | 897                         | NR                      | 755               | 30                          | NR                      | 885               | 1                           | NR                      |
| 370               | 0                           | NR                      | 500               | 300                         | NR                      | 630               | 847                         | NR                      | 760               | 26                          | NR                      | 890               | 1                           | NR                      |
| 375               | 0                           | NR                      | 505               | 372                         | NR                      | 635               | 790                         | NR                      | 765               | 22                          | NR                      | 895               | 1                           | NR                      |
| 380               | 0                           | NR                      | 510               | 430                         | NR                      | 640               | 730                         | NR                      | 770               | 19                          | NR                      | 900               | 1                           | NR                      |
| 385               | 0                           | NR                      | 515               | 483                         | NR                      | 645               | 668                         | NR                      | 775               | 16                          | NR                      | 905               | 1                           | NR                      |
| 390               | 0                           | NR                      | 520               | 524                         | NR                      | 650               | 605                         | NR                      | 780               | 14                          | NR                      | 910               | 0                           | NR                      |
| 395               | 2                           | NR                      | 525               | 555                         | NR                      | 655               | 545                         | NR                      | 785               | 12                          | NR                      | 915               | 0                           | NR                      |
| 400               | 4                           | NR                      | 530               | 581                         | NR                      | 660               | 485                         | NR                      | 790               | 10                          | NR                      | 920               | 0                           | NR                      |
| 405               | 7                           | NR                      | 535               | 604                         | NR                      | 665               | 430                         | NR                      | 795               | 9                           | NR                      | 925               | 0                           | NR                      |
| 410               | 17                          | NR                      | 540               | 623                         | NR                      | 670               | 378                         | NR                      | 800               | 8                           | NR                      | 930               | 0                           | NR                      |
| 415               | 34                          | NR                      | 545               | 645                         | NR                      | 675               | 331                         | NR                      | 805               | 7                           | NR                      | 935               | 0                           | NR                      |
| 420               | 68                          | NR                      | 550               | 667                         | NR                      | 680               | 290                         | NR                      | 810               | 6                           | NR                      | 940               | 0                           | NR                      |
| 425               | 128                         | NR                      | 555               | 693                         | NR                      | 685               | 251                         | NR                      | 815               | 5                           | NR                      | 945               | 0                           | NR                      |
| 430               | 214                         | NR                      | 560               | 719                         | NR                      | 690               | 218                         | NR                      | 820               | 4                           | NR                      | 950               | 0                           | NR                      |
| 435               | 339                         | NR                      | 565               | 754                         | NR                      | 695               | 188                         | NR                      | 825               | 4                           | NR                      | 955               | 0                           | NR                      |
| 440               | 507                         | NR                      | 570               | 791                         | NR                      | 700               | 162                         | NR                      | 830               | 3                           | NR                      | 960               | 0                           | NR                      |
| 445               | 573                         | NR                      | 575               | 830                         | NR                      | 705               | 139                         | NR                      | 835               | 3                           | NR                      | 965               | 0                           | NR                      |
| 450               | 356                         | NR                      | 580               | 873                         | NR                      | 710               | 119                         | NR                      | 840               | 3                           | NR                      | 970               | 0                           | NR                      |
| 455               | 217                         | NR                      | 585               | 913                         | NR                      | 715               | 102                         | NR                      | 845               | 2                           | NR                      | 975               | 0                           | NR                      |
| 460               | 168                         | NR                      | 590               | 948                         | NR                      | 720               | 88                          | NR                      | 850               | 2                           | NR                      | 980               | 0                           | NR                      |
| 465               | 113                         | NR                      | 595               | 974                         | NR                      | 725               | 76                          | NR                      | 855               | 2                           | NR                      | 985               | 0                           | NR                      |
| 470               | 85                          | NR                      | 600               | 994                         | NR                      | 730               | 65                          | NR                      | 860               | 1                           | NR                      | 990               | 0                           | NR                      |
| 475               | 85                          | NR                      | 605               | 998                         | NR                      | 735               | 55                          | NR                      | 865               | 1                           | NR                      | 995               | 0                           | NR                      |
| 480               | 94                          | NR                      | 610               | 994                         | NR                      | 740               | 47                          | NR                      | 870               | 1                           | NR                      | 1000              | 0                           | NR                      |
| 485               | 120                         | NR                      | 615               | 973                         | NR                      | 745               | 41                          | NR                      | 875               | 1                           | NR                      |                   |                             |                         |

REPORT NUMBER: SP1-2408-195-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.27**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 168                      | NR            | 620    | 940                      | NR            | 750    | 35                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 233                      | NR            | 625    | 897                      | NR            | 755    | 30                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 300                      | NR            | 630    | 847                      | NR            | 760    | 26                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 372                      | NR            | 635    | 790                      | NR            | 765    | 22                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 430                      | NR            | 640    | 730                      | NR            | 770    | 19                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 483                      | NR            | 645    | 668                      | NR            | 775    | 16                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 524                      | NR            | 650    | 605                      | NR            | 780    | 14                       | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 555                      | NR            | 655    | 545                      | NR            | 785    | 12                       | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 581                      | NR            | 660    | 485                      | NR            | 790    | 10                       | NR            | 920    | 0                        | NR            |
| 405    | 7                        | NR            | 535    | 604                      | NR            | 665    | 430                      | NR            | 795    | 9                        | NR            | 925    | 0                        | NR            |
| 410    | 17                       | NR            | 540    | 623                      | NR            | 670    | 378                      | NR            | 800    | 8                        | NR            | 930    | 0                        | NR            |
| 415    | 34                       | NR            | 545    | 645                      | NR            | 675    | 331                      | NR            | 805    | 7                        | NR            | 935    | 0                        | NR            |
| 420    | 68                       | NR            | 550    | 667                      | NR            | 680    | 290                      | NR            | 810    | 6                        | NR            | 940    | 0                        | NR            |
| 425    | 128                      | NR            | 555    | 693                      | NR            | 685    | 251                      | NR            | 815    | 5                        | NR            | 945    | 0                        | NR            |
| 430    | 214                      | NR            | 560    | 719                      | NR            | 690    | 218                      | NR            | 820    | 4                        | NR            | 950    | 0                        | NR            |
| 435    | 339                      | NR            | 565    | 754                      | NR            | 695    | 188                      | NR            | 825    | 4                        | NR            | 955    | 0                        | NR            |
| 440    | 507                      | NR            | 570    | 791                      | NR            | 700    | 162                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 573                      | NR            | 575    | 830                      | NR            | 705    | 139                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 356                      | NR            | 580    | 873                      | NR            | 710    | 119                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 217                      | NR            | 585    | 913                      | NR            | 715    | 102                      | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 168                      | NR            | 590    | 948                      | NR            | 720    | 88                       | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 113                      | NR            | 595    | 974                      | NR            | 725    | 76                       | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 85                       | NR            | 600    | 994                      | NR            | 730    | 65                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 85                       | NR            | 605    | 998                      | NR            | 735    | 55                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 94                       | NR            | 610    | 994                      | NR            | 740    | 47                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 120                      | NR            | 615    | 973                      | NR            | 745    | 41                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2408-195-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 2.32**


| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 168                      | NR            | 620    | 940                      | NR            | 750    | 35                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 233                      | NR            | 625    | 897                      | NR            | 755    | 30                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 300                      | NR            | 630    | 847                      | NR            | 760    | 26                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 372                      | NR            | 635    | 790                      | NR            | 765    | 22                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 430                      | NR            | 640    | 730                      | NR            | 770    | 19                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 483                      | NR            | 645    | 668                      | NR            | 775    | 16                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 524                      | NR            | 650    | 605                      | NR            | 780    | 14                       | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 555                      | NR            | 655    | 545                      | NR            | 785    | 12                       | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 581                      | NR            | 660    | 485                      | NR            | 790    | 10                       | NR            | 920    | 0                        | NR            |
| 405    | 7                        | NR            | 535    | 604                      | NR            | 665    | 430                      | NR            | 795    | 9                        | NR            | 925    | 0                        | NR            |
| 410    | 17                       | NR            | 540    | 623                      | NR            | 670    | 378                      | NR            | 800    | 8                        | NR            | 930    | 0                        | NR            |
| 415    | 34                       | NR            | 545    | 645                      | NR            | 675    | 331                      | NR            | 805    | 7                        | NR            | 935    | 0                        | NR            |
| 420    | 68                       | NR            | 550    | 667                      | NR            | 680    | 290                      | NR            | 810    | 6                        | NR            | 940    | 0                        | NR            |
| 425    | 128                      | NR            | 555    | 693                      | NR            | 685    | 251                      | NR            | 815    | 5                        | NR            | 945    | 0                        | NR            |
| 430    | 214                      | NR            | 560    | 719                      | NR            | 690    | 218                      | NR            | 820    | 4                        | NR            | 950    | 0                        | NR            |
| 435    | 339                      | NR            | 565    | 754                      | NR            | 695    | 188                      | NR            | 825    | 4                        | NR            | 955    | 0                        | NR            |
| 440    | 507                      | NR            | 570    | 791                      | NR            | 700    | 162                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 573                      | NR            | 575    | 830                      | NR            | 705    | 139                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 356                      | NR            | 580    | 873                      | NR            | 710    | 119                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 217                      | NR            | 585    | 913                      | NR            | 715    | 102                      | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 168                      | NR            | 590    | 948                      | NR            | 720    | 88                       | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 113                      | NR            | 595    | 974                      | NR            | 725    | 76                       | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 85                       | NR            | 600    | 994                      | NR            | 730    | 65                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 85                       | NR            | 605    | 998                      | NR            | 735    | 55                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 94                       | NR            | 610    | 994                      | NR            | 740    | 47                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 120                      | NR            | 615    | 973                      | NR            | 745    | 41                       | NR            | 875    | 1                        | NR            |        |                          |               |

**Summary**

$R_f = 81.5$   
 $R_g = 99.2$   
 $CIE R_a = 81.0$   
 $R_9 = 7.1$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 74 | CES51 = 89 | CES76 = 70 |
| CES02 = 63 | CES27 = 88 | CES52 = 92 | CES77 = 86 |
| CES03 = 31 | CES28 = 89 | CES53 = 81 | CES78 = 72 |
| CES04 = 70 | CES29 = 67 | CES54 = 87 | CES79 = 90 |
| CES05 = 50 | CES30 = 68 | CES55 = 85 | CES80 = 88 |
| CES06 = 51 | CES31 = 71 | CES56 = 78 | CES81 = 78 |
| CES07 = 42 | CES32 = 70 | CES57 = 76 | CES82 = 95 |
| CES08 = 41 | CES33 = 71 | CES58 = 78 | CES83 = 90 |
| CES09 = 29 | CES34 = 82 | CES59 = 92 | CES84 = 94 |
| CES10 = 76 | CES35 = 90 | CES60 = 95 | CES85 = 86 |
| CES11 = 59 | CES36 = 93 | CES61 = 93 | CES86 = 72 |
| CES12 = 65 | CES37 = 87 | CES62 = 83 | CES87 = 85 |
| CES13 = 43 | CES38 = 75 | CES63 = 77 | CES88 = 83 |
| CES14 = 74 | CES39 = 94 | CES64 = 83 | CES89 = 75 |
| CES15 = 71 | CES40 = 89 | CES65 = 77 | CES90 = 81 |
| CES16 = 47 | CES41 = 85 | CES66 = 80 | CES91 = 96 |
| CES17 = 50 | CES42 = 86 | CES67 = 79 | CES92 = 73 |
| CES18 = 56 | CES43 = 81 | CES68 = 84 | CES93 = 84 |
| CES19 = 72 | CES44 = 99 | CES69 = 91 | CES94 = 64 |
| CES20 = 66 | CES45 = 87 | CES70 = 78 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 76 | CES96 = 84 |
| CES22 = 79 | CES47 = 77 | CES72 = 92 | CES97 = 87 |
| CES23 = 92 | CES48 = 71 | CES73 = 71 | CES98 = 81 |
| CES24 = 91 | CES49 = 81 | CES74 = 93 | CES99 = 74 |
| CES25 = 72 | CES50 = 89 | CES75 = 74 |            |





Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)