

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631548

Luminaire Tested: GWS-SA1F-830-U-SL4-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1F-830-U-SL4-W
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS
Light Source: (16) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6427.6 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 67.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P631548
 CATALOG NUMBER: GWS-SA1F-830-U-SL4-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P631548
CATALOG NUMBER: GWS-SA1F-830-U-SL4-W

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P631548

CATALOG NUMBER: GWS-SA1F-830-U-SL4-W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	990.0	0.0	990.0
	% Fixture	15.4	0.0	15.4
Street Side	Lumens	5437.6	0.0	5437.6
	% Fixture	84.6	0.0	84.6
Total	Lumens	6427.6	0.0	6427.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	1.5
10°-20°	251.3	3.9
20°-30°	394.6	6.1
30°-40°	593.3	9.2
40°-50°	915.9	14.2
50°-60°	1360.1	21.2
60°-70°	1714.4	26.7
70°-80°	991.4	15.4
80°-90°	110.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6427.6	100.0
0°-180°	6427.6	100.0

Coefficient of Utilization




REPORT NUMBER: P631548

CATALOG NUMBER: GWS-SA1F-830-U-SL4-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	487.3	7.6			
FM (30°-60°)	2381.3	37.0			
FH (60°-80°)	2477.3	38.5			G2/5000
FVH (80°-90°)	91.6	1.4			G1/100
BL (0°-30°)	255.1	4.0	B1/500		
BM (30°-60°)	488.0	7.6	B1/1000		
BH (60°-80°)	228.5	3.6	B1/500		G1/500
BVH (80°-90°)	18.4	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P631548

CATALOG NUMBER: GWS-SA1F-830-U-SL4-W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°	85°
0°	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5
2.5°	1098.2	1100.1	1101.6	1103.5	1102.5	1099.6	1102.0	1102.0	1096.8	1091.0	1085.7
5°	1099.6	1102.0	1101.6	1101.1	1097.2	1092.4	1092.4	1089.6	1080.4	1071.3	1062.7
7.5°	1096.8	1096.3	1095.8	1094.4	1090.0	1084.8	1083.8	1078.0	1066.1	1053.6	1041.1
10°	1083.8	1083.3	1084.8	1088.1	1087.2	1082.4	1082.4	1077.1	1063.2	1047.8	1031.5
12.5°	1073.2	1073.2	1079.0	1088.1	1091.5	1089.6	1090.0	1086.2	1070.4	1052.1	1032.9
15°	1074.7	1075.2	1087.6	1102.5	1108.8	1107.3	1107.8	1103.5	1085.7	1067.5	1041.6
17.5°	1084.3	1086.7	1108.3	1128.9	1137.1	1135.1	1131.8	1124.6	1104.4	1083.8	1052.1
20°	1104.4	1108.3	1136.1	1162.0	1171.6	1167.3	1161.5	1147.1	1125.1	1102.5	1063.7
22.5°	1144.3	1146.7	1177.4	1202.8	1210.5	1205.2	1193.7	1173.0	1147.6	1124.1	1077.6
25°	1200.4	1203.3	1232.5	1256.0	1254.1	1247.9	1232.1	1206.6	1176.4	1151.5	1097.7
27.5°	1267.1	1271.9	1300.7	1319.4	1306.9	1297.8	1280.0	1249.3	1215.3	1192.7	1128.4
30°	1340.0	1341.9	1366.4	1385.1	1365.9	1353.4	1331.8	1298.7	1268.0	1251.2	1174.5
32.5°	1410.5	1412.4	1433.6	1444.1	1424.0	1414.8	1396.1	1361.1	1339.5	1330.4	1243.1
35°	1484.9	1484.4	1501.7	1510.8	1490.2	1486.3	1467.1	1440.3	1436.4	1448.4	1343.4
37.5°	1559.3	1554.9	1564.1	1576.0	1564.5	1568.4	1555.9	1546.8	1561.7	1592.8	1476.7
40°	1618.7	1618.7	1628.3	1643.2	1647.1	1663.8	1656.7	1668.6	1716.6	1791.0	1641.8
42.5°	1671.5	1672.0	1692.2	1715.2	1743.0	1768.9	1774.7	1805.9	1905.2	2021.8	1849.0
45°	1726.7	1727.2	1754.5	1788.1	1847.1	1896.5	1908.1	1978.1	2120.1	2262.1	2074.1
47.5°	1790.5	1785.2	1823.1	1879.3	1963.2	2034.2	2064.0	2163.3	2342.7	2517.4	2286.1
50°	1862.5	1851.4	1893.7	1990.6	2094.2	2191.6	2241.5	2355.2	2581.7	2752.9	2485.7
52.5°	1943.6	1937.3	1981.5	2099.5	2257.8	2370.1	2437.7	2586.9	2813.9	2987.5	2644.0
55°	2044.3	2029.4	2093.2	2243.4	2449.7	2592.7	2672.8	2816.3	3067.7	3200.6	2764.9
57.5°	2154.7	2138.3	2223.7	2423.3	2699.2	2856.1	2956.4	3074.4	3306.6	3363.7	2835.9
60°	2273.6	2268.4	2369.6	2634.4	2996.7	3179.0	3251.4	3358.4	3514.3	3458.2	2818.2
62.5°	2382.5	2380.6	2527.9	2863.3	3311.9	3512.4	3570.0	3598.3	3664.0	3452.0	2677.1
65°	2497.2	2513.5	2712.6	3128.6	3673.1	3869.8	3893.8	3821.9	3714.4	3288.4	2388.3
67.5°	2511.6	2543.3	2828.7	3377.1	4015.7	4201.4	4182.2	3906.8	3565.7	2833.1	1872.1
70°	2246.3	2301.5	2643.5	3415.0	4257.0	4393.7	4255.1	3724.0	3025.9	2052.5	1177.4
72.5°	1876.9	1924.4	2226.6	2912.2	3945.6	4119.8	3932.2	3152.1	2138.3	1177.4	599.7
75°	1460.9	1516.1	1794.8	2314.9	2954.0	3023.5	2929.5	2198.3	1175.4	485.5	272.5
77.5°	891.4	931.2	1148.1	1568.4	2066.9	1962.7	1663.4	1232.5	515.8	232.7	168.4
80°	394.4	418.8	565.7	842.5	1194.2	1128.9	890.0	526.3	282.1	147.8	117.5
82.5°	211.6	227.4	278.7	333.4	524.4	548.4	444.7	303.2	151.6	84.4	67.2
85°	93.1	102.2	126.7	120.9	172.2	169.4	170.8	208.2	72.4	38.9	43.7
87.5°	0.0	0.0	0.0	0.0	0.5	0.5	5.3	27.8	7.2	11.5	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P631548
 CATALOG NUMBER: GWS-SA1F-830-U-SL4-W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5
2.5°	1080.0	1071.3	1068.9	1066.1	1060.8	1051.7	1044.9	1037.3	1033.9	1030.1	1030.5
5°	1053.1	1042.5	1032.5	1019.5	1003.2	985.0	972.5	958.1	950.4	943.2	945.1
7.5°	1030.1	1013.8	993.1	965.8	936.5	903.9	877.5	856.9	843.0	833.4	838.2
10°	1015.7	996.5	960.5	915.9	866.5	816.6	778.7	743.2	721.1	703.8	702.9
12.5°	1012.8	987.8	935.6	870.8	799.3	732.6	677.0	629.0	599.7	578.1	586.3
15°	1015.7	984.0	914.0	829.0	738.8	648.7	579.6	524.4	489.4	469.7	468.3
17.5°	1019.0	980.2	889.5	783.9	675.5	572.4	492.2	433.7	397.7	378.1	378.5
20°	1021.9	974.4	860.7	734.5	611.2	501.4	418.4	362.7	330.6	316.2	318.6
22.5°	1026.7	968.7	830.0	681.8	545.5	432.8	359.8	314.7	295.5	285.9	286.4
25°	1035.8	965.3	798.3	624.2	480.7	378.1	319.5	289.3	277.3	271.6	271.1
27.5°	1054.5	968.2	765.2	568.5	422.2	336.3	293.6	273.9	265.8	262.0	261.5
30°	1085.7	979.7	736.4	511.9	371.8	303.7	275.9	263.9	259.1	255.7	255.2
32.5°	1133.2	1001.3	705.3	459.1	331.0	279.7	262.0	255.7	252.4	250.4	250.4
35°	1205.2	1040.6	674.6	413.1	299.4	261.0	250.9	248.5	245.6	244.7	245.6
37.5°	1308.8	1103.5	646.7	372.8	276.8	246.6	238.9	239.9	237.5	238.9	240.4
40°	1440.3	1187.4	623.2	339.7	260.0	236.0	228.4	231.7	230.3	231.7	234.1
42.5°	1606.8	1291.5	605.5	313.8	248.0	227.4	220.2	223.6	222.6	224.5	226.9
45°	1792.4	1428.8	597.3	295.5	239.4	221.2	213.5	215.9	214.9	216.4	218.8
47.5°	1970.4	1553.5	604.5	285.0	232.2	215.9	207.7	208.7	208.2	207.7	209.2
50°	2123.9	1652.8	625.1	281.6	227.4	210.6	202.9	203.4	202.0	199.1	200.1
52.5°	2249.2	1732.5	637.6	281.6	225.0	204.9	197.7	198.1	195.3	191.4	191.9
55°	2331.7	1764.6	627.5	281.1	224.1	200.1	192.4	192.9	190.0	185.2	185.7
57.5°	2355.2	1733.4	585.3	275.9	223.1	196.2	187.1	188.1	186.2	180.9	180.9
60°	2289.5	1619.2	508.1	263.9	220.7	193.8	183.3	184.7	183.8	178.5	178.5
62.5°	2117.2	1416.3	416.0	245.6	214.0	190.9	179.9	182.8	185.2	182.3	181.8
65°	1794.8	1134.7	338.2	225.5	205.3	186.2	175.1	182.3	187.6	191.4	191.4
67.5°	1346.7	812.3	275.9	204.4	192.4	176.6	168.9	175.6	179.4	181.8	183.3
70°	820.9	477.9	217.3	179.9	173.7	162.2	156.4	149.7	144.4	143.5	143.9
72.5°	401.6	273.5	176.6	153.0	148.2	137.7	124.7	121.9	119.5	118.0	117.5
75°	221.2	190.5	145.9	127.1	118.5	105.5	102.7	97.9	96.9	95.0	95.5
77.5°	156.4	150.2	120.4	103.2	90.2	83.5	84.9	81.6	81.6	80.1	79.6
80°	117.5	118.0	92.6	75.3	66.7	64.3	65.7	65.7	64.8	64.3	63.8
82.5°	74.4	84.0	62.4	48.5	47.5	48.0	47.5	47.0	48.0	46.5	46.1
85°	51.3	60.5	37.9	28.8	28.8	28.3	29.3	28.8	29.7	28.3	28.3
87.5°	11.5	26.9	13.9	8.6	9.1	8.6	9.1	9.6	10.6	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)