

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643910

Luminaire Tested: GWS-SA6F-830-U-AFL-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-45)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGF-830-U-AFL-W
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS
Light Source: (96) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 40260.9 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 372.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643910
 CATALOG NUMBER: GWS-SA6F-830-U-AFL-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 13.4 fc
 Type II - Short - N/A

REPORT NUMBER: P643910
CATALOG NUMBER: GWS-SA6F-830-U-AFL-W

Luminous Intensity Polar Plot



— Vertical Plane Through 59-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P643910

CATALOG NUMBER: GWS-SA6F-830-U-AFL-W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6248.3	0.0	6248.3
	% Fixture	15.5	0.0	15.5
Street Side	Lumens	34012.6	0.0	34012.6
	% Fixture	84.5	0.0	84.5
Total	Lumens	40260.9	0.0	40260.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	917.7	2.3
10°-20°	2325.4	5.8
20°-30°	3769.5	9.4
30°-40°	6063.7	15.1
40°-50°	9416.4	23.4
50°-60°	10142.7	25.2
60°-70°	5886.4	14.6
70°-80°	1536.7	3.8
80°-90°	202.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	40260.9	100.0
0°-180°	40260.9	100.0

Coefficient of Utilization



REPORT NUMBER: P643910


CATALOG NUMBER: GWS-SA6F-830-U-AFL-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	4939.6	12.3			
FM (30°-60°)	22852.5	56.8			
FH (60°-80°)	6123.5	15.2			G3/7500
FVH (80°-90°)	96.9	0.2			G1/100
BL (0°-30°)	2072.9	5.1	B3/2500		
BM (30°-60°)	2770.2	6.9	B3/5000		
BH (60°-80°)	1299.6	3.2	B3/2500		G3/2500
BVH (80°-90°)	105.5	0.3			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P643910
 CATALOG NUMBER: GWS-SA6F-830-U-AFL-W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	59°	65°	75°	85°
0°	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2
2.5°	11209.7	11116.2	11181.4	11065.2	11017.0	10889.4	10725.0	10614.5	10444.4	10223.4	10030.6
5°	12323.6	12258.4	12272.6	12147.9	12037.3	11824.7	11487.5	11300.4	11011.3	10566.3	10152.5
7.5°	12289.6	12366.1	12408.6	12516.3	12547.5	12527.7	12224.4	11963.6	11646.2	10977.3	10353.7
10°	11017.0	11161.5	11291.9	11660.4	12108.2	12675.0	12745.9	12590.0	12269.7	11501.6	10594.7
12.5°	9631.0	9741.5	9857.7	10299.9	10985.8	12119.5	12887.6	12984.0	12856.4	12020.3	10866.8
15°	8950.8	9001.8	9112.3	9404.2	9951.3	11209.7	12641.0	13063.3	13292.9	12570.2	11172.9
17.5°	8922.4	8945.1	8998.9	9154.8	9534.6	10506.8	12196.0	12904.6	13635.9	13151.2	11530.0
20°	9509.1	9449.6	9415.6	9412.8	9599.8	10271.5	11765.2	12649.5	13797.4	13746.4	11912.6
22.5°	10322.6	10342.4	10268.7	10087.3	10064.6	10438.8	11549.8	12391.6	13845.6	14273.6	12266.9
25°	11476.1	11575.3	11357.1	11011.3	10841.2	10923.4	11683.0	12312.3	13839.9	14712.9	12488.0
27.5°	12822.4	12899.0	12677.9	12224.4	11872.9	11674.5	12079.8	12547.5	13888.1	15092.7	12621.2
30°	14355.8	14381.3	14078.0	13601.9	13088.9	12663.7	12740.2	13032.2	14134.7	15591.6	12777.1
32.5°	16229.3	16337.0	15877.8	15123.9	14406.8	13862.6	13627.4	13814.4	14667.6	16181.1	13018.0
35°	18607.3	18644.1	18060.2	16980.4	15965.7	15211.8	14718.6	14817.8	15478.2	17005.9	13380.8
37.5°	20849.2	20886.0	20265.3	19262.0	17810.8	16779.1	16064.9	16019.5	16515.5	18170.8	13973.2
40°	22272.0	22376.9	22099.1	21469.9	20083.9	18692.3	17723.0	17567.1	17876.0	19596.4	14797.9
42.5°	23037.3	23082.6	23077.0	23159.2	22334.4	20951.2	19593.6	19281.8	19488.7	21135.5	15631.2
45°	23043.0	23156.3	23459.6	24250.4	24287.2	23425.6	21957.4	21469.9	21280.0	22685.8	16501.4
47.5°	22011.3	22133.1	22966.4	24522.5	25670.4	25865.9	24788.9	23811.1	23011.8	24020.8	17215.6
50°	18887.9	19194.0	20781.2	23533.3	25942.5	27821.6	27490.0	26163.5	24550.8	25052.5	17663.4
52.5°	16175.4	16164.1	17141.9	20738.7	24805.9	28683.2	30103.2	28584.0	26072.8	25707.2	17776.8
55°	11844.6	11909.8	12910.3	15860.8	21773.2	27849.9	31540.2	30811.8	27818.8	26055.8	17731.5
57.5°	6142.0	6465.1	7491.1	10121.3	16543.9	24981.6	31157.6	31642.3	29593.1	26302.4	17791.0
60°	3103.6	3041.2	3409.7	4832.5	9585.6	19511.4	28799.4	30344.1	29913.3	26495.1	17827.8
62.5°	2071.9	2054.9	1952.8	2239.1	3917.0	11555.5	24550.8	26716.2	27688.4	26041.7	17357.3
65°	1794.1	1760.1	1573.0	1561.7	1901.8	4792.8	17995.0	21002.3	22884.2	24026.5	16232.1
67.5°	1615.6	1564.5	1374.6	1281.1	1366.1	2105.9	10141.2	14086.5	16898.2	20319.2	13766.3
70°	1442.7	1417.2	1227.3	1091.2	1082.7	1283.9	3735.6	7270.0	10339.6	13862.6	10064.6
72.5°	1292.4	1247.1	1085.5	955.2	890.0	909.8	1621.2	2800.3	5351.2	8647.5	6020.1
75°	1119.6	1085.5	943.8	813.4	734.1	666.1	989.2	1295.3	2440.3	4109.8	2842.8
77.5°	864.5	841.8	745.4	646.2	600.9	496.0	600.9	816.3	1128.1	1731.8	1479.5
80°	501.7	515.8	555.5	504.5	442.2	354.3	391.1	470.5	677.4	938.2	839.0
82.5°	252.3	269.3	360.0	291.9	263.6	206.9	232.4	277.8	354.3	518.7	328.8
85°	19.8	19.8	65.2	73.7	90.7	73.7	93.5	113.4	161.6	206.9	110.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	8.5	14.2	25.5	48.2	31.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P643910
 CATALOG NUMBER: GWS-SA6F-830-U-AFL-W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2	9883.2
2.5°	9900.3	9755.7	9582.8	9441.1	9222.9	9106.6	8959.3	8777.9	8704.2	8670.2	8650.3
5°	9920.1	9665.0	9296.5	8956.4	8579.5	8281.9	7950.2	7604.5	7406.1	7357.9	7323.9
7.5°	9993.8	9636.7	9050.0	8488.8	7788.7	7139.6	6507.6	5881.2	5560.9	5439.0	5427.7
10°	10095.8	9625.3	8800.5	7868.1	6686.1	5660.1	4920.4	4430.0	4223.1	4155.1	4132.4
12.5°	10223.4	9616.8	8471.8	7006.4	5413.5	4444.2	4021.9	3942.5	3970.9	3965.2	3965.2
15°	10384.9	9628.2	8075.0	6031.4	4379.0	3857.5	3866.0	3959.5	4047.4	4061.6	4061.6
17.5°	10560.6	9616.8	7499.6	5053.6	3758.3	3718.6	3849.0	3979.4	4058.7	4070.1	4070.1
20°	10750.5	9563.0	6774.0	4132.4	3486.2	3630.8	3772.5	3874.5	3922.7	3934.0	3934.0
22.5°	10863.9	9409.9	5986.1	3497.5	3313.3	3491.9	3585.4	3690.3	3695.9	3605.2	3602.4
25°	10846.9	9123.7	5087.6	3089.4	3129.1	3285.0	3404.0	3330.3	3239.6	3188.6	3180.1
27.5°	10739.2	8692.8	4172.1	2780.5	2910.8	3086.6	3049.7	2987.4	2964.7	2908.0	2902.3
30°	10603.2	8162.8	3350.2	2539.5	2684.1	2845.6	2789.0	2783.3	2760.6	2698.3	2698.3
32.5°	10472.8	7615.8	2729.4	2361.0	2539.5	2550.9	2630.2	2635.9	2624.6	2516.9	2505.5
35°	10435.9	7068.8	2310.0	2219.3	2397.8	2392.2	2505.5	2502.7	2307.1	2156.9	2154.1
37.5°	10546.5	6513.2	2060.5	2103.1	2202.3	2276.0	2366.7	2202.3	2137.1	2046.4	2040.7
40°	10781.7	6000.2	1933.0	2035.0	2077.6	2185.3	2043.5	2054.9	2037.9	1969.8	1961.3
42.5°	11093.5	5563.8	1862.1	2012.4	2006.7	2035.0	1879.1	1924.5	1950.0	1899.0	1890.5
45°	11393.9	5184.0	1825.3	1927.3	1955.7	1791.3	1760.1	1802.6	1842.3	1822.5	1814.0
47.5°	11615.0	4855.2	1805.5	1811.1	1890.5	1709.1	1658.1	1677.9	1726.1	1734.6	1731.8
50°	11683.0	4574.6	1782.8	1714.8	1697.8	1626.9	1587.2	1581.5	1638.2	1677.9	1683.6
52.5°	11552.7	4325.2	1723.3	1629.7	1547.5	1558.9	1544.7	1516.4	1573.0	1626.9	1632.6
55°	11359.9	4183.4	1629.7	1547.5	1451.2	1496.5	1502.2	1476.7	1513.5	1550.4	1550.4
57.5°	11374.1	4265.6	1539.0	1471.0	1366.1	1425.7	1456.8	1445.5	1445.5	1473.8	1476.7
60°	11467.6	4384.7	1479.5	1374.6	1281.1	1343.5	1414.3	1403.0	1377.5	1414.3	1414.3
62.5°	11198.4	4226.0	1439.8	1281.1	1190.4	1264.1	1349.1	1343.5	1315.1	1374.6	1380.3
65°	10404.8	3800.8	1394.5	1164.9	1099.7	1184.7	1258.4	1278.3	1252.8	1332.1	1346.3
67.5°	8721.2	3197.1	1306.6	1054.4	1009.0	1088.4	1159.2	1187.6	1167.7	1261.3	1272.6
70°	6501.9	2587.7	1167.7	932.5	898.5	969.3	1034.5	1045.9	1048.7	1159.2	1170.6
72.5°	4146.6	2012.4	983.5	796.4	770.9	824.8	873.0	918.3	938.2	1043.0	1040.2
75°	2312.8	1496.5	790.8	674.6	629.2	671.7	728.4	782.3	839.0	992.0	1009.0
77.5°	1332.1	1051.5	626.4	541.4	487.5	532.9	581.0	657.6	827.6	960.8	943.8
80°	751.1	683.1	473.3	396.8	362.8	396.8	433.6	578.2	651.9	708.6	717.1
82.5°	351.5	382.6	323.1	243.8	243.8	266.4	300.4	447.8	493.2	402.5	351.5
85°	127.5	172.9	158.7	124.7	110.5	107.7	187.1	255.1	158.7	141.7	121.9
87.5°	34.0	48.2	45.3	31.2	17.0	14.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)