

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630547

Luminaire Tested: GWS-SA1D-830-U-RW-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-830-U-RW-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (16) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4246.4 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B2 - U0 - G0


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630547
 CATALOG NUMBER: GWS-SA1D-830-U-RW-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7.8 fc
 Type V - Short - N/A

REPORT NUMBER: P630547
CATALOG NUMBER: GWS-SA1D-830-U-RW-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 49-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P630547

CATALOG NUMBER: GWS-SA1D-830-U-RW-W-GRSWH


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2102.4	0.0	2102.4
	% Fixture	49.5	0.0	49.5
Street Side	Lumens	2144.0	0.0	2144.0
	% Fixture	50.5	0.0	50.5
Total	Lumens	4246.4	0.0	4246.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	1.6
10°-20°	226.3	5.3
20°-30°	431.1	10.2
30°-40°	730.8	17.2
40°-50°	1099.8	25.9
50°-60°	1203.9	28.4
60°-70°	380.7	9.0
70°-80°	91.4	2.2
80°-90°	13.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4246.4	100.0
0°-180°	4246.4	100.0

Coefficient of Utilization



REPORT NUMBER: P630547


CATALOG NUMBER: GWS-SA1D-830-U-RW-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	367.1	8.6			
FM (30°-60°)	1541.6	36.3			
FH (60°-80°)	229.0	5.4			G0/660
FVH (80°-90°)	6.3	0.1			G0/10
BL (0°-30°)	358.9	8.5	B1/500		
BM (30°-60°)	1493.0	35.2	B2/2500		
BH (60°-80°)	243.1	5.7	B1/500		G0/660
BVH (80°-90°)	7.4	0.2			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G0

Type V Short





REPORT NUMBER: P630547

CATALOG NUMBER: GWS-SA1D-830-U-RW-W-GRSWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	49°	55°	65°	75°	85°
0°	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4
2.5°	693.1	693.8	695.2	697.6	700.0	703.4	704.8	706.5	706.2	708.3	708.3
5°	689.6	690.7	692.7	696.2	700.3	706.9	708.6	712.8	716.9	722.1	723.8
7.5°	693.8	695.2	697.6	703.1	709.3	717.9	721.4	728.3	736.2	745.6	749.4
10°	701.7	703.4	707.6	716.6	726.6	739.7	742.8	751.4	764.2	777.0	784.6
12.5°	710.7	713.5	721.1	735.2	750.1	767.3	772.2	782.9	796.7	813.3	823.6
15°	721.1	723.5	735.2	755.2	778.4	801.2	806.7	817.1	832.6	848.8	863.3
17.5°	742.8	747.0	760.8	783.9	810.8	837.8	844.0	855.7	868.2	880.9	894.8
20°	772.5	776.0	793.6	822.2	854.0	878.5	884.7	895.1	901.0	907.5	919.3
22.5°	802.2	807.0	827.1	860.9	898.2	924.8	929.6	939.3	935.2	933.1	940.7
25°	839.2	845.7	865.4	902.4	940.3	973.1	976.9	985.2	978.3	967.6	967.3
27.5°	885.1	891.0	911.3	949.3	987.0	1021.1	1028.4	1039.5	1024.3	1011.1	1001.8
30°	939.6	943.4	965.9	1006.3	1045.0	1077.4	1086.8	1097.8	1086.4	1064.7	1055.3
32.5°	1003.2	1008.4	1034.3	1076.7	1111.3	1143.7	1153.1	1166.9	1154.4	1129.9	1118.2
35°	1079.5	1084.7	1112.0	1158.2	1193.5	1227.0	1233.5	1244.9	1229.4	1201.1	1191.7
37.5°	1162.4	1168.9	1203.5	1247.3	1284.3	1323.3	1323.7	1327.1	1305.0	1269.8	1259.4
40°	1255.6	1264.3	1298.8	1344.4	1388.9	1420.7	1420.4	1410.7	1373.4	1318.8	1302.9
42.5°	1347.8	1354.7	1389.6	1436.6	1481.1	1511.2	1502.2	1478.7	1424.8	1350.6	1329.5
45°	1414.5	1419.7	1456.3	1509.1	1554.3	1573.0	1556.8	1528.4	1455.6	1370.6	1339.5
47.5°	1445.9	1452.8	1489.8	1542.3	1593.4	1604.1	1584.7	1558.1	1473.5	1389.3	1347.5
50°	1429.0	1438.0	1479.7	1528.4	1586.1	1608.2	1594.4	1567.8	1492.5	1407.6	1361.6
52.5°	1385.1	1393.8	1446.6	1505.6	1570.9	1614.8	1614.4	1592.7	1514.3	1412.8	1362.3
55°	1235.3	1252.2	1334.4	1436.2	1552.3	1634.1	1642.4	1619.3	1517.7	1414.1	1369.6
57.5°	803.9	833.6	911.7	1044.3	1277.0	1486.3	1542.3	1547.8	1492.9	1408.3	1371.0
60°	335.7	359.5	421.3	509.4	701.7	950.7	1059.1	1167.9	1299.1	1346.8	1358.2
62.5°	208.6	210.7	216.9	236.9	301.1	422.7	492.4	594.3	789.4	955.5	1032.2
65°	188.2	189.2	190.6	189.2	192.4	207.2	225.8	261.4	340.8	423.4	521.5
67.5°	165.8	167.1	168.2	167.1	168.2	168.9	170.9	174.0	188.6	200.3	209.3
70°	134.0	136.1	137.8	137.1	141.2	141.2	143.3	145.7	153.0	161.6	167.8
72.5°	102.2	100.5	102.6	103.3	107.1	109.1	112.2	115.0	123.3	128.5	136.4
75°	66.3	64.6	67.7	69.4	74.6	77.4	80.1	82.9	88.8	92.2	99.8
77.5°	35.9	35.6	38.7	41.1	46.6	50.1	52.1	54.2	59.1	60.1	64.9
80°	20.7	20.7	22.8	24.5	28.0	31.8	33.8	35.6	39.0	40.1	42.1
82.5°	11.4	11.4	12.4	13.5	16.2	18.3	20.0	21.4	24.5	25.6	26.6
85°	5.5	5.2	5.9	6.6	7.6	8.6	9.7	10.4	12.8	13.5	14.8
87.5°	0.7	0.7	0.7	1.0	1.4	2.1	2.4	2.4	3.8	4.5	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P630547

CATALOG NUMBER: GWS-SA1D-830-U-RW-W-GRSWH

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4	703.4
2.5°	710.3	705.9	708.6	709.7	709.7	708.6	704.1	702.8	700.7	697.6	697.6
5°	726.2	722.8	723.5	721.7	717.6	712.4	704.1	700.0	696.5	692.7	692.4
7.5°	753.5	749.0	748.3	741.8	730.7	719.7	707.2	699.6	694.5	689.6	689.3
10°	789.1	784.9	779.8	766.6	750.4	734.2	717.3	706.9	699.3	692.4	692.0
12.5°	828.8	824.0	814.3	795.0	774.6	758.7	739.4	723.5	712.1	702.8	701.0
15°	872.0	865.1	848.5	825.7	805.7	788.7	768.0	745.2	728.0	713.1	711.4
17.5°	905.1	896.1	878.2	856.8	840.2	823.3	796.3	767.7	742.8	724.2	721.4
20°	927.9	920.7	900.3	884.4	874.7	859.9	828.5	796.0	768.0	744.5	743.2
22.5°	949.0	940.3	920.3	911.0	911.0	901.0	870.9	832.6	799.8	772.5	769.1
25°	972.8	963.5	948.3	947.2	952.1	947.6	911.3	870.2	831.9	801.2	795.6
27.5°	1006.0	995.6	986.6	992.8	999.7	994.9	954.5	906.8	866.4	835.4	830.5
30°	1058.8	1046.0	1037.7	1045.3	1058.8	1044.6	1000.8	950.4	909.6	875.4	873.0
32.5°	1120.3	1105.8	1097.1	1109.2	1121.3	1099.2	1055.7	1007.3	964.5	928.6	924.5
35°	1194.2	1175.9	1163.1	1179.3	1191.7	1170.0	1126.8	1080.9	1033.2	995.9	990.4
37.5°	1259.8	1237.7	1229.0	1251.8	1268.4	1254.2	1207.3	1164.1	1112.0	1071.2	1068.8
40°	1307.4	1285.7	1279.5	1317.1	1346.1	1342.7	1300.5	1251.1	1202.1	1155.1	1150.6
42.5°	1328.1	1313.0	1314.3	1365.1	1410.0	1432.1	1394.5	1341.6	1294.3	1245.6	1242.5
45°	1332.6	1323.3	1334.4	1397.9	1457.0	1502.2	1470.1	1425.9	1372.4	1325.4	1324.0
47.5°	1337.5	1332.3	1349.2	1416.6	1486.7	1539.1	1521.2	1475.6	1421.4	1375.5	1372.0
50°	1348.9	1346.8	1365.8	1429.7	1500.8	1549.2	1528.8	1483.5	1427.9	1382.7	1374.4
52.5°	1352.3	1348.9	1376.1	1450.1	1524.3	1548.8	1505.0	1445.9	1390.0	1339.5	1330.9
55°	1363.0	1356.8	1375.5	1457.6	1556.8	1568.8	1503.6	1415.2	1337.1	1268.4	1248.0
57.5°	1365.8	1358.9	1371.0	1445.2	1521.5	1510.8	1321.6	1142.0	994.9	918.6	927.2
60°	1350.9	1353.0	1332.3	1324.0	1220.4	1077.4	809.1	646.8	508.0	449.3	462.1
62.5°	1028.4	1037.0	966.2	840.2	646.1	512.1	338.8	263.1	222.7	212.4	214.1
65°	519.0	530.8	457.2	378.1	281.1	227.2	196.5	190.3	188.2	185.8	185.8
67.5°	205.5	208.9	206.2	193.0	179.6	174.7	173.4	172.7	170.2	168.9	169.2
70°	165.1	167.8	163.7	155.4	149.9	149.5	148.8	147.5	145.7	145.7	146.8
72.5°	134.7	137.4	131.6	126.4	122.2	119.1	117.4	116.4	114.0	114.0	115.0
75°	99.1	100.8	96.0	95.3	90.8	87.7	85.0	83.6	80.5	79.1	80.1
77.5°	66.0	65.6	63.2	63.2	61.5	57.7	54.6	51.5	47.3	44.5	45.2
80°	42.8	42.8	41.8	41.8	40.1	37.0	33.2	30.0	27.6	25.6	25.6
82.5°	27.3	26.9	26.6	26.2	25.6	22.4	19.7	17.6	15.9	14.5	14.8
85°	15.2	15.2	14.5	14.5	13.1	11.4	10.0	8.6	7.6	7.3	7.3
87.5°	5.2	5.2	4.8	4.8	4.1	3.1	2.4	2.1	1.7	1.4	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)