

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P642922

Luminaire Tested: GWS-SA6D-830-U-RW-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P642922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6D-830-U-RW-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (96) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25085.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1


Input Watts (W): 245.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P642922
 CATALOG NUMBER: GWS-SA6D-830-U-RW-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.4 fc
 Type V - Short - N/A

REPORT NUMBER: P642922
CATALOG NUMBER: GWS-SA6D-830-U-RW-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 49-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P642922

CATALOG NUMBER: GWS-SA6D-830-U-RW-W-GRSWH


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	12419.6	0.0	12419.6
	% Fixture	49.5	0.0	49.5
Street Side	Lumens	12665.7	0.0	12665.7
	% Fixture	50.5	0.0	50.5
Total	Lumens	25085.3	0.0	25085.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	405.4	1.6
10°-20°	1337.1	5.3
20°-30°	2546.8	10.2
30°-40°	4317.3	17.2
40°-50°	6497.3	25.9
50°-60°	7111.9	28.4
60°-70°	2248.8	9.0
70°-80°	539.7	2.2
80°-90°	81.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25085.3	100.0
0°-180°	25085.3	100.0

Coefficient of Utilization



REPORT NUMBER: P642922


CATALOG NUMBER: GWS-SA6D-830-U-RW-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2168.9	8.6			
FM (30°-60°)	9106.7	36.3			
FH (60°-80°)	1352.7	5.4			G1/1800
FVH (80°-90°)	37.5	0.1			G1/100
BL (0°-30°)	2120.4	8.5	B3/2500		
BM (30°-60°)	8819.9	35.2	B5		
BH (60°-80°)	1435.8	5.7	B3/2500		G1/1800
BVH (80°-90°)	43.5	0.2			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G1

Type V Short





REPORT NUMBER: P642922

CATALOG NUMBER: GWS-SA6D-830-U-RW-W-GRSWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	49°	55°	65°	75°	85°
0°	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5
2.5°	4094.3	4098.4	4106.6	4120.9	4135.1	4155.5	4163.7	4173.9	4171.9	4184.1	4184.1
5°	4073.9	4080.1	4092.3	4112.7	4137.2	4175.9	4186.1	4210.6	4235.1	4265.7	4275.9
7.5°	4098.4	4106.6	4120.9	4153.5	4190.2	4241.2	4261.6	4302.4	4349.3	4404.4	4426.9
10°	4145.3	4155.5	4180.0	4233.1	4292.2	4369.7	4388.1	4439.1	4514.6	4590.1	4634.9
12.5°	4198.4	4214.7	4259.6	4343.2	4430.9	4532.9	4561.5	4624.7	4706.3	4804.3	4865.5
15°	4259.6	4273.9	4343.2	4461.5	4598.2	4732.9	4765.5	4826.7	4918.5	5014.4	5100.1
17.5°	4388.1	4412.6	4494.2	4630.9	4790.0	4949.1	4985.8	5055.2	5128.6	5204.1	5285.7
20°	4563.5	4583.9	4688.0	4857.3	5045.0	5189.8	5226.5	5287.7	5322.4	5361.2	5430.5
22.5°	4739.0	4767.5	4885.9	5085.8	5306.1	5463.2	5491.7	5548.9	5524.4	5512.1	5557.0
25°	4957.3	4996.0	5112.3	5330.6	5555.0	5748.8	5771.2	5820.2	5779.4	5716.2	5714.1
27.5°	5228.6	5263.3	5383.6	5608.0	5830.4	6032.4	6075.2	6140.5	6050.7	5973.2	5918.1
30°	5550.9	5573.3	5706.0	5944.6	6173.1	6364.9	6420.0	6485.2	6417.9	6289.4	6234.3
32.5°	5926.3	5956.9	6109.9	6360.8	6564.8	6756.6	6811.6	6893.2	6819.8	6675.0	6605.6
35°	6377.1	6407.7	6568.9	6842.2	7050.3	7248.2	7287.0	7354.3	7262.5	7095.2	7040.1
37.5°	6866.7	6905.5	7109.5	7368.6	7586.9	7817.4	7819.4	7839.8	7709.3	7501.2	7440.0
40°	7417.5	7468.5	7672.5	7941.8	8205.0	8392.7	8390.6	8333.5	8113.2	7790.9	7697.0
42.5°	7962.2	8003.0	8209.1	8486.5	8749.7	8927.2	8874.1	8735.4	8417.1	7978.5	7854.1
45°	8355.9	8386.5	8602.8	8914.9	9182.2	9292.3	9196.4	9029.2	8598.7	8096.9	7913.3
47.5°	8541.6	8582.4	8800.7	9110.8	9412.7	9475.9	9361.7	9204.6	8704.8	8207.0	7960.2
50°	8441.6	8494.7	8741.5	9029.2	9369.8	9500.4	9418.8	9261.7	8817.0	8315.1	8043.8
52.5°	8182.5	8233.5	8545.7	8894.5	9280.1	9539.2	9537.1	9408.6	8945.5	8345.7	8047.9
55°	7297.2	7397.1	7882.7	8484.5	9169.9	9653.4	9702.4	9565.7	8965.9	8353.9	8090.7
57.5°	4749.2	4924.6	5385.7	6169.0	7544.0	8780.3	9110.8	9143.4	8819.0	8319.2	8098.9
60°	1982.9	2123.7	2488.8	3009.0	4145.3	5616.2	6256.8	6899.4	7674.6	7956.1	8023.4
62.5°	1232.2	1244.4	1281.1	1399.5	1778.9	2497.0	2909.1	3510.9	4663.5	5644.8	6097.6
65°	1111.8	1117.9	1126.1	1117.9	1136.3	1224.0	1334.2	1544.3	2013.5	2501.1	3080.4
67.5°	979.2	987.4	993.5	987.4	993.5	997.6	1009.8	1028.2	1113.9	1183.2	1236.3
70°	791.5	803.8	814.0	809.9	834.4	834.4	846.6	860.9	903.7	954.7	991.5
72.5°	603.8	593.6	605.9	610.0	632.4	644.6	663.0	679.3	728.3	758.9	805.8
75°	391.7	381.5	399.8	410.0	440.6	457.0	473.3	489.6	524.3	544.7	589.6
77.5°	212.2	210.1	228.5	242.8	275.4	295.8	308.0	320.3	348.8	355.0	383.5
80°	122.4	122.4	134.6	144.8	165.2	187.7	199.9	210.1	230.5	236.6	248.9
82.5°	67.3	67.3	73.4	79.6	95.9	108.1	118.3	126.5	144.8	151.0	157.1
85°	32.6	30.6	34.7	38.8	44.9	51.0	57.1	61.2	75.5	79.6	87.7
87.5°	4.1	4.1	4.1	6.1	8.2	12.2	14.3	14.3	22.4	26.5	30.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P642922

CATALOG NUMBER: GWS-SA6D-830-U-RW-W-GRSWH

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5	4155.5
2.5°	4196.3	4169.8	4186.1	4192.3	4192.3	4186.1	4159.6	4151.5	4139.2	4120.9	4120.9
5°	4290.2	4269.8	4273.9	4263.7	4239.2	4208.6	4159.6	4135.1	4114.7	4092.3	4090.3
7.5°	4451.3	4424.8	4420.7	4382.0	4316.7	4251.4	4178.0	4133.1	4102.5	4073.9	4071.9
10°	4661.5	4637.0	4606.4	4528.9	4433.0	4337.1	4237.1	4175.9	4131.1	4090.3	4088.2
12.5°	4896.1	4867.5	4810.4	4696.1	4575.8	4481.9	4367.7	4273.9	4206.5	4151.5	4141.3
15°	5151.1	5110.3	5012.3	4877.7	4759.4	4659.4	4537.0	4402.4	4300.4	4212.7	4202.5
17.5°	5346.9	5293.9	5187.8	5061.3	4963.4	4863.4	4704.3	4535.0	4388.1	4277.9	4261.6
20°	5481.5	5438.7	5318.3	5224.5	5167.4	5079.7	4894.0	4702.3	4537.0	4398.3	4390.1
22.5°	5606.0	5555.0	5436.7	5381.6	5381.6	5322.4	5144.9	4918.5	4724.7	4563.5	4543.1
25°	5746.8	5691.7	5601.9	5595.8	5624.4	5597.8	5383.6	5140.9	4914.4	4732.9	4700.2
27.5°	5942.6	5881.4	5828.4	5865.1	5905.9	5877.3	5638.6	5357.1	5118.4	4934.8	4906.3
30°	6254.7	6179.2	6130.3	6175.2	6254.7	6171.1	5912.0	5614.2	5373.4	5171.5	5157.2
32.5°	6617.8	6532.2	6481.2	6552.6	6624.0	6493.4	6236.4	5950.8	5697.8	5485.6	5461.1
35°	7054.4	6946.3	6870.8	6966.7	7040.1	6911.6	6656.6	6385.3	6103.8	5883.4	5850.8
37.5°	7442.0	7311.5	7260.5	7395.1	7493.0	7409.4	7131.9	6876.9	6568.9	6328.2	6313.9
40°	7723.5	7595.0	7558.3	7780.7	7952.0	7931.6	7682.7	7391.0	7101.3	6823.9	6797.4
42.5°	7845.9	7756.2	7764.3	8064.2	8329.4	8460.0	8237.6	7925.5	7646.0	7358.4	7340.0
45°	7872.5	7817.4	7882.7	8258.0	8606.9	8874.1	8684.4	8423.3	8107.1	7829.6	7821.5
47.5°	7901.0	7870.4	7970.4	8368.2	8782.3	9092.4	8986.3	8717.0	8396.7	8125.4	8105.0
50°	7968.3	7956.1	8068.3	8445.7	8866.0	9151.6	9031.2	8763.9	8435.5	8168.3	8119.3
52.5°	7988.7	7968.3	8129.5	8566.1	9004.7	9149.5	8890.4	8541.6	8211.1	7913.3	7862.3
55°	8052.0	8015.3	8125.4	8610.9	9196.4	9267.8	8882.3	8360.0	7899.0	7493.0	7372.7
57.5°	8068.3	8027.5	8098.9	8537.5	8988.4	8925.1	7807.2	6746.4	5877.3	5426.5	5477.5
60°	7980.6	7992.8	7870.4	7821.5	7209.5	6364.9	4779.8	3821.0	3000.9	2654.1	2729.6
62.5°	6075.2	6126.2	5708.0	4963.4	3816.9	3025.4	2001.3	1554.5	1315.8	1254.6	1264.8
65°	3066.2	3135.5	2701.0	2233.8	1660.6	1342.3	1160.8	1124.1	1111.8	1097.5	1097.5
67.5°	1213.8	1234.2	1217.9	1140.4	1060.8	1032.3	1024.1	1020.0	1005.7	997.6	999.6
70°	975.1	991.5	967.0	918.0	885.4	883.3	879.3	871.1	860.9	860.9	867.0
72.5°	795.6	811.9	777.2	746.6	722.2	703.8	693.6	687.5	673.2	673.2	679.3
75°	585.5	595.7	567.1	563.0	536.5	518.2	501.8	493.7	475.3	467.2	473.3
77.5°	389.6	387.6	373.3	373.3	363.1	340.7	322.3	304.0	279.5	263.2	267.2
80°	253.0	253.0	246.8	246.8	236.6	218.3	195.8	177.5	163.2	151.0	151.0
82.5°	161.2	159.1	157.1	155.0	151.0	132.6	116.3	104.0	93.8	85.7	87.7
85°	89.8	89.8	85.7	85.7	77.5	67.3	59.2	51.0	44.9	42.8	42.8
87.5°	30.6	30.6	28.6	28.6	24.5	18.4	14.3	12.2	10.2	8.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)