

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P387036

Luminaire Tested: **GWC-SA2D-730-U-SLR-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P387036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA2D-730-U-SLR-HSS
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 3000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10932 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B1 - U0 - G2

Input Watts (W): 129
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT






REPORT NUMBER: P387036
 CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.9 fc
 Type IV - Medium - N/A

REPORT NUMBER: P387036
CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P387036

CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1323.1	0.0	1323.1
	% Fixture	12.1	0.0	12.1
Street Side	Lumens	9608.9	0.0	9608.9
	% Fixture	87.9	0.0	87.9
Total	Lumens	10932.0	0.0	10932.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.3	2.5
10°-20°	544.0	5.0
20°-30°	772.5	7.1
30°-40°	1141.0	10.4
40°-50°	1645.6	15.1
50°-60°	2310.1	21.1
60°-70°	2692.9	24.6
70°-80°	1376.7	12.6
80°-90°	175.8	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10932.0	100.0
0°-180°	10932.0	100.0

Coefficient of Utilization



REPORT NUMBER: P387036


CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1199.0	11.0			
FM (30°-60°)	4497.6	41.1			
FH (60°-80°)	3747.1	34.3			G2/5000
FVH (80°-90°)	165.1	1.5			G2/225
BL (0°-30°)	390.8	3.6	B1/500		
BM (30°-60°)	599.2	5.5	B1/1000		
BH (60°-80°)	322.5	2.9	B1/500		G1/500
BVH (80°-90°)	10.7	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Medium





REPORT NUMBER: P387036

CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1
2.5°	3899.3	3869.2	3836.1	3727.8	3627.4	3512.4	3418.7	3353.4	3271.6	3165.4	3138.5
5°	3871.3	3839.2	3735.1	3494.3	3283.5	3078.4	2880.6	2764.5	2620.6	2474.5	2438.3
7.5°	3590.1	3556.4	3406.2	3076.3	2792.5	2496.3	2239.4	2080.4	1917.8	1784.2	1713.2
10°	3297.5	3260.7	3091.9	2691.5	2341.9	2074.2	1885.7	1733.9	1580.1	1437.2	1323.2
12.5°	3096.0	3047.8	2864.5	2410.8	2106.3	1924.5	1748.4	1566.6	1358.5	1205.2	1079.8
15°	3011.6	2956.7	2763.0	2302.6	2022.9	1809.5	1580.1	1356.9	1113.0	937.4	822.4
17.5°	3076.8	3005.4	2797.7	2295.3	1918.3	1627.8	1337.7	1075.7	811.0	633.4	551.6
20°	3298.5	3204.8	2941.2	2293.3	1791.4	1411.8	1044.1	747.8	534.5	429.9	386.9
22.5°	3647.6	3523.8	3147.3	2309.8	1660.4	1185.0	754.1	508.1	401.4	347.0	321.6
25°	4069.1	3925.7	3444.0	2368.4	1545.4	964.3	547.9	401.4	338.7	298.8	277.6
27.5°	4470.0	4353.5	3819.0	2452.8	1456.3	786.2	444.9	340.3	289.5	263.1	246.0
30°	4870.3	4723.8	4203.8	2553.2	1349.1	665.5	391.0	310.2	259.5	231.5	220.6
32.5°	5161.4	5039.7	4505.2	2625.8	1234.7	586.8	349.6	283.8	242.4	213.9	197.8
35°	5503.7	5366.0	4763.6	2641.8	1161.1	537.1	314.4	255.3	210.3	184.9	167.8
37.5°	5873.5	5702.1	5062.0	2606.6	1103.6	512.7	288.0	242.4	196.3	170.4	152.3
40°	6282.6	6088.9	5348.4	2555.8	1047.2	504.4	267.8	232.5	185.4	159.0	140.4
42.5°	6713.5	6485.1	5596.4	2502.5	1011.5	475.9	265.7	222.7	177.1	148.6	130.0
45°	7075.5	6844.0	5851.2	2484.9	986.1	444.9	274.5	216.0	171.4	140.4	122.2
47.5°	7364.0	7144.9	6112.3	2524.2	971.6	416.4	250.1	224.8	168.3	133.1	115.5
50°	7708.4	7460.3	6480.0	2641.8	950.3	387.9	226.3	257.4	168.3	128.4	109.8
52.5°	8140.3	7894.9	6890.1	2824.1	907.9	348.5	203.5	257.9	169.9	122.2	102.5
55°	8683.6	8505.5	7475.9	3024.0	840.0	290.5	176.1	221.7	163.7	110.8	95.8
57.5°	9204.6	9059.1	8009.8	3160.7	749.4	226.8	153.3	178.7	149.7	97.4	85.5
59°	9347.1	9188.1	8205.6	3167.0	681.6	197.8	141.9	147.6	146.6	91.2	79.2
60°	9347.1	9178.2	8262.1	3133.8	632.4	181.8	134.7	131.5	152.8	87.0	75.6
62.5°	9177.7	8940.5	8078.7	2909.6	515.8	154.9	117.6	108.8	137.2	78.2	66.8
65°	8825.5	8480.1	7454.1	2504.0	459.9	141.9	101.5	89.1	95.3	68.9	58.5
67.5°	8238.2	7770.1	6553.5	2022.9	437.6	138.3	87.5	75.6	72.0	59.0	51.3
70°	7204.0	6684.5	5460.2	1590.5	418.5	136.7	73.5	63.7	58.0	49.7	43.5
72.5°	5243.2	4701.5	3876.5	1243.5	407.1	139.8	59.0	53.3	47.6	38.8	33.7
75°	2999.2	2644.4	2178.8	821.4	347.0	133.6	45.6	44.5	34.2	28.0	23.3
77.5°	1549.6	1502.4	1305.6	315.4	166.2	58.5	30.0	25.9	20.2	17.1	14.0
80°	668.6	661.4	572.3	91.2	44.0	32.6	17.1	10.9	9.3	7.3	5.7
82.5°	231.0	231.0	203.5	30.6	19.7	16.1	2.1	0.0	0.0	0.0	0.0
85°	46.6	52.3	36.8	0.0	6.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P387036

CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1
2.5°	3105.8	3043.2	3039.0	2999.7	2950.5	2928.2	2915.3	2938.0	2966.0	2969.1	3011.1
5°	2410.8	2345.1	2372.5	2302.6	2316.6	2302.6	2279.8	2283.9	2296.4	2257.5	2305.7
7.5°	1693.0	1643.3	1674.9	1656.2	1681.1	1690.9	1677.0	1656.2	1595.1	1587.9	1629.8
10°	1276.1	1219.7	1186.0	1150.8	1158.5	1174.6	1169.4	1154.4	1115.6	1117.6	1158.0
12.5°	1025.4	962.3	895.4	809.0	787.7	799.6	787.7	778.9	741.6	744.7	780.5
15°	777.9	726.1	656.2	586.8	549.0	552.6	519.5	496.1	472.8	444.9	466.6
17.5°	525.2	493.6	472.8	452.1	407.1	396.7	354.8	309.7	292.1	279.1	288.5
20°	371.9	354.8	346.5	345.4	319.5	306.6	265.7	237.7	228.9	226.3	232.0
22.5°	310.7	298.3	286.4	279.7	266.7	251.7	220.6	206.6	200.4	197.3	201.5
25°	270.3	261.0	248.6	237.2	232.0	216.0	193.7	183.3	179.2	176.1	178.2
27.5°	240.3	232.0	217.5	210.3	206.1	192.1	173.0	164.7	161.1	160.0	159.5
30°	216.5	208.7	195.2	187.0	179.7	167.3	155.9	147.6	144.0	142.9	141.9
32.5°	192.7	186.4	177.6	169.4	161.6	150.2	140.4	133.6	127.9	126.9	126.4
35°	162.6	156.4	151.7	151.2	144.0	133.1	125.8	117.0	112.4	110.8	111.3
37.5°	144.5	136.2	125.8	129.5	127.4	119.6	109.8	101.0	96.3	95.3	95.3
40°	133.1	124.3	112.4	106.2	112.4	110.8	95.3	86.5	81.8	81.3	80.3
42.5°	122.2	113.4	100.0	89.6	92.7	97.4	82.3	74.1	69.4	68.4	66.8
45°	114.5	105.1	90.1	78.2	72.0	81.8	70.4	60.1	57.5	55.4	54.4
47.5°	107.2	98.4	81.3	67.8	57.5	59.0	56.5	49.2	46.1	44.0	43.5
50°	101.0	91.7	73.5	58.0	47.6	43.5	45.6	38.8	36.3	34.2	33.1
52.5°	93.7	84.9	65.3	50.2	39.9	34.2	34.7	30.6	28.0	26.4	25.9
55°	88.0	79.2	58.5	44.0	35.2	28.0	24.9	23.8	22.3	21.2	20.7
57.5°	80.3	72.0	51.8	37.3	30.0	22.8	19.2	19.2	18.6	17.6	17.1
59°	75.6	68.4	47.6	33.7	27.4	19.7	17.1	17.6	17.1	16.1	15.5
60°	72.0	65.3	44.5	31.1	25.9	18.1	15.5	16.6	16.1	15.0	14.5
62.5°	63.7	59.0	38.3	25.9	22.8	14.5	12.9	14.0	14.0	13.5	12.9
65°	55.9	50.8	32.6	21.8	21.2	12.4	10.4	12.4	12.9	11.9	10.9
67.5°	48.7	43.5	28.5	17.6	19.7	9.8	7.8	10.4	14.0	10.9	9.8
70°	41.4	36.3	22.3	14.0	20.7	6.7	6.2	9.3	16.6	11.9	9.3
72.5°	32.1	28.0	15.5	10.4	22.3	4.7	4.7	7.8	18.6	12.9	8.8
75°	22.3	18.1	9.3	6.2	18.1	3.1	3.1	7.3	17.6	11.9	8.3
77.5°	12.9	9.8	3.1	0.5	9.3	0.0	0.5	5.2	12.4	7.3	3.6
80°	4.7	2.1	0.0	0.0	5.7	0.0	0.0	0.0	1.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P387036

CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1
2.5°	3021.9	3091.9	3154.5	3249.3	3361.7	3491.2	3602.5	3722.1	3834.5	3881.1	3913.3
5°	2315.5	2402.0	2503.0	2642.3	2827.7	3056.1	3270.0	3511.9	3771.9	3901.9	4024.1
7.5°	1637.1	1725.1	1850.5	1998.6	2222.8	2494.7	2774.4	3108.4	3460.6	3666.2	3868.7
10°	1177.2	1285.4	1402.5	1605.0	1832.8	2090.8	2378.7	2751.6	3144.2	3372.0	3616.0
12.5°	801.2	924.5	1101.6	1328.4	1596.2	1848.9	2099.0	2454.8	2910.6	3136.4	3397.9
15°	480.6	549.0	736.5	999.0	1327.4	1642.3	1916.2	2273.1	2758.9	3035.4	3307.3
17.5°	296.2	327.8	429.9	645.3	990.2	1388.5	1764.0	2211.4	2780.6	3117.2	3408.3
20°	236.2	248.6	281.2	381.2	656.2	1108.8	1592.5	2199.0	2958.2	3372.6	3684.9
22.5°	205.1	217.0	238.8	277.1	412.8	830.2	1429.9	2210.4	3213.1	3755.3	4119.9
25°	180.7	191.1	211.8	243.4	302.5	584.7	1255.9	2261.2	3545.0	4230.2	4617.6
27.5°	161.6	170.4	189.6	218.6	259.5	408.1	1058.6	2322.8	3938.6	4716.0	5098.2
30°	144.0	151.7	168.8	195.8	225.3	313.8	842.1	2364.7	4332.7	5098.2	5441.6
32.5°	129.0	134.7	150.2	173.0	195.8	250.1	640.1	2358.0	4625.4	5416.2	5688.6
35°	113.4	119.1	132.6	152.3	170.4	206.6	503.4	2232.1	4880.2	5746.1	5971.4
37.5°	96.3	103.6	116.5	134.1	146.6	181.8	407.1	2080.4	5138.6	6123.1	6286.8
40°	81.8	89.1	100.5	119.6	127.4	172.5	312.8	1895.5	5429.1	6544.7	6632.7
42.5°	67.8	74.6	86.5	103.1	120.2	148.6	231.5	1684.2	5708.3	6905.2	6948.1
45°	54.9	61.6	74.1	90.6	128.4	123.3	179.2	1457.9	5933.6	7205.0	7219.0
47.5°	43.5	49.7	62.7	85.5	119.6	98.4	127.9	1280.2	6122.6	7439.1	7402.3
50°	33.7	38.8	52.3	97.9	104.6	81.3	96.8	1221.2	6292.0	7584.1	7488.8
52.5°	26.4	31.1	43.0	91.7	81.3	67.3	81.3	1276.6	6524.0	7704.3	7537.5
55°	21.2	25.9	33.7	52.3	55.4	57.0	69.4	1328.4	6924.3	7986.0	7824.9
57.5°	17.6	22.3	27.4	36.8	41.9	48.2	61.6	1334.1	7396.1	8454.2	8301.9
59°	16.1	20.2	24.9	32.6	36.8	44.0	58.0	1303.0	7562.4	8624.6	8548.5
60°	15.0	19.2	23.3	30.0	34.2	41.4	55.9	1273.5	7569.6	8618.4	8653.6
62.5°	12.9	17.1	20.7	25.4	29.0	35.2	50.2	1164.2	7263.0	8336.1	8590.4
65°	11.4	15.0	18.6	21.8	24.9	31.6	45.6	964.8	6739.4	7880.9	8158.0
67.5°	10.4	12.9	17.1	19.2	22.3	28.0	40.4	687.8	6085.3	7324.1	7503.8
70°	9.3	12.4	15.5	17.6	20.2	24.3	34.7	395.2	5138.6	6509.0	6636.9
72.5°	8.8	11.9	14.0	16.6	18.1	21.8	31.6	185.9	3762.5	5214.2	5548.3
75°	7.8	10.9	12.9	15.5	17.1	19.7	26.9	89.1	2502.5	3773.4	4153.0
77.5°	4.7	8.8	11.9	14.0	15.0	17.1	22.3	51.3	1597.2	2611.8	3076.3
80°	0.0	3.1	8.8	11.9	12.9	14.5	17.1	40.4	854.5	1492.1	1790.9
82.5°	0.0	0.0	6.2	9.3	8.8	9.8	12.9	25.4	385.3	975.2	1099.0
85°	0.0	0.0	2.1	7.3	6.2	4.7	8.8	8.8	84.4	493.6	615.8
87.5°	0.0	0.0	0.0	0.5	3.1	2.1	3.6	1.0	0.5	36.8	149.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P387036

CATALOG NUMBER: GWC-SA2D-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1	3561.1
2.5°	4025.6	4064.0	4128.7	4159.3	4144.2	4080.5	4004.4	3926.7	3881.1	3899.3
5°	4273.2	4470.5	4584.4	4622.3	4559.1	4416.1	4229.2	3982.6	3895.1	3871.3
7.5°	4273.2	4644.5	4879.7	4921.1	4780.2	4500.0	4149.4	3764.6	3636.7	3590.1
10°	4123.0	4628.5	4956.3	5022.1	4825.3	4406.3	3936.6	3497.4	3345.6	3297.5
12.5°	3953.6	4498.0	4843.4	4934.0	4772.4	4313.1	3789.0	3316.6	3138.0	3096.0
15°	3849.5	4337.4	4623.3	4689.1	4620.7	4258.7	3753.7	3262.3	3052.0	3011.6
17.5°	3886.8	4213.1	4316.2	4354.5	4400.6	4239.5	3849.5	3381.4	3115.2	3076.8
20°	4027.2	4082.1	4028.7	4076.9	4201.2	4258.2	4077.9	3669.3	3349.8	3298.5
22.5°	4265.4	4014.2	3864.6	3883.7	4035.0	4319.8	4427.0	4080.5	3711.8	3647.6
25°	4543.0	4069.1	3773.4	3756.3	3911.7	4401.1	4746.0	4528.0	4140.1	4069.1
27.5°	4892.1	4192.4	3754.8	3737.7	3868.7	4477.2	5011.2	4970.3	4591.2	4470.0
30°	5161.4	4313.6	3810.2	3770.8	3911.7	4530.1	5224.1	5345.8	4950.6	4870.3
32.5°	5354.6	4456.5	3900.3	3843.3	4032.9	4621.2	5388.2	5689.6	5283.1	5161.4
35°	5501.6	4611.9	4045.8	3952.1	4199.6	4759.5	5542.0	6055.8	5636.8	5503.7
37.5°	5639.4	4829.9	4273.2	4161.3	4461.2	4982.2	5704.7	6471.2	6032.5	5873.5
40°	5831.6	5077.0	4623.8	4524.4	4900.9	5285.7	5907.7	6904.1	6482.6	6282.6
42.5°	6023.7	5342.1	4982.7	5009.6	5449.3	5654.4	6169.7	7361.9	6926.9	6713.5
45°	6199.3	5615.6	5493.9	5618.2	5958.4	6058.9	6430.2	7626.6	7281.7	7075.5
47.5°	6355.7	5957.4	6001.9	6332.9	6537.4	6425.1	6625.0	7855.0	7545.8	7364.0
50°	6537.4	6399.7	6671.6	7139.8	7204.0	6756.5	6802.1	8125.3	7854.5	7708.4
52.5°	6736.3	6865.8	7413.2	7826.0	7805.3	7116.5	6980.3	8428.3	8277.6	8140.3
55°	6962.1	7242.3	8066.3	8468.2	8450.6	7518.4	7275.5	8802.7	8807.9	8683.6
57.5°	7297.2	7566.5	8509.6	8987.6	9017.2	7982.4	7775.7	9222.2	9287.5	9204.6
59°	7537.5	7776.8	8685.2	9204.6	9324.8	8341.3	8141.4	9465.7	9422.7	9347.1
60°	7715.7	7910.4	8772.2	9318.1	9503.5	8584.7	8411.2	9608.6	9438.7	9347.1
62.5°	8156.4	8201.5	8929.1	9446.5	9709.1	9125.4	9170.5	9852.0	9327.4	9177.7
65°	8362.0	8385.3	8927.0	9216.5	9510.2	9546.4	9859.3	9859.3	9055.5	8825.5
67.5°	8276.0	8163.7	8484.2	8454.2	8747.3	9296.3	10118.2	9497.8	8535.5	8238.2
70°	7576.9	7144.4	7002.0	7015.0	7239.2	8086.0	9605.5	8434.0	7551.5	7204.0
72.5°	6304.4	5267.0	4915.4	5316.8	5375.3	6214.3	8185.9	6351.5	5569.0	5243.2
75°	5070.8	3712.8	3141.1	3564.7	3664.1	4547.7	6332.4	3955.7	3252.9	2999.2
77.5°	3642.9	2665.1	2253.9	2224.4	2352.8	2884.2	4493.3	1990.8	1660.4	1549.6
80°	2069.5	1754.1	1888.8	1782.1	1846.8	1803.3	2134.8	873.2	715.2	668.6
82.5°	1249.2	1036.8	1122.8	934.8	1182.9	1030.1	822.4	279.7	242.9	231.0
85°	812.6	566.6	295.2	197.8	407.6	658.3	183.9	76.1	58.5	46.6
87.5°	280.2	144.5	14.5	6.2	43.5	122.7	6.7	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)