

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639528

Luminaire Tested: GWS-SA5C-722-U-SLR-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P639528  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA5C-722-U-SLR-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (80) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9357.6 lumens  
Efficiency: N/A  
Efficacy: 59.4 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 157.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P639528  
 CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 29.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P639528  
CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P639528

CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2095.4	0.0	2095.4
	% Fixture	22.4	0.0	22.4
<b>Street Side</b>	Lumens	7262.2	0.0	7262.2
	% Fixture	77.6	0.0	77.6
<b>Total</b>	Lumens	9357.6	0.0	9357.6
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.8	1.7
10°-20°	523.4	5.6
20°-30°	850.3	9.1
30°-40°	1313.8	14.0
40°-50°	2106.6	22.5
50°-60°	2879.2	30.8
60°-70°	1394.5	14.9
70°-80°	127.7	1.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9357.6	100.0
0°-180°	9357.6	100.0

**Coefficient of Utilization**



REPORT NUMBER: P639528


CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	915.5	9.8			
FM (30°-60°)	4981.3	53.2			
FH (60°-80°)	1365.1	14.6			G1/1800
FVH (80°-90°)	0.4	0.0			G0/10
BL (0°-30°)	620.0	6.6	B2/1000		
BM (30°-60°)	1318.3	14.1	B2/2500		
BH (60°-80°)	157.1	1.7	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G1**

Type III Short





REPORT NUMBER: P639528

CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7
2.5°	1781.8	1793.1	1811.9	1852.2	1886.1	1908.8	1918.8	1916.3	1902.5	1892.4	1872.3
5°	1972.9	1972.9	2009.3	2101.1	2171.6	2215.6	2238.2	2224.4	2196.7	2152.7	2084.8
7.5°	2140.1	2146.4	2208.0	2338.8	2445.7	2508.5	2545.0	2537.5	2488.4	2404.2	2268.4
10°	2270.9	2278.4	2360.2	2519.9	2645.6	2709.7	2763.8	2768.8	2714.8	2602.8	2446.9
12.5°	2397.9	2405.4	2490.9	2644.3	2755.0	2781.4	2829.2	2848.0	2834.2	2755.0	2592.8
15°	2534.9	2552.6	2625.5	2739.9	2786.4	2755.0	2786.4	2820.4	2866.9	2859.4	2713.5
17.5°	2669.5	2682.1	2756.3	2796.5	2744.9	2663.2	2678.3	2718.5	2824.2	2927.3	2833.0
20°	2794.0	2811.6	2873.2	2820.4	2664.5	2537.5	2538.7	2591.5	2752.5	2968.8	2954.9
22.5°	2924.7	2951.2	2995.2	2846.8	2590.3	2438.1	2444.4	2492.2	2695.9	3007.7	3093.2
25°	3095.8	3120.9	3149.8	2912.2	2566.4	2389.1	2413.0	2457.0	2695.9	3074.4	3264.2
27.5°	3327.1	3344.7	3346.0	3034.1	2607.9	2396.6	2446.9	2497.2	2776.4	3207.7	3493.1
30°	3617.6	3645.2	3608.8	3224.0	2737.4	2497.2	2571.4	2634.3	2949.9	3432.7	3830.1
32.5°	3970.9	4009.9	3960.9	3505.7	3007.7	2844.3	2978.8	3015.3	3226.5	3758.4	4212.3
35°	4385.9	4418.6	4365.7	3895.5	3639.0	3669.1	3913.1	3866.6	3782.3	4159.5	4658.7
37.5°	4841.0	4871.2	4769.4	4486.5	4572.0	4702.7	5092.5	4932.8	4661.2	4676.3	5142.8
40°	5258.5	5291.2	5131.5	5129.0	5305.0	5543.9	6014.2	5794.2	5424.5	5352.8	5596.8
42.5°	5691.1	5713.7	5569.1	5471.0	5870.9	6362.5	6860.5	6563.7	5930.0	5852.0	6165.1
45°	6308.5	6356.2	6098.5	5639.5	6380.1	7304.3	7998.4	7418.7	6274.5	6211.6	7035.2
47.5°	7216.3	7251.5	6725.9	5745.1	6854.2	8477.5	9420.6	8527.8	6577.5	6434.2	8224.8
50°	7967.0	7990.9	7303.1	5860.8	7358.4	9742.5	11041.4	9843.0	6918.3	6802.6	9335.0
52.5°	8520.2	8610.8	8061.3	6098.5	8021.0	11230.0	12835.7	11401.0	7450.2	7514.3	10255.5
55°	8634.7	8757.9	8579.3	6244.3	8604.5	12745.2	14493.0	12795.5	7980.8	8053.7	10564.8
57.5°	7588.5	7686.6	7835.0	5655.9	8590.7	13439.3	15454.9	13258.2	7739.4	7222.6	9406.7
60°	5684.8	5752.7	6021.8	4323.0	7900.3	12825.6	14705.5	12471.0	6767.4	5511.2	7167.3
62.5°	3371.1	3401.3	3742.1	2800.3	6557.4	11045.1	12195.7	10761.0	5347.8	3706.9	4389.6
65°	1293.9	1281.3	1541.6	1381.9	4822.2	8798.1	9071.0	8203.4	3669.1	1698.8	1673.6
67.5°	199.9	191.1	257.8	408.7	3478.0	6097.2	5985.3	5912.4	2298.6	396.1	345.8
70°	45.3	45.3	55.3	120.7	2125.0	3582.4	3833.9	3655.3	1471.2	84.2	45.3
72.5°	21.4	21.4	26.4	51.6	769.5	1476.2	1720.1	1693.7	477.8	27.7	16.3
75°	7.5	8.8	8.8	11.3	46.5	76.7	176.0	125.7	30.2	0.0	0.0
77.5°	2.5	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	1.3	1.3	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P639528

CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7
2.5°	1828.3	1819.5	1786.8	1742.8	1700.0	1662.3	1623.3	1576.8	1542.8	1503.9	1491.3
5°	2032.0	1976.7	1887.4	1794.3	1708.8	1635.9	1565.5	1490.0	1434.7	1379.4	1360.5
7.5°	2204.2	2122.5	1977.9	1838.3	1721.4	1618.3	1516.4	1413.3	1332.9	1267.5	1247.4
10°	2358.9	2264.6	2071.0	1898.7	1751.6	1632.1	1508.9	1379.4	1275.0	1197.1	1178.2
12.5°	2492.2	2382.8	2150.2	1944.0	1764.2	1627.1	1507.6	1404.5	1310.2	1220.9	1197.1
15°	2604.1	2483.4	2216.8	1974.1	1745.3	1564.2	1459.9	1443.5	1436.0	1337.9	1291.4
17.5°	2713.5	2577.7	2270.9	1988.0	1692.5	1453.6	1378.1	1452.3	1531.5	1467.4	1408.3
20°	2827.9	2673.3	2326.2	1990.5	1604.5	1329.1	1316.5	1433.5	1534.0	1513.9	1458.6
22.5°	2962.5	2792.7	2395.4	1989.2	1493.8	1223.5	1271.2	1397.0	1478.7	1477.5	1433.5
25°	3157.4	2943.6	2488.4	1996.8	1373.1	1141.7	1220.9	1335.4	1402.0	1399.5	1363.0
27.5°	3366.1	3123.4	2609.1	2015.6	1270.0	1094.0	1161.9	1251.1	1309.0	1306.5	1275.0
30°	3659.1	3330.9	2724.8	2016.9	1195.8	1068.8	1096.5	1158.1	1213.4	1207.1	1183.2
32.5°	4014.9	3564.8	2821.6	1945.2	1149.3	1044.9	1028.6	1060.0	1102.8	1094.0	1087.7
35°	4445.0	3842.7	2904.6	1788.0	1077.6	997.1	953.1	959.4	989.6	994.6	992.1
37.5°	4935.4	4173.4	3007.7	1580.6	980.8	928.0	868.9	863.8	881.4	897.8	910.4
40°	5419.5	4545.6	3147.3	1370.6	892.8	840.0	783.4	770.8	778.3	807.3	833.7
42.5°	5963.9	4976.8	3298.2	1190.8	832.4	743.1	689.1	665.2	686.5	733.1	764.5
45°	6748.5	5581.7	3445.3	1047.4	807.3	657.6	584.7	582.2	606.1	666.4	701.6
47.5°	7850.0	6363.8	3542.1	935.5	806.0	591.0	504.2	519.3	547.0	606.1	646.3
50°	8923.9	7343.3	3435.3	850.0	779.6	547.0	443.9	474.0	501.7	553.3	594.8
52.5°	9571.4	7870.2	3019.1	769.5	697.9	526.9	384.8	437.6	442.6	489.1	533.1
55°	9503.5	7529.4	2312.4	645.1	577.2	497.9	323.2	394.8	397.3	432.6	470.3
57.5°	8248.6	6464.4	1588.1	523.1	433.8	411.2	266.6	333.2	357.1	378.5	406.1
60°	6147.5	4716.6	707.9	425.0	275.4	277.9	227.6	251.5	287.9	313.1	337.0
62.5°	3622.6	2713.5	287.9	255.3	152.1	174.8	183.6	183.6	206.2	225.1	240.2
65°	1369.3	949.3	116.9	128.3	79.2	81.7	108.1	133.3	150.9	167.2	187.4
67.5°	240.2	166.0	60.4	47.8	46.5	41.5	55.3	86.8	96.8	109.4	118.2
70°	40.2	34.0	25.1	23.9	21.4	22.6	36.5	61.6	67.9	71.7	75.4
72.5°	11.3	10.1	7.5	6.3	5.0	6.3	22.6	47.8	50.3	52.8	56.6
75°	0.0	0.0	0.0	0.0	0.0	0.0	8.8	34.0	36.5	37.7	41.5
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.5	10.1	12.6	10.1
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P639528

CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7
2.5°	1483.7	1458.6	1444.8	1437.2	1437.2	1427.2	1415.8	1412.1	1428.4	1428.4	1456.1
5°	1336.6	1316.5	1293.9	1280.0	1258.7	1262.4	1249.9	1248.6	1265.0	1272.5	1301.4
7.5°	1234.8	1209.6	1195.8	1187.0	1175.7	1170.7	1159.3	1155.6	1164.4	1176.9	1204.6
10°	1166.9	1163.1	1161.9	1168.1	1168.1	1161.9	1151.8	1145.5	1148.0	1171.9	1203.3
12.5°	1184.5	1192.0	1194.5	1204.6	1209.6	1204.6	1197.1	1199.6	1215.9	1259.9	1306.5
15°	1261.2	1254.9	1252.4	1257.4	1261.2	1256.2	1253.6	1272.5	1329.1	1392.0	1444.8
17.5°	1342.9	1302.7	1285.1	1285.1	1287.6	1285.1	1287.6	1324.1	1415.8	1478.7	1517.7
20°	1384.4	1310.2	1282.6	1276.3	1281.3	1282.6	1291.4	1332.9	1433.5	1477.5	1486.3
22.5°	1371.8	1278.8	1247.4	1242.3	1247.4	1252.4	1261.2	1296.4	1390.7	1413.3	1409.6
25°	1309.0	1217.2	1192.0	1192.0	1203.3	1202.1	1205.9	1231.0	1309.0	1322.8	1316.5
27.5°	1229.8	1143.0	1121.6	1134.2	1144.2	1141.7	1143.0	1164.4	1222.2	1226.0	1219.7
30°	1149.3	1073.8	1053.7	1068.8	1082.6	1080.1	1081.4	1102.8	1139.2	1135.4	1126.6
32.5°	1067.5	1012.2	997.1	1005.9	1027.3	1024.8	1029.8	1052.5	1066.3	1049.9	1039.9
35°	992.1	963.2	951.9	956.9	973.2	977.0	985.8	1000.9	1000.9	980.8	963.2
37.5°	921.7	917.9	910.4	904.1	919.2	930.5	943.1	960.7	935.5	906.6	890.2
40°	856.3	872.6	862.6	846.2	855.0	871.4	896.5	910.4	880.2	851.3	823.6
42.5°	795.9	823.6	819.8	799.7	807.3	822.3	851.3	862.6	827.4	794.7	768.3
45°	738.1	777.1	779.6	754.4	762.0	777.1	811.0	814.8	769.5	734.3	715.5
47.5°	687.8	730.6	731.8	713.0	715.5	736.8	768.3	769.5	718.0	685.3	661.4
50°	640.0	689.1	692.8	676.5	679.0	704.2	730.6	725.5	670.2	636.3	614.9
52.5°	582.2	648.8	657.6	650.1	660.1	680.3	696.6	679.0	614.9	580.9	562.1
55°	519.3	606.1	624.9	619.9	631.2	647.6	651.3	640.0	559.5	525.6	508.0
57.5°	446.4	499.2	531.9	521.8	530.6	547.0	558.3	549.5	489.1	462.7	447.6
60°	369.7	404.9	412.4	396.1	388.5	417.5	443.9	432.6	381.0	364.7	347.0
62.5°	270.3	310.6	315.6	294.2	285.4	316.9	339.5	328.2	271.6	254.0	240.2
65°	216.3	254.0	264.1	243.9	238.9	262.8	276.6	249.0	208.7	189.9	174.8
67.5°	142.1	172.3	198.7	197.4	187.4	194.9	184.8	162.2	133.3	123.2	113.2
70°	88.0	105.6	122.0	128.3	127.0	124.5	110.7	94.3	85.5	81.7	76.7
72.5°	67.9	85.5	98.1	101.9	103.1	99.3	88.0	72.9	64.1	59.1	55.3
75°	50.3	64.1	74.2	79.2	81.7	79.2	67.9	57.8	49.0	45.3	41.5
77.5°	17.6	21.4	26.4	28.9	27.7	26.4	23.9	23.9	18.9	17.6	15.1
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P639528

CATALOG NUMBER: GWS-SA5C-722-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7	1644.7
2.5°	1487.5	1510.2	1551.6	1589.4	1629.6	1671.1	1716.4	1762.9	1784.3	1781.8
5°	1345.4	1394.5	1462.4	1536.6	1619.6	1708.8	1808.2	1910.0	1954.0	1972.9
7.5°	1256.2	1325.3	1414.6	1508.9	1618.3	1745.3	1894.9	2054.6	2118.7	2140.1
10°	1267.5	1347.9	1422.1	1513.9	1630.9	1795.6	1981.7	2171.6	2247.0	2270.9
12.5°	1359.3	1376.9	1397.0	1472.4	1619.6	1833.3	2060.9	2287.2	2374.0	2397.9
15°	1442.3	1360.5	1322.8	1392.0	1579.3	1859.7	2141.4	2411.7	2507.3	2534.9
17.5°	1446.0	1322.8	1238.6	1292.6	1513.9	1871.0	2220.6	2538.7	2643.1	2669.5
20°	1399.5	1281.3	1173.2	1174.4	1424.7	1868.5	2286.0	2653.1	2770.1	2794.0
22.5°	1331.6	1232.3	1120.4	1081.4	1329.1	1863.5	2357.7	2775.1	2902.1	2924.7
25°	1256.2	1169.4	1070.1	1011.0	1233.5	1868.5	2458.2	2934.8	3074.4	3095.8
27.5°	1174.4	1100.2	1031.1	983.3	1153.0	1887.4	2579.0	3138.5	3304.5	3327.1
30°	1088.9	1033.6	1005.9	977.0	1102.8	1892.4	2709.7	3376.2	3586.1	3617.6
32.5°	1004.7	974.5	975.8	980.8	1055.0	1857.2	2829.2	3640.2	3920.6	3970.9
35°	926.7	917.9	943.1	968.2	985.8	1766.7	2933.5	3952.1	4334.3	4385.9
37.5°	860.1	867.6	899.1	924.2	910.4	1638.4	3071.9	4341.9	4797.0	4841.0
40°	795.9	814.8	851.3	862.6	852.5	1488.8	3237.8	4717.8	5198.2	5258.5
42.5°	736.8	750.7	802.2	804.7	836.2	1336.6	3397.5	5122.7	5659.6	5691.1
45°	689.1	686.5	739.4	755.7	857.6	1168.1	3553.5	5662.1	6263.2	6308.5
47.5°	642.5	640.0	652.6	726.8	866.4	1012.2	3708.1	6451.8	7138.3	7216.3
50°	598.5	602.3	563.3	713.0	818.6	892.8	3778.5	7182.4	7934.3	7967.0
52.5°	559.5	545.7	477.8	667.7	716.7	779.6	3578.6	7514.3	8427.2	8520.2
55°	504.2	427.5	393.6	541.9	565.8	680.3	2931.0	7321.9	8469.9	8634.7
57.5°	431.3	335.7	334.5	399.9	399.9	631.2	1877.3	6255.6	7299.3	7588.5
60°	332.0	260.3	276.6	277.9	256.5	460.2	1053.7	4531.7	5396.8	5684.8
62.5°	236.4	198.7	208.7	166.0	147.1	230.1	505.5	2609.1	3330.9	3371.1
65°	158.4	134.5	109.4	91.8	90.5	98.1	208.7	943.1	1146.8	1293.9
67.5°	104.4	81.7	57.8	57.8	65.4	65.4	79.2	155.9	218.8	199.9
70°	67.9	56.6	36.5	35.2	42.8	42.8	40.2	42.8	45.3	45.3
72.5°	50.3	42.8	21.4	18.9	23.9	25.1	22.6	21.4	21.4	21.4
75°	37.7	30.2	12.6	8.8	11.3	15.1	12.6	8.8	8.8	7.5
77.5°	15.1	11.3	5.0	3.8	6.3	8.8	7.5	3.8	2.5	2.5
80°	1.3	2.5	2.5	2.5	3.8	5.0	6.3	2.5	1.3	1.3
82.5°	0.0	1.3	1.3	1.3	2.5	3.8	5.0	2.5	1.3	1.3
85°	0.0	0.0	0.0	0.0	2.5	3.8	2.5	1.3	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	1.3	3.8	2.5	1.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)