

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P385494

Luminaire Tested: **GWC-SA1A-735-U-SLL-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P385494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA1A-735-U-SLL-HSS
Description: GALLEON WALL LUMINAIRE
(1) 70 CRI, 3500K, 615mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3465.4 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G1


Input Watts (W): 34
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P385494
 CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.1 fc
 Type III - Medium - N/A

REPORT NUMBER: P385494
CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P385494

CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	520.0	0.0	520.0
	% Fixture	15.0	0.0	15.0
Street Side	Lumens	2945.4	0.0	2945.4
	% Fixture	85.0	0.0	85.0
Total	Lumens	3465.4	0.0	3465.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	2.5
10°-20°	173.6	5.0
20°-30°	245.7	7.1
30°-40°	361.2	10.4
40°-50°	519.1	15.0
50°-60°	730.8	21.1
60°-70°	853.5	24.6
70°-80°	435.4	12.6
80°-90°	57.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3465.4	100.0
0°-180°	3465.4	100.0

Coefficient of Utilization



REPORT NUMBER: P385494


CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	371.5	10.7			
FM (30°-60°)	1363.9	39.4			
FH (60°-80°)	1153.9	33.3			G1/1800
FVH (80°-90°)	56.1	1.6			G1/100
BL (0°-30°)	136.0	3.9	B1/500		
BM (30°-60°)	247.2	7.1	B1/1000		
BH (60°-80°)	135.1	3.9	B1/500		G1/500
BVH (80°-90°)	1.8	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type III Medium





REPORT NUMBER: P385494

CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1260.3	1262.3	1272.4	1296.1	1321.8	1323.8	1341.2	1323.3	1317.2	1288.4	1258.5
5°	1269.8	1277.3	1312.3	1381.8	1442.0	1461.3	1475.1	1440.0	1403.1	1332.5	1257.2
7.5°	1193.1	1205.8	1260.8	1391.1	1498.8	1546.4	1555.4	1500.4	1409.9	1293.7	1180.4
10°	1095.0	1109.4	1175.7	1335.9	1483.9	1565.4	1577.9	1505.8	1375.8	1231.1	1097.6
12.5°	1015.5	1032.4	1100.2	1273.9	1432.5	1522.8	1547.4	1487.6	1346.2	1186.5	1040.9
15°	978.8	998.3	1069.5	1233.8	1375.6	1446.6	1467.0	1441.2	1329.9	1179.5	1027.8
17.5°	999.9	1020.9	1094.5	1237.3	1322.0	1352.4	1368.8	1379.3	1329.9	1222.1	1066.2
20°	1086.1	1108.8	1186.5	1272.2	1277.7	1266.3	1283.9	1320.9	1345.3	1302.8	1158.5
22.5°	1205.2	1231.8	1319.7	1332.2	1256.0	1213.1	1215.5	1273.4	1373.4	1405.2	1286.5
25°	1350.6	1383.1	1472.4	1421.5	1265.0	1181.5	1180.6	1234.4	1400.8	1507.8	1429.2
27.5°	1494.9	1530.6	1609.1	1530.5	1302.3	1175.7	1174.1	1222.5	1427.5	1599.1	1584.9
30°	1615.9	1650.6	1718.2	1609.5	1342.5	1189.2	1181.3	1235.1	1443.5	1658.3	1698.6
32.5°	1714.3	1742.2	1796.9	1663.8	1385.5	1215.3	1198.2	1268.9	1470.5	1708.4	1803.0
35°	1822.7	1852.1	1873.9	1715.5	1433.8	1252.9	1228.4	1322.7	1512.2	1759.3	1917.4
37.5°	1946.3	1975.5	1972.9	1762.8	1495.0	1315.1	1299.5	1407.7	1577.1	1809.7	2045.2
40°	2067.3	2097.2	2075.8	1814.4	1566.9	1417.7	1406.2	1535.4	1663.9	1874.2	2194.8
42.5°	2180.5	2212.9	2167.3	1863.4	1652.6	1547.1	1566.7	1699.9	1772.6	1953.7	2323.9
45°	2271.8	2304.8	2243.9	1911.0	1742.9	1704.0	1763.2	1882.1	1903.3	2020.8	2411.0
47.5°	2338.2	2369.3	2297.1	1958.6	1858.5	1895.9	1999.1	2073.1	2021.3	2079.1	2473.0
50°	2380.5	2404.8	2312.7	2018.2	2010.1	2119.8	2244.9	2281.0	2132.4	2131.7	2548.1
52.5°	2407.4	2418.5	2324.2	2080.4	2168.4	2363.6	2485.5	2496.9	2246.8	2189.4	2649.4
55°	2500.2	2509.0	2405.6	2155.7	2299.3	2577.1	2703.2	2692.8	2376.4	2302.5	2768.9
57.5°	2658.4	2667.8	2573.8	2264.1	2405.1	2709.1	2861.0	2879.9	2528.3	2461.4	2897.0
60°	2737.9	2755.2	2721.8	2401.4	2507.7	2793.6	2968.5	3028.8	2718.0	2670.9	3021.1
62.5°	2665.8	2691.1	2739.6	2553.6	2609.6	2840.0	3002.0	3082.2	2912.4	2915.0	3097.6
65°	2522.0	2542.2	2624.6	2636.9	2668.7	2834.2	2919.3	3007.6	3031.4	3139.3	3093.4
67.5°	2348.3	2355.9	2425.8	2643.5	2583.1	2661.6	2670.7	2736.1	2937.3	3218.7	2969.1
70°	2098.3	2102.5	2163.5	2423.6	2219.8	2237.1	2223.4	2236.7	2525.3	3025.1	2655.5
72.5°	1688.7	1699.1	1785.9	2012.7	1617.2	1567.4	1674.5	1668.6	1944.8	2555.8	1972.3
75°	1243.4	1261.2	1392.4	1621.3	1135.0	1026.7	1104.8	1125.7	1382.6	1977.0	1233.3
77.5°	870.5	883.9	1010.9	1191.8	821.5	734.1	705.9	730.7	912.5	1430.1	621.3
80°	501.5	506.4	587.5	688.2	553.6	633.3	573.8	590.8	546.8	636.3	267.3
82.5°	328.1	329.0	360.6	409.6	344.8	400.6	296.5	379.0	336.4	255.6	87.0
85°	177.3	178.3	209.1	290.7	195.2	110.3	64.8	133.1	208.0	58.6	23.8
87.5°	19.5	17.8	63.0	105.7	54.2	10.1	3.5	14.9	33.3	3.8	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P385494

CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1243.2	1229.6	1195.6	1159.7	1130.7	1103.7	1076.5	1043.1	1017.3	1012.0	1003.6
5°	1216.6	1173.4	1102.2	1030.6	973.0	900.2	854.1	818.2	783.1	780.9	773.9
7.5°	1123.7	1066.9	966.5	867.6	786.5	717.2	647.2	600.5	563.7	550.8	543.1
10°	1034.4	970.5	845.3	732.4	659.9	598.7	549.5	500.5	456.2	425.6	411.9
12.5°	972.0	901.4	763.4	666.0	614.1	556.0	495.9	434.8	383.8	347.0	324.6
15°	947.8	872.5	735.9	639.7	575.8	502.2	425.4	355.6	298.9	265.6	245.5
17.5°	976.6	888.9	733.8	607.7	518.3	426.9	341.9	259.6	206.2	180.9	168.0
20°	1049.5	941.2	733.0	568.5	450.0	337.5	231.7	170.7	138.4	124.3	118.2
22.5°	1152.5	1007.8	739.6	529.7	378.9	241.1	159.9	125.4	108.9	101.3	97.9
25°	1285.2	1101.3	758.1	494.6	312.1	179.9	124.6	105.0	93.4	87.5	85.0
27.5°	1426.6	1209.1	787.0	464.1	257.8	143.4	106.7	90.0	81.6	77.5	75.2
30°	1543.1	1333.8	816.2	430.1	218.3	125.1	97.7	82.1	72.4	69.8	67.6
32.5°	1645.1	1428.2	836.9	399.4	192.6	111.1	88.3	73.4	66.8	61.7	59.5
35°	1750.7	1506.9	836.2	377.9	174.8	100.6	80.4	65.7	57.8	51.9	50.1
37.5°	1864.9	1595.7	822.0	359.5	167.1	92.2	76.0	61.5	53.6	47.8	45.5
40°	1998.7	1688.9	807.3	342.3	165.0	85.5	72.9	58.2	49.9	44.2	41.9
42.5°	2129.0	1772.9	794.5	329.4	155.8	85.4	70.1	55.8	47.0	41.3	38.7
45°	2233.2	1851.3	792.1	321.7	146.1	88.3	68.6	54.2	44.6	39.1	36.6
47.5°	2319.9	1936.3	807.9	316.3	136.9	80.6	72.2	53.0	42.6	37.1	34.3
50°	2423.0	2040.6	845.0	307.5	127.2	72.5	82.8	53.4	40.7	35.1	32.2
52.5°	2566.8	2185.1	899.5	292.5	113.9	65.2	81.4	53.6	38.7	33.0	30.1
55°	2728.0	2365.6	958.1	267.7	95.3	55.5	69.8	51.4	34.9	30.7	27.9
57.5°	2897.5	2529.2	992.8	238.2	75.8	47.9	55.8	46.8	30.9	27.6	25.7
60°	2924.1	2591.4	977.0	201.9	60.2	41.7	41.3	47.6	27.6	24.3	23.0
62.5°	2857.9	2513.3	899.9	169.6	50.4	36.6	34.0	41.5	25.0	21.7	20.4
65°	2730.6	2302.1	775.2	152.8	46.8	31.4	28.3	29.2	21.8	18.9	17.8
67.5°	2553.6	2020.0	636.4	143.4	46.3	27.0	24.1	22.2	18.9	16.4	15.4
70°	2191.9	1682.8	507.7	138.1	45.0	22.6	20.4	18.0	15.8	14.0	13.2
72.5°	1613.2	1192.5	395.0	132.4	45.3	18.0	17.8	14.9	12.7	10.8	10.5
75°	932.1	681.2	259.1	107.2	43.2	14.0	14.7	10.5	8.8	7.5	7.5
77.5°	496.8	415.5	98.6	44.6	15.8	8.8	8.4	6.2	5.5	4.6	4.4
80°	216.5	182.9	29.7	12.5	8.7	4.8	3.1	2.8	2.4	2.0	1.8
82.5°	76.7	66.1	9.7	6.1	3.8	0.0	0.0	0.0	0.0	0.0	0.0
85°	17.4	12.5	0.0	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P385494
 CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	986.1	982.5	961.2	961.9	965.8	971.1	958.4	964.3	980.2	995.5	1001.2
5°	762.5	763.4	750.4	758.5	765.6	770.6	749.9	750.2	762.9	780.1	789.1
7.5°	537.3	536.0	536.7	555.8	569.5	559.6	567.3	540.6	542.2	554.5	545.3
10°	399.4	381.3	371.2	385.6	400.6	395.1	381.9	373.1	379.2	392.9	391.8
12.5°	313.9	287.9	272.7	262.4	274.7	264.4	264.2	256.5	248.4	249.9	271.7
15°	236.1	217.2	199.2	182.5	182.2	178.8	161.2	141.5	139.9	140.8	152.2
17.5°	162.3	155.9	148.6	134.2	130.5	116.0	99.0	91.1	87.2	89.0	92.7
20°	114.1	111.6	112.4	104.7	99.3	85.5	75.5	72.4	71.8	73.6	75.3
22.5°	94.6	90.1	89.6	86.1	80.8	70.7	65.4	63.5	62.8	64.3	65.7
25°	82.8	78.3	76.5	74.4	68.6	61.7	58.4	56.8	56.0	56.9	57.8
27.5°	72.9	68.8	67.2	65.7	60.1	55.1	52.5	51.0	50.4	50.7	51.6
30°	65.5	61.9	59.7	58.0	53.2	49.7	47.4	45.9	45.3	45.3	46.1
32.5°	57.8	55.8	53.8	51.6	47.2	44.8	42.6	40.9	40.2	40.4	41.1
35°	48.1	47.4	47.9	45.8	42.0	40.0	37.8	36.0	35.4	35.6	36.3
37.5°	42.6	39.7	41.5	40.4	38.2	35.6	32.7	31.0	30.2	30.7	31.0
40°	39.3	35.6	34.3	35.4	35.1	30.9	28.3	26.6	25.9	26.1	26.4
42.5°	36.3	32.0	29.0	28.9	30.9	27.0	24.1	22.6	21.8	21.8	22.2
45°	33.4	28.9	25.3	22.5	25.9	22.8	20.2	18.9	17.8	17.8	18.0
47.5°	31.4	26.3	22.0	18.4	19.5	18.7	16.5	15.3	14.3	14.3	14.5
50°	29.4	23.7	19.1	15.4	14.7	15.4	13.4	12.0	11.4	11.2	11.5
52.5°	27.2	21.0	16.3	13.2	11.5	11.6	10.5	9.5	8.7	8.7	9.0
55°	25.1	18.9	14.1	11.2	9.5	8.7	8.4	7.7	7.0	7.0	7.4
57.5°	23.0	16.5	12.0	9.2	7.5	6.9	6.9	6.4	5.9	5.9	6.2
60°	21.0	14.3	9.9	7.5	5.9	5.7	5.9	5.4	5.1	5.1	5.4
62.5°	18.7	12.1	8.1	6.2	4.8	4.6	5.1	4.8	4.4	4.4	4.8
65°	16.0	10.3	6.4	4.8	3.6	3.6	4.2	3.9	3.6	3.6	3.9
67.5°	13.4	8.7	4.9	3.5	2.6	2.8	3.6	3.3	3.1	3.1	3.5
70°	11.2	6.8	3.5	2.2	1.5	2.2	2.8	2.8	2.8	2.8	3.1
72.5°	8.4	4.6	2.0	0.8	0.7	1.5	2.3	2.6	2.4	2.4	2.9
75°	5.4	2.6	0.7	0.0	0.0	0.8	1.8	2.2	2.2	2.0	2.4
77.5°	3.1	0.8	0.0	0.0	0.0	0.0	1.1	0.9	0.8	0.7	1.1
80°	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P385494
 CATALOG NUMBER: GWC-SA1A-735-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1024.4	1043.8	1071.0	1099.8	1144.4	1179.7	1214.3	1244.0	1255.5	1260.3
5°	810.8	839.2	879.1	930.3	1010.6	1082.8	1156.0	1229.8	1261.7	1269.8
7.5°	581.8	618.0	668.8	733.0	827.0	920.6	1022.9	1131.0	1180.6	1193.1
10°	430.6	475.0	533.0	600.6	690.5	786.6	898.2	1021.8	1078.3	1095.0
12.5°	305.5	365.4	443.2	525.5	603.3	689.1	802.0	938.2	997.6	1015.5
15°	179.4	237.4	329.4	439.6	539.3	626.3	740.9	895.3	960.8	978.8
17.5°	103.0	131.8	201.4	324.2	459.5	580.0	721.6	906.0	983.2	999.9
20°	78.6	87.8	116.0	208.8	366.3	534.5	721.6	966.4	1061.4	1086.1
22.5°	68.8	75.5	87.0	124.6	269.5	485.8	730.0	1053.7	1178.0	1205.2
25°	61.1	67.2	77.0	93.8	183.8	427.8	749.9	1160.9	1315.2	1350.6
27.5°	54.7	60.4	69.2	82.1	125.8	357.9	776.7	1286.7	1466.6	1494.9
30°	48.9	54.3	62.4	71.4	97.0	278.6	799.4	1405.2	1585.5	1615.9
32.5°	43.5	48.5	55.6	62.4	79.5	206.0	802.0	1499.1	1684.1	1714.3
35°	38.4	42.8	49.4	54.7	65.9	162.7	763.6	1580.5	1782.8	1822.7
37.5°	33.4	37.8	43.5	47.4	58.0	132.6	705.2	1671.4	1909.3	1946.3
40°	28.9	32.7	38.6	41.2	54.9	101.9	641.7	1766.5	2033.5	2067.3
42.5°	24.6	28.3	34.0	39.1	48.1	76.2	573.1	1855.9	2145.1	2180.5
45°	20.5	24.3	30.1	41.3	39.9	56.9	499.7	1915.1	2233.2	2271.8
47.5°	16.5	20.9	28.7	39.4	31.8	41.9	441.6	1971.2	2300.1	2338.2
50°	13.3	17.6	32.3	35.1	26.1	32.0	417.3	2021.5	2343.9	2380.5
52.5°	10.8	14.7	30.5	27.0	21.8	26.4	430.4	2102.9	2384.5	2407.4
55°	9.0	11.6	18.4	18.7	18.5	22.5	446.7	2219.8	2489.3	2500.2
57.5°	7.9	9.4	12.8	14.5	15.6	20.0	447.1	2387.6	2651.7	2658.4
60°	6.8	8.2	10.7	11.6	13.4	17.8	430.8	2446.2	2715.6	2737.9
62.5°	5.9	7.2	8.8	9.7	11.4	16.1	392.7	2361.3	2627.9	2665.8
65°	5.3	6.6	7.4	8.2	10.1	14.5	330.0	2191.5	2482.4	2522.0
67.5°	4.6	5.7	6.6	7.4	9.0	12.8	242.9	1994.4	2315.5	2348.3
70°	4.1	5.1	5.9	6.6	7.9	10.8	147.4	1692.3	2084.7	2098.3
72.5°	3.9	4.6	5.4	5.9	6.9	9.5	74.7	1243.7	1666.6	1688.7
75°	3.5	4.1	4.9	5.3	6.1	8.2	30.3	816.9	1207.8	1243.4
77.5°	2.8	3.8	4.4	4.8	5.3	6.8	15.4	522.0	847.5	870.5
80°	0.9	2.8	3.8	3.9	4.4	4.9	10.1	285.8	491.7	501.5
82.5°	0.0	1.8	2.9	2.8	3.1	3.8	6.6	135.9	324.6	328.1
85°	0.0	0.8	2.3	1.8	1.3	2.6	2.3	29.7	170.2	177.3
87.5°	0.0	0.0	0.2	0.8	0.7	0.9	0.3	0.2	15.4	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)