Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630651

Luminaire Tested: GWS-SA1E-727-U-5WQ-W

Issue Date: 1/10/2023

Report Generated By 670246102 / DESKTOP-G35701P

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

**Test Information**

| | |
|---|---|
| Test Method: | LM-79-2019 |
| Report Number: | P630651 |
| | TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-1) |
| Test Lab: | COOPER LIGHTING SOLUTIONS |
| Issue Date: | 1/10/2023 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS |
| Product Line: | McGRAW-EDISON |
| Catalog Number: | GWS-SA1E-727-U-5WQ-W |
| Description: | GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS |
| Light Source: | (16) 2700K CCT, 70 CRI LEDS |
| Ballast/Driver: | - |

**Summary**

| | |
|---|---|
| Lumens per Lamp: | N/A |
| Luminaire Lumens: | 6424.6 lumens |
| Efficiency: | N/A |
| Efficacy: | 110.0 lumens/watt |
| Luminous Opening: | Rectangular (W 0.5' x L: 0.5' x H: 0') |
| IES Classification: | Type V - Short |
| BUG Rating: | B3 - U0 - G1 |

| | |
|---|---|
| Input Watts (W): | 58.4 |
| Input Voltage (V): | 120 |
| Input Current (Ain): | NR |
| Voltage Rise (V): | NR |
| Power Factor: | NR |
| Total Harmonic Distortion (THDi): | NR |
| Frequency (hertz): | 0 |
| Stabilization Time: | NR |
| Operation Time: | NR |
| Ambient Temperature (°C): | NR |
| Test Distance: | 28.75 FT |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P630651
CATALOG NUMBER: GWS-SA1E-727-U-5WQ-W

## Iso-Footcandle Lines of Horizontal Illumination




Based on 10 foot mounting height. Maximum calculated value = 5 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P630651
CATALOG NUMBER: GWS-SA1E-727-U-5WQ-W

## Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P630651
CATALOG NUMBER: GWS-SA1E-727-U-5WQ-W

**FLUX DISTRIBUTION:**

| | | Downward | Upward | Total |
|---|---|---|---|---|
| **House Side** | Lumens | 3212.3 | 0.0 | 3212.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| **Street Side** | Lumens | 3212.3 | 0.0 | 3212.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| **Total** | Lumens | 6424.6 | 0.0 | 6424.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

**ZONAL LUMENS:**

| Zone | Lumens | % Fixture |
|---|---|---|
| 0°-10° | 47.3 | 0.7 |
| 10°-20° | 140.4 | 2.2 |
| 20°-30° | 251.8 | 3.9 |
| 30°-40° | 425.4 | 6.6 |
| 40°-50° | 747.4 | 11.6 |
| 50°-60° | 1441.8 | 22.4 |
| 60°-70° | 2091.9 | 32.6 |
| 70°-80° | 1196.9 | 18.6 |
| 80°-90° | 81.7 | 1.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 6424.6 | 100.0 |
| 0°-180° | 6424.6 | 100.0 |



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P630651
CATALOG NUMBER: GWS-SA1E-727-U-5WQ-W

## LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | | Lumens | % Fixture | Zone Rating/Lumen Limit B | U | G |
|---|---|---|---|---|---|---|
| FL | (0°-30°) | 219.8 | 3.4 | | | |
| FM | (30°-60°) | 1307.3 | 20.3 | | | |
| FH | (60°-80°) | 1644.4 | 25.6 | | | G1/1800 |
| FVH | (80°-90°) | 40.8 | 0.6 | | | G1/100 |
| BL | (0°-30°) | 219.8 | 3.4 | B1/500 | | |
| BM | (30°-60°) | 1307.3 | 20.3 | B2/2500 | | |
| BH | (60°-80°) | 1644.4 | 25.6 | B3/2500 | | G1/1800 |
| BVH | (80°-90°) | 40.8 | 0.6 | | | G1/100 |
| UL | (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH | (100°-180°) | 0.0 | 0.0 | | U0/0 | |

**BUG Rating: B3-U0-G1**
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P630651
CATALOG NUMBER: GWS-SA1E-727-U-5WQ-W

**CANDELA DISTRIBUTION (FULL):**

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|---|---|---|---|---|---|---|---|---|---|---|---|
| 0° | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 | 503.8 |
| 2.5° | 499.7 | 500.2 | 501.1 | 501.1 | 502.0 | 503.4 | 503.8 | 502.9 | 503.4 | 501.1 | 503.4 |
| 5° | 498.4 | 498.8 | 499.3 | 498.4 | 498.4 | 498.8 | 498.8 | 497.9 | 498.4 | 496.1 | 498.4 |
| 7.5° | 495.2 | 495.6 | 495.6 | 494.3 | 492.9 | 493.8 | 493.8 | 492.9 | 493.4 | 491.1 | 493.8 |
| 10° | 492.5 | 492.5 | 492.0 | 489.3 | 487.9 | 489.3 | 489.7 | 490.2 | 492.0 | 490.2 | 493.4 |
| 12.5° | 494.3 | 494.3 | 492.9 | 489.3 | 487.0 | 487.9 | 488.8 | 489.7 | 492.9 | 492.5 | 496.1 |
| 15° | 499.3 | 499.7 | 496.1 | 492.0 | 490.6 | 492.0 | 491.1 | 490.6 | 494.7 | 496.1 | 500.2 |
| 17.5° | 503.4 | 503.4 | 498.8 | 494.7 | 495.2 | 497.5 | 495.6 | 493.4 | 497.5 | 500.2 | 504.7 |
| 20° | 507.0 | 506.5 | 501.5 | 498.8 | 500.6 | 503.8 | 502.5 | 499.3 | 502.0 | 505.2 | 509.3 |
| 22.5° | 516.1 | 515.6 | 510.2 | 508.8 | 510.6 | 513.8 | 512.5 | 509.7 | 512.9 | 517.4 | 522.4 |
| 25° | 542.0 | 541.1 | 532.9 | 528.4 | 527.4 | 529.7 | 529.3 | 528.4 | 533.3 | 538.8 | 544.7 |
| 27.5° | 576.5 | 576.1 | 570.1 | 565.6 | 559.7 | 557.9 | 559.2 | 563.3 | 570.6 | 574.7 | 579.7 |
| 30° | 593.8 | 593.8 | 592.9 | 600.1 | 612.9 | 625.1 | 615.6 | 600.1 | 593.8 | 592.0 | 597.0 |
| 32.5° | 616.5 | 618.8 | 615.6 | 623.8 | 645.1 | 663.3 | 645.1 | 620.1 | 615.6 | 615.6 | 621.0 |
| 35° | 668.7 | 669.6 | 664.6 | 663.3 | 670.1 | 672.4 | 663.7 | 654.6 | 659.6 | 660.6 | 667.4 |
| 37.5° | 710.5 | 710.5 | 708.3 | 711.9 | 726.0 | 734.6 | 720.5 | 704.2 | 705.5 | 706.4 | 715.1 |
| 40° | 775.0 | 776.9 | 771.4 | 770.9 | 776.4 | 784.1 | 769.1 | 758.7 | 766.0 | 768.2 | 781.4 |
| 42.5° | 855.4 | 855.4 | 847.3 | 845.0 | 848.6 | 856.8 | 842.7 | 835.9 | 845.5 | 847.3 | 855.0 |
| 45° | 951.3 | 953.6 | 942.7 | 938.6 | 940.4 | 943.1 | 933.1 | 930.0 | 939.0 | 943.1 | 956.8 |
| 47.5° | 1068.1 | 1070.3 | 1060.8 | 1060.3 | 1058.5 | 1060.3 | 1050.8 | 1049.0 | 1056.2 | 1053.1 | 1067.6 |
| 50° | 1212.1 | 1216.2 | 1208.0 | 1219.3 | 1218.0 | 1223.4 | 1210.3 | 1200.7 | 1200.7 | 1192.1 | 1200.3 |
| 52.5° | 1373.4 | 1381.5 | 1385.6 | 1404.7 | 1419.2 | 1432.9 | 1411.1 | 1396.1 | 1374.3 | 1356.5 | 1378.8 |
| 55° | 1549.2 | 1546.9 | 1572.8 | 1614.6 | 1657.3 | 1689.5 | 1646.8 | 1599.6 | 1564.2 | 1527.4 | 1536.0 |
| 57.5° | 1703.2 | 1710.9 | 1745.0 | 1821.3 | 1905.8 | 1973.9 | 1897.2 | 1806.3 | 1725.9 | 1673.2 | 1680.5 |
| 60° | 1831.3 | 1837.6 | 1883.1 | 1993.0 | 2140.7 | 2234.7 | 2113.0 | 1963.0 | 1846.3 | 1773.6 | 1781.3 |
| 62.5° | 1949.4 | 1955.3 | 2001.2 | 2122.5 | 2308.8 | 2431.4 | 2274.2 | 2069.3 | 1939.4 | 1866.3 | 1870.8 |
| 65° | 2017.6 | 2021.2 | 2083.9 | 2211.5 | 2407.8 | 2534.5 | 2357.4 | 2146.1 | 2018.5 | 1944.0 | 1946.7 |
| 67.5° | 1893.5 | 1899.4 | 2031.6 | 2207.9 | 2426.9 | 2536.4 | 2361.0 | 2148.4 | 2004.8 | 1907.6 | 1909.9 |
| 70° | 1493.7 | 1488.7 | 1646.4 | 1949.4 | 2317.4 | 2460.0 | 2256.1 | 1987.1 | 1765.4 | 1629.6 | 1627.3 |
| 72.5° | 1138.9 | 1140.3 | 1228.0 | 1435.6 | 1889.4 | 2270.1 | 1990.7 | 1600.0 | 1361.1 | 1258.0 | 1253.9 |
| 75° | 825.9 | 838.6 | 910.0 | 1062.2 | 1321.6 | 1696.8 | 1498.7 | 1185.7 | 1025.8 | 964.0 | 954.9 |
| 77.5° | 372.1 | 388.4 | 487.9 | 666.9 | 883.6 | 937.7 | 941.3 | 805.0 | 607.4 | 504.7 | 488.8 |
| 80° | 108.6 | 116.3 | 149.5 | 255.8 | 411.6 | 532.0 | 422.5 | 355.3 | 221.2 | 173.5 | 165.4 |
| 82.5° | 45.9 | 52.2 | 64.1 | 70.9 | 119.5 | 246.7 | 153.6 | 97.7 | 90.9 | 73.6 | 67.2 |
| 85° | 19.5 | 20.9 | 26.8 | 28.6 | 38.6 | 52.7 | 48.6 | 44.1 | 42.2 | 32.7 | 30.0 |
| 87.5° | 8.2 | 8.2 | 8.2 | 7.3 | 6.8 | 7.3 | 10.0 | 12.7 | 16.8 | 13.2 | 12.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

# LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v6.13

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

## Test Information

| | |
|---|---|
| Test Method: | LM-79-2008 |
| Report Number: | SP1-1908-441-1-R4 |
| Test Lab: | COOPER LIGHTING SOLUTIONS |
| Photometer: | SP1 - 76IN SPHERE |
| Measurement Geometry: | 4π |
| Issue Date: | 10/28/2024 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS |
| Product Line: | McGRAW-EDISON |
| Catalog Number: | **SA1C-727-U-5WQ** |
| Description: | McGRAW EDISON ROADWAY AND AREA LUMINAIRE |

***THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.***TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

## Spectral Parameters

| | | | | | |
|---|---|---|---|---|---|
| CCT (K): | 2741 | CRI (Ra): | 71.5 | | |
| CIE u': | 0.2605 | R1: | 69.2 | R9: | -16.1 |
| CIE v': | 0.5272 | R2: | 79.4 | R10: | 51.4 |
| Duv: | 0.0005 | R3: | 87.8 | R11: | 63.1 |
| CIE x: | 0.4573 | R4: | 69.4 | R12: | 42.0 |
| CIE y: | 0.4113 | R5: | 66.4 | R13: | 70.2 |
| CIE z: | 0.1313 | R6: | 69.8 | R14: | 92.4 |
| Peak Wavelength (nm): | 602 | R7: | 79.8 | | |
| Dominant Wavelength (nm): | 583 | R8: | 50.1 | | |
| Purity: | 61.2 | | | | |

| | |
|---|---|
| Rf: | 69.9 |
| Rg: | 98.3 |




## Test Conditions

| | |
|---|---|
| Stabilization Time: | 56M |
| Operation Time: | 12H |
| Room Temperature (°C) / RH%: | 25.3./42% |
| Sphere Temperature (°C): | 25.7 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|---|---|---|---|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## CIE 1931 Chromaticity Diagram




## CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2741K
CIE x = 0.4573
CIE y = 0.4113
Duv = 0.0005

Point lies inside the ANSI 2700K 4-step quadrangle

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## Photopic Flux vs. Wavelength




**Photopic Lumens: 6211.7**

| λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## Scotopic Flux vs. Wavelength




**Scotopic Lumens: 6474.3** **S/P: 1.04**

| λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## Melanopic Flux vs. Wavelength




**Melanopic Lumens: 2145.7** **M/P: 0.35**

| λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) | λ (nm) | Power (µW/nm) | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

# TM-30-18

## Summary

$R_f$ = 69.9
$R_g$ = 98.3
CIE $R_a$ = 71.5
$R_9$ = -16.1

## Spectral Power Distribution Comparison




## Color Vector Graphics












Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## TM-30-18

**Individual Sample Fidelity Index ($R_{f,i}$)**

| | | | |
|---|---|---|---|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## TM-30-18

### Color Rendition by Hue-Angle Bin









Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-1908-441-1-R4

## TM-30-18

### Measure Comparisons







(END OF REPORT)