

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633121

Luminaire Tested: GWS-SA2E-727-U-5NQ-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P633121  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA2E-727-U-5NQ-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V NARROW OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (32) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8586.6 lumens  
Efficiency: N/A  
Efficacy: 79.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G0  
  
Input Watts (W): 108.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P633121  
 CATALOG NUMBER: GWS-SA2E-727-U-5NQ-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 14 fc  
 Type V - Short - N/A

REPORT NUMBER: P633121  
CATALOG NUMBER: GWS-SA2E-727-U-5NQ-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P633121

CATALOG NUMBER: GWS-SA2E-727-U-5NQ-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 4293.3   | 0.0    | 4293.3 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 4293.3   | 0.0    | 4293.3 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 8586.6   | 0.0    | 8586.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 136.0  | 1.6       |
| 10°-20°   | 440.9  | 5.1       |
| 20°-30°   | 853.9  | 9.9       |
| 30°-40°   | 1529.8 | 17.8      |
| 40°-50°   | 2564.8 | 29.9      |
| 50°-60°   | 2745.5 | 32.0      |
| 60°-70°   | 301.7  | 3.5       |
| 70°-80°   | 13.3   | 0.2       |
| 80°-90°   | 0.6    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 8586.6 | 100.0     |
| 0°-180°   | 8586.6 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P633121

CATALOG NUMBER: GWS-SA2E-727-U-5NQ-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 715.4  | 8.3       |                         |      |        |
| FM (30°-60°)   | 3420.1 | 39.8      |                         |      |        |
| FH (60°-80°)   | 157.5  | 1.8       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.3    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 715.4  | 8.3       | B2/1000                 |      |        |
| BM (30°-60°)   | 3420.1 | 39.8      | B3/5000                 |      |        |
| BH (60°-80°)   | 157.5  | 1.8       | B1/500                  |      | G0/660 |
| BVH (80°-90°)  | 0.3    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B3-U0-G0**  
 Type V Short





REPORT NUMBER: P633121  
 CATALOG NUMBER: GWS-SA2E-727-U-5NQ-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 | 1388.3 |
| 2.5°  | 1385.7 | 1385.7 | 1389.2 | 1391.8 | 1391.8 | 1398.8 | 1396.2 | 1393.5 | 1393.5 | 1390.0 | 1397.0 |
| 5°    | 1405.8 | 1404.9 | 1408.4 | 1410.2 | 1406.7 | 1413.7 | 1409.3 | 1406.7 | 1404.9 | 1401.4 | 1408.4 |
| 7.5°  | 1427.7 | 1428.5 | 1429.4 | 1432.9 | 1431.2 | 1438.2 | 1434.7 | 1429.4 | 1427.7 | 1422.4 | 1429.4 |
| 10°   | 1453.9 | 1453.9 | 1455.6 | 1460.0 | 1460.9 | 1469.6 | 1466.1 | 1460.0 | 1454.8 | 1449.5 | 1456.5 |
| 12.5° | 1487.1 | 1488.0 | 1490.6 | 1496.8 | 1500.3 | 1509.9 | 1504.6 | 1492.4 | 1484.5 | 1478.4 | 1486.3 |
| 15°   | 1535.3 | 1534.4 | 1537.9 | 1546.6 | 1551.0 | 1558.0 | 1550.1 | 1533.5 | 1523.9 | 1516.9 | 1522.1 |
| 17.5° | 1587.7 | 1587.7 | 1589.5 | 1598.2 | 1604.4 | 1614.9 | 1605.2 | 1585.1 | 1576.4 | 1566.7 | 1572.0 |
| 20°   | 1645.5 | 1648.1 | 1649.8 | 1656.0 | 1666.5 | 1677.0 | 1669.1 | 1649.0 | 1639.4 | 1627.1 | 1633.2 |
| 22.5° | 1721.6 | 1719.0 | 1719.8 | 1730.3 | 1745.2 | 1755.7 | 1749.6 | 1726.0 | 1709.3 | 1699.7 | 1703.2 |
| 25°   | 1806.4 | 1805.6 | 1808.2 | 1823.9 | 1840.6 | 1851.9 | 1843.2 | 1812.6 | 1795.9 | 1779.3 | 1786.3 |
| 27.5° | 1910.5 | 1911.4 | 1913.2 | 1932.4 | 1958.6 | 1975.3 | 1953.4 | 1922.8 | 1900.0 | 1878.2 | 1883.4 |
| 30°   | 2033.9 | 2032.1 | 2037.4 | 2063.6 | 2102.1 | 2128.4 | 2103.0 | 2060.1 | 2027.8 | 2006.8 | 2009.4 |
| 32.5° | 2165.1 | 2166.8 | 2180.8 | 2222.8 | 2273.6 | 2319.9 | 2268.3 | 2211.5 | 2169.5 | 2130.1 | 2135.4 |
| 35°   | 2306.8 | 2311.2 | 2342.7 | 2404.8 | 2487.9 | 2550.0 | 2478.3 | 2384.7 | 2325.2 | 2274.4 | 2276.2 |
| 37.5° | 2473.9 | 2484.4 | 2528.1 | 2620.9 | 2739.8 | 2822.9 | 2718.0 | 2593.7 | 2516.8 | 2453.8 | 2449.4 |
| 40°   | 2693.5 | 2705.7 | 2765.2 | 2875.4 | 3019.8 | 3095.9 | 2974.3 | 2846.6 | 2751.2 | 2683.0 | 2672.5 |
| 42.5° | 2945.4 | 2961.2 | 3025.9 | 3138.7 | 3283.1 | 3334.7 | 3215.7 | 3108.1 | 3022.4 | 2941.9 | 2938.4 |
| 45°   | 3229.7 | 3238.5 | 3291.0 | 3377.6 | 3481.7 | 3493.9 | 3404.7 | 3345.2 | 3258.6 | 3183.4 | 3177.2 |
| 47.5° | 3496.5 | 3505.3 | 3541.1 | 3585.8 | 3610.2 | 3566.5 | 3550.8 | 3524.5 | 3412.5 | 3319.8 | 3300.6 |
| 50°   | 3699.5 | 3706.5 | 3751.1 | 3768.6 | 3700.4 | 3607.6 | 3638.2 | 3582.3 | 3460.7 | 3356.6 | 3326.8 |
| 52.5° | 3685.5 | 3703.0 | 3817.6 | 3917.3 | 3874.4 | 3799.2 | 3717.0 | 3596.3 | 3407.3 | 3264.7 | 3228.0 |
| 55°   | 3172.9 | 3196.5 | 3442.3 | 3770.3 | 4063.4 | 4095.8 | 3766.8 | 3377.6 | 3022.4 | 2813.3 | 2775.7 |
| 57.5° | 2039.1 | 2045.3 | 2345.3 | 2805.4 | 3465.9 | 3674.1 | 3123.9 | 2546.5 | 2104.7 | 1874.7 | 1858.9 |
| 60°   | 749.7  | 737.4  | 964.0  | 1345.4 | 1996.3 | 2216.7 | 1838.8 | 1287.7 | 918.5  | 755.8  | 742.7  |
| 62.5° | 180.2  | 182.0  | 225.7  | 338.5  | 626.3  | 775.1  | 612.4  | 342.0  | 217.8  | 182.8  | 181.1  |
| 65°   | 91.0   | 89.2   | 90.1   | 97.1   | 133.8  | 160.1  | 131.2  | 92.7   | 89.2   | 90.1   | 89.2   |
| 67.5° | 58.6   | 57.7   | 59.5   | 60.4   | 59.5   | 56.0   | 55.1   | 56.9   | 56.9   | 57.7   | 56.0   |
| 70°   | 35.9   | 35.0   | 36.7   | 39.4   | 37.6   | 33.2   | 35.0   | 36.7   | 35.0   | 34.1   | 34.1   |
| 72.5° | 19.2   | 19.2   | 21.0   | 22.7   | 21.0   | 19.2   | 19.2   | 20.1   | 19.2   | 19.2   | 19.2   |
| 75°   | 8.7    | 8.7    | 9.6    | 10.5   | 8.7    | 8.7    | 8.7    | 8.7    | 8.7    | 8.7    | 8.7    |
| 77.5° | 2.6    | 2.6    | 3.5    | 3.5    | 2.6    | 2.6    | 2.6    | 2.6    | 3.5    | 3.5    | 3.5    |
| 80°   | 0.9    | 1.7    | 1.7    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 1.7    | 1.7    | 1.7    |
| 82.5° | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    |
| 85°   | 0.9    | 0.9    | 0.9    | 0.0    | 0.0    | 0.0    | 0.0    | 0.9    | 0.9    | 0.9    | 0.9    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.9    | 0.9    | 0.9    | 0.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ



**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**  
 Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 1.0           | 620    | 118034        | 30.7          | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 1.9           | 625    | 111884        | 24.7          | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 3.4           | 630    | 106119        | 19.2          | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 6.3           | 635    | 99706         | 15.0          | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 10.4          | 640    | 92142         | 11.0          | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 16.3          | 645    | 84987         | 8.2           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 22.9          | 650    | 78016         | 5.7           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 29.7          | 655    | 71541         | 4.1           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 36.7          | 660    | 64863         | 2.7           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 42.5          | 665    | 58485         | 1.9           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.0           | 540    | 73435         | 47.8          | 670    | 51641         | 1.1           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.0           | 545    | 78677         | 52.4          | 675    | 46030         | 0.8           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 0.0           | 550    | 83331         | 56.6          | 680    | 40590         | 0.5           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 0.1           | 555    | 89120         | 60.9          | 685    | 35691         | 0.3           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 0.3           | 560    | 94613         | 64.3          | 690    | 31631         | 0.2           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 0.6           | 565    | 99818         | 66.4          | 695    | 27437         | 0.1           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 0.9           | 570    | 106526        | 69.3          | 700    | 24589         | 0.1           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 1.1           | 575    | 111610        | 69.4          | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 1.0           | 580    | 117163        | 69.6          | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 0.8           | 585    | 122201        | 67.9          | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 0.6           | 590    | 125662        | 65.0          | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 0.5           | 595    | 127415        | 60.4          | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 0.4           | 600    | 129155        | 55.7          | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 0.4           | 605    | 128057        | 49.6          | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 0.5           | 610    | 126031        | 43.3          | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 0.7           | 615    | 123059        | 37.1          | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)