

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633632

Luminaire Tested: GWS-SA2F-727-U-SL2-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633632
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2F-727-U-SL2-W
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13332 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 124.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633632
 CATALOG NUMBER: GWS-SA2F-727-U-SL2-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 7.4 fc
 Type II - Short - N/A

REPORT NUMBER: P633632
CATALOG NUMBER: GWS-SA2F-727-U-SL2-W

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P633632

CATALOG NUMBER: GWS-SA2F-727-U-SL2-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2705.4 | 0.0 | 2705.4 |
| | % Fixture | 20.3 | 0.0 | 20.3 |
| Street Side | Lumens | 10626.6 | 0.0 | 10626.6 |
| | % Fixture | 79.7 | 0.0 | 79.7 |
| Total | Lumens | 13332.0 | 0.0 | 13332.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 258.5 | 1.9 |
| 10°-20° | 635.4 | 4.8 |
| 20°-30° | 873.4 | 6.6 |
| 30°-40° | 1194.1 | 9.0 |
| 40°-50° | 1809.3 | 13.6 |
| 50°-60° | 2812.7 | 21.1 |
| 60°-70° | 3424.4 | 25.7 |
| 70°-80° | 2085.9 | 15.6 |
| 80°-90° | 238.3 | 1.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 13332.0 | 100.0 |
| 0°-180° | 13332.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P633632

CATALOG NUMBER: GWS-SA2F-727-U-SL2-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1044.6 | 7.8 | | | |
| FM (30°-60°) | 4860.0 | 36.5 | | | |
| FH (60°-80°) | 4523.9 | 33.9 | | | G2/5000 |
| FVH (80°-90°) | 198.1 | 1.5 | | | G2/225 |
| BL (0°-30°) | 722.7 | 5.4 | B2/1000 | | |
| BM (30°-60°) | 956.0 | 7.2 | B1/1000 | | |
| BH (60°-80°) | 986.4 | 7.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 40.2 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2
 Type II Short





REPORT NUMBER: P633632
 CATALOG NUMBER: GWS-SA2F-727-U-SL2-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 66° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|--------|
| 0° | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 |
| 2.5° | 2759.3 | 2769.0 | 2763.1 | 2800.1 | 2802.0 | 2848.7 | 2875.0 | 2897.4 | 2899.3 | 2928.5 | 2947.9 |
| 5° | 2570.6 | 2576.4 | 2576.4 | 2611.4 | 2634.8 | 2697.0 | 2757.3 | 2821.5 | 2826.4 | 2896.4 | 2949.9 |
| 7.5° | 2417.9 | 2423.7 | 2419.8 | 2466.5 | 2496.7 | 2565.7 | 2642.5 | 2740.8 | 2750.5 | 2863.3 | 2956.7 |
| 10° | 2298.2 | 2296.3 | 2306.0 | 2348.8 | 2387.7 | 2470.4 | 2556.0 | 2667.8 | 2682.4 | 2825.4 | 2964.5 |
| 12.5° | 2216.5 | 2218.5 | 2224.3 | 2269.1 | 2310.9 | 2392.6 | 2481.1 | 2602.7 | 2618.2 | 2781.6 | 2960.6 |
| 15° | 2177.6 | 2173.8 | 2178.6 | 2219.5 | 2259.3 | 2331.3 | 2422.7 | 2548.2 | 2563.8 | 2742.7 | 2961.6 |
| 17.5° | 2168.9 | 2166.0 | 2165.0 | 2194.2 | 2224.3 | 2291.4 | 2379.0 | 2506.4 | 2522.9 | 2717.4 | 2967.4 |
| 20° | 2196.1 | 2192.2 | 2181.5 | 2194.2 | 2206.8 | 2263.2 | 2347.8 | 2476.2 | 2494.7 | 2700.9 | 2979.1 |
| 22.5° | 2271.0 | 2264.2 | 2247.7 | 2232.1 | 2215.6 | 2249.6 | 2328.4 | 2453.9 | 2472.3 | 2690.2 | 2990.7 |
| 25° | 2384.8 | 2379.0 | 2361.5 | 2326.4 | 2266.1 | 2260.3 | 2324.5 | 2444.1 | 2462.6 | 2682.4 | 2995.6 |
| 27.5° | 2541.4 | 2532.6 | 2515.1 | 2464.6 | 2366.3 | 2300.2 | 2339.1 | 2443.2 | 2460.7 | 2673.7 | 2990.7 |
| 30° | 2727.2 | 2721.3 | 2711.6 | 2650.3 | 2519.0 | 2384.8 | 2372.2 | 2450.9 | 2464.6 | 2668.8 | 2981.0 |
| 32.5° | 2915.8 | 2910.0 | 2917.8 | 2888.6 | 2727.2 | 2524.9 | 2444.1 | 2472.3 | 2482.1 | 2667.8 | 2972.3 |
| 35° | 3082.2 | 3089.0 | 3145.4 | 3150.2 | 2991.7 | 2714.5 | 2557.9 | 2521.9 | 2523.9 | 2687.3 | 2976.1 |
| 37.5° | 3256.3 | 3282.5 | 3356.4 | 3419.6 | 3287.4 | 2965.4 | 2727.2 | 2615.3 | 2613.4 | 2736.9 | 3000.5 |
| 40° | 3486.8 | 3498.4 | 3592.8 | 3711.4 | 3628.8 | 3309.7 | 2967.4 | 2768.0 | 2754.4 | 2838.0 | 3065.6 |
| 42.5° | 3711.4 | 3739.6 | 3890.4 | 4026.5 | 3999.3 | 3697.8 | 3269.9 | 2996.6 | 2972.3 | 3017.0 | 3199.8 |
| 45° | 3997.4 | 4024.6 | 4193.8 | 4368.9 | 4418.5 | 4136.5 | 3657.0 | 3321.4 | 3297.1 | 3286.4 | 3445.9 |
| 47.5° | 4283.3 | 4311.5 | 4463.2 | 4716.1 | 4890.2 | 4685.0 | 4160.8 | 3750.3 | 3710.5 | 3668.6 | 3817.4 |
| 50° | 4475.9 | 4509.0 | 4653.9 | 4957.3 | 5365.8 | 5369.7 | 4757.9 | 4312.5 | 4261.9 | 4195.8 | 4340.7 |
| 52.5° | 4469.1 | 4490.5 | 4628.6 | 4978.7 | 5708.2 | 6156.5 | 5557.4 | 5028.3 | 4987.5 | 4843.5 | 4970.0 |
| 55° | 4118.0 | 4150.1 | 4289.1 | 4726.8 | 5745.1 | 6902.5 | 6732.3 | 5872.5 | 5799.6 | 5541.9 | 5680.9 |
| 57.5° | 3412.8 | 3440.1 | 3580.1 | 4119.9 | 5417.4 | 7284.7 | 8224.3 | 6948.2 | 6848.0 | 6302.4 | 6462.9 |
| 60° | 2576.4 | 2543.3 | 2609.5 | 3082.2 | 4633.4 | 7294.5 | 9541.2 | 8407.1 | 8239.8 | 7115.5 | 7249.7 |
| 62.5° | 1933.5 | 1900.5 | 1915.0 | 2048.3 | 3141.5 | 6705.1 | 10292.0 | 10402.9 | 10126.7 | 8033.6 | 8007.4 |
| 65° | 1527.9 | 1509.5 | 1551.3 | 1642.7 | 1831.4 | 5106.1 | 10297.8 | 12561.1 | 12387.0 | 9097.7 | 8784.5 |
| 67.5° | 1244.9 | 1233.3 | 1276.0 | 1445.3 | 1485.2 | 2743.7 | 9233.8 | 13568.7 | 13636.8 | 10262.8 | 9505.2 |
| 70° | 1002.7 | 985.2 | 1052.3 | 1275.1 | 1381.1 | 1660.2 | 6614.6 | 13055.2 | 13165.1 | 10957.3 | 9301.9 |
| 72.5° | 692.5 | 693.5 | 727.5 | 1032.9 | 1333.4 | 1433.6 | 3741.6 | 10870.7 | 11109.0 | 10328.0 | 8177.6 |
| 75° | 466.8 | 470.7 | 480.5 | 681.8 | 1228.4 | 1390.8 | 1993.8 | 8230.1 | 8398.4 | 8536.5 | 6759.5 |
| 77.5° | 282.1 | 284.0 | 306.4 | 412.4 | 847.1 | 1298.4 | 1350.9 | 5965.9 | 6098.2 | 5627.4 | 4189.9 |
| 80° | 163.4 | 170.2 | 190.6 | 276.2 | 571.9 | 975.5 | 1045.5 | 3657.9 | 3807.7 | 2501.5 | 1331.5 |
| 82.5° | 72.0 | 76.8 | 104.1 | 160.5 | 333.6 | 829.6 | 816.0 | 1445.3 | 1423.9 | 697.4 | 462.0 |
| 85° | 12.6 | 15.6 | 22.4 | 50.6 | 122.5 | 437.7 | 633.2 | 638.0 | 600.1 | 264.5 | 191.6 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.9 | 95.3 | 171.2 | 170.2 | 74.9 | 66.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633632
 CATALOG NUMBER: GWS-SA2F-727-U-SL2-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 | 2946.0 |
| 2.5° | 2960.6 | 2934.3 | 2957.7 | 2960.6 | 2955.7 | 2951.8 | 2922.7 | 2897.4 | 2894.4 | 2867.2 | 2867.2 |
| 5° | 2971.3 | 2947.0 | 2958.6 | 2936.3 | 2901.3 | 2865.3 | 2803.0 | 2760.2 | 2740.8 | 2705.8 | 2705.8 |
| 7.5° | 2985.9 | 2960.6 | 2947.0 | 2891.5 | 2809.8 | 2731.0 | 2630.9 | 2547.2 | 2513.2 | 2463.6 | 2461.6 |
| 10° | 2999.5 | 2967.4 | 2920.7 | 2812.7 | 2682.4 | 2557.0 | 2411.1 | 2292.4 | 2211.7 | 2152.4 | 2152.4 |
| 12.5° | 2998.5 | 2956.7 | 2864.3 | 2704.8 | 2524.9 | 2343.0 | 2148.5 | 1969.5 | 1862.5 | 1770.1 | 1764.3 |
| 15° | 2996.6 | 2939.2 | 2792.3 | 2579.3 | 2341.0 | 2089.1 | 1824.6 | 1591.2 | 1432.6 | 1342.2 | 1334.4 |
| 17.5° | 2994.6 | 2916.8 | 2711.6 | 2436.4 | 2117.3 | 1774.0 | 1424.9 | 1172.0 | 1039.7 | 984.3 | 986.2 |
| 20° | 2994.6 | 2891.5 | 2625.0 | 2272.0 | 1859.6 | 1396.6 | 1045.5 | 861.7 | 828.7 | 831.6 | 834.5 |
| 22.5° | 2985.9 | 2860.4 | 2528.7 | 2093.0 | 1572.7 | 1027.1 | 771.3 | 709.0 | 726.5 | 753.8 | 757.7 |
| 25° | 2965.4 | 2808.9 | 2416.9 | 1894.6 | 1231.3 | 747.9 | 629.3 | 617.6 | 649.7 | 683.7 | 693.5 |
| 27.5° | 2933.3 | 2749.5 | 2291.4 | 1662.2 | 906.5 | 601.1 | 553.4 | 552.4 | 577.7 | 603.0 | 611.8 |
| 30° | 2899.3 | 2683.4 | 2159.2 | 1403.5 | 656.5 | 523.3 | 504.8 | 504.8 | 517.4 | 533.0 | 531.0 |
| 32.5° | 2859.4 | 2616.3 | 2017.2 | 1134.0 | 534.9 | 479.5 | 473.7 | 470.7 | 472.7 | 478.5 | 478.5 |
| 35° | 2825.4 | 2557.0 | 1871.3 | 849.1 | 479.5 | 455.2 | 449.3 | 442.5 | 439.6 | 435.7 | 437.7 |
| 37.5° | 2812.7 | 2510.3 | 1720.5 | 640.0 | 452.3 | 437.7 | 427.9 | 418.2 | 411.4 | 409.5 | 408.5 |
| 40° | 2833.2 | 2490.8 | 1569.8 | 527.1 | 432.8 | 419.2 | 408.5 | 395.8 | 390.0 | 390.0 | 390.0 |
| 42.5° | 2912.9 | 2505.4 | 1416.1 | 476.6 | 419.2 | 403.6 | 388.1 | 376.4 | 374.4 | 376.4 | 377.4 |
| 45° | 3058.8 | 2561.8 | 1256.6 | 451.3 | 407.5 | 388.1 | 369.6 | 360.8 | 360.8 | 362.8 | 362.8 |
| 47.5° | 3319.5 | 2709.7 | 1099.0 | 435.7 | 395.8 | 375.4 | 356.0 | 347.2 | 346.2 | 348.2 | 348.2 |
| 50° | 3770.8 | 2976.1 | 957.0 | 425.0 | 387.1 | 365.7 | 346.2 | 334.6 | 331.7 | 330.7 | 330.7 |
| 52.5° | 4339.7 | 3438.1 | 866.6 | 417.2 | 376.4 | 355.0 | 335.5 | 320.0 | 314.1 | 311.2 | 311.2 |
| 55° | 5027.3 | 4053.8 | 866.6 | 411.4 | 362.8 | 342.4 | 320.0 | 304.4 | 295.7 | 291.8 | 291.8 |
| 57.5° | 5806.4 | 4770.6 | 1016.4 | 406.5 | 352.1 | 327.8 | 303.4 | 287.9 | 278.2 | 272.3 | 272.3 |
| 60° | 6599.1 | 5528.2 | 1386.9 | 399.7 | 342.4 | 309.3 | 285.0 | 270.4 | 257.7 | 250.9 | 250.0 |
| 62.5° | 7420.9 | 6362.7 | 1875.2 | 403.6 | 335.5 | 291.8 | 265.5 | 249.0 | 238.3 | 231.5 | 230.5 |
| 65° | 8173.7 | 7157.3 | 2302.1 | 433.8 | 336.5 | 276.2 | 243.1 | 228.6 | 219.8 | 211.1 | 210.1 |
| 67.5° | 8812.7 | 7596.0 | 2002.6 | 495.1 | 356.9 | 257.7 | 220.8 | 206.2 | 198.4 | 192.6 | 191.6 |
| 70° | 8365.3 | 6926.8 | 1136.0 | 533.0 | 385.1 | 238.3 | 195.5 | 185.8 | 178.0 | 174.1 | 173.1 |
| 72.5° | 7153.4 | 5864.8 | 759.6 | 470.7 | 351.1 | 213.0 | 172.1 | 164.4 | 158.5 | 153.7 | 152.7 |
| 75° | 5794.7 | 4651.0 | 580.6 | 386.1 | 273.3 | 173.1 | 147.8 | 142.0 | 136.2 | 131.3 | 130.3 |
| 77.5° | 3428.4 | 2687.3 | 427.9 | 305.4 | 192.6 | 135.2 | 122.5 | 117.7 | 111.8 | 108.0 | 107.0 |
| 80° | 1094.2 | 933.7 | 271.4 | 210.1 | 127.4 | 104.1 | 94.3 | 90.5 | 84.6 | 79.8 | 78.8 |
| 82.5° | 417.2 | 360.8 | 143.9 | 107.0 | 84.6 | 71.0 | 63.2 | 59.3 | 55.4 | 50.6 | 49.6 |
| 85° | 184.8 | 173.1 | 79.8 | 57.4 | 45.7 | 35.0 | 31.1 | 29.2 | 24.3 | 20.4 | 19.5 |
| 87.5° | 65.2 | 65.2 | 34.0 | 16.5 | 9.7 | 4.9 | 2.9 | 1.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_g = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)