

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633657

Luminaire Tested: GWS-SA2F-727-U-T3-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2F-727-U-T3-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11579.5 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 124.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633657
 CATALOG NUMBER: GWS-SA2F-727-U-T3-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6 fc
 Type II - Short - N/A

REPORT NUMBER: P633657
CATALOG NUMBER: GWS-SA2F-727-U-T3-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P633657

CATALOG NUMBER: GWS-SA2F-727-U-T3-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3664.9 | 0.0 | 3664.9 |
| | % Fixture | 31.6 | 0.0 | 31.6 |
| Street Side | Lumens | 7914.6 | 0.0 | 7914.6 |
| | % Fixture | 68.4 | 0.0 | 68.4 |
| Total | Lumens | 11579.5 | 0.0 | 11579.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 211.8 | 1.8 |
| 10°-20° | 696.6 | 6.0 |
| 20°-30° | 1254.4 | 10.8 |
| 30°-40° | 1894.6 | 16.4 |
| 40°-50° | 2551.3 | 22.0 |
| 50°-60° | 3065.7 | 26.5 |
| 60°-70° | 1493.1 | 12.9 |
| 70°-80° | 367.8 | 3.2 |
| 80°-90° | 44.2 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11579.5 | 100.0 |
| 0°-180° | 11579.5 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P633657


CATALOG NUMBER: GWS-SA2F-727-U-T3-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1163.1 | 10.0 | | | |
| FM (30°-60°) | 5504.3 | 47.5 | | | |
| FH (60°-80°) | 1230.6 | 10.6 | | | G1/1800 |
| FVH (80°-90°) | 16.6 | 0.1 | | | G1/100 |
| BL (0°-30°) | 999.7 | 8.6 | B2/1000 | | |
| BM (30°-60°) | 2007.2 | 17.3 | B2/2500 | | |
| BH (60°-80°) | 630.3 | 5.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 27.6 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type II Short





REPORT NUMBER: P633657

CATALOG NUMBER: GWS-SA2F-727-U-T3-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 |
| 2.5° | 2143.5 | 2142.6 | 2142.6 | 2148.4 | 2148.4 | 2150.4 | 2153.3 | 2156.2 | 2157.2 | 2152.3 | 2141.6 |
| 5° | 2166.9 | 2166.9 | 2166.9 | 2171.7 | 2171.7 | 2173.7 | 2177.6 | 2178.6 | 2177.6 | 2169.8 | 2159.1 |
| 7.5° | 2203.8 | 2203.8 | 2204.8 | 2210.7 | 2215.5 | 2218.4 | 2225.2 | 2224.3 | 2221.4 | 2208.7 | 2195.1 |
| 10° | 2264.1 | 2267.1 | 2270.0 | 2276.8 | 2286.5 | 2293.3 | 2298.2 | 2298.2 | 2294.3 | 2274.8 | 2257.3 |
| 12.5° | 2349.7 | 2353.6 | 2356.5 | 2362.4 | 2370.2 | 2381.8 | 2392.5 | 2392.5 | 2387.7 | 2363.3 | 2337.1 |
| 15° | 2449.9 | 2453.8 | 2452.8 | 2454.8 | 2469.4 | 2485.9 | 2494.6 | 2500.5 | 2502.4 | 2468.4 | 2427.5 |
| 17.5° | 2564.7 | 2568.6 | 2564.7 | 2558.8 | 2560.8 | 2587.0 | 2602.6 | 2624.0 | 2636.6 | 2590.9 | 2525.8 |
| 20° | 2668.7 | 2664.8 | 2664.8 | 2668.7 | 2674.6 | 2706.7 | 2730.0 | 2765.0 | 2780.6 | 2725.1 | 2624.0 |
| 22.5° | 2778.6 | 2787.4 | 2783.5 | 2783.5 | 2806.8 | 2860.3 | 2888.5 | 2934.2 | 2950.8 | 2878.8 | 2742.6 |
| 25° | 2920.6 | 2928.4 | 2926.5 | 2928.4 | 2955.6 | 3031.5 | 3059.7 | 3144.3 | 3160.9 | 3057.8 | 2873.9 |
| 27.5° | 3076.2 | 3088.9 | 3094.7 | 3092.8 | 3136.5 | 3235.7 | 3270.8 | 3388.4 | 3418.6 | 3258.1 | 3014.0 |
| 30° | 3278.5 | 3292.2 | 3297.0 | 3295.1 | 3346.6 | 3481.8 | 3521.7 | 3655.9 | 3698.7 | 3495.4 | 3192.0 |
| 32.5° | 3512.9 | 3526.5 | 3541.1 | 3547.0 | 3613.1 | 3751.2 | 3808.6 | 3947.7 | 4008.9 | 3769.7 | 3406.9 |
| 35° | 3745.4 | 3757.0 | 3785.2 | 3831.0 | 3921.4 | 4062.4 | 4113.0 | 4250.1 | 4309.5 | 4054.6 | 3666.6 |
| 37.5° | 4002.1 | 4009.9 | 4034.2 | 4097.4 | 4227.8 | 4362.0 | 4412.6 | 4543.8 | 4550.7 | 4329.9 | 3960.3 |
| 40° | 4283.2 | 4283.2 | 4278.3 | 4340.6 | 4476.7 | 4611.9 | 4655.7 | 4731.6 | 4691.7 | 4541.9 | 4246.2 |
| 42.5° | 4521.5 | 4517.6 | 4521.5 | 4579.8 | 4681.0 | 4790.9 | 4828.8 | 4814.2 | 4763.6 | 4704.3 | 4504.9 |
| 45° | 4736.4 | 4739.3 | 4774.3 | 4819.1 | 4871.6 | 4936.8 | 4959.1 | 4876.5 | 4830.8 | 4834.6 | 4712.1 |
| 47.5° | 4882.3 | 4885.2 | 4966.9 | 5041.8 | 5073.9 | 5094.3 | 5084.6 | 4969.8 | 4946.5 | 4990.3 | 4871.6 |
| 50° | 4901.8 | 4917.3 | 5058.3 | 5212.0 | 5291.8 | 5294.7 | 5267.4 | 5127.4 | 5120.6 | 5170.2 | 4957.2 |
| 52.5° | 4905.6 | 4921.2 | 5097.2 | 5374.4 | 5581.6 | 5625.3 | 5594.2 | 5448.3 | 5377.3 | 5327.7 | 5062.2 |
| 55° | 4891.1 | 4908.6 | 5103.1 | 5483.4 | 5880.2 | 6055.2 | 6058.1 | 5852.0 | 5625.3 | 5592.3 | 5361.8 |
| 57.5° | 4318.2 | 4325.0 | 4626.5 | 5206.2 | 5868.5 | 6364.5 | 6402.4 | 6122.3 | 5863.6 | 5832.5 | 5602.0 |
| 60° | 3008.2 | 3035.4 | 3363.1 | 4128.6 | 4930.0 | 5804.3 | 5926.8 | 5845.1 | 5672.0 | 5445.4 | 4806.4 |
| 62.5° | 1506.5 | 1529.9 | 1858.6 | 2582.2 | 3400.1 | 4090.6 | 4221.9 | 4308.5 | 4349.3 | 4106.2 | 3272.7 |
| 65° | 648.7 | 666.2 | 870.5 | 1349.0 | 1924.7 | 2258.3 | 2304.0 | 2408.1 | 2662.9 | 2376.0 | 1763.3 |
| 67.5° | 433.8 | 445.4 | 549.5 | 822.8 | 1134.0 | 1155.4 | 1148.6 | 1171.0 | 1226.4 | 1012.4 | 796.5 |
| 70° | 332.6 | 342.3 | 412.4 | 603.0 | 815.0 | 697.3 | 660.4 | 599.1 | 650.6 | 663.3 | 645.8 |
| 72.5° | 241.2 | 249.0 | 301.5 | 411.4 | 510.6 | 445.4 | 439.6 | 470.7 | 540.7 | 560.2 | 549.5 |
| 75° | 155.6 | 159.5 | 191.6 | 225.6 | 263.6 | 285.9 | 297.6 | 354.0 | 425.0 | 439.6 | 427.0 |
| 77.5° | 104.1 | 107.0 | 125.5 | 144.9 | 149.8 | 150.7 | 154.6 | 179.9 | 228.6 | 255.8 | 252.9 |
| 80° | 54.5 | 54.5 | 61.3 | 61.3 | 70.0 | 83.6 | 87.5 | 104.1 | 126.4 | 140.1 | 141.0 |
| 82.5° | 21.4 | 22.4 | 26.3 | 29.2 | 35.0 | 42.8 | 45.7 | 54.5 | 66.1 | 75.9 | 84.6 |
| 85° | 8.8 | 9.7 | 10.7 | 12.6 | 15.6 | 19.5 | 20.4 | 23.3 | 31.1 | 38.9 | 43.8 |
| 87.5° | 0.0 | 0.0 | 1.0 | 1.0 | 1.9 | 2.9 | 2.9 | 3.9 | 4.9 | 8.8 | 11.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633657
 CATALOG NUMBER: GWS-SA2F-727-U-T3-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 | 2147.4 |
| 2.5° | 2154.2 | 2141.6 | 2154.2 | 2158.1 | 2168.8 | 2172.7 | 2165.9 | 2164.9 | 2164.9 | 2155.2 | 2152.3 |
| 5° | 2168.8 | 2157.2 | 2169.8 | 2175.6 | 2191.2 | 2200.9 | 2202.9 | 2210.7 | 2215.5 | 2211.6 | 2210.7 |
| 7.5° | 2204.8 | 2190.2 | 2203.8 | 2212.6 | 2233.0 | 2248.6 | 2255.4 | 2272.9 | 2285.5 | 2283.6 | 2282.6 |
| 10° | 2268.0 | 2248.6 | 2264.1 | 2278.7 | 2301.1 | 2319.6 | 2320.6 | 2330.3 | 2342.9 | 2339.0 | 2337.1 |
| 12.5° | 2341.0 | 2322.5 | 2340.0 | 2354.6 | 2380.9 | 2388.6 | 2376.0 | 2372.1 | 2374.0 | 2369.2 | 2365.3 |
| 15° | 2430.5 | 2404.2 | 2419.8 | 2436.3 | 2450.9 | 2442.1 | 2414.9 | 2404.2 | 2403.2 | 2396.4 | 2392.5 |
| 17.5° | 2519.9 | 2486.9 | 2498.5 | 2507.3 | 2500.5 | 2473.2 | 2439.2 | 2420.7 | 2412.0 | 2398.4 | 2394.5 |
| 20° | 2608.4 | 2566.6 | 2564.7 | 2557.9 | 2526.7 | 2477.1 | 2431.4 | 2394.5 | 2372.1 | 2353.6 | 2346.8 |
| 22.5° | 2709.6 | 2651.2 | 2622.0 | 2590.9 | 2522.8 | 2442.1 | 2373.1 | 2320.6 | 2284.6 | 2261.2 | 2253.4 |
| 25° | 2818.5 | 2735.8 | 2675.5 | 2613.3 | 2483.9 | 2367.2 | 2271.0 | 2199.0 | 2156.2 | 2130.9 | 2122.1 |
| 27.5° | 2926.5 | 2812.7 | 2722.2 | 2616.2 | 2406.1 | 2259.3 | 2129.9 | 2032.7 | 1989.9 | 1969.5 | 1962.6 |
| 30° | 3072.3 | 2914.8 | 2777.7 | 2578.3 | 2304.0 | 2109.5 | 1948.1 | 1849.8 | 1821.6 | 1807.0 | 1801.2 |
| 32.5° | 3240.6 | 3044.1 | 2851.6 | 2498.5 | 2173.7 | 1934.4 | 1764.2 | 1696.2 | 1676.7 | 1648.5 | 1647.5 |
| 35° | 3462.3 | 3228.9 | 2921.6 | 2380.9 | 2009.3 | 1746.7 | 1623.2 | 1574.6 | 1539.6 | 1494.8 | 1491.0 |
| 37.5° | 3721.1 | 3459.4 | 2959.5 | 2231.1 | 1817.7 | 1592.1 | 1518.2 | 1463.7 | 1407.3 | 1348.0 | 1340.2 |
| 40° | 3988.5 | 3728.8 | 2962.4 | 2054.1 | 1630.0 | 1490.0 | 1427.7 | 1356.7 | 1286.7 | 1220.6 | 1211.8 |
| 42.5° | 4269.6 | 3979.8 | 2910.9 | 1849.8 | 1476.4 | 1401.5 | 1338.3 | 1248.8 | 1170.0 | 1125.3 | 1120.4 |
| 45° | 4520.5 | 4182.1 | 2794.2 | 1634.9 | 1362.6 | 1327.6 | 1246.8 | 1150.6 | 1108.7 | 1076.6 | 1069.8 |
| 47.5° | 4717.9 | 4316.3 | 2636.6 | 1442.3 | 1270.2 | 1251.7 | 1146.7 | 1097.1 | 1065.0 | 1035.8 | 1029.0 |
| 50° | 4815.2 | 4346.4 | 2431.4 | 1285.7 | 1184.6 | 1162.2 | 1090.3 | 1052.3 | 1030.9 | 1007.6 | 1001.7 |
| 52.5° | 4935.8 | 4380.5 | 2254.4 | 1154.4 | 1100.9 | 1070.8 | 1043.6 | 1013.4 | 997.9 | 983.3 | 978.4 |
| 55° | 5213.0 | 4508.8 | 2161.1 | 1049.4 | 1021.2 | 1007.6 | 1003.7 | 978.4 | 973.5 | 963.8 | 955.1 |
| 57.5° | 5325.8 | 4426.2 | 1940.3 | 963.8 | 958.0 | 959.9 | 969.7 | 946.3 | 941.4 | 929.8 | 923.9 |
| 60° | 4283.2 | 3345.6 | 1313.9 | 889.9 | 905.5 | 918.1 | 927.8 | 904.5 | 897.7 | 895.7 | 888.0 |
| 62.5° | 2744.6 | 2058.0 | 917.1 | 820.8 | 844.2 | 859.8 | 865.6 | 843.2 | 838.4 | 853.9 | 854.9 |
| 65° | 1428.7 | 1121.4 | 744.0 | 746.9 | 766.4 | 789.7 | 801.4 | 793.6 | 791.7 | 808.2 | 809.2 |
| 67.5° | 729.4 | 685.7 | 648.7 | 659.4 | 675.0 | 705.1 | 732.3 | 766.4 | 778.1 | 780.0 | 781.0 |
| 70° | 621.5 | 602.0 | 583.5 | 590.4 | 606.9 | 623.4 | 649.7 | 666.2 | 646.8 | 641.9 | 640.0 |
| 72.5° | 529.1 | 514.5 | 505.7 | 513.5 | 522.3 | 519.4 | 511.6 | 519.4 | 522.3 | 523.2 | 524.2 |
| 75° | 411.4 | 400.7 | 393.9 | 394.9 | 394.9 | 384.2 | 369.6 | 360.8 | 351.1 | 343.3 | 343.3 |
| 77.5° | 251.9 | 253.8 | 260.6 | 259.7 | 258.7 | 254.8 | 240.2 | 232.4 | 209.1 | 202.3 | 202.3 |
| 80° | 143.9 | 146.9 | 153.7 | 155.6 | 155.6 | 150.7 | 136.2 | 127.4 | 116.7 | 111.8 | 110.9 |
| 82.5° | 87.5 | 91.4 | 95.3 | 97.3 | 98.2 | 92.4 | 79.8 | 72.9 | 67.1 | 62.2 | 62.2 |
| 85° | 45.7 | 47.7 | 51.5 | 52.5 | 49.6 | 43.8 | 37.0 | 34.0 | 28.2 | 27.2 | 27.2 |
| 87.5° | 12.6 | 13.6 | 15.6 | 12.6 | 11.7 | 8.8 | 4.9 | 3.9 | 1.9 | 1.0 | 1.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)