

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643528

Luminaire Tested: GWS-SA6F-727-U-RW-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6F-727-U-RW-W
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS
Light Source: (96) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 42847.4 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B5 - U0 - G5


Input Watts (W): 372.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643528
 CATALOG NUMBER: GWS-SA6F-727-U-RW-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 5.6 fc
 Type III - Short - N/A

REPORT NUMBER: P643528
CATALOG NUMBER: GWS-SA6F-727-U-RW-W

Luminous Intensity Polar Plot



— Vertical Plane Through 67-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P643528

CATALOG NUMBER: GWS-SA6F-727-U-RW-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 21187.3 | 0.0 | 21187.3 |
| | % Fixture | 49.4 | 0.0 | 49.4 |
| Street Side | Lumens | 21660.1 | 0.0 | 21660.1 |
| | % Fixture | 50.6 | 0.0 | 50.6 |
| Total | Lumens | 42847.4 | 0.0 | 42847.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 425.7 | 1.0 |
| 10°-20° | 1438.1 | 3.4 |
| 20°-30° | 2821.4 | 6.6 |
| 30°-40° | 4806.8 | 11.2 |
| 40°-50° | 7718.8 | 18.0 |
| 50°-60° | 10488.3 | 24.5 |
| 60°-70° | 10032.7 | 23.4 |
| 70°-80° | 4769.9 | 11.1 |
| 80°-90° | 345.7 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 42847.4 | 100.0 |
| 0°-180° | 42847.4 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P643528


CATALOG NUMBER: GWS-SA6F-727-U-RW-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2389.1 | 5.6 | | | |
| FM (30°-60°) | 11941.9 | 27.9 | | | |
| FH (60°-80°) | 7173.8 | 16.7 | | | G3/7500 |
| FVH (80°-90°) | 155.4 | 0.4 | | | G2/225 |
| BL (0°-30°) | 2296.1 | 5.4 | B3/2500 | | |
| BM (30°-60°) | 11072.0 | 25.8 | B5 | | |
| BH (60°-80°) | 7628.9 | 17.8 | B5 | | G5 |
| BVH (80°-90°) | 190.3 | 0.4 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G5

Type III Short





REPORT NUMBER: P643528
 CATALOG NUMBER: GWS-SA6F-727-U-RW-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 67° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 |
| 2.5° | 4249.0 | 4255.0 | 4263.9 | 4281.8 | 4299.7 | 4326.6 | 4353.5 | 4350.5 | 4362.4 | 4371.4 | 4380.3 |
| 5° | 4225.2 | 4231.1 | 4246.0 | 4269.9 | 4296.8 | 4341.5 | 4398.2 | 4422.1 | 4440.0 | 4472.8 | 4502.7 |
| 7.5° | 4275.9 | 4287.8 | 4308.7 | 4341.5 | 4383.3 | 4440.0 | 4517.6 | 4559.3 | 4586.2 | 4645.9 | 4696.6 |
| 10° | 4344.5 | 4359.4 | 4401.2 | 4463.9 | 4526.5 | 4613.1 | 4711.5 | 4774.2 | 4792.1 | 4869.7 | 4965.1 |
| 12.5° | 4410.2 | 4428.1 | 4496.7 | 4610.1 | 4723.5 | 4839.8 | 4956.2 | 5033.8 | 5039.7 | 5144.2 | 5251.6 |
| 15° | 4514.6 | 4529.5 | 4622.0 | 4768.2 | 4941.3 | 5102.4 | 5245.6 | 5299.3 | 5323.2 | 5397.8 | 5532.1 |
| 17.5° | 4744.3 | 4762.2 | 4881.6 | 5039.7 | 5221.8 | 5391.8 | 5535.1 | 5579.8 | 5579.8 | 5642.5 | 5752.9 |
| 20° | 4992.0 | 5009.9 | 5168.1 | 5371.0 | 5591.8 | 5764.8 | 5875.2 | 5833.5 | 5818.5 | 5836.4 | 5914.0 |
| 22.5° | 5269.5 | 5302.3 | 5454.5 | 5690.2 | 5961.8 | 6173.6 | 6230.3 | 6105.0 | 6063.2 | 6021.4 | 6039.3 |
| 25° | 5624.6 | 5663.4 | 5812.6 | 6063.2 | 6328.8 | 6552.6 | 6585.4 | 6391.4 | 6367.6 | 6221.4 | 6167.6 |
| 27.5° | 6033.4 | 6063.2 | 6248.2 | 6495.9 | 6743.5 | 6931.5 | 6967.3 | 6728.6 | 6648.0 | 6445.1 | 6319.8 |
| 30° | 6561.5 | 6588.4 | 6749.5 | 6994.2 | 7209.0 | 7340.3 | 7385.1 | 7056.8 | 6994.2 | 6683.9 | 6489.9 |
| 32.5° | 7137.4 | 7149.3 | 7313.5 | 7549.2 | 7740.1 | 7865.5 | 7802.8 | 7420.9 | 7328.4 | 6979.3 | 6713.7 |
| 35° | 7796.8 | 7796.8 | 8008.7 | 8199.7 | 8351.8 | 8387.6 | 8268.3 | 7832.6 | 7725.2 | 7346.3 | 7015.1 |
| 37.5° | 8444.3 | 8462.2 | 8659.2 | 8885.9 | 9020.2 | 9014.3 | 8796.4 | 8319.0 | 8196.7 | 7784.9 | 7417.9 |
| 40° | 9145.5 | 9184.3 | 9381.3 | 9634.9 | 9763.2 | 9745.3 | 9411.1 | 8880.0 | 8754.7 | 8268.3 | 7910.2 |
| 42.5° | 9790.1 | 9852.7 | 10082.5 | 10342.1 | 10482.3 | 10470.4 | 10121.3 | 9524.5 | 9402.2 | 8853.1 | 8495.1 |
| 45° | 10303.3 | 10368.9 | 10655.4 | 11016.4 | 11240.2 | 11219.3 | 10867.2 | 10192.9 | 10043.7 | 9467.8 | 9073.9 |
| 47.5° | 10753.8 | 10822.5 | 11141.7 | 11523.7 | 11878.8 | 11914.6 | 11592.3 | 10867.2 | 10709.1 | 10127.2 | 9682.6 |
| 50° | 11100.0 | 11132.8 | 11490.9 | 11908.6 | 12320.4 | 12520.3 | 12239.8 | 11544.6 | 11353.6 | 10777.7 | 10276.4 |
| 52.5° | 11073.1 | 11117.9 | 11559.5 | 12126.4 | 12678.4 | 13006.7 | 12812.7 | 12183.1 | 11998.1 | 11371.5 | 10882.2 |
| 55° | 10527.1 | 10571.8 | 11097.0 | 11923.5 | 12878.4 | 13361.7 | 13340.9 | 12791.8 | 12657.6 | 11977.2 | 11511.7 |
| 57.5° | 9730.4 | 9828.8 | 10351.0 | 11243.2 | 12615.8 | 13645.2 | 13728.8 | 13346.8 | 13206.6 | 12571.0 | 12135.4 |
| 60° | 8304.1 | 8435.4 | 9038.1 | 10195.9 | 11774.3 | 13549.7 | 14143.5 | 13815.3 | 13728.8 | 13123.0 | 12699.3 |
| 62.5° | 6033.4 | 6128.9 | 6931.5 | 8450.3 | 10527.1 | 12869.4 | 14492.6 | 14298.7 | 14233.0 | 13618.4 | 13209.6 |
| 65° | 3613.5 | 3831.3 | 4475.8 | 5976.7 | 8492.1 | 11586.3 | 14301.7 | 14931.3 | 14862.6 | 14128.6 | 13645.2 |
| 67.5° | 1829.1 | 1927.6 | 2181.2 | 3240.5 | 5711.1 | 9587.2 | 13343.8 | 15325.1 | 15408.7 | 14564.2 | 13800.4 |
| 70° | 1133.9 | 1160.7 | 1232.3 | 1599.4 | 2852.6 | 6298.9 | 10912.0 | 14298.7 | 14707.5 | 14495.6 | 13397.5 |
| 72.5° | 910.1 | 916.0 | 928.0 | 996.6 | 1369.6 | 2945.1 | 6898.7 | 11198.4 | 11935.5 | 13537.8 | 12821.7 |
| 75° | 754.9 | 757.9 | 760.9 | 781.8 | 853.4 | 1202.5 | 3356.8 | 7695.4 | 8557.7 | 11505.8 | 11887.7 |
| 77.5° | 605.7 | 590.8 | 602.7 | 611.7 | 629.6 | 671.4 | 1157.7 | 4105.8 | 4980.1 | 7552.2 | 9193.3 |
| 80° | 393.9 | 387.9 | 411.8 | 420.7 | 438.6 | 465.5 | 617.7 | 1393.5 | 1691.9 | 2748.1 | 2924.2 |
| 82.5° | 211.9 | 199.9 | 250.6 | 241.7 | 250.6 | 271.5 | 364.0 | 510.2 | 572.9 | 829.5 | 701.2 |
| 85° | 65.6 | 65.6 | 68.6 | 80.6 | 98.5 | 95.5 | 158.1 | 250.6 | 277.5 | 355.1 | 262.6 |
| 87.5° | 11.9 | 11.9 | 11.9 | 11.9 | 11.9 | 14.9 | 32.8 | 50.7 | 68.6 | 122.3 | 92.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643528

CATALOG NUMBER: GWS-SA6F-727-U-RW-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 | 4338.5 |
| 2.5° | 4398.2 | 4371.4 | 4386.3 | 4395.2 | 4392.2 | 4386.3 | 4356.4 | 4350.5 | 4335.6 | 4311.7 | 4305.7 |
| 5° | 4529.5 | 4499.7 | 4502.7 | 4493.7 | 4463.9 | 4425.1 | 4359.4 | 4326.6 | 4299.7 | 4269.9 | 4266.9 |
| 7.5° | 4735.4 | 4702.6 | 4693.6 | 4651.8 | 4568.3 | 4478.8 | 4374.3 | 4314.7 | 4269.9 | 4231.1 | 4225.2 |
| 10° | 4998.0 | 4965.1 | 4935.3 | 4836.8 | 4699.6 | 4580.2 | 4443.0 | 4356.4 | 4290.8 | 4243.1 | 4234.1 |
| 12.5° | 5290.4 | 5263.5 | 5188.9 | 5045.7 | 4881.6 | 4741.4 | 4601.1 | 4493.7 | 4398.2 | 4326.6 | 4317.7 |
| 15° | 5615.6 | 5556.0 | 5442.6 | 5257.6 | 5102.4 | 4989.0 | 4818.9 | 4672.7 | 4520.6 | 4425.1 | 4404.2 |
| 17.5° | 5842.4 | 5791.7 | 5657.4 | 5478.4 | 5356.0 | 5257.6 | 5057.6 | 4848.8 | 4642.9 | 4502.7 | 4472.8 |
| 20° | 6003.5 | 5949.8 | 5797.6 | 5666.4 | 5627.6 | 5544.0 | 5311.3 | 5069.6 | 4830.9 | 4657.8 | 4619.0 |
| 22.5° | 6119.9 | 6063.2 | 5908.1 | 5842.4 | 5896.1 | 5881.2 | 5654.4 | 5379.9 | 5096.4 | 4890.6 | 4842.8 |
| 25° | 6230.3 | 6176.6 | 6039.3 | 6063.2 | 6206.4 | 6251.2 | 6006.5 | 5687.2 | 5365.0 | 5123.3 | 5066.6 |
| 27.5° | 6334.7 | 6266.1 | 6203.5 | 6334.7 | 6537.6 | 6621.2 | 6361.6 | 6000.6 | 5651.4 | 5403.8 | 5359.0 |
| 30° | 6495.9 | 6415.3 | 6406.4 | 6597.3 | 6919.6 | 6991.2 | 6704.7 | 6343.7 | 5997.6 | 5746.9 | 5690.2 |
| 32.5° | 6698.8 | 6624.2 | 6630.1 | 6916.6 | 7289.6 | 7349.3 | 7104.6 | 6767.4 | 6421.3 | 6170.6 | 6093.1 |
| 35° | 6973.3 | 6880.8 | 6931.5 | 7283.6 | 7659.6 | 7770.0 | 7573.0 | 7292.6 | 6955.4 | 6698.8 | 6612.2 |
| 37.5° | 7352.2 | 7218.0 | 7322.4 | 7692.4 | 8071.4 | 8235.5 | 8083.3 | 7874.4 | 7540.2 | 7280.6 | 7200.1 |
| 40° | 7835.6 | 7725.2 | 7767.0 | 8175.8 | 8566.7 | 8763.6 | 8668.1 | 8462.2 | 8131.0 | 7859.5 | 7767.0 |
| 42.5° | 8408.5 | 8298.1 | 8283.2 | 8718.9 | 9109.7 | 9408.1 | 9315.6 | 9127.6 | 8784.5 | 8474.2 | 8384.7 |
| 45° | 8969.5 | 8868.0 | 8888.9 | 9333.5 | 9772.2 | 10097.4 | 10004.9 | 9784.1 | 9411.1 | 9053.0 | 8981.4 |
| 47.5° | 9554.3 | 9470.8 | 9488.7 | 9960.1 | 10443.5 | 10768.8 | 10652.4 | 10383.8 | 9948.2 | 9566.3 | 9479.7 |
| 50° | 10154.1 | 10058.6 | 10085.5 | 10580.8 | 11103.0 | 11410.3 | 11231.3 | 10834.4 | 10354.0 | 9981.0 | 9906.4 |
| 52.5° | 10750.9 | 10637.5 | 10706.1 | 11174.6 | 11714.6 | 11959.3 | 11628.1 | 11147.7 | 10682.2 | 10312.2 | 10228.7 |
| 55° | 11437.2 | 11317.8 | 11243.2 | 11744.5 | 12278.6 | 12380.1 | 11926.5 | 11365.5 | 10813.5 | 10392.8 | 10342.1 |
| 57.5° | 12063.8 | 11962.3 | 11822.1 | 12323.4 | 12717.2 | 12642.6 | 12156.3 | 11305.9 | 10494.2 | 9954.2 | 9882.6 |
| 60° | 12624.7 | 12538.2 | 12415.9 | 12842.6 | 13021.6 | 12854.5 | 11971.3 | 10598.7 | 9706.5 | 9142.6 | 9109.7 |
| 62.5° | 13140.9 | 13048.4 | 12935.0 | 13299.1 | 13275.2 | 12887.3 | 11129.8 | 9512.6 | 8319.0 | 7713.3 | 7659.6 |
| 65° | 13549.7 | 13466.2 | 13433.4 | 13719.8 | 13681.0 | 12245.8 | 9819.9 | 7734.2 | 6078.1 | 5394.8 | 5373.9 |
| 67.5° | 13666.1 | 13633.3 | 13809.3 | 14295.7 | 13690.0 | 10956.7 | 7701.4 | 5129.3 | 3264.3 | 2616.8 | 2578.1 |
| 70° | 13230.5 | 13227.5 | 13731.7 | 14427.0 | 12448.7 | 8369.7 | 4544.4 | 2312.5 | 1641.1 | 1456.1 | 1432.3 |
| 72.5° | 12663.5 | 12654.6 | 13054.4 | 12445.7 | 9232.1 | 4580.2 | 1912.7 | 1238.3 | 1026.4 | 975.7 | 975.7 |
| 75° | 11732.6 | 11708.7 | 12010.1 | 9467.8 | 5191.9 | 1724.7 | 1014.5 | 850.4 | 805.6 | 796.7 | 796.7 |
| 77.5° | 9563.3 | 9363.4 | 8888.9 | 5851.4 | 1811.2 | 847.4 | 671.4 | 668.4 | 641.5 | 638.5 | 638.5 |
| 80° | 3145.0 | 3145.0 | 3655.2 | 2231.9 | 799.7 | 522.2 | 474.4 | 498.3 | 471.5 | 453.5 | 450.6 |
| 82.5° | 513.2 | 707.2 | 1005.6 | 638.5 | 432.7 | 325.2 | 292.4 | 310.3 | 325.2 | 259.6 | 259.6 |
| 85° | 202.9 | 265.6 | 387.9 | 298.4 | 199.9 | 131.3 | 140.2 | 155.2 | 137.3 | 119.4 | 116.4 |
| 87.5° | 77.6 | 95.5 | 137.3 | 71.6 | 41.8 | 23.9 | 14.9 | 14.9 | 11.9 | 11.9 | 11.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)