

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636615

Luminaire Tested: GWS-SA4B-727-U-SLR-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-727-U-SLR-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (64) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7512.2 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636615
 CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P636615
CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P636615
 CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 927.0 | 0.0 | 927.0 |
| | % Fixture | 12.3 | 0.0 | 12.3 |
| Street Side | Lumens | 6585.2 | 0.0 | 6585.2 |
| | % Fixture | 87.7 | 0.0 | 87.7 |
| Total | Lumens | 7512.2 | 0.0 | 7512.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 34.6 | 0.5 |
| 10°-20° | 131.0 | 1.7 |
| 20°-30° | 284.7 | 3.8 |
| 30°-40° | 467.3 | 6.2 |
| 40°-50° | 859.1 | 11.4 |
| 50°-60° | 1844.9 | 24.6 |
| 60°-70° | 2478.0 | 33.0 |
| 70°-80° | 1290.3 | 17.2 |
| 80°-90° | 122.3 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 7512.2 | 100.0 |
| 0°-180° | 7512.2 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P636615
 CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 317.4 | 4.2 | | | |
| FM (30°-60°) | 2636.7 | 35.1 | | | |
| FH (60°-80°) | 3514.3 | 46.8 | | | G2/5000 |
| FVH (80°-90°) | 116.9 | 1.6 | | | G2/225 |
| BL (0°-30°) | 133.0 | 1.8 | B1/500 | | |
| BM (30°-60°) | 534.6 | 7.1 | B1/1000 | | |
| BH (60°-80°) | 254.0 | 3.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 5.5 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P636615

CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|--------|--------|--------|
| 0° | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 |
| 2.5° | 398.3 | 400.0 | 401.8 | 407.8 | 412.2 | 415.6 | 416.5 | 413.9 | 407.8 | 401.8 | 393.1 |
| 5° | 386.1 | 387.9 | 393.9 | 410.4 | 426.9 | 439.9 | 444.3 | 441.7 | 426.9 | 407.8 | 387.9 |
| 7.5° | 385.3 | 388.7 | 403.5 | 438.2 | 473.8 | 500.7 | 507.6 | 501.5 | 473.8 | 435.6 | 394.8 |
| 10° | 416.5 | 422.6 | 444.3 | 506.8 | 571.8 | 619.6 | 638.6 | 612.6 | 568.4 | 498.9 | 432.1 |
| 12.5° | 498.1 | 508.5 | 550.1 | 641.3 | 741.9 | 805.3 | 831.3 | 799.2 | 729.8 | 629.1 | 523.2 |
| 15° | 626.5 | 642.1 | 704.6 | 840.8 | 959.7 | 1016.1 | 1024.8 | 1006.6 | 925.9 | 814.8 | 672.5 |
| 17.5° | 807.9 | 830.4 | 927.6 | 1066.4 | 1152.3 | 1172.3 | 1169.7 | 1150.6 | 1091.6 | 1015.2 | 880.7 |
| 20° | 1024.8 | 1051.7 | 1147.1 | 1261.7 | 1270.4 | 1246.9 | 1233.9 | 1222.6 | 1202.7 | 1189.7 | 1084.7 |
| 22.5° | 1243.5 | 1276.4 | 1376.2 | 1404.9 | 1326.8 | 1259.1 | 1227.0 | 1235.6 | 1265.1 | 1329.4 | 1286.8 |
| 25° | 1461.3 | 1492.5 | 1586.2 | 1509.0 | 1352.8 | 1240.0 | 1199.2 | 1220.0 | 1290.3 | 1429.1 | 1483.8 |
| 27.5° | 1715.5 | 1738.9 | 1794.5 | 1580.1 | 1357.1 | 1224.4 | 1184.4 | 1216.6 | 1302.5 | 1491.6 | 1699.9 |
| 30° | 1980.2 | 1994.0 | 1967.1 | 1599.2 | 1342.4 | 1200.9 | 1169.7 | 1216.6 | 1323.3 | 1533.3 | 1862.1 |
| 32.5° | 2174.5 | 2177.1 | 2089.5 | 1601.0 | 1334.6 | 1181.8 | 1155.8 | 1211.3 | 1343.2 | 1568.0 | 2019.2 |
| 35° | 2375.0 | 2362.0 | 2206.6 | 1627.0 | 1355.4 | 1188.8 | 1166.2 | 1226.1 | 1374.5 | 1608.8 | 2157.2 |
| 37.5° | 2578.0 | 2554.6 | 2337.7 | 1669.5 | 1409.2 | 1264.3 | 1250.4 | 1301.6 | 1424.8 | 1665.2 | 2309.0 |
| 40° | 2786.3 | 2754.2 | 2473.9 | 1733.7 | 1528.9 | 1521.1 | 1568.9 | 1562.8 | 1562.8 | 1737.2 | 2465.2 |
| 42.5° | 3040.5 | 3003.2 | 2675.2 | 1915.1 | 1808.3 | 1982.8 | 2112.9 | 2032.2 | 1883.0 | 1902.9 | 2668.3 |
| 45° | 3376.3 | 3344.2 | 3024.0 | 2262.2 | 2246.5 | 2647.4 | 2822.7 | 2663.1 | 2291.7 | 2285.6 | 3007.5 |
| 47.5° | 3913.4 | 3907.4 | 3580.2 | 2664.8 | 2782.8 | 3493.5 | 3831.9 | 3524.7 | 2757.6 | 2690.8 | 3649.7 |
| 50° | 4668.4 | 4650.1 | 4273.6 | 3136.8 | 3420.6 | 4541.7 | 5145.6 | 4633.7 | 3320.8 | 3163.7 | 4509.6 |
| 52.5° | 5518.7 | 5537.8 | 5244.5 | 3652.3 | 4098.3 | 5707.9 | 6548.7 | 5904.0 | 3932.5 | 3765.1 | 5591.6 |
| 55° | 6319.7 | 6429.0 | 6351.8 | 4255.3 | 4760.4 | 6995.6 | 8089.8 | 7297.6 | 4690.1 | 4552.1 | 6804.7 |
| 57.5° | 6946.2 | 7254.2 | 7795.7 | 5131.7 | 5538.7 | 8502.0 | 9810.5 | 8808.3 | 5574.3 | 5830.3 | 8456.0 |
| 60° | 6980.9 | 7388.7 | 8646.0 | 6965.2 | 6540.1 | 9794.0 | 11528.6 | 10284.3 | 6964.4 | 8000.4 | 9749.8 |
| 62.5° | 6457.6 | 6895.0 | 8092.4 | 7798.3 | 7630.8 | 10893.4 | 12410.2 | 11360.3 | 8331.9 | 9271.7 | 9366.2 |
| 65° | 5858.9 | 6300.6 | 7474.6 | 6853.3 | 7504.1 | 10846.6 | 12186.4 | 11385.4 | 8456.0 | 8407.4 | 8679.9 |
| 67.5° | 4953.9 | 5350.4 | 6413.4 | 6066.3 | 6916.7 | 10323.3 | 11152.0 | 10667.8 | 7790.5 | 7863.3 | 7984.8 |
| 70° | 3615.8 | 3997.6 | 4984.2 | 5001.6 | 6040.2 | 9380.1 | 9582.3 | 9515.5 | 7174.4 | 7251.6 | 6904.5 |
| 72.5° | 2611.9 | 2933.8 | 3785.0 | 4101.7 | 4822.0 | 7865.9 | 7726.2 | 7984.0 | 6155.7 | 6458.5 | 5545.6 |
| 75° | 1877.8 | 2119.0 | 2776.7 | 3568.1 | 3822.3 | 5841.5 | 5530.9 | 6183.4 | 4939.1 | 5561.3 | 4169.4 |
| 77.5° | 761.9 | 846.9 | 1092.5 | 2403.6 | 2512.1 | 3929.9 | 3385.9 | 4491.4 | 3521.2 | 3654.0 | 2020.9 |
| 80° | 31.2 | 34.7 | 45.1 | 1240.8 | 1722.4 | 2211.0 | 1811.8 | 2401.0 | 2325.5 | 1471.7 | 477.2 |
| 82.5° | 3.5 | 3.5 | 7.8 | 357.5 | 754.1 | 1220.0 | 853.8 | 1383.2 | 1177.5 | 623.9 | 216.9 |
| 85° | 0.9 | 0.9 | 1.7 | 40.8 | 177.0 | 195.2 | 115.4 | 424.3 | 547.5 | 255.1 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 4.3 | 7.8 | 8.7 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636615

CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 |
| 2.5° | 393.1 | 388.7 | 383.5 | 378.3 | 375.7 | 368.8 | 366.2 | 364.4 | 362.7 | 363.6 | 363.6 |
| 5° | 380.1 | 370.5 | 359.2 | 348.0 | 341.9 | 334.9 | 331.5 | 329.7 | 330.6 | 334.1 | 334.1 |
| 7.5° | 378.3 | 360.1 | 335.8 | 321.1 | 314.1 | 308.9 | 305.4 | 303.7 | 304.6 | 308.9 | 310.6 |
| 10° | 407.0 | 374.9 | 331.5 | 306.3 | 298.5 | 293.3 | 289.8 | 287.2 | 285.5 | 289.0 | 289.8 |
| 12.5° | 468.6 | 424.3 | 352.3 | 304.6 | 290.7 | 283.7 | 281.1 | 275.9 | 273.3 | 275.1 | 275.9 |
| 15° | 596.1 | 519.8 | 393.9 | 311.5 | 283.7 | 275.9 | 271.6 | 267.3 | 262.9 | 262.1 | 262.9 |
| 17.5° | 762.7 | 653.4 | 457.3 | 328.0 | 278.5 | 269.0 | 262.9 | 256.8 | 250.8 | 249.9 | 249.0 |
| 20° | 969.3 | 817.4 | 545.8 | 354.0 | 274.2 | 262.9 | 254.2 | 245.6 | 237.8 | 235.2 | 235.2 |
| 22.5° | 1157.5 | 1015.2 | 659.5 | 386.1 | 268.1 | 254.2 | 243.8 | 233.4 | 224.7 | 220.4 | 219.5 |
| 25° | 1387.5 | 1225.2 | 795.7 | 423.5 | 259.5 | 243.0 | 231.7 | 221.3 | 212.6 | 207.4 | 205.7 |
| 27.5° | 1619.2 | 1446.5 | 950.2 | 472.0 | 249.0 | 231.7 | 221.3 | 211.7 | 202.2 | 196.1 | 194.4 |
| 30° | 1843.9 | 1685.1 | 1123.7 | 532.8 | 241.2 | 220.4 | 211.7 | 202.2 | 193.5 | 184.0 | 181.4 |
| 32.5° | 2085.1 | 1929.0 | 1318.1 | 600.5 | 235.2 | 212.6 | 203.0 | 194.4 | 183.1 | 174.4 | 170.1 |
| 35° | 2317.7 | 2180.6 | 1532.4 | 666.4 | 229.1 | 205.7 | 195.2 | 186.6 | 174.4 | 164.9 | 158.8 |
| 37.5° | 2552.0 | 2436.6 | 1756.3 | 706.3 | 220.4 | 196.1 | 186.6 | 179.6 | 165.7 | 154.5 | 147.5 |
| 40° | 2800.2 | 2701.2 | 1998.4 | 689.8 | 212.6 | 185.7 | 180.5 | 172.7 | 157.1 | 144.0 | 135.4 |
| 42.5° | 3072.6 | 2953.7 | 2244.8 | 626.5 | 205.7 | 177.0 | 171.8 | 164.0 | 149.2 | 133.6 | 122.3 |
| 45° | 3415.4 | 3230.5 | 2447.0 | 531.0 | 209.1 | 168.3 | 157.9 | 156.2 | 142.3 | 122.3 | 108.5 |
| 47.5° | 4004.6 | 3655.7 | 2604.0 | 469.4 | 232.6 | 158.8 | 146.6 | 151.0 | 136.2 | 111.1 | 95.4 |
| 50° | 4906.1 | 4360.3 | 2750.7 | 465.1 | 268.1 | 154.5 | 136.2 | 147.5 | 130.2 | 99.8 | 84.2 |
| 52.5° | 5765.2 | 5076.2 | 2844.4 | 503.3 | 299.4 | 165.7 | 125.8 | 143.2 | 125.8 | 92.0 | 76.4 |
| 55° | 6586.9 | 5489.2 | 2676.9 | 531.0 | 328.9 | 199.6 | 118.0 | 136.2 | 120.6 | 87.6 | 73.8 |
| 57.5° | 7472.9 | 5673.2 | 2107.7 | 587.5 | 349.7 | 228.2 | 119.7 | 125.8 | 113.7 | 85.0 | 72.9 |
| 60° | 7737.5 | 5438.0 | 1272.1 | 661.2 | 338.4 | 236.9 | 132.8 | 111.9 | 104.1 | 79.8 | 70.3 |
| 62.5° | 7326.2 | 4880.1 | 750.6 | 602.2 | 328.9 | 223.9 | 151.9 | 103.3 | 94.6 | 72.9 | 65.1 |
| 65° | 6711.0 | 4122.6 | 489.4 | 508.5 | 348.8 | 199.6 | 161.4 | 98.9 | 85.9 | 65.9 | 57.3 |
| 67.5° | 6008.1 | 3320.8 | 342.8 | 300.2 | 321.9 | 179.6 | 136.2 | 98.1 | 77.2 | 55.5 | 46.9 |
| 70° | 5060.6 | 2486.9 | 241.2 | 198.7 | 268.1 | 159.7 | 105.9 | 95.4 | 67.7 | 45.1 | 36.4 |
| 72.5° | 3910.0 | 1556.7 | 179.6 | 128.4 | 190.9 | 130.2 | 84.2 | 80.7 | 54.7 | 37.3 | 27.8 |
| 75° | 2883.5 | 887.7 | 126.7 | 92.8 | 125.8 | 98.9 | 62.5 | 57.3 | 46.9 | 35.6 | 25.2 |
| 77.5° | 1505.5 | 444.3 | 79.0 | 71.2 | 72.0 | 61.6 | 45.1 | 41.7 | 43.4 | 35.6 | 23.4 |
| 80° | 289.0 | 88.5 | 47.7 | 52.1 | 39.0 | 39.0 | 33.0 | 34.7 | 38.2 | 28.6 | 20.0 |
| 82.5° | 120.6 | 19.1 | 26.0 | 29.5 | 24.3 | 26.9 | 26.9 | 27.8 | 26.9 | 20.8 | 14.8 |
| 85° | 0.0 | 0.0 | 11.3 | 12.1 | 16.5 | 16.5 | 13.9 | 13.9 | 13.9 | 12.1 | 8.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 2.6 | 5.2 | 6.1 | 6.9 | 5.2 | 3.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636615

CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 |
| 2.5° | 362.7 | 361.0 | 363.6 | 365.3 | 367.0 | 367.0 | 365.3 | 363.6 | 361.0 | 363.6 | 361.0 |
| 5° | 334.9 | 337.5 | 341.9 | 343.6 | 345.4 | 341.9 | 340.1 | 334.9 | 330.6 | 331.5 | 329.7 |
| 7.5° | 313.2 | 315.9 | 321.1 | 324.5 | 324.5 | 322.8 | 317.6 | 312.4 | 305.4 | 305.4 | 304.6 |
| 10° | 293.3 | 296.8 | 302.8 | 307.2 | 308.9 | 307.2 | 302.0 | 295.0 | 289.0 | 289.0 | 286.3 |
| 12.5° | 276.8 | 281.1 | 288.1 | 294.2 | 295.9 | 294.2 | 289.0 | 282.0 | 275.1 | 275.1 | 273.3 |
| 15° | 262.9 | 268.1 | 275.9 | 282.9 | 285.5 | 282.9 | 276.8 | 268.1 | 261.2 | 262.1 | 259.5 |
| 17.5° | 249.9 | 254.2 | 264.7 | 272.5 | 275.1 | 272.5 | 264.7 | 253.4 | 246.4 | 248.2 | 246.4 |
| 20° | 235.2 | 240.4 | 250.8 | 259.5 | 262.1 | 259.5 | 250.8 | 238.6 | 231.7 | 231.7 | 232.6 |
| 22.5° | 219.5 | 224.7 | 235.2 | 241.2 | 244.7 | 242.1 | 233.4 | 222.1 | 215.2 | 215.2 | 216.1 |
| 25° | 205.7 | 208.3 | 216.1 | 222.1 | 223.0 | 220.4 | 213.5 | 204.8 | 199.6 | 202.2 | 203.0 |
| 27.5° | 192.6 | 192.6 | 196.1 | 199.6 | 198.7 | 196.1 | 193.5 | 186.6 | 185.7 | 188.3 | 190.9 |
| 30° | 178.8 | 174.4 | 172.7 | 170.1 | 169.2 | 168.3 | 170.9 | 170.9 | 172.7 | 176.1 | 178.8 |
| 32.5° | 166.6 | 157.9 | 150.1 | 142.3 | 138.0 | 141.4 | 148.4 | 154.5 | 160.5 | 165.7 | 168.3 |
| 35° | 152.7 | 138.8 | 125.8 | 115.4 | 108.5 | 113.7 | 125.0 | 136.2 | 146.6 | 153.6 | 157.9 |
| 37.5° | 138.8 | 118.9 | 103.3 | 90.2 | 85.0 | 89.4 | 101.5 | 117.1 | 132.8 | 141.4 | 147.5 |
| 40° | 124.1 | 98.9 | 80.7 | 70.3 | 65.1 | 69.4 | 81.6 | 97.2 | 118.0 | 129.3 | 137.1 |
| 42.5° | 109.3 | 81.6 | 65.1 | 54.7 | 52.1 | 54.7 | 64.2 | 79.8 | 102.4 | 116.3 | 126.7 |
| 45° | 94.6 | 67.7 | 52.1 | 44.3 | 41.7 | 44.3 | 52.1 | 65.1 | 87.6 | 103.3 | 115.4 |
| 47.5° | 81.6 | 57.3 | 43.4 | 36.4 | 34.7 | 37.3 | 43.4 | 54.7 | 73.8 | 89.4 | 103.3 |
| 50° | 71.2 | 50.3 | 37.3 | 31.2 | 29.5 | 32.1 | 37.3 | 46.0 | 62.5 | 76.4 | 91.1 |
| 52.5° | 64.2 | 46.9 | 33.0 | 26.9 | 26.0 | 27.8 | 32.1 | 39.0 | 52.9 | 65.1 | 79.0 |
| 55° | 62.5 | 46.9 | 30.4 | 24.3 | 23.4 | 25.2 | 28.6 | 33.8 | 46.0 | 56.4 | 68.6 |
| 57.5° | 64.2 | 50.3 | 28.6 | 20.8 | 20.0 | 21.7 | 25.2 | 29.5 | 39.9 | 48.6 | 59.9 |
| 60° | 64.2 | 51.2 | 25.2 | 16.5 | 15.6 | 17.4 | 20.8 | 26.0 | 35.6 | 42.5 | 52.1 |
| 62.5° | 58.1 | 46.9 | 20.8 | 13.0 | 11.3 | 13.0 | 17.4 | 21.7 | 31.2 | 38.2 | 46.0 |
| 65° | 50.3 | 39.9 | 17.4 | 9.5 | 7.8 | 9.5 | 13.9 | 18.2 | 26.9 | 33.0 | 41.7 |
| 67.5° | 40.8 | 30.4 | 13.0 | 6.9 | 5.2 | 6.9 | 10.4 | 14.8 | 22.6 | 28.6 | 37.3 |
| 70° | 30.4 | 21.7 | 10.4 | 6.1 | 5.2 | 6.1 | 9.5 | 13.9 | 20.0 | 26.0 | 34.7 |
| 72.5° | 22.6 | 14.8 | 8.7 | 6.1 | 4.3 | 6.1 | 8.7 | 13.0 | 19.1 | 25.2 | 33.0 |
| 75° | 19.1 | 12.1 | 7.8 | 5.2 | 4.3 | 5.2 | 7.8 | 12.1 | 17.4 | 23.4 | 31.2 |
| 77.5° | 18.2 | 11.3 | 6.9 | 4.3 | 3.5 | 4.3 | 6.9 | 10.4 | 15.6 | 21.7 | 30.4 |
| 80° | 15.6 | 9.5 | 6.1 | 3.5 | 2.6 | 3.5 | 6.1 | 8.7 | 12.1 | 16.5 | 23.4 |
| 82.5° | 12.1 | 7.8 | 4.3 | 1.7 | 0.9 | 1.7 | 4.3 | 5.2 | 7.8 | 9.5 | 13.9 |
| 85° | 7.8 | 4.3 | 1.7 | 0.0 | 0.0 | 0.0 | 1.7 | 3.5 | 3.5 | 4.3 | 6.9 |
| 87.5° | 3.5 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 1.7 | 2.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636615
 CATALOG NUMBER: GWS-SA4B-727-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|
| 0° | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 | 390.5 |
| 2.5° | 366.2 | 367.0 | 368.8 | 371.4 | 377.5 | 382.7 | 387.9 | 394.8 | 398.3 | 398.3 |
| 5° | 331.5 | 332.3 | 333.2 | 336.7 | 345.4 | 352.3 | 363.6 | 377.5 | 384.4 | 386.1 |
| 7.5° | 304.6 | 306.3 | 308.0 | 310.6 | 319.3 | 328.9 | 343.6 | 369.7 | 382.7 | 385.3 |
| 10° | 289.0 | 291.6 | 295.0 | 300.2 | 308.0 | 318.5 | 343.6 | 390.5 | 412.2 | 416.5 |
| 12.5° | 276.8 | 281.1 | 284.6 | 290.7 | 300.2 | 316.7 | 367.0 | 449.5 | 487.7 | 498.1 |
| 15° | 264.7 | 269.9 | 275.1 | 281.1 | 291.6 | 322.8 | 412.2 | 555.3 | 618.7 | 626.5 |
| 17.5° | 252.5 | 258.6 | 265.5 | 272.5 | 285.5 | 337.5 | 483.3 | 702.0 | 790.5 | 807.9 |
| 20° | 238.6 | 246.4 | 256.0 | 264.7 | 279.4 | 361.0 | 582.2 | 876.4 | 987.5 | 1024.8 |
| 22.5° | 223.9 | 233.4 | 244.7 | 256.0 | 272.5 | 389.6 | 702.0 | 1063.8 | 1219.2 | 1243.5 |
| 25° | 211.7 | 221.3 | 231.7 | 243.0 | 261.2 | 424.3 | 846.9 | 1296.4 | 1437.8 | 1461.3 |
| 27.5° | 200.4 | 210.0 | 219.5 | 229.9 | 249.9 | 469.4 | 1021.3 | 1543.7 | 1691.2 | 1715.5 |
| 30° | 188.3 | 199.6 | 209.1 | 219.5 | 239.5 | 525.0 | 1222.6 | 1817.9 | 1957.6 | 1980.2 |
| 32.5° | 177.9 | 189.2 | 198.7 | 209.1 | 231.7 | 585.7 | 1434.4 | 2060.9 | 2174.5 | 2174.5 |
| 35° | 169.2 | 181.4 | 188.3 | 202.2 | 225.6 | 624.8 | 1634.8 | 2292.5 | 2378.4 | 2375.0 |
| 37.5° | 159.7 | 174.4 | 179.6 | 189.2 | 217.8 | 629.1 | 1823.1 | 2537.2 | 2600.6 | 2578.0 |
| 40° | 150.1 | 165.7 | 173.5 | 178.8 | 209.1 | 593.5 | 2029.6 | 2762.0 | 2815.8 | 2786.3 |
| 42.5° | 141.4 | 153.6 | 164.9 | 170.9 | 203.9 | 531.0 | 2195.3 | 3002.3 | 3066.5 | 3040.5 |
| 45° | 132.8 | 143.2 | 150.1 | 161.4 | 207.4 | 487.7 | 2337.7 | 3282.6 | 3395.4 | 3376.3 |
| 47.5° | 124.1 | 132.8 | 137.1 | 154.5 | 230.8 | 467.7 | 2424.4 | 3716.5 | 3929.1 | 3913.4 |
| 50° | 114.5 | 125.0 | 125.0 | 152.7 | 265.5 | 474.6 | 2499.9 | 4344.7 | 4673.6 | 4668.4 |
| 52.5° | 105.0 | 116.3 | 114.5 | 165.7 | 292.4 | 506.8 | 2585.8 | 4899.2 | 5471.0 | 5518.7 |
| 55° | 95.4 | 105.9 | 107.6 | 191.8 | 308.0 | 534.5 | 2253.5 | 5132.6 | 6152.2 | 6319.7 |
| 57.5° | 85.0 | 91.1 | 111.9 | 211.7 | 302.8 | 615.2 | 1543.7 | 5175.1 | 6586.9 | 6946.2 |
| 60° | 73.8 | 79.0 | 126.7 | 207.4 | 286.3 | 568.4 | 971.9 | 4793.3 | 6525.3 | 6980.9 |
| 62.5° | 64.2 | 72.9 | 133.6 | 183.1 | 291.6 | 492.9 | 619.6 | 4085.3 | 5937.9 | 6457.6 |
| 65° | 56.4 | 70.3 | 121.5 | 165.7 | 295.0 | 334.1 | 418.2 | 3323.4 | 5364.3 | 5858.9 |
| 67.5° | 50.3 | 78.1 | 99.8 | 147.5 | 253.4 | 235.2 | 287.2 | 2582.4 | 4510.4 | 4953.9 |
| 70° | 46.0 | 79.8 | 81.6 | 126.7 | 196.1 | 151.0 | 189.2 | 1738.1 | 3109.1 | 3615.8 |
| 72.5° | 41.7 | 59.0 | 61.6 | 101.5 | 126.7 | 92.0 | 122.3 | 994.4 | 2266.5 | 2611.9 |
| 75° | 39.9 | 39.9 | 42.5 | 65.9 | 70.3 | 66.8 | 79.0 | 593.5 | 1625.3 | 1877.8 |
| 77.5° | 37.3 | 30.4 | 26.9 | 42.5 | 38.2 | 47.7 | 46.9 | 263.8 | 704.6 | 761.9 |
| 80° | 29.5 | 21.7 | 18.2 | 26.9 | 26.0 | 32.1 | 27.8 | 21.7 | 32.1 | 31.2 |
| 82.5° | 18.2 | 13.9 | 13.0 | 16.5 | 14.8 | 16.5 | 13.0 | 3.5 | 3.5 | 3.5 |
| 85° | 8.7 | 7.8 | 6.9 | 6.9 | 7.8 | 6.9 | 5.2 | 1.7 | 0.9 | 0.9 |
| 87.5° | 4.3 | 4.3 | 3.5 | 2.6 | 3.5 | 3.5 | 2.6 | 0.9 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)