

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636627

Luminaire Tested: GWS-SA4B-727-U-T3-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P636627  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-25)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4B-727-U-T3-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (64) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10331.6 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B2 - U0 - G2  
  
Input Watts (W): 94.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P636627  
 CATALOG NUMBER: GWS-SA4B-727-U-T3-W-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.3 fc  
 Type II - Short - N/A

REPORT NUMBER: P636627  
CATALOG NUMBER: GWS-SA4B-727-U-T3-W-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636627

CATALOG NUMBER: GWS-SA4B-727-U-T3-W-GRSWH

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3269.9   | 0.0    | 3269.9  |
|                    | % Fixture | 31.6     | 0.0    | 31.6    |
| <b>Street Side</b> | Lumens    | 7061.7   | 0.0    | 7061.7  |
|                    | % Fixture | 68.4     | 0.0    | 68.4    |
| <b>Total</b>       | Lumens    | 10331.6  | 0.0    | 10331.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 189.0   | 1.8       |
| 10°-20°   | 621.6   | 6.0       |
| 20°-30°   | 1119.2  | 10.8      |
| 30°-40°   | 1690.4  | 16.4      |
| 40°-50°   | 2276.3  | 22.0      |
| 50°-60°   | 2735.3  | 26.5      |
| 60°-70°   | 1332.2  | 12.9      |
| 70°-80°   | 328.2   | 3.2       |
| 80°-90°   | 39.4    | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 10331.6 | 100.0     |
| 0°-180°   | 10331.6 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P636627


CATALOG NUMBER: GWS-SA4B-727-U-T3-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1037.8 | 10.0      |                         |      |         |
| FM (30°-60°)   | 4911.2 | 47.5      |                         |      |         |
| FH (60°-80°)   | 1097.9 | 10.6      |                         |      | G1/1800 |
| FVH (80°-90°)  | 14.8   | 0.1       |                         |      | G1/100  |
| BL (0°-30°)    | 892.0  | 8.6       | B2/1000                 |      |         |
| BM (30°-60°)   | 1790.9 | 17.3      | B2/2500                 |      |         |
| BH (60°-80°)   | 562.4  | 5.4       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 24.6   | 0.2       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**

Type II Short





REPORT NUMBER: P636627  
 CATALOG NUMBER: GWS-SA4B-727-U-T3-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 47°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 |
| 2.5°  | 1912.5 | 1911.7 | 1911.7 | 1916.9 | 1916.9 | 1918.6 | 1921.2 | 1923.8 | 1924.7 | 1920.3 | 1910.8 |
| 5°    | 1933.4 | 1933.4 | 1933.4 | 1937.7 | 1937.7 | 1939.4 | 1942.9 | 1943.8 | 1942.9 | 1936.0 | 1926.4 |
| 7.5°  | 1966.3 | 1966.3 | 1967.2 | 1972.4 | 1976.8 | 1979.4 | 1985.4 | 1984.6 | 1982.0 | 1970.7 | 1958.5 |
| 10°   | 2020.1 | 2022.7 | 2025.3 | 2031.4 | 2040.1 | 2046.2 | 2050.5 | 2050.5 | 2047.0 | 2029.7 | 2014.1 |
| 12.5° | 2096.5 | 2100.0 | 2102.6 | 2107.8 | 2114.7 | 2125.1 | 2134.7 | 2134.7 | 2130.3 | 2108.7 | 2085.2 |
| 15°   | 2185.9 | 2189.4 | 2188.5 | 2190.2 | 2203.2 | 2218.0 | 2225.8 | 2231.0 | 2232.7 | 2202.4 | 2165.9 |
| 17.5° | 2288.3 | 2291.7 | 2288.3 | 2283.1 | 2284.8 | 2308.2 | 2322.1 | 2341.2 | 2352.5 | 2311.7 | 2253.6 |
| 20°   | 2381.1 | 2377.7 | 2377.7 | 2381.1 | 2386.3 | 2415.0 | 2435.8 | 2467.0 | 2480.9 | 2431.5 | 2341.2 |
| 22.5° | 2479.2 | 2487.0 | 2483.5 | 2483.5 | 2504.4 | 2552.1 | 2577.2 | 2618.0 | 2632.8 | 2568.6 | 2447.1 |
| 25°   | 2605.9 | 2612.8 | 2611.1 | 2612.8 | 2637.1 | 2704.8 | 2730.0 | 2805.5 | 2820.2 | 2728.2 | 2564.2 |
| 27.5° | 2744.7 | 2756.0 | 2761.2 | 2759.5 | 2798.5 | 2887.0 | 2918.3 | 3023.3 | 3050.2 | 2907.0 | 2689.2 |
| 30°   | 2925.2 | 2937.4 | 2941.7 | 2940.0 | 2986.0 | 3106.6 | 3142.2 | 3261.9 | 3300.1 | 3118.7 | 2848.0 |
| 32.5° | 3134.3 | 3146.5 | 3159.5 | 3164.7 | 3223.7 | 3346.9 | 3398.1 | 3522.2 | 3576.9 | 3363.4 | 3039.8 |
| 35°   | 3341.7 | 3352.1 | 3377.3 | 3418.1 | 3498.8 | 3624.6 | 3669.7 | 3792.1 | 3845.0 | 3617.7 | 3271.4 |
| 37.5° | 3570.8 | 3577.8 | 3599.5 | 3655.9 | 3772.1 | 3891.9 | 3937.0 | 4054.2 | 4060.2 | 3863.3 | 3533.5 |
| 40°   | 3821.6 | 3821.6 | 3817.3 | 3872.8 | 3994.3 | 4114.9 | 4154.0 | 4221.6 | 4186.1 | 4052.4 | 3788.6 |
| 42.5° | 4034.2 | 4030.7 | 4034.2 | 4086.3 | 4176.5 | 4274.6 | 4308.4 | 4295.4 | 4250.3 | 4197.3 | 4019.5 |
| 45°   | 4226.0 | 4228.6 | 4259.8 | 4299.7 | 4346.6 | 4404.7 | 4424.7 | 4350.9 | 4310.2 | 4313.6 | 4204.3 |
| 47.5° | 4356.1 | 4358.7 | 4431.6 | 4498.5 | 4527.1 | 4545.3 | 4536.6 | 4434.2 | 4413.4 | 4452.5 | 4346.6 |
| 50°   | 4373.5 | 4387.4 | 4513.2 | 4650.3 | 4721.5 | 4724.1 | 4699.8 | 4574.8 | 4568.7 | 4613.0 | 4423.0 |
| 52.5° | 4377.0 | 4390.9 | 4547.9 | 4795.2 | 4980.1 | 5019.1 | 4991.3 | 4861.2 | 4797.8 | 4753.6 | 4516.7 |
| 55°   | 4364.0 | 4379.6 | 4553.1 | 4892.4 | 5246.5 | 5402.7 | 5405.3 | 5221.3 | 5019.1 | 4989.6 | 4784.0 |
| 57.5° | 3852.8 | 3858.9 | 4127.9 | 4645.1 | 5236.1 | 5678.6 | 5712.5 | 5462.5 | 5231.7 | 5203.9 | 4998.3 |
| 60°   | 2684.0 | 2708.3 | 3000.7 | 3683.6 | 4398.7 | 5178.8 | 5288.1 | 5215.2 | 5060.8 | 4858.6 | 4288.5 |
| 62.5° | 1344.2 | 1365.0 | 1658.3 | 2303.9 | 3033.7 | 3649.8 | 3766.9 | 3844.2 | 3880.6 | 3663.7 | 2920.0 |
| 65°   | 578.8  | 594.4  | 776.6  | 1203.6 | 1717.3 | 2014.9 | 2055.7 | 2148.6 | 2375.9 | 2119.9 | 1573.2 |
| 67.5° | 387.0  | 397.4  | 490.3  | 734.1  | 1011.8 | 1030.9 | 1024.8 | 1044.8 | 1094.2 | 903.3  | 710.7  |
| 70°   | 296.8  | 305.5  | 367.9  | 538.0  | 727.2  | 622.2  | 589.2  | 534.5  | 580.5  | 591.8  | 576.2  |
| 72.5° | 215.2  | 222.1  | 269.0  | 367.1  | 455.6  | 397.4  | 392.2  | 420.0  | 482.5  | 499.8  | 490.3  |
| 75°   | 138.8  | 142.3  | 170.9  | 201.3  | 235.2  | 255.1  | 265.5  | 315.9  | 379.2  | 392.2  | 380.9  |
| 77.5° | 92.9   | 95.5   | 111.9  | 129.3  | 133.6  | 134.5  | 138.0  | 160.5  | 203.9  | 228.2  | 225.6  |
| 80°   | 48.6   | 48.6   | 54.7   | 54.7   | 62.5   | 74.6   | 78.1   | 92.9   | 112.8  | 125.0  | 125.8  |
| 82.5° | 19.1   | 20.0   | 23.4   | 26.0   | 31.2   | 38.2   | 40.8   | 48.6   | 59.0   | 67.7   | 75.5   |
| 85°   | 7.8    | 8.7    | 9.5    | 11.3   | 13.9   | 17.4   | 18.2   | 20.8   | 27.8   | 34.7   | 39.0   |
| 87.5° | 0.0    | 0.0    | 0.9    | 0.9    | 1.7    | 2.6    | 2.6    | 3.5    | 4.3    | 7.8    | 10.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P636627

CATALOG NUMBER: GWS-SA4B-727-U-T3-W-GRSWH

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 | 1916.0 |
| 2.5°  | 1922.1 | 1910.8 | 1922.1 | 1925.6 | 1935.1 | 1938.6 | 1932.5 | 1931.6 | 1931.6 | 1923.0 | 1920.3 |
| 5°    | 1935.1 | 1924.7 | 1936.0 | 1941.2 | 1955.1 | 1963.7 | 1965.5 | 1972.4 | 1976.8 | 1973.3 | 1972.4 |
| 7.5°  | 1967.2 | 1954.2 | 1966.3 | 1974.1 | 1992.4 | 2006.3 | 2012.3 | 2028.0 | 2039.2 | 2037.5 | 2036.6 |
| 10°   | 2023.6 | 2006.3 | 2020.1 | 2033.2 | 2053.1 | 2069.6 | 2070.5 | 2079.1 | 2090.4 | 2087.0 | 2085.2 |
| 12.5° | 2088.7 | 2072.2 | 2087.8 | 2100.8 | 2124.3 | 2131.2 | 2119.9 | 2116.5 | 2118.2 | 2113.9 | 2110.4 |
| 15°   | 2168.5 | 2145.1 | 2159.0 | 2173.7 | 2186.8 | 2178.9 | 2154.6 | 2145.1 | 2144.2 | 2138.2 | 2134.7 |
| 17.5° | 2248.4 | 2218.9 | 2229.3 | 2237.1 | 2231.0 | 2206.7 | 2176.3 | 2159.9 | 2152.0 | 2139.9 | 2136.4 |
| 20°   | 2327.3 | 2290.0 | 2288.3 | 2282.2 | 2254.4 | 2210.2 | 2169.4 | 2136.4 | 2116.5 | 2100.0 | 2093.9 |
| 22.5° | 2417.6 | 2365.5 | 2339.5 | 2311.7 | 2251.0 | 2178.9 | 2117.3 | 2070.5 | 2038.4 | 2017.5 | 2010.6 |
| 25°   | 2514.8 | 2441.0 | 2387.2 | 2331.7 | 2216.3 | 2112.1 | 2026.2 | 1962.0 | 1923.8 | 1901.3 | 1893.4 |
| 27.5° | 2611.1 | 2509.6 | 2428.9 | 2334.3 | 2146.8 | 2015.8 | 1900.4 | 1813.6 | 1775.4 | 1757.2 | 1751.1 |
| 30°   | 2741.2 | 2600.7 | 2478.3 | 2300.4 | 2055.7 | 1882.2 | 1738.1 | 1650.5 | 1625.3 | 1612.3 | 1607.1 |
| 32.5° | 2891.4 | 2716.1 | 2544.3 | 2229.3 | 1939.4 | 1726.0 | 1574.1 | 1513.4 | 1496.0 | 1470.9 | 1470.0 |
| 35°   | 3089.2 | 2881.0 | 2606.7 | 2124.3 | 1792.8 | 1558.5 | 1448.3 | 1404.9 | 1373.7 | 1333.7 | 1330.3 |
| 37.5° | 3320.0 | 3086.6 | 2640.6 | 1990.6 | 1621.8 | 1420.5 | 1354.6 | 1306.0 | 1255.6 | 1202.7 | 1195.8 |
| 40°   | 3558.7 | 3327.0 | 2643.2 | 1832.7 | 1454.4 | 1329.4 | 1273.9 | 1210.5 | 1148.0 | 1089.0 | 1081.2 |
| 42.5° | 3809.5 | 3550.9 | 2597.2 | 1650.5 | 1317.3 | 1250.4 | 1194.0 | 1114.2 | 1043.9 | 1004.0 | 999.7  |
| 45°   | 4033.3 | 3731.4 | 2493.1 | 1458.7 | 1215.7 | 1184.5 | 1112.5 | 1026.6 | 989.2  | 960.6  | 954.5  |
| 47.5° | 4209.5 | 3851.1 | 2352.5 | 1286.9 | 1133.3 | 1116.8 | 1023.1 | 978.8  | 950.2  | 924.2  | 918.1  |
| 50°   | 4296.3 | 3878.0 | 2169.4 | 1147.2 | 1056.9 | 1037.0 | 972.8  | 938.9  | 919.8  | 899.0  | 893.8  |
| 52.5° | 4403.9 | 3908.4 | 2011.5 | 1030.0 | 982.3  | 955.4  | 931.1  | 904.2  | 890.3  | 877.3  | 873.0  |
| 55°   | 4651.2 | 4022.9 | 1928.2 | 936.3  | 911.1  | 899.0  | 895.5  | 873.0  | 868.6  | 859.9  | 852.1  |
| 57.5° | 4751.8 | 3949.2 | 1731.2 | 859.9  | 854.7  | 856.5  | 865.2  | 844.3  | 840.0  | 829.6  | 824.4  |
| 60°   | 3821.6 | 2985.1 | 1172.3 | 794.0  | 807.9  | 819.2  | 827.8  | 807.0  | 800.9  | 799.2  | 792.3  |
| 62.5° | 2448.8 | 1836.2 | 818.3  | 732.4  | 753.2  | 767.1  | 772.3  | 752.3  | 748.0  | 761.9  | 762.8  |
| 65°   | 1274.7 | 1000.5 | 663.8  | 666.4  | 683.8  | 704.6  | 715.0  | 708.1  | 706.4  | 721.1  | 722.0  |
| 67.5° | 650.8  | 611.8  | 578.8  | 588.3  | 602.2  | 629.1  | 653.4  | 683.8  | 694.2  | 695.9  | 696.8  |
| 70°   | 554.5  | 537.1  | 520.7  | 526.7  | 541.5  | 556.2  | 579.7  | 594.4  | 577.1  | 572.7  | 571.0  |
| 72.5° | 472.1  | 459.0  | 451.2  | 458.2  | 466.0  | 463.4  | 456.4  | 463.4  | 466.0  | 466.9  | 467.7  |
| 75°   | 367.1  | 357.5  | 351.4  | 352.3  | 352.3  | 342.8  | 329.7  | 321.9  | 313.3  | 306.3  | 306.3  |
| 77.5° | 224.7  | 226.5  | 232.6  | 231.7  | 230.8  | 227.4  | 214.3  | 207.4  | 186.6  | 180.5  | 180.5  |
| 80°   | 128.4  | 131.0  | 137.1  | 138.8  | 138.8  | 134.5  | 121.5  | 113.7  | 104.1  | 99.8   | 98.9   |
| 82.5° | 78.1   | 81.6   | 85.0   | 86.8   | 87.6   | 82.4   | 71.2   | 65.1   | 59.9   | 55.5   | 55.5   |
| 85°   | 40.8   | 42.5   | 46.0   | 46.9   | 44.3   | 39.0   | 33.0   | 30.4   | 25.2   | 24.3   | 24.3   |
| 87.5° | 11.3   | 12.1   | 13.9   | 11.3   | 10.4   | 7.8    | 4.3    | 3.5    | 1.7    | 0.9    | 0.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3 S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_g = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)