

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629672

Luminaire Tested: GWS-SA1C-727-U-SL2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1C-727-U-SL2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (16) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3423.7 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629672
 CATALOG NUMBER: GWS-SA1C-727-U-SL2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10.9 fc
 Type II - Short - N/A

REPORT NUMBER: P629672
CATALOG NUMBER: GWS-SA1C-727-U-SL2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P629672

CATALOG NUMBER: GWS-SA1C-727-U-SL2-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1070.5 | 0.0 | 1070.5 |
| | % Fixture | 31.3 | 0.0 | 31.3 |
| Street Side | Lumens | 2353.2 | 0.0 | 2353.2 |
| | % Fixture | 68.7 | 0.0 | 68.7 |
| Total | Lumens | 3423.7 | 0.0 | 3423.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 98.9 | 2.9 |
| 10°-20° | 259.4 | 7.6 |
| 20°-30° | 382.2 | 11.2 |
| 30°-40° | 534.9 | 15.6 |
| 40°-50° | 703.2 | 20.5 |
| 50°-60° | 824.5 | 24.1 |
| 60°-70° | 485.7 | 14.2 |
| 70°-80° | 120.8 | 3.5 |
| 80°-90° | 14.2 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 3423.7 | 100.0 |
| 0°-180° | 3423.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P629672


CATALOG NUMBER: GWS-SA1C-727-U-SL2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 416.3 | 12.2 | | | |
| FM (30°-60°) | 1531.8 | 44.7 | | | |
| FH (60°-80°) | 400.4 | 11.7 | | | G0/660 |
| FVH (80°-90°) | 4.7 | 0.1 | | | G0/10 |
| BL (0°-30°) | 324.1 | 9.5 | B1/500 | | |
| BM (30°-60°) | 530.8 | 15.5 | B1/1000 | | |
| BH (60°-80°) | 206.1 | 6.0 | B1/500 | | G1/500 |
| BVH (80°-90°) | 9.4 | 0.3 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type II Short





REPORT NUMBER: P629672
 CATALOG NUMBER: GWS-SA1C-727-U-SL2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 53° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 |
| 2.5° | 1030.5 | 1033.3 | 1033.9 | 1042.9 | 1043.4 | 1056.4 | 1065.0 | 1063.3 | 1072.2 | 1083.2 | 1091.8 |
| 5° | 981.2 | 981.5 | 984.4 | 995.0 | 1000.8 | 1017.8 | 1032.2 | 1032.2 | 1049.5 | 1072.0 | 1091.3 |
| 7.5° | 940.6 | 940.3 | 942.9 | 954.7 | 964.2 | 984.6 | 1004.2 | 1006.5 | 1030.7 | 1063.6 | 1095.0 |
| 10° | 902.8 | 904.8 | 907.7 | 922.1 | 934.2 | 959.6 | 982.9 | 986.7 | 1017.2 | 1057.8 | 1100.2 |
| 12.5° | 878.6 | 878.9 | 883.2 | 899.3 | 914.9 | 942.0 | 966.5 | 971.1 | 1006.3 | 1052.4 | 1103.9 |
| 15° | 863.0 | 863.3 | 867.9 | 885.8 | 904.0 | 931.3 | 956.4 | 961.6 | 999.9 | 1051.5 | 1111.1 |
| 17.5° | 856.1 | 855.8 | 860.2 | 878.0 | 897.9 | 926.4 | 953.2 | 959.6 | 1002.8 | 1058.1 | 1123.8 |
| 20° | 856.1 | 856.4 | 858.7 | 874.9 | 895.0 | 925.3 | 956.4 | 964.2 | 1014.0 | 1073.1 | 1143.4 |
| 22.5° | 868.2 | 869.4 | 870.5 | 881.5 | 897.3 | 927.0 | 964.8 | 975.1 | 1038.2 | 1098.2 | 1169.1 |
| 25° | 891.9 | 892.1 | 893.3 | 902.2 | 909.4 | 931.9 | 978.6 | 994.2 | 1076.0 | 1134.8 | 1201.3 |
| 27.5° | 923.6 | 927.6 | 928.7 | 934.5 | 934.5 | 944.0 | 1000.2 | 1022.7 | 1127.0 | 1187.5 | 1242.5 |
| 30° | 967.9 | 969.4 | 971.4 | 977.7 | 970.8 | 966.8 | 1031.9 | 1060.7 | 1186.1 | 1251.2 | 1292.1 |
| 32.5° | 1006.8 | 1010.0 | 1021.0 | 1031.3 | 1018.9 | 1006.3 | 1078.6 | 1112.6 | 1242.8 | 1317.5 | 1344.8 |
| 35° | 1040.0 | 1047.8 | 1068.8 | 1091.8 | 1083.2 | 1070.5 | 1140.5 | 1176.0 | 1289.5 | 1365.0 | 1391.5 |
| 37.5° | 1080.0 | 1086.1 | 1114.9 | 1152.4 | 1160.1 | 1154.1 | 1216.0 | 1241.4 | 1320.6 | 1377.1 | 1416.9 |
| 40° | 1120.7 | 1129.9 | 1167.0 | 1218.9 | 1248.6 | 1252.9 | 1285.8 | 1302.8 | 1331.3 | 1353.5 | 1412.0 |
| 42.5° | 1162.2 | 1178.0 | 1229.0 | 1289.5 | 1342.3 | 1352.0 | 1344.6 | 1351.8 | 1327.8 | 1320.9 | 1389.2 |
| 45° | 1212.9 | 1231.6 | 1289.2 | 1366.5 | 1435.9 | 1451.2 | 1402.2 | 1395.6 | 1327.3 | 1308.5 | 1375.1 |
| 47.5° | 1272.8 | 1291.5 | 1346.6 | 1436.5 | 1525.2 | 1536.5 | 1461.3 | 1449.2 | 1347.4 | 1327.6 | 1394.1 |
| 50° | 1325.8 | 1338.8 | 1388.1 | 1488.6 | 1608.5 | 1615.1 | 1526.4 | 1511.7 | 1397.6 | 1380.3 | 1453.5 |
| 52.5° | 1271.9 | 1270.5 | 1322.4 | 1446.3 | 1651.7 | 1731.6 | 1626.7 | 1612.5 | 1494.4 | 1467.9 | 1545.4 |
| 55° | 1079.2 | 1062.7 | 1109.1 | 1231.0 | 1531.0 | 1835.0 | 1806.5 | 1778.2 | 1623.5 | 1556.1 | 1631.6 |
| 57.5° | 789.0 | 784.4 | 795.6 | 910.0 | 1226.4 | 1674.8 | 1916.6 | 1914.0 | 1735.0 | 1636.8 | 1717.4 |
| 60° | 617.0 | 610.0 | 580.1 | 583.2 | 836.0 | 1308.2 | 1663.3 | 1739.6 | 1804.2 | 1685.2 | 1777.4 |
| 62.5° | 547.8 | 542.6 | 527.0 | 484.1 | 497.9 | 877.2 | 1219.2 | 1289.2 | 1576.5 | 1488.3 | 1526.7 |
| 65° | 453.6 | 452.1 | 465.1 | 463.4 | 417.3 | 484.4 | 688.1 | 758.7 | 991.3 | 1003.7 | 991.3 |
| 67.5° | 329.7 | 327.1 | 359.9 | 424.7 | 401.7 | 365.7 | 383.5 | 408.0 | 508.3 | 456.4 | 410.9 |
| 70° | 214.4 | 210.6 | 229.7 | 306.9 | 359.6 | 318.7 | 276.3 | 272.3 | 279.5 | 173.8 | 187.9 |
| 72.5° | 143.8 | 139.5 | 139.2 | 168.9 | 217.3 | 214.7 | 214.1 | 212.1 | 189.3 | 137.2 | 152.1 |
| 75° | 80.1 | 76.7 | 75.8 | 72.9 | 77.8 | 79.2 | 84.4 | 87.3 | 94.5 | 104.0 | 115.3 |
| 77.5° | 13.5 | 13.3 | 16.7 | 21.3 | 29.4 | 37.7 | 46.7 | 49.3 | 60.8 | 72.0 | 79.2 |
| 80° | 7.5 | 7.8 | 10.1 | 12.4 | 16.4 | 22.5 | 28.8 | 30.5 | 37.5 | 43.5 | 49.3 |
| 82.5° | 4.0 | 4.0 | 5.2 | 6.6 | 8.9 | 11.8 | 15.6 | 17.0 | 21.6 | 25.4 | 29.4 |
| 85° | 1.4 | 1.4 | 2.0 | 2.6 | 3.7 | 4.9 | 6.1 | 6.9 | 9.5 | 13.0 | 14.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.6 | 1.2 | 1.2 | 1.4 | 2.6 | 3.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629672

CATALOG NUMBER: GWS-SA1C-727-U-SL2-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 | 1093.3 |
| 2.5° | 1099.0 | 1091.3 | 1101.9 | 1106.8 | 1108.6 | 1109.7 | 1102.2 | 1097.0 | 1095.3 | 1089.8 | 1086.7 |
| 5° | 1103.1 | 1097.9 | 1108.0 | 1108.0 | 1100.8 | 1093.3 | 1078.0 | 1067.3 | 1059.9 | 1050.9 | 1049.5 |
| 7.5° | 1110.0 | 1106.2 | 1111.7 | 1100.5 | 1082.3 | 1062.2 | 1035.6 | 1014.9 | 998.2 | 987.2 | 987.5 |
| 10° | 1119.2 | 1114.6 | 1110.3 | 1085.2 | 1052.1 | 1014.9 | 974.3 | 944.0 | 916.3 | 903.7 | 896.8 |
| 12.5° | 1125.3 | 1118.6 | 1100.5 | 1059.0 | 1010.3 | 960.4 | 903.1 | 858.1 | 818.1 | 799.9 | 798.5 |
| 15° | 1132.8 | 1120.7 | 1084.3 | 1025.0 | 957.3 | 889.3 | 815.5 | 753.0 | 698.8 | 670.5 | 669.1 |
| 17.5° | 1142.6 | 1122.7 | 1065.0 | 986.1 | 901.4 | 801.1 | 708.3 | 629.6 | 572.0 | 550.1 | 553.8 |
| 20° | 1156.4 | 1125.0 | 1043.1 | 942.9 | 831.9 | 700.8 | 585.3 | 512.9 | 490.7 | 489.3 | 486.4 |
| 22.5° | 1171.9 | 1126.4 | 1018.9 | 894.4 | 747.8 | 593.9 | 483.5 | 452.7 | 452.4 | 459.6 | 461.3 |
| 25° | 1189.5 | 1127.6 | 991.6 | 838.0 | 656.7 | 487.3 | 427.6 | 418.4 | 425.6 | 439.2 | 440.9 |
| 27.5° | 1212.0 | 1129.9 | 958.4 | 776.0 | 559.9 | 421.0 | 396.8 | 394.5 | 403.1 | 415.8 | 415.2 |
| 30° | 1245.1 | 1138.2 | 923.3 | 704.8 | 460.5 | 389.6 | 378.1 | 378.4 | 381.8 | 387.9 | 388.7 |
| 32.5° | 1278.9 | 1151.2 | 889.0 | 624.7 | 403.4 | 371.7 | 366.5 | 366.0 | 366.0 | 368.6 | 369.1 |
| 35° | 1310.8 | 1165.9 | 851.8 | 541.2 | 375.8 | 361.4 | 357.9 | 356.2 | 355.3 | 354.7 | 353.9 |
| 37.5° | 1328.7 | 1173.1 | 815.5 | 458.8 | 361.1 | 354.4 | 351.0 | 348.7 | 345.5 | 343.2 | 342.6 |
| 40° | 1320.9 | 1164.7 | 773.4 | 397.1 | 352.1 | 347.8 | 343.8 | 340.6 | 336.3 | 334.3 | 333.1 |
| 42.5° | 1295.0 | 1138.8 | 727.6 | 368.0 | 344.9 | 340.6 | 335.7 | 330.5 | 327.6 | 325.9 | 325.6 |
| 45° | 1267.6 | 1107.4 | 672.3 | 351.0 | 338.0 | 332.8 | 327.1 | 321.3 | 318.1 | 317.3 | 317.0 |
| 47.5° | 1266.8 | 1091.8 | 613.5 | 337.4 | 329.7 | 324.5 | 317.3 | 311.5 | 308.0 | 306.9 | 305.7 |
| 50° | 1304.8 | 1107.7 | 547.2 | 325.6 | 321.0 | 315.5 | 307.5 | 301.1 | 296.8 | 295.4 | 295.1 |
| 52.5° | 1383.7 | 1167.3 | 487.9 | 313.8 | 309.5 | 303.1 | 296.5 | 290.2 | 285.0 | 282.4 | 282.1 |
| 55° | 1469.0 | 1243.1 | 451.0 | 301.7 | 295.9 | 290.5 | 284.4 | 277.5 | 271.7 | 267.7 | 267.1 |
| 57.5° | 1557.2 | 1325.8 | 439.7 | 286.4 | 282.1 | 278.4 | 271.2 | 263.7 | 257.0 | 253.3 | 252.4 |
| 60° | 1629.8 | 1397.0 | 460.8 | 270.3 | 268.0 | 263.1 | 256.5 | 249.3 | 244.6 | 241.8 | 241.2 |
| 62.5° | 1364.4 | 1137.4 | 372.0 | 252.7 | 252.7 | 247.5 | 240.0 | 234.9 | 231.7 | 229.7 | 229.1 |
| 65° | 865.9 | 704.3 | 253.9 | 235.1 | 234.9 | 227.9 | 221.6 | 218.1 | 216.7 | 213.5 | 213.0 |
| 67.5° | 377.2 | 321.9 | 217.0 | 217.3 | 216.1 | 208.6 | 202.3 | 199.7 | 196.8 | 193.4 | 193.1 |
| 70° | 195.7 | 199.4 | 194.2 | 197.4 | 195.4 | 186.4 | 180.4 | 176.4 | 170.3 | 166.8 | 167.1 |
| 72.5° | 157.9 | 161.9 | 167.7 | 172.6 | 168.3 | 161.1 | 151.6 | 146.7 | 138.9 | 135.1 | 135.4 |
| 75° | 120.5 | 124.8 | 130.2 | 135.4 | 132.0 | 123.0 | 117.0 | 112.1 | 103.2 | 98.8 | 99.7 |
| 77.5° | 83.0 | 85.3 | 91.9 | 91.6 | 90.5 | 87.9 | 79.0 | 73.2 | 64.0 | 58.8 | 59.4 |
| 80° | 51.6 | 53.0 | 56.2 | 57.6 | 57.1 | 53.6 | 46.4 | 42.1 | 36.6 | 33.4 | 33.7 |
| 82.5° | 31.1 | 32.0 | 34.9 | 35.2 | 34.9 | 32.3 | 26.8 | 23.6 | 20.2 | 18.4 | 18.4 |
| 85° | 15.8 | 16.4 | 18.2 | 18.2 | 16.4 | 13.8 | 12.4 | 11.0 | 8.9 | 8.1 | 8.1 |
| 87.5° | 4.3 | 4.3 | 5.5 | 4.6 | 3.7 | 3.5 | 1.7 | 1.4 | 0.6 | 0.3 | 0.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)