

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634636

Luminaire Tested: GWS-SA3C-727-U-SLR-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P634636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3C-727-U-SLR-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS
Light Source: (48) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11045.8 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 93
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P634636
 CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.2 fc
 Type III - Short - N/A

REPORT NUMBER: P634636
CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P634636

CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2635.7 | 0.0 | 2635.7 |
| | % Fixture | 23.9 | 0.0 | 23.9 |
| Street Side | Lumens | 8410.1 | 0.0 | 8410.1 |
| | % Fixture | 76.1 | 0.0 | 76.1 |
| Total | Lumens | 11045.8 | 0.0 | 11045.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 143.2 | 1.3 |
| 10°-20° | 448.8 | 4.1 |
| 20°-30° | 697.1 | 6.3 |
| 30°-40° | 946.5 | 8.6 |
| 40°-50° | 1500.1 | 13.6 |
| 50°-60° | 2646.3 | 24.0 |
| 60°-70° | 2944.4 | 26.7 |
| 70°-80° | 1493.3 | 13.5 |
| 80°-90° | 226.1 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11045.8 | 100.0 |
| 0°-180° | 11045.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P634636


CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 721.2 | 6.5 | | | |
| FM (30°-60°) | 3750.5 | 34.0 | | | |
| FH (60°-80°) | 3766.7 | 34.1 | | | G2/5000 |
| FVH (80°-90°) | 171.6 | 1.6 | | | G2/225 |
| BL (0°-30°) | 567.9 | 5.1 | B2/1000 | | |
| BM (30°-60°) | 1342.4 | 12.2 | B2/2500 | | |
| BH (60°-80°) | 670.9 | 6.1 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 54.5 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P634636
 CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|--------|--------|---------|
| 0° | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 |
| 2.5° | 1575.6 | 1574.7 | 1590.6 | 1614.9 | 1637.4 | 1647.5 | 1664.2 | 1662.5 | 1649.1 | 1631.6 | 1625.7 |
| 5° | 1699.3 | 1702.7 | 1730.3 | 1783.8 | 1843.2 | 1868.3 | 1879.1 | 1874.9 | 1850.7 | 1819.8 | 1765.4 |
| 7.5° | 1811.4 | 1817.2 | 1859.9 | 1940.2 | 2013.8 | 2047.2 | 2074.0 | 2069.0 | 2033.8 | 1976.1 | 1895.9 |
| 10° | 1893.3 | 1900.0 | 1951.0 | 2045.5 | 2127.5 | 2156.8 | 2191.1 | 2192.7 | 2161.8 | 2084.0 | 2002.1 |
| 12.5° | 1975.3 | 1982.0 | 2029.7 | 2115.8 | 2169.3 | 2170.2 | 2190.2 | 2201.1 | 2202.8 | 2166.8 | 2084.9 |
| 15° | 2060.6 | 2066.5 | 2109.9 | 2158.4 | 2155.9 | 2109.1 | 2109.1 | 2130.0 | 2176.0 | 2201.9 | 2145.1 |
| 17.5° | 2133.4 | 2140.9 | 2174.3 | 2158.4 | 2084.0 | 1999.6 | 1989.5 | 2016.3 | 2096.6 | 2196.1 | 2190.2 |
| 20° | 2193.6 | 2199.4 | 2217.8 | 2112.4 | 1977.0 | 1866.6 | 1847.3 | 1878.3 | 1987.0 | 2160.1 | 2224.5 |
| 22.5° | 2251.3 | 2254.6 | 2244.6 | 2052.2 | 1861.6 | 1735.3 | 1711.9 | 1744.5 | 1861.6 | 2096.6 | 2253.8 |
| 25° | 2319.8 | 2316.5 | 2268.8 | 1989.5 | 1756.2 | 1631.6 | 1607.3 | 1644.1 | 1766.2 | 2012.1 | 2285.6 |
| 27.5° | 2399.3 | 2386.8 | 2289.7 | 1921.8 | 1675.1 | 1554.6 | 1537.9 | 1577.2 | 1691.0 | 1934.3 | 2310.6 |
| 30° | 2467.0 | 2442.8 | 2293.1 | 1861.6 | 1633.3 | 1522.0 | 1512.0 | 1548.8 | 1654.2 | 1881.6 | 2342.4 |
| 32.5° | 2542.3 | 2508.8 | 2312.3 | 1845.7 | 1656.7 | 1600.6 | 1614.0 | 1616.5 | 1664.2 | 1866.6 | 2390.1 |
| 35° | 2650.2 | 2606.7 | 2365.0 | 1891.7 | 1897.5 | 1992.0 | 2040.5 | 1975.3 | 1815.6 | 1900.0 | 2480.4 |
| 37.5° | 2813.3 | 2758.1 | 2472.1 | 2090.7 | 2395.1 | 2606.7 | 2723.8 | 2574.9 | 2275.5 | 2026.3 | 2616.7 |
| 40° | 3011.5 | 2941.2 | 2609.2 | 2458.7 | 2860.1 | 3198.8 | 3407.0 | 3188.7 | 2748.9 | 2341.6 | 2808.2 |
| 42.5° | 3288.3 | 3214.7 | 2875.1 | 2819.9 | 3290.8 | 3795.0 | 4066.8 | 3741.5 | 3166.2 | 2748.9 | 3115.2 |
| 45° | 3770.8 | 3699.7 | 3362.7 | 3182.1 | 3795.0 | 4529.3 | 4910.7 | 4458.2 | 3590.2 | 3157.8 | 3688.8 |
| 47.5° | 4662.3 | 4578.6 | 4086.9 | 3583.5 | 4370.4 | 5482.7 | 6016.2 | 5357.2 | 4030.9 | 3626.1 | 4652.2 |
| 50° | 5732.7 | 5652.4 | 4996.0 | 4058.5 | 5006.0 | 6502.1 | 7243.9 | 6413.5 | 4538.5 | 4195.6 | 5803.8 |
| 52.5° | 7020.6 | 7005.5 | 6293.0 | 4658.9 | 5667.5 | 7589.3 | 8606.2 | 7583.4 | 5094.6 | 4962.5 | 7108.4 |
| 55° | 8181.4 | 8328.5 | 7940.5 | 5574.7 | 6522.2 | 8954.9 | 10007.0 | 8859.6 | 5849.0 | 6230.3 | 8636.3 |
| 57.5° | 8806.9 | 9202.5 | 9798.7 | 7442.9 | 7764.9 | 10587.3 | 11735.6 | 10417.6 | 7145.2 | 8341.1 | 10053.0 |
| 60° | 8393.8 | 8842.0 | 9922.5 | 8849.5 | 8997.6 | 11895.3 | 13162.3 | 11727.2 | 8418.0 | 9806.2 | 9972.7 |
| 62.5° | 7706.3 | 8108.6 | 9069.5 | 8028.3 | 9188.2 | 12183.0 | 13195.7 | 11955.5 | 8924.0 | 9062.8 | 9008.4 |
| 65° | 6891.0 | 7296.6 | 8314.3 | 7008.0 | 8581.9 | 11499.7 | 12222.3 | 11284.0 | 8014.9 | 8188.0 | 8208.1 |
| 67.5° | 5808.0 | 6182.6 | 7218.8 | 6231.1 | 7822.6 | 10497.0 | 10727.8 | 10327.3 | 7381.0 | 7657.0 | 7368.5 |
| 70° | 4339.5 | 4677.3 | 5592.2 | 5063.7 | 6594.1 | 9190.7 | 9004.3 | 9063.6 | 6669.4 | 6943.7 | 6155.0 |
| 72.5° | 2965.5 | 3219.7 | 4004.1 | 3979.0 | 5049.5 | 7357.6 | 7097.5 | 7660.3 | 5570.5 | 5934.3 | 4692.4 |
| 75° | 2074.0 | 2272.2 | 2894.4 | 3143.6 | 3816.8 | 5453.4 | 5054.5 | 5733.6 | 4350.3 | 4869.7 | 3423.7 |
| 77.5° | 1272.8 | 1404.1 | 1828.1 | 2329.0 | 2455.3 | 3732.3 | 3139.4 | 4314.4 | 3054.9 | 3551.7 | 2283.9 |
| 80° | 636.4 | 700.0 | 888.1 | 1464.3 | 1628.2 | 2199.4 | 1733.6 | 2504.7 | 2067.3 | 2199.4 | 1263.6 |
| 82.5° | 192.3 | 212.4 | 260.1 | 556.1 | 843.8 | 1266.1 | 1024.4 | 1455.1 | 1129.0 | 1031.1 | 497.6 |
| 85° | 51.0 | 57.7 | 71.9 | 164.7 | 296.0 | 454.1 | 346.2 | 705.0 | 541.1 | 380.5 | 187.3 |
| 87.5° | 4.2 | 4.2 | 3.3 | 3.3 | 1.7 | 0.0 | 0.0 | 50.2 | 101.2 | 57.7 | 32.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634636
 CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 |
| 2.5° | 1596.5 | 1593.1 | 1558.8 | 1533.7 | 1504.5 | 1476.0 | 1446.8 | 1420.8 | 1391.6 | 1362.3 | 1353.9 |
| 5° | 1725.3 | 1701.8 | 1629.1 | 1568.0 | 1507.8 | 1455.1 | 1409.1 | 1361.5 | 1323.0 | 1285.4 | 1271.1 |
| 7.5° | 1839.0 | 1798.0 | 1692.6 | 1599.8 | 1516.2 | 1451.0 | 1383.2 | 1313.8 | 1259.4 | 1205.9 | 1192.5 |
| 10° | 1941.8 | 1887.5 | 1754.5 | 1637.4 | 1544.6 | 1470.2 | 1390.7 | 1297.9 | 1219.3 | 1154.1 | 1136.5 |
| 12.5° | 2017.9 | 1958.6 | 1808.0 | 1673.4 | 1568.0 | 1484.4 | 1405.8 | 1323.8 | 1241.0 | 1156.6 | 1137.3 |
| 15° | 2078.2 | 2016.3 | 1852.4 | 1701.0 | 1568.9 | 1461.0 | 1384.9 | 1356.5 | 1330.5 | 1247.7 | 1212.6 |
| 17.5° | 2126.7 | 2061.4 | 1890.8 | 1717.7 | 1546.3 | 1389.9 | 1323.8 | 1365.6 | 1431.7 | 1379.9 | 1313.8 |
| 20° | 2171.0 | 2104.9 | 1920.1 | 1729.4 | 1496.1 | 1292.1 | 1255.3 | 1343.9 | 1443.4 | 1441.8 | 1382.4 |
| 22.5° | 2219.5 | 2155.1 | 1962.8 | 1736.1 | 1425.9 | 1192.5 | 1214.3 | 1312.1 | 1393.2 | 1417.5 | 1380.7 |
| 25° | 2281.4 | 2224.5 | 2022.1 | 1751.2 | 1346.4 | 1124.0 | 1184.2 | 1271.1 | 1338.9 | 1344.7 | 1323.0 |
| 27.5° | 2353.3 | 2310.6 | 2110.8 | 1786.3 | 1269.5 | 1088.8 | 1149.1 | 1213.4 | 1275.3 | 1277.8 | 1251.9 |
| 30° | 2431.9 | 2403.5 | 2192.7 | 1815.6 | 1211.8 | 1078.0 | 1103.9 | 1155.7 | 1195.0 | 1201.7 | 1179.2 |
| 32.5° | 2532.3 | 2507.2 | 2265.5 | 1796.3 | 1177.5 | 1075.5 | 1062.1 | 1088.8 | 1121.5 | 1121.5 | 1103.9 |
| 35° | 2670.3 | 2635.1 | 2342.4 | 1722.7 | 1135.7 | 1065.4 | 1017.8 | 1025.3 | 1039.5 | 1042.0 | 1032.0 |
| 37.5° | 2865.9 | 2808.2 | 2420.2 | 1577.2 | 1067.1 | 1029.5 | 966.7 | 957.5 | 962.6 | 969.3 | 966.7 |
| 40° | 3108.5 | 3014.0 | 2533.9 | 1402.4 | 985.1 | 960.1 | 914.1 | 896.5 | 892.3 | 905.7 | 910.7 |
| 42.5° | 3413.7 | 3269.0 | 2656.0 | 1239.4 | 910.7 | 880.6 | 852.2 | 837.1 | 830.4 | 853.0 | 866.4 |
| 45° | 3901.3 | 3662.9 | 2773.1 | 1078.0 | 868.9 | 812.9 | 793.6 | 782.8 | 786.1 | 812.9 | 829.6 |
| 47.5° | 4743.4 | 4264.2 | 2884.3 | 975.9 | 865.6 | 764.4 | 740.9 | 743.5 | 752.7 | 781.1 | 801.2 |
| 50° | 5808.8 | 5069.5 | 2958.8 | 933.3 | 875.6 | 735.1 | 704.1 | 717.5 | 731.7 | 759.3 | 782.8 |
| 52.5° | 6893.5 | 5819.7 | 2870.1 | 909.9 | 874.8 | 735.9 | 669.9 | 710.0 | 716.7 | 744.3 | 769.4 |
| 55° | 7639.4 | 5903.3 | 2479.6 | 873.9 | 861.4 | 769.4 | 643.1 | 706.7 | 710.8 | 735.9 | 758.5 |
| 57.5° | 7923.8 | 5617.3 | 1890.8 | 884.0 | 821.2 | 795.3 | 631.4 | 683.2 | 713.3 | 735.1 | 758.5 |
| 60° | 7580.1 | 5077.9 | 1149.1 | 909.9 | 756.8 | 793.6 | 638.9 | 640.6 | 692.4 | 729.2 | 752.7 |
| 62.5° | 6931.9 | 4385.5 | 807.0 | 836.3 | 710.0 | 749.3 | 656.5 | 590.4 | 655.6 | 700.0 | 720.9 |
| 65° | 6189.3 | 3570.9 | 615.5 | 720.0 | 687.4 | 680.7 | 662.3 | 546.1 | 605.5 | 649.0 | 667.4 |
| 67.5° | 5415.8 | 2775.6 | 500.1 | 536.9 | 621.4 | 615.5 | 605.5 | 506.8 | 546.1 | 577.0 | 597.9 |
| 70° | 4441.5 | 1941.8 | 422.3 | 403.1 | 532.7 | 551.9 | 529.4 | 457.4 | 470.0 | 501.8 | 518.5 |
| 72.5° | 3249.0 | 1210.1 | 347.1 | 332.8 | 428.2 | 482.5 | 470.8 | 403.1 | 408.9 | 439.0 | 452.4 |
| 75° | 2336.6 | 692.4 | 278.5 | 274.3 | 327.0 | 413.1 | 389.7 | 347.1 | 353.7 | 376.3 | 385.5 |
| 77.5° | 1485.2 | 385.5 | 214.9 | 220.8 | 234.2 | 308.6 | 332.8 | 296.9 | 296.9 | 310.3 | 317.8 |
| 80° | 795.3 | 220.8 | 157.2 | 159.7 | 163.9 | 235.8 | 262.6 | 230.0 | 230.0 | 220.8 | 230.0 |
| 82.5° | 324.5 | 127.1 | 107.9 | 100.4 | 109.6 | 161.4 | 184.0 | 146.3 | 153.0 | 138.0 | 141.3 |
| 85° | 107.0 | 63.6 | 53.5 | 52.7 | 51.8 | 71.1 | 88.6 | 72.8 | 87.0 | 55.2 | 57.7 |
| 87.5° | 14.2 | 11.7 | 6.7 | 5.0 | 5.9 | 2.5 | 5.0 | 5.9 | 5.9 | 4.2 | 4.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634636
 CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 |
| 2.5° | 1348.1 | 1341.4 | 1317.1 | 1323.0 | 1318.8 | 1312.1 | 1318.8 | 1306.3 | 1316.3 | 1319.7 | 1340.6 |
| 5° | 1260.3 | 1244.4 | 1221.0 | 1209.3 | 1206.8 | 1200.1 | 1200.9 | 1195.0 | 1196.7 | 1210.9 | 1234.4 |
| 7.5° | 1181.7 | 1166.6 | 1148.2 | 1139.9 | 1132.3 | 1124.8 | 1124.0 | 1123.1 | 1129.8 | 1142.4 | 1164.9 |
| 10° | 1124.8 | 1116.4 | 1108.9 | 1112.3 | 1108.9 | 1105.6 | 1099.7 | 1099.7 | 1110.6 | 1133.2 | 1160.8 |
| 12.5° | 1124.8 | 1123.1 | 1124.8 | 1134.8 | 1134.0 | 1134.8 | 1127.3 | 1131.5 | 1161.6 | 1200.1 | 1239.4 |
| 15° | 1185.0 | 1171.6 | 1171.6 | 1176.6 | 1175.0 | 1175.0 | 1175.0 | 1192.5 | 1261.1 | 1320.5 | 1362.3 |
| 17.5° | 1258.6 | 1219.3 | 1202.6 | 1200.1 | 1199.2 | 1199.2 | 1202.6 | 1240.2 | 1347.3 | 1410.0 | 1434.2 |
| 20° | 1309.6 | 1235.2 | 1207.6 | 1196.7 | 1197.6 | 1199.2 | 1209.3 | 1261.1 | 1379.0 | 1410.8 | 1405.0 |
| 22.5° | 1318.8 | 1222.6 | 1189.2 | 1173.3 | 1175.8 | 1177.5 | 1192.5 | 1247.7 | 1335.5 | 1340.6 | 1328.9 |
| 25° | 1276.2 | 1187.5 | 1151.6 | 1139.0 | 1142.4 | 1141.5 | 1154.9 | 1195.0 | 1257.8 | 1256.1 | 1249.4 |
| 27.5° | 1212.6 | 1131.5 | 1104.7 | 1096.4 | 1102.2 | 1095.5 | 1099.7 | 1130.7 | 1179.2 | 1177.5 | 1175.0 |
| 30° | 1147.4 | 1077.1 | 1052.9 | 1048.7 | 1056.2 | 1046.2 | 1047.0 | 1073.0 | 1106.4 | 1104.7 | 1103.9 |
| 32.5° | 1082.1 | 1022.8 | 1001.0 | 1001.0 | 1008.6 | 997.7 | 999.4 | 1021.9 | 1044.5 | 1037.8 | 1037.8 |
| 35° | 1020.3 | 978.5 | 960.9 | 957.5 | 963.4 | 955.9 | 959.2 | 980.1 | 988.5 | 979.3 | 973.4 |
| 37.5° | 965.9 | 947.5 | 929.9 | 918.2 | 919.1 | 919.9 | 929.9 | 945.8 | 940.8 | 927.4 | 919.9 |
| 40° | 915.7 | 915.7 | 899.0 | 877.3 | 874.8 | 880.6 | 897.3 | 914.9 | 900.7 | 885.6 | 876.4 |
| 42.5° | 879.8 | 887.3 | 871.4 | 849.7 | 844.6 | 854.7 | 873.1 | 885.6 | 868.9 | 852.2 | 839.6 |
| 45° | 846.3 | 864.7 | 853.8 | 829.6 | 822.9 | 834.6 | 858.0 | 863.0 | 840.5 | 824.6 | 815.4 |
| 47.5° | 822.9 | 848.0 | 840.5 | 817.0 | 807.0 | 823.7 | 848.0 | 847.2 | 818.7 | 802.0 | 794.5 |
| 50° | 806.2 | 838.0 | 837.1 | 817.0 | 806.2 | 827.1 | 848.8 | 838.0 | 807.0 | 789.5 | 781.9 |
| 52.5° | 792.8 | 837.1 | 843.0 | 831.3 | 823.7 | 842.1 | 855.5 | 834.6 | 798.6 | 780.3 | 774.4 |
| 55° | 786.9 | 840.5 | 844.6 | 833.8 | 827.1 | 843.8 | 855.5 | 841.3 | 798.6 | 781.9 | 776.9 |
| 57.5° | 788.6 | 836.3 | 837.1 | 822.1 | 810.4 | 831.3 | 849.7 | 845.5 | 807.8 | 788.6 | 782.8 |
| 60° | 778.6 | 813.7 | 815.4 | 792.0 | 778.6 | 803.7 | 836.3 | 833.8 | 803.7 | 783.6 | 772.7 |
| 62.5° | 745.1 | 776.1 | 776.9 | 755.2 | 735.9 | 771.9 | 807.8 | 807.0 | 779.4 | 759.3 | 746.8 |
| 65° | 689.1 | 721.7 | 730.1 | 709.2 | 694.1 | 732.6 | 770.2 | 768.5 | 740.9 | 722.5 | 710.0 |
| 67.5° | 619.7 | 654.8 | 670.7 | 656.5 | 650.6 | 685.8 | 720.9 | 720.0 | 697.5 | 679.9 | 669.0 |
| 70° | 535.2 | 564.5 | 591.3 | 591.3 | 587.1 | 627.2 | 664.8 | 661.5 | 640.6 | 627.2 | 618.8 |
| 72.5° | 465.0 | 487.6 | 495.9 | 504.3 | 516.8 | 558.6 | 590.4 | 592.9 | 577.9 | 571.2 | 577.9 |
| 75° | 395.6 | 409.8 | 417.3 | 410.6 | 432.4 | 475.8 | 517.7 | 521.8 | 506.0 | 495.1 | 497.6 |
| 77.5° | 325.3 | 341.2 | 348.7 | 333.7 | 332.0 | 387.2 | 438.2 | 447.4 | 434.0 | 417.3 | 422.3 |
| 80° | 235.0 | 255.9 | 268.4 | 258.4 | 255.1 | 279.3 | 349.6 | 359.6 | 347.1 | 333.7 | 341.2 |
| 82.5° | 143.8 | 155.5 | 158.9 | 168.9 | 189.8 | 199.9 | 225.0 | 258.4 | 249.2 | 237.5 | 258.4 |
| 85° | 56.9 | 67.7 | 75.3 | 85.3 | 99.5 | 117.9 | 138.8 | 165.6 | 150.5 | 145.5 | 171.4 |
| 87.5° | 3.3 | 0.8 | 0.0 | 1.7 | 14.2 | 27.6 | 59.4 | 82.0 | 68.6 | 73.6 | 88.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634636
 CATALOG NUMBER: GWS-SA3C-727-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 | 1466.0 |
| 2.5° | 1357.3 | 1379.0 | 1408.3 | 1432.6 | 1463.5 | 1492.8 | 1522.9 | 1553.0 | 1568.9 | 1575.6 |
| 5° | 1261.1 | 1301.3 | 1348.1 | 1399.9 | 1460.1 | 1523.7 | 1588.1 | 1654.2 | 1696.0 | 1699.3 |
| 7.5° | 1203.4 | 1261.1 | 1325.5 | 1390.7 | 1465.2 | 1553.0 | 1655.0 | 1757.0 | 1799.7 | 1811.4 |
| 10° | 1221.8 | 1286.2 | 1337.2 | 1398.3 | 1480.2 | 1589.8 | 1710.2 | 1829.8 | 1879.1 | 1893.3 |
| 12.5° | 1295.4 | 1307.9 | 1323.8 | 1379.9 | 1480.2 | 1621.6 | 1767.1 | 1909.2 | 1961.9 | 1975.3 |
| 15° | 1356.5 | 1296.2 | 1267.8 | 1327.2 | 1460.1 | 1649.1 | 1827.3 | 1984.5 | 2048.1 | 2060.6 |
| 17.5° | 1361.5 | 1257.8 | 1195.9 | 1249.4 | 1425.0 | 1668.4 | 1885.0 | 2068.1 | 2121.6 | 2133.4 |
| 20° | 1310.5 | 1216.8 | 1136.5 | 1169.1 | 1377.4 | 1676.7 | 1926.8 | 2129.2 | 2181.9 | 2193.6 |
| 22.5° | 1252.8 | 1183.3 | 1096.4 | 1094.7 | 1319.7 | 1685.9 | 1977.0 | 2186.9 | 2243.7 | 2251.3 |
| 25° | 1198.4 | 1137.3 | 1063.8 | 1040.3 | 1252.8 | 1703.5 | 2044.7 | 2273.9 | 2317.3 | 2319.8 |
| 27.5° | 1134.8 | 1088.0 | 1037.8 | 1015.2 | 1194.2 | 1737.0 | 2145.1 | 2377.6 | 2403.5 | 2399.3 |
| 30° | 1077.1 | 1042.0 | 1019.4 | 1012.7 | 1157.4 | 1762.0 | 2240.4 | 2479.6 | 2481.3 | 2467.0 |
| 32.5° | 1016.1 | 1002.7 | 1002.7 | 1024.4 | 1127.3 | 1756.2 | 2318.2 | 2579.1 | 2563.2 | 2542.3 |
| 35° | 961.7 | 964.2 | 981.8 | 1032.8 | 1077.1 | 1697.7 | 2392.6 | 2703.7 | 2680.3 | 2650.2 |
| 37.5° | 909.9 | 929.1 | 954.2 | 1003.5 | 1011.1 | 1610.7 | 2479.6 | 2880.2 | 2850.9 | 2813.3 |
| 40° | 865.6 | 894.8 | 924.1 | 948.3 | 940.8 | 1486.9 | 2600.8 | 3087.6 | 3054.9 | 3011.5 |
| 42.5° | 830.4 | 858.9 | 891.5 | 894.0 | 896.5 | 1358.1 | 2729.6 | 3341.8 | 3335.9 | 3288.3 |
| 45° | 807.8 | 826.2 | 857.2 | 853.0 | 894.0 | 1216.0 | 2848.4 | 3729.8 | 3806.8 | 3770.8 |
| 47.5° | 792.8 | 807.0 | 810.4 | 827.9 | 915.7 | 1088.8 | 3001.4 | 4489.2 | 4703.3 | 4662.3 |
| 50° | 784.4 | 798.6 | 761.0 | 829.6 | 919.1 | 1006.9 | 3213.0 | 5442.5 | 5787.1 | 5732.7 |
| 52.5° | 783.6 | 780.3 | 723.4 | 847.2 | 900.7 | 956.7 | 3323.4 | 6138.3 | 6902.7 | 7020.6 |
| 55° | 785.3 | 743.5 | 704.1 | 852.2 | 863.9 | 938.3 | 2953.7 | 6472.8 | 7932.1 | 8181.4 |
| 57.5° | 770.2 | 703.3 | 715.0 | 832.1 | 794.5 | 987.6 | 2183.5 | 6353.2 | 8343.6 | 8806.9 |
| 60° | 741.8 | 664.8 | 735.1 | 777.7 | 723.4 | 903.2 | 1503.6 | 5819.7 | 7917.1 | 8393.8 |
| 62.5° | 700.8 | 638.1 | 732.6 | 707.5 | 697.5 | 739.3 | 1033.6 | 5072.9 | 7240.5 | 7706.3 |
| 65° | 654.8 | 616.3 | 693.3 | 639.8 | 645.6 | 568.7 | 730.9 | 4229.9 | 6432.7 | 6891.0 |
| 67.5° | 605.5 | 603.0 | 635.6 | 569.5 | 545.3 | 450.8 | 532.7 | 3390.3 | 5394.9 | 5808.0 |
| 70° | 549.4 | 567.8 | 577.9 | 506.0 | 442.4 | 353.7 | 395.6 | 2370.9 | 3979.9 | 4339.5 |
| 72.5° | 493.4 | 495.1 | 509.3 | 439.9 | 331.2 | 283.5 | 296.9 | 1435.9 | 2703.7 | 2965.5 |
| 75° | 436.5 | 420.7 | 434.0 | 357.9 | 246.7 | 232.5 | 229.1 | 887.3 | 1867.4 | 2074.0 |
| 77.5° | 375.5 | 357.9 | 340.4 | 269.3 | 198.2 | 179.8 | 175.6 | 497.6 | 1145.7 | 1272.8 |
| 80° | 305.2 | 281.8 | 254.2 | 197.4 | 144.7 | 128.8 | 128.0 | 242.5 | 571.2 | 636.4 |
| 82.5° | 237.5 | 193.2 | 185.7 | 122.9 | 89.5 | 78.6 | 83.6 | 92.8 | 172.3 | 192.3 |
| 85° | 166.4 | 140.5 | 98.7 | 49.3 | 40.1 | 32.6 | 31.8 | 27.6 | 46.0 | 51.0 |
| 87.5° | 92.8 | 61.0 | 31.8 | 5.9 | 6.7 | 7.5 | 5.9 | 4.2 | 4.2 | 4.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2
 Rf: 69.9
 Rg: 98.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |



Test Conditions


Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4



TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_g = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)