

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637095

Luminaire Tested: GWS-SA4C-727-U-SL2-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P637095  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-29)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4C-727-U-SL2-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (64) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13826.7 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B3 - U0 - G2  
  
Input Watts (W): 128.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P637095  
 CATALOG NUMBER: GWS-SA4C-727-U-SL2-W-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 11 fc  
 Type II - Short - N/A

REPORT NUMBER: P637095  
CATALOG NUMBER: GWS-SA4C-727-U-SL2-W-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P637095

CATALOG NUMBER: GWS-SA4C-727-U-SL2-W-GRSWH


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 4323.1   | 0.0    | 4323.1  |
|                    | % Fixture | 31.3     | 0.0    | 31.3    |
| <b>Street Side</b> | Lumens    | 9503.6   | 0.0    | 9503.6  |
|                    | % Fixture | 68.7     | 0.0    | 68.7    |
| <b>Total</b>       | Lumens    | 13826.7  | 0.0    | 13826.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 399.3   | 2.9       |
| 10°-20°   | 1047.5  | 7.6       |
| 20°-30°   | 1543.3  | 11.2      |
| 30°-40°   | 2160.3  | 15.6      |
| 40°-50°   | 2839.8  | 20.5      |
| 50°-60°   | 3329.7  | 24.1      |
| 60°-70°   | 1961.6  | 14.2      |
| 70°-80°   | 488.0   | 3.5       |
| 80°-90°   | 57.2    | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 13826.7 | 100.0     |
| 0°-180°   | 13826.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P637095


CATALOG NUMBER: GWS-SA4C-727-U-SL2-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1681.1 | 12.2      |                         |      |         |
| FM (30°-60°)   | 6186.2 | 44.7      |                         |      |         |
| FH (60°-80°)   | 1617.2 | 11.7      |                         |      | G1/1800 |
| FVH (80°-90°)  | 19.2   | 0.1       |                         |      | G1/100  |
| BL (0°-30°)    | 1309.1 | 9.5       | B3/2500                 |      |         |
| BM (30°-60°)   | 2143.6 | 15.5      | B2/2500                 |      |         |
| BH (60°-80°)   | 832.3  | 6.0       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 38.1   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type II Short





REPORT NUMBER: P637095

CATALOG NUMBER: GWS-SA4C-727-U-SL2-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 53°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 |
| 2.5°  | 4161.5 | 4173.2 | 4175.5 | 4211.6 | 4213.9 | 4266.3 | 4301.2 | 4294.2 | 4330.3 | 4374.5 | 4409.4 |
| 5°    | 3962.5 | 3963.7 | 3975.3 | 4018.4 | 4041.7 | 4110.3 | 4168.5 | 4168.5 | 4238.4 | 4329.1 | 4407.1 |
| 7.5°  | 3798.5 | 3797.3 | 3807.8 | 3855.5 | 3893.9 | 3976.5 | 4055.6 | 4065.0 | 4162.7 | 4295.4 | 4422.2 |
| 10°   | 3646.0 | 3654.2 | 3665.8 | 3724.0 | 3772.9 | 3875.3 | 3969.5 | 3984.7 | 4108.0 | 4272.1 | 4443.2 |
| 12.5° | 3548.3 | 3549.4 | 3566.9 | 3632.0 | 3694.9 | 3804.3 | 3903.2 | 3921.8 | 4063.8 | 4250.0 | 4458.3 |
| 15°   | 3485.4 | 3486.6 | 3505.2 | 3577.3 | 3650.7 | 3761.2 | 3862.5 | 3883.4 | 4038.2 | 4246.5 | 4487.4 |
| 17.5° | 3457.5 | 3456.3 | 3473.8 | 3545.9 | 3626.2 | 3741.4 | 3849.7 | 3875.3 | 4049.8 | 4273.3 | 4538.6 |
| 20°   | 3457.5 | 3458.6 | 3468.0 | 3533.1 | 3614.6 | 3736.8 | 3862.5 | 3893.9 | 4095.2 | 4333.8 | 4617.7 |
| 22.5° | 3506.4 | 3511.0 | 3515.7 | 3559.9 | 3623.9 | 3743.8 | 3896.2 | 3938.1 | 4193.0 | 4435.0 | 4721.3 |
| 25°   | 3601.8 | 3602.9 | 3607.6 | 3643.7 | 3672.8 | 3763.5 | 3952.1 | 4014.9 | 4345.4 | 4582.8 | 4851.6 |
| 27.5° | 3729.8 | 3746.1 | 3750.7 | 3774.0 | 3774.0 | 3812.4 | 4039.4 | 4130.1 | 4551.4 | 4795.8 | 5018.1 |
| 30°   | 3909.0 | 3914.8 | 3923.0 | 3948.6 | 3920.6 | 3904.4 | 4167.4 | 4283.7 | 4790.0 | 5053.0 | 5218.2 |
| 32.5° | 4066.1 | 4078.9 | 4123.1 | 4165.0 | 4115.0 | 4063.8 | 4355.9 | 4493.2 | 5019.2 | 5320.6 | 5431.2 |
| 35°   | 4199.9 | 4231.4 | 4316.3 | 4409.4 | 4374.5 | 4323.3 | 4606.1 | 4749.2 | 5207.7 | 5512.6 | 5619.7 |
| 37.5° | 4361.7 | 4386.1 | 4502.5 | 4653.8 | 4685.2 | 4660.8 | 4911.0 | 5013.4 | 5333.4 | 5561.5 | 5722.1 |
| 40°   | 4525.8 | 4563.0 | 4713.2 | 4922.6 | 5042.5 | 5060.0 | 5192.6 | 5261.3 | 5376.5 | 5466.1 | 5702.3 |
| 42.5° | 4693.4 | 4757.4 | 4963.4 | 5207.7 | 5420.7 | 5460.3 | 5430.0 | 5459.1 | 5362.5 | 5334.6 | 5610.4 |
| 45°   | 4898.2 | 4973.8 | 5206.6 | 5518.5 | 5798.9 | 5860.6 | 5662.8 | 5636.0 | 5360.2 | 5284.6 | 5553.4 |
| 47.5° | 5140.3 | 5215.9 | 5438.2 | 5801.3 | 6159.7 | 6205.1 | 5901.3 | 5852.5 | 5441.7 | 5361.4 | 5630.2 |
| 50°   | 5354.4 | 5406.7 | 5605.7 | 6011.9 | 6496.0 | 6522.8 | 6164.3 | 6105.0 | 5644.2 | 5574.3 | 5869.9 |
| 52.5° | 5136.8 | 5130.9 | 5340.4 | 5840.8 | 6670.6 | 6992.9 | 6569.3 | 6512.3 | 6035.2 | 5928.1 | 6241.2 |
| 55°   | 4358.2 | 4291.9 | 4479.2 | 4971.5 | 6183.0 | 7410.7 | 7295.5 | 7181.5 | 6556.5 | 6284.2 | 6589.1 |
| 57.5° | 3186.3 | 3167.7 | 3213.1 | 3675.1 | 4952.9 | 6763.7 | 7740.1 | 7729.6 | 7006.9 | 6610.1 | 6935.9 |
| 60°   | 2491.6 | 2463.6 | 2342.6 | 2355.4 | 3376.0 | 5283.4 | 6717.1 | 7025.5 | 7286.2 | 6805.6 | 7178.0 |
| 62.5° | 2212.3 | 2191.3 | 2128.5 | 1955.1 | 2010.9 | 3542.4 | 4923.8 | 5206.6 | 6366.8 | 6010.7 | 6165.5 |
| 65°   | 1831.7 | 1825.9 | 1878.3 | 1871.3 | 1685.1 | 1956.3 | 2779.0 | 3064.1 | 4003.3 | 4053.3 | 4003.3 |
| 67.5° | 1331.3 | 1320.8 | 1453.5 | 1715.4 | 1622.3 | 1476.8 | 1548.9 | 1647.9 | 2052.8 | 1843.4 | 1659.5 |
| 70°   | 865.8  | 850.7  | 927.5  | 1239.4 | 1452.4 | 1287.1 | 1116.0 | 1099.7 | 1128.8 | 701.7  | 758.8  |
| 72.5° | 580.7  | 563.3  | 562.1  | 682.0  | 877.5  | 867.0  | 864.7  | 856.5  | 764.6  | 553.9  | 614.5  |
| 75°   | 323.5  | 309.6  | 306.1  | 294.4  | 314.2  | 320.0  | 341.0  | 352.6  | 381.7  | 420.1  | 465.5  |
| 77.5° | 54.7   | 53.5   | 67.5   | 86.1   | 118.7  | 152.5  | 188.5  | 199.0  | 245.5  | 290.9  | 320.0  |
| 80°   | 30.3   | 31.4   | 40.7   | 50.0   | 66.3   | 90.8   | 116.4  | 123.4  | 151.3  | 175.7  | 199.0  |
| 82.5° | 16.3   | 16.3   | 20.9   | 26.8   | 36.1   | 47.7   | 62.8   | 68.7   | 87.3   | 102.4  | 118.7  |
| 85°   | 5.8    | 5.8    | 8.1    | 10.5   | 15.1   | 19.8   | 24.4   | 27.9   | 38.4   | 52.4   | 59.4   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 1.2    | 2.3    | 4.7    | 4.7    | 5.8    | 10.5   | 15.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P637095

CATALOG NUMBER: GWS-SA4C-727-U-SL2-W-GRSWH

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 | 4415.2 |
| 2.5°  | 4438.5 | 4407.1 | 4450.2 | 4469.9 | 4476.9 | 4481.6 | 4451.3 | 4430.4 | 4423.4 | 4401.3 | 4388.5 |
| 5°    | 4454.8 | 4433.9 | 4474.6 | 4474.6 | 4445.5 | 4415.2 | 4353.6 | 4310.5 | 4280.2 | 4244.2 | 4238.4 |
| 7.5°  | 4482.7 | 4467.6 | 4489.7 | 4444.3 | 4371.0 | 4289.6 | 4182.5 | 4098.7 | 4031.2 | 3987.0 | 3988.1 |
| 10°   | 4520.0 | 4501.4 | 4483.9 | 4382.7 | 4248.8 | 4098.7 | 3934.6 | 3812.4 | 3700.7 | 3649.5 | 3621.6 |
| 12.5° | 4544.4 | 4517.6 | 4444.3 | 4276.8 | 4080.1 | 3878.8 | 3647.2 | 3465.6 | 3303.9 | 3230.5 | 3224.7 |
| 15°   | 4574.7 | 4525.8 | 4379.2 | 4139.4 | 3866.0 | 3591.3 | 3293.4 | 3040.9 | 2822.1 | 2708.0 | 2702.2 |
| 17.5° | 4614.2 | 4533.9 | 4301.2 | 3982.3 | 3640.2 | 3235.2 | 2860.5 | 2542.8 | 2310.0 | 2221.6 | 2236.7 |
| 20°   | 4670.1 | 4543.3 | 4212.7 | 3807.8 | 3359.7 | 2830.2 | 2363.6 | 2071.5 | 1981.9 | 1976.0 | 1964.4 |
| 22.5° | 4732.9 | 4549.1 | 4115.0 | 3612.3 | 3019.9 | 2398.5 | 1952.8 | 1828.2 | 1827.1 | 1856.2 | 1863.2 |
| 25°   | 4803.9 | 4553.7 | 4004.4 | 3384.2 | 2652.2 | 1967.9 | 1727.0 | 1689.8 | 1718.8 | 1773.5 | 1780.5 |
| 27.5° | 4894.7 | 4563.0 | 3870.6 | 3134.0 | 2261.2 | 1700.2 | 1602.5 | 1593.2 | 1628.1 | 1679.3 | 1677.0 |
| 30°   | 5028.5 | 4596.8 | 3728.6 | 2846.5 | 1859.7 | 1573.4 | 1526.8 | 1528.0 | 1542.0 | 1566.4 | 1569.9 |
| 32.5° | 5164.7 | 4649.2 | 3590.1 | 2523.0 | 1629.2 | 1501.2 | 1480.3 | 1478.0 | 1478.0 | 1488.4 | 1490.8 |
| 35°   | 5293.9 | 4708.5 | 3440.0 | 2185.5 | 1517.5 | 1459.3 | 1445.4 | 1438.4 | 1434.9 | 1432.6 | 1429.1 |
| 37.5° | 5366.0 | 4737.6 | 3293.4 | 1852.7 | 1458.2 | 1431.4 | 1417.4 | 1408.1 | 1395.3 | 1386.0 | 1383.7 |
| 40°   | 5334.6 | 4703.8 | 3123.5 | 1603.6 | 1422.1 | 1404.6 | 1388.3 | 1375.5 | 1358.1 | 1349.9 | 1345.3 |
| 42.5° | 5229.9 | 4599.1 | 2938.4 | 1486.1 | 1393.0 | 1375.5 | 1355.8 | 1334.8 | 1323.2 | 1316.2 | 1315.0 |
| 45°   | 5119.3 | 4472.3 | 2715.0 | 1417.4 | 1365.1 | 1344.1 | 1320.8 | 1297.6 | 1284.8 | 1281.3 | 1280.1 |
| 47.5° | 5115.8 | 4409.4 | 2477.6 | 1362.7 | 1331.3 | 1310.4 | 1281.3 | 1258.0 | 1244.0 | 1239.4 | 1234.7 |
| 50°   | 5269.4 | 4473.4 | 2209.9 | 1315.0 | 1296.4 | 1274.3 | 1241.7 | 1216.1 | 1198.7 | 1192.8 | 1191.7 |
| 52.5° | 5588.3 | 4714.3 | 1970.2 | 1267.3 | 1249.9 | 1224.3 | 1197.5 | 1171.9 | 1150.9 | 1140.5 | 1139.3 |
| 55°   | 5932.8 | 5020.4 | 1821.3 | 1218.4 | 1195.2 | 1173.1 | 1148.6 | 1120.7 | 1097.4 | 1081.1 | 1078.8 |
| 57.5° | 6288.9 | 5354.4 | 1775.9 | 1156.8 | 1139.3 | 1124.2 | 1095.1 | 1064.8 | 1038.1 | 1022.9 | 1019.4 |
| 60°   | 6582.1 | 5641.8 | 1860.8 | 1091.6 | 1082.3 | 1062.5 | 1035.7 | 1006.6 | 988.0  | 976.4  | 974.1  |
| 62.5° | 5510.3 | 4593.3 | 1502.4 | 1020.6 | 1020.6 | 999.7  | 969.4  | 948.5  | 935.6  | 927.5  | 925.2  |
| 65°   | 3497.0 | 2844.2 | 1025.3 | 949.6  | 948.5  | 920.5  | 894.9  | 881.0  | 875.1  | 862.3  | 860.0  |
| 67.5° | 1523.3 | 1299.9 | 876.3  | 877.5  | 872.8  | 842.5  | 816.9  | 806.5  | 794.8  | 780.9  | 779.7  |
| 70°   | 790.2  | 805.3  | 784.4  | 797.2  | 789.0  | 752.9  | 728.5  | 712.2  | 687.8  | 673.8  | 675.0  |
| 72.5° | 637.7  | 654.0  | 677.3  | 697.1  | 679.6  | 650.5  | 612.1  | 592.3  | 560.9  | 545.8  | 547.0  |
| 75°   | 486.4  | 503.9  | 526.0  | 547.0  | 533.0  | 496.9  | 472.5  | 452.7  | 416.6  | 399.2  | 402.7  |
| 77.5° | 335.2  | 344.5  | 371.2  | 370.1  | 365.4  | 354.9  | 318.9  | 295.6  | 258.4  | 237.4  | 239.7  |
| 80°   | 208.3  | 214.1  | 226.9  | 232.7  | 230.4  | 216.5  | 187.4  | 169.9  | 147.8  | 135.0  | 136.2  |
| 82.5° | 125.7  | 129.2  | 140.8  | 142.0  | 140.8  | 130.3  | 108.2  | 95.4   | 81.5   | 74.5   | 74.5   |
| 85°   | 64.0   | 66.3   | 73.3   | 73.3   | 66.3   | 55.9   | 50.0   | 44.2   | 36.1   | 32.6   | 32.6   |
| 87.5° | 17.5   | 17.5   | 22.1   | 18.6   | 15.1   | 14.0   | 7.0    | 5.8    | 2.3    | 1.2    | 1.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 11.1          | 620    | 118034        | 1.5           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 16.9          | 625    | 111884        | 0.9           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 26.0          | 630    | 106119        | 0.6           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 38.2          | 635    | 99706         | 0.4           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 51.6          | 640    | 92142         | 0.2           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 65.1          | 645    | 84987         | 0.1           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 75.2          | 650    | 78016         | 0.1           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 82.9          | 655    | 71541         | 0.1           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 86.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.1           | 535    | 68520         | 85.4          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.2           | 540    | 73435         | 81.1          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.7           | 545    | 78677         | 75.4          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 2.3           | 550    | 83331         | 68.1          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 6.2           | 555    | 89120         | 60.9          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 13.0          | 560    | 94613         | 52.9          | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 22.2          | 565    | 99818         | 44.8          | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 32.0          | 570    | 106526        | 37.6          | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 36.7          | 575    | 111610        | 30.4          | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 30.4          | 580    | 117163        | 24.1          | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 19.7          | 585    | 122201        | 18.7          | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 13.2          | 590    | 125662        | 14.0          | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 10.0          | 595    | 127415        | 10.2          | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 7.7           | 600    | 129155        | 7.3           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 6.7           | 605    | 128057        | 5.0           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 6.9           | 610    | 126031        | 3.4           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 8.1           | 615    | 123059        | 2.3           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)