

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637102

Luminaire Tested: GWS-SA4C-727-U-SL4-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4C-727-U-SL4-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: (64) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12790.9 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 128.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637102
 CATALOG NUMBER: GWS-SA4C-727-U-SL4-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P637102
CATALOG NUMBER: GWS-SA4C-727-U-SL4-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P637102
 CATALOG NUMBER: GWS-SA4C-727-U-SL4-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1046.0 | 0.0 | 1046.0 |
| | % Fixture | 8.2 | 0.0 | 8.2 |
| Street Side | Lumens | 11744.9 | 0.0 | 11744.9 |
| | % Fixture | 91.8 | 0.0 | 91.8 |
| Total | Lumens | 12790.9 | 0.0 | 12790.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 183.4 | 1.4 |
| 10°-20° | 465.3 | 3.6 |
| 20°-30° | 778.7 | 6.1 |
| 30°-40° | 1223.0 | 9.6 |
| 40°-50° | 1934.6 | 15.1 |
| 50°-60° | 2822.0 | 22.1 |
| 60°-70° | 3498.3 | 27.4 |
| 70°-80° | 1769.9 | 13.8 |
| 80°-90° | 115.5 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 12790.9 | 100.0 |
| 0°-180° | 12790.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P637102
 CATALOG NUMBER: GWS-SA4C-727-U-SL4-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1093.4 | 8.5 | | | |
| FM (30°-60°) | 5424.5 | 42.4 | | | |
| FH (60°-80°) | 5119.1 | 40.0 | | | G3/7500 |
| FVH (80°-90°) | 107.9 | 0.8 | | | G2/225 |
| BL (0°-30°) | 334.0 | 2.6 | B1/500 | | |
| BM (30°-60°) | 555.2 | 4.3 | B1/1000 | | |
| BH (60°-80°) | 149.1 | 1.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 7.6 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G3
 Type IV Short





REPORT NUMBER: P637102

CATALOG NUMBER: GWS-SA4C-727-U-SL4-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 40° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 |
| 2.5° | 2333.4 | 2341.5 | 2340.4 | 2343.9 | 2335.7 | 2322.9 | 2320.6 | 2303.1 | 2271.7 | 2232.1 | 2187.9 |
| 5° | 2381.1 | 2390.4 | 2383.4 | 2379.9 | 2364.8 | 2350.8 | 2347.4 | 2328.7 | 2292.7 | 2239.1 | 2162.3 |
| 7.5° | 2421.8 | 2424.2 | 2419.5 | 2411.4 | 2389.3 | 2370.6 | 2357.8 | 2332.2 | 2289.2 | 2235.6 | 2147.2 |
| 10° | 2428.8 | 2427.7 | 2430.0 | 2431.2 | 2417.2 | 2400.9 | 2390.4 | 2355.5 | 2300.8 | 2243.8 | 2148.4 |
| 12.5° | 2420.7 | 2420.7 | 2435.8 | 2453.3 | 2453.3 | 2445.1 | 2434.6 | 2403.2 | 2339.2 | 2271.7 | 2171.6 |
| 15° | 2431.2 | 2434.6 | 2463.7 | 2496.3 | 2506.8 | 2498.7 | 2494.0 | 2461.4 | 2395.1 | 2320.6 | 2213.5 |
| 17.5° | 2468.4 | 2471.9 | 2518.4 | 2567.3 | 2580.1 | 2570.8 | 2561.5 | 2528.9 | 2457.9 | 2376.5 | 2261.2 |
| 20° | 2523.1 | 2532.4 | 2591.8 | 2654.6 | 2666.2 | 2654.6 | 2636.0 | 2590.6 | 2519.6 | 2437.0 | 2306.6 |
| 22.5° | 2623.2 | 2629.0 | 2693.0 | 2759.3 | 2765.2 | 2746.5 | 2718.6 | 2655.8 | 2581.3 | 2501.0 | 2357.8 |
| 25° | 2755.8 | 2764.0 | 2828.0 | 2892.0 | 2876.9 | 2849.0 | 2810.5 | 2739.6 | 2654.6 | 2576.6 | 2423.0 |
| 27.5° | 2914.1 | 2923.4 | 2986.3 | 3042.1 | 3002.6 | 2970.0 | 2926.9 | 2838.5 | 2752.4 | 2681.4 | 2506.8 |
| 30° | 3085.2 | 3093.3 | 3149.2 | 3199.2 | 3146.9 | 3108.5 | 3057.3 | 2966.5 | 2879.2 | 2825.7 | 2625.5 |
| 32.5° | 3250.5 | 3249.3 | 3302.8 | 3343.6 | 3290.0 | 3259.8 | 3213.2 | 3121.3 | 3051.4 | 3028.2 | 2802.4 |
| 35° | 3404.1 | 3404.1 | 3448.3 | 3489.0 | 3450.6 | 3434.3 | 3391.3 | 3318.0 | 3278.4 | 3306.3 | 3038.6 |
| 37.5° | 3558.9 | 3550.7 | 3592.6 | 3638.0 | 3634.5 | 3635.7 | 3611.2 | 3576.3 | 3578.6 | 3677.6 | 3363.3 |
| 40° | 3686.9 | 3683.4 | 3732.3 | 3791.6 | 3838.2 | 3875.4 | 3860.3 | 3873.1 | 3946.4 | 4131.4 | 3778.8 |
| 42.5° | 3789.3 | 3797.4 | 3860.3 | 3954.5 | 4072.1 | 4147.7 | 4158.2 | 4210.6 | 4399.1 | 4685.4 | 4247.8 |
| 45° | 3906.8 | 3908.0 | 3995.3 | 4139.6 | 4327.0 | 4446.8 | 4488.7 | 4623.7 | 4891.4 | 5260.3 | 4762.2 |
| 47.5° | 4051.1 | 4037.2 | 4134.9 | 4337.4 | 4608.6 | 4785.5 | 4860.0 | 5028.7 | 5443.0 | 5821.3 | 5181.2 |
| 50° | 4210.6 | 4185.0 | 4295.5 | 4571.4 | 4924.0 | 5145.1 | 5296.4 | 5543.1 | 5990.0 | 6282.1 | 5493.1 |
| 52.5° | 4395.6 | 4371.2 | 4496.9 | 4840.2 | 5302.2 | 5571.0 | 5765.4 | 6014.5 | 6459.0 | 6633.6 | 5679.3 |
| 55° | 4630.7 | 4606.3 | 4738.9 | 5162.6 | 5749.1 | 6098.2 | 6301.9 | 6511.4 | 6895.4 | 6893.1 | 5814.3 |
| 57.5° | 4891.4 | 4857.6 | 5041.5 | 5569.9 | 6306.6 | 6669.7 | 6876.8 | 6979.2 | 7227.1 | 7094.4 | 5905.1 |
| 60° | 5190.5 | 5160.2 | 5415.1 | 6055.2 | 6950.1 | 7286.5 | 7416.8 | 7374.9 | 7499.4 | 7213.2 | 5873.6 |
| 62.5° | 5460.5 | 5446.5 | 5763.1 | 6569.6 | 7563.5 | 7847.4 | 7883.5 | 7700.8 | 7699.6 | 7215.5 | 5661.8 |
| 65° | 5741.0 | 5767.7 | 6237.9 | 7161.9 | 8180.3 | 8371.1 | 8309.4 | 8024.3 | 7779.9 | 6930.4 | 5035.7 |
| 67.5° | 5845.7 | 5923.7 | 6551.0 | 7697.3 | 8666.7 | 8815.7 | 8707.5 | 8186.1 | 7445.9 | 5971.4 | 3834.7 |
| 70° | 5198.6 | 5345.3 | 6255.4 | 7727.5 | 8868.1 | 9010.0 | 8750.5 | 7750.8 | 6207.6 | 3955.7 | 2100.6 |
| 72.5° | 3953.4 | 4124.5 | 5212.6 | 6327.5 | 7975.4 | 8299.0 | 7855.6 | 6314.7 | 4001.1 | 1732.9 | 705.3 |
| 75° | 2212.4 | 2397.4 | 3882.4 | 4764.5 | 5354.6 | 5650.2 | 5487.3 | 4051.1 | 1772.4 | 452.7 | 210.6 |
| 77.5° | 748.3 | 810.0 | 1806.2 | 2947.9 | 3534.4 | 3269.1 | 2767.5 | 2012.2 | 651.7 | 172.2 | 111.7 |
| 80° | 443.4 | 466.7 | 672.7 | 1467.5 | 1859.7 | 1542.0 | 1217.3 | 743.7 | 331.7 | 91.9 | 78.0 |
| 82.5° | 132.7 | 157.1 | 371.2 | 544.7 | 728.5 | 453.9 | 384.0 | 424.8 | 172.2 | 50.0 | 65.2 |
| 85° | 0.0 | 0.0 | 79.1 | 168.7 | 190.9 | 74.5 | 74.5 | 240.9 | 31.4 | 20.9 | 47.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.2 | 5.8 | 3.5 | 4.7 | 10.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637102

CATALOG NUMBER: GWS-SA4C-727-U-SL4-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 | 2170.5 |
| 2.5° | 2156.5 | 2115.8 | 2068.0 | 2022.7 | 1979.6 | 1923.7 | 1897.0 | 1864.4 | 1836.5 | 1821.3 | 1829.5 |
| 5° | 2113.4 | 2049.4 | 1951.7 | 1852.7 | 1752.7 | 1658.4 | 1573.4 | 1516.4 | 1465.2 | 1438.4 | 1444.3 |
| 7.5° | 2076.2 | 1990.1 | 1837.6 | 1675.9 | 1515.3 | 1353.5 | 1222.0 | 1119.6 | 1040.4 | 1007.8 | 1002.0 |
| 10° | 2059.9 | 1951.7 | 1736.4 | 1503.6 | 1256.9 | 1039.3 | 853.1 | 740.2 | 659.9 | 620.3 | 627.3 |
| 12.5° | 2068.0 | 1931.9 | 1650.2 | 1334.9 | 1014.8 | 761.1 | 583.1 | 477.2 | 420.1 | 396.9 | 391.0 |
| 15° | 2091.3 | 1927.2 | 1573.4 | 1162.6 | 783.2 | 531.9 | 402.7 | 359.6 | 348.0 | 345.6 | 345.6 |
| 17.5° | 2118.1 | 1928.4 | 1494.3 | 988.1 | 594.7 | 394.5 | 344.5 | 336.3 | 332.8 | 330.5 | 331.7 |
| 20° | 2144.9 | 1928.4 | 1403.5 | 811.2 | 446.9 | 341.0 | 328.2 | 322.4 | 318.9 | 317.7 | 317.7 |
| 22.5° | 2177.4 | 1928.4 | 1302.3 | 647.1 | 358.4 | 323.5 | 313.1 | 309.6 | 306.1 | 304.9 | 303.7 |
| 25° | 2217.0 | 1929.6 | 1190.6 | 506.2 | 325.9 | 308.4 | 300.3 | 296.8 | 293.3 | 290.9 | 290.9 |
| 27.5° | 2274.0 | 1938.9 | 1067.2 | 394.5 | 307.2 | 294.4 | 287.5 | 284.0 | 280.5 | 277.0 | 277.0 |
| 30° | 2356.7 | 1962.1 | 928.7 | 325.9 | 289.8 | 279.3 | 272.3 | 270.0 | 266.5 | 263.0 | 261.9 |
| 32.5° | 2480.0 | 2002.9 | 785.6 | 292.1 | 273.5 | 263.0 | 254.9 | 252.5 | 249.1 | 245.6 | 244.4 |
| 35° | 2652.3 | 2077.4 | 645.9 | 271.2 | 252.5 | 242.1 | 237.4 | 236.2 | 231.6 | 228.1 | 228.1 |
| 37.5° | 2904.8 | 2198.4 | 512.1 | 250.2 | 235.1 | 226.9 | 221.1 | 218.8 | 214.1 | 210.6 | 209.5 |
| 40° | 3213.2 | 2355.5 | 398.0 | 233.9 | 218.8 | 210.6 | 204.8 | 201.3 | 195.5 | 190.9 | 188.5 |
| 42.5° | 3606.6 | 2547.5 | 314.2 | 216.5 | 203.7 | 195.5 | 190.9 | 183.9 | 175.7 | 168.7 | 167.6 |
| 45° | 4016.2 | 2745.4 | 259.5 | 200.2 | 189.7 | 182.7 | 176.9 | 167.6 | 155.9 | 147.8 | 145.5 |
| 47.5° | 4330.5 | 2868.7 | 226.9 | 182.7 | 174.6 | 168.7 | 161.8 | 150.1 | 136.2 | 126.9 | 124.5 |
| 50° | 4555.1 | 2887.4 | 202.5 | 166.4 | 161.8 | 155.9 | 145.5 | 131.5 | 116.4 | 107.1 | 104.7 |
| 52.5° | 4665.6 | 2803.6 | 182.7 | 151.3 | 147.8 | 142.0 | 129.2 | 114.1 | 97.8 | 88.4 | 86.1 |
| 55° | 4715.7 | 2645.3 | 164.1 | 138.5 | 133.8 | 126.9 | 112.9 | 96.6 | 80.3 | 72.2 | 69.8 |
| 57.5° | 4695.9 | 2411.4 | 147.8 | 125.7 | 119.9 | 111.7 | 96.6 | 79.1 | 66.3 | 58.2 | 57.0 |
| 60° | 4549.2 | 2083.2 | 131.5 | 112.9 | 105.9 | 96.6 | 81.5 | 65.2 | 53.5 | 47.7 | 46.6 |
| 62.5° | 4232.7 | 1675.9 | 115.2 | 97.8 | 93.1 | 83.8 | 69.8 | 53.5 | 44.2 | 40.7 | 39.6 |
| 65° | 3584.5 | 1184.7 | 98.9 | 82.6 | 80.3 | 71.0 | 58.2 | 44.2 | 38.4 | 36.1 | 34.9 |
| 67.5° | 2576.6 | 720.4 | 83.8 | 71.0 | 68.7 | 60.5 | 48.9 | 38.4 | 34.9 | 33.7 | 33.7 |
| 70° | 1295.3 | 341.0 | 66.3 | 58.2 | 58.2 | 50.0 | 41.9 | 34.9 | 33.7 | 32.6 | 32.6 |
| 72.5° | 439.9 | 145.5 | 50.0 | 45.4 | 47.7 | 43.1 | 36.1 | 32.6 | 32.6 | 32.6 | 32.6 |
| 75° | 150.1 | 76.8 | 34.9 | 32.6 | 34.9 | 34.9 | 31.4 | 31.4 | 32.6 | 32.6 | 32.6 |
| 77.5° | 97.8 | 51.2 | 24.4 | 22.1 | 26.8 | 26.8 | 26.8 | 29.1 | 31.4 | 31.4 | 31.4 |
| 80° | 80.3 | 27.9 | 16.3 | 15.1 | 19.8 | 19.8 | 22.1 | 26.8 | 29.1 | 29.1 | 29.1 |
| 82.5° | 68.7 | 17.5 | 9.3 | 10.5 | 14.0 | 15.1 | 18.6 | 22.1 | 25.6 | 26.8 | 26.8 |
| 85° | 46.6 | 9.3 | 7.0 | 8.1 | 9.3 | 11.6 | 15.1 | 18.6 | 20.9 | 23.3 | 23.3 |
| 87.5° | 12.8 | 3.5 | 4.7 | 5.8 | 5.8 | 8.1 | 11.6 | 14.0 | 16.3 | 17.5 | 17.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2
 Rf: 69.9
 Rg: 98.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)