

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637116

Luminaire Tested: GWS-SA4C-727-U-T2-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-19)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4C-727-U-T2-W
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS
Light Source: (64) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16106.5 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 128.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637116
 CATALOG NUMBER: GWS-SA4C-727-U-T2-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.3 fc
 Type II - Medium - N/A

REPORT NUMBER: P637116
CATALOG NUMBER: GWS-SA4C-727-U-T2-W

Luminous Intensity Polar Plot



— Vertical Plane Through 70-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P637116

CATALOG NUMBER: GWS-SA4C-727-U-T2-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2886.3 | 0.0 | 2886.3 |
| | % Fixture | 17.9 | 0.0 | 17.9 |
| Street Side | Lumens | 13220.2 | 0.0 | 13220.2 |
| | % Fixture | 82.1 | 0.0 | 82.1 |
| Total | Lumens | 16106.5 | 0.0 | 16106.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 190.9 | 1.2 |
| 10°-20° | 621.0 | 3.9 |
| 20°-30° | 1100.2 | 6.8 |
| 30°-40° | 1655.8 | 10.3 |
| 40°-50° | 2505.0 | 15.6 |
| 50°-60° | 3588.6 | 22.3 |
| 60°-70° | 3966.8 | 24.6 |
| 70°-80° | 2238.6 | 13.9 |
| 80°-90° | 239.4 | 1.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 16106.5 | 100.0 |
| 0°-180° | 16106.5 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P637116

CATALOG NUMBER: GWS-SA4C-727-U-T2-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1250.4 | 7.8 | | | |
| FM (30°-60°) | 6470.0 | 40.2 | | | |
| FH (60°-80°) | 5330.6 | 33.1 | | | G3/7500 |
| FVH (80°-90°) | 169.3 | 1.1 | | | G2/225 |
| BL (0°-30°) | 661.8 | 4.1 | B2/1000 | | |
| BM (30°-60°) | 1279.5 | 7.9 | B2/2500 | | |
| BH (60°-80°) | 874.8 | 5.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 70.2 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3
 Type II Medium





REPORT NUMBER: P637116
 CATALOG NUMBER: GWS-SA4C-727-U-T2-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 70° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|
| 0° | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 |
| 2.5° | 2080.9 | 2077.4 | 2079.7 | 2077.4 | 2064.6 | 2033.1 | 2007.5 | 1974.9 | 1952.8 | 1940.0 | 1909.8 |
| 5° | 2325.2 | 2321.8 | 2313.6 | 2302.0 | 2278.7 | 2235.6 | 2171.6 | 2100.6 | 2057.6 | 2025.0 | 1961.0 |
| 7.5° | 2501.0 | 2501.0 | 2499.8 | 2485.8 | 2469.6 | 2424.2 | 2348.5 | 2255.4 | 2192.6 | 2136.7 | 2032.0 |
| 10° | 2590.6 | 2596.4 | 2604.6 | 2624.3 | 2620.8 | 2596.4 | 2525.4 | 2425.3 | 2346.2 | 2281.0 | 2125.1 |
| 12.5° | 2639.5 | 2643.0 | 2656.9 | 2697.7 | 2739.6 | 2745.4 | 2703.5 | 2598.7 | 2512.6 | 2425.3 | 2228.7 |
| 15° | 2702.3 | 2703.5 | 2722.1 | 2771.0 | 2832.7 | 2894.3 | 2883.9 | 2779.1 | 2690.7 | 2594.1 | 2343.9 |
| 17.5° | 2751.2 | 2759.3 | 2793.1 | 2850.1 | 2926.9 | 3011.9 | 3063.1 | 2997.9 | 2888.5 | 2778.0 | 2469.6 |
| 20° | 2768.6 | 2774.5 | 2818.7 | 2906.0 | 3010.7 | 3130.6 | 3244.6 | 3227.2 | 3116.6 | 2986.3 | 2611.5 |
| 22.5° | 2831.5 | 2831.5 | 2864.1 | 2937.4 | 3060.8 | 3235.3 | 3420.4 | 3465.8 | 3368.0 | 3215.5 | 2764.0 |
| 25° | 2970.0 | 2965.3 | 2980.5 | 3010.7 | 3103.8 | 3319.1 | 3593.8 | 3729.9 | 3620.5 | 3449.5 | 2916.4 |
| 27.5° | 3159.7 | 3157.4 | 3156.2 | 3160.8 | 3192.3 | 3392.4 | 3740.4 | 3976.7 | 3867.3 | 3674.1 | 3052.6 |
| 30° | 3365.7 | 3358.7 | 3373.8 | 3359.9 | 3352.9 | 3479.7 | 3864.9 | 4197.8 | 4112.8 | 3896.4 | 3165.5 |
| 32.5° | 3646.1 | 3633.3 | 3629.9 | 3584.5 | 3556.5 | 3615.9 | 3965.0 | 4449.2 | 4381.7 | 4136.1 | 3292.4 |
| 35° | 4016.2 | 4004.6 | 3945.2 | 3873.1 | 3790.5 | 3818.4 | 4089.5 | 4694.7 | 4699.4 | 4436.4 | 3458.8 |
| 37.5° | 4389.8 | 4392.1 | 4345.6 | 4175.7 | 4090.7 | 4074.4 | 4279.2 | 4993.8 | 5093.9 | 4794.8 | 3674.1 |
| 40° | 4700.5 | 4714.5 | 4714.5 | 4535.3 | 4408.4 | 4393.3 | 4545.8 | 5348.8 | 5547.8 | 5234.7 | 3946.4 |
| 42.5° | 4936.8 | 4949.6 | 4990.3 | 4861.1 | 4727.3 | 4779.7 | 4869.3 | 5704.9 | 6062.2 | 5778.2 | 4290.9 |
| 45° | 5196.3 | 5206.8 | 5228.9 | 5154.4 | 5076.4 | 5216.1 | 5235.9 | 6130.8 | 6651.0 | 6388.0 | 4691.2 |
| 47.5° | 5540.8 | 5531.5 | 5533.8 | 5479.1 | 5418.6 | 5644.4 | 5639.7 | 6489.3 | 7220.1 | 7056.0 | 5125.3 |
| 50° | 5969.1 | 5986.5 | 5970.2 | 5862.0 | 5791.0 | 5997.0 | 6023.8 | 6886.1 | 7720.6 | 7717.1 | 5562.9 |
| 52.5° | 6381.0 | 6388.0 | 6474.1 | 6478.8 | 6333.3 | 6290.3 | 6360.1 | 7286.5 | 8143.0 | 8322.2 | 5983.0 |
| 55° | 6402.0 | 6428.8 | 6687.1 | 6873.3 | 7108.4 | 6762.8 | 6699.9 | 7668.2 | 8551.5 | 8914.6 | 6419.4 |
| 57.5° | 5956.3 | 5999.3 | 6438.1 | 6839.6 | 7493.6 | 7573.9 | 7281.8 | 8161.6 | 8960.0 | 9497.7 | 6924.5 |
| 60° | 5004.3 | 5093.9 | 5689.8 | 6304.2 | 7320.2 | 8157.0 | 8472.4 | 8832.0 | 9496.5 | 10093.5 | 7537.8 |
| 62.5° | 3195.8 | 3230.7 | 4066.3 | 5095.1 | 6539.3 | 8100.0 | 9768.8 | 10013.2 | 10313.5 | 10869.8 | 8482.8 |
| 65° | 1600.2 | 1711.9 | 2201.9 | 3041.0 | 4715.7 | 7137.5 | 10424.0 | 12176.7 | 11808.9 | 12198.8 | 10014.4 |
| 67.5° | 1085.8 | 1121.9 | 1369.8 | 1827.1 | 2765.2 | 5056.7 | 10017.9 | 13999.2 | 13891.0 | 13955.0 | 11647.2 |
| 70° | 800.7 | 824.0 | 1019.5 | 1294.1 | 1672.4 | 2871.1 | 7975.4 | 13861.9 | 14600.9 | 14577.6 | 11476.1 |
| 72.5° | 584.2 | 595.9 | 743.7 | 988.1 | 1239.4 | 1485.0 | 4870.4 | 11198.0 | 12745.8 | 13417.3 | 10036.5 |
| 75° | 424.8 | 438.7 | 516.7 | 739.0 | 963.6 | 926.4 | 2404.4 | 8088.3 | 9719.9 | 11011.7 | 8176.8 |
| 77.5° | 316.5 | 334.0 | 370.1 | 463.2 | 675.0 | 663.4 | 1039.3 | 5252.2 | 6286.8 | 7192.2 | 4967.0 |
| 80° | 228.1 | 231.6 | 252.5 | 296.8 | 428.3 | 388.7 | 494.6 | 2738.4 | 3139.9 | 3440.2 | 1947.0 |
| 82.5° | 138.5 | 142.0 | 168.7 | 182.7 | 265.3 | 244.4 | 257.2 | 886.8 | 1270.9 | 1348.8 | 727.4 |
| 85° | 40.7 | 43.1 | 76.8 | 83.8 | 110.6 | 104.7 | 103.6 | 360.8 | 430.6 | 550.5 | 286.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.2 | 7.0 | 12.8 | 64.0 | 96.6 | 133.8 | 69.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637116
 CATALOG NUMBER: GWS-SA4C-727-U-T2-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 | 1878.4 |
| 2.5° | 1898.1 | 1871.4 | 1857.4 | 1833.0 | 1815.5 | 1798.1 | 1780.6 | 1764.3 | 1757.3 | 1746.8 | 1749.2 |
| 5° | 1931.9 | 1890.0 | 1848.1 | 1800.4 | 1759.6 | 1725.9 | 1695.6 | 1668.9 | 1657.2 | 1646.8 | 1651.4 |
| 7.5° | 1983.1 | 1920.2 | 1839.9 | 1752.7 | 1688.7 | 1642.1 | 1610.7 | 1592.1 | 1586.2 | 1578.1 | 1578.1 |
| 10° | 2048.3 | 1954.0 | 1813.2 | 1688.7 | 1611.8 | 1574.6 | 1560.6 | 1559.5 | 1565.3 | 1566.5 | 1564.1 |
| 12.5° | 2120.4 | 1986.6 | 1773.6 | 1613.0 | 1547.8 | 1536.2 | 1546.7 | 1566.5 | 1586.2 | 1596.7 | 1594.4 |
| 15° | 2194.9 | 2007.5 | 1706.1 | 1540.9 | 1501.3 | 1516.4 | 1550.2 | 1589.7 | 1628.1 | 1647.9 | 1646.8 |
| 17.5° | 2264.7 | 2012.2 | 1618.8 | 1471.0 | 1460.6 | 1499.0 | 1557.1 | 1618.8 | 1671.2 | 1699.1 | 1700.3 |
| 20° | 2342.7 | 2004.0 | 1529.2 | 1408.2 | 1419.8 | 1482.7 | 1559.5 | 1634.0 | 1695.6 | 1723.6 | 1730.6 |
| 22.5° | 2413.7 | 1976.1 | 1441.9 | 1348.8 | 1384.9 | 1462.9 | 1540.9 | 1610.7 | 1665.4 | 1692.1 | 1701.5 |
| 25° | 2477.7 | 1922.6 | 1346.5 | 1298.8 | 1358.1 | 1434.9 | 1494.3 | 1543.2 | 1581.6 | 1597.9 | 1610.7 |
| 27.5° | 2512.6 | 1842.3 | 1274.3 | 1259.2 | 1332.5 | 1395.4 | 1428.0 | 1443.1 | 1455.9 | 1451.2 | 1460.6 |
| 30° | 2519.6 | 1742.2 | 1211.5 | 1227.8 | 1294.1 | 1340.7 | 1347.7 | 1332.5 | 1310.4 | 1274.3 | 1282.5 |
| 32.5° | 2512.6 | 1627.0 | 1159.1 | 1194.0 | 1251.1 | 1279.0 | 1269.7 | 1230.1 | 1176.6 | 1120.7 | 1124.2 |
| 35° | 2514.9 | 1510.6 | 1116.1 | 1156.8 | 1201.0 | 1216.2 | 1192.9 | 1138.2 | 1081.2 | 1030.0 | 1027.6 |
| 37.5° | 2540.5 | 1412.8 | 1080.0 | 1120.7 | 1152.1 | 1154.5 | 1128.9 | 1071.8 | 1042.8 | 1004.3 | 999.7 |
| 40° | 2611.5 | 1340.7 | 1047.4 | 1084.6 | 1104.4 | 1103.3 | 1074.2 | 1033.4 | 1053.2 | 1040.4 | 1036.9 |
| 42.5° | 2727.9 | 1296.5 | 1020.6 | 1046.2 | 1060.2 | 1062.5 | 1039.3 | 1013.7 | 1056.7 | 1040.4 | 1034.6 |
| 45° | 2915.3 | 1294.1 | 1002.0 | 1007.8 | 1030.0 | 1046.2 | 1030.0 | 1000.9 | 1017.1 | 938.0 | 922.9 |
| 47.5° | 3137.6 | 1333.7 | 988.1 | 974.1 | 1012.5 | 1041.6 | 1016.0 | 969.4 | 935.7 | 863.5 | 853.1 |
| 50° | 3405.2 | 1414.0 | 975.3 | 938.0 | 986.9 | 1024.1 | 998.5 | 934.5 | 883.3 | 844.9 | 839.1 |
| 52.5° | 3723.0 | 1519.9 | 959.0 | 897.3 | 948.5 | 1014.8 | 998.5 | 931.0 | 863.5 | 828.6 | 822.8 |
| 55° | 4055.8 | 1642.1 | 940.3 | 848.4 | 905.4 | 1017.1 | 1006.7 | 906.6 | 848.4 | 829.8 | 825.1 |
| 57.5° | 4468.9 | 1788.7 | 906.6 | 791.4 | 867.0 | 996.2 | 974.1 | 892.6 | 837.9 | 822.8 | 818.1 |
| 60° | 5005.4 | 2006.4 | 842.6 | 733.2 | 822.8 | 959.0 | 945.0 | 869.3 | 810.0 | 797.2 | 793.7 |
| 62.5° | 5855.0 | 2375.3 | 764.6 | 677.3 | 770.4 | 881.0 | 901.9 | 825.1 | 775.1 | 773.9 | 772.8 |
| 65° | 7239.9 | 2818.7 | 672.7 | 627.3 | 715.7 | 817.0 | 844.9 | 779.7 | 739.0 | 751.8 | 750.6 |
| 67.5° | 8210.5 | 2857.1 | 597.0 | 574.9 | 651.7 | 747.2 | 787.9 | 733.2 | 689.0 | 713.4 | 712.2 |
| 70° | 7520.4 | 2228.7 | 531.9 | 520.2 | 583.1 | 671.5 | 726.2 | 675.0 | 630.8 | 654.0 | 649.4 |
| 72.5° | 6342.6 | 1708.4 | 470.2 | 463.2 | 513.2 | 592.4 | 647.1 | 616.8 | 570.3 | 570.3 | 559.8 |
| 75° | 5097.4 | 1409.3 | 405.0 | 401.5 | 435.3 | 512.1 | 573.7 | 522.5 | 479.5 | 477.2 | 470.2 |
| 77.5° | 2923.4 | 924.0 | 339.8 | 337.5 | 348.0 | 428.3 | 445.7 | 435.3 | 402.7 | 387.5 | 382.9 |
| 80° | 1165.0 | 480.6 | 267.7 | 252.5 | 263.0 | 314.2 | 351.5 | 334.0 | 306.1 | 287.5 | 277.0 |
| 82.5° | 451.5 | 240.9 | 188.5 | 165.3 | 180.4 | 226.9 | 254.9 | 249.1 | 230.4 | 188.5 | 176.9 |
| 85° | 183.9 | 117.5 | 112.9 | 95.4 | 104.7 | 122.2 | 146.6 | 126.9 | 104.7 | 74.5 | 71.0 |
| 87.5° | 48.9 | 43.1 | 41.9 | 25.6 | 19.8 | 5.8 | 1.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)