

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P632677

Luminaire Tested: GWS-SA2D-727-U-T4W-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P632677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2D-727-U-T4W-W
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9681.1 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 82.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P632677
 CATALOG NUMBER: GWS-SA2D-727-U-T4W-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12.1 fc
 Type III - Short - N/A

REPORT NUMBER: P632677
CATALOG NUMBER: GWS-SA2D-727-U-T4W-W

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P632677

CATALOG NUMBER: GWS-SA2D-727-U-T4W-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 2206.4 | 0.0 | 2206.4 |
| | % Fixture | 22.8 | 0.0 | 22.8 |
| Street Side | Lumens | 7474.7 | 0.0 | 7474.7 |
| | % Fixture | 77.2 | 0.0 | 77.2 |
| Total | Lumens | 9681.1 | 0.0 | 9681.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 98.1 | 1.0 |
| 10°-20° | 326.8 | 3.4 |
| 20°-30° | 555.4 | 5.7 |
| 30°-40° | 813.6 | 8.4 |
| 40°-50° | 1239.7 | 12.8 |
| 50°-60° | 2218.1 | 22.9 |
| 60°-70° | 2959.8 | 30.6 |
| 70°-80° | 1338.5 | 13.8 |
| 80°-90° | 131.1 | 1.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 9681.1 | 100.0 |
| 0°-180° | 9681.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P632677


CATALOG NUMBER: GWS-SA2D-727-U-T4W-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 528.0 | 5.5 | | | |
| FM (30°-60°) | 3214.2 | 33.2 | | | |
| FH (60°-80°) | 3654.5 | 37.7 | | | G2/5000 |
| FVH (80°-90°) | 78.0 | 0.8 | | | G1/100 |
| BL (0°-30°) | 452.3 | 4.7 | B1/500 | | |
| BM (30°-60°) | 1057.2 | 10.9 | B2/2500 | | |
| BH (60°-80°) | 643.8 | 6.6 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 53.1 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P632677
 CATALOG NUMBER: GWS-SA2D-727-U-T4W-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 |
| 2.5° | 1023.4 | 1026.9 | 1026.2 | 1020.6 | 1017.1 | 1010.8 | 1011.5 | 1001.7 | 987.0 | 977.2 | 966.0 |
| 5° | 1113.7 | 1119.3 | 1112.3 | 1103.2 | 1089.2 | 1068.9 | 1066.8 | 1044.4 | 1016.4 | 996.8 | 976.5 |
| 7.5° | 1192.1 | 1195.6 | 1187.2 | 1171.8 | 1151.5 | 1124.2 | 1119.3 | 1092.7 | 1057.7 | 1026.9 | 997.5 |
| 10° | 1253.0 | 1257.2 | 1246.0 | 1225.7 | 1199.1 | 1171.8 | 1168.3 | 1141.0 | 1103.9 | 1067.5 | 1030.4 |
| 12.5° | 1304.8 | 1306.2 | 1294.3 | 1267.0 | 1238.3 | 1210.3 | 1206.8 | 1181.6 | 1147.3 | 1110.2 | 1069.6 |
| 15° | 1334.9 | 1335.6 | 1320.9 | 1290.8 | 1263.5 | 1239.0 | 1236.9 | 1215.2 | 1183.7 | 1148.7 | 1105.3 |
| 17.5° | 1332.8 | 1334.2 | 1323.7 | 1297.1 | 1273.3 | 1258.6 | 1256.5 | 1242.5 | 1218.0 | 1186.5 | 1143.1 |
| 20° | 1306.9 | 1308.3 | 1301.3 | 1283.8 | 1271.2 | 1267.0 | 1267.7 | 1263.5 | 1248.8 | 1222.9 | 1178.8 |
| 22.5° | 1286.6 | 1288.7 | 1282.4 | 1269.8 | 1268.4 | 1278.2 | 1280.3 | 1282.4 | 1275.4 | 1252.3 | 1209.6 |
| 25° | 1296.4 | 1299.9 | 1290.1 | 1272.6 | 1275.4 | 1297.1 | 1301.3 | 1308.3 | 1302.7 | 1283.1 | 1246.0 |
| 27.5° | 1364.3 | 1366.4 | 1341.2 | 1305.5 | 1297.1 | 1320.2 | 1326.5 | 1337.7 | 1333.5 | 1315.3 | 1286.6 |
| 30° | 1521.8 | 1520.4 | 1466.5 | 1379.0 | 1344.0 | 1353.1 | 1358.0 | 1374.1 | 1375.5 | 1363.6 | 1336.3 |
| 32.5° | 1743.7 | 1736.7 | 1653.4 | 1514.1 | 1412.6 | 1390.2 | 1395.8 | 1417.5 | 1433.6 | 1421.0 | 1383.9 |
| 35° | 1978.2 | 1971.9 | 1880.2 | 1717.1 | 1539.3 | 1461.6 | 1455.3 | 1472.1 | 1496.6 | 1461.6 | 1408.4 |
| 37.5° | 2201.5 | 2191.7 | 2097.9 | 1896.3 | 1695.4 | 1586.9 | 1577.8 | 1561.0 | 1546.3 | 1479.1 | 1438.5 |
| 40° | 2449.3 | 2438.1 | 2356.2 | 2128.0 | 1867.6 | 1682.8 | 1659.7 | 1593.2 | 1579.9 | 1537.2 | 1516.9 |
| 42.5° | 2713.9 | 2713.9 | 2646.0 | 2421.3 | 2075.5 | 1820.0 | 1789.9 | 1689.8 | 1703.8 | 1675.8 | 1652.0 |
| 45° | 2978.5 | 2986.2 | 2932.3 | 2716.7 | 2353.4 | 2079.0 | 2030.7 | 1888.6 | 1922.2 | 1909.6 | 1897.7 |
| 47.5° | 3203.9 | 3218.6 | 3208.1 | 3018.4 | 2693.6 | 2394.0 | 2320.5 | 2172.8 | 2244.9 | 2275.0 | 2308.6 |
| 50° | 3446.8 | 3462.9 | 3452.4 | 3377.5 | 3091.9 | 2775.5 | 2709.7 | 2557.1 | 2681.0 | 2771.3 | 2881.2 |
| 52.5° | 3807.3 | 3830.4 | 3742.9 | 3714.2 | 3575.6 | 3208.8 | 3150.0 | 2976.4 | 3201.1 | 3350.9 | 3595.9 |
| 55° | 4111.8 | 4111.1 | 4080.3 | 4146.1 | 4095.0 | 3738.7 | 3673.6 | 3516.1 | 3803.1 | 3962.0 | 4320.4 |
| 57.5° | 4253.2 | 4270.0 | 4375.7 | 4561.9 | 4664.1 | 4386.2 | 4323.9 | 4162.9 | 4449.2 | 4531.8 | 4918.9 |
| 60° | 4326.0 | 4347.0 | 4551.4 | 4919.6 | 5194.7 | 5093.2 | 5068.7 | 4863.6 | 5024.6 | 5014.8 | 5423.6 |
| 62.5° | 4223.8 | 4265.8 | 4594.1 | 5083.4 | 5573.4 | 5803.7 | 5796.0 | 5485.9 | 5513.9 | 5418.0 | 5736.5 |
| 65° | 3754.8 | 3800.3 | 4315.5 | 5001.5 | 5789.7 | 6344.1 | 6346.2 | 6049.4 | 5889.8 | 5614.0 | 5684.0 |
| 67.5° | 2685.2 | 2750.3 | 3387.3 | 4475.1 | 5713.4 | 6636.0 | 6660.5 | 6304.9 | 5978.0 | 5440.4 | 5132.4 |
| 70° | 1463.7 | 1511.3 | 2010.4 | 3252.9 | 5026.0 | 6566.0 | 6611.5 | 6181.7 | 5588.8 | 4706.1 | 3950.8 |
| 72.5° | 665.0 | 680.4 | 935.2 | 1785.0 | 3433.5 | 5651.8 | 5842.2 | 5516.7 | 4589.9 | 3476.2 | 2512.3 |
| 75° | 304.5 | 311.5 | 407.4 | 854.0 | 1794.1 | 3782.1 | 3915.8 | 4109.0 | 3194.1 | 2195.2 | 1309.7 |
| 77.5° | 191.1 | 193.2 | 231.7 | 390.6 | 894.6 | 1887.9 | 2028.6 | 2446.5 | 1870.4 | 1086.4 | 547.4 |
| 80° | 112.7 | 114.8 | 144.2 | 211.4 | 420.0 | 863.8 | 997.5 | 967.4 | 879.2 | 469.0 | 249.2 |
| 82.5° | 56.7 | 58.8 | 83.3 | 120.4 | 228.9 | 343.7 | 404.6 | 406.7 | 327.6 | 254.1 | 140.7 |
| 85° | 20.3 | 21.0 | 27.3 | 47.6 | 97.3 | 113.4 | 126.7 | 154.7 | 160.3 | 147.7 | 67.9 |
| 87.5° | 0.0 | 0.0 | 0.7 | 1.4 | 2.8 | 11.2 | 11.9 | 22.4 | 46.9 | 52.5 | 27.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P632677
 CATALOG NUMBER: GWS-SA2D-727-U-T4W-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 | 959.7 |
| 2.5° | 962.5 | 952.0 | 948.5 | 945.0 | 939.4 | 937.3 | 933.1 | 928.9 | 928.9 | 924.7 | 922.6 |
| 5° | 967.4 | 953.4 | 944.3 | 940.1 | 936.6 | 938.7 | 938.7 | 940.1 | 945.0 | 942.2 | 943.6 |
| 7.5° | 984.9 | 968.8 | 956.2 | 952.7 | 952.7 | 961.1 | 966.7 | 973.7 | 982.8 | 984.2 | 984.2 |
| 10° | 1015.7 | 996.8 | 983.5 | 981.4 | 984.9 | 996.8 | 1005.2 | 1013.6 | 1024.8 | 1025.5 | 1026.9 |
| 12.5° | 1049.3 | 1030.4 | 1017.1 | 1019.9 | 1023.4 | 1038.8 | 1047.9 | 1054.9 | 1066.1 | 1066.1 | 1065.4 |
| 15° | 1084.3 | 1063.3 | 1052.1 | 1057.7 | 1068.2 | 1085.7 | 1087.1 | 1087.8 | 1093.4 | 1092.0 | 1091.3 |
| 17.5° | 1120.7 | 1098.3 | 1089.9 | 1098.3 | 1109.5 | 1117.9 | 1110.9 | 1101.1 | 1099.0 | 1096.2 | 1094.8 |
| 20° | 1156.4 | 1133.3 | 1129.8 | 1136.1 | 1139.6 | 1132.6 | 1110.9 | 1092.7 | 1084.3 | 1080.1 | 1078.7 |
| 22.5° | 1187.2 | 1167.6 | 1165.5 | 1165.5 | 1148.0 | 1123.5 | 1091.3 | 1066.8 | 1055.6 | 1050.0 | 1048.6 |
| 25° | 1223.6 | 1205.4 | 1201.9 | 1183.0 | 1138.2 | 1093.4 | 1050.0 | 1027.6 | 1018.5 | 1015.7 | 1016.4 |
| 27.5° | 1266.3 | 1253.7 | 1242.5 | 1188.6 | 1110.2 | 1040.2 | 991.2 | 981.4 | 977.9 | 981.4 | 983.5 |
| 30° | 1318.8 | 1306.2 | 1281.0 | 1181.6 | 1065.4 | 970.9 | 924.0 | 923.3 | 933.8 | 942.9 | 944.3 |
| 32.5° | 1361.5 | 1355.9 | 1314.6 | 1159.2 | 1002.4 | 894.6 | 854.7 | 857.5 | 876.4 | 889.0 | 891.1 |
| 35° | 1395.1 | 1404.2 | 1342.6 | 1122.1 | 927.5 | 822.5 | 791.0 | 792.4 | 802.9 | 820.4 | 821.1 |
| 37.5° | 1442.7 | 1473.5 | 1367.8 | 1065.4 | 841.4 | 760.2 | 731.5 | 721.0 | 719.6 | 724.5 | 725.9 |
| 40° | 1538.6 | 1584.8 | 1386.0 | 982.8 | 758.1 | 704.2 | 672.0 | 651.7 | 634.2 | 620.9 | 616.7 |
| 42.5° | 1683.5 | 1736.7 | 1396.5 | 882.7 | 683.9 | 648.9 | 612.5 | 586.6 | 555.8 | 527.8 | 518.0 |
| 45° | 1949.5 | 1967.0 | 1396.5 | 776.3 | 618.1 | 597.1 | 560.7 | 529.9 | 490.7 | 457.8 | 450.8 |
| 47.5° | 2375.1 | 2319.1 | 1397.9 | 673.4 | 560.0 | 551.6 | 520.1 | 485.1 | 441.7 | 414.4 | 410.2 |
| 50° | 3016.3 | 2819.6 | 1426.6 | 588.0 | 511.7 | 513.1 | 490.0 | 451.5 | 412.3 | 392.0 | 388.5 |
| 52.5° | 3742.9 | 3436.3 | 1503.6 | 525.0 | 471.1 | 481.6 | 469.0 | 431.9 | 396.9 | 379.4 | 375.9 |
| 55° | 4426.1 | 4003.3 | 1569.4 | 480.2 | 436.8 | 455.0 | 454.3 | 420.0 | 388.5 | 371.0 | 368.9 |
| 57.5° | 5007.1 | 4391.8 | 1559.6 | 443.8 | 407.4 | 430.5 | 441.0 | 412.3 | 382.9 | 368.2 | 366.1 |
| 60° | 5368.3 | 4597.6 | 1420.3 | 410.2 | 385.0 | 413.0 | 433.3 | 410.2 | 385.7 | 382.2 | 382.9 |
| 62.5° | 5525.1 | 4559.8 | 1152.9 | 385.0 | 370.3 | 404.6 | 441.7 | 424.9 | 411.6 | 420.0 | 424.9 |
| 65° | 5281.5 | 4235.0 | 848.4 | 366.1 | 356.3 | 406.7 | 461.3 | 448.0 | 411.6 | 417.2 | 419.3 |
| 67.5° | 4605.3 | 3605.0 | 613.2 | 347.2 | 338.8 | 413.0 | 489.3 | 444.5 | 387.8 | 387.8 | 383.6 |
| 70° | 3318.7 | 2592.8 | 445.2 | 328.3 | 321.3 | 403.9 | 490.7 | 420.7 | 360.5 | 358.4 | 347.9 |
| 72.5° | 1997.1 | 1529.5 | 347.2 | 307.3 | 294.7 | 358.4 | 459.9 | 392.7 | 333.9 | 316.4 | 303.8 |
| 75° | 1037.4 | 766.5 | 291.2 | 284.2 | 252.7 | 303.8 | 420.7 | 349.3 | 285.6 | 270.2 | 263.2 |
| 77.5° | 444.5 | 358.4 | 249.9 | 253.4 | 210.0 | 255.5 | 339.5 | 302.4 | 253.4 | 233.8 | 227.5 |
| 80° | 219.1 | 203.7 | 197.4 | 203.0 | 168.0 | 197.4 | 292.6 | 264.6 | 214.9 | 192.5 | 183.4 |
| 82.5° | 125.3 | 119.0 | 142.1 | 144.2 | 119.7 | 165.2 | 247.1 | 224.0 | 177.8 | 153.3 | 138.6 |
| 85° | 58.1 | 62.3 | 86.1 | 86.8 | 74.2 | 113.4 | 161.7 | 126.0 | 94.5 | 78.4 | 74.9 |
| 87.5° | 23.1 | 27.3 | 37.8 | 37.1 | 21.7 | 21.0 | 14.0 | 7.7 | 6.3 | 5.6 | 4.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)